
# **SEARAY**<sup>M</sup>

## HIGH-DENSITY OPEN-PIN-FIELD ARRAYS


(1.27 mm) .050" PITCH



• 7 mm to 40 mm stack heights


integrity performance.

- Variety of designs and options: Right-Angle, Guide Posts, 85  $\Omega$  Elevated Risers, 85  $\Omega$  Tuned, Press-Fit and Press-Fit Right-Angle, Guide Post Field Termination Kits
- Cable mates (SEAC Series) and Jack Screw Standoffs (JSO Series) also available
- Standards: VITA 47, VITA 57.1 FMC, VITA 57.4 FMC+, VITA 74 VNX. PISMO™ 2
- Supports high-speed protocols such as Ethernet, PCI Express<sup>®</sup>, Fibre Channel & InfiniBand™
- Severe Environment Testing qualified (SEAM/SEAF); aligns with MIL-DTL-55302. Visit samtec.com/set



(1.12 mm) .044" Nominal Wipe

#### **MAXIMUM GROUNDING & ROUTING FLEXIBILITY**



Differential Pair

Single-Ended

| Power

SERIES	INSULATOR MATERIAL	CONTACT MATERIAL	PLATING	OPERATING TEMP RANGE	CURRENT RATING	VOLTAGE RATING	LEAD-FREE SOLDERABLE
SEAM/SEAF	Black LCP	Copper Alloy	Au or Sn over 50 μ" (1.27 μm) Ni	-55 °C to +125 °C	2.7 A (10 pins powered)	240 VAC	Yes
SEAM-RA/SEAF-RA	Black LCP	Copper Alloy	Au or Sn over 50 $\mu$ " (1.27 $\mu$ m) Ni	-55 °C to +125 °C	1.9 A (10 pins powered)	260 VAC	Yes
SEAM-GP	Black LCP	Copper Alloy	Au or Sn over 50 μ" (1.27 μm) Ni	-55 °C to +125 °C	2.7 A (10 pins powered)	240 VAC	Yes
SEAMP/SEAFP	Natural High Temp Nylon	Copper Alloy (SEAMP) BeCu Alloy (SEAFP)	Au or Sn over 50 μ" (1.27 μm) Ni	-55 °C to +125 °C	1.9 A (6 pins powered)	225 VAC	Not Available
SEAR	Black LCP	Hard Gold Plated	Au over 50 μ" (1.27 μm) Ni	-55 °C to +125 °C	Contact Samtec	240 VAC	Not Available
SEAMI	Black LCP	Copper Alloy	Au or Sn over 50 μ" (1.27 μm) Ni	-55 °C to +125 °C	Not Available	Not Available	Yes

**Note:** Some lengths, styles and options are non-standard, non-returnable




### (1.27 mm) .050" PITCH • SEAM/SEAF SERIES

PLATING OPTION IFAD NO. OF **SOLDER SERIES POSITIONS PER ROW** STYLE ROWS Specify LEAD -04 **SEAM** –10, –15, –20, –30, = 10 µ" (0.25 µm) Gold on contact area, Matte Tin on solder tail Terminal -40, -50 Tin/Lead -A **STYLE** Alloy Solder Charge -05 = Alignment Pin **SEAF** from SEAM & SEAF: -10 only chart **–K** Polyimide Film Pick & Socket available in -04 Row -06  $-S \\ = 30 \ \mu'' \ (0.76 \ \mu m) \\ Gold on contact area,$ -2 SEAM: –15 only available in –04 Row with -02.0 Lead Style, and –10 Row with any Lead Style = Lead-Free -08 Place Pad Solder Matte Tin on solder tail Charge -TR -10 = Tape & Reel SEAF: -15 only available in -04 or -10 Row with -5.0 Lead Style **-STL** = 30 μ" (0.76 μm) Gold on contact area, Tin/Lead on solder tail (SEAM -04. -05 & -06 -FR Rows not = Full Reel Tape & Reel

SEAM
Board Mates:
SEAF, SEAFP
Standoffs:





available with -06.5

Lead Style)

LEAD STYLE Α (5.61) .221 -02.0 -03.0 (6.60) .260 -03.5 (7.11) .280 -06.5 (10.16) .400 -07.0 (10.59) .417 -09.0 (12.60) .496 -11.0 (14.61) .575

	NO. OF ROWS	В
	-04	(7.06) .278
_	-05, -06	(9.60) .378
	-08	(12.14) .478
)	-10	(14.68) .578
_		
5		
5		

В

(5.66) .223

(8.20) .323

(must order max. quantity per reel; contact Samtec

for quantity breaks)


View complete specifications at: samtec.com?SEAM

**ALSO AVAILABLE**See website for 14 row option.

SEAF Board Mates: SEAM, SEAMP, SEAR, SEAMI

Standoffs: JSO





View complete specifications at: samtec.com?SEAF

MATED HEIGHTS						
	SEAF LEAD STYLE					
SEAM LEAD STYLE	-05.0	-06.0	-06.5	-07.5		
-02.0	7 mm	8 mm	8.5 mm	9.5 mm		
-03.0	8 mm	9 mm	9.5 mm	10.5 mm		
-03.5	8.5 mm	9.5 mm	10 mm	11 mm		
-06.5	11.5 mm	12.5 mm	13 mm	14 mm		
-07.0	12 mm	13 mm	13.5 mm	14.5 mm		
-09.0	14 mm	15 mm	15.5 mm	16.5 mm		
-11.0	16 mm	17 mm	17.5 mm	18.5 mm		

LEAD STYLE	A	NO. O
-05.0	(5.05) .199	-04
-06.0	(6.05) .238	-05, -0
-06.5	(6.55) .258	-08
-07.5	(7.54) .297	-10

.55) .258	-08	(10.74) .423
'.54) .297	-10	(13.28) .523

### STANDARDS VITA 47

VITA 57.1 FMC VITA 57.4 FMC+ VITA 74 VNX PISMO™2

Visit www.samtec.com/standards for more information.

**Notes:** IPC-A-610F and IPC J-STD-001F Class 3 solder joint.

Severe Environment Testing qualified; aligns with MIL-DTL-55302. Visit samtec.com/set