



85 Ω, 32 AWG MICRO TWINAX CABLE

TTF-3285-XX-XX





PERFORMANCE DATA

Capacitance:	16 pF/ft (nominal)
Skew:	10 ps/m within pairs
Propagation Delay:	1.46 ns/foot
Flex Cycles:	8,000 cycles, 4-wide ribbon*
Current Rating:	Single conductor = 2.7 Amps** 16 conductors = 1.0 Amps**
Shield DCR:	120 Ω/1000 ft
CC DCR:	164 Ω/1000 ft
Min. Bend Radius:	.125"
Availability:	Single, 2-10 ribbon, tape bonded
Temperature Rating:	-25 °C to 105 °C, UL VW-1 Tested ***
DWV Working Voltage:	188 V [†]

Insertion Loss	0.25 m	1 m
-3 dB	>20 GHz	3.3 GHz
-7 dB	>20 GHz	16.3 GHz

* Test Conditions – 8 oz. weight, dia 7/8" mandrel, +/-90 bend X2
 ** Rating – 30 °C Temperature Rise, 20% de-rated. Testing performed on 8-position ribbon.
 *** Test Conditions – Heat Shock/Cold Bend per UL1581, wire wrap 1/4" mandrel, visual inspection
[†]Test Conditions – IR/DWV/Thermal Shock/Humidity per EIA-364-20, 21, 31 and 32

INSERTION LOSS AND RETURN LOSS GRAPHS[‡]



[‡]IL and RL data are typical. Results may vary.



1.800.SAMTEC.9 • HDR@samtec.com