

FIG 1  
ARM6 TO AMF6-V MATED VIEW

TABLE 1				
	AMF6-V		WIPE	
	"A" FULLY MATED	"A" MAX	FULLY MATED	MIN
ARM6	14.78 [0.582]	15.50 [0.610]	1.10 [0.043]	0.38 [0.015]




FIG 2  
ARM6 TO AMF6-RA MATED VIEW

TABLE 2				
	AMF6-RA		WIPE	
	"B" FULLY MATED	"B" MAX	FULLY MATED	MIN
ARM6	14.03 [0.552]	14.75 [0.581]	1.10 [0.043]	0.38 [0.015]

- NOTES:
1. ALL DIMENSIONS BASED ON NOMINAL VALUES FOR SAMTEC RECOMMENDED PCB LAYOUTS.
  2. ALTHOUGH MAX DIMENSIONS ARE LISTED, SAMTEC RECOMMENDS FULLY MATING COMPONENTS.

• PROPRIETARY NOTE •  
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.



520 PARK EAST BLVD, NEW ALBANY, IN 47150  
PHONE: 812-944-6733 FAX: 812-948-5047  
e-Mail info@SAMTEC.com code 55322





FIG 3

AMF6-V MINIMUM SPACING REQUIREMENT (HORIZONTAL DIRECTION)

TABLE 3		
PARIS	"C"	"D"
-01	9.46 [0.37]	6.96 [0.27]
-02	12.00 [0.47]	9.50 [0.37]




FIG 5

MINIMUM RECOMMENDED BEND RADIUS





FIG 4

AMF6-V MINIMUM SPACING REQUIREMENT (VERTICAL DIRECTION)

- NOTES:  
 1. NOTE DELETED.  
 2. RECOMMEND A MINIMUM SPACING OF 3.18 [0.125] FOR REWORK PROCESS.

PROPRIETARY NOTE  
 THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.



520 PARK EAST BLVD., NEW ALBANY, IN 47150  
 PHONE: 812-944-6733 FAX: 812-948-5047  
 e-Mail info@SAMTEC.com code 55322

TABLE 4

PARIS	"E"
-01	9.46 [0.37]
-02	12.00 [0.47]





FIG 6  
AMF6-RA MINIMUM SPACING REQUIREMENT  
(HORIZONTAL DIRECTION)





FIG 7  
AMF6-RA MINIMUM SPACING REQUIREMENT  
(VERTICAL DIRECTION)




FIG 8  
MINIMUM RECOMMENDED BEND RADIUS

PROPRIETARY NOTE  
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

