

DO NOT SCALE FROM

THIS PRINT

THIS PRODUCT MANUFACTURED WITH LEAD-FREE PROCESSING

PATENT NUMBER 7,544,093

DESIGNED & DIMENSIONED IN MILLIMETERS[INCHES]

BE23S-XXXXX-XX-XX-XXXX

OVERALL CABLE LENGTH (MILLIMETERS) 0100-9999 [3.9 - 393.7] (SEE NOTE 4)

-No. OF PHASE MATCHED CABLES

-02: (2 CABLES FOR THIS PART NUMBER)

-04: (4 CABLES FOR THIS PART NUMBER) -06: (6 CABLES FOR THIS PART NUMBER) -08: (8 CABLES FOR THIS PART NUMBER)

PHASE MATCHING SPEC (RANGE)

⟨C⟩-02: 2.0 PICO-SECOND -05: 5.0 PICO-SECONDS -10: 10.0 PICO-SECONDS (SEE NOTE 5)

CABLE CALLOUT END 1-23S: MWC-2350-01 CABLE, WITH PRB3-P-C-XX-ST-CS3 CONNECTOR (SEE FIG 4, SHT 4) **END 2 CONNECTOR**

(SEE TABLE 1, SHT 2)

TABLE 2 **OVERALL LENGTH** "A" 0100-0200 [3.94-7.87] +3.0 [.12]/-0.0 [.00] 0201-0500 [7.91-19.69] +5.0 [.20]/-0.0 [.00] 0501-1100 [19.72-43.30] +10.0 [.40]/-0.0 [.00]




FIG 1 BE23S-92SPP-XX-02-XXXX SHOWN

NOTES:

I. © REPRESENTS A CRITICAL DIMENSION

(C)2. ASSEMBLY TO BE 100% TESTED FOR OPENS, SHORTS & HI-POT TESTED (PER TABLE 3, AC OR DC), THE HI-POT VOLTAGE FOR THE ASSEMBLY SHOULD BE SET TO THE END OPTION WITH THE LOWEST TEST VOLTAGE RATING.

3. CABLE ASSEMBLY TO HAVE PROTECTIVE CAP ASSEMBLED ON EACH END AND TO BE INDIVIDUALLY PACKAGED IN ESD BAG (BG-09-12).

4. CABLE LENGTHS LONGER THAN 1000 MILLIMETERS ARE NOT SUPPORTED BY S.I. TEST DATA

5. PARTS TO BE PHASE MATCHED PER CO-HD-WI-3062-M.

6. FERRULE AND SPRING ARE FREE FLOATING AND ARE NOT STATIONARY.

F:\DWG\MISC\MKTG\BE23S-XXXXX-XX-XX-XXX-MKT.SLDDRW

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS [INCHES]. TOLERANCES ARE:

DECIMALS **ANGLES** .X: ±0.3 [.01] .XX: ±0.13 [.005] .XXX: ±0.051 [.0020]

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING REPRODUCTION LISE PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOL OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NO REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC INC

SHEET SCALE: 2:

PROPRIETARY NOTE

DO NOT SCALE DRAWING

INSULATORS: PTFE (SCC31)
PCTFE OR ULTEM-1000(OTHERS)
GASKETS: SILICONE
INNER PIN, RETAINER, FERRULE, NUT: BRASS C-RING: STAINLESS STEEL
SHELLS, INSERT, CABLE BODY, SPRING: BRASS OR STAINLESS STEEL



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FA e-Mail: info@SAMTEC.com FAX: 812-948-5047

DESCRIPTIO

BULLSEYE 23 AWG CABLE ASSEMBLY

BE23S-XXXXX-XX-XX-XXXX

3/10/2014 SHEET 1 OF 7

BY:EMMA CHEN

REVISION E

PATENT NUMBER 7,544,093

	TABLE 1									
END 2 OPTION	SERIES	GENDER	PLATING CONFIGURATION					CONFIGURATION		FIGURE
				CENTER CONTACT	OUTER CONTACT	OTHER COMPONENTS				
-92SJP	2.92 MM	JACK	STRAIGHT	30µ" GOLD	STAINLESS STEEL	3µ" GOLD	SHT 3, FIG 2			
-92SPP	2.92 MM	PLUG	STRAIGHT	30µ" GOLD	STAINLESS STEEL	3μ" GOLD	SHT 3, FIG 3			
-SCC31	Bull's Eye ®	PLUG	STRAIGHT	30µ" GOLD	3μ" GOLD	3µ" GOLD	SHT 4, FIG 4			
-35SJP	3.50 MM	JACK	STRAIGHT	30µ" GOLD	STAINLESS STEEL	3μ" GOLD	SHT 4, FIG 5			
-35SPP	3.50 MM	PLUG	STRAIGHT	30µ" GOLD	STAINLESS STEEL	3μ" GOLD	SHT 5, FIG 6			

TABLE 3						
END OPTION	SUBTRACTOR	STRIP DIMENSIONS			HI POT	
	"Y"	"B"	"C"	"D"	"DC"	"AC"
-92SJP	7.7 [0.30]	2.25 [0.089]	3.25 [0.128]	6.75 [0.266]	1000	1000
-92SPP	8.4 [0.33]	2.25 [0.089]	3.25 [0.128]	6.75 [0.266]	1000	1000
-SCC31	1.7 [0.07]	2.16 [0.085]	2.16 [0.085]	5.94 [0.234]	1000	750
-35SJP	8.3 [0.33]	1.65 [0.065]	2.45 [0.096]	5.95 [0.234]	1000	1000
-35SPP	9.2 [0.36]	1.65 [0.065]	2.45 [0.096]	5.95 [0.234]	1000	1000

F:\DWG\MISC\MKTG\BE23S-XXXXX-XX-XX-XXX-MKT.SLDDRW

* PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,

THIS DECORATION OF THE ATTEMPT OF TH

DO NOT SCALE DRAWING

SHEET SCALE: 1:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code: 55322


DESCRIPTION:


BULLSEYE 23 AWG CABLE ASSEMBLY


DWG NO

BE23S-XXXXX-XX-XXX-XXX

BY:EMMA CHEN 3/10/2014 SHEET 2 OF 7







	вом			
ITEM	COMPONENT	-HP		
1	SUB ASSEMBLY	SUB-292PS-P-C-HP-ST-CS3		
2	INSULATOR	292-ST-INS-CS3		
3	SUB CABLE BODY	SUB-292-C-F-ST-CS3-CBDY		
4	BODY	292PS-C-P-ST-CA7-BDY		
5	HEAT SHRINK	HST-0.125-02-BLK-A		

REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

* PROPRIETARY NOTE *
THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMMEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE

OR PART. TO ANY UNAUTHORIZED PERSON OR ENTITY NOR

SHEET SCALE: 3:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:

BULLSEYE 23 AWG CABLE ASSEMBLY

DWG. NO.

BE23S-XXXXX-XX-XX-XXXX

BY:EMMA CHEN 3/10/2014 SHEET 3 OF 7

F:\DWG\MISC\MKTG\BE23S-XXXXX-XX-XXX-XXX-MKT.SLDDRW





FIG 4 -SCC31 SHOWN

_3.68[.145] REF


0

6.60[.260]

Ø2.69[.106] REF




PATENT NUMBER 7,544,093




|--|


Ø0.69[.027]

вом			
ITEM	COMPONENT	-HF	
1	INSULATOR 1	PRB3-INS-003	
2	PIN	PRB3-PIN-002-H	
3	FERRULE	PRB3-FER-002-F	
4	RETAINER	PRB3-RET-002-F	
5	SPRING	PRB3-SPR-002	
6	INSULATOR 2	PRB3-INS-004	
7	HEAT SHRINK	HST-0.125-02-BLK	



0.89[.035] REF





ВОМ			
ITEM	COMPONENT	-HP	
1	SHELL	350-J-C-P-ST-CS3-SHL	
2	SUB SOCKET ASSEMBLY	SUB-350-J-C-HP-ST-CS3-SKT	
3	INSULATOR	350-ST-CS3-INS	
4	CABLE BODY	350-C-F-ST-CS3-CBDY	
5	BODY	350-C-P-ST-CS3-BDY	
6	HEAT SHRINK	HST-0.125-02-BLK-A	

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, U.S., PATENT RIGHTS AND SALES RIGHTS ARE DOWNESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE ESCLOSED, IN WHOLE

INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

PROPRIETARY NOTE

SHEET SCALE: 3:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:


BULLSEYE 23 AWG CABLE ASSEMBLY


DWG. NO.

BE23S-XXXXX-XX-XX-XXXX

BY:EMMA CHEN 3/10/2014 | SHEET 4 OF 7

F:\DWG\MISC\MKTG\BE23S-XXXXX-XX-XXX-XXX-MKT.SLDDRW





	ВОМ			
ITEM	COMPONENT	-HP		
1	SUB SHELL ASSEMBLY	SUB-350-P-C-P-ST-CS3-SHL		
2	SUB PIN ASSEMBLY	SUB-350-P-C-HP-ST-CS3-PIN		
3	INSULATOR	350-ST-CS3-INS		
4	CABLE BODY	350-C-F-ST-CS3-CBDY		
5	BODY	350-C-P-ST-CS3-BDY		
6	HEAT SHRINK	HST-0.125-02-BLK-A		



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code: 55322

DO NOT SCALE DRAWING

SHEET SCALE: 3:1


DESCRIPTION:


BULLSEYE 23 AWG CABLE ASSEMBLY

DWG. NO.

BE23S-XXXXX-XX-XXXXX

BY: EMMA CHEN 3/10/2014 | SHEET 5 OF 7





e-Mail: info@SAMTEC.com DESCRIPTION: DO NOT SCALE DRAWING **BULLSEYE 23 AWG CABLE ASSEMBLY** BE23S-XXXXX-XX-XX-XXXX BY: EMMA CHEN 3/10/2014 | SHEET 7 OF 7

F:\DWG\MISC\MKTG\BE23S-XXXXX-XX-XX-XXX-MKT.SLDDRW

SHEET SCALE: 5:4