


# 50 Ω, 32 AWG MICRO COAX CABLE

TCF-3250F-XX-XX



## PERFORMANCE DATA

Capacitance:	26 pF/ft (nominal)
Propagation Delay:	1.29 ns/foot
Flex Cycles:	50,000 cycles, 13-wide ribbon*
Current Rating:	Single conductor = 2.4 Amps** 20 conductors = 1.0 Amps**
Shield DCR:	91 Ω/1000 ft
CC DCR:	166 Ω/1000 ft
Min. Bend Radius:	.125"
Availability:	Single, 2-30 ribbon, tape bonded
Temperature Rating:	-25 °C to 105 °C, UL VW-1 Tested ***
DWV Working Voltage:	281 V†

Insertion Loss	0.25 m	1 m
-3 dB	14 GHz	3 GHz
-7 dB	>20 GHz	10 GHz



\* Test Conditions – 8 oz. weight, dia 1/4" mandrel, +/-90 bend X2

\*\* Rating – 30 °C Temperature Rise, 20% de-rated. Testing performed on 20-position ribbon.

\*\*\* Test Conditions – Heat Shock/Cold Bend per UL1581, wire wrap 1/4" mandrel, visual inspection

†Test Conditions – IR/DWV/Thermal Shock/Humidity per EIA-364-20, 21, 31 and 32

## INSERTION LOSS AND RETURN LOSS GRAPHS‡



‡IL and RL data are typical. Results may vary.



1.800.SAMTEC.9 • HDR@samtec.com

October 21, 2019 • Rev: I