


100 Ω, 34 AWG SOLID, CU MICRO TWINAX CABLE HT

TTF-34100CU-01-T01-S





PERFORMANCE DATA

Capacitance:	13.3 pF/ft leg-to-leg (nominal)
Skew:	3.5 ps/m max within pairs
Propagation Delay:	1.46 ns/foot
Flex Cycles:	4,000 cycles, single*
Current Rating:	Single conductor: 1.5 Amps** 2 conductors: 1.1 Amps**
Shield DCR:	133 Ω/1000 ft
CC DCR:	300 Ω/1000 ft
Min. Bend Radius:	.125"
Availability:	Single, tape bonded
Temperature Rating:	-40 °C to 140 °C ***
Flammability Rating:	UL VW-1†
DWV Working Voltage:	283 V‡

Insertion Loss	0.25 m	1 m
-3 dB	30 GHz	2.6 GHz
-7 dB	> 32 GHz	13 GHz

* Test Conditions – 4 oz. weight, dia 7/8" mandrel, +/-90 bend X2
 ** Rating – 30 °C Temperature Rise, 20% de-rated. Testing performed on single.
 *** Test Conditions – Heat Shock/Cold Soak per UL #1581, wire wrap 7/8" mandrel, visual inspection
 †TX-34100CU-T01-S has undergone UL VW-1 Research Testing and complies with UL 2556.
 ‡Test Conditions – IR/DWV/Thermal Shock/Humidity per EIA-364-20, 21, 31 and 32

INSERTION LOSS AND RETURN LOSS GRAPHS[§]



[§]IL and RL data is typical. Results may vary.



1.800.SAMTEC.9 • HDR@samtec.com

February 7, 2024 • Rev: D