




DO NOT
SCALE FROM
THIS PRINT



SERIES _____
100: 1.0MM

GENDER
-J: JACK

TYPE—
-P: PCB



FINISH _____ -ST: STRA
-VP: 50μ" PRECISION GOLD
CENTER CONTACT, PASSIVATED
OUTER CONTACT

TERMINATION
-CMM: COMPRESSION MOUNT MICROSTRIP

— ORIENTATION
-ST: STRAIGHT

PACKAGING
-BLANK: INDIVIDUALLY BAGGED
-B: FULL TRAY (QTY >= 100)

OPTION
-1: OPTION 1 (WITHOUT SCREWS)
-2: OPTION 2 (WITH MOUNTING HARDWARE)



RECOMMENDED PCB LAYOUT
(SEE NOTE 2)

NOTES:

1. RECOMMENDED MOUNTING TORQUE 0.5~0.8 INCH-POUNDS.
2. THIS IS A GENERAL FOOTPRINT AND IS NOT OPTIMIZED FOR ELECTRICAL PERFORMANCE,
CONTACT SIG@SAMTEC.COM FOR ASSISTANCE WITH ELECTRICAL LAYOUT.

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL: SHEET SCALE: 6:1

BODY, BUSHING & SCREW: STAINLESS STEEL
SOCKET: COPPER ALLOY

DESCRIPTION:	1.0MM VERTICAL COMPRESSION MOUNT MICROSTRIP APPLICATION
--------------	---

DWG. NO.

100-J-P-VP-ST-CMM-X-X

BY: SCOTT G	3/31/2025	SHEET 1 OF 1
-------------	-----------	--------------

F:\dwg\misc\mktg\100-J-P-VP-ST-CMM-X-X-MKT.SLDDRW