







DO NOT
SCALE FROM
THIS PRINT

- NOTES:
1. **VITA 88. CUSTOM BODY WITH NO ALIGNMENT PINS, NOT AVAILABLE AS STANDARD.**
 2. C REPRESENTS A CRITICAL DIMENSION.
 3. MINIMUM PUSHOUT FORCE: 0.50 LBS.
 4. DIMENSION MUST BE MEASURED USING INSPECTION FIXTURE AT-1817-836-2, USE CO-AU-WI-2003-M FOR PROCESS.
 5. MEASURED FIRST & LAST POSITIONS ONLY, ALL ROWS.
 6. NON-FUNCTIONAL VOIDING IN PLASTIC BODY TO BE AT SAMTEC'S DISCRETION.
 7. PARTS TO BE PACKAGED IN TAPE AND REEL.
ATTACH LABEL "SEAX-0001" TO EACH TAPE & REEL PACKAGE.

**THIS PRODUCT MANUFACTURED
WITH LEAD-FREE PROCESSING**



BY SIGNING THIS DOCUMENT
YOU ARE ACCEPTING THE
CONDITIONS SET WITHIN.
YOUR REQUIREMENTS MUST BE
LISTED WITHIN THIS DRAWING.
WHERE NO DIRECTION FROM THE
CUSTOMER IS IDENTIFIED
SAMTEC'S PROCESS
REQUIREMENTS WILL BE USED.

DATE: _____
COMPANY: _____
CUSTOMER SIGNATURE: _____
PRINTED NAME: _____
PHONE NO: _____
EXCEPTIONS: _____

ITEM NO	PART NUMBER	QUANTITY	MATERIAL
1	ASP-213618-01-B	1.0000	LCP, COLOR: BLACK
2	NEW-SUB-C-209-05-0-S-2	114.00	BeCu/LEAD FREE SOLDER
3	K-DOT-.256-.375-.005	1.0000	POLYIMIDE FILM
4	CT-ASP5762MS	.00250	CONDUCTIVE POLYMER

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS ANGLES
.XX: ±.01[0.3]
.XXX: ±.005[0.13]
.XXXX: ±.0020[0.051]

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 3:1

PLATING:
CONTACT AREA: .000030 GOLD OVER .000100 NICKEL
REMAINDER: .000200 TIN OVER .000050 NICKEL
SOLDER COMPOSITION: 95.5%TIN/3.8% SILVER/0.7% COPPER

F:\DWG\MISC\MKTG\ASP-212942-04-MKT.SLDRW


samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 53322




DESCRIPTION:
VITA 88 MODIFIED SEAF ASM 19 POS, 6 ROW

DWG. NO. **ASP-212942-04**

BY: T BEHAGG 09/09/2019 SHEET 1 OF 2



- NOTES:
1. ALL DIMENSIONS ARE SYMMETRIC ABOUT THE CENTERLINE.
 2. CONNECTOR ENVELOPE DIMENSIONS, OTHER COMPONENTS PLACED ON PCB SHALL AVOID THIS ZONE.



(ALL DIMENSIONS ARE SYMMETRIC ABOUT THE CENTERLINE.)

NOTE:
STENCIL TO BE .0060 [0.152] THICK.

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

samtec

520 PARK EAST BLVD. NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

SHEET SCALE: 3:1

DESCRIPTION:
VITA 88 MODIFIED SEAF ASM 19 POS, 6 ROW

DWG. NO.

ASP-212942-04

BY: T BEHAGG 09/09/2019 SHEET 2 OF 2