


TABLE 4		
END TO END	"L"	
DV TO DV	950	[24.13]
DV TO EM (-TXX)	835	[21.21]
DV TO EM (-SXX)	806	[20.48]
EM (-TXX) TO EM (-TXX)	720	[18.29]
EM (-TXX) TO EM (-SXX)	691	[17.55]
EM (-SXX) TO EM (-SXX)	662	[16.81]
DV-N TO DV-N	840	[21.34]
DV-N TO EM-N (-TXX)	780	[19.81]
DV-N TO EM-N (-SXX)	751	[19.08]

DO NOT SCALE FROM THIS PRINT

**FIG. 1**  
VERTICAL  
(EQCD-040-XX.XX-STR-STR-1 SHOWN)  
LENGTH: XX.XX + "L" REF (SEE TABLE 4)  
(SEE NOTE 14)



EQCD-XXX-XX.XX-XXX-XXX-X-X

No OF POSITIONS  
-020, -040, -060, -080  
(PER ROW)  
02  
LENGTH  
-XX.XX (INCHES)  
(01.72[43.7] MIN)  
(SEE NOTE 2)  
(SEE NOTE 9)  
FIRST END

**END OPTION**  
 -F: SCREW OPTION FIRST END ONLY (NOT AVAILABLE WITH XPX OPTIONS)  
 -S: SCREW OPTION SECOND END ONLY  
 -B: SCREW OPTION BOTH ENDS (NOT AVAILABLE WITH XPX OPTIONS)  
 -L: FIRST END RT1 OPTION (SEE NOTE 10 & 11)  
 -R: SECOND END RT1 OPTION (SEE NOTE 10 & 11)  
 -D: BOTH ENDS RT1 OPTION (SEE NOTE 10 & 11)  
 -1: FIRST END SCREW OPTION, SECOND END RT1 OPTION (SEE NOTE 10 & 11)  
 -2: FIRST END RT1 OPTION, SECOND END SCREW OPTION (SEE NOTE 10 & 11)  
 -N: NO CAPS (LEAVE BLANK FOR STANDARD CAPS BOTH ENDS) (SEE FIG. 3, SHEET 5 FOR EDGE MOUNT END OPTIONS) (SEE FIG. 4, SHEET 5 FOR DOUBLE VERTICAL END OPTIONS) (RT1 OPTIONS NOT AVAILABLE WITH XPX OR XEX OPTIONS) (RT1 OPTIONS NOT AVAILABLE FOR 080 POSITION) (SEE SHEET 6 FOR RT1 AND NO CAP OPTIONS)

-TTR: TERMINAL, TOP, RIGHT  
 -TTL: TERMINAL, TOP, LEFT  
 -TBR: TERMINAL, BOTTOM, RIGHT  
 -TBL: TERMINAL, BOTTOM, LEFT  
 -STR: SOCKET, TOP, RIGHT  
 -STL: SOCKET, TOP, LEFT  
 -SBR: SOCKET, BOTTOM, RIGHT  
 -SBL: SOCKET, BOTTOM, LEFT (SEE TABLE 1 & SHEET 2)  
 -TEU: TERMINAL, EDGE MOUNT, UP  
 -TED: TERMINAL, EDGE MOUNT, DOWN  
 -SEU: SOCKET, EDGE MOUNT, UP  
 -SED: SOCKET, EDGE MOUNT, DOWN (SEE TABLE 5 & SHEET 5)  
 -TPU: TERMINAL, PANEL MOUNT, UP  
 -TPD: TERMINAL, PANEL MOUNT, DOWN  
 -SPU: SOCKET, PANEL MOUNT, UP  
 -SPD: SOCKET, PANEL MOUNT, DOWN (SEE TABLE 10 & SHEET 5) (ONLY AVAILABLE ON -020, -040, AND -060)


**WIRING OPTION**  
 -1: PIN 1 TO PIN 1  
 -2: PIN 1 TO PIN 2  
 -3: PIN 1 TO PIN N-1  
 -4: PIN 1 TO PIN N (SEE TABLE 9, SHEET 7)  
**SECOND END**  
 -TTR: TERMINAL, TOP, RIGHT  
 -TTL: TERMINAL, TOP, LEFT  
 -TBR: TERMINAL, BOTTOM, RIGHT  
 -TBL: TERMINAL, BOTTOM, LEFT  
 -STR: SOCKET, TOP, RIGHT  
 -STL: SOCKET, TOP, LEFT  
 -SBR: SOCKET, BOTTOM, RIGHT  
 -SBL: SOCKET, BOTTOM, LEFT (SEE TABLE 1 & SHEET 3)  
 -TEU: TERMINAL, EDGE MOUNT, UP  
 -TED: TERMINAL, EDGE MOUNT, DOWN  
 -SEU: SOCKET, EDGE MOUNT, UP  
 -SED: SOCKET, EDGE MOUNT, DOWN (SEE TABLE 5 & SHEET 5)

**TABLE 3**

No. OF POSITIONS	N	N-1
-020	40	39
-040	80	79
-060	120	119
-080	160	159

- NOTES:**
- ⊕ REPRESENTS A CRITICAL DIMENSION.
  - SUB-TCF LENGTH IS EQUAL TO EQCD LENGTH.
  - ⊕ ALL ASSEMBLIES TO BE 100% ELECTRICALLY TESTED FOR SHORTS AND OPENS.
  - ⊕ ALL ASSEMBLIES TO BE 100% HI-POT TESTED AT 300V.
  - TOP SUB-TCF NOT SHOWN IN THIS VIEW FOR CLARITY; HDRL-11 TO BE CENTERED ON LOWER SUB-TCF AS SHOWN; HDRL-11 IS TO CONTAIN PART NUMBER, SHOP ORDER & DATE CODE.
  - PACKAGE ASSEMBLIES IN ANTI-STATIC & STATIC DISSIPATIVE BAGS.
  - TOP SURFACE OF SCREW TO BE FLUSH OR BELOW TOP SURFACE OF CAP.
  - PARTS TO BE PROCESSED PER SAMTEC ACCEPTABILITY REQUIREMENTS: HDR-PI-01 "CABLE ASSEMBLY WORKMANSHIP STANDARDS".
  - CABLE LENGTHS LONGER THAN 40.00 INCHES ARE NOT SUPPORTED BY S.I. TEST DATA.
  - RT1 OPTION IS NOT AVAILABLE WITH EDGMOUNT OR PANEL MOUNT END OPTIONS.
  - RT1 OPTION IS NOT AVAILABLE WITH -080 POSITIONS.
  - ALL POSITIONS ARE TRANSMITTED AS SIGNALS ACROSS COAX CENTER CONDUCTORS. CONNECTOR GROUND BLADES ARE TIED TO THE COAX SHIELD. FOR MULTIPLE BANK ASSEMBLIES, EACH BANK IS GROUND INDEPENDENT OF THE OTHERS.
  - REFER TO PREP-SPEC DRAWING FOR CABLE PREP DIMENSIONS. ASSEMBLY USES STANDARD PCB PREP.
  - FOR CABLE LENGTHS LESS THAN 5 INCHES, CABLE LENGTH AND OVERALL LENGTH TOLERANCE IS ±0.05 INCHES. FOR CABLE LENGTHS GREATER THAN 5 INCHES, USE ±1% FOR BOTH.

**THIS PRODUCT MANUFACTURED WITH LEAD-FREE PROCESSING**



**TABLE 2**

END	* "C"
-TXX	.333[8.46]
-SXX	.296[7.52]

\* -DV END OPTIONS ONLY

DETAIL 'A'  
SCALE 2.5 : 1


**TABLE 1**

No. OF POSITIONS	"A"	"B"	QCD-XX-01	QCD-XX-02	QTY OF SUB-TCF	SUB-EQCD-X-XXX-XX-XX
-020	1.175[29.85]	1.078[27.38]	QCD-01-01	QCD-01-02	2	SUB-EQCD-X-020-XX-XX
-040	1.963[49.85]	1.866[47.40]	QCD-02-01	QCD-02-02	4	SUB-EQCD-X-040-XX-XX
-060	2.750[69.85]	2.653[67.39]	QCD-03-01	QCD-03-02	6	SUB-EQCD-X-060-XX-XX
-080	3.538[89.85]	3.441[87.39]	QCD-04-01	QCD-04-02	8	SUB-EQCD-X-080-XX-XX


UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:  
 DECIMALS: .XX: ±.01 [.3] .XXX: ±.005 [.13] .XXXX: ±.0020 [.051]  
 ANGLES: 2°  
**MATERIAL:** DO NOT SCALE DRAWING SHEET SCALE: 1:0.8  
 PLATING: -H GOLD: 30µ" CONTACT  
**PROPRIETARY NOTE**  
 THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.  
 F:\DWG\MISC\MKTG\EQCD-XXX-XX.XX-XXX-XXX-X-X-MKT.SLDDRW

**samtec**  
 520 PARK EAST BLVD, NEW ALBANY, IN 47150  
 PHONE: 812-944-6733 FAX: 812-948-5047  
 e-Mail: info@SAMTEC.com code: 55322


DESCRIPTION:  
0.8mm HIGH-SPEED COAX CABLE ASSEMBLY  
 DWG. NO.  
EQCD-XXX-XX.XX-XXX-XXX-X-X  
 BY: KEVIN B 02/19/03 SHEET 1 OF 7




WIRING OPTION	FIRST END PIN #	SECOND END PIN #	WIRE NUMBER
1	1	1	B20
2	1	2	B20
3	1	N-1	B20
4	1	N	B20




WIRING OPTION	FIRST END PIN #	SECOND END PIN #	WIRE NUMBER
1	1	1	T1
2	1	2	T1
3	1	N-1	T1
4	1	N	T1




WIRING OPTION	FIRST END PIN #	SECOND END PIN #	WIRE NUMBER
1	1	1	B1
2	1	2	B1
3	1	N-1	B1
4	1	N	B1





WIRING OPTION	FIRST END PIN #	SECOND END PIN #	WIRE NUMBER
1	1	1	T20
2	1	2	T20
3	1	N-1	T20
4	1	N	T20





WIRING OPTION	FIRST END PIN #	SECOND END PIN #	WIRE NUMBER
1	1	1	T1
2	1	2	T1
3	1	N-1	T1
4	1	N	T1



WIRING OPTION	FIRST END PIN #	SECOND END PIN #	WIRE NUMBER
1	1	1	B20
2	1	2	B20
3	1	N-1	B20
4	1	N	B20



WIRING OPTION	FIRST END PIN #	SECOND END PIN #	WIRE NUMBER
1	1	1	T20
2	1	2	T20
3	1	N-1	T20
4	1	N	T20



WIRING OPTION	FIRST END PIN #	SECOND END PIN #	WIRE NUMBER
1	1	1	B1
2	1	2	B1
3	1	N-1	B1
4	1	N	B1

**PROPRIETARY NOTE**  
 THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 1:25:1




520 PARK EAST BLVD, NEW ALBANY, IN 47150  
 PHONE: 812-944-6733 FAX: 812-948-5047  
 e-Mail: info@SAMTEC.com code: 53322


DESCRIPTION:  
 0.8mm HIGH-SPEED COAX CABLE ASSEMBLY

DWG. NO.  
 EQCD-XXX-XX.XX-XXX-XXX-X-X


BY: KEVIN B 02/19/03 SHEET 2 OF 7




WIRING OPTION	FIRST END PIN #	SECOND END PIN #
1	1	1
2	1	2
3	1	N-1
4	1	N




WIRING OPTION	FIRST END PIN #	SECOND END PIN #
1	1	1
2	1	2
3	1	N-1
4	1	N




WIRING OPTION	FIRST END PIN #	SECOND END PIN #
1	1	1
2	1	2
3	1	N-1
4	1	N




WIRING OPTION	FIRST END PIN #	SECOND END PIN #
1	1	1
2	1	2
3	1	N-1
4	1	N




WIRING OPTION	FIRST END PIN #	SECOND END PIN #
1	1	1
2	1	2
3	1	N-1
4	1	N



WIRING OPTION	FIRST END PIN #	SECOND END PIN #
1	1	1
2	1	2
3	1	N-1
4	1	N



WIRING OPTION	FIRST END PIN #	SECOND END PIN #
1	1	1
2	1	2
3	1	N-1
4	1	N



WIRING OPTION	FIRST END PIN #	SECOND END PIN #
1	1	1
2	1	2
3	1	N-1
4	1	N

**PROPRIETARY NOTE**  
 THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 1:25:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150  
 PHONE: 812-944-6733 FAX: 812-948-5047  
 e-Mail: info@SAMTEC.com code: 53322

DESCRIPTION:  
 0.8mm HIGH-SPEED COAX CABLE ASSEMBLY


DWG. NO.  
 EQCD-XXX-XX.XX-XXX-XXX-X-X

BY: KEVIN B 02/19/03 SHEET 3 OF 7

REVISION AB




FIRST END - EDGE MOUNT (SEE TABLE 9, SHEET 7)

-TEU






WIRING OPTION	FIRST END PIN #	SECOND END PIN #	WIRE #
1	1	1	T1
2	1	2	T1
3	1	N-1	T1
4	1	N	T1

-TED




WIRING OPTION	FIRST END PIN #	SECOND END PIN #	WIRE #
1	1	1	T20
2	1	2	T20
3	1	N-1	T20
4	1	N	T20

-SED





FIRST END - PANEL MOUNT (SEE TABLE 9, SHEET 6)

-SEU



WIRING OPTION	FIRST END PIN #	SECOND END PIN #	WIRE #
1	1	1	B1
2	1	2	B1
3	1	N-1	B1
4	1	N	B1


-SPD



WIRING OPTION	FIRST END PIN #	SECOND END PIN #	WIRE #
1	1	1	T20
2	1	2	T20
3	1	N-1	T20
4	1	N	T20


SECOND END - EDGE MOUNT (SEE TABLE 9, SHEET 7)

-TEU





WIRING OPTION	FIRST END PIN #	SECOND END PIN #
1	1	1
2	1	2
3	1	N-1
4	1	N


-TED



WIRING OPTION	FIRST END PIN #	SECOND END PIN #
1	1	1
2	1	2
3	1	N-1
4	1	N




-SEU





WIRING OPTION	FIRST END PIN #	SECOND END PIN #
1	1	1
2	1	2
3	1	N-1
4	1	N


-SED



WIRING OPTION	FIRST END PIN #	SECOND END PIN #
1	1	1
2	1	2
3	1	N-1
4	1	N




-SPU



WIRING OPTION	FIRST END PIN #	SECOND END PIN #	WIRE #
1	1	1	B1
2	1	2	B1
3	1	N-1	B1
4	1	N	B1

-TPU



WIRING OPTION	FIRST END PIN #	SECOND END PIN #	WIRE #
1	1	1	B20
2	1	2	B20
3	1	N-1	B20
4	1	N	B20

**PROPRIETARY NOTE**  
 THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING


SHEET SCALE: 1:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150  
 PHONE: 812-944-6733 FAX: 812-948-5047  
 e-Mail: info@SAMTEC.com code: 55322


DESCRIPTION:  
 0.8mm HIGH-SPEED COAX CABLE ASSEMBLY  
 DWG. NO.  
 EQCD-XXX-XX.XX-XXX-XXX-X-X  
 BY: KEVIN B 02/19/03 SHEET 4 OF 7

**FIG 3**  
EDGE MOUNT (WITH CAPTIVE PANEL SCREWS)  
(EQCD-020-XX.XX-SEU-XXX-1-F SHOWN)  
(SAME AS FIG. 2, UNLESS OTHERWISE STATED)




No. OF POSITIONS	"E"	"F"	QCD-XX-03-CPS
-020	1.649[41.87]	1.449[36.80]	QCD-01-03-CPS
-040	2.436[61.87]	2.237[56.80]	QCD-02-03-CPS
-060	3.224[81.87]	3.024[76.80]	QCD-03-03-CPS
-080	4.011[101.87]	3.812[96.80]	QCD-04-03-CPS

**FIG 2**  
EDGE MOUNT (NO CAPTIVE PANEL SCREWS)  
(EQCD-020-XX.XX-TEU-STR-X SHOWN)  
(SAME AS FIG. 1, UNLESS OTHERWISE STATED)



No. OF POSITIONS	"D"	QCD-XXX-03	SUB-EQCD-X-XXX-XX-XX
-020	1.213[30.80]	QCD-01-03	SUB-EQCD-X-020-03-XX
-040	2.000[50.80]	QCD-02-03	SUB-EQCD-X-040-03-XX
-060	2.788[70.80]	QCD-03-03	SUB-EQCD-X-060-03-XX
-080	3.575[90.80]	QCD-04-03	SUB-EQCD-X-080-03-XX

**FIG 4**  
DOUBLE VERTICAL (WITH SCREW DOWN OPTION)  
(EQCD-020-XX.XX-TTR-XXX-1-F SHOWN)  
(SAME AS FIG. 1, UNLESS OTHERWISE STATED)




END	"N"
-TXX	.104[2.65]
-SXX	.068[1.73]

No. OF POSITIONS	"G"	"H"	QCD-XX-02-SDO
-020	1.579[40.10]	1.339[34.00]	QCD-01-02-SDO
-040	2.366[60.10]	2.126[54.00]	QCD-02-02-SDO
-060	3.154[80.10]	2.913[74.00]	QCD-03-02-SDO
-080	3.941[100.10]	3.701[94.00]	QCD-04-02-SDO

**FIG 5**  
PANEL MOUNT (BULK HEAD SCREW INSERTS)  
(EQCD-020-XX.XX-TPU-XXX-X SHOWN)  
(SAME AS FIG. 2, UNLESS OTHERWISE STATED)

No. OF POSITIONS	"J"	"K"	"L"	"M"	SUB-QCD-XX-03-BULK
-020	2.010 [51.05]	1.449 [36.80]	2.250 [57.15]	1.73 [43.94]	SUB-QCD-01-03-BULK
-040	2.798 [71.07]	2.237 [56.82]	3.038 [77.17]	2.518 [63.96]	SUB-QCD-02-03-BULK
-060	3.586 [91.08]	3.024 [76.81]	3.826 [97.18]	3.306 [83.97]	SUB-QCD-03-03-BULK



**PROPRIETARY NOTE**  
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

SHEET SCALE: 1.25:1




520 PARK EAST BLVD, NEW ALBANY, IN 47150  
PHONE: 812-944-6733 FAX: 812-948-5047  
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:  
0.8mm HIGH-SPEED COAX CABLE ASSEMBLY

DWG. NO.  
EQCD-XXX-XX.XX-XXX-XXX-X-X

BY: KEVIN B 02/19/03 SHEET 5 OF 7


**FIG 6**  
(EQCD-020-XX.X-STL-TTR-1-D SHOWN)  
(SAME AS FIG 1, UNLESS OTHERWISE STATED)



**TABLE 11**

No. OF POSITIONS	"P"		"S"		"V"		QCD-XX-01	QCD-XX-14	SUB-EQCD-X-XXX-XX-XX-RT1
-020	1.777	[45.14]	1.680	[42.67]	1.129	[28.66]	QCD-07-01	QCD-01-14	SUB-EQCD-X-020-XX-XX-RT1
-040	2.565	[65.15]	2.468	[62.69]	1.916	[48.67]	QCD-08-01	QCD-02-14	SUB-EQCD-X-040-XX-XX-RT1
-060	3.352	[85.14]	3.255	[82.68]	2.704	[68.67]	QCD-09-01	QCD-03-14	SUB-EQCD-X-060-XX-XX-RT1
-080	4.140	[105.16]	4.043	[102.69]	3.491	[88.67]	QCD-10-01	QCD-04-14	SUB-EQCD-X-080-XX-XX-RT1

**FIG 7**  
(EQCD-XXX-XX.X-XXX-XXX-X-N)  
(SAME AS FIG 1, UNLESS OTHERWISE STATED)



**TABLE 12**

No. OF POSITIONS	"T"	"U"
-20	0.877 [22.28]	1.185 [30.10]
-40	1.665 [42.29]	1.973 [50.11]
-60	2.453 [62.31]	2.760 [70.10]
-80	3.240 [82.30]	3.548 [90.12]

**PROPRIETARY NOTE**

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

SHEET SCALE: 1.5:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150  
PHONE: 812-944-6733 FAX: 812-948-5047  
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:  
0.8mm HIGH-SPEED COAX CABLE ASSEMBLY

DWG. NO.  
**EQCD-XXX-XX.XX-XXX-XXX-X-X**

BY: KEVIN B 02/19/03 SHEET 6 OF 7

FIRST END OPTION	FIRST END SUB-EQCD-X-XXX-XX-01	WIRING OPTION	FIRST END PIN #	SECOND END PIN #	WIRE #	TABLE 9 SECOND END OPTION (SUB-EQCD-X-XXX-XX-XX)												
						-TTR	-TTL	-TBR	-TBL	-STR	-STL	-SBR	-SBL	-TEU	-TED	-SEU	-SED	
-TTR	-T-XXX-01-01	1	1	1	B20	-T-XXX-02-02	N/A	N/A	-T-XXX-01-02	N/A	S-XXX-01-01	S-XXX-02-01	N/A	N/A	-T-XXX-03-02	S-XXX-03-01	N/A	
		2	1	2	B20	-T-XXX-02-01	N/A	N/A	-T-XXX-01-01	N/A	S-XXX-01-02	S-XXX-02-02	N/A	N/A	-T-XXX-03-01	S-XXX-03-02	N/A	
		3	1	N-1	B20	N/A	-T-XXX-01-01	-T-XXX-02-01	N/A	-S-XXX-02-02	N/A	N/A	S-XXX-01-02	S-XXX-03-01	N/A	N/A	S-XXX-03-02	S-XXX-03-01
		4	1	N	B20	N/A	-T-XXX-01-02	-T-XXX-02-02	N/A	-S-XXX-02-01	N/A	N/A	S-XXX-01-01	-T-XXX-03-02	N/A	N/A	S-XXX-03-01	S-XXX-03-02
-TTL	-T-XXX-02-01	1	1	1	T1	N/A	-T-XXX-01-01	-T-XXX-02-01	N/A	-S-XXX-02-02	N/A	N/A	S-XXX-01-02	-T-XXX-03-01	N/A	N/A	S-XXX-03-02	
		2	1	N-1	T1	-T-XXX-02-01	N/A	N/A	-T-XXX-01-01	N/A	S-XXX-01-02	S-XXX-02-02	N/A	N/A	-T-XXX-03-01	S-XXX-03-02	N/A	
		3	1	N	T1	-T-XXX-02-02	N/A	N/A	-T-XXX-01-02	N/A	S-XXX-01-01	S-XXX-02-01	N/A	N/A	-T-XXX-03-02	S-XXX-03-01	N/A	
		4	1	N	T1	-T-XXX-02-02	N/A	N/A	-T-XXX-01-02	N/A	S-XXX-01-01	S-XXX-02-01	N/A	N/A	-T-XXX-03-02	S-XXX-03-01	N/A	
-TBR	-T-XXX-01-01	1	1	1	T1	N/A	-T-XXX-01-02	-T-XXX-02-02	N/A	-S-XXX-02-01	N/A	N/A	S-XXX-01-01	-T-XXX-03-02	N/A	N/A	S-XXX-03-01	
		2	1	2	T1	N/A	-T-XXX-01-01	-T-XXX-02-01	N/A	-S-XXX-02-02	N/A	N/A	S-XXX-01-02	-T-XXX-03-01	N/A	N/A	S-XXX-03-02	
		3	1	N-1	T1	-T-XXX-02-01	N/A	N/A	-T-XXX-01-01	N/A	S-XXX-01-02	S-XXX-02-02	N/A	N/A	-T-XXX-03-01	S-XXX-03-02	N/A	
		4	1	N	T1	-T-XXX-02-02	N/A	N/A	-T-XXX-01-02	N/A	S-XXX-01-01	S-XXX-02-01	N/A	N/A	-T-XXX-03-02	S-XXX-03-01	N/A	
-TBL	-T-XXX-02-01	1	1	1	B20	-T-XXX-02-02	N/A	N/A	-T-XXX-01-02	N/A	S-XXX-01-01	S-XXX-02-01	N/A	N/A	-T-XXX-03-02	S-XXX-03-01	N/A	
		2	1	2	B20	-T-XXX-02-01	N/A	N/A	-T-XXX-01-01	N/A	S-XXX-01-02	S-XXX-02-02	N/A	N/A	-T-XXX-03-01	S-XXX-03-02	N/A	
		3	1	N-1	B20	N/A	-T-XXX-01-01	-T-XXX-02-01	N/A	-S-XXX-02-02	N/A	N/A	S-XXX-01-02	S-XXX-03-01	N/A	N/A	S-XXX-03-02	
		4	1	N	B20	N/A	-T-XXX-01-02	-T-XXX-02-02	N/A	-S-XXX-02-01	N/A	N/A	S-XXX-01-01	-T-XXX-03-02	N/A	N/A	S-XXX-03-01	
-STR	-S-XXX-01-01	1	1	1	B1	N/A	-T-XXX-01-01	-T-XXX-02-01	N/A	-S-XXX-02-02	N/A	N/A	S-XXX-01-02	-T-XXX-03-01	N/A	N/A	S-XXX-03-02	
		2	1	2	B1	N/A	-T-XXX-01-02	-T-XXX-02-02	N/A	-S-XXX-02-01	N/A	N/A	S-XXX-01-01	-T-XXX-03-02	N/A	N/A	S-XXX-03-01	
		3	1	N-1	B1	-T-XXX-02-01	N/A	N/A	-T-XXX-01-01	N/A	S-XXX-01-02	S-XXX-02-02	N/A	N/A	-T-XXX-03-01	S-XXX-03-02	N/A	
		4	1	N	B1	-T-XXX-02-02	N/A	N/A	-T-XXX-01-02	N/A	S-XXX-01-01	S-XXX-02-01	N/A	N/A	-T-XXX-03-02	S-XXX-03-01	N/A	
-STL	-S-XXX-02-01	1	1	1	T20	N/A	-T-XXX-02-01	-T-XXX-02-01	N/A	-S-XXX-02-02	N/A	N/A	S-XXX-01-02	-T-XXX-03-01	N/A	N/A	S-XXX-03-02	
		2	1	2	T20	-T-XXX-02-02	N/A	N/A	-T-XXX-01-02	N/A	S-XXX-01-01	S-XXX-02-01	N/A	N/A	-T-XXX-03-02	S-XXX-03-01	N/A	
		3	1	N-1	T20	N/A	-T-XXX-01-01	-T-XXX-02-01	N/A	-S-XXX-02-01	N/A	N/A	S-XXX-01-01	-T-XXX-03-02	N/A	N/A	S-XXX-03-01	
		4	1	N	T20	N/A	-T-XXX-01-02	-T-XXX-02-02	N/A	-S-XXX-02-02	N/A	N/A	S-XXX-01-02	-T-XXX-03-01	N/A	N/A	S-XXX-03-02	
-SBR	-S-XXX-01-01	1	1	1	T20	-T-XXX-02-01	N/A	N/A	-T-XXX-01-01	N/A	S-XXX-01-02	S-XXX-02-02	N/A	N/A	-T-XXX-03-01	S-XXX-03-02	N/A	
		2	1	2	T20	-T-XXX-02-02	N/A	N/A	-T-XXX-01-02	N/A	S-XXX-01-01	S-XXX-02-01	N/A	N/A	-T-XXX-03-02	S-XXX-03-01	N/A	
		3	1	N-1	T20	N/A	-T-XXX-01-01	-T-XXX-02-01	N/A	-S-XXX-02-01	N/A	N/A	S-XXX-01-01	-T-XXX-03-02	N/A	N/A	S-XXX-03-01	
		4	1	N	T20	N/A	-T-XXX-01-02	-T-XXX-02-02	N/A	-S-XXX-02-02	N/A	N/A	S-XXX-01-02	-T-XXX-03-01	N/A	N/A	S-XXX-03-02	
-SBL	-S-XXX-02-01	1	1	1	B1	N/A	-T-XXX-01-01	-T-XXX-02-01	N/A	-S-XXX-02-02	N/A	N/A	S-XXX-01-02	-T-XXX-03-01	N/A	N/A	S-XXX-03-02	
		2	1	2	B1	N/A	-T-XXX-01-02	-T-XXX-02-02	N/A	-S-XXX-02-01	N/A	N/A	S-XXX-01-01	-T-XXX-03-02	N/A	N/A	S-XXX-03-01	
		3	1	N-1	B1	-T-XXX-02-01	N/A	N/A	-T-XXX-01-01	N/A	S-XXX-01-02	S-XXX-02-02	N/A	N/A	-T-XXX-03-01	S-XXX-03-02	N/A	
		4	1	N	B1	-T-XXX-02-02	N/A	N/A	-T-XXX-01-02	N/A	S-XXX-01-01	S-XXX-02-01	N/A	N/A	-T-XXX-03-02	S-XXX-03-01	N/A	
-TEU	-T-XXX-03-01	1	1	1	B20	-T-XXX-02-02	N/A	N/A	-T-XXX-01-02	N/A	S-XXX-01-01	S-XXX-02-01	N/A	N/A	-T-XXX-03-02	S-XXX-03-01	N/A	
		2	1	2	B20	-T-XXX-02-01	N/A	N/A	-T-XXX-01-01	N/A	S-XXX-01-02	S-XXX-02-02	N/A	N/A	-T-XXX-03-01	S-XXX-03-02	N/A	
		3	1	N-1	B20	N/A	-T-XXX-01-01	-T-XXX-02-01	N/A	-S-XXX-02-02	N/A	N/A	S-XXX-01-02	-T-XXX-03-01	N/A	N/A	S-XXX-03-02	
		4	1	N	B20	N/A	-T-XXX-01-02	-T-XXX-02-02	N/A	-S-XXX-02-01	N/A	N/A	S-XXX-01-01	-T-XXX-03-02	N/A	N/A	S-XXX-03-01	
-TED	-T-XXX-03-01	1	1	1	T1	N/A	-T-XXX-01-02	-T-XXX-02-02	N/A	-S-XXX-02-01	N/A	N/A	S-XXX-01-02	-T-XXX-03-01	N/A	N/A	S-XXX-03-02	
		2	1	2	T1	N/A	-T-XXX-01-01	-T-XXX-02-01	N/A	-S-XXX-02-02	N/A	N/A	S-XXX-01-01	-T-XXX-03-02	N/A	N/A	S-XXX-03-01	
		3	1	N-1	T1	-T-XXX-02-01	N/A	N/A	-T-XXX-01-01	N/A	S-XXX-01-02	S-XXX-02-02	N/A	N/A	-T-XXX-03-01	S-XXX-03-02	N/A	
		4	1	N	T1	-T-XXX-02-02	N/A	N/A	-T-XXX-01-02	N/A	S-XXX-01-01	S-XXX-02-01	N/A	N/A	-T-XXX-03-02	S-XXX-03-01	N/A	
-SEU	-S-XXX-03-01	1	1	1	B1	N/A	-T-XXX-01-01	-T-XXX-02-01	N/A	-S-XXX-02-02	N/A	N/A	S-XXX-01-02	-T-XXX-03-01	N/A	N/A	S-XXX-03-02	
		2	1	2	B1	N/A	-T-XXX-01-02	-T-XXX-02-02	N/A	-S-XXX-02-01	N/A	N/A	S-XXX-01-01	-T-XXX-03-02	N/A	N/A	S-XXX-03-01	
		3	1	N-1	B1	-T-XXX-02-01	N/A	N/A	-T-XXX-01-01	N/A	S-XXX-01-02	S-XXX-02-02	N/A	N/A	-T-XXX-03-01	S-XXX-03-02	N/A	
		4	1	N	B1	-T-XXX-02-02	N/A	N/A	-T-XXX-01-02	N/A	S-XXX-01-01	S-XXX-02-01	N/A	N/A	-T-XXX-03-02	S-XXX-03-01	N/A	
-SED	-S-XXX-03-01	1	1	1	T20	-T-XXX-02-01	N/A	N/A	-T-XXX-01-01	N/A	S-XXX-01-02	S-XXX-02-02	N/A	N/A	-T-XXX-03-01	S-XXX-03-02	N/A	
		2	1	2	T20	-T-XXX-02-02	N/A	N/A	-T-XXX-01-02	N/A	S-XXX-01-01	S-XXX-02-01	N/A	N/A	-T-XXX-03-02	S-XXX-03-01	N/A	
		3	1	N-1	T20	N/A	-T-XXX-01-01	-T-XXX-02-01	N/A	-S-XXX-02-01	N/A	N/A	S-XXX-01-02	-T-XXX-03-01	N/A	N/A	S-XXX-03-02	
		4	1	N	T20	N/A	-T-XXX-01-02	-T-XXX-02-02	N/A	-S-XXX-02-02	N/A	N/A	S-XXX-01-01	-T-XXX-03-02	N/A	N/A	S-XXX-03-01	
-TPU	-T-XXX-03-01	1	1	1	B20	-T-XXX-02-02	N/A	N/A	-T-XXX-01-02	N/A	S-XXX-01-01	S-XXX-02-01	N/A	N/A	-T-XXX-03-02	S-XXX-03-01	N/A	
		2	1	2	B20	-T-XXX-02-01	N/A	N/A	-T-XXX-01-01	N/A	S-XXX-01-02	S-XXX-02-02	N/A	N/A	-T-XXX-03-01	S-XXX-03-02	N/A	
		3	1	N-1	B20	N/A	-T-XXX-01-01	-T-XXX-02-01	N/A	-S-XXX-02-02	N/A	N/A	S-XXX-01-02	-T-XXX-03-01	N/A	N/A	S-XXX-03-02	
		4	1	N	B20	N/A	-T-XXX-01-02	-T-XXX-02-02	N/A	-S-XXX-02-01	N/A	N/A	S-XXX-01-01	-T-XXX-03-02	N/A	N/A	S-XXX-03-01	
-TPD	-T-XXX-03-01	1	1	1	T1	N/A	-T-XXX-01-02	-T-XXX-02-02	N/A	-S-XXX-02-01	N/A	N/A	S-XXX-01-02	-T-XXX-03-01	N/A	N/A	S-XXX-03-02	
		2	1	2	T1	N/A	-T-XXX-01-01	-T-XXX-02-01	N/A	-S-XXX-02-02	N/A	N/A	S-XXX-01-01	-T-XXX-03-02	N/A	N/A	S-XXX-03-01	
		3	1	N-1	T1	-T-XXX-02-01	N/A	N/A	-T-XXX-01-01	N/A	S-XXX-01-02	S-XXX-02-02	N/A	N/A	-T-XXX-03-01	S-XXX-03-02	N/A	
		4	1	N	T1	-T-XXX-02-02	N/A	N/A	-T-XXX-01-02	N/A	S-XXX-01-01	S-XXX-02-01	N/A	N/A	-T-XXX-03-02	S-XXX-03-01	N/A	
-SPU	-S-XXX-03-01	1	1	1	B1	N/A	-T-XXX-01-01	-T-XXX-02-01	N/A	-S-XXX-02-02	N/A	N/A	S-XXX-01-02	-T-XXX-03-01	N/A	N/A	S-XXX-03-02	
		2	1	2	B1	N/A	-T-XXX-01-02	-T-XXX-02-02	N/A	-S-XXX-02-01	N/A	N/A	S-XXX-01-01	-T-XXX-03-02	N/A	N/A	S-XXX-03-01	
		3	1	N-1	B1	-T-XXX-02-01	N/A	N/A	-T-XXX-01-01	N/A	S-XXX-01-02	S-XXX-02-02	N/A	N/A	-T-XXX-03-01	S-XXX-03-02	N/A	
		4	1	N	B1	-T-XXX-02-02	N/A	N/A	-T-XXX-01-02	N/A	S-XXX-01-01	S-XXX-02-01	N/A	N/A	-T-XXX-03-02	S-XXX-03-01	N/A	
-SPD	-S-XXX-03-01	1	1	1	T20	-T-XXX-02-01	N/A	N/A	-T-XXX-01-01	N/A	S-XXX-01-02	S-XXX-02-02	N/A	N/A	-T-XXX-03-01	S-XXX-03-02	N/A	
		2	1	2	T20	-T-XXX-02-02	N/A	N/A	-T-XXX-01-02	N/A	S-XXX-01-01	S-XXX-02-01	N/A	N/A	-T-XXX-03-02	S-XXX-03-01	N/A	
		3	1	N-1	T20	N/A	-T-XXX-01-01	-T-XXX-02-01	N/A	-S-XXX-02-01	N/A	N/A	S-XXX-01-02	-T-XXX-03-01	N/A	N/A	S-XXX-03-02	
		4	1	N	T20	N/A	-T-XXX-01-02	-T-XXX-02-02	N/A	-S-XXX-02-02	N/A	N/A	S-XXX-01-01	-T-XXX-03-02	N/A	N/A	S-XXX-03-01	

**FOR RT1 OPTION SUB ASSEMBLY ADD -RT1 TO THE END OF THE SUB ASSEMBLY CALLOUT LISTED IN THE TABLE ABOVE.**

**PROPRIETARY NOTE**  
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.



520 PARK EAST BLVD. NEW ALBANY, IN 47150  
PHONE: 812-944-6733 FAX: 812-948-5047  
e-Mail: info@SAMTEC.com code: 55322

DO NOT SCALE DRAWING  
SHEET SCALE: 1:25:1

DESCRIPTION:  
0.8mm HIGH-SPEED COAX CABLE ASSEMBLY  
DWG. NO. EQCD-XXX-XX.XX-XXX-XXX-X-X  
BY: KEVIN B 02/19/03 SHEET 7 OF 7