

DESIGNED AND DIMENSIONED IN MILLIMETERS
ALL DIMENSIONS REFERENCE EXCEPT AS SHOWN

DO NOT
SCALE FROM
THIS PRINT

ASSEMBLY ENGLTH LIMITS [cm]										
FIBER TYPE	MIN						MAX			
	END OPTION						HEAT SINK			
	-21	-22	-27	-2A	-2C	-2E	-1	-2	-3	-4
-5	13	13	12	9	11	10	100	100	50	100
-6	13	13	12	11	11	10	100	100	50	100
-7	16	16	14	13	15	12	300	300	300	300
-8	14	14	12	11	13	10	300	300	300	300

TABLE 2: LENGTH TOLERANCE	
ASSEMBLY LENGTH [cm]	TOLERANCE [cm]*
000-016	±0.16
017-999	±1%

* ROUNDED UP TO 2 DECIMAL PLACES

ETUO-Y12-XX-XXX-0-X-1-X-XX


DATA RATE
-10: 10.3125 Gbps
-12: 12.5 Gbps

END OPTION
-21: MTP® MALE
-22: MTP® FEMALE
-27: MXC® INTERNAL PLUG
-2A: VITA 66.1/66.4 READY (SEE NOTE 8)
-2C: MT38999 MALE (SEE NOTE 9)
-2E: MPO PLUS® BAYONET MALE


ASSEMBLY LENGTH
-XXX: LENGTH (cm)
(SEE TABLES 1 & 2)

FIBER TYPE
-5: BLACK JACKETED RIBBON WITH BOOT
-6: BLACK JACKETED RIBBON
-7: BLACK LOOSE TUBE WITH BOOT
-8: BLACK LOOSE TUBE


HEAT SINK
-1: FLAT
-2: PIN FIN
-3: FLAT WITH GROOVE (SEE NOTE 2)
-4: PCIe® PIN FIN




ETUO-Y12-XX-XXX-0-1-1-5-21 SHOWN



VIEW "A"-"A"
END OPTIONS -21/-22/-2E







ETUO-Y12-XX-XXX-0-1-1-5-27 SHOWN




VIEW "B"-"B"
END OPTION -27
(SEE NOTE 1)

- NOTES:
1. QUANTITY OF LENSES PRESENT MAY VARY.
 2. FIBER POSITION DOES NOT CHANGE REGARDLESS OF THE NUMBER OF LENSES PRESENT.
 3. GROOVE ALLOWS ONE JACKETED RIBBON (FIBER TYPE -5/-6) OF CABLE LENGTH MAX 50 cm OR TWO CABLES OF JACKETED LOOSE TUBE (FIBER TYPE -7/-8) TO PASS ABOVE HEAT SINK AND UNDER COLD PLATE.
 4. FIREFLY MUST BE INSTALLED IN A NO-TENSION STATE FREE FROM DYNAMIC FLEXING.
 5. ALL MTP®/MPO ARE INTERMATABLE WITH CONNECTORS ADHERING TO TIA-604-5.
 6. ALL CABLES WITH A LENGTH GREATER THAN 50cm ARE LABELED.
 7. LABEL TO CONTAIN PART NUMBER AND SERIAL NUMBER INFORMATION.
 8. DUST CAPS REMOVED FROM ALL VIEWS FOR CLARITY.
 9. YELLOW LATCH PINS NOT SHOWN FOR CLARITY. SEE FIREFLY INSTALLATION INSTRUCTIONS FOR MORE DETAILS.
 10. FOR USE WITH TE VITA 66.1 (2000974-1) AND VITA 66.4 (2226881-1) DAUGHTER CARD PART NUMBERS.
 11. ASSEMBLIES SHIPPED WITH AMPHENOL PART NUMBER CF-594711-01S INSTALLED.
 12. DIMENSIONED FROM THE CENTER OF THE ALIGNMENT PIN HOLE AS SHOWN ON THE UEC5/UCC8 CONNECTOR FOOTPRINT.
 13. DUE TO THE COMPLIANT NATURE OF FIBER CABLE AND THE MOLDED FIBER BOOT COMPONENTS, THE DIMENSIONS SHOWN ARE FOR GUIDANCE ONLY.
 14. EACH APPLICATION IS UNIQUE AND MAY RESULT IN UNIQUE CLEARENCE DIMENSIONS FOR THE CABLE ESCAPE.

PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.	 520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code 55322
DO NOT SCALE DRAWING SHEET SCALE: 1:1	DESCRIPTION: EXTENDED TEMPERATURE OPTICAL FIREFLY ASM DWG. NO. ETUO-Y12-XX-XXX-0-X-1-X-XX BY: AARON B. 08/13/2020 SHEET 1 OF 11




* PROPRIETARY NOTE * THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.	 520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322	
	DESCRIPTION: EXTENDED TEMPERATURE OPTICAL FIREFLY ASM	
SHEET SCALE: 1:1 DO NOT SCALE DRAWING	DWG. NO. ETUO-Y12-XX-XXX-0-X-1-X-XX	
	BY: AARON B. 08/13/2020 SHEET 2 OF 11	



ETUO-Y12-XX-XXX-0-1-1-7-2A SHOWN




ETUO-Y12-XX-XXX-0-1-1-7-21 SHOWN




ETUO-Y12-XX-XXX-0-1-1-7-2C SHOWN



ETUO-Y12-XX-XXX-0-1-1-7-22 SHOWN



ETUO-Y12-XX-XXX-0-1-1-7-2E SHOWN



ETUO-Y12-XX-XXX-0-1-1-7-27 SHOWN

• PROPRIETARY NOTE •
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

SHEET SCALE: 1:1
DO NOT SCALE DRAWING




520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322


DESCRIPTION:
EXTENDED TEMPERATURE OPTICAL FIREFLY ASM

DWG. NO.
ETUO-Y12-XX-XXX-0-X-1-X-XX


BY: AARON B. 08/13/2020 SHEET 3 OF 11




ETUO-Y12-XX-XXX-0-1-1-8-2A SHOWN




ETUO-Y12-XX-XXX-0-1-1-8-21 SHOWN




ETUO-Y12-XX-XXX-0-1-1-8-2C SHOWN



ETUO-Y12-XX-XXX-0-1-1-8-22 SHOWN



ETUO-Y12-XX-XXX-0-1-1-8-2E SHOWN



ETUO-Y12-XX-XXX-0-1-1-8-27 SHOWN

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.


DO NOT SCALE DRAWING

SHEET SCALE: 1:1




520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322


DESCRIPTION:
EXTENDED TEMPERATURE OPTICAL
FLYREY ASM
DWG. NO.
ETUO-Y12-XX-XXX-0-X-1-X-XX
BY: AARON B. 08/13/2020 SHEET 4 OF 11




7 NO LOAD ON HEAT SINK
6.9 LOAD > 16N ON HEAT SINK




-1 FLAT HEAT SINK






8.1 NO LOAD ON HEAT SINK
8 LOAD > 16N ON HEAT SINK






-3 FLAT HEAT SINK WITH PASS THROUGH



KEEP OUT AREA FOR DE-MATING
TYPICAL FOR HEAT SINKS -1/-2/-3/-4
REFER TO UEC5 FOOTPRINT DRAWING
FOR DETAILED KEEPOUT AREAS



-2 PIN-FIN HEAT SINK



-4 LOW-PROFILE PIN-FIN HEAT SINK

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

SHEET SCALE: 1:1
DO NOT SCALE DRAWING


samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322


DESCRIPTION:
EXTENDED TEMPERATURE OPTICAL FIREFLY ASM

DWG. NO.
ETUO-Y12-XX-XXX-0-X-1-X-XX


BY: AARON B. 08/13/2020 SHEET 5 OF 11




-5 FIBER TYPE, ≤ 50 cm LENGTH




-5 FIBER TYPE, > 50 cm LENGTH




-6 FIBER TYPE, ≤ 50 cm LENGTH



-6 FIBER TYPE, > 50 cm LENGTH



-7 FIBER TYPE



-8 FIBER TYPE

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

SHEET SCALE: 1:1
DO NOT SCALE DRAWING



samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:
EXTENDED TEMPERATURE OPTICAL FIREFLY ASM



DWG. NO.
ETUO-Y12-XX-XXX-0-X-1-X-XX

BY: AARON B. 08/13/2020 SHEET 6 OF 11




-5/-6 FIBER TYPE, -21/-22 END OPTION
DUST CAPS/PLUGS NOT SHOWN FOR CLARITY


SAMTEC PART NUMBER
OPA-S-1-F SHOWN FOR REFERENCE



-5/-6 FIBER TYPE, -21/-22 END OPTION MATED WITH BULKHEAD
DUST CAPS/PLUGS NOT SHOWN FOR CLARITY




-5/-6 FIBER TYPE, -27 END OPTION
DUST CAPS/PLUGS NOT SHOWN FOR CLARITY



-5/-6 FIBER TYPE -2A END OPTION
DUST CAPS/PLUGS NOT SHOWN FOR CLARITY

VITA 66.4 CONNECTOR HOUSING NOT INCLUDED WITH ASSEMBLY,
SHOWN FOR REFERENCE ONLY.



-5/-6 FIBER TYPE -2A END OPTION WITH VITA 66.4 INSTALLED
DUST CAPS/PLUGS NOT SHOWN FOR CLARITY

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

SHEET SCALE: 1:1
DO NOT SCALE DRAWING


samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322


DESCRIPTION:
EXTENDED TEMPERATURE OPTICAL FIREFLY ASM

DWG. NO.
ETUO-Y12-XX-XXX-0-X-1-X-XX


BY: AARON B. 08/13/2020 SHEET 7 OF 11




-2C END OPTION



-2C END OPTION RECOMMENDED PANEL CUTOUT



-2E END OPTION



-2E END OPTION MATED WITH BULKHEAD

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

SHEET SCALE: 1:1
DO NOT SCALE DRAWING




520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DESCRIPTION:
EXTENDED TEMPERATURE OPTICAL FIREFLY ASM


DWG. NO.
ETUO-Y12-XX-XXX-0-X-1-X-XX

BY: AARON B. 08/13/2020 SHEET 8 OF 11




-7/-8 FIBER TYPE, -21/-22 END OPTION
DUST CAPS/PLUGS NOT SHOWN FOR CLARITY


SAMTEC PART NUMBER
OPA-S-1-F SHOWN FOR REFERENCE



-7/-8 FIBER TYPE, -21/-22 END OPTION MATED WITH BULKHEAD
DUST CAPS/PLUGS NOT SHOWN FOR CLARITY




-7/-8 FIBER TYPE, -27 END OPTION
DUST CAPS/PLUGS NOT SHOWN FOR CLARITY



-7/-8 FIBER TYPE -2A END OPTION
DUST CAPS/PLUGS NOT SHOWN FOR CLARITY

VITA 66.4 CONNECTOR HOUSING NOT INCLUDED WITH ASSEMBLY,
SHOWN FOR REFERENCE ONLY



-7/-8 FIBER TYPE -2A END OPTION WITH VITA 66.4 INSTALLED
DUST CAPS/PLUGS NOT SHOWN FOR CLARITY

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

SHEET SCALE: 1:1
DO NOT SCALE DRAWING


samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322


DESCRIPTION:
EXTENDED TEMPERATURE OPTICAL FIREFLY ASM

DWG. NO.
ETUO-Y12-XX-XXX-0-X-1-X-XX


BY: AARON B. 08/13/2020 SHEET 9 OF 11




-7/-8 FIBER TYPE, -2C END OPTION



-2C END OPTION RECOMMENDED PANEL CUTOUT
mm [in]



-7/-8 FIBER TYPE, -2E END OPTION



-7/-8 FIBER TYPE, -2E END OPTION MATED WITH BULKHEAD

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

SHEET SCALE: 1:1
DO NOT SCALE DRAWING




520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322


DESCRIPTION:
EXTENDED TEMPERATURE OPTICAL FIREFLY ASM

DWG. NO.
ETUO-Y12-XX-XXX-0-X-1-X-XX


BY: AARON B. 08/13/2020 SHEET 10 OF 11




-5 FIBER TYPE RECOMMENDED CABLE ESCAPE CLEARANCE



-6 FIBER TYPE RECOMMENDED CABLE ESCAPE CLEARANCE



-7 FIBER TYPE RECOMMENDED CABLE ESCAPE CLEARANCE



-8 FIBER TYPE RECOMMENDED CABLE ESCAPE CLEARANCE

• PROPRIETARY NOTE •
THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

SHEET SCALE: 1:1
DO NOT SCALE DRAWING



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DESCRIPTION:
EXTENDED TEMPERATURE OPTICAL FIREFLY ASM

DWG. NO.
ETUO-Y12-XX-XXX-0-X-1-X-XX

BY: AARON B. 08/13/2020 SHEET 11 OF 11