



DESIGNED AND DIMENSIONED IN INCHES[MILLIMETERS]
ALL DIMENSIONS REFERENCE EXCEPT AS SHOWN

DO NOT
SCALE FROM
THIS PRINT

GPCC-20-X-X-X-XX-XXXX-SD-2

SIZE
-20: SIZE 20
SERIES
-V: VNX, 50 OHM
GENDER
-S: SOCKET
TYPE
-C: CABLE
OPTION
-2
ORIENTATION
-SD: DIRECT SOLDER
CABLE CALLOUT
-047A: CCA-047-PFA
FINISH
-GG: 10μ" GOLD CENTER CONTACT
10μ" GOLD FERRULE



- NOTES:
- 1. MATERIAL:
CONTACT, FERRULE, OUTER CONTACT, CLIP: BERYLLIUM COPPER.
HOOD: STAINLESS STEEL.
FORWARD BEAD: PCTFE.
REAR BEAD: PEEK VICTREX.
 - 2. FINISH:
CONTACT, FERRULE: 10μ" MIN GOLD OVER 50μ" MIN NICKEL.
OUTER CONTACT: 30μ" MIN GOLD OVER 50μ" MIN NICKEL.
CLIP: ELECTRO-POLISH
HOOD: PASSIVATED

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING
SHEET SCALE: 12:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DESCRIPTION:
GPCC, SOCKET, ST, CONTACT ASSEMBLY
DWG. NO.
GPCC-20-X-X-X-XX-XXXX-SD-2

BY: MATT M. 10/12/2021 SHEET 1 OF 2

