

REVISION F												
"F"±0.08[.003]												
							Ø7.01[.276] K-DOT276375005 FIG 3 -K OPTION (SOME FEATURES NOT SHOWN FOR CLARITY)					
								PTION 2	No C	TABLE 4 IF POS IRU -30	"P (("A" - 7.01	
		••• ۳/ ۲/						-WT -BL	-10 TH -09, -13, -25, -3 -10 TH	7, -40 THRU -100 IRU -30 7, -40 THRU -100 IRU -30 7, -40 THRU -100	(("F" - 7.01[- (("S" - 7.01[- (("U" - 7.01]	.276]) / 2)
										TABLE 5		
	(DIFFEREI	<u>FI0</u> FOR POSITIONS -40, -49, -50, -60 HTEC8-160-01- NT AS SHOWN, C E FEATURES NOT	,-70, -80, -90, -1 X-DV-A SHOWI DTHERWISE SAM	00 N 1E AS FIG 1)			CAR THICKN -01 -03	ESS		"Y" "Z" 5.60 [.220] 7.00 [.276 6.39 [.252] 7.79 [.307		"AB" 4.32 [.170] 5.11 [.201]
TABLE 3												
No OF "F" POSITIONS "F"	"G"	"H"	"J"	"K"	"L"	"M"	"N"					
-09 15.00 [.591] -13 18.20 [.717]	11.800 [.4646] 15.000 [.5906]	4.500 [.1772] 6.100 [.2402]	2.400 [.094] 4.000 [.157]	5.30 [.209] 6.90 [.272]	9.60 [.378] 12.80 [.504]	12.60 [.496] 15.80 [.622]	9.60 [.378 12.80 [.504					
-25 27.80 [1.094] -37 37.40 [1.472] -40 39.80 [1.567]	24.600 [.9685] 34.200 [1.3465] 36.600 [1.4409]	6.100 [.2402] 18.100 [.7126] 18.900 [.7441]	4.000 [.157] 16.000 [.630] 16.800 [.661]	16.50 [.650] 14.10 [.555] 15.70 [.618]	22.40 [.882] 32.00 [1.260] 34.40 [1.354]	25.40 [1.000] 35.00 [1.378] 37.40 [1.472]	22.40 [.882 32.00 [1.26 34.40 [1.35	* *	PROPRIETARY NOTE SCUMENT CONTAINS CONFIDENTIAL AND ETARY INFORMATION AND ALL DESIGN, ACTURING, REPRODUCTION, USE, PATENT RIGHTS LES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,	sar	nte	
-49 47.00 [1.850] -50 47.80 [1.882] -60 55.80 [2.197]	43.800 [1.7244] 44.600 [1.7559] 52.600 [2.0709]	22.900 [.9016] 26.900 [1.0591]	20.800 [.819] 20.800 [.819] 24.800 [.976]	18.90 [.744] 19.70 [.776] 23.70 [.933]	41.60 [1.638] 42.40 [1.669] 50.40 [1.984]	44.60 [1.756] 45.40 [1.787] 53.40 [2.102]	42.40 [1.66 50.40 [1.98	9 OK PAR REPROD 0THER WRITTE	IS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE T, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR TUGED, TRANSFERRED OR INCOMPORATED IN ANY PROJECT IN ANY MANNER WITHOUT THE EXPRESS N CONSENT OF SAMTEC, INC.	520 PARK EAST BLVD, PHONE: 812-944-6733 e-Mail info@SAMTEC DESCRIPTION:	NEW ALBANY, IN 4 FAX: 812-948-5	047
-70 63.80 [2.512] -80 71.80 [2.827] -90 79.80 [3.142] -100 87.80 [3.457]	60.600 [2.3858] 68.600 [2.7008] 76.600 [3.0157] 84.600 [3.3307]	26.900 [1.0591] 26.900 [1.0591]	24.800 [.976] 24.800 [.976] 24.800 [.976] 24.800 [.976]	31.70 [1.248] 39.70 [1.563] 47.70 [1.878] 55.70 [2.193]	58.40 [2.299] 66.40 [2.614] 74.40 [2.929] 82.40 [3.244]	61.40 [2.417] 69.40 [2.732] 77.40 [3.047] 85.40 [3.362]	66.40 [2.61 74.40 [2.92	4] !9]	DO NOT SCALE DRAWING	0.8mm HIGH SPEED DWG. NO. HTEC8-1XXX-XX-		

F:\DWG\MISC\MKTG\HTEC8-1XXX-XX-DV-XX-X-XX-MKT.SLDDRW

BY: JERRY SU 08/11/2018 SHEET 2 OF 4

REVISION	F
----------	---

TABLE 6									
No OF POS	"S"	"Ţ"							
-09	19.60 [.772]	17.30 [.681]							
-10	17.20 [.677]	14.90 [.587]							
-13	22.80 [.898]	20.50 [.807]							
-20	25.20 [.992]	22.90 [.902]							
-25	32.40 [1.276]	30.10 [1.185]							
-30	33.20 [1.307]	30.90 [1.217]							
-37	42.00 [1.654]	39.70 [1.563]							
-40	44.40 [1.748]	42.10 [1.657]							
-49	51.60 [2.031]	49.30 [1.941]							
-50	52.40 [2.063]	50.10 [1.972]							
-60	60.40 [2.378]	58.10 [2.287]							
-70	68.40 [2.693]	66.10 [2.602]							
-80	76.40 [3.008]	74.10 [2.917]							
-90	84.40 [3.323]	82.10 [3.232]							
-100	92.40 [3.638]	90.10 [3.547]							





