


DO NOT
SCALE FROM
THIS PRINT

FIG 1

-A: ALIGNMENT PIN OPTION
(QTS-048-01-XXX-D-DP-A SHOWN)

NOTES:

1. Ⓢ REPRESENTS A CRITICAL DIMENSION.
2. NOTE DELETED.
3. NOTE DELETED.
4. MINIMUM TERMINAL RETENTION: 5 OZ.
5. MINIMUM GROUND PLANE RETENTION: 1 LB.
6. NOTE DELETED.
7. PARTS TO BE MOLDED TO POSITION.
8. NOTE DELETED.
9. NOTE DELETED.
10. NOTE DELETED.
11. -L PLATING CAN BE SUBSTITUTED FOR -F PLATING.
12. NOTE DELETED.
13. LEAD STYLES -03 THRU -06: TOP BODY (QTS) CANNOT HAVE -A OPTION.
14. NOTE DELETED.
15. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -LC OPTION IS NOT COMPATIBLE WITH AUTO PLACEMENT. SAMTEC RECOMMENDS MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -LC OPTION.
16. MINIMUM ROW TO ROW IS .152. PIN CAN EXTEND PAST WALL .003 MAX.
17. AVAILABLE FOR EXISTING CUSTOMERS ONLY.
18. TRAYS ARE STANDARD PACKAGING.
19. ORDERS WILL BE PACKAGED ACCORDING TO THE SAMTEC PACKAGING EFFICIENCY STANDARDS (SPES) FOUND ON WWW.SAMTEC.COM.
20. ATTACH LABEL -4X2 TO EACH REEL.
21. NOTE DELETED.
22. DIMENSION MEASURED, ON EACH BANK, FROM A PLANE CREATED FROM THE SIGNAL PINS.
23. COPLANARITY INCLUDES SIGNAL PINS AND GROUND PLANES.

No OF POSITIONS

-016, -032, -048,
**-064, **-080
(PER ROW)

**SEE NOTE 17

LEAD STYLE

-01: .1680 [4.267]
-02: .2861 [7.264]
-03: .4042 [1.123]
-04: .6000 [15.240]
-05: .7180 [18.237]
-06: .8360 [21.234]

PLATING SPECIFICATION

-F: 3μ" FLASH SELECTIVE GOLD, MATTE TIN TAILS
(USE T-1SXX-XX-F & T-1G1-XX-F) (SEE NOTE 11)
-L: 10μ" LIGHT SELECTIVE GOLD, MATTE TIN TAILS
(USE T-1SXX-XX-L & T-1G1-XX-L)
-H: 30μ" HEAVY GOLD, 3μ" GOLD TAILS
(USE T-1SXX-XX-H & T-1G1-XX-G)
-STL: 30μ" HEAVY SELECTIVE GOLD, TIN LEAD TAILS
(USE T-1SXX-XX-STL & T-1G1-XX-STL)
-FTL: 3μ" FLASH SELECTIVE GOLD, TIN LEAD TAILS
(USE T-1SXX-XX-FTL & T-1G1-XX-FTL)

Ⓢ = SEE SHEET 3

* = NOT ENGINEERING APPROVED

PACKAGING

BLANK: TRAY (SEE NOTES 18 & 19)
-TR: TAPE & REEL (SEE NOTES 19 & 20)
(48 POS MAX)
-FR: FULL REEL QTY TAPE & REEL
(SEE NOTES 19 & 20)
(48 POS MAX)

PICK & PLACE OPTION

-K: POLYIMIDE FILM
(SEE FIG 3, SHT 2)
(USE K-DOT-.276-.375-.005)

OPTION


-A: ALIGNMENT PINS (SEE FIG 1)
(USE QTS-25-01-D-XX-A)
-LC: LOCKING CLIPS (SEE FIG 2, NOTE 15)
(USE LC-08-TM-01)
-GP: GUIDE POST, (SEE FIG 6, SHT4)
(AVAILABLE ON STYLE -01 ONLY)

-DP: DIFFERENTIAL PAIRS

ROW SPECIFICATION

-D: DOUBLE (USE QTS-25-XX-D-XX
& QTS-25-XX-D-XX)

No OF BANKS



SECTION "A"-"A"

TABLE 6

No. OF POS	"D"	"E"
-016	.788 [20.00]	.728 [18.48]
-032	1.575 [40.01]	1.515 [38.48]
-048	2.363 [60.01]	2.303 [58.48]
-064	3.150 [80.01]	3.090 [78.49]
-080	3.938 [100.01]	3.878 [98.49]

TABLE 2

No OF POSITIONS	COPLANARITY (INCLUDES GP)
-016 THRU -048	.004 [10]
-064 & -080	.006 [15]

TABLE 1

STYLE	"A"	"B"	BODY	GROUND PLANE	TERMINAL	MATED HEIGHT WITH QSS-01-DP
-01	.1680 [4.27]	.1600 [4.06]	QTS-25-01-D-XX	T-1G1-01-XXX	T-1S56-01-XXX	.197 [5.00] REF
-02	.2861 [7.27]	.2781 [7.06]	QTS-25-02-D-XX	T-1G1-02-XXX	T-1S56-22-XXX	.315 [8.00] REF

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS: .XX: ±.01 [3]
.XXX: ±.005 [13]
.XXXX: ±.0020 [0.51]

ANGLES

± 2°

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL:

DO NOT SCALE DRAWING

SHEET SCALE: 1.5:1

INSULATOR: LCP, UL94V-0; COLOR: BLACK
TERMINAL & GROUND PLANE: PHOS BRONZE

DESCRIPTION:

.635mm DIFFERENTIAL PAIRS HS TERMINAL ASSEMBLY

DWG. NO.

QTS-XXX-XX-XXX-D-DP-XX-X-XX

BY: KEVIN B

09/14/2010

SHEET 1 OF 4

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322





FIG 2
-LC: LOCKING CLIP OPTION
(QTS-048-01-XXX-D-DP-LC SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)




FIG 3
-K: POLYIMIDE FILM PAD

TABLE 7	
No OF POS	"S"
-016	.256 [6.50]
-032	.650 [16.51]
-048	1.043 [26.49]
-064	1.437 [36.50]
-080	1.831 [46.51]

TABLE 4	
STYLE	"C"
-01	.173 [4.39]
-02	.291 [7.39]
-03	.409 [10.39]
-04	.605 [15.37]
-05	.723 [18.36]
-06	.841 [21.36]

c:\enterprisevault\DWG\MISC\MKTG\QTS-XXX-XX-XXX-D-DP-XX-X-XX-MKT.SLDDRW

• PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2.5:1

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
.635mm DIFFERENTIAL PAIRS HS TERMINAL ASSEMBLY

DWG. NO.
QTS-XXX-XX-XXX-D-DP-XX-X-XX

BY: KEVIN B 09/14/2010 SHEET 2 OF 4

TABLE 5					MATED HEIGHT WITH QSS-01-DP
STYLE	"A"	GROUND PLANE	TERMINAL	SPACER BODY	
-03	.4042 [10.267]	T-1G1-03-XXX	T-1S51-03-XXX	QTSH-25-01-D-XX-X	.433 [11.00] REF
-04	.6000 [15.240]	T-1G1-04-XXX	T-1S51-04-XXX	QTSH-25-01-D-XX-X	.630 [16.00] REF
-05	.7180 [18.237]	T-1G1-05-XXX	T-1S51-05-XXX	QTSH-25-02-D-XX-X	.748 [19.00] REF
-06	.8360 [21.234]	T-1G1-06-XXX	T-1S51-06-XXX	QTSH-25-02-D-XX-X	.866 [22.00] REF





FIG 4
QTS-048-03-XXX-D-DP-LC SHOWN
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)



SECTION "B"-"B"




FIG 5
(QTS-048-04-XXX-D-DP-A SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)
(STYLE -03, -04, -05 & -06)

c:\enterprisevault\DWG\MISC\MKTG\QTS-XXX-XX-XXX-D-DP-XX-X-XX-MKT.SLDDRW

• PROPRIETARY NOTE •
THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 1.75:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
.635mm DIFFERENTIAL PAIRS HS TERMINAL ASSEMBLY

DWG. NO.
QTS-XXX-XX-XXX-D-DP-XX-X-XX

BY: KEVIN B 09/14/2010 SHEET 3 OF 4




FIG 6
-GP: GUIDE POST SHOWN
(QTS-048-01-XXX-D-DP-GP SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)
(AVAILABLE ON STYLE -01 ONLY)

TABLE 8		
POS	"F"	"G"
-016	1.305 [33.15]	1.013 [25.72]
-032	2.093 [53.15]	1.800 [45.72]
-048	2.880 [73.15]	2.588 [65.72]
-064	3.668 [93.15]	3.375 [85.73]
-080	4.455 [113.16]	4.163 [105.73]

c:\enterprisevault\DWG\MISC\MKTG\QTS-XXX-XX-XXX-D-DP-XX-X-XX-MKT.SLDDRW

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING
SHEET SCALE: 2:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
.635mm DIFFERENTIAL PAIRS HS TERMINAL ASSEMBLY

DWG. NO.
QTS-XXX-XX-XXX-D-DP-XX-X-XX

BY: KEVIN B 09/14/2010 SHEET 4 OF 4