


DO NOT
SCALE FROM
THIS PRINT


NOTES:

1. REPRESENTS A CRITICAL DIMENSION.
2. SAMTEC LOGO TO APPEAR ON SURFACE AS SHOWN, APPROXIMATELY 4.83[.190] x 17.78[.700], RECESSED 0.25[.010].
3. MOLDED SURFACES SHALL HAVE MATTE FINISH, SURFACES TO BE FREE OF SCRATCHES, NICKS, SINK AREAS, VOIDS, OR OTHER BLEMISHES.
4. MOLD TO BE INSERTED TO ACCEPT DIFFERENT CABLE DIAMETERS.
5. ALL EJECTOR PIN AND GATE LOCATIONS MUST BE APPROVED BY SAMTEC PRODUCT ENGINEERING.
6. ANY ADDITIONAL VOIDING AND/OR MODIFICATIONS TO VOIDING MUST BE APPROVED BY SAMTEC PRODUCT ENGINEERING.
7. ALL DRAFT MUST BE WITHIN THE SPECIFIED TOLERANCES.
8. ALL INSIDE/OUTSIDE RADII 0.13[.005] MAX UNLESS OTHERWISE STATED.
9. FOR ALL LENGTHS, TOLERANCE SHALL BE $\pm 2\%$.
10. ASSEMBLY TO BE 100% HI-POT TESTED AT 300V FOR OPENS AND SHORTS. TEST TO BE DONE AFTER IN-PROCESS 2 AND IN-PROCESS 4.
11. MINIMUM LATCH PUSHOUT FORCE: 2.2N[.50LB]
12. ASSEMBLY TO BE BULK PACKAGED WITH ASBBLT4X5.5 ON EACH END PER PACKAGING STANDARD CO-RF-WI-3001-M.
13. DELETED
14. DELETED
15. REFER TO CRIMP SPECIFICATION PRINT FOR CRIMP AND STRIP DIMENSIONS, TOLERANCES, AND TOOLING.
16. CONTACT MUST BE INSERTED UNTIL RETENTION FEATURE LOCKS INTO PLACE, TO BE VIEWED FROM THE FRONT CORE.
17. CONTACT MUST FULLY BE INSIDE OF THE RC5B-XX-D & RC5-XX-D BODY.
18. REFER TO MD-XXX-XX-XXXXX-XX FOR SAMTEC MATERIAL PART NUMBER.
19. CABLE SURROUND INCLUDES 2 JOINING RC5R-XX-D PARTS.



DETAIL 'A'
SCALE 2 : 1

TABLE 2	
No. OF POS.	"C"
-10	15.88 [.625]
-15	22.23 [.875]
-20	28.58 [1.125]



DETAIL 'B'
SCALE 4 : 1

C:\EnterpriseVault\DWG\MISC\MKTG\RC5-XX-XX-X-XX-XX-XX-MKT.SLDRW

RC5-XX-XX-X-X-XX.XX-XX

No OF POSITIONS
-10, -15, -20
(PER ROW)

LEAD STYLE
-01

PLATING SPECIFICATION
-H: 30μ" HEAVY GOLD IN CONTACT
AREA, 3μ" GOLD ON TAIL
-G: 10μ" GOLD IN CONTACT
AREA, 3μ" GOLD ON TAIL

END OPTION
-D: DOUBLE ENDED (SEE FIG. 1)
-BC: BLUNT CUT (SEE FIG. 2)

CABLE LENGTH*
-XX.XX:
(00.25M [9.842] MIN
- 50.00M [1968.504] MAX)"

ROW SPECIFICATION
-D: DOUBLE

*NOTE: -02.00, -03.00, AND -05.00 ARE CATALOG STANDARD LENGTHS. FOR OTHER LENGTHS CONTACT SAMTEC.

DESIGNED & DIMENSIONED
IN MILLIMETERS[INCHES]




FIG 1
RC5-10-XX-X-D-X.XX-D SHOWN

TABLE 1				
PART NUMBER	CABLE	END 1	END 2	"B"
RC5-XX-XX-X-D-XX.XX-D	BWC-05-XX-01	C-203-2830-X	C-203-2830-X	14.12 [.556]
RC5-XX-XX-X-D-XX.XX-BC	BWC-05-XX-01	C-203-2830-X	NA	7.06 [.278]

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN MILLIMETERS.
TOLERANCES ARE:
DECIMALS ANGLES
X.X: ± 0.3 [.01]
X.XX: ± 0.13 [.005]
X.XXX: ± 0.051 [.0020]

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING
INSULATOR: LCP, COLOR: BLACK
CABLE: PVC JACKET/COPPER CONDUCTORS
O-RING: NBR
CONTACT: PHOS BRONZE MAX FLASH ALLOWED: .05[.002]
PREMOLD: RITEFLEX 640-RD3056P62-BLACK MAX GATE VESTIGE: .05[.002]
OVERMOLD: ZYTEL PA70G13L 52-91908BKS; MAX REGRIND: 10%
LATCH: BeCu

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:
RECTANGULAR ACCLIMATE
DWG. NO.
RC5-XX-XX-X-X-XX.XX-XX
BY: B RAY 06/18/2008 SHEET 1 OF 3

-BC: BLUNT CUT
ADD LABEL-ET (BOTH ENDS)
(BUILD DOUBLE-ENDED INITIALLY FOR E-TEST)







FIG 2
RC5-10-XX-X-D-XX.XX-BC SHOWN
(SAME AS FIG. 1, EXCEPT AS SHOWN)

-BC: BLUNT CUT
IN-PROCESS 5



IN-PROCESS 1
ADD RC5B-XX-D TO RC5-XX-D



SECTION "D"-"D"
SCALE 2 : 1

IN-PROCESS 2
STRIP, CRIMP, & ADD RC5-XX-D & RC5R-XX-D




TABLE 4 (BWC-05-XX-01)

END 1 POS	WIRE COLOR	END 2 POS	END 1 POS	WIRE COLOR	END 2 POS
1	BLACK	1	21	ORANGE/BLACK STRIPE	21
2	BROWN	2	22	YELLOW/BLACK STRIPE	22
3	RED	3	23	GREEN/BLACK STRIPE	23
4	ORANGE	4	24	GRAY/BLACK STRIPE	24
5	YELLOW	5	25	PINK/BLACK STRIPE	25
6	GREEN	6	26	PINK/RED STRIPE	26
7	BLUE	7	27	PINK/BLUE STRIPE	27
8	PURPLE	8	28	PINK/GREEN STRIPE	28
9	GREY	9	29	LIGHT BLUE	29
10	WHITE	10	30	LIGHT BLUE/BLACK STRIPE	30
11	PINK	11	31	LIGHT BLUE/RED STRIPE	31
12	LIGHT GREEN	12	32	LIGHT BLUE/BLUE STRIPE	32
13	BLACK/WHITE STRIPE	13	33	LIGHT BLUE/GREEN STRIPE	33
14	BROWN/WHITE STRIPE	14	34	GRAY/RED STRIPE	34
15	RED/WHITE STRIPE	15	35	GRAY/GREEN STRIPE	35
16	ORANGE/WHITE STRIPE	16	36	PURPLE/BLACK	36
17	GREEN/WHITE STRIPE	17	37	BLUE/BLACK	37
18	BLUE/WHITE STRIPE	18	38	LIGHT GREEN/BLACK	38
19	PURPLE/WHITE STRIPE	19	39	LIGHT GREEN/RED	39
20	RED/BLACK STRIPE	20	40	LIGHT GREEN/BLUE	40

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 1:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:
RECTANGULAR ACCLIMATE

DWG. NO.
RC5-XX-XX-X-X-XX.XX-XX

BY: B RAY 06/18/2008 SHEET 2 OF 3

