



SECTION "A"-A"

	"A"	"B"	"C"
HASL	0.041	.036±.002	0.005 MAX
GOLD	0.041	.038±.002	N/A
SILVER	0.041	.038±.002	N/A
TIN	0.041	.038±.002	N/A

## NOTE:

1. MAX HARDNESS OF COPPER LAYER: 150 KNOOP.
2. CONTACT SAMTEC FOR INSERTION TOOLING: P/N CAT-PT-PTX-1XX-X-X