

REVISION H

DIMENSIONS ARE IN INCHES

UNLESS OTHERWISE NOTED

TOLERANCES ARE:

ONE PLACE DECIMALS $\pm .1$
TWO PLACE DECIMALS $\pm .01$ THREE PLACE DECIMALS $\pm .005$
FOUR PLACE DECIMALS $\pm .0020$ ANGLES
 $\pm 2^\circ$


TITLE:

THRU-HOLE
TERMINAL STRIP
.018 DIA POST

DWG NO:

TSF-1XX-01-XX-X-XX

SHEET 1 OF 1



TSF-1XX-01-XX-X-XX

No. OF POSITIONS PER ROW
-01 THRU -40 (SINGLE ROW)
-01 THRU -36 (DOUBLE ROW)

POLARIZING OPTION
POLARIZED POSITION
SPECIFY OMITTED PIN

LEAD STYLE
-01: T-1RS7-01-X-2


ROW SPECIFICATION
-S: SINGLE ROW
(USE TLW-40-S)
-D: DOUBLE ROW
(USE TLW-36-D)

PLATING SPECIFICATIONS
-S: SELECTIVE (USE T-1RS7-01-R-2)
-T: TIN (USE T-1RS7-01-T-2)
-D: GOLD (USE T-1RS7-01-D-2)
-SM: SELECTIVE GOLD / MATTE TIN TAIL
(USE T-1RS7-01-S-2)

.018 DIA REF

2° MAX SWAY
EITHER DIRECTION

.060 REF.



2° MAX TOE
EITHER DIRECTION

2° MAX TOE
EITHER DIRECTION

NOTES:

- 1.) TERMINAL PUSHOUT FORCE: 1 lbs MIN.
- 2.) © REPRESENTS A CRITICAL DIMENSION FOR STATISTICAL PROCESS CONTROL USE.
- 3.) MAXIMUM CUT FLASH: .010
- 4.) MAXIMUM FLASH ALLOWED IN THIS AREA: .020

* PROPRIETARY NOTE *

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

samtec

EXISTPROD/ASSEMBLY/100
TSF-ASM

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: REIDINGER 11-23-92
CHECKED BY: MCCARTIN

ENG.
APPROVAL
DEM

TSF-1XX-01-XX-X-XX
SHEET 1 OF 1