


REVISION T

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED	TOLERANCES ARE:
ONE PLACE DECIMALS $\pm .1$	THREE PLACE DECIMALS $\pm .005$	ANGLES $\pm 2^\circ$	
TWO PLACE DECIMALS $\pm .01$	FOUR PLACE DECIMALS $\pm .0020$		

TITLE: DOUBLE ROW SURFACE MOUNT TERMINAL STRIP .018 DIA POST	DWG NO: TSF-1XX-02-XX-D-XX SHEET 1 OF 1
---	--



TSF-1XX-02-XX-D-XX



No. OF POSITIONS ————
-02 THRU -36

LEAD STYLE ————
-02: T-1RS7-01-XX-2

PLATING SPECIFICATIONS ————
S: SELECTIVE (USE T-1RS7-01-R-2)
T: TIN (USE T-1RS7-01-T-2)
TM: MATTE TIN (USE T-1RS7-01-TM-2)
SM: SELECTIVE GOLD/MATTE TIN TAIL (USE T-1RS7-01-SM-2)

POLARIZING OPTION
POLARIZED POSITION
SPECIFY OMITTED PIN

ROW SPECIFICATION
-D: DOUBLE ROW
(USE TLW-36-D)




- NOTES:
- 1.) TERMINAL PUSHOUT FORCE: 1 POS MIN
 - 2.) Ø REPRESENTS A CRITICAL DIMENSION FOR STATISTICAL PROCESS CONTROL USE.
 - 3.) COPLANARITY: PECS:
P-2 POS: .006
23-29 POS: .008
30-36 POS: .010
 - 4.) PARTS TO BE PACKAGED IN TUBES (4 POS MIN)
(USE PT-1-03-15 & TP-03 2/TUBE)
 - 5.) 00 PARTS POS 1 FIRST IN SAME DIRECTION
ARROW.
 - 6.) MAXIMUM CUT FLASH: .010
 - 7.) MAXIMUM FLASH ALLOWED IN THIS AREA: .020

* PROPRIETARY NOTE *

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT ANY MANNER WITHOUT THE EXPRESS

PACKAGE AS SHOWN



EP/ASM/100
TSFf-1XX-02-XX-D-XX

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: REIDINGER 2-1-91
CHECKED BY: ECKERT

ENG. APPROVAL PAE	TSF-1XX-02-XX-D-XX SHEET 1 OF 1
-------------------------	------------------------------------