


REVISION Q

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED TOLERANCES ARE:		TITLE: SINGLE ROW SURFACE MOUNT TERMINAL STRIP .018 SQ POST	DWG NO: TSF-1XX-02-XX-S-XX
ONE PLACE DECIMALS $\pm .1$	THREE PLACE DECIMALS $\pm .005$	ANGLES $\pm 2^\circ$	FOUR PLACE DECIMALS $\pm .0020$		SHEET 1 OF 1
TWO PLACE DECIMALS $\pm .01$					

DO NOT SCALE FROM THIS PRINT



TSF-1XX-02-XX-S-XX

No. OF POSITIONS -02 THRU -40

LEAD STYLE -02: T-1RS7-01-XX-2

PLATING SPECIFICATIONS

-S: SELECTIVE (USE T-1RS7-01-R-2)

-T: TIN (USE T-1RS7-01-T-2)



-TM: MATTE TIN (USE T-1RS7-01-TM-2)

-SM: SELECTIVE GOLD/MATTE TIN TAIL (USE T-1RS7-01-RM-2)

POLARIZING OPTION

POLARIZED POSITION SPECIFY OMITTED PIN

ROW SPECIFICATION -S: SINGLE ROW (USE TLW-40-S)




NOTES:

- 1.) TERMINAL PUSHOUT FORCE: 1 lbs MIN.
- 2.) Ⓢ REPRESENTS A CRITICAL DIMENSION.
- 3.) COPLANARITY SPECS:
2-22 POS: .006
23-29 POS: .008
30-36 POS: .010
- 4.) PARTS TO BE PACKAGED IN TUBES (USE PT-1-24-01-17 & TP-24 2/TUBE) 4 POSTION MIN.
- 5.) LOAD PARTS POS 1 FIRST IN SAME DIRECTION AS ARROW.
- 6.) MAXIMUM CUT FLASH: .010
- 7.) MAXIMUM FLASH ALLOWED IN THIS AREA: .020


C1-A,I-MV

PACKAGE AS SHOWN

PT-1-24-01-17



(SEE NOTES 4 & 5)



IN-PROCESS VIEW
SHEAR TAILS TO .125

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC INC.

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: GARY PURVIS 12-3-91	ENG. APPROVAL: ECKERT	TSF-1XX-02-XX-S-XX
CHECKED BY: ECKERT	PAE	SHEET 1 OF 1

MISC MKT
TSF-1XX-02-XX-S-XX-MKT