

FEP CABLE OPTION
*T: FEP INSULATION
(LEAVE BLANK FOR STANDARD
PVC INSULATION)

No OF POSITIONS
-02, -03, -04, -05,
-06, -07, -08, -09,
-10

PLATING SPECIFICATION
-T: BRIGHT ACID TIN (BAT)
-L: 10 μ " SELECTIVE GOLD IN CONTACT
AREA, BRIGHT ACID TIN (BAT) ON THE TAIL.
-S: 30 μ " SELECTIVE GOLD IN CONTACT
AREA, BRIGHT ACID TIN (BAT) ON THE TAIL.



LATCHING
(LEAVE BLANK FOR PANEL MOUNT LATCH)
**-L1: NON-PANEL MOUNT LATCH

PINOUT
(LEAVE BLANK FOR SINGLE ENDED ASSEMBLY)
-M1: METAL LATCH 1 TO 1
-M2: METAL LATCH 1 TO N
-P1: PLASTIC LATCH 1 TO 1
-P2: PLASTIC LATCH 1 TO N

ASSEMBLY LENGTH
SPECIFY IN INCHES
SINGLE ENDED: 03.0 INCH MINIMUM
DOUBLE ENDED, 2-4 POSITIONS: 04.0 INCH MINIMUM
DOUBLE ENDED, 5-10 POSITIONS: 05.0 INCH MINIMUM

COLOR CODE
C: COLOR CODE WIRE
(SEE COLOR SEQUENCE TABLE, SHEET 3)
(LEAVE BLANK FOR STANDARD WIRE) (* = NOT TOOLED)
NOT AVAILABLE WITH UMPIT (** = NOT RELEASED)

WIRE GAUGE
-16: 16 AWG
(UMPI USES 16 AWG 300 VOLT PVC)
*(UMPIIT USES 16 AWG 600 VOLT FEP)
-18: 18 AWG
(UMPI USES 18 AWG 300 VOLT PVC)
*(UMPIIT USES 18 AWG 300 VOLT FEP)



NOTES:

1. ALL ASSEMBLIES TO BE 100% ELECTRICALLY TESTED FOR SHORTS AND OPENS.
2. ALL FINISHED GOODS ARE TO BE ELECTRICAL TESTED INCLUDING HI-POT TEST @ 1000 VOLTS DC. AFTER FINAL ELECTRICAL TEST, MARK EACH ASSEMBLY PER INSTRUCTIONS REFERENCED IN CO-{AD-ID}-WI-3092-M.
3. FOR LENGTHS LESS THAN 12 IN, TOLERANCE SHALL BE ± 1.25 . FOR OTHER LENGTHS, TOLERANCES SHALL BE $\pm 2\%$.
4. SUPPORT 13-21 GAUGE PANEL.
5. PARTS TO BE INDIVIDUALLY PACKAGED IN A ASBBLTXXXXX BUBBLE BAG.

FIG 1
UMPIX-04-X-XX-XX.X SHOWN

* PROPRIETARY NOTE *

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL:
INSULATOR: LCP
CONTACT: COPPER ALLOY
HOLDER: NYLON

DO NOT SCALE DRAWING
SHEET SCALE: 2:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.COM code 55322

DESCRIPTION:
2MM ULTRA MICRO POWER CABLE

DWG. NO.
UMPIX-XX-X-XXX-XX.X-XX-XX

BY: JACK Z 09/23/2021 SHEET 1 OF 5




FIG 4
UMPIX-04-X-XX-XX.X-L1 SHOWN
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)




FIG 2
UMPIX-04-X-XX-XX.X-M1 SHOWN
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)

TABLE 2

No. OF POS	"C"	"D"	"E"	"F"
-02	15.38 [.606]	9.95 [.392]	14.55 [.573]	12.85 [.506]
-03	17.38 [.684]	11.95 [.470]	16.55 [.652]	14.85 [.585]
-04	19.38 [.763]	13.95 [.549]	18.55 [.730]	16.85 [.663]
-05	21.38 [.842]	15.95 [.628]	20.55 [.809]	18.85 [.742]
-06	23.38 [.920]	17.95 [.707]	22.55 [.888]	20.85 [.821]
-07	25.38 [.999]	19.95 [.785]	24.55 [.967]	22.85 [.900]
-08	27.38 [1.078]	21.95 [.864]	26.55 [1.045]	24.85 [.978]
-09	29.38 [1.157]	23.95 [.943]	28.55 [1.124]	26.85 [1.057]
-10	31.38 [1.235]	25.95 [1.022]	30.55 [1.203]	28.85 [1.136]

c:\enterprisevault\DWG\MISC\MKTG\UMPIX-XX-X-XXX-XX.X-XX-XX-MKT.SLDDRW

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DO NOT SCALE DRAWING

SHEET SCALE: 3:2

DESCRIPTION: 2MM ULTRA MICRO POWER CABLE

DWG. NO. UMPIX-XX-X-XXX-XX.X-XX-XX

BY: JACK Z 09/23/2021 SHEET 2 OF 5




FIG 3
UMPIX-04-X-XX-XX.X-P1 SHOWN
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)

UMPI COLOR CODED WIRE SEQUENCE										
PIN #	COLOR									
	BROWN	RED	ORANGE	YELLOW	GREEN	BLUE	VIOLET	GRAY	WHITE	BLACK
1	2	3	4	5	6	7	8	9	10	

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

SHEET SCALE: 3:2


samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DESCRIPTION:
2MM ULTRA MICRO POWER CABLE


DWG. NO.
UMPIX-XX-X-XXX-XX.X-XX-XX

BY: JACK Z 09/23/2021 SHEET 3 OF 5



EXPLODED VIEW

TABLE 4						
SERIES	WIRE GAUGE	VOLTAGE	BODY	HOLDER	CONTACT	CABLE
UMPI	16 AWG	300V	END 1: S-UMPI-XX-XX END 2-MX: SUB-UMPC-XX-ML END 2-PX: UMPC-XX-P	UMPCC-XX-01	C-489-01-X	DWC-16-XX-300
	18 AWG			UMPCC-XX-02		DWC-18-XX-300
UMPIT	16 AWG	600V		UMPCC-XX-03	C-489-02-X	TBD
	18 AWG	300V		UMPCC-XX-04	C-489-03-X	SEE NOTE 11



RECOMMENDED PANEL CUTOUT

TABLE 3		
No. OF POS	"G"	"H"
-02	17.45 [.687]	13.25 [.522]
-03	19.45 [.766]	15.25 [.600]
-04	21.45 [.844]	17.25 [.679]
-05	23.45 [.923]	19.25 [.758]
-06	25.45 [1.002]	21.25 [.837]
-07	27.45 [1.081]	23.25 [.915]
-08	29.45 [1.159]	25.25 [.994]
-09	31.45 [1.238]	27.25 [1.073]
-10	33.45 [1.317]	29.25 [1.152]

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

SHEET SCALE: 3:2
DO NOT SCALE DRAWING




520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322


DESCRIPTION:
2MM ULTRA MICRO POWER CABLE

DWG. NO.
UMPIX-XX-X-XXX-XX.X-XX-XX

BY: JACK Z 09/23/2021 SHEET 4 OF 5



IN-PROCESS 1
CONTACT WITH CABLE AND HOLDER INSTALLATION



IN-PROCESS 2
BODY INSTALLATION

PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.	samtec 520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322		
	DESCRIPTION: 2MM ULTRA MICRO POWER CABLE		
	DWG. NO. UMPIX-XX-X-XXX-XX.X-XX-XX		
	BY: JACK Z 09/23/2021 SHEET 5 OF 5		