


Series: LSS 0,635mm (.025") Razor Beam™ High Speed Hermaphroditic Terminal/Socket Strip

LSS Series – Terminal/Socket, Vertical Orientation



Series: LSS 0,635mm (.025") Razor Beam™ High Speed Hermaphroditic Terminal/Socket Strip

1.0 SCOPE

1.1 This specification covers performance, testing and quality requirements for Samtec LSS Series 0,635 mm (.025") Razor Beam™ High Speed Hermaphroditic Terminal/Socket Strip connectors. All information contained in this specification is for two LSS Series connectors in a 6 mm mated height vertical configuration unless otherwise noted.

2.0 DETAILED INFORMATION

2.1 Product prints, footprints, catalog pages, test reports and other specific, detailed information can be found at www.samtec.com?LSS.

3.0 TESTING

3.1 Current Rating: 1.7 A (6 Adjacent Pins Powered)

3.2 Voltage Rating: 300 VAC

3.3 Operating Temperature Range: -55°C to +125°C

3.4 Electrical:

| ITEM | TEST CONDITION | REQUIREMENT |
|---------------------------|--|--|
| Withstanding Voltage | EIA-364-20 (No Flashover, Sparkover, or Breakdown) | 900 VAC |
| Insulation Resistance | EIA-364-21 (1000 MΩ minimum) | 5,000 MΩ |
| Contact Resistance (LLCR) | EIA-364-23 | Δ 15 mΩ maximum (Samtec defined)/ No damage |

3.5 Mechanical:

| ITEM | TEST CONDITION | REQUIREMENT | STATUS |
|------------------|--|---|--------|
| Durability | EIA-364-09C | 100 cycles | Pass |
| Random Vibration | EIA-364-28 Condition V, Letter B 7.56 G 'RMS', 50 to 2000 Hz, 2 hours per axis, 3 axis total , PSD 0.04 | Visual Inspection: No Damage LLCR: Δ 15 mΩ maximum Event Detection: No interruption > 50 Nanoseconds | Pass |
| Mechanical Shock | EIA-364-27 100 G, 6 milliseconds, sawtooth wave, 11.3 fps, 3 shocks/direction, 3 axis (18 total shocks) | Visual Inspection: No Damage LLCR: Δ 15 mΩ maximum Event Detection: No interruption > 50 Nanoseconds | Pass |
| Normal Force | EIA-364-04 | 30 grams minimum for gold interface | Pass |

Series: LSS 0,635mm (.025") Razor Beam™ High Speed Hermaphroditic Terminal/Socket Strip

3.6 Environmental:

| ITEM | TEST CONDITION | REQUIREMENT | STATUS |
|------------------------------|---|--|--------|
| Thermal Shock | EIA-364-32 Thermal Cycles: 100 (30 minute dwell) Hot Temp: 85°C Cold Temp: -55°C Hot/Cold Transition: Immediate | Visual Inspection: No Damage LLCR: Δ 15 m Ω DWV: 900 VAC IR: >25,000 M Ω | Pass |
| Thermal Aging (Temp Life) | EIA-364-17 Test Condition 4 @ 105°C Condition B for 250 hours | Visual Inspection: No Damage LLCR: Δ 15 m Ω DWV: 900 VAC IR: >25,000 M Ω | Pass |
| Cyclic Humidity | EIA-364-31 Test Temp: 25°C to 65°C Relative Humidity: 90 to 95% Test Duration: 240 hours | Visual Inspection: No Damage LLCR: Δ 15 m Ω DWV: 900 VAC IR: >25,000 M Ω | Pass |
| Gas Tight | EIA-364-36 Gas Exposure: Nitric Acid Vapor Duration: 60 min. Drying Temp.: 50°C +/- 3°C Measurements: Within 1 hour of Exposure | LLCR: Δ 15 m Ω | Pass |

Series: LSS 0,635mm (.025") Razor Beam™ High Speed Hermaphroditic Terminal/Socket Strip


4.0 MATED SYSTEM

4.1 Mated Views

Mated view information can be found at link below:

<http://cloud.samtec.com/Prints/LSS%20MATED%20VIEWS-MKT.pdf>

5.0 POLARIZING FEATURES



6.0 HIGH SPEED PERFORMANCE

6.1 Based on a 3 dB insertion loss

6.2 System Impedance: 50 ohm for single-ended and 100 ohm for differential pair



| Stack Height | Single-Ended Signaling | Differential Pair Signaling |
|--------------|------------------------|-----------------------------|
| 6 mm | 10.0 GHz/20.0 Gbps | 9.0 GHz/18.0 Gbps |

Series: LSS 0,635mm (.025") Razor Beam™ High Speed Hermaphroditic Terminal/Socket Strip


7.0 PROCESSING RECOMMENDATIONS

7.1 Mating Alignment Requirements:

7.1.1 Maximum guidance/capture in applications where at least one half of the interface is free to float.




7.1.2 The parts can be rigidly misaligned by no more than .002" (0,05 mm) in the X- and .002" (0,05 mm) in the Y-direction to ensure a good mate.




Series: LSS 0,635mm (.025") Razor Beam™ High Speed Hermaphroditic Terminal/Socket Strip

7.2 Mating Angle Requirements: Connectors to be mated and unmated axially only. Zippering angles may damage connector and/or solder joints.



7.2.1



7.2.2

7.3 Multiple Connector Applications: Due to the interlocking features and fine pitch of the LSXX (LSEM, LSS or LSHM) connectors, maintaining proper linear and angular alignment during mating and unmating is essential to minimize the potential for connector damage. As a result, Samtec highly recommends against the use of multiple LSXX connectors, mated simultaneously, per board. However, for applications requiring two or more simultaneously mated connectors per board, please review the [Multiple LSXX Connector Applications](#) document. For more information, please contact IPG@Samtec.com.

Series: LSS 0,635mm (.025") Razor Beam™ High Speed Hermaphroditic Terminal/Socket Strip

7.4 Due to variances in equipment, solder pastes and applications (board design, component density, etc.), Samtec does not specify a recommended reflow profile for our connectors. The processing parameters provided by the solder paste manufacturer should be employed and can usually be found on their website.

All of Samtec's surface mount components are lead free reflow compatible and compliant with the profile parameters detailed in IPC/JEDEC J-STD-020 which requires that components be capable of withstanding a peak temperature of 260°C as well as 30 seconds above 255°C.


Samtec Recommended Temperature Profile Ranges (SMT)

Sn-Pb Eutectic Assembly

| Preheat/Soak (100°C-150°C) | Max Ramp Up Rate | Reflow Time (above 183°C) | Peak Temp | Time within 5°C of 235°C | Max Ramp Down Rate | Time 25°C to Peak Temp |
|----------------------------|------------------|---------------------------|-----------|--------------------------|--------------------|------------------------|
| 60-120 sec. | 3°C/s max. | 40-150 sec. | 235°C | 20 sec. max. | 6°C/s max. | 6 min. max. |

Pb-Free Assembly

| Preheat/Soak (150°C-200°C) | Max Ramp Up Rate | Reflow Time (above 217°C) | Peak Temp | Time within 5°C of 260°C | Max Ramp Down Rate | Time 25°C to Peak Temp |
|----------------------------|------------------|---------------------------|-----------|--------------------------|--------------------|------------------------|
| 60-120 sec. | 3°C/s max. | 40-150 sec. | 260°C | 30 sec. max. | 6°C/s max. | 8 min. max. |



These guidelines should not be considered design requirements for all applications. Samtec recommends testing interconnects on your boards in your process to guarantee optimum results.

7.5 Maximum Reflow Passes: The parts can withstand three reflow passes at a maximum component temperature of 260°C.

Series: LSS 0,635mm (.025") Razor Beam™ High Speed Hermaphroditic Terminal/Socket Strip

7.6 Stencil Thickness: The stencil thickness is .006" (0,15 mm).

7.7 Placement: Machine placement of the parts is recommended.

7.8 Hardware: Board-to-board standoffs are recommended to provide a robust mechanical connection. Samtec offers two different types:

7.8.1 Traditional Standoffs (SO) – Rigid design to statically support board-to-board applications. See options here: [SO - Board Stacking Standoff](#)

7.8.2 Jack Screw Standoffs (JSO) – Serve same function as traditional standoffs but unique, nested construction facilitates the mating and unmating process. This is especially helpful for multiple connector applications where the mating and unmating forces increase with the number of connectors used. See options here: [JSO - Jack Screw Standoffs](#)

7.9 Reflow Environment: Samtec recommends the use of a low level oxygen environment (typically achieved through Nitrogen gas infusion) in the reflow process to improve solderability.

7.10 Cleaning: Samtec, Inc. has verified that our connectors may be cleaned in accordance with the solvents and conditions designated in the EIA-364-11 standard.

8.0 ADDITIONAL RESOURCES

8.1 For additional mechanical testing or product information, contact our Customer Engineering Support Group at CES@samtec.com

8.2 For additional information on high speed performance testing, contact our Signal Integrity Group at SIG@samtec.com

8.3 For additional processing information, contact our Interconnect Processing Group at IPG@samtec.com

8.4 For RoHS, REACH or other environmental compliance information, contact our Product Environmental Compliance Group at PEC@samtec.com

USE OF PRODUCT SPECIFICATION SHEET

This Product Specification Sheet ("PSS") is a brief summary of information related to the Product identified. As a summary, it should only be used for the limited purpose of considering the purchase/use of Product. For specific, detailed information, including but not limited to testing and Product footprint, refer to Section 2.0 of this document and the links there provided to test reports and prints. This PSS is the property of Samtec, Inc. ("Samtec") and contains proprietary information of Samtec, our various licensors, or both. Samtec does not grant express or implied rights or license under any patent, copyright, trademark or other proprietary rights and the use of the PSS for building, reverse engineering or replication is strictly prohibited. By using the PSS, the user agrees to not infringe, directly or indirectly, upon any intellectual property rights of Samtec and acknowledges that Samtec, our various licensors, or both own all intellectual property therein. The PSS is presented "AS IS". While Samtec makes every effort to present excellent information, the PSS is only provided as a guideline and does not, therefore, warrant it is without error or defect or that the PSS contains all necessary and/or relevant information about the Product. The user agrees that all access and use of the PSS is at its own risk. **NO WARRANTIES EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR OF ANY KIND WHATSOEVER ARE PROVIDED.**