




Project Number: Mixed Flowing Gas test report	Tracking Code: 2123966_Report_Rev_1
Requested by: Chad Humphres	Date: 1/2/2020
Part #: ARF6-16-S-D-A-K-TR/ARC6-16-XX-X-LU-LU-3-1	
Part description: ARF6-ARC6	Tech: Keney Chen
Test Start: 9/26/2019	Test Completed: 10/14/2019



(Actual part not depicted)

MIXED FLOWING GAS TEST REPORT

ARF6/ARC6

ARF6-16-S-D-A-K-TR/ARC6-16-XX-X-LU-LU-3-1

REVISION HISTORY

DATE	REV.NUM.	DESCRIPTION	ENG
1/2/2020	1	Initial Issue	KC

CERTIFICATION

All instruments and measuring equipment were calibrated to National Institute for Standards and Technology (NIST) traceable standards according to ISO 10012-1 and ANSI/NCSL 2540-1, as applicable.

All contents contained herein are the property of Samtec. No portion of this report, in part or in full shall be reproduced without prior written approval of Samtec.

SCOPE

To perform the following tests: Mixed Flowing Gas per EIA-364-65 test. Please see test plan.

APPLICABLE DOCUMENTS

Standards: EIA Publication 364.

TEST SAMPLES AND PREPARATION

- 1) All materials were manufactured in accordance with the applicable product specification.
- 2) All test samples were identified and encoded to maintain traceability throughout the test sequences.
- 3) After soldering, the parts to be used for LLCR testing were cleaned according to TLWI-0001.
- 4) Either an automated cleaning procedure or an ultrasonic cleaning procedure may be used.
- 5) The automated procedure is used with aqueous compatible soldering materials.
- 6) Parts not intended for testing LLCR are visually inspected and cleaned if necessary.
- 7) Any additional preparation will be noted in the individual test sequences.
- 8) Solder Information: Lead Free
- 9) Samtec Test PCBs used: PCB-110078-TST-01A

FLOWCHARTS

Mixed Flowing Gas

Note: LLCR - Minimum of 25% of the contact positions to be tested.

Group 1

ARF6-16-S-D-A-K-TR

ARC6-16-XX-X-LU-LU-3-1

8 Assemblies

Step	Description
1.	LLCR ⁽¹⁾
2.	Cycles Quantity = 20
3.	Thermal Age ⁽⁴⁾ - Non Standard Note: EIA-364-1000, Table 9, 60°C for 10 years.
4.	LLCR ⁽¹⁾ Max Delta = 10 mOhm
5.	Mixed Flowing Gas Unmated ⁽²⁾ Duration = 168 hrs Note: Half of samples mated. Half of samples unmated.
6.	LLCR ⁽¹⁾ Max Delta = 10 mOhm
7.	Mixed Flowing Gas Mated ⁽²⁾ Duration = 168 hrs Note: All samples mated.
8.	LLCR ⁽¹⁾ Max Delta = 10 mOhm
9.	Cycles Quantity = 1 Cycles Note: Manually unmated/mate the interconnect system once
10.	LLCR ⁽¹⁾ Max Delta = 10 mOhm

(1) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max
Test Current = 100 mA Max

(2) Mixed Flowing Gas Mated = EIA-364-65

Environmental Conditions = Class IIA

(3) Mixed Flowing Gas Unmated = EIA-364-65

Environmental Conditions = Class IIA

(4) Thermal Age = Other

Test Condition = 105°C
Time Condition = 66 Hours
EIA-364-17

ATTRIBUTE DEFINITIONS

The following is a brief, simplified description of attributes.

MATING/UNMATING:

- 1) Reference document: EIA-364-13, *Mating and Unmating Forces Test Procedure for Electrical Connectors*.
- 2) The full insertion position was to within 0.003" to 0.004" of the plug bottoming out in the receptacle to prevent damage to the system under test.
- 3) One of the mating parts is secured to a floating X-Y table to prevent damage during cycling.

Mixed Flowing Gas:

- 1) EIA-364-65B, *Mixed Flowing Test Procedure For Electrical Connectors Contacts And Sockets*.
- 2) To adequately evaluate the risk of corrosion, the Mixed Flowing Gas test shall be done with the gas mixtures in below table.

Table 1 - Environmental classes

Class	Relative humidity, %	Temperature, °C	Concentration, ppb			
			Cl ₂	NO ₂	H ₂ S	SO ₂
I	Discontinued as a test procedure.					
II	Superseded by class IIA					
IIA	70 ± 2	30 ± 1	10 ± 3	200 ± 50	10 ± 5	100 ± 20
III	Superseded by class IIIA					
IIIA	70 ± 2	30 ± 1	20 ± 5	200 ± 50	100 ± 20	200 ± 50
IV	75 ± 2	40 ± 2	30 ± 5	200 ± 50	200 ± 20	N/A

- 3) The mated and unmated exposure is done in parallel for qualification at Class IIA conditions.
- 4) Exposure time for mated and unmated is 14 days

LLCR:

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
 - a. ≤ +5.0 mOhms: ----- Stable
 - b. +5.1 to +10.0 mOhms: ----- Minor
 - c. +10.1 to +15.0 mOhms: ----- Acceptable
 - d. +15.1 to +50.0 mOhms: ----- Marginal
 - e. +50.1 to +1000 mOhms: ----- Unstable
 - f. >+1000 mOhms: ----- Open Failure

RESULTS**LLCR Mixed Flowing Gas Group (192 LLCR test points)**

- **Initial (Ground Pin) ----- 37.04 mOhms Max**
- **Initial (Signal Pin) -----172.41 mOhms Max**
- **Preprocessing, 20 Cycles and Thermal Age**
 - **<= +5.0 mOhms ----- 192 Points ----- Stable**
 - **+5.1 to +10.0 mOhms -----0 Points ----- Minor**
 - **+10.1 to +15.0 mOhms -----0 Points ----- Acceptable**
 - **+15.1 to +50.0 mOhms -----0 Points ----- Marginal**
 - **+50.1 to +1000 mOhms -----0 Points ----- Unstable**
 - **>+1000 mOhms -----0 Points ----- Open Failure**
- **7 Days Mixed Flowing Gas (with 4 Samples Unmated & 4 Samples Mated During Exposure)**
 - **<= +5.0 mOhms ----- 190 Points ----- Stable**
 - **+5.1 to +10.0 mOhms -----2 Points ----- Minor**
 - **+10.1 to +15.0 mOhms -----0 Points ----- Acceptable**
 - **+15.1 to +50.0 mOhms -----0 Points ----- Marginal**
 - **+50.1 to +1000 mOhms -----0 Points ----- Unstable**
 - **>+1000 mOhms -----0 Points ----- Open Failure**
- **14 Days Total Mixed Flowing Gas (with All 8 Samples Mated During Exposure)**
 - **<= +5.0 mOhms ----- 189 Points ----- Stable**
 - **+5.1 to +10.0 mOhms -----3 Points ----- Minor**
 - **+10.1 to +15.0 mOhms -----0 Points ----- Acceptable**
 - **+15.1 to +50.0 mOhms -----0 Points ----- Marginal**
 - **+50.1 to +1000 mOhms -----0 Points ----- Unstable**
 - **>+1000 mOhms -----0 Points ----- Open Failure**
- **1 Cycle**
 - **<= +5.0 mOhms ----- 182 Points ----- Stable**
 - **+5.1 to +10.0 mOhms ----- 10 Points ----- Minor**
 - **+10.1 to +15.0 mOhms -----0 Points ----- Acceptable**
 - **+15.1 to +50.0 mOhms -----0 Points ----- Marginal**
 - **+50.1 to +1000 mOhms -----0 Points ----- Unstable**
 - **>+1000 mOhms -----0 Points ----- Open Failure**

DATA SUMMARIES**LLCR Mixed Flowing Gas Group**

- 1). A total of 240 points were measured.
- 2). EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3). A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4). The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms:-----Stable
 - b. $+5.1$ to $+10.0$ mOhms: -----Minor
 - c. $+10.1$ to $+15.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms -----Unstable
 - f. $> +1000$ mOhms: -----Open Failure

LLCR Measurement Summaries by Pin Type					
Date	9/26/2019	9/29/2019	10/7/2019	10/14/2019	10/14/2019
Room Temp (Deg C)	23	23	23	22	22
Rel Humidity (%)	50	50	50	50	50
Technician	Keney Chen	Keney Chen	Keney Chen	Kason He	Kason He
mOhm values	Actual	Delta	Delta	Delta	Delta
	Initial	20 Cycles High Temp	7 Days MFG	14 Days MFG	1 Cycles
Pin Type 1: Signal					
Average	168.75	0.62	0.64	1.02	1.42
St. Dev.	1.08	0.62	0.87	1.15	1.51
Min	165.96	0.00	0.00	0.00	0.02
Max	172.41	4.80	5.73	8.09	9.37
Summary Count	160	160	160	160	160
Total Count	160	160	160	160	160
Pin Type 2: Ground					
Average	35.51	0.89	0.70	1.46	1.90
St. Dev.	0.88	0.78	0.65	1.61	1.59
Min	34.21	0.07	0.02	0.01	0.16
Max	37.04	3.55	2.82	5.99	5.90
Summary Count	32	32	32	32	32
Total Count	32	32	32	32	32

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
	≤ 5	>5 & ≤ 10	>10 & ≤ 15	>15 & ≤ 50	>50 & ≤ 1000	>1000
20 Cycles/High Temp	192	0	0	0	0	0
7 Days MFG	190	2	0	0	0	0
14 Days MFG	189	3	0	0	0	0
1 Cycles	182	10	0	0	0	0

EQUIPMENT AND CALIBRATION SCHEDULES

Equipment #: HZ-TCT-01

Description: Normal force analyzer

Manufacturer: Mecmesin Multitester

Model: Mecmesin Multitester 2.5-i

Serial #: 08-1049-04

Accuracy: Last Cal: 3/7/2019, Next Cal: 3/6/2020

Equipment #: HZ-MO-05

Description: Micro-ohmmeter

Manufacturer: Keithley

Model: 3706

Serial #: 1285188

Accuracy: Last Cal: 9/25/2019, Next Cal: 9/24/2020

Equipment #: DG-MFG-01

Description: Mixed Flow Gas Chamber

Manufacturer: Yamasaki

Model: GH-180

Serial #: 715

Accuracy: Last Cal: 12/5/2019, Next Cal: 12/3/2020