




Project Number: Design Qualification Test Report	Tracking Code: 230122_Report_Rev_2
Requested by: Matt Graston	Date: 7/2/2013
Part #: BCS-125-F-D-TE/TSM-125-01-F-DV-A	Tech: Troy Cook
Part description: BCS/TSM	Qty to test: 8
Test Start: 12/12/2012	Test Completed: 01/07/2013



DESIGN QUALIFICATION TEST REPORT

BCS/TSM

BCS-125-F-D-TE/TSM-125-01-F-DV-A

REVISION HISTORY

DATA	REV.NUM.	DESCRIPTION	ENG
04/19/2013	1	Initial Issue	KH
07/02/2013	2	Update the title page	KH

CERTIFICATION

All instruments and measuring equipment were calibrated to National Institute for Standards and Technology (NIST) traceable standards according to ISO 10012-1 and ANSI/NCSL 2540-1, as applicable.

All contents contained herein are the property of Samtec. No portion of this report, in part or in full shall be reproduced without prior written approval of Samtec.

SCOPE


To perform the following tests: Design Qualification test. Please see test plan.

APPLICABLE DOCUMENTS

Standards: EIA Publication 364

TEST SAMPLES AND PREPARATION

- 1) All materials were manufactured in accordance with the applicable product specification.
- 2) All test samples were identified and encoded to maintain traceability throughout the test sequences.
- 3) The automated procedure is used with aqueous compatible soldering materials.
- 4) Parts not intended for testing LLCR are visually inspected.
- 5) Any additional preparation will be noted in the individual test sequences.
- 6) Solder Information: Lead Free
- 7) Re-Flow Time/Temp: See accompanying profile.
- 8) Samtec Test PCBs used: PCB-104134-TST

TYPICAL OVEN PROFILE (Soldering Parts to Test Boards)

FLOWCHARTS**Durability/LLCR**

TEST STEP	GROUP A1 3u" Gold (-F) 8 Mated Sets
01	LLCR-1
02	10 Cycles
03	LLCR-2
04	Thermal Shock (Mated and Undisturbed)
05	LLCR-3
06	Cyclic Humidity (Mated and Undisturbed)
07	LLCR-4

Thermal Shock = EIA-364-32, Table II, Test Condition I:

-55°C to +85°C 1/2 hour dwell, 100 cycles

Humidity = EIA-364-31, Test Condition B (240 Hours)

and Method III (+25°C to +65°C @ 90% RH to 98% RH)

ambient pre-condition and delete steps 7a and 7b

LLCR = EIA-364-23, LLCR

20 mV Max, 100 mA Max

Use Keithley 580 or 3706 in 4 wire dry circuit mode

ATTRIBUTE DEFINITIONS

The following is a brief, simplified description of attributes.

THERMAL SHOCK:

- 1) EIA-364-32, *Thermal Shock (Temperature Cycling) Test Procedure for Electrical Connectors*.
- 2) Test Condition 1: -55°C to +85°C
- 3) Test Time: ½ hour dwell at each temperature extreme
- 4) Number of Cycles: 100
- 5) All test samples are pre-conditioned at ambient.
- 6) All test samples are exposed to environmental stressing in the mated condition.

HUMIDITY:

- 1) Reference document: EIA-364-31, *Humidity Test Procedure for Electrical Connectors*.
- 2) Test Condition B, 240 Hours.
- 3) Method III, +25° C to + 65° C, 90% to 98% Relative Humidity excluding sub-cycles 7a and 7b.
- 4) All samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

LLCR:

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
 - a. $\leq +5.0$ mOhms:----- Stable
 - b. +5.1 to +10.0 mOhms:----- Minor
 - c. +10.1 to +15.0 mOhms:----- Acceptable
 - d. +15.1 to +50.0 mOhms:----- Marginal
 - e. +50.1 to +2000 mOhms:----- Unstable
 - f. $>+2000$ mOhms:----- Open Failure

RESULTS**LLCR Durability:**

Initial-----4.98mOhms Max

- **Durability, 10 Cycles**
 - **<= +5.0 mOhms ----- 192 Points ----- Stable**
 - **+5.1 to +10.0 mOhms -----0 Points ----- Minor**
 - **+10.1 to +15.0 mOhms -----0 Points ----- Acceptable**
 - **+15.1 to +50.0 mOhms -----0 Points ----- Marginal**
 - **+50.1 to +2000 mOhms-----0 Points ----- Unstable**
 - **>+2000 mOhms -----0 Points ----- Open Failure**
- **Thermal Shock**
 - **<= +5.0 mOhms ----- 192 Points ----- Stable**
 - **+5.1 to +10.0 mOhms -----0 Points ----- Minor**
 - **+10.1 to +15.0 mOhms -----0 Points ----- Acceptable**
 - **+15.1 to +50.0 mOhms -----0 Points ----- Marginal**
 - **+50.1 to +2000 mOhms-----0 Points ----- Unstable**
 - **>+2000 mOhms -----0 Points ----- Open Failure**
- **Humidity**
 - **<= +5.0 mOhms ----- 192 Points ----- Stable**
 - **+5.1 to +10.0 mOhms -----0 Points ----- Minor**
 - **+10.1 to +15.0 mOhms -----0 Points ----- Acceptable**
 - **+15.1 to +50.0 mOhms -----0 Points ----- Marginal**
 - **+50.1 to +2000 mOhms-----0 Points ----- Unstable**
 - **>+2000 mOhms -----0 Points ----- Open Failure**

DATA SUMMARIES**LLCR Durability:**

- 1) A total of 192 points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: ----- Stable
 - b. $+5.1$ to $+10.0$ mOhms: ----- Minor
 - c. $+10.1$ to $+15.0$ mOhms: ----- Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: ----- Marginal
 - e. $+50.1$ to $+2000$ mOhms ----- Unstable
 - f. $>+2000$ mOhms: ----- Open Failure

LLCR Measurement Summaries by Pin Type				
Date	2012-12-11	2012-12-12	2012-12-27	2013-1-7
Room Temp (Deg C)	22	23	22	22
Rel Humidity (%)	32	31	32	32
Technician	Troy Cook	Troy Cook	Troy Cook	Troy Cook
mOhm values	Actual Initial	Delta 10 Cycles	Delta Therm Shck	Delta Humidity
Pin Type 1: Signal				
Average	4.36	0.10	0.13	0.13
St. Dev.	0.28	0.09	0.10	0.11
Min	3.06	0.00	0.00	0.00
Max	4.98	0.47	0.54	0.69
Summary Count	192	192	192	192
Total Count	192	192	192	192

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	≤ 5	>5 & ≤ 10	>10 & ≤ 15	>15 & ≤ 50	>50 & ≤ 1000	>1000
10 Cycles	192	0	0	0	0	0
Therm Shck	192	0	0	0	0	0
Humidity	192	0	0	0	0	0

EQUIPMENT AND CALIBRATION SCHEDULES**Equipment #:** MO-04**Description:** Multimeter /Data Acquisition System**Manufacturer:** Keithley**Model:** 2700**Serial #:** 0798688**Accuracy:** See Manual

... Last Cal: 04/30/2012, Next Cal: 04/30/2013

Equipment #: THC-02**Description:** Temperature/Humidity Chamber**Manufacturer:** Thermotron**Model:** SE-1000-6-6**Serial #:** 31808**Accuracy:** See Manual

... Last Cal: 02/16/2012, Next Cal: 02/16/2013

Equipment #: TSC-01**Description:** Vertical Thermal Shock Chamber**Manufacturer:** Cincinnatti Sub Zero**Model:** VTS-3-6-6-SC/AC**Serial #:** 10-VT14993**Accuracy:** See Manual

... Last Cal: 05/18/2012, Next Cal: 05/18/2013