

Series: QRM8/QRF8 Q Rate® Slim Body Ground Plane Connector

Description: Board-to-Board, 10mm (.394") Stack Height, 0.8mm (.0315") Pitch

Connector Overview

Samtec's QRM8/QRF8 Q Rate® Slim Body Ground Plane Connector is designed for high-speed board-to-board applications where signal integrity is essential. The connectors have surface mount contacts as well as a surface mount ground plane between the two rows of signals for improved electrical performance. QRM8/QRF8 is a double row contacts system available with up to 156 I/Os in stack heights from 7mm (.276") through 14mm (0.551"). The data in this report is applicable only to a 10mm stack height.

Connector System Speed Rating

QRM8/QRF8 Q Rate® Slim Body Ground Plane Connector, Board-to-Board, 0.8mm (.0315") Pitch, 10mm (0.394") Stack Height

<u>Signaling</u>	<u>Speed Rating</u>
Single-Ended:	16.5 GHz/ 33Gbps
Differential:	15 GHz/ 30Gbps

The Speed Rating is based on the -3 dB insertion loss point of the connector system. The -3 dB point can be used to estimate usable system bandwidth in a typical, two-level signaling environment.

To calculate the Speed Rating, the measured -3 dB point is rounded-up to the nearest half-GHz level. The up rounding corrects for a portion of the test board's trace loss, since a short length of trace loss included in the loss data in this report. The resulting loss value is then doubled to determine the approximate maximum data rate in Gigabits per second (Gbps).

For example, a connector with a -3 dB point of 7.8 GHz would have a Speed Rating of 8 GHz/ 16 Gbps. A connector with a -3 dB point of 7.2 GHz would have a Speed Rating of 7.5 GHz/ 15 Gbps.