

Series: SEAMP/SEAF-RA

Description: 1.27mm x 1.27mm grid interconnect system, Vertical (Press-Fit) to Right Angle

Connector Overview

SEAMP/SEAF-RA series is a 1.27mm x 1.27mm pitch interconnects system for elevated high-speed board-to-board applications. The SEAMP/SEAF-RA Series is available in 4, 6, 8, and 10 row open pin field arrays. Pins per row selections are 10, 20, 30, 40, or 50. This report reflects only the hi-speed electrical characteristics specific to a mated 10 to 50 contacts/row, 10 rows, SEAMP/SEAF-RA test system.

Connector System Speed Rating

SEAMP/ SEAF-RA Series, 1.27mm x 1.27mm (.050" x .050") pitch interconnect	
<u>Signaling</u>	<u>Speed Rating</u>
Single-Ended: 1:1 S/G, row1	6 GHz/ 12Gbps
Single-Ended: 1:1 S/G, row4	8.5 GHz/ 17Gbps
Single-Ended: 1:1 S/G, row6	7 GHz/ 14Gbps
Single-Ended: 1:1 S/G, row8	6 GHz/ 12Gbps
Single-Ended: 1:1 S/G, row10	6 GHz/ 12Gbps
Single-Ended: 2:1 S/G, row1	6 GHz/ 12Gbps
Single-Ended: 2:1 S/G, row4	11 GHz/ 22Gbps
Single-Ended: 2:1 S/G, row6	9.5 GHz/ 19Gbps
Single-Ended: 2:1 S/G, row8	6 GHz/ 12Gbps
Single-Ended: 2:1 S/G, row10	8.5 GHz/ 17Gbps
Differential: Optimal Horizontal, row1	11 GHz/ 22Gbps
Differential: Optimal Horizontal, row4	8.5 GHz/ 17Gbps
Differential: Optimal Horizontal, row7	6.5 GHz/ 13Gbps
Differential: Optimal Horizontal, row8	6 GHz/ 12Gbps
Differential: Optimal Horizontal, row10	6 GHz/ 12Gbps

Series: SEAMP/SEAF-RA

Description: 1.27mm x 1.27mm grid interconnect system, Vertical (Press-Fit) to Right Angle

Differential: Optimal Vertical, row1,2	9 GHz/ 18Gbps
Differential: Optimal Vertical, row3,4	8.5 GHz/ 17Gbps
Differential: Optimal Vertical, row5,6	8.5 GHz/ 17Gbps
Differential: Optimal Vertical, row7,8	8.5 GHz/ 17Gbps
Differential: Optimal Vertical, row9,10	9 GHz/ 18Gbps
Differential: High Density Vertical, row1,2	7.5 GHz/ 15Gbps
Differential: High Density Vertical, row4,5	7.5 GHz/ 15Gbps
Differential: High Density Vertical, row7,8	8.5 GHz/ 17Gbps
Differential: High Density Vertical, row8,9	8 GHz/ 16Gbps
Differential: High Density Vertical, row9,10	9.5 GHz/ 19Gbps

The Speed Rating is based on the -3 dB insertion loss point of the connector system. The -3 dB point can be used to estimate usable system bandwidth in a typical, two-level signaling environment.

To calculate the Speed Rating, the measured -3 dB point is rounded up to the nearest half-GHz level. The up-rounding corrects for a portion of the test board's trace loss, since a short length of trace loss is included in the loss data in this report. The resulting loss value is then doubled to determine the approximate maximum data rate in Gigabits per second (Gbps).

For example, a connector with a -3 dB point of 7.8 GHz would have a Speed Rating of 8 GHz/ 16 Gbps. A connector with a -3 dB point of 7.2 GHz would have a Speed Rating of 7.5 GHz/15 Gbps.