

Series: FW/CLP Micro Socket and Terminal Board Stacker

Description: Parallel Board-to-Board, 0.050" [1.27mm] Pitch, 17.7mm (0.696") Stack Height

Connector Overview

Micro 1.27mm (.050") pitch CLP socket and FW terminal series connector combinations provide for several lead styles and optional board spacing considerations. The connector series is available with up to 50 contacts per row. The data in this report is applicable only to a CLP-02 and FW-05-610-065 connector combination resulting in a surface mount 17.7mm (0.696") board-to-board stack height version.

Connector System Speed Rating

FW/CLP Series, Parallel Board-to-Board, 1.27mm Pitch, 17.7mm (0.696") Stack Height

<u>Signaling</u>	<u>Speed Rating</u>
Single-Ended:	3.0 GHz / 6 Gbps
Differential:	4.0 GHz / 8 Gbps

The Speed Rating is based on the -3 dB insertion loss point of the connector system. The -3 dB point can be used to estimate usable system bandwidth in a typical, two-level signaling environment.

To calculate the Speed Rating, the measured -3 dB point is rounded up to the nearest half-GHz level. The up-rounding corrects for a portion of the test board's trace loss, since trace losses are included in the loss data in this report. The resulting loss value is then doubled to determine the approximate maximum data rate in Gigabits per second (Gbps).

For example, a connector with a -3 dB point of 7.8 GHz would have a Speed Rating of 8 GHz/ 16 Gbps. A connector with a -3 dB point of 7.2 GHz would have a Speed Rating of 7.5 GHz/ 15 Gbps.