

Series: QSE-DP/QTE-DP

Description: Parallel Board-to-Board, 0.8mm Pitch, 19mm (0.748") Stack Height

Connector Overview

Q Strip® .8mm (.0315") pitch interfaces (QSE/QTE Series) are available with up to 140 I/Os and with standard board-to-board spacing of 5mm (0.197"), 8mm (0.315"), 11mm (0.433"), and 16mm (0.630") between boards. The data in this report is applicable only to the application specific differential pair 19mm (0.748") board-to-board stack height version.

Connector System Speed Rating

QSE-DP/QTE-DP Series, Parallel Board-to-Board, 0.8mm Pitch, 19mm (0.748") Stack Height

| <u>Signaling</u> | <u>Speed Rating</u> |
|------------------|--------------------------|
| Differential: | 7.5 GHz / 15 Gbps |

The Speed Rating is based on the -3 dB insertion loss point of the connector system. The -3 dB point can be used to estimate usable system bandwidth in a typical, two-level signaling environment.

To calculate the Speed Rating, the measured -3 dB point is rounded up to the nearest half-GHz level. The up-rounding corrects for a portion of the test board's trace loss, since trace losses are included in the loss data in this report. The resulting loss value is then doubled to determine the approximate maximum data rate in Gigabits per second (Gbps).

For example, a connector with a -3 dB point of 7.8 GHz would have a Speed Rating of 8 GHz/ 16 Gbps. A connector with a -3 dB point of 7.2 GHz would have a Speed Rating of 7.5 GHz/ 15 Gbps.