

Series: QFS-DP/QMS-DP, Micro High Speed

Description: Parallel Board-to-Board, 0.635mm Pitch, 11mm (0.433") Stack Height

Connector Overview

Micro High Speed .635mm (.025") pitch interfaces (QFS-DP/QMS-DP Series) are available with up to 64 contacts per row and a board-to-board spacing of 11mm (0.433"). The data in this report is applicable only to the 11mm (0.433") board-to-board DP connector version stack height

Connector System Speed Rating

QFS-DP/QMS-DP Series, Parallel Board-to-Board, 0.635mm Pitch, 11mm (0.433") Stack Height

<u>Signaling</u>	<u>Speed Rating</u>
Differential:	7.0 GHz / 14 Gbps

The Speed Rating is based on the -3 dB insertion loss point of the connector system. The -3 dB point can be used to estimate usable system bandwidth in a typical, two-level signaling environment.

To calculate the Speed Rating, the measured -3 dB point is rounded up to the nearest half-GHz level. The up-rounding corrects for a portion of the test board's trace loss, since trace losses are included in the loss data in this report. The resulting loss value is then doubled to determine the approximate maximum data rate in Gigabits per second (Gbps).

For example, a connector with a -3 dB point of 7.8 GHz would have a Speed Rating of 8 GHz/ 16 Gbps. A connector with a -3 dB point of 7.2 GHz would have a Speed Rating of 7.5 GHz/ 15 Gbps.