



Project Number: Design Qualification Test Report	Tracking Code: CR-868803_ELP-Report_Rev_1
Requested by: Will Luo	Date: 12/11/2023
Part #: AMF6-02-S-V-XR /ARM6-02-06.0-LU-XX-X-1	
Part description: AMF6/ ARM6	Tech: Peter Chen
Test Start: 1/5/2023	Test Completed: 2/25/2023



DESIGN QUALIFICATION TEST REPORT
AMF6/ ARM6
AMF6-02-S-V-XR /ARM6-02-06.0-LU-XX-X-1

REVISION HISTORY

DATA	REV.NUM.	DESCRIPTION	ENG
11/21/2023	1	Initial test	PC

CERTIFICATION

All instruments and measuring equipment were calibrated to National Institute for Standards and Technology (NIST) traceable standards according to ISO 10012-1 and ANSI/NCSL 2540-1, as applicable.

All contents contained herein are the property of Samtec. No portion of this report, in part or in full shall be reproduced without prior written approval of Samtec.

SCOPE

To perform the following tests: Design Qualification test. Please see test plan.

APPLICABLE DOCUMENTS

Standards: EIA Publication 364

TEST SAMPLES AND PREPARATION

- 1) All materials were manufactured in accordance with the applicable product specification.
- 2) All test samples were identified and encoded to maintain traceability throughout the test sequences.
- 3) After soldering, the parts to be used for LLCR testing was cleaned according to CO-SC-WI-3029.
- 4) Either an automated cleaning procedure or an ultrasonic cleaning procedure may be used.
- 5) The automated procedure is used with aqueous compatible soldering materials.
- 6) Parts not intended for testing LLCR is visually inspected and cleaned if necessary.
- 7) Any additional preparation will be noted in the individual test sequences.
- 8) Solder Information: Lead Free
- 9) Samtec Test PCBs used: PCB-112497-TST.

FLOWCHARTS

Extended Life

Group 1 AMF6-02-S-V-XR ARM6-02-06.0-LU-XX-X-1 8 Assemblies 100 Cycles		Group 2 AMF6-02-S-V-XR ARM6-02-06.0-LU-XX-X-1 8 Assemblies 250 Cycles		Group 3 AMF6-02-S-V-XR ARM6-02-06.0-LU-XX-X-1 8 Assemblies 500 Cycles		Group 4 AMF6-02-S-V-XR ARM6-02-06.0-LU-XX-X-1 8 Assemblies 1000 Cycles	
Step	Description	Step	Description	Step	Description	Step	Description
1.	Plating Thickness Verification ⁽⁴⁾	1.	Plating Thickness Verification ⁽⁴⁾	1.	Plating Thickness Verification ⁽⁴⁾	1.	Plating Thickness Verification ⁽⁴⁾
2.	LLCR ⁽²⁾	2.	LLCR ⁽²⁾	2.	LLCR ⁽²⁾	2.	LLCR ⁽²⁾
3.	Cycles Quantity = 100 Cycles	3.	Cycles Quantity = 250 Cycles	3.	Cycles Quantity = 500 Cycles	3.	Cycles Quantity = 1000 Cycles
4.	LLCR ⁽²⁾ Max Delta = 15 mOhm	4.	LLCR ⁽²⁾ Max Delta = 15 mOhm	4.	LLCR ⁽²⁾ Max Delta = 15 mOhm	4.	LLCR ⁽²⁾ Max Delta = 15 mOhm
5.	Thermal Shock ⁽⁵⁾ - Non Standard	5.	Thermal Shock ⁽⁵⁾ - Non Standard	5.	Thermal Shock ⁽⁵⁾ - Non Standard	5.	Thermal Shock ⁽⁵⁾ - Non Standard
6.	LLCR ⁽²⁾ Max Delta = 15 mOhm	6.	LLCR ⁽²⁾ Max Delta = 15 mOhm	6.	LLCR ⁽²⁾ Max Delta = 15 mOhm	6.	LLCR ⁽²⁾ Max Delta = 15 mOhm
7.	Humidity ⁽¹⁾	7.	Humidity ⁽¹⁾	7.	Humidity ⁽¹⁾	7.	Humidity ⁽¹⁾
8.	LLCR ⁽²⁾ Max Delta = 15 mOhm	8.	LLCR ⁽²⁾ Max Delta = 15 mOhm	8.	LLCR ⁽²⁾ Max Delta = 15 mOhm	8.	LLCR ⁽²⁾ Max Delta = 15 mOhm
9.	Photos ⁽³⁾	9.	Photos ⁽³⁾	9.	Photos ⁽³⁾	9.	Photos ⁽³⁾

(1) Humidity = EIA-364-31

Test Condition = B (240 Hours)
 Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)
 Test Exceptions: ambient pre-condition and delete steps 7a and 7b

(2) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max
 Test Current = 100 mA Max

(3) Photos

Attach 2-3 photos of contact area

(4) Plating Thickness Verification

Measure, verify, and document plating thickness on both male and female (one group only)
 Plating thickness to be measured on loose pins used during assembly

(5) Thermal Shock = Other

Exposure Time at Temperature Extremes = 1/2 Hour
 Method A, Test Condition = I (-40°C to +85°C)
 Test Duration = A-3 (100 Cycles)
 EIA-364-32, change Thermal Shock profile from -55°C/85°C to -40°C/85°C, due to temp limit of cable.

ATTRIBUTE DEFINITIONS

The following is a brief, simplified description of attributes.

THERMAL SHOCK:

- 1) EIA-364-32, *Thermal Shock (Temperature Cycling) Test Procedure for Electrical Connectors*.
- 2) Test Condition I: -40°C to +85°C
- 3) Test Time: ½ hour dwell at each temperature extreme
- 4) Number of Cycles: 100
- 5) All test samples are pre-conditioned at ambient.
- 6) All test samples are exposed to environmental stressing in the mated condition.

HUMIDITY:

- 1) Reference document: EIA-364-31, *Humidity Test Procedure for Electrical Connectors*.
- 2) Test Condition B, 240 Hours.
- 3) Method III, +25° C to + 65° C, 90% to 98% Relative Humidity excluding sub-cycles 7a and 7b.
- 4) All samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

LLCR:

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
 - a. <= +5.0 mOhms: -----Stable
 - b. +5.1 to +10.0 mOhms:-----Minor
 - c. +10.1 to +15.0 mOhms: -----Acceptable
 - d. +15.1 to +50.0 mOhms: -----Marginal
 - e. +50.1 to +1000 mOhms: -----Unstable
 - f. >+1000 mOhms:-----Open Failure

RESULTS**LLCR Extended Life (40 LLCR test points)**

100 cycles

Signal pin

- Initial ----- 161.95 mOhms Max

Ground Pin

- Initial ----- 35.12 mOhms Max
- Durability, 100 Cycles
 - <= +5.0 mOhms ----- 38 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 2 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure
- Thermal
 - <= +5.0 mOhms ----- 38 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 2 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure
- Humidity
 - <= +5.0 mOhms ----- 33 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 7 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure

250 cycles

Signal pin

- Initial ----- 163.63 mOhms Max

Ground Pin

- Initial ----- 35.93 mOhms Max
- Durability, 250 Cycles
 - <= +5.0 mOhms ----- 40 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure
- Thermal
 - <= +5.0 mOhms ----- 37 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 2 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 1 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure
- Humidity
 - <= +5.0 mOhms ----- 33 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 6 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 1 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure

RESULTS Continued

500 cycles

Signal pin

- Initial ----- 164.30 mOhms Max

Ground Pin

- Initial ----- 35.78 mOhms Max
- Durability, 500 Cycles
 - <= +5.0 mOhms ----- 40 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure
- Thermal
 - <= +5.0 mOhms ----- 33 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 7 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure
- Humidity
 - <= +5.0 mOhms ----- 36 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 4 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure

1000 cycles

Signal pin

- Initial ----- 164.69 mOhms Max

Ground Pin

- Initial ----- 36.36 mOhms Max
- Durability, 1000 Cycles
 - <= +5.0 mOhms ----- 33 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 7 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure
- Thermal
 - <= +5.0 mOhms ----- 28 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 12 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure
- Humidity
 - <= +5.0 mOhms ----- 22 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 17 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 1 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure

DATA SUMMARIES

LLCR Extended Life:

- 1) A total of 40 points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: -----Stable
 - b. $+5.1$ to $+10.0$ mOhms: -----Minor
 - c. $+10.1$ to $+15.0$ mOhms:-----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms:-----Marginal
 - e. $+50.1$ to $+1000$ mOhms-----Unstable
 - f. $>+1000$ mOhms:-----Open Failure

100 Cycles

LLCR Measurement Summaries by Pin Type				
Date	4/23/2023	4/27/2023	6/5/2023	6/21/2023
Room Temp (Deg C)	23	23	23	23
Rel Humidity (%)	55	53	54	54
Technician	Peter Chen	Peter Chen	Peter Chen	Peter Chen
mOhm values				
	Actual	Delta	Delta	Delta
	Initial	Cycles	Therm Shck	Humidity
Pin Type: Signal 1				
Average	154.7	1.65	2.96	2.65
St. Dev.	5.76	1.58	1.4	2.08
Min	140.21	0.09	0.19	0.05
Max	161.95	7.29	5.57	8.39
Summary Count	32	32	32	32
Total Count	32	32	32	32
Pin Type: GND 1				
Average	33.97	1.22	2.41	4.43
St. Dev.	0.97	0.52	1.12	2.1
Min	32.4	0.66	0.87	2.51
Max	35.12	2.08	4.18	8.28
Summary Count	8	8	8	8
Total Count	8	8	8	8

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	≤ 5	$>5 \ \& \ \leq 10$	$>10 \ \& \ \leq 15$	$>15 \ \& \ \leq 50$	$>50 \ \& \ \leq 1000$	>1000
Cycles	38	2	0	0	0	0
Therm Shck	38	2	0	0	0	0
Humidity	33	7	0	0	0	0

DATA SUMMARIES**250 Cycles**

LLCR Measurement Summaries by Pin Type				
Date	4/23/2023	4/27/2023	6/5/2023	6/21/2023
Room Temp (Deg C)	23	23	23	23
Rel Humidity (%)	55	54	54	54
Technician	Peter Chen	Peter Chen	Peter Chen	Peter Chen
mOhm values	Actual	Delta	Delta	Delta
	Initial	Cycles	Therm Shck	Humidity
Pin Type: Signal 1				
Average	156.93	1.81	2.68	3.18
St. Dev.	4.17	0.99	1.79	2.08
Min	147.33	0.47	0.16	0.42
Max	163.63	4.45	10.52	8.38
Summary Count	32	32	32	32
Total Count	32	32	32	32
Pin Type: GND 1				
Average	35.05	0.9	2.56	5.22
St. Dev.	0.75	0.41	2.11	3.12
Min	33.5	0.27	0.45	1.84
Max	35.93	1.39	7.3	11.34
Summary Count	8	8	8	8
Total Count	8	8	8	8

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	<=5	>5 & <=10	>10 & <=15	>15 & <=50	>50 & <=1000	>1000
Cycles	40	0	0	0	0	0
Therm Shck	37	2	1	0	0	0
Humidity	33	6	1	0	0	0

DATA SUMMARIES**500 Cycles**

LLCR Measurement Summaries by Pin Type				
Date	4/23/2023	4/27/2023	6/13/2023	6/26/2023
Room Temp (Deg C)	23	23	23	23
Rel Humidity (%)	55	52	54	54
Technician	Peter Chen	Peter Chen	Peter Chen	Peter Chen
mOhm values	Actual	Delta	Delta	Delta
	Initial	Cycles	Therm Shck	Humidity
Pin Type: Signal 1				
Average	156	1.22	3.42	3.05
St. Dev.	5.39	1	2.08	2.62
Min	141.4	0.11	0.35	0.07
Max	164.3	4.8	8.54	9.84
Summary Count	32	32	32	32
Total Count	32	32	32	32
Pin Type: GND 1				
Average	34.45	0.97	2.61	3.41
St. Dev.	1.07	0.56	1.3	0.8
Min	32.1	0.3	0.74	1.74
Max	35.78	1.87	5	4.18
Summary Count	8	8	8	8
Total Count	8	8	8	8

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	<=5	>5 & <=10	>10 & <=15	>15 & <=50	>50 & <=1000	>1000
Cycles	40	0	0	0	0	0
Therm Shck	33	7	0	0	0	0
Humidity	36	4	0	0	0	0

DATA SUMMARIES**1000 Cycles**

LLCR Measurement Summaries by Pin Type				
Date	4/27/2023	5/8/2023	6/13/2023	6/25/2023
Room Temp (Deg C)	23	23	23	23
Rel Humidity (%)	54	54	58	51
Technician	Peter Chen	Peter Chen	Peter Chen	Peter Chen
mOhm values	Actual	Delta	Delta	Delta
	Initial	Cycles	Therm Shck	Humidity
Pin Type: Signal 1				
Average	157.14	2.91	3.82	4.36
St. Dev.	4.05	1.98	2.2	2.71
Min	148.22	0.08	0	0.18
Max	164.69	6.52	8.65	11.13
Summary Count	32	32	32	32
Total Count	32	32	32	32
Pin Type: GND 1				
Average	34	1.16	3.32	5.55
St. Dev.	1.44	0.94	1.32	1.74
Min	31.75	0.04	0.74	2.54
Max	36.36	3.07	4.81	8.67
Summary Count	8	8	8	8
Total Count	8	8	8	8

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	<=5	>5 & <=10	>10 & <=15	>15 & <=50	>50 & <=1000	>1000
Cycles	33	7	0	0	0	0
Therm Shck	28	12	0	0	0	0
Humidity	22	17	1	0	0	0

EQUIPMENT AND CALIBRATION SCHEDULES**Equipment #:** HZ-THC-01**Description:** Humidity transmitter**Manufacturer:** Thermtron**Model:** SM-8-8200**Serial #:** 38846**Accuracy:** Last Cal: 2/28/2023, Next Cal: 2/27/2024**Equipment #:** HZ-TSC-01**Description:** Vertical Thermal Shock Chamber**Manufacturer:** Cincinnatti Sub Zero**Model:** VTS-3-6-6-SC/AC**Serial #:** 10-VT14994**Accuracy:** See Manual

... Last Cal: 06/28/2021, Next Cal: 06/27/2022

Equipment #: HZ-MO-05**Description:** Micro-ohmmeter**Manufacturer:** Keithley**Model:** 3706**Serial #:** 1285188**Accuracy:** Last Cal: 11/15/2022, Next Cal: 11/14/2023**Equipment #:** HZ-PS-01**Description:** Power Supply**Manufacturer:** Agilent**Model:** 6031A**Serial #:** MY41000982**Accuracy:** Last Cal: 04/28/2022, Next Cal: 04/28/2023