

Series: QTE/QSE

Description: High Speed Ground Plane Header, 0.8mm (.0315") Pitch, 25mm (.984") Stack Height

Frequency Domain Data Summary

Table 1 - Single-Ended Connector System Performance		
Test Parameter	Configuration	
Insertion Loss	GSG	3dB @ 3.113 GHz
Return Loss	GSG	>10dB to 1.913 GHz
Near-End Crosstalk	GAQG	< -20dB to 0.263 GHz
	GAGQG	< -20dB to 3.475 GHz
	Xrow, GAG to GQG	< -20dB to 4.050 GHz
Far-End Crosstalk	GAQG	< -20dB to 3.125 GHz
	GAGQG	< -20dB to 3.563 GHz
	Xrow, GAG to GQG	< -20dB to 15.563 GHz

Table 2 - Differential Connector System Performance		
Test Parameter	Configuration	
Insertion Loss	GSSG	3dB @ 11.888 GHz
Return Loss	GSSG	>10dB to 0.700 GHz
Near-End Crosstalk	GAAQQG	< -20dB to 11.100 GHz
	GAAGQQG	< -20dB to 16.088 GHz
	Xrow, GAAG to GQQG	< -20dB to 20.000 GHz
Far-End Crosstalk	GAAQQG	< -20dB to 11.363 GHz
	GAAGQQG	< -20dB to 20.000 GHz
	Xrow, GAAG to GQQG	< -20dB to 20.000 GHz

Series: QTE/QSE

Description: High Speed Ground Plane Header, 0.8mm (.0315") Pitch, 25mm (.984") Stack Height

Bandwidth Chart – Single-Ended & Differential Insertion Loss

QTE/QSE Ground Plane Header Series

