

Series: SS5/ST5

Description: Razor Beam™ Low Profile Terminal/Socket Strip, 0.5mm Pitch, 5mm Stack Height

Frequency Domain Data Summary

Table 1 - Single-Ended Connector System Performance		
Test Parameter	Configuration	
Insertion Loss	GSG	3dB@ 13.5 GHz
Return Loss	GSG	>10dB to 11.3 GHz
Near-End Crosstalk	GAQG	<-20dB to 0.9 GHz
	GAGQG	<-20dB to 17.4 GHz
	Xrow, GAG to GQG	<-20dB to 12.2 GHz
Far-End Crosstalk	GAQG	<-20dB to 13.1 GHz
	GAGQG	<-20dB to 11.9 GHz
	Xrow, GAG to GQG	<-20dB to 11.5 GHz

Table 2 - Differential Connector System Performance		
Test Parameter	Configuration	
Insertion Loss	GSSG	3dB@ 20 GHz
Return Loss	GSSG	>10dB to 2.4 GHz
Near-End Crosstalk	GAAQQG	<-20dB to 20 GHz
	GAAGQQG	<-20dB to 19.8 GHz
	Xrow, GAAG to GQQG	<-20dB to 20 GHz
Far-End Crosstalk	GAAQQG	<-20dB to 20 GHz
	GAAGQQG	<-20dB to 20 GHz
	Xrow, GAAG to GQQG	<-20dB to 20 GHz

Series: SS5/ST5

Description: Razor Beam™ Low Profile Terminal/Socket Strip, 0.5mm Pitch, 5mm Stack Height

Bandwidth Chart – Single-Ended & Differential Insertion Loss

SS5/ ST5 Connector Series

