



Series: MEC8

Description: Mini Edge Card Connector, Edge Mount, 0.8mm Pitch, Mates with 1.6mm thick cards

Frequency Domain Data Summary

Table 1 - Single-Ended Connector System Performance				
Test Parameter	Configuration	Driver	Receiver	
Insertion Loss	GSG	Edge_Card_62	MEC8_62	3dB@ 9.1 GHz
Return Loss	GSG	Edge_Card_62	Edge_Card_62	>10dB to 7 GHz
Near-End Crosstalk	GAQG	Edge_Card_22	Edge_Card_24	<-20dB to 0.6 GHz
	GAGQG	Edge_Card_62	Edge_Card_66	<-20dB to 6.8 GHz
	Xrow, GAG to GQG	Edge_Card_61	Edge_Card_62	<-20dB to 20 GHz
Far-End Crosstalk	GAQG	Edge_Card_22	MEC8_24	<-20dB to 6.9 GHz
	GAGQG	Edge_Card_62	MEC8_66	<-20dB to 6.8 GHz
	Xrow, GAG to GQG	Edge_Card_62	MEC8_61	<-20dB to 20 GHz

Table 2 - Differential Connector System Performance				
Test Parameter	Configuration	Driver	Receiver	
Insertion Loss	GSSG	Edge_Card_28,30	MEC8_28,30	3dB@ 8.6 GHz
Return Loss	GSSG	Edge_Card_28,30	Edge_Card_28,30	>10dB to 7.2 GHz
Near-End Crosstalk	GAAQQG	Edge_Card_28,30	Edge_Card_32,34	<-20dB to 8.4 GHz
	GAAGQQG	Edge_Card_28,30	Edge_Card_34,36	<-20dB to 20GHz
	Xrow, GAAG to GQQG	Edge_Card_21,23	Edge_Card_22,24	<-20dB to 20GHz
Far-End Crosstalk	GAAQQG	Edge_Card_28,30	MEC8_32,34	<-20dB to 18.8GHz
	GAAGQQG	Edge_Card_28,30	MEC8_34,36	<-20dB to 20GHz
	Xrow, GAAG to GQQG	Edge_Card_22,24	MEC8_21,23	<-20dB to 20GHz

Series: MEC8

Description: Mini Edge Card Connector, Edge Mount, 0.8mm Pitch, Mates with 1.6mm thick cards

Bandwidth Chart – Single-Ended & Differential Insertion Loss

MEC8 Connector Series

