

Series: LSEM

Description: Board-to-Board, 0.8mm (.0315") Pitch, , 6mm (0.2362") Stack Height

## Frequency Domain Data Summary

Table 1 - Single-Ended Connector System Performance			
Case	Test Parameter	Configuration	
1	Insertion Loss	GSG	3dB @ 9.513 GHz
	Return Loss	GSG	>10dB to 8.150 GHz
	Near-End Crosstalk	GAQG	< -20dB to 0.863 GHz
		GAGQG	< -20dB to 20.000 GHz
		Xrow, GAG to GQG	< -20dB to 9.188 GHz
	Far-End Crosstalk	GAQG	< -20dB to 5.500 GHz
		GAGQG	< -20dB to 9.388 GHz
		Xrow, GAG to GQG	< -20dB to 9.175 GHz

Table 2 - Differential Connector System Performance			
Case	Test Parameter	Configuration	
1	Insertion Loss	GSSG	3dB @ 12.125 GHz
	Return Loss	GSSG	>10dB to 8.563 GHz
	Near-End Crosstalk	GAAQQG	< -20dB to 20.000 GHz
		GAAGQQG	< -20dB to 20.000 GHz
		Xrow, GAAG to GQQG	< -20dB to 20.000 GHz
	Far-End Crosstalk	GAAQQG	< -20dB to 20.000 GHz
		GAAGQQG	< -20dB to 20.000 GHz
		Xrow, GAAG to GQQG	< -20dB to 15.500 GHz

**Series:** LSEM

**Description:** Board-to-Board, 0.8mm (.0315") Pitch, , 6mm (0.2362") Stack Height

## Bandwidth Chart – Single-Ended & Differential Insertion Loss

LSEM Hermaphroditic Series

