

**Series:** SS5/ST5

**Description:** Razor Beam™ Low Profile Terminal/Socket Strip,0.5mm Pitch, 4mm Stack Height

## Frequency Domain Data Summary

Table 1 - Single-Ended Connector System Performance		
Test Parameter	Configuration	
Insertion Loss	GSG	3dB@ 12.9 GHz
Return Loss	GSG	>10dB to 10.4GHz
Near-End Crosstalk	GAQG	<-20dB to 1GHz
	GAGQG	<-20dB to 18.0GHz
	Xrow, GAG to GQG	<-20dB to 14.1 GHz
Far-End Crosstalk	GAQG	<-20dB to 5.8GHz
	GAGQG	<-20dB to 13.2 GHz
	Xrow, GAG to GQG	<-20dB to 13.9 GHz

Table 2 - Differential Connector System Performance		
Test Parameter	Configuration	
Insertion Loss	GSSG	3dB@ 13.1 GHz
Return Loss	GSSG	>10dB to 2 GHz
Near-End Crosstalk	GAAQQG	<-20dB to 20GHz
	GAAGQQG	<-20dB to 20GHz
	Xrow, GAAG to GQQG	<-20dB to 20GHz
Far-End Crosstalk	GAAQQG	<-20dB to 20GHz
	GAAGQQG	<-20dB to 20GHz
	Xrow, GAAG to GQQG	<-20dB to 20GHz

Series: SS5/ST5

Description: Razor Beam™ Low Profile Terminal/Socket Strip, 0.5mm Pitch, 4mm Stack Height

## Bandwidth Chart – Single-Ended & Differential Insertion Loss

SS5/ ST5 Connector Series

