


Series: HDAM/HDAF Series (HDMezz)

Description: 1.2mm x 2mm grid interconnect system, high density array, 30mm Stack Height

Frequency Domain Data Summary

Table 1 - Single-Ended Signaling System Performance			
Test Parameter	Source	Victim	
Insertion Loss	port1=HDAM_B14; port2=HDAF_B14		-3dB @ 9.72 GHz
Return Loss	port1=HDAM_B14; port2=HDAF_B14		≤ -5dB to 9.72 GHz
Near-End Crosstalk	HDAM_C3	HDAM_D3	≤ -8dB to 9.72 GHz
	HDAM_B14	HDAM_D14	≤ -22dB to 9.72 GHz
	HDAM_B14	HDAM_B13	≤ -20dB to 9.72 GHz
	HDAM_C3	HDAM_B2	≤ -22dB to 9.72 GHz
Far-End Crosstalk	HDAM_C3	HDAF_D3	≤ -10dB to 9.72 GHz
	HDAM_B14	HDAF_D14	≤ -22dB to 9.72 GHz
	HDAM_B14	HDAF_B13	≤ -22dB to 9.72 GHz
	HDAM_C3	HDAF_B2	≤ -32dB to 9.72 GHz

Pin Map (reference Appendix C for full description of test boards)




Series: HDAM/HDAF Series (HDMezz)

Description: 1.2mm x 2mm grid interconnect system, high density array, 30mm Stack Height

Table 2 – Differential Pair Signaling System Performance			
Test Parameter	Source	Victim	
Insertion Loss	port1=HDAM_B14-C14; port2=HDAF_B14-C14		-3dB D33 7.32 GHz
Return Loss	port1=HDAM_B14-C14; port2=HDAF_B14-C14		≤ -5dB to 7.32 GHz
Near-End Crosstalk	HDAM_B3-C3	HDAM_D3-E3	≤ -15dB to 7.32 GHz
	HDAM_B14-C14	HDAM_E14-F14	≤ -35dB to 7.32 GHz
	HDAM_E8-F8	HDAM_E7-F7	≤ -28dB to 7.32 GHz
	HDAM_E8-F8	HDAM_B7-C7	≤ -35dB to 7.32GHz
Far-End Crosstalk	HDAM_B3-C3	HDAF_D3-E3	≤ -42dB to 7.32 GHz
	HDAM_B14-C14	HDAF_E14-F14	≤ -34dB to 7.32 GHz
	HDAM_E8-F8	HDAM_E7-F7	≤ -25dB to 7.32 GHz
	HDAM_E8-F8	HDAM_B7-C7	≤ -38dB to 7.32 GHz

Pin Map (reference Appendix C for full description of test boards)



Series: HDAM/HDAF Series (HDMezz)

Description: 1.2mm x 2mm grid interconnect system, high density array, 30mm Stack Height

Bandwidth Chart – Single-Ended & Differential Insertion Loss

