

# HIGH-SPEED CABLE SOLUTIONS

## **SAMTEC FLYOVER**\* ARCHITECTURE

Improves Signal Integrity & Reach at Higher Data Rates

In-House High Level Design & Engineering Support

Full System Signal Integrity Expertise





### **FLEXIBILITY** & CUSTOMIZATION

Mix & Match Connector End Options

Extensive Customization Capabilities

Modular Backplane Flexibility

## MANUFACTURING & CAPABILITIES

R&D/Manufacturing of Precision Extruded Cable & Next Gen RF Cable in Several Global Locations

Multiple Proprietary Ultra-High Performance Cable Technologies





## TABLE OF CONTENTS

FLYOVER® SYSTEMS  Flyover® Technology
Backplane Assemblies
HIGH-SPEED CABLE SYSTEMS  Mix-and-Match Assemblies
Customized Assemblies
OPTICAL SYSTEMS
OPTICAL SYSTEMS 22-23  RF SOLUTIONS 24-25

HIGH-SPEED CABLE OVERVIEW ......4-5

# HIGH-SPEED CABLE PRODUCT OVERVIEW








#### **HIGH-SPEED CABLE ASSEMBLIES** | 16-19

MICRO COAX & TWINAX CABLE | MIX-AND-MATCH END OPTIONS | ARRAYS, GROUND PLANE & EDGE CARD SYSTEMS PCle\* 2.0/3.0/4.0/5.0 | EDGE RATE\* RUGGED, HIGH-SPEED CONTACTS





FLEXIBLE WAVEGUIDES | NEXT GEN RF CABLE



#### THE PROBLEM

#### PCB REACH AT NEXT GEN SPEEDS

As bandwidth requirements rapidly increase, effectively managing heat and routing signals through lossy PCBs, vias and other components have become complex challenges.

#### **BANDWIDTH VS. TRADITIONAL & HIGH-SPEED MATERIALS**


(Comparison at -5 dB Insertion Loss Point)


	FR408	MEGTRON 6	MICRO TWINAX
56 G b p s	0.0"	up to 2"	36"+
112 6 b p s	0.0"	0.0"	18"+

#### **THE SOLUTION**

#### SAMTEC FLYOVER® SYSTEMS

Samtec Flyover® design breaks the constraints of traditional signaling substrate and hardware offerings, resulting in a cost-effective, high-performance and heat efficient answer to the challenges of 56 Gbps bandwidths and beyond.





#### EYE SPEED® TWINAX CABLE TECHNOLOGY

- Ideal for 28-112+ Gbps applications
- Tight coupling between signal conductors
- Ultra low skew twinax < 3.5 ps/meter
- 40% smaller cross-sectional area (Thinax<sup>™</sup>)
- See page 20-21 for cable specifications
- In Development: Eye Speed® AIR foamed twinax for significantly improved signal integrity and even lower intra-pair skew

#### SPEED C A B L E



**INDUSTRY CABLE** 



#### PERFORMANCE & COST ADVANTAGES

- 28-56 Gbps NRZ & Beyond
- Simplified Board Layout
- Fewer PCB Layers
- Less Expensive PCB Materials
- Eliminate Expensive Re-timers

## NRZ PAM4 NRZ PAM4 28 56 56 112 G b p s G b p s G b p s

#### **SUPPORT**

Fully integrated technology teams provide support to enable full system optimization from Silicon-to-Silicon<sup>™</sup>. See page 26 for information about Samtec's High-Speed Cable Plants.

#### THERMAL IMPROVEMENT






Standard Network Switch VS. Samtec Flyover® Technology

# FLYOVER® PANEL ASSEMBLIES






#### FLYOVER® QSFP SYSTEMS

- Up to 800 Gbps PAM4 aggregate data rate (112 Gbps PAM4 per channel)
- 4 channels (x4 bidirectional, 8 differential pairs) or 8 channels (x8 bidirectional,
   16 differential pairs)
- Double density versions feature belly-to-belly mating for maximum density (FQSFP-DD, FQSFP-D8)
- Multiple heat sink options for optimal dissipation
- Variety of end 2 options including AcceleRate<sup>®</sup>, NovaRay<sup>®</sup>, Si-Fly<sup>™</sup>, FireFly<sup>™</sup> and ExaMAX<sup>®</sup>
- Evaluation Kits available, see page 27 or visit samtec.com/kits
- Additional front panel ports in development: SFP112, OSFP200







Sideband signals are routed through press-fit contacts for increased airflow



**FLY**OVER®

High-speed contacts directly soldered to Eye Speed\* ultra low skew twinax

#### NOVARAY® I/O EXTREME PERFORMANCE SYSTEM

- Up to 3,584 Gbps PAM4 aggregate data from the IC package to the panel and beyond
- No heat sinks required for panel space savings

#### **NOVARAY® I/O**

- 16 and 32 differential pair configurations
- Accommodates PCle® x4 or x8 plus sidebands
- 28 or 34 AWG (external) and 34 AWG (internal) ultra low skew twinax
- Cable-to-cable bulkhead panel connection using Flyover® cable technology
- Multiple end 2 high-speed connector options including AcceleRate<sup>®</sup>, NovaRay<sup>®</sup> and Si-Fly<sup>™</sup>




NVACP/NVACE/NVC





TARGETED CONFIGURATIONS	AGGREGATE DATA RATE
8 Pair (in development)	896 Gbps
16 Pair	1792 Gbps
32 Pair	3584 Gbps
x4 (8 Pair + PCle® Sidebands)	512 Gbps
x8 (16 Pair + PCle® Sidebands)	1024 Gbps



 $PCI-SIG^*, PCI\ Express^*\ and\ the\ PCIe^*\ design\ marks\ are\ registered\ trademarks\ and/or\ service\ marks\ of\ PCI-SIG.$ 



Right-angle to front panel available for design flexibility



Roadmap: NovaRay® I/O in a rugged 38999 shell & salt fog resistant to 48 hours

#### ExaMAX® I/O SHIELDED CABLE SYSTEM

- Fully shielded external cable and cage for EMI protection
- Rugged pull latch for mating/unmating
- Cage designed for use with ExaMAX® right-angle board connector (EBTM-RA)
- 30 and 34 AWG ultra low skew twinax
- 24 to 72 pairs (4 and 6 pairs; 6, 8, 10 and 12 columns)
- Roadmap: cable-to-cable bulkhead panel connection for increased performance to 112 Gbps PAM4








## **FLYOVER®** MID-BOARD ASSEMBLIES





#### NOVARAY® EXTREME HIGH-SPEED, HIGH-DENSITY CABLE

- Industry leading aggregate data rate density 2x the data rate in 60% of the space
- Proprietary pin to ground configuration enables very low crosstalk (to 40 GHz) and very tight impedance control
- Two reliable points of contact guaranteed
- BGA attach for density and optimized trace breakout region
- Evaluation Kits available, see page 27 or visit samtec.com/kits












**NVAC/NVAM-CT** 


AGGREGATE DATA RATE (NRZ)						
448 Gbps	672 Gbps	896 Gbps		1344 Gbps	1792 Gbps	4032 Gbps*
	1 Bank			2 Bank		3 Bank*
2 Row	3 Row	4 Row	2 Row	3 Row	4 Row	6 Row*
8 Pairs	12 Pairs	16 Pairs		24 Pairs	32 Pairs	72 Pairs*

\*In development



#### **ACCELERATE® HP EXTREME DENSITY SYSTEM**

- Industry's highest density 112 Gbps PAM4 cable-to-board system
- Supports today's 256-channel chip and tomorrow's 512-channel chip
- Staggered row-to-row spacing of 2.2 mm x 2.4 mm allows adequate routing lanes for optimized traces; 0.635 mm contact pitch
- 32 to 72 differential pairs; up to 96 pairs in development
- Eye Speed® 34 AWG ultra low skew twinax cable
- BGA solder ball attach for simplified processing
- Right-angle shielded mating connector in development (APF6-RA)









ACCELERATE"HP

35 mm x 35 mm footprint holds two 72 differential pair connectors (144 total pins)


#### **ACCELERATE® HP GEN 2 ON-PACKAGE SYSTEM**

- Samtec is the first to achieve a direct-to-chip package solution with the industry's highest density 112 Gbps PAM4 interconnect
- Double the density in the same Gen 1 footprint; up to 144 differential pairs
- 182 differential pairs per square inch
- Staggered row-to-row spacing; 0.635 mm contact pitch
- Eye Speed® Thinax™ ultra performance twinax cable (see page 20 for information)
- Vertical cable application provides the highest footprint density
- 2-piece system for high reliability and thermal performance required for co-packaged solutions
- Roadmap: Single-ended signaling micro coax cable assembly, and mixed wafer technology with micro coax and Thinax<sup>™</sup> cable





AcceleRate\* HP routing in HDI PCB with excellent crosstalk isolation and unimpeded routing channels




#### Flyover® Mid-Board Assemblies (continued)




#### ACCELERATE® SLIM, DIRECT ATTACH SYSTEM

- Slimmest cable assembly in the industry 7.6 mm width
- 8, 16 and 24 differential pair configurations in a high-density 2-row design; 72 pairs in development
- NRZ PAM4
  28 56
  6 b p s

- PCIe® 5.0 capable
- Contacts directly soldered to the cable improves signal integrity by eliminating the transition board and its variability
- Eye Speed® 34 AWG ultra low skew twinax cable
- Rugged metal latching and shielding
- "Reversed Polarity" pinout option for reduced Far-End Crosstalk
- Evaluation Kit available, see page 27 or visit samtec.com/kits







## ACCELERATE® MINI EXTREME PERFORMANCE SYSTEM

- Design flexibility as an End 2 option for Flyover® assemblies
- One or two differential pairs
- Eye Speed® 34 AWG Thinax™ ultra performance twinax cable (see page 20 for more information)
- Vertical and right-angle mating board connector

#### **ACCELERATE**® mini




**ACCELERATE®** 

ARC6/ARF6

#### GENERATE™ HIGH-SPEED EDGE CARD SYSTEM


- Compatible with SFF-TA-1002 (1C, 2C, 4C & 4C+)
- Surpasses PCIe® 4.0 and 5.0 performance requirements
- Edge Rate® contacts optimized for signal integrity performance
- Vertical or right-angle cable launch
- Mates with Generate<sup>™</sup>
   0.60 mm pitch high-speed edge card socket (HSEC6)
- Rugged metal latching system





#### SI-FLY™ LOW PROFILE CABLE SYSTEM

- Up to 16 pairs in an extremely low 3.8 mm profile for placement adjacent to the IC package, under heat sinks or other cooling hardware
- 112 Gbps PAM4 per lane enabling 25.6 TB aggregate with a path to 51.2 TB
- High-density 8 or 16 pairs for routing 4 or 8 channels
- Eye Speed® 34 AWG ultra low skew twinax cable
- 8.4 mm minimum height required for mating
- Evaluation Kit available, see page 27 or visit samtec.com/kits









CPC/CPI






- Vertically launched cables for the highest density package
- 64 pairs in an incredibly small 13 mm x 13 mm footprint
- 245 differential pairs per square inch
- 0.53 mm (Signal-Ground) and 0.40 mm (Signal-Signal) contact pitch; 1.25 mm row-to-row pitch
- Designed for High Density Interconnect (HDI) and package substrates
- Eye Speed® Thinax™
   ultra performance twinax
   cable (see page 20 for
   additional information)














Ultra-high density solution for co-packaged applications.

# FLYOVER® BACKPLANE CABLES





## NOVARAY® MICRO RUGGED BACKPLANE SYSTEM


- True 112 Gbps PAM4 signal integrity with Flyover® support
- Cable-to-board, cable-to-cable, board-to-board
- Configurable signal banks for design flexibility
- Offset footprint for optimal signal integrity performance
- Reliable two points of contact for stub free mating
- Large continuous ground blades between and surrounding the differential pairs eliminates resonances
- Optional guidance and keying for blind mate



Precision Insert Molded Contact System



Solder Charge Termination for Higher Densities





Single-Ended or Differential Pair Wafers

#### ExaMAX® HIGH-SPEED BACKPLANE SYSTEM

**ExaMAX**®

- Cable-to-cable, cable-to-board, mid-board and panel applications
- Highly customizable with modular flexibility
- Reduced costs due to lower PCB layer counts
- 4 and 6 pairs; 4-16 columns
- Integrated guidance and keying options
- Multiple end 2 options available
- Evaluation Kit available, see page 27 or visit samtec.com/kits








EBCF/EBDM-RA

Cable-to-DMO (Direct Mate Orthogonal)






ExaMAX® I/O Cable System also available (see page 9)




Roadmap: 8 Pairs for Greater Design Flexibility



# **HIGH-SPEED**CABLE ASSEMBLIES








## MICRO COAX & TWINAX CABLE ASSEMBLIES

- Ability to mix-and-match end options for applicationspecific requirements with extensive customizing capabilities
- Single-ended 50  $\Omega$  & differential 100  $\Omega$  standards
- Rugged features and options including strain relief, plastic housings, screw downs, latches, locks, etc.
- Many non-cataloged standards available including 75  $\Omega$  micro coax and high-density twinax solutions

## EYE® EYE SPEED® SPEED CABLE TECHNOLOGY

- Excellent signal integrity performance with individual copper serve or braid shielding
- Stranded conductor for small bend radii and dynamic high flexing cycle applications
- Cost-effective ribbonizing eliminates discrete wires
- 26-38 AWG coax and twinax construction; 20  $\Omega,$  50  $\Omega,$  85  $\Omega$  & 100  $\Omega$



Samtec's Eye Speed® cable supports a wide variety of assemblies and applications

#### **HIGH-DENSITY ASSEMBLIES**

- 1.27 mm (SEAC) and 0.80 mm pitch (ESCA)
- 34 or 36 AWG coax; 32 AWG twinax
- Mates with SEARAY<sup>™</sup> and SEARAY<sup>™</sup> 0.80 mm arrays
- Optional rugged latching





#### **GROUND PLANE ASSEMBLIES**

- Integral power/ground plane
- 34 and 38 AWG coax; 30 AWG twinax
- 0.50 mm (HQCD/HQDP) and 0.80 mm pitch (EQCD/EQDP/EQRD)
- Mates with Q Series® and Q Rate® connectors







#### **EDGE CARD ASSEMBLIES**

30 AWG twinax (ECDP); mates with Generate<sup>™</sup> 0.80 mm pitch edge cards (HSEC8)

• PCI Express® twinax assemblies support 3.0/4.0/5.0 data transfer rates (PCIEC)

 FireFly<sup>™</sup> copper available as standard (14 Gbps), optimized (56 Gbps PAM4) and PCle<sup>®</sup> 4.0; Evaluation Kit available, see page 27 or visit samtec.com/kits

 34 AWG ultra low skew twinax (FEDP); mates with 0.50 mm pitch edge card (FCDP)









#### HIGH-SPEED ASSEMBLIES

- Ultra-micro hermaphroditic Razor Beam<sup>™</sup> coax assemblies with rugged shielding (HLCD)
- 0.80 mm pitch Edge Rate® coax and twinax assemblies (ERCD, ERDP)
- 38 AWG coax & 30 AWG twinax assemblies



# HIGH-SPEED CABLE DESIGN FLEXIBILITY






ANY
high-speed
connector

ANY break-out configuration

high-speed precision cable

... to create a solution for any specific application.

HDR@samtec.com



Visit **samtec.com/custom** for additional information.

#### WILLINGNESS, SUPPORT & EXPERTISE

#### **Industry-Leading Customer Service**

- Quotes and samples in 24 hours
- Prototype and processing assistance
- **Dedicated Application Specific** Product engineers and technicians


#### Flexible, In-House Manufacturing

- Global Operations, including multiple cable fabrication & assembly facilities
- Quick-turn samples and prototypes
- Custom & modified product support

#### **Signal Integrity Expertise**

- Industry-leading engineering support for high-performance system design
- Full system optimization assistance, including simulation, testing, analysis and evaluation











#### **CUSTOMS & EXPRESS MODIFICATIONS**


Samtec is able to support completely new and/or custom designs, as well as common simple modifications to cable assemblies and board-to-board products - often with low or no NRE charges, short lead times, quick-turn samples, and low or no MOQ's. Capabilities include:

- Contacts
- **Bodies**
- Stamping
- Ruggedizing features
- Wiring
- Molding
- Plating
- Polarization

- Packaging
- Labeling
- Ink printing

• Shielding modifications





# **EYE SPEED**<sup>®</sup> CABLE TECHNOLOGY



Additional Metalized Barrier

> for Ultimate Reliability

High-Temp Extruded Jacket

Advanced Cu Alloy

Twinax Shield

Low Dk Dielectric Co-extruded Technology

for Dimensional Consistency

Ag Plated Cu Solid Center Conductor

#### ULTRA LOW SKEW TWINAX CABLE

Samtec's proprietary Eye Speed® co-extruded twinax cable technology eliminates the performance limitations and inconsistencies of individually extruded dielectric twinax cabling, improving signal integrity, bandwidth and reach for high-performance system architectures.

- Tight coupling between signal conductors
- Improved bandwidth (28-112+ Gbps) and reach
- Improved signal integrity and eye pattern opening
- Low skew (< 3.5 ps/meter) over extended lengths
- Supports Samtec Flyover® technology

#### Micro Cellular Dielectric Extrusion

- Critical dimensions measured at every dielectric spool
- Inline laser and CAPAC devices for capacitance monitoring and diameter control
- In-process stats summary sheet for Cpk acceptance



<sup>\*</sup> Eye Speed\* Ultra Low Skew Twinax Cable is available in engineered impedance configurations of 85  $\Omega$ , 92  $\Omega$  and 100  $\Omega$ .

#### THINAX™ ULTRA PERFORMANCE TWINAX CABLE


- 40% smaller cross-sectional area
- 112 Gbps PAM4 performance
- Taped jacket miniaturizes the cable to match smaller, more dense connectors
- Allows for a smaller pitch within a row
- Achieving a smaller row-to-row pitch is dependent upon stack-up and BOR; customizable per application needs





#### **DIRECT ATTACH CABLE**

- High-density contacts directly soldered to the Eye Speed® ultra low skew twinax cable
- Improved signal integrity by eliminating the transition board and its variability
- Achieves tighter tolerances



#### MICRO COAX CABLE

- Foaming introduces air voids for signal to travel faster
- Solid extrusion of foamed dielectric provides a constant and more durable construction
- Lighter weight and smaller size with higher bandwidth capabilities at longer lengths
- 26 38 AWG cable available
- Choice of signal conductor, shield and FEP dielectric to meet performance and cost specifications




#### DYNAMIC TESTING

**Samtec Eye Speed**\* **Ultra Low Skew Twinax** cable underwent Dynamic Insertion and Return Loss testing, proving the cable to be rugged with stable electrical performance after 250 flex/bend cycles.

This arduous flex and bend test determined that the performance of Samtec Eye Speed® ultra low skew twinax is essentially indistinguishable from the original raw, unbent cable.

Ultra low skew twinax provides the lowest insertion loss in the industry, controlled performance across temperature, and robust insertion loss in any assembly and operation environment. Contact **HDR@samtec.com** for higher cycle results.



Six feet of ultra low skew twinax cable on mandrels was coiled/uncoiled moving back and forth on a slide at a rate of 20-25 cycles per minute.

#### CABLE MANAGEMENT

- Samtec works with system architects in the early stages to optimize the architecture for cable management while keeping signal integrity and thermals in mind
- Complimentary service using mockups with accurate cable lengths
- Minimize number of SKUs within one system
- Minimize pressure drop




# **ADVANCED**OPTICAL SYSTEMS




### FIREFLY™ MICRO FLYOVER SYSTEM™ samtec.com/firefly

- Designed for flexibility, optical (ECUO) for greater distances and copper (ECUE; page 17) for cost optimization
- Industry leading miniature footprint allows for higher density close to the data source
- x4 and x12 configurations
- PCle®-Over-Fiber supports 3.0/4.0 data rates for low latency, power savings and guaranteed transmission
- -40 °C to +85 °C extended temperature system (ETUO) for military, aerospace and industrial applications
- Extreme Environment FireFly<sup>™</sup> sealed and Parylene-Coated for exposed applications (ETMO)
- Supports data center, HPC and FPGA protocols, including Ethernet, InfiniBand<sup>™</sup>, Fibre Channel, Aurora and PCle<sup>®</sup>
- Multiple end options available: MTP<sup>®</sup>, MXC<sup>®</sup>, MT, Glenair<sup>®</sup> Series 79, VITA 66.X and other common interfaces
- Development Kit available, see page 27 or visit samtec.com/kits





PCIe\*-Over-Fiber Adaptor Card (PCOA), available in x4, x8 or x16 configurations; supports 3.0/4.0 platforms and transparent or non-transparent bridging



Extended Temp FireFly™ (ETUO) with Amphenol® Aerospace's bulkhead interconnects (MT38999) for rugged optical solutions



Glenair® Series 79 MT connector is an End 2 option featuring a miniature form factor and shielding; ideal for mil/aero and industrial applications

ECUO	PCUO	ETUO	PCOA
FireFly™ Optical  14 x4 x12 25 x4 x12	PCle®-Over-Fiber  PCle® 3.0 x4 PCle® 3.0 x8 PCle® 3.0 x16	Extended Temp FireFly™  10  x4, x12	PCle®-Over-Fiber 3.0/4.0 Adaptor Card
16 x12 28 x4	PCle® 4.0 x4 PCle® 4.0 x8 PCle® 4.0 x16	<b>25</b> x4	with FireFly <sup>™</sup>

MTP® and MXC® are registered trademarks of US Conec Ltd. Amphenol® is a registered trademark of Amphenol Corp.




#### FIREHAWK™ RUGGEDIZED OPTICAL TRANSCEIVERS

#### samtec.com/firehawk

- Chip Scale Package (CSP) with the industry's smallest footprint and lowest profile, weighing less than 0.4 grams
- FireHawk<sup>™</sup> for Mil/Aero with an integrated microcontroller to automate key functions (CSPO)
- FireHawk<sup>™</sup> for Space designed to withstand the impacts of radiation without the need for a microcontroller (CSSO)
- Extreme performance with up to 40 Gbps transfer rate
- 10G x 4 data rate (10 Mbps to 10 Gbps per channel)
- Rugged BGA board attach withstands high shock and vibration
- -40 °C to +85 °C extreme temperature range (+95 °C available)
- RVCON® optical cables are removable and replaceable for repair or reconfiguration
- Development Kit available, see page 27 or visit samtec.com/kits
- Roadmap: 25G x 4 system (up to 25 Gbps per channel) in the same 10G connector footprint






Ultra-compact, SWaP-optimized (Size, Weight and Power)



SMT reflow solderable with standard pick-and-place pad




Direct mount to the PCB provides shortest possible thermal path



#### HALO™ NEXT GEN OPTICAL

- Capable of up to 112 Gbps PAM4 per lane
- Up to 16 channels (8 channel bidirectional)
- Low 6 mm profile with a 2-piece contact system
- Designed to withstand high shock and vibration
- Features a low center of gravity for a stable connection to the board
- Optically pluggable for easy replacement and increased uptime



## HIGH-PERFORMANCE RF SOLUTIONS



DC TO

BULLS EYE® HIGH-PERFORMANCE TEST TO 90 GHz


 High-density, space-saving design that enables smaller evaluation boards and shorter trace lengths in test and measurement applications to 90 GHz

 Compression mounts to the board for placement directly adjacent to the SerDes being characterized



- End 2 connection to instrumentation:
   1.00 mm, 1.85 mm, 2.40 mm or 2.92 mm
- Single or double row
- Complete list of applications: SerDes characterization, clock/data recovery (CDR), mmWave radar, automated test equipment, FR2 5G networks
- Evaluation Kits available, see page 27 or visit samtec.com/kits

Frequency		90 GHz	70 GHz	50 GHz
Samtec Series		BE90A	BE70A	BE40A
Connection to Instrumentation 1.00 mm		1.85 mm	2.40 mm (50 GHz) 2.92 mm (40 GHz)	
No. of Block Rows		Single or Double		Double Row
Options	No. of Positions	1x: 2, 4, 8, 12 2x: 4, 8, 12, 16	1x: 2, 4, 8, 12 2x: 3, 4, 6, 8, 10, 12, 14, 16	2x: 3, 4, 6, 8, 10, 12, 14, 16



Test Assembly	BE90A	ВЕ70А	BE40A	
SerDes Characterization	4 Z Z 4 G b p s	4 M M M M M M M M M M M M M M M M M M M	26 g p b s	

# HIGH-SPEED TEST CABLES • Breakout test cables with RF connectors • Capable of supporting PCle\* 4.0 and 5.0 (PCRF-G4/-G5) • Capable of supporting 56 Gbps PAM4 (GC6-RF) PCRF-G5 GC6-RF



#### PRECISION RF CABLE ASSEMBLIES & CONNECTORS

• High-frequency, microwave/millimeter wave solutions to 110 GHz

Cable assemblies, cable connectors & board level connectors

 Variety of interfaces: 1.00 mm, 1.35 mm, 1.85 mm, 2.40 mm, 2.92 mm, 3.50 mm, SSMA, SMP, SMPM, ganged SMPM, SMA, N Type, TNCA

- Magnum RF<sup>™</sup> ganged SMPM for 40% greater density, less processing time and better positional alignment
- Low-loss microwave and millimeter wave cable from .047" to .277"
- Vertical or edge launch solderless compression mount board connectors for test and measurement applications
- Soldered push-on board connectors for high-density, blind-mate applications
- Between-series and in-series adaptors designed for well-performing VSWR



#### **NEXT GEN RF CABLE ASSEMBLIES**

 Phase and insertion loss stable microwave/millimeter wave cables -Orange is the New Cable!

- Optimized coaxial structure to meet increased demands placed on the Aerospace, Defense, Datacom, Computer/Semi and Instrumentation markets
- Cable construction designed to support extended frequency ranges for emerging applications
- Next gen cable provides improved IL performance vs. industry standard cable at the extended frequency range
- Interface options include 1.00 mm, 1.35 mm, 1.85 mm, 2.40 mm, 2.92 mm, SMPM, SMP, SMA, N Type and TNCA

#### FLEXIBLE WAVEGUIDE

- Innovative technology that is flexible, easier to use and lower cost, while also maintaining low insertion loss, versus traditional metallic rigid waveguides
- E-Band frequency range of 60 to 90 GHz in development
- Flexible cable construction with dynamic stability
- Less signal loss than standard microwave coax cable
- Ultra-small form factor with threaded coupling and stripline routing



# CABLE TECHNOLOGY & MANUFACTURING EXPERTISE

Samtec's state-of-the-art High-Speed Cable Plants provide industry-leading R&D and manufacturing of precision extruded micro coax and twinax cable, and next generation RF cable technology. Our priority is the development of differentiated products and technologies that address the existing and future challenges of bandwidth, reach, signal integrity, and phase stability demands.


#### MANUFACTURING TECHNOLOGY


- World-class in-house expertise
- Internally developed proprietary processes
- Extensive customization capabilities
- Procurement and test of new materials
- Quick-turn design and manufacturing
- Unparalleled pricing and delivery

#### **NEXT GENERATION INNOVATION**


- Real-time closed-loop control to adjust parameters
- Microcellular dielectric extrusion
- Co-extruded, low loss twinax cable
- Extreme density twinax cable
- Phase and insertion loss stable high frequency RF cable
- Halogen-free materials
- Thermal capabilities















# **EVALUATION &**DEVELOPMENT KITS

Samtec Evaluation and Development Kits provide system designers and engineers easy-to-use platforms for testing many of Samtec's popular products, helping to simplify the design process and reduce time to market.

Each kit includes the evaluation platform, calibration board(s), technical documentation and test reports. Additionally, each kit is tested and verified by Samtec's signal integrity experts before customer delivery. Visit <a href="mailto:samtec.com/kits">samtec.com/kits</a> or contact <a href="mailto:kitsandboards@samtec.com">kitsandboards@samtec.com</a> for current availability.

#### SIGNAL INTEGRITY EVALUATION KITS



AcceleRate® Flyover® Slim Cable System (ARC6/ARF6)



NovaRay® Flyover® Cable System (NVAC/NVAM-C)



Si-Fly™ Low Profile Cable System (CPC/CPI)



Flyover® QSFP Cable System (FQSFP to ARC6)



Flyover® QSFP
Double Density Cable System
(FQSFP-DD to NVAC/ARC6)



ExaMAX\* Backplane Cable System (EBCM/EBTF-RA)



FireFly™ Copper Micro Flyover System™ (ECUE/UEC5-2/UCC8)



Bulls Eye\* 50 GHz High-Performance Test System (BE40A)



Bulls Eye\* 70 GHz High-Performance Test System (BE70A)

#### **OPTICS KITS**



25/28 Gbps FireFly™ FMC+ Kit



28 Gbps FireFly™ Kit



14 Gbps FireFly™ FMC Kit



10 Gbps FireHawk™ Kit

# **SAMTEC**SUDDEN SERVICE®



#### **UNMATCHED LEADTIMES** Deliveries in Days, Not Weeks

Optimized logistics and innovative programs, along with Samtec's unique infrastructure and flexibility, help expedite the ordering process and get parts delivered in the fastest most efficient way possible.



This designation allows customers to quickly and easily identify availability of over 200,000 of Samtec's most popular connectors and cables - guaranteed to ship in 1-day.

Look for the **Reserve** badge throughout **samtec.com** to quickly determine if your part number is eligible, along with current availability, quantity breaks and pricing. Hundreds of part numbers are being added daily!





Free product samples, shipped in 24-hours or less have been a cornerstone of Samtec Sudden Service\* since the company was founded. Visit samtec.com to quickly request your sample.



An innovative shipping program that bridges the gap between manufacturing facilities and customers, allowing for manufacturing flexibility without increased costs, and with even faster lead-times. Contact eCustomerService@samtec.com to learn more.

#### 24/7 WORLDWIDE ACCESS | The Industry's Service & Technology Leader

#### **Technical Support**

Signal Integrity Group: sig@samtec.com

Application Support Group: asg@samtec.com

Interconnect Processing Group: <a href="mailto:ipg@samtec.com">ipg@samtec.com</a>

#### **Supply Chain Support**

MySamtec™ Real-Time Account Access: account.samtec.com

Personal Account Managers/CSRs: eCustomerService@samtec.com

Upfront, Aggressive 24-Hour Quotes: ePricing@samtec.com

#### mySamtec™ | A Personalized Web Experience for Easy Ordering

Samtec's user-friendly eCommerce platform allows you to quickly and easily check product availability and pricing, as well as place and manage your orders online. Visit account.samtec.com to access your account.

#### **ONLINE TOOLS** Find, Design & Validate Your Solution

Quickly and easily find the right solution, whether you prefer to search by product name or characteristics, browse through pictures, or build an assembly by entering physical specifications.

#### Picture Search

Browse through a highlight reel of Samtec's most popular products to find the ideal solution for your application, view specifications, check availability, order samples and more.





samtec.com/picturesearch/high-speed-cable

#### Downloadable Resources

Samtec offers immediate and unlimited access to all the resources needed to select the right solution - from 3D models, prints and footprints, to test reports, white papers and much more. Visit **samtec.com** to start exploring.



#### Solutionator<sup>®</sup>

Quickly build mated connector sets or design full cable assemblies using a wide variety of user-defined search parameters and filters, view specs and order samples in Samtec's online design tools.





samtec.com/cablebuilder





samtec.com/hsb2b-solutionator

#### Solutionator RF



samtec.com/rf-cablebuilder

#### Solutionator FLEX STACKING



samtec.com/flex-solutionator

#### Solutionator OPTICS




samtec.com/optics-solutionato

# INTEGRATION LEADS TO INNOVATION

Samtec's integrated business model facilitates high-level design and development of advanced interconnect systems and **TECHNOLOGIES**. Along with industry-leading expertise, this allows us to offer effective strategies and support for **optimizing the entire signal channel of high-performance systems**.


Samtec is structured like no other company in the interconnect industry. We work in a fully integrated capacity that enables true collaboration and results in uniquely innovative **PRODUCTS** because **our technology teams are not limited by the boundaries of traditional business units.** 



# SILICON-TO-SILICON<sup>TM</sup> SOLUTIONS

As bandwidth, scale and power requirements continue to challenge conventional engineering methods, Samtec strives to help optimize the landscape of your entire system - and develop solutions, together.

Samtec's industry-leading signal integrity expertise, full system optimization strategies, and innovative products



## **GLOBAL SUPPORT NETWORK**





www.samtec.com

ISO-9001 and/or IATF 16949 Certified © JUNE 2023, SAMTEC INC.