




Project Number: Design Qualification Test Report	Tracking Code: 1382911_Report_Rev_1
Requested by: Mark Shireman	Date: 5/2/2018
Part #: SS-132-S-2/BBL-132-G-E	
Part description: SS/BBL	Tech: Kason He
Test Start: 3/28/2018	Test Completed: 4/25/2018



## **DESIGN QUALIFICATION TEST REPORT**

**SS/BBL**  
**SS-132-S-2/BBL-132-G-E**

Tracking Code: 1382911_Report_Rev_1	Part #: SS-132-S-2/BBL-132-G-E
Part description: SS/BBL	

## REVISION HISTORY

DATA	REV.NUM.	DESCRIPTION	ENG
5/2/2018	1	Initial Issue	KH

## CERTIFICATION

All instruments and measuring equipment were calibrated to National Institute for Standards and Technology (NIST) traceable standards according to ISO 10012-1 and ANSI/NCSL 2540-1, as applicable.

All contents contained herein are the property of Samtec. No portion of this report, in part or in full shall be reproduced without prior written approval of Samtec.

### SCOPE

To perform the following tests: Design Qualification test. Please see test plan.

### APPLICABLE DOCUMENTS

Standards: EIA Publication 364

### TEST SAMPLES AND PREPARATION

- 1) All materials were manufactured in accordance with the applicable product specification.
- 2) All test samples were identified and encoded to maintain traceability throughout the test sequences.
- 3) After soldering, the parts to be used for LLCR and DWV/IR testing were cleaned according to TLWI-0001.
- 4) Either an automated cleaning procedure or an ultrasonic cleaning procedure may be used.
- 5) The automated procedure is used with aqueous compatible soldering materials.
- 6) Parts not intended for testing LLCR and DWV/IR are visually inspected and cleaned if necessary.
- 7) Any additional preparation will be noted in the individual test sequences.
- 8) Solder Information: Lead free
- 9) Samtec Test PCBs used: PCB-108900-TST/PCB-108901-TST/PCB-108903-TST

## FLOWCHARTS

### Gas Tight

#### Group 1

SS-132-S-2

BBL-132-G-E

8 Assemblies

---

#### **Step    Description**

1.    LLCR <sup>(2)</sup>
2.    Gas Tight <sup>(1)</sup>
3.    LLCR <sup>(2)</sup>  
Max Delta = 15 mOhm

---

(1) Gas Tight = EIA-364-36

(2) LLCR = EIA-364-23

    Open Circuit Voltage = 20 mV Max

    Test Current = 100 mA Max

### Thermal Aging

#### Group 1

SS-132-S-2

BBL-132-G-E

8 Assemblies

---

#### **Step    Description**

1.    Contact Gaps
2.    Mating/Unmating Force <sup>(2)</sup>
3.    LLCR <sup>(1)</sup>
4.    Thermal Age <sup>(3)</sup>
5.    LLCR <sup>(1)</sup>  
Max Delta = 15 mOhm
6.    Mating/Unmating Force <sup>(2)</sup>
7.    Contact Gaps

---

(1) LLCR = EIA-364-23

    Open Circuit Voltage = 20 mV Max

    Test Current = 100 mA Max

(2) Mating/Unmating Force = EIA-364-13

(3) Thermal Age = EIA-364-17

    Test Condition = 4 (105°C)

    Time Condition = B (250 Hours)

## FLOWCHARTS Continued

### Mating/Unmating/Durability

**Group 1**

SS-132-S-2  
BBL-132-G-E  
8 Assemblies

**Group 2**

SS-116-S-2  
BBL-116-G-E  
8 Assemblies

**Group 3**

SS-104-S-2  
BBL-104-G-E  
8 Assemblies

**Step Description**

1. Contact Gaps
2. LLCR <sup>(2)</sup>
3. Mating/Unmating Force <sup>(3)</sup>
4. Cycles  
Quantity = 25 Cycles
5. Mating/Unmating Force <sup>(3)</sup>
6. Cycles  
Quantity = 25 Cycles
7. Mating/Unmating Force <sup>(3)</sup>
8. Cycles  
Quantity = 25 Cycles
9. Mating/Unmating Force <sup>(3)</sup>
10. Cycles  
Quantity = 25 Cycles
11. Mating/Unmating Force <sup>(3)</sup>
12. Contact Gaps
13. LLCR <sup>(2)</sup>  
Max Delta = 15 mOhm
14. Thermal Shock <sup>(4)</sup>
15. LLCR <sup>(2)</sup>  
Max Delta = 15 mOhm
16. Humidity <sup>(1)</sup>
17. LLCR <sup>(2)</sup>  
Max Delta = 15 mOhm
18. Mating/Unmating Force <sup>(3)</sup>

**Step Description**

1. Contact Gaps
2. Mating/Unmating Force <sup>(3)</sup>
3. Cycles  
Quantity = 25 Cycles
4. Mating/Unmating Force <sup>(3)</sup>

**Step Description**

1. Contact Gaps
2. Mating/Unmating Force <sup>(3)</sup>
3. Cycles  
Quantity = 25 Cycles
4. Mating/Unmating Force <sup>(3)</sup>

(1) Humidity = EIA-364-31

Test Condition = B (240 Hours)

Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)

Test Exceptions: ambient pre-condition and delete steps 7a ar

(2) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(3) Mating/Unmating Force = EIA-364-13

(4) Thermal Shock = EIA-364-32

Exposure Time at Temperature Extremes = 1/2 Hour

Method A, Test Condition = I (-55°C to +85°C)

Test Duration = A-3 (100 Cycles)

## FLOWCHARTS Continued

### IR/DWV

#### Pin-to-Pin

Group 1		Group 2		Group 3		Group 4	
SS-132-S-2		SS-132-S-2		BBL-132-G-E		SS-132-S-2	
BBL-132-G-E		2 Assemblies		2 Assemblies		BBL-132-G-E	
2 Assemblies		2 Assemblies		2 Assemblies		2 Assemblies	
Step	Description	Step	Description	Step	Description	Step	Description
1.	DWV Breakdown <sup>(2)</sup>	1.	DWV Breakdown <sup>(2)</sup>	1.	DWV Breakdown <sup>(2)</sup>	1.	IR <sup>(4)</sup>
							DWV at Test Voltage <sup>(1)</sup>
							Thermal Shock <sup>(5)</sup>
							IR <sup>(4)</sup>
							DWV at Test Voltage <sup>(1)</sup>
							Humidity <sup>(3)</sup>
							IR <sup>(4)</sup>
							DWV at Test Voltage <sup>(1)</sup>

(1) DWV at Test Voltage = EIA-364-20

Test Condition = 1 (Sea Level)

DWV test voltage is equal to 75% of the lowest breakdown voltage

Test voltage applied for 60 seconds

(2) DWV Breakdown = EIA-364-20

Test Condition = 1 (Sea Level)

DWV test voltage is equal to 75% of the lowest breakdown voltage

Test voltage applied for 60 seconds

(3) Humidity = EIA-364-31

Test Condition = B (240 Hours)

Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)

Test Exceptions: ambient pre-condition and delete steps 7a and 7b

(4) IR = EIA-364-21

Test Condition = 500 Vdc, 2 Minutes Max

(5) Thermal Shock = EIA-364-32

Exposure Time at Temperature Extremes = 1/2 Hour

Method A, Test Condition = I (-55°C to +85°C)

Test Duration = A-3 (100 Cycles)

## FLOWCHARTS Continued

### Current Carrying Capacity

<u>Group 1</u>		<u>Group 2</u>		<u>Group 3</u>		<u>Group 4</u>	
SS-132-S-2		SS-132-S-2		SS-132-S-2		SS-132-S-2	
BBL-132-G-E		BBL-132-G-E		BBL-132-G-E		BBL-132-G-E	
<b>Step</b>	<b>Description</b>	<b>Step</b>	<b>Description</b>	<b>Step</b>	<b>Description</b>	<b>Step</b>	<b>Description</b>
1.	CCC (1) Rows = 1 Number of Positions = 1	1.	CCC (1) Rows = 1 Number of Positions = 2	1.	CCC (1) Rows = 1 Number of Positions = 3	1.	CCC (1) Rows = 1 Number of Positions = 4
<hr/>							
<u>Group 5</u>							
SS-132-S-2							
BBL-132-G-E							
32 Pins Powered							
Signal							
<b>Step</b>	<b>Description</b>						
1.	CCC (1) Rows = 1 Number of Positions = 32						

(1) CCC = EIA-364-70

Method 2, Temperature Rise Versus Current Curve

(TIN PLATING) - Tabulate calculated current at RT, 65°C, 75°C and 95°C after derating 20% and based on 105°C

(GOLD PLATING) - Tabulate calculated current at RT, 85°C, 95°C and 115°C after derating 20% and based on 125°C

## FLOWCHARTS Continued

### Mechanical Shock/Random Vibration/LLCR

Group 1

SS-132-S-2

BBL-132-G-E

8 Assemblies

---

**Step Description**

1. LLCR <sup>(1)</sup>
2. Mechanical Shock <sup>(2)</sup>
3. Random Vibration <sup>(3)</sup>
4. LLCR <sup>(1)</sup>  
Max Delta = 15 mOhm

---

(1) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(2) Mechanical Shock = EIA-364-27

Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)

Number of Shocks = 3 Per Direction, Per Axis, 18 Total

(3) Random Vibration = EIA-364-28

Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

### Mechanical Shock/Random Vibration/Event Detection

Group 1

SS-132-S-2

BBL-132-G-E

60 Points

---

**Step Description**

1. Nanosecond Event Detection  
(Mechanical Shock) <sup>(1)</sup>
2. Nanosecond Event Detection  
(Random Vibration) <sup>(2)</sup>

---

(1) Nanosecond Event Detection (Mechanical Shock)

Use EIA-364-87 for Nanosecond Event Detection:

Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-27 for Mechanical Shock:

Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)

Number of Shocks = 3 Per Direction, Per Axis, 18 Total

(2) Nanosecond Event Detection (Random Vibration)

Use EIA-364-87 for Nanosecond Event Detection:

Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-28 for Random Vibration:

Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

## ATTRIBUTE DEFINITIONS

The following is a brief, simplified description of attributes.

### **THERMAL SHOCK:**

- 1) EIA-364-32, *Thermal Shock (Temperature Cycling) Test Procedure for Electrical Connectors*.
- 2) Test Condition 1: -55°C to +85°C
- 3) Test Time: ½ hour dwell at each temperature extreme
- 4) Number of Cycles: 100
- 5) All test samples are pre-conditioned at ambient.
- 6) All test samples are exposed to environmental stressing in the mated condition.

### **THERMAL:**

- 1) EIA-364-17, *Temperature Life with or without Electrical Load Test Procedure for Electrical Connectors*.
- 2) Test Condition 4 at 105°C
- 3) Test Time Condition B for 250 hours.
- 4) All test samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

### **HUMIDITY:**

- 1) Reference document: EIA-364-31, *Humidity Test Procedure for Electrical Connectors*.
- 2) Test Condition B, 240 Hours.
- 3) Method III, +25°C to +65°C, 90% to 98% Relative Humidity excluding sub-cycles 7a and 7b.
- 4) All samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

### **MECHANICAL SHOCK (Specified Pulse):**

- 1) Reference document: EIA-364-27, *Mechanical Shock Test Procedure for Electrical Connectors*
- 2) Test Condition C
- 3) Peak Value: 100 G
- 4) Duration: 6 Milliseconds
- 5) Wave Form: Half Sine
- 6) Velocity: 12.3 ft/s
- 7) Number of Shocks: 3 Shocks / Direction, 3 Axis (18 Total)

### **VIBRATION:**

- 1) Reference document: EIA-364-28, *Vibration Test Procedure for Electrical Connectors*
- 2) Test Condition V, Letter B
- 3) Power Spectral Density: 0.04 G<sup>2</sup> / Hz
- 4) G 'RMS': 7.56
- 5) Frequency: 50 to 2000 Hz
- 6) Duration: 2.0 Hours per axis (3 axis total)

### **NANOSECOND-EVENT DETECTION:**

- 1) Reference document: EIA-364-87, *Nanosecond-Event Detection for Electrical Connectors*
- 2) Prior to test, the samples were characterized to assure the low nanosecond event being monitored will trigger the detector.
- 3) After characterization it was determined the test samples could be monitored for 50 nanosecond events

### **MATING/UNMATING:**

- 1) Reference document: EIA-364-13, *Mating and Unmating Forces Test Procedure for Electrical Connectors*.
- 2) The full insertion position was to within 0.003" to 0.004" of the plug bottoming out in the receptacle to prevent damage to the system under test.
- 3) One of the mating parts is secured to a floating X-Y table to prevent damage during cycling.

**ATTRIBUTE DEFINITIONS Continued**

The following is a brief, simplified description of attributes.

**LLCR:**

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
  - a.  $\leq +5.0$  mOhms: ----- Stable
  - b.  $+5.1$  to  $+10.0$  mOhms: ----- Minor
  - c.  $+10.1$  to  $+15.0$  mOhms: ----- Acceptable
  - d.  $+15.1$  to  $+50.0$  mOhms: ----- Marginal
  - e.  $+50.1$  to  $+2000$  mOhms: ----- Unstable
  - f.  $>+2000$  mOhms: ----- Open Failure

**TEMPERATURE RISE (Current Carrying Capacity, CCC):**

- 1) EIA-364-70, *Temperature Rise versus Current Test Procedure for Electrical Connectors and Sockets*.
- 2) When current passes through a contact, the temperature of the contact increases as a result of  $I^2R$  (resistive) heating.
- 3) The number of contacts being investigated plays a significant part in power dissipation and therefore temperature rise.
- 4) The size of the temperature probe can affect the measured temperature.
- 5) Copper traces on PC boards will contribute to temperature rise:
  - a. Self heating (resistive)
  - b. Reduction in heat sink capacity affecting the heated contacts
- 6) A de-rating curve, usually 20%, is calculated.
- 7) Calculated de-rated currents at four temperature points are reported:
  - a. Ambient
  - b.  $85^\circ C$
  - c.  $95^\circ C$
  - d.  $115^\circ C$
- 8) Typically, neighboring contacts (in close proximity to maximize heat build up) are energized.
- 9) The thermocouple (or temperature measuring probe) will be positioned at a location to sense the maximum temperature in the vicinity of the heat generation area.
- 10) A computer program, *TR 803.exe*, ensures accurate stability for data acquisition.
- 11) Hook-up wire cross section is larger than the cross section of any connector leads/PC board traces, jumpers, etc.
- 12) Hook-up wire length is longer than the minimum specified in the referencing standard.

**ATTRIBUTE DEFINITIONS Continued**

The following is a brief, simplified description of attributes.

**GAS TIGHT:**

To provide method for evaluating the ability of the contacting surfaces in preventing penetration of harsh vapors which might lead to oxide formation that may degrade the electrical performance of the contact system.

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
  - a.  $\leq +5.0$  mOhms: ----- Stable
  - b.  $+5.1$  to  $+10.0$  mOhms: ----- Minor
  - c.  $+10.1$  to  $+15.0$  mOhms: ----- Acceptable
  - d.  $+15.1$  to  $+50.0$  mOhms: ----- Marginal
  - e.  $+50.1$  to  $+2000$  mOhms: ----- Unstable
  - f.  $>+2000$  mOhms: ----- Open Failure
- 4) Procedure:
  - a. Reference document: EIA-364-36, *Test Procedure for Determination of Gas-Tight Characteristics for Electrical Connectors, Sockets and/or Contact Systems*.
  - b. Test Conditions:
    - i. Class II--- Mated pairs of contacts assembled to their plastic housings.
    - ii. Reagent grade Nitric Acid shall be used of sufficient volume to saturate the test chamber
    - iii. The ratio of the volume of the test chamber to the surface area of the acid shall be 10:1.
    - iv. The chamber shall be saturated with the vapor for at least 15 minutes before samples are added.
    - v. Exposure time, 55 to 65 minutes.
    - vi. The samples shall be no closer to the chamber walls than 1 inches and no closer to the surface of the acid than 3 inches.
    - vii. The samples shall be dried after exposure for a minimum of 1 hour.
    - viii. Drying temperature  $50^{\circ}\text{C}$
    - ix. The final LLCR shall be conducted within 1 hour after drying.

**ATTRIBUTE DEFINITIONS Continued**

The following is a brief, simplified description of attributes

**INSULATION RESISTANCE (IR):**

To determine the resistance of insulation materials to leakage of current through or on the surface of these materials when a DC potential is applied.

- 1) PROCEDURE:
  - a. Reference document: EIA-364-21, *Insulation Resistance Test Procedure for Electrical Connectors*.
  - b. Test Conditions:
    - i. Between Adjacent Contacts or Signal-to-Ground
    - ii. Electrification Time 2.0 minutes
    - iii. Test Voltage (500 VDC) corresponds to calibration settings for measuring resistances.
- 2) MEASUREMENTS:
- 3) When the specified test voltage is applied (VDC), the insulation resistance shall not be less than 5000 megohms.

**DIELECTRIC WITHSTANDING VOLTAGE (DWV):**

To determine if the sockets can operate at its rated voltage and withstand momentary over potentials due to switching, surges, and other similar phenomenon. Separate samples are used to evaluate the effect of environmental stresses so not to influence the readings from arcing that occurs during the measurement process.

- 1) PROCEDURE:
  - a. Reference document: EIA-364-20, *Withstanding Voltage Test Procedure for Electrical Connectors*.
  - b. Test Conditions:
    - i. Between Adjacent Contacts or Signal-to-Ground
    - ii. Barometric Test Condition 1
    - iii. Rate of Application 500 V/Sec
    - iv. Test Voltage (VAC) until breakdown occurs
- 2) MEASUREMENTS/CALCULATIONS
  - a. The breakdown voltage shall be measured and recorded.
  - b. The dielectric withstand voltage shall be recorded as 75% of the minimum breakdown voltage.
  - c. The working voltage shall be recorded as one-third (1/3) of the dielectric withstand voltage (one-fourth of the breakdown voltage).

## RESULTS

### Temperature Rise, CCC at a 20% de-rating

- CCC for a 30°C Temperature Rise-----5.0 A per contact with 1 contacts (1x1) powered
- CCC for a 30°C Temperature Rise-----4.4 A per contact with 2 contacts (1x2) powered
- CCC for a 30°C Temperature Rise-----3.9 A per contact with 3 contacts (1x3) powered
- CCC for a 30°C Temperature Rise-----3.9 A per contact with 4 contacts (1x4) powered
- CCC for a 30°C Temperature Rise-----2.6 A per contact with 32 contacts (1x32) powered

### Mating – Unmating Forces

#### Thermal Aging Group

- Initial
  - Mating
    - Min -----19.11 Lbs
    - Max-----23.06 Lbs
  - Unmating
    - Min -----10.48 Lbs
    - Max-----12.44 Lbs
- After Thermal
  - Mating
    - Min -----15.38 Lbs
    - Max-----16.89 Lbs
  - Unmating
    - Min -----10.09 Lbs
    - Max-----11.23 Lbs

## RESULTS Continued

### Mating – Unmating Forces

#### Mating-Unmating Durability Group (SS-132-S-2/BBL-132-G-E)

- Initial
  - Mating
    - Min -----18.03 Lbs
    - Max-----23.09 Lbs
  - Unmating
    - Min -----9.92 Lbs
    - Max-----15.92 Lbs
- After 25 Cycles
  - Mating
    - Min -----20.93 Lbs
    - Max-----28.26 Lbs
  - Unmating
    - Min -----13.93 Lbs
    - Max-----20.34 Lbs
- After 50 Cycles
  - Mating
    - Min -----23.29 Lbs
    - Max-----29.93 Lbs
  - Unmating
    - Min -----16.59 Lbs
    - Max-----23.34 Lbs
- After 75 Cycles
  - Mating
    - Min -----26.12 Lbs
    - Max-----32.12 Lbs
  - Unmating
    - Min -----18.74 Lbs
    - Max-----25.46 Lbs
- After 100 Cycles
  - Mating
    - Min -----28.80 Lbs
    - Max-----33.28 Lbs
  - Unmating
    - Min -----20.86 Lbs
    - Max-----26.59 Lbs
- Humidity
  - Mating
    - Min -----16.33 Lbs
    - Max-----19.55 Lbs
  - Unmating
    - Min -----8.92 Lbs
    - Max-----13.02 Lbs

## RESULTS Continued

### Mating-Unmating Basic Group (SS-116-S-2/BBL-116-G-E)

- Initial
  - Mating
    - Min ----- 9.04 Lbs
    - Max----- 11.83 Lbs
  - Unmating
    - Min ----- 5.13 Lbs
    - Max----- 8.39 Lbs
- After 25 Cycles
  - Mating
    - Min ----- 11.75 Lbs
    - Max----- 16.40 Lbs
  - Unmating
    - Min ----- 8.52 Lbs
    - Max----- 14.00 Lbs

### Mating-Unmating Basic Group (SS-104-S-2/BBL-104-G-E)

- Initial
  - Mating
    - Min ----- 2.32 Lbs
    - Max----- 3.59 Lbs
  - Unmating
    - Min ----- 1.46 Lbs
    - Max----- 2.62 Lbs
- After 25 Cycles
  - Mating
    - Min ----- 2.58 Lbs
    - Max----- 4.64 Lbs
  - Unmating
    - Min ----- 1.71 Lbs
    - Max----- 4.15 Lbs

## RESULTS Continued

### Insulation Resistance minimums, IR

#### Pin to Pin

- Initial

- Mated ----- 450000 Meg  $\Omega$  ----- Passed
  - Unmated ----- 450000 Meg  $\Omega$  ----- Passed

- Thermal Shock

- Mated ----- 450000 Meg  $\Omega$  ----- Passed
  - Unmated ----- 450000 Meg  $\Omega$  ----- Passed

- Humidity

- Mated ----- 450000 Meg  $\Omega$  ----- Passed
  - Unmated ----- 450000 Meg  $\Omega$  ----- Passed

### Dielectric Withstanding Voltage minimums, DWV

- Minimums

- Breakdown Voltage ----- 1828 VAC
  - Test Voltage ----- 1375 VAC
  - Working Voltage ----- 455 VAC

#### Pin to Pin

- Initial DWV ----- Passed
- Thermal DWV ----- Passed
- Humidity DWV ----- Passed

## RESULTS Continued

### LLCR Thermal Aging Group (128 LLCR test points)

- Initial ----- 4.66 mOhms Max
- Thermal
  - <= +5.0 mOhms ----- 128 Points ----- Stable
  - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
  - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
  - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
  - >+2000 mOhms ----- 0 Points ----- Open Failure

### LLCR Gas Tight Group (128 LLCR test points)

- Initial ----- 3.92 mOhms Max
- Gas-Tight
  - <= +5.0 mOhms ----- 128 Points ----- Stable
  - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
  - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
  - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
  - >+2000 mOhms ----- 0 Points ----- Open Failure

### LLCR Mating/Unmating Durability Group (128 LLCR test points)

- Initial ----- 4.19 mOhms Max
- Durability, 100 Cycles
  - <= +5.0 mOhms ----- 128 Points ----- Stable
  - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
  - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
  - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
  - >+2000 mOhms ----- 0 Points ----- Open Failure
- Thermal Shock
  - <= +5.0 mOhms ----- 128 Points ----- Stable
  - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
  - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
  - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
  - >+2000 mOhms ----- 0 Points ----- Open Failure
- Humidity
  - <= +5.0 mOhms ----- 128 Points ----- Stable
  - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
  - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
  - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
  - >+2000 mOhms ----- 0 Points ----- Open Failure

## RESULTS Continued

### LLCR Shock & Vibration (128 LLCR test points)

- Initial ----- 4.90 mOhms Max
- Shock & Vibration
  - <= +5.0 mOhms ----- 128 Points ----- Stable
  - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
  - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
  - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
  - >+2000 mOhms ----- 0 Points ----- Open Failure


### Mechanical Shock & Random Vibration:


- Shock
  - No Damage----- Pass
  - 50 Nanoseconds ----- Pass
- Vibration
  - No Damage----- Pass
  - 50 Nanoseconds ----- Pass

## DATA SUMMARIES

### TEMPERATURE RISE (Current Carrying Capacity, CCC):



- 1) High quality thermocouples whose temperature slopes track one another were used for temperature monitoring.
- 2) The thermocouples were placed at a location to sense the maximum temperature generated during testing.
- 3) Temperature readings recorded are those for which three successive readings, 15 minutes apart, differ less than 1° C (computer controlled data acquisition).
- 4) Adjacent contacts were powered:
  - a. Linear configuration with 1 adjacent conductors/contacts powered



**DATA SUMMARIES Continued**



## DATA SUMMARIES Continued

b. Linear configuration with 2 adjacent conductors/contacts powered





## DATA SUMMARIES Continued

c. Linear configuration with 3 adjacent conductors/contacts powered





## DATA SUMMARIES Continued

d. Linear configuration with 4 adjacent conductors/contacts powered



## DATA SUMMARIES Continued

e. Linear configuration with all adjacent conductors/contacts powered



## DATA SUMMARIES Continued

### MATING-UNMATING FORCE:

#### Thermal Aging Group

	Initial				After Thermals			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	85.00	19.11	46.62	10.48	68.28	15.35	44.88	10.09
Maximum	102.57	23.06	55.33	12.44	75.13	16.89	49.95	11.23
Average	93.70	<b>21.07</b>	50.48	<b>11.35</b>	71.29	<b>16.03</b>	47.42	<b>10.66</b>
St Dev	6.12	1.38	3.19	0.72	2.46	0.55	1.86	0.42
Count	8	8	8	8	8	8	8	8

#### Mating-Unmating Durability Group (HSEC1-040-01-L-DV-WT/0.056" EDGE CARD)

	Initial				After 25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	80.20	18.03	44.12	9.92	93.10	20.93	61.96	13.93
Maximum	102.70	23.09	70.81	15.92	125.70	28.26	90.47	20.34
Average	88.80	<b>19.96</b>	56.63	<b>12.73</b>	113.72	<b>25.57</b>	82.08	<b>18.45</b>
St Dev	6.97	1.57	8.98	2.02	9.40	2.11	9.32	2.10
Count	8	8	8	8	8	8	8	8
	After 50 Cycles				After 75 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	103.59	23.29	73.79	16.59	116.18	26.12	83.36	18.74
Maximum	133.13	29.93	103.82	23.34	142.87	32.12	113.25	25.46
Average	125.70	<b>28.26</b>	94.82	<b>21.32</b>	132.49	<b>29.79</b>	102.88	<b>23.13</b>
St Dev	9.56	2.15	9.12	2.05	8.74	1.97	9.09	2.04
Count	8	8	8	8	8	8	8	8
	After 100 Cycles				After Humidity			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	128.10	28.80	92.79	20.86	72.64	16.33	39.68	8.92
Maximum	148.03	33.28	118.27	26.59	86.96	19.55	57.91	13.02
Average	137.19	<b>30.84</b>	108.13	<b>24.31</b>	82.16	<b>18.47</b>	48.23	<b>10.84</b>
St Dev	6.44	1.45	7.79	1.75	4.54	1.02	5.34	1.20
Count	8	8	8	8	8	8	8	8

## DATA SUMMARIES Continued

### Mating-Unmating Basic Group (SS-116-S-2/BBL-132-G-E)

	Initial				After 25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	40.21	9.04	22.82	5.13	52.26	11.75	37.90	8.52
Maximum	52.62	11.83	37.32	8.39	72.95	16.40	62.27	14.00
<b>Average</b>	46.09	<b>10.36</b>	28.97	<b>6.51</b>	60.27	<b>13.55</b>	47.25	<b>10.62</b>
St Dev	4.36	0.98	5.36	1.20	7.06	1.59	7.16	1.61
Count	8	8	8	8	8	8	8	8

### Mating-Unmating Basic Group (SS-104-S-2/BBL-104-G-E)

	Initial				After 25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	10.32	2.32	6.49	1.46	11.48	2.58	7.61	1.71
Maximum	15.97	3.59	11.65	2.62	20.64	4.64	18.46	4.15
<b>Average</b>	12.51	<b>2.81</b>	8.38	<b>1.88</b>	14.37	<b>3.23</b>	11.01	<b>2.48</b>
St Dev	1.90	0.43	1.74	0.39	3.18	0.72	3.48	0.78
Count	8	8	8	8	8	8	8	8

**DATA SUMMARIES Continued****INSULATION RESISTANCE (IR):**

	Pin to Pin		
	Mated	Unmated	Unmated
Minimum	<b>SS/BBL</b>	<b>SS</b>	<b>BBL</b>
<b>Initial</b>	45000	45000	45000
<b>Thermal</b>	45000	45000	45000
<b>Humidity</b>	45000	45000	45000

**DIELECTRIC WITHSTANDING VOLTAGE (DWV):**

Voltage Rating Summary	
Minimum	<b>SS/BBL</b>
<b>Break Down Voltage</b>	1828
<b>Test Voltage</b>	1375
<b>Working Voltage</b>	455

Pin to Pin	
<b>Initial Test Voltage</b>	Passed
<b>After Thermal Test Voltage</b>	Passed
<b>After Humidity Test Voltage</b>	Passed

## DATA SUMMARIES Continued

### LLCR Thermal Aging Group

- 1) A total of 128 points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
  - a.  $\leq +5.0$  mOhms: -----Stable
  - b.  $+5.1$  to  $+10.0$  mOhms: -----Minor
  - c.  $+10.1$  to  $+15.0$  mOhms: -----Acceptable
  - d.  $+15.1$  to  $+50.0$  mOhms: -----Marginal
  - e.  $+50.1$  to  $+2000$  mOhms: -----Unstable
  - f.  $>+2000$  mOhms: -----Open Failure

LLCR Measurement Summaries by Pin Type						
mOhm values	Date	3/27/2018	4/9/2018			
	Room Temp (Deg C)	26	24			
	Rel Humidity (%)	52	48			
	Technician	Kason He	Kason He			
	Actual	Delta	Delta	Delta	Delta	
	Initial	Thermal				
	Pin Type 1: Signal					
Average	3.04	0.17				
St. Dev.	0.45	0.33				
Min	1.32	0.00				
Max	4.66	2.38				
Summary Count	128	128				
Total Count	128	128				

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
	$\leq 5$	$>5 \text{ & } \leq 10$	$>10 \text{ & } \leq 15$	$>15 \text{ & } \leq 50$	$>50 \text{ & } \leq 1000$	$>1000$
Thermal	128	0	0	0	0	0

## DATA SUMMARIES Continued

### LLCR Mating/Unmating Durability Group

- 1). A total of 128 points were measured.
- 2). EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3). A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4). The following guidelines are used to categorize the changes in LLCR as a result from stressing.
  - a.  $\leq +5.0$  mOhms: -----Stable
  - b.  $+5.1$  to  $+10.0$  mOhms: -----Minor
  - c.  $+10.1$  to  $+15.0$  mOhms: -----Acceptable
  - d.  $+15.1$  to  $+50.0$  mOhms: -----Marginal
  - e.  $+50.1$  to  $+2000$  mOhms: -----Unstable
  - f.  $> +2000$  mOhms: -----Open Failure

		LLCR Measurement Summaries by Pin Type			
		3/28/2018	4/2/2018	4/8/2018	4/20/2018
Date	Room Temp (Deg C)	26	22	25	23
	Rel Humidity (%)	61	53	57	53
Technician	Kason He	Kason He	Kason He	Kason He	Kason He
	Actual Initial	Delta 100 Cycles	Delta Therm Shck	Delta Humidity	
Pin Type 1: Signal					
Average	2.98	0.35	0.30	0.32	
St. Dev.	0.58	0.50	0.41	0.45	
Min	1.23	0.00	0.00	0.01	
Max	4.19	3.24	2.09	1.97	
Summary Count	128	128	128	128	
Total Count	128	128	128	128	

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
	$\leq 5$	$> 5 \text{ & } \leq 10$	$> 10 \text{ & } \leq 15$	$> 15 \text{ & } \leq 50$	$> 50 \text{ & } \leq 1000$	$> 1000$
100 Cycles	128	0	0	0	0	0
Therm Shck	128	0	0	0	0	0
Humidity	128	0	0	0	0	0

## DATA SUMMARIES Continued

### LLCR Gas Tight Group

- 1) A total of 128 points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
  - a.  $\leq +5.0$  mOhms:-----Stable
  - b.  $+5.1$  to  $+10.0$  mOhms:-----Minor
  - c.  $+10.1$  to  $+15.0$  mOhms:-----Acceptable
  - d.  $+15.1$  to  $+50.0$  mOhms:-----Marginal
  - e.  $+50.1$  to  $+2000$  mOhms:-----Unstable
  - f.  $>+2000$  mOhms:-----Open Failure

		LLCR Measurement Summaries by Pin Type			
		4/12/2018	4/13/2018		
Date	Room Temp (Deg C)	22	24		
	Rel Humidity (%)	54	55		
Technician	Kason He	Kason He			
	Actual Initial	Delta Acid Vapor	Delta	Delta	
Pin Type 1: Signal					
Average	3.17	0.11			
St. Dev.	0.33	0.23			
Min	1.54	0.00			
Max	3.92	1.54			
Summary Count	128	128			
Total Count	128	128			

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
	$\leq 5$	$>5 \text{ & } \leq 10$	$>10 \text{ & } \leq 15$	$>15 \text{ & } \leq 50$	$>50 \text{ & } \leq 1000$	$>1000$
Acid Vapor	128	0	0	0	0	0

## DATA SUMMARIES Continued

### LLCR Shock & Vibration:

- 1). A total of 128 points were measured.
- 2). EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3). The following guidelines are used to categorize the changes in LLCR as a result from stressing.
  - a.  $\leq +5.0$  mOhms: ----- Stable
  - b.  $+5.1$  to  $+10.0$  mOhms: ----- Minor
  - c.  $+10.1$  to  $+15.0$  mOhms: ----- Acceptable
  - d.  $+15.1$  to  $+50.0$  mOhms: ----- Marginal
  - e.  $+50.1$  to  $+2000$  mOhms ----- Unstable
  - f.  $>+2000$  mOhms: ----- Open Failure

LLCR Measurement Summaries by Pin Type					
mOhm values	Date	4/24/2018	4/25/2018		
	Room Temp (Deg C)	23	23		
	Rel Humidity (%)	38	40		
	Technician	Tony Wagoner	Tony Wagoner		
	Actual	Delta	Delta	Delta	
	Initial	Shock-Vib			
	Pin Type 1: Signal				
Average	2.64	0.14			
St. Dev.	0.87	0.21			
Min	1.12	0.00			
Max	4.90	1.29			
Summary Count	128	128			
Total Count	128	128			

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
	$\leq 5$	$>5 \text{ & } \leq 10$	$>10 \text{ & } \leq 15$	$>15 \text{ & } \leq 50$	$>50 \text{ & } \leq 1000$	$>1000$
Shock-Vib	128	0	0	0	0	0

### Nanosecond Event Detection:

Shock and Vibration Event Detection Summary	
Contacts tested	60
Test Condition	C, 100g's, 6ms, Half-Sine
Shock Events	0
Test Condition	V-B, 7.56 rms g
Vibration Events	0
Total Events	0

Tracking Code: 1382911_Report_Rev_1	Part #: SS-132-S-2/BBL-132-G-E
Part description: SS/BBL	

## EQUIPMENT AND CALIBRATION SCHEDULES

**Equipment #:** HZ-TCT-01

**Description:** Normal force analyzer

**Manufacturer:** Mecmesin Multitester

**Model:** Mecmesin Multitester 2.5-i

**Serial #:** 08-1049-04

**Accuracy:** Last Cal: 4/26/2018, Next Cal: 4/25/2019

**Equipment #:** HZ-OV-01

**Description:** Oven

**Manufacturer:** Huida

**Model:** CS101-1E

**Serial #:** CS101-1E-B

**Accuracy:** Last Cal: 12/13/2017, Next Cal: 12/12/2018

**Equipment #:** HZ-THC-01

**Description:** Humidity transmitter

**Manufacturer:** Thermtron

**Model:** SM-8-8200

**Serial #:** 38846

**Accuracy:** Last Cal: 2/27/2018, Next Cal: 2/26/2019

**Equipment #:** HZ-TSC-01

**Description:** Vertical Thermal Shock Chamber

**Manufacturer:** Cincinnati Sub Zero

**Model:** VTS-3-6-6-SC/AC

**Serial #:** 10-VT14994

**Accuracy:** See Manual

... Last Cal: 06/28/2017, Next Cal: 06/27/2018

**Equipment #:** HZ-HPM-01

**Description:** NA9636H

**Manufacturer:** Ainuo

**Model:** 6031A

**Serial #:** 089601091

**Accuracy:** Last Cal: 3/7/2018, Next Cal: 3/6/2019

**Equipment #:** HZ-MO-05

**Description:** Micro-ohmmeter

**Manufacturer:** Keithley

**Model:** 3706

**Serial #:** 1285188

**Accuracy:** Last Cal: 11/15/2017, Next Cal: 11/14/2018

## EQUIPMENT AND CALIBRATION SCHEDULES Continued

**Equipment #:** HZ-MO-01

**Description:** Micro-ohmmeter

**Manufacturer:** Keithley

**Model:** 2700

**Serial #:** 1199807

**Accuracy:** Last Cal: 04/26/2018, Next Cal: 04/25/2019

**Equipment #:** HZ-PS-01

**Description:** Power Supply

**Manufacturer:** Agilent

**Model:** 6031A

**Serial #:** MY41000982

**Accuracy:** Last Cal: 04/26/2018, Next Cal: 04/25/2019

**Equipment #:** ACLM-01

**Description:** Accelerometer

**Manufacturer:** PCB Piezotronics

**Model:** 352C03

**Serial #:** 115819

**Accuracy:** See Manual

... Last Cal: 07/18/2017, Next Cal: 07/18/2018

**Equipment #:** ED-03

**Description:** Event Detector

**Manufacturer:** Analysis Tech

**Model:** 32EHD

**Serial #:** 1100604

**Accuracy:** See Manual

... Last Cal: 10/31/2017, Next Cal: 10/31/2018

**Equipment #:** MO-04

**Description:** Multimeter /Data Acquisition System

**Manufacturer:** Keithley

**Model:** 2700

**Serial #:** 0798688

**Accuracy:** See Manual

... Last Cal: 09/11/2017, Next Cal: 09/11/2018