



Project Number: Design Qualification Test Report	Tracking Code: 1845443_Report_Rev_1
Requested by: Chad Humphres	Date: 5/24/2019
Part #: ARF6-16-L-D-A-K-TR/ARC6-16-XX.X-LU-XX-X-1	Tech: Aaron McKim
Part description: ARF6/ARC6	Qty to test: 100
Test Start: 02/1/2019	Test Completed: 03/04/2019



Design Qualification Test Report

ARF6/ARC6

ARF6-16-L-D-A-K-TR/ARC6-16-XX.X-LU-XX-X-1

Tracking Code: 1845443_Report_Rev_1	Part #: ARF6-16-L-D-A-K-TR/ARC6-16-XX.X-LU-XX-X-1
Part description: ARF6/ARC6	

REVISION HISTORY

DATA	REV.NUM.	DESCRIPTION	ENG
4/8/2019	1	Initial Issue	PC

CERTIFICATION

All instruments and measuring equipment were calibrated to National Institute for Standards and Technology (NIST) traceable standards according to ISO 10012-1 and ANSI/NCSL 2540-1, as applicable.

All contents contained herein are the property of Samtec. No portion of this report, in part or in full shall be reproduced without prior written approval of Samtec.

SCOPE

To perform the following tests: Design Qualification Test, please see test plan.

APPLICABLE DOCUMENTS

Standards: EIA Publication 364

TEST SAMPLES AND PREPARATION

- 1) All materials were manufactured in accordance with the applicable product specification.
- 2) All test samples were identified and encoded to maintain traceability throughout the test sequences.
- 3) After soldering, the parts to be used for LLCR and DWV/IR testing were cleaned according to TLWI-0001.
- 4) Either an automated cleaning procedure or an ultrasonic cleaning procedure may be used.
- 5) The automated procedure is used with aqueous compatible soldering materials.
- 6) Parts not intended for testing LLCR and DWV/IR are visually inspected and cleaned if necessary.
- 7) Any additional preparation will be noted in the individual test sequences.
- 8) Samtec Test PCBs used: PCB-109510-TST-XX, PCB-108511-TST-XX.

FLOWCHARTS

Gas Tight

Group 1

ARF6-16-L-D-A-K-TR
ARC6-16-06.0-LU-XX-X-1
8 Assemblies

Step	Description
1.	LLCR ⁽²⁾
2.	Gas Tight ⁽¹⁾
3.	LLCR ⁽²⁾ Max Delta = 15 mOhm

(1) Gas Tight = EIA-364-36

(2) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max
Test Current = 100 mA Max

Normal Force

Group 1

ARF6-16-L-D-A-K-TR

8 Contacts Minimum
Signal Without Thermals

Step	Description
1.	Contact Gaps
2.	Normal Force ⁽¹⁾ Expected Force at Max Deflection = 50 g Deflection = 0.009"

Group 2

ARF6-16-L-D-A-K-TR
ARC6-16-06.0-LU-XX-X-1
8 Contacts Minimum
Signal With Thermals

Step	Description
1.	Contact Gaps
2.	Thermal Age ⁽²⁾
3.	Contact Gaps
4.	Normal Force ⁽¹⁾ Deflection = 0.009" Expected Force at Max Deflection = 50 g

(1) Normal Force = EIA-364-04

(2) Thermal Age = EIA-364-17

Test Condition = 4 (105°C)
Time Condition = B (250 Hours)

FLOWCHARTS Continued**Thermal Aging**Group 1

ARF6-16-L-D-A-K-TR

ARC6-16-06.0-LU-XX-X-1

8 Assemblies

Step	Description
1.	Contact Gaps
2.	Mating/Unmating Force ⁽²⁾
3.	LLCR ⁽¹⁾
4.	Thermal Age ⁽³⁾
5.	LLCR ⁽¹⁾ Max Delta = 15 mOhm
6.	Mating/Unmating Force ⁽²⁾
7.	Contact Gaps

(1) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(2) Mating/Unmating Force = EIA-364-13

(3) Thermal Age = EIA-364-17

Test Condition = 4 (105°C)

Time Condition = B (250 Hours)

FLOWCHARTS Continued**Mating/Unmating/Durability**Group 1

ARF6-16-L-D-A-K-TR
ARC6-16-06.0-LU-XX-X-1
8 Assemblies

Step	Description
1.	Contact Gaps
2.	LLCR ⁽²⁾
3.	Mating/Unmating Force ⁽³⁾
4.	Cycles Quantity = 25 Cycles
5.	Mating/Unmating Force ⁽³⁾
6.	Contact Gaps
7.	LLCR ⁽²⁾ Max Delta = 15 mOhm
8.	Thermal Shock ⁽⁴⁾ - Non Standard
9.	LLCR ⁽²⁾ Max Delta = 15 mOhm
10.	Humidity ⁽¹⁾
11.	LLCR ⁽²⁾ Max Delta = 15 mOhm
12.	Mating/Unmating Force ⁽³⁾

Group 2

ARF6-08-L-D-A-K-TR
ARC6-08-06.0-LU-XX-X-1
8 Assemblies

Step	Description
1.	Contact Gaps
2.	Mating/Unmating Force ⁽³⁾
3.	Cycles Quantity = 25 Cycles
4.	Mating/Unmating Force ⁽³⁾

(1) Humidity = EIA-364-31

Test Condition = B (240 Hours)

Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)

Test Exceptions: ambient pre-condition and delete steps 7a and 7b

(2) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(3) Mating/Unmating Force = EIA-364-13

(4) Thermal Shock = Other

Exposure Time at Temperature Extremes = 1/2 Hour

Method A, Test Condition = I (-40°C to +85°C)

Test Duration = A-3 (100 Cycles)

FLOWCHARTS Continued**IR/DWV****Pin-to-Pin**

<u>Group 1</u> ARF6-16-L-D-A-K-TR ARC6-16-06.0-LU-XX-X-1 2 Assemblies		<u>Group 2</u> ARF6-16-L-D-A-K-TR 2 Assemblies		<u>Group 3</u> ARC6-16-06.0-LU-XX-X-1 2 Assemblies		<u>Group 4</u> ARF6-16-L-D-A-K-TR ARC6-16-06.0-LU-XX-X-1 2 Assemblies	
Step	Description	Step	Description	Step	Description	Step	Description
1.	DWV Breakdown (2)	1.	DWV Breakdown (2)	1.	DWV Breakdown (2)	1.	IR (4)
						2.	DWV at Test Voltage (1)
						3.	Thermal Shock (5) - Non Standard
						4.	IR (4)
						5.	DWV at Test Voltage (1)
						6.	Humidity (3)
						7.	IR (4)
						8.	DWV at Test Voltage (1)

Row-to-Row

<u>Group 5</u> ARF6-16-L-D-A-K-TR ARC6-16-06.0-LU-XX-X-1 2 Assemblies		<u>Group 6</u> ARF6-16-L-D-A-K-TR 2 Assemblies		<u>Group 7</u> ARC6-16-06.0-LU-XX-X-1 2 Assemblies		<u>Group 8</u> ARF6-16-L-D-A-K-TR ARC6-16-06.0-LU-XX-X-1 2 Assemblies	
Step	Description	Step	Description	Step	Description	Step	Description
1.	DWV Breakdown (2)	1.	DWV Breakdown (2)	1.	DWV Breakdown (2)	1.	IR (4)
						2.	DWV at Test Voltage (1)
						3.	Thermal Shock (5) - Non Standard
						4.	IR (4)
						5.	DWV at Test Voltage (1)
						6.	Humidity (3)
						7.	IR (4)
						8.	DWV at Test Voltage (1)

FLOWCHARTS Continued

Pin-to-GroundGroup 9

ARF6-16-L-D-A-K-TR
ARC6-16-06.0-LU-XX-X-1
2 Assemblies

Step	Description
1.	DWV Breakdown ⁽²⁾

Group 10

ARF6-16-L-D-A-K-TR
2 Assemblies

Step	Description
1.	DWV Breakdown ⁽²⁾

Group 11

ARC6-16-06.0-LU-XX-X-1
2 Assemblies

Step	Description
1.	DWV Breakdown ⁽²⁾

Group 12

ARF6-16-L-D-A-K-TR
ARC6-16-06.0-LU-XX-X-1
2 Assemblies

Step	Description
1.	IR ⁽⁴⁾
2.	DWV at Test Voltage ⁽¹⁾
3.	Thermal Shock ⁽⁵⁾ - Non Standard
4.	IR ⁽⁴⁾
5.	DWV at Test Voltage ⁽¹⁾
6.	Humidity ⁽³⁾
7.	IR ⁽⁴⁾
8.	DWV at Test Voltage ⁽¹⁾

(1) DWV at Test Voltage = EIA-364-20

Test Condition = 1 (Sea Level)

DWV test voltage is equal to 75% of the lowest breakdown voltage

Test voltage applied for 60 seconds

(2) DWV Breakdown = EIA-364-20

Test Condition = 1 (Sea Level)

DWV test voltage is equal to 75% of the lowest breakdown voltage

Test voltage applied for 60 seconds

(3) Humidity = EIA-364-31

Test Condition = B (240 Hours)

Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)

Test Exceptions: ambient pre-condition and delete steps 7a and 7b

(4) IR = EIA-364-21

Test Condition = 500 Vdc, 2 Minutes Max

(5) Thermal Shock = Other

Exposure Time at Temperature Extremes = 1/2 Hour

Method A, Test Condition = I (-40°C to +85°C)

Test Duration = A-3 (100 Cycles)

FLOWCHARTS Continued**Current Carrying Capacity**

Group 1
ARF6-16-L-D-A-K-TR
ARC6-16-12.0-LU-LU-3-1
2 Pins Powered
Signal

Step	Description
1.	CCC (2) Rows = 2 Number of Positions = 1

Group 2
ARF6-16-L-D-A-K-TR
ARC6-16-12.0-LU-LU-3-1
4 Pins Powered
Signal

Step	Description
1.	CCC (2) Rows = 2 Number of Positions = 2

Group 3
ARF6-16-L-D-A-K-TR
ARC6-16-12.0-LU-LU-3-1
6 Pins Powered
Signal

Step	Description
1.	CCC (2) Rows = 2 Number of Positions = 3

Group 4
ARF6-16-L-D-A-K-TR
ARC6-16-12.0-LU-LU-3-1
8 Pins Powered
Signal

Step	Description
1.	CCC (2) Rows = 2 Number of Positions = 4

Group 5
ARF6-16-L-D-A-K-TR
ARC6-16-12.0-LU-LU-3-1
32 Pins Powered
Signal

Step	Description
1.	CCC (2) Rows = 2 Number of Positions = 16

Group 6
ARF6-16-L-D-A-K-TR
ARC6-16-12.0-LU-LU-3-1
2 Pins Powered
Ground

Step	Description
1.	CCC (2) Rows = 2 Number of Positions = 1

Group 7
ARF6-16-L-D-A-K-TR
ARC6-16-12.0-LU-LU-3-1
All Power

Step	Description
1.	CCC - All Power (1)

(1) CCC - All Power = EIA-364-70

Method 2, Temperature Rise Versus Current Curve

(TIN PLATING) - Tabulate calculated current at RT, 65°C, 75°C and 95°C after derating 20% and based on 105°C

(GOLD PLATING) - Tabulate calculated current at RT, 85°C, 95°C and 115°C after derating 20% and based on 125°C

(2) CCC = EIA-364-70

Method 2, Temperature Rise Versus Current Curve

(TIN PLATING) - Tabulate calculated current at RT, 65°C, 75°C and 95°C after derating 20% and based on 105°C

(GOLD PLATING) - Tabulate calculated current at RT, 85°C, 95°C and 115°C after derating 20% and based on 125°C

FLOWCHARTS Continued**Mechanical Shock/Random Vibration/LLCR**Group 1

ARF6-16-L-D-A-K-TR

ARC6-16-12.0-LU-XX-X-1

8 Assemblies

Step Description

1. LLCR⁽¹⁾
2. Mechanical Shock⁽²⁾
3. Random Vibration⁽³⁾
4. LLCR⁽¹⁾
Max Delta = 15 mOhm

 (1) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(2) Mechanical Shock = EIA-364-27

Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)

Number of Shocks = 3 Per Direction, Per Axis, 18 Total

(3) Random Vibration = EIA-364-28

Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

Mechanical Shock/Random Vibration/Event DetectionGroup 1

ARF6-16-L-D-A-K-TR

ARC6-16-12.0-LU-XX-X-1

60 Points

Step Description

1. Nanosecond Event Detection
(Mechanical Shock)⁽¹⁾
2. Nanosecond Event Detection
(Random Vibration)⁽²⁾

 (1) Nanosecond Event Detection (Mechanical Shock)

Use EIA-364-87 for Nanosecond Event Detection:

Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-27 for Mechanical Shock:

Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)

Number of Shocks = 3 Per Direction, Per Axis, 18 Total

(2) Nanosecond Event Detection (Random Vibration)

Use EIA-364-87 for Nanosecond Event Detection:

Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-28 for Random Vibration:

Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

FLOWCHARTS Continued**Cable Pull**Group 1

ARF6-16-L-D-A-K-TR
 ARC6-16-12.0-LU-LU-3-1
 5 Assemblies
 0 Degrees

Step	Description
1.	Cable Pull ⁽¹⁾

Group 2

ARF6-16-L-D-A-K-TR
 ARC6-16-12.0-LU-LU-3-1
 5 Assemblies
 90 Degrees

Step	Description
1.	Cable Pull ⁽¹⁾

(1) Cable Pull = EIA-364-38

Measure and Record Force Required to Failure

Failure = Discontinuity >1 microsecond at 10 ohms

Cable FlexGroup 1

ARF6-16-L-D-A-K-TR
 ARC6-16-12.0-LU-LU-3-1
 8 Assemblies
 Flat Cable

Step	Description
1.	IR ⁽³⁾
2.	DWV at Test Voltage ⁽²⁾
3.	Cable Flex ⁽¹⁾
4.	Visual Inspection
5.	IR ⁽³⁾
6.	DWV at Test Voltage ⁽²⁾

(1) Cable Flex = EIA-364-41

Circular Jacket Cable - to be tested 90° each direction (180° total)

Flat Cable - to be tested 70° each direction (140° total)

Monitor continuity during flex testing

Failure = Discontinuity >1 microsecond at 10 ohms

(2) DWV at Test Voltage = EIA-364-20

Test Condition = 1 (Sea Level)

DWV test voltage is equal to 75% of the lowest breakdown voltage

Test voltage applied for 60 seconds

(3) IR = EIA-364-21

Test Condition = 500 Vdc, 2 Minutes Max

FLOWCHARTS Continued**Latch Cycling/Pull**Group 1

ARF6-08-L-D-A-K-TR

ARC6-08-06.0-LU-XX-X-1

5 Assemblies

Custom Group

Step	Description
1.	Cycles Quantity = 100 Cycles
2.	Mating Force <i>Note: Record force it takes to mate the cable, with the latch attached, into the connector.</i>
3.	Cable Pull (1) - Non Standard

(1) Cable Pull = Other

Pull cable to a max of 20lbs and record if latch fails to hold onto the cable assembly.

ATTRIBUTE DEFINITIONS

The following is a brief, simplified description of attributes.

THERMAL SHOCK:

- 1) EIA-364-32, *Thermal Shock (Temperature Cycling) Test Procedure for Electrical Connectors*.
- 2) Test Condition: -40°C to +85°C
- 3) Test Time: ½ hour dwell at each temperature extreme
- 4) Number of Cycles: 100
- 5) All test samples are pre-conditioned at ambient.
- 6) All test samples are exposed to environmental stressing in the mated condition.

THERMAL:

- 1) EIA-364-17, *Temperature Life with or without Electrical Load Test Procedure for Electrical Connectors*.
- 2) Test Condition :105° C.
- 3) Test Time Condition B for 250 hours.
- 4) All test samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

HUMIDITY:

- 1) Reference document: EIA-364-31, *Humidity Test Procedure for Electrical Connectors*.
- 2) Test Condition B, 240 Hours.
- 3) Method III, +25° C to + 65° C, 90% to 98% Relative Humidity excluding sub-cycles 7a and 7b.
- 4) All samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

MECHANICAL SHOCK (Specified Pulse):

- 1) Reference document: EIA-364-27, *Mechanical Shock Test Procedure for Electrical Connectors*
- 2) Test Condition C
- 3) Peak Value: 100 G
- 4) Duration: 6 Milliseconds
- 5) Wave Form: Half Sine
- 6) Velocity: 12.3 ft/s
- 7) Number of Shocks: 3 Shocks / Direction, 3 Axis (18 Total)

VIBRATION:

- 1) Reference document: EIA-364-28, *Vibration Test Procedure for Electrical Connectors*
- 2) Test Condition V, Letter B
- 3) Power Spectral Density: 0.04 G² / Hz
- 4) G 'RMS': 7.56
- 5) Frequency: 50 to 2000 Hz
- 6) Duration: 2.0 Hours per axis (3 axis total)

NANOSECOND-EVENT DETECTION:

- 1) Reference document: EIA-364-87, *Nanosecond-Event Detection for Electrical Connectors*
- 2) Prior to test, the samples were characterized to assure the low nanosecond event being monitored will trigger the detector.
- 3) After characterization it was determined the test samples could be monitored for 50 nanosecond events

MATING/UNMATING:

- 1) Reference document: EIA-364-13, *Mating and Unmating Forces Test Procedure for Electrical Connectors*.
- 2) The full insertion position was to within 0.003" to 0.004" of the plug bottoming out in the receptacle to prevent damage to the system under test.
- 3) One of the mating parts is secured to a floating X-Y table to prevent damage during cycling.

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes.

NORMAL FORCE (FOR CONTACTS TESTED IN THE HOUSING):

- 1) Reference document: EIA-364-04, *Normal Force Test Procedure for Electrical Connectors*.
- 2) The contacts shall be tested in the connector housing.
- 3) If necessary, a "window" shall be made in the connector body to allow a probe to engage and deflect the contact at the same attitude and distance (plus 0.05 mm [0.002"]) as would occur in actual use.
- 4) The connector housing shall be placed in a holding fixture that does not interfere with or otherwise influence the contact force or deflection.
- 5) Said holding fixture shall be mounted on a floating, adjustable, X-Y table on the base of the Dillon TC², computer controlled test stand with a deflection measurement system accuracy of 5.0 µm (0.0002").
- 6) The nominal deflection rate shall be 5 mm (0.2")/minute.
- 7) Unless otherwise noted a minimum of five contacts shall be tested.
- 8) The force/deflection characteristic to load and unload each contact shall be repeated five times.
- 9) The system shall utilize the TC² software in order to acquire and record the test data.
- 10) The permanent set of each contact shall be measured within the TC² software.
- 11) The acquired data shall be graphed with the deflection data on the X-axis and the force data on the Y-axis and a print out will be stored with the Tracking Code paperwork.

INSULATION RESISTANCE (IR):

To determine the resistance of insulation materials to leakage of current through or on the surface of these materials when a DC potential is applied.

- 1) PROCEDURE:
 - a. Reference document: EIA-364-21, *Insulation Resistance Test Procedure for Electrical Connectors*.
 - b. Test Conditions:
 - i. Between Adjacent Contacts or Signal-to-Ground
 - ii. Electrification Time 2.0 minutes
 - iii. Test Voltage (500 VDC) corresponds to calibration settings for measuring resistances.
- 2) MEASUREMENTS:
- 3) When the specified test voltage is applied (VDC), the insulation resistance shall not be less than 1000 megohms.

DIELECTRIC WITHSTANDING VOLTAGE (DWV):

To determine if the sockets can operate at its rated voltage and withstand momentary over potentials due to switching, surges, and other similar phenomenon. Separate samples are used to evaluate the effect of environmental stresses so not to influence the readings from arcing that occurs during the measurement process.

- 1) PROCEDURE:
 - a. Reference document: EIA-364-20, *Withstanding Voltage Test Procedure for Electrical Connectors*.
 - b. Test Conditions:
 - i. Between Adjacent Contacts or Signal-to-Ground
 - ii. Rate of Application 500 V/Sec
 - iii. Test Voltage (VAC) until breakdown occurs
- 2) MEASUREMENTS/CALCULATIONS
 - a. The breakdown voltage shall be measured and recorded.
 - b. The dielectric withstanding voltage shall be recorded as 75% of the minimum breakdown voltage.
 - c. The working voltage shall be recorded as one-third (1/3) of the dielectric withstanding voltage (one-fourth of the breakdown voltage).

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes.

TEMPERATURE RISE (Current Carrying Capacity, CCC):

- 1) EIA-364-70, *Temperature Rise versus Current Test Procedure for Electrical Connectors and Sockets*.
- 2) When current passes through a contact, the temperature of the contact increases as a result of I^2R (resistive) heating.
- 3) The number of contacts being investigated plays a significant part in power dissipation and therefore temperature rise.
- 4) The size of the temperature probe can affect the measured temperature.
- 5) Copper traces on PC boards will contribute to temperature rise:
 - a. Self heating (resistive)
 - b. Reduction in heat sink capacity affecting the heated contacts
- 6) A de-rating curve, usually 20%, is calculated.
- 7) Calculated de-rated currents at four temperature points are reported:
 - c. Ambient
 - d. 85° C
 - e. 95° C
 - f. 115° C
- 8) Typically, neighboring contacts (in close proximity to maximize heat build up) are energized.
- 9) The thermocouple (or temperature measuring probe) will be positioned at a location to sense the maximum temperature in the vicinity of the heat generation area.
- 10) A computer program, *TR 803.exe*, ensures accurate stability for data acquisition.
- 11) Hook-up wire cross section is larger than the cross section of any connector leads/PC board traces, jumpers, etc.
- 12) Hook-up wire length is longer than the minimum specified in the referencing standard.

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes.

LLCR:

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
 - a. $\leq +5.0$ mOhms:----- Stable
 - b. $+5.1$ to $+10.0$ mOhms:----- Minor
 - c. $+10.1$ to $+15.0$ mOhms:----- Acceptable
 - d. $+15.1$ to $+50.0$ mOhms:----- Marginal
 - e. $+50.1$ to $+1000$ mOhms:----- Unstable
 - f. $>+1000$ mOhms:----- Open Failure

GAS TIGHT:

To provide method for evaluating the ability of the contacting surfaces in preventing penetration of harsh vapors which might lead to oxide formation that may degrade the electrical performance of the contact system.

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
 - a. $\leq +5.0$ mOhms:----- Stable
 - b. $+5.1$ to $+10.0$ mOhms:----- Minor
 - c. $+10.1$ to $+15.0$ mOhms:----- Acceptable
 - d. $+15.1$ to $+50.0$ mOhms:----- Marginal
 - e. $+50.1$ to $+1000$ mOhms:----- Unstable
 - f. $>+1000$ mOhms:----- Open Failure
- 4) Procedure:
 - g. Reference document: EIA-364-36, *Test Procedure for Determination of Gas-Tight Characteristics for Electrical Connectors, Sockets and/or Contact Systems*.
 - h. Test Conditions:
 - i. Class II--- Mated pairs of contacts assembled to their plastic housings.
 - ii. Reagent grade Nitric Acid shall be used of sufficient volume to saturate the test chamber
 - iii. The ratio of the volume of the test chamber to the surface area of the acid shall be 10:1.
 - iv. The chamber shall be saturated with the vapor for at least 15 minutes before samples are added.
 - v. Exposure time, 55 to 65 minutes.
 - vi. The samples shall be no closer to the chamber walls than 1 inches and no closer to the surface of the acid than 3 inches.
 - vii. The samples shall be dried after exposure for a minimum of 1 hour.
 - viii. Drying temperature 50° C
 - ix. The final LLCR shall be conducted within 1 hour after drying.

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes.

CABLE PULL:

- 1) Secure cable near center and pull on connector
 - a. At 90°, right angle to cable
 - b. At 0°, in-line with cable




Fig. 1

0° Connector pull, notice the electrical continuity hook-up wires.

CABLE FLEX:

- 1) Oscillate and monitor electrical continuity for open circuit indication.
 - a. $\pm 70^\circ$ Flex Mode, bend up to 500 cycles. load on cable end.




Fig. 2
(Setup picture)

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes.

Latch Cycling/Pull:

- a) Record force to mate cable/connector assembly with latch.
- b) Pull cable to 20lbs and record if latch fails.



Fig. 3
(Setup picture)

RESULTS

Temperature Rise, CCC at a 20% de-rating

- CCC for a 30°C Temperature Rise-----1.24 A per contact with 2 contacts (2x1) powered
- CCC for a 30°C Temperature Rise-----1.11 A per contact with 4 contacts (2x2) powered
- CCC for a 30°C Temperature Rise-----0.96 A per contact with 6 contacts (2x3) powered
- CCC for a 30°C Temperature Rise-----0.84 A per contact with 8 contacts (2x4) powered
- CCC for a 30°C Temperature Rise-----0.50 A per contact with 32 contacts (2x16) powered
- CCC for a 30°C Temperature Rise-----7.40 A per contact with 2 ground contacts (1x2) powered
- CCC for a 30°C Temperature Rise-----6.70 A per contact with 2 ground contacts (1x2) powered (Signal at 1/2 rated current)

Mating – Unmating Forces

Thermal aging Group

- Initial
 - Mating
 - Min ----- 2.29 lbs
 - Max ----- 3.16 lbs
 - Unmating
 - Min ----- 1.22 lbs
 - Max ----- 1.66 lbs
- After Thermal
 - Mating
 - Min ----- 1.88 lbs
 - Max ----- 2.21 lbs
 - Unmating
 - Min ----- 1.02 lbs
 - Max ----- 1.21 lbs

RESULTS Continued**Mating – Unmating Forces
Mating/Unmating Durability Group**

- **Initial**
 - **Mating**
 - Min ----- 2.48 lbs
 - Max ----- 3.15 lbs
 - **Unmating**
 - Min ----- 1.16 lbs
 - Max ----- 1.72 lbs
- **After 25 Cycles**
 - **Mating**
 - Min ----- 2.51 lbs
 - Max ----- 3.25 lbs
 - **Unmating**
 - Min ----- 1.15 lbs
 - Max ----- 1.75 lbs
- **Humidity**
 - **Mating**
 - Min ----- 2.06 lbs
 - Max ----- 2.49 lbs
 - **Unmating**
 - Min ----- 1.18 lbs
 - Max ----- 1.71 lbs

Mating/Unmating Basic Group

- **Initial**
 - **Mating**
 - Min ----- 1.31 lbs
 - Max ----- 1.48 lbs
 - **Unmating**
 - Min ----- 0.48 lbs
 - Max ----- 0.61 lbs
- **After 25 Cycles**
 - **Mating**
 - Min ----- 1.39 lbs
 - Max ----- 1.75 lbs
 - **Unmating**
 - Min ----- 0.60 lbs
 - Max ----- 0.75 lbs

RESULTS Continued**Normal Force at 0.009 Inch deflection**

- **Initial**
 - Min-----45.20 gf Set ---- 0.0005 inch
 - Max -----49.20 gf Set ---- 0.0008 inch
- **Thermal**
 - Min-----30.30 gf Set ---- 0.0030 inch
 - Max -----34.80 gf Set ---- 0.0037 inch

Cable Pull force

- **0° Pull**
 - Min-----14.14 lbs
 - Max -----16.51 lbs
- **90° Pull**
 - Min-----12.31 lbs
 - Max -----14.29 lbs

Latch Cycling/Pull:

- **Mating Force with Latch**
 - Min----- 1.37 lbs
 - Max ----- 1.83 lbs
- **20lb Cable Pull -----Passed**

Cable Flex:**Insulation Resistance minimums, IR****Pin to Pin**

- **Initial**
 - Mated-----45000 Meg Ω ----- Passed
- **After 500 flex cycles**
 - Mated-----45000 Meg Ω ----- Passed

Row to Row

- **Initial**
 - Mated-----45000 Meg Ω ----- Passed
- **After 500 flex cycles**
 - Mated-----45000 Meg Ω ----- Passed

Pin to Ground

- **Initial**
 - Mated-----45000 Meg Ω ----- Passed
- **After 500 flex cycles**
 - Mated-----45000 Meg Ω ----- Passed

Dielectric Withstanding Voltage minimums, DWV

- Test Voltage -----405 VAC

Pin to Pin

- **Initial DWV -----Passed**
- **After 500 Flex cycles DWV -----Passed**

Row to Row

- **Initial DWV -----Passed**
- **After 500 Flex cycles DWV -----Passed**

Pin to Ground

- **Initial DWV -----Passed**
- **After 500 Flex cycles DWV -----Passed**

RESULTS Continued**LLCR Durability (128 signal and 64 ground LLCR test points)****Signal pin:**

- Initial ----- 174.52 mOhms Max

Ground pin:

- Initial ----- 37.85 mOhms Max
- After 25 cycles
 - <= +5.0 mOhms ----- 192 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure
- After thermal shock
 - <= +5.0 mOhms ----- 189 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 3 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure
- After humidity
 - <= +5.0 mOhms ----- 188 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 4 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure

LLCR Thermal Aging (128 signal and 64 ground LLCR test points)**Signal pin:**

- Initial ----- 173.95 mOhms Max

Ground pin:

- Initial ----- 36.25 mOhms Max
- Thermal Aging
 - <= +5.0 mOhms ----- 192 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure

LLCR Gas Tight (128 signal and 64 ground LLCR test points)**Signal pin:**

- Initial ----- 174.91 mOhms Max

Ground pin:

- Initial ----- 42.03 mOhms Max
- Gas-Tight
 - <= +5.0 mOhms ----- 192 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure

RESULTS Continued**LLCR Shock Vib (128 signal and 64 ground LLCR test points)****Signal pin:**

- Initial -----305.10 mOhms Max

Ground pin:

- Initial ----- 42.28 mOhms Max
- S&V
 - <= +5.0 mOhms ----- 178 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 8 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 6 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +1000 mOhms ----- 0 Points ----- Unstable
 - >+1000 mOhms ----- 0 Points ----- Open Failure

Mechanical Shock & Random Vibration:

- Shock
 - No Damage----- Passed
 - 50 Nanoseconds----- Passed
- Vibration
 - No Damage----- Passed
 - 50 Nanoseconds----- Passed

Insulation Resistance minimums, IR**Pin to Pin**

- Initial
 - Mated-----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- Thermal Shock
 - Mated-----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- Humidity
 - Mated-----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed

Row to Row

- Initial
 - Mated-----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- Thermal Shock
 - Mated-----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- Humidity
 - Mated-----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed

Pin to Ground

- Initial
 - Mated-----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- Thermal Shock
 - Mated-----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- Humidity
 - Mated-----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed

RESULTS Continued

Dielectric Withstanding Voltage minimums, DWV

- **Minimums**
 - Breakdown Voltage-----537 VAC
 - Test Voltage -----405 VAC
 - Working Voltage -----130 VAC

Pin to Pin

- Initial DWV -----Passed
- Thermal DWV-----Passed
- Humidity DWV-----Passed

Row to Row

- Initial DWV -----Passed
- Thermal DWV-----Passed
- Humidity DWV-----Passed


Pin to Ground


- Initial DWV -----Passed
- Thermal DWV-----Passed
- Humidity DWV-----Passed

DATA SUMMARIES**TEMPERATURE RISE (Current Carrying Capacity, CCC):**

- 1) High quality thermocouples whose temperature slopes track one another were used for temperature monitoring.
- 2) The thermocouples were placed at a location to sense the maximum temperature generated during testing.
- 3) Temperature readings recorded are those for which three successive readings, 15 minutes apart, differ less than 1° C (computer controlled data acquisition).
- 4) Adjacent contacts were powered:



- a. Linear configuration with 2 adjacent power conductors/contacts powered



DATA SUMMARIES



DATA SUMMARIES**b. Linear configuration with 4 adjacent power conductors/contacts powered**

1845443
4 (2X2) Signal Contacts Powered in Series (Cable)
Part Numbers: ARF6-16-L-D-A-K-TR/ARC6-16-12.0-LU-LU-3-1



DATA SUMMARIES

c. Linear configuration with 6 adjacent power conductors/contacts powered




DATA SUMMARIES

d. Linear configuration with 8 adjacent power conductors/contacts powered

1845443

8 (2X4) Signal Contacts Powered in Series (Cable)


Part Numbers: ARF6-16-L-D-A-K-TR/ARC6-16-12.0-LU-LU-3-1

Current Rating per Contact (30 Deg. Rise, 20% Derated) = 0.84 Amps

1845443



8 (2X4) Signal Contacts Powered in Series (Cable)

Part Numbers: ARF6-16-L-D-A-K-TR/ARC6-16-12.0-LU-LU-3-1



DATA SUMMARIES


e. Linear configuration with 32 adjacent power conductors/contacts powered




DATA SUMMARIES

f. Linear configuration with 2 adjacent Ground power conductors/contacts powered

1845443



2 (All Power) Ground Contacts Powered in Series (Cable)
Part Numbers: ARF6-16-L-D-A-K-TR/ARC6-16-12.0-LU-LU-3-1*Current Rating per Contact (30 Deg. Rise, 20% Derated) = 7.4 Amps*

1845443

2 (All Power) Ground Contacts Powered in Series (Cable)
Part Numbers: ARF6-16-L-D-A-K-TR/ARC6-16-12.0-LU-LU-3-1

DATA SUMMARIES

- g. Linear configuration with 2 adjacent Ground power conductors/contacts powered (Signal at 1/2 rated current)



DATA SUMMARIES

MATING/UNMATING:
Thermal Aging Group

	Initial				After Thermals			
	Mating		Unmating		Mating		Unmating	
	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)
Minimum	10.19	2.29	5.43	1.22	8.81	1.98	4.54	1.02
Maximum	14.04	3.16	7.38	1.66	9.83	2.21	5.38	1.21
Average	12.88	2.90	6.48	1.46	9.27	2.09	4.93	1.11
St Dev	1.24	0.28	0.68	0.15	0.39	0.09	0.29	0.07
Count	8	8	8	8	8	8	8	8

Mating/Unmating Durability Group

	Initial				25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)
Minimum	11.04	2.48	5.16	1.16	11.16	2.51	5.11	1.15
Maximum	14.02	3.15	7.65	1.72	14.44	3.25	7.89	1.77
Average	12.78	2.87	6.33	1.42	13.30	2.99	6.79	1.53
St Dev	1.14	0.26	0.90	0.20	1.10	0.25	0.87	0.20
Count	8	8	8	8	8	8	8	8

	After Humidity			
	Mating		Unmating	
	Newtons	Force (Lbs)	Newtons	Force (Lbs)
Minimum	9.18	2.06	5.25	1.18
Maximum	11.08	2.49	7.58	1.71
Average	9.97	2.24	5.88	1.32
St Dev	0.70	0.16	0.75	0.17
Count	8	8	8	8

Mating/Unmating Basic Group


	Initial				25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)
Minimum	5.82	1.31	2.14	0.48	6.19	1.39	2.66	0.60
Maximum	6.58	1.48	2.72	0.61	7.77	1.75	3.33	0.75
Average	6.17	1.39	2.44	0.55	6.80	1.53	2.92	0.66
St Dev	0.28	0.06	0.22	0.05	0.45	0.10	0.21	0.05
Count	8	8	8	8	8	8	8	8

DATA SUMMARIES Continued**NORMAL FORCE (FOR CONTACTS TESTED IN THE HOUSING):**

- 1) Calibrated force gauges are used along with computer controlled positioning equipment.
- 2) For Normal force 8-10 measurements are taken and the averages reported.

Initial	Deflections in inches Forces in Grams										
	<u>0.0010</u>	<u>0.0020</u>	<u>0.0030</u>	<u>0.0040</u>	<u>0.0050</u>	<u>0.0060</u>	<u>0.0070</u>	<u>0.0080</u>	<u>0.0090</u>	<u>0.0100</u>	<i>SET</i>
Averages	4.82	9.84	14.95	20.05	25.13	30.10	34.80	39.28	43.37	46.94	0.0007
Min	4.20	8.90	13.90	19.10	24.00	28.70	33.20	37.50	41.60	45.20	0.0005
Max	5.20	10.50	15.80	21.10	26.90	31.90	37.20	41.60	45.70	49.20	0.0008
St. Dev	0.341	0.464	0.611	0.665	0.936	1.039	1.226	1.276	1.285	1.293	0.0001
Count	12	12	12	12	12	12	12	12	12	12	12

After Thermals	Deflections in inches Forces in Grams										
	<u>0.0010</u>	<u>0.0020</u>	<u>0.0030</u>	<u>0.0040</u>	<u>0.0050</u>	<u>0.0060</u>	<u>0.0070</u>	<u>0.0080</u>	<u>0.0090</u>	<u>0.0100</u>	<i>SET</i>
Averages	0.01	0.01	0.04	2.63	6.86	11.48	16.38	21.33	26.45	31.91	0.0033
Min	0.00	0.00	-0.10	1.60	5.90	10.50	15.30	19.90	25.00	30.30	0.0030
Max	0.10	0.10	0.30	4.60	8.90	13.50	19.30	24.60	29.30	34.80	0.0037
St. Dev	0.029	0.029	0.124	0.855	0.833	0.872	1.145	1.328	1.240	1.320	0.0002
Count	12	12	12	12	12	12	12	12	12	12	12

Normal Force - Average Initial vs Average Thermal

DATA SUMMARIES Continued**Cable Pull:****0° Pull**

	Force (lbs)
Minimum	14.14
Maximum	16.51
Average	15.62

90° Pull

	Force (lbs)
Minimum	12.31
Maximum	14.29
Average	13.55

Latch Cycling

	Force (lbs)
Minimum	1.37
Maximum	1.83
Average	1.56

Cable Flex:**Insulation Resistance minimums, IR**

Pin to Pin	
Mated	
Minimum	
Initial	45000
After 500 Flex Cycles	45000

Pin to Ground	
Mated	
Minimum	
Initial	45000
After 500 Flex Cycles	45000

Row to Row	
Mated	
Minimum	
Initial	45000
After 500 Flex Cycles	45000

DATA SUMMARIES Continued

Dielectric Withstanding Voltage minimums, DWV

Voltage Rating Summary	
Minimum	
Break Down Voltage	537
Test Voltage	405
Working Voltage	130

Pin to Pin	
Initial Test Voltage	Passed
After 500 Flex Cycles Test Voltage	Passed

Row to Row	
Initial Test Voltage	Passed
After 500 Flex Cycles Test Voltage	Passed

Pin to Ground	
Initial Test Voltage	Passed
After 500 Flex Cycles Test Voltage	Passed

DATA SUMMARIES Continued**INSULATION RESISTANCE (IR):**

	Pin to Pin		
	Mated	Unmated	Unmated
Minimum	ARF6/ARC6	ARF6	ARC6
Initial	45000	45000	45000
Thermal	45000	45000	45000
Humidity	45000	45000	45000

	Pin to Ground		
	Mated	Unmated	Unmated
Minimum	ARF6/ARC6	ARF6	ARC6
Initial	45000	45000	45000
Thermal	45000	45000	45000
Humidity	45000	45000	45000

	Row to Row		
	Mated	Unmated	Unmated
Minimum	ARF6/ARC6	ARF6	ARC6
Initial	45000	45000	45000
Thermal	45000	45000	45000
Humidity	45000	45000	45000

DATA SUMMARIES Continued**DIELECTRIC WITHSTANDING VOLTAGE (DWV):**

Voltage Rating Summary	
Minimum	ARF6/ARC6
Break Down Voltage	537
Test Voltage	405
Working Voltage	130

Pin to Pin	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed
After Humidity Test Voltage	Passed

Row to Row	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed
After Humidity Test Voltage	Passed

Pin to Ground	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed
After Humidity Test Voltage	Passed

DATA SUMMARIES Continued**LLCR Durability:**

- 1) A total of 192 points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms:----- Stable
 - b. $+5.1$ to $+10.0$ mOhms:----- Minor
 - c. $+10.1$ to $+15.0$ mOhms:----- Acceptable
 - d. $+15.1$ to $+50.0$ mOhms:----- Marginal
 - e. $+50.1$ to $+1000$ mOhms ----- Unstable
 - f. $>+1000$ mOhms:----- Open Failure

LLCR Measurement Summaries by Pin Type				
Date	2/1/2019	2/11/2019	2/16/2019	3/4/2019
Room Temp (Deg C)	23	23	22	23
Rel Humidity (%)	33	35	33	25
Technician	Aaron McKim	Aaron McKim	Aaron McKim	Aaron McKim
mOhm values	Actual Initial	Delta 25 Cycles	Delta Therm Shck	Delta Humidity
Pin Type 1: Signal				
Average	164.75	0.53	1.02	1.19
St. Dev.	6.07	0.59	1.10	1.47
Min	149.86	0.00	0.00	0.00
Max	174.52	3.48	7.17	7.68
Summary Count	128	128	128	128
Total Count	128	128	128	128
Pin Type 2: Ground				
Average	35.52	0.61	1.06	0.84
St. Dev.	1.14	0.47	0.66	0.77
Min	31.30	0.00	0.02	0.03
Max	37.85	2.36	3.86	4.59
Summary Count	64	64	64	64
Total Count	64	64	64	64

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	≤ 5	$>5 \text{ \& } \leq 10$	$>10 \text{ \& } \leq 15$	$>15 \text{ \& } \leq 50$	$>50 \text{ \& } \leq 1000$	>1000
25 Cycles	192	0	0	0	0	0
Therm Shck	189	3	0	0	0	0
Humidity	188	4	0	0	0	0

DATA SUMMARIES Continued**LLCR Thermal aging**

- 1) A total of 192 points were measured
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms:----- Stable
 - b. $+5.1$ to $+10.0$ mOhms:----- Minor
 - c. $+10.1$ to $+15.0$ mOhms:----- Acceptable
 - d. $+15.1$ to $+50.0$ mOhms:----- Marginal
 - e. $+50.1$ to $+1000$ mOhms ----- Unstable
 - f. $>+1000$ mOhms:----- Open Failure

LLCR Measurement Summaries by Pin Type				
Date	2/8/2019	2/19/2019		
Room Temp (Deg C)	23	23		
Rel Humidity (%)	26	25		
Technician	Aaron McKim	Aaron McKim		
mOhm values	Actual Initial	Delta Thermal	Delta	Delta
Pin Type 1: Signal				
Average	166.15	0.93		
St. Dev.	5.57	0.94		
Min	156.32	0.01		
Max	173.95	6.19		
Summary Count	128	128		
Total Count	128	128		
Pin Type 2: Ground				
Average	34.96	1.27		
St. Dev.	0.70	0.69		
Min	33.28	0.20		
Max	36.25	3.34		
Summary Count	64	64		
Total Count	64	64		

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	≤ 5	>5 & ≤ 10	>10 & ≤ 15	>15 & ≤ 50	>50 & ≤ 1000	>1000
Thermal	190	2	0	0	0	0

DATA SUMMARIES Continued**LLCR GAS TIGHT:**

- 1) A total of 192 points were measured
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms:----- Stable
 - b. $+5.1$ to $+10.0$ mOhms:----- Minor
 - c. $+10.1$ to $+15.0$ mOhms:----- Acceptable
 - d. $+15.1$ to $+50.0$ mOhms:----- Marginal
 - e. $+50.1$ to $+1000$ mOhms:----- Unstable
 - f. $>+1000$ mOhms:----- Open Failure

LLCR Measurement Summaries by Pin Type				
Date	2/15/2019	2/18/2019		
Room Temp (Deg C)	23	23		
Rel Humidity (%)	31	28		
Technician	Aaron McKim	Aaron McKim		
mOhm values	Actual Initial	Delta Acid Vapor	Delta	Delta
Pin Type 1: Signal				
Average	165.35	0.55		
St. Dev.	5.58	0.66		
Min	153.32	0.01		
Max	174.91	4.71		
Summary Count	128	128		
Total Count	128	128		
Pin Type 2: Ground				
Average	35.00	0.72		
St. Dev.	1.12	0.46		
Min	32.85	0.00		
Max	42.03	2.26		
Summary Count	64	64		
Total Count	64	64		

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	≤ 5	>5 & ≤ 10	>10 & ≤ 15	>15 & ≤ 50	>50 & ≤ 1000	>1000
Acid Vapor	192	0	0	0	0	0

DATA SUMMARIES Continued**LLCR Shock Vib:**

- 1) A total of 192 points were measured
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms:----- Stable
 - b. $+5.1$ to $+10.0$ mOhms:----- Minor
 - c. $+10.1$ to $+15.0$ mOhms:----- Acceptable
 - d. $+15.1$ to $+50.0$ mOhms:----- Marginal
 - e. $+50.1$ to $+1000$ mOhms:----- Unstable
 - f. $>+1000$ mOhms:----- Open Failure

LLCR Measurement Summaries by Pin Type				
Date	2/20/2019	2/27/2019		
Room Temp (Deg C)	23	23		
Rel Humidity (%)	33	28		
Technician	Aaron McKim	Aaron McKim		
mOhm values	Actual Initial	Delta Shock-Vib	Delta	Delta
Pin Type 1: Signal				
Average	291.59	1.88		
St. Dev.	9.18	2.70		
Min	265.36	0.07		
Max	305.10	13.56		
Summary Count	128	128		
Total Count	128	128		
Pin Type 2: Ground				
Average	40.22	0.86		
St. Dev.	0.88	0.64		
Min	38.32	0.03		
Max	42.28	3.11		
Summary Count	64	64		
Total Count	64	64		

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	≤ 5	$>5 \text{ \& } \leq 10$	$>10 \text{ \& } \leq 15$	$>15 \text{ \& } \leq 50$	$>50 \text{ \& } \leq 1000$	>1000
Shock-Vib	178	8	6	0	0	0

Shock Vibration Event Detection:

Shock and Vibration Event Detection Summary	
Contacts tested	60
Test Condition	C, 100g's, 6ms, Half-Sine
Shock Events	0
Test Condition	V-B, 7.56 rms g
Vibration Events	0
Total Events	0

EQUIPMENT AND CALIBRATION SCHEDULES**Equipment #:** HPM-01**Description:** Hipot Megommeter**Manufacturer:** Hipotronics**Model:** H306B-A**Serial #:** M9905004**Accuracy:** 2 % Full Scale Accuracy

... Last Cal: 05/24/2018, Next Cal: 08/24/2019

Equipment #: TCT-06**Description:** Test Resources test stand**Manufacturer:** Test Resources**Model:** 100R250-12**Serial #:** 0710016-01**Accuracy:** Speed Accuracy: +/- 5% of indicated speed; Displacement: +/- 5 micrometers.

... Last Cal: 05/03/2018, Next Cal: 05/03/2019

Equipment #: MO-04**Description:** Multimeter /Data Acquisition System**Manufacturer:** Keithley**Model:** 2700**Serial #:** 0798688**Accuracy:** See Manual

... Last Cal: 04/30/2018, Next Cal: 04/30/2019

Equipment #: OV-05**Description:** Forced Air Oven, 5 Cu. Ft., 120 V (Chamber Room)**Manufacturer:** Sheldon Mfg.**Model:** CE5F**Serial #:** 02008008**Accuracy:** +/- 5 deg. C

... Last Cal: 02/18/2019, Next Cal: 02/18/2020

Equipment #: THC-01**Description:** Temperature/Humidity Chamber (Chamber Room)**Manufacturer:** Thermotron**Model:** SM-8-7800**Serial #:** 30676**Accuracy:** See Manual

... Last Cal: 10/24/2018, Next Cal: 10/24/2019

Equipment #: TSC-01**Description:** Vertical Thermal Shock Chamber**Manufacturer:** Cincinnati Sub Zero**Model:** VTS-3-6-6-SC/AC**Serial #:** 10-VT14993**Accuracy:** See Manual

... Last Cal: 06/30/2018, Next Cal: 06/30/2019

EQUIPMENT AND CALIBRATION SCHEDULES**Equipment #:** MO-02**Description:** Multimeter /Data Acquisition System**Manufacturer:** Keithley**Model:** 2700**Serial #:** 0780546**Accuracy:** Last Cal: 6/16/2018, Next Cal: 6/16/2019**Equipment #:** PS-01**Description:** Power Supply**Manufacturer:** Hewlett Packard**Model:** 6033A**Serial #:** 3329A-07330**Accuracy:** Last Cal: 6/12/2018, Next Cal: 6/12/2019**Equipment #:** PS-02**Description:** Power Supply**Manufacturer:** Hewlett Packard**Model:** 6033A**Serial #:** 2847A-04167**Accuracy:** Last Cal: 6/12/2018, Next Cal: 6/12/2019**Equipment #:** SVC-01**Description:** Shock & Vibration Table**Manufacturer:** Data Physics**Model:** LE-DSA-10-20K**Serial #:** 10037**Accuracy:** See Manual

... Last Cal: 11/30/2018, Next Cal: 11/30/2019

Equipment #: ACLM-01**Description:** Accelerometer**Manufacturer:** PCB Piezotronics**Model:** 352C03**Serial #:** 115819**Accuracy:** See Manual

... Last Cal: 7/9/2018, Next Cal: 7/9/2019

Equipment #: ED-03**Description:** Event Detector**Manufacturer:** Analysis Tech**Model:** 32EHD**Serial #:** 1100604**Accuracy:** See Manual

... Last Cal: 6/4/2018, Next Cal: 6/4/2019