





High Speed Characterization Report

ARP6-DP-025-04-XX.X-T-L-L



Mated with:

APF6-025-03.5-L-04-2-L-TR



Description:

**AcceleRate® HP High-Density, High-Performance Cable System,
34 AWG 92-Ohm Twinax, 4-Row**

Series: ARP6-DP**Description:** AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm
Twinax, 4-Row

Table of Contents

Cable Assembly Overview	1
Frequency Domain Data Summary	2
Bandwidth Figures – Differential Insertion Loss.....	2
Time Domain Data Summary	3
Characterization Details	5
Differential and Single-Ended Data.....	5
Cable assembly Signal to Ground Ratio	5
Frequency Domain Data	7
Time Domain Data	8
Appendix A – Frequency Domain Responses.....	9
Differential Application – Insertion Loss.....	9
Differential Application – Return Loss.....	10
Differential Application – NEXT Configurations	12
Differential Application – FEXT Configurations	15
Differential Application – Differential to Common Mode Conversion	18
Appendix B – Time Domain Responses.....	20
Differential Application – Input Pulse	20
Differential Application – Cable assembly Impedance	21
Differential Application – Propagation Delay.....	26
Appendix C – Product and Test System Descriptions	30
Product Description	30
Test System Description	30
PCB-ARP6-112097-SIG-0 Test Fixtures	31
PCB Fixtures	31
Appendix D – Test and Measurement Setup.....	32
N5225B Measurement Setup	32
Test Instruments.....	32
Test Cables & Adapters.....	32
DCA-X86100D Measurement Setup.....	33
Test Instruments.....	33
Test Cables & Adapters.....	33
Appendix E - Frequency and Time Domain Measurements	34
Frequency (S-Parameter) Domain Procedures	34
Time Domain Procedures	34
Propagation Delay (TDT)	34
Impedance (TDR).....	35
Appendix F – Glossary of Terms	36

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row

Cable Assembly Overview

The 0.635 mm (.025") ARP6 Cable Assembly is constructed using 34 AWG Eye Speed® ultra-low skew twinax cable (ARP6-DP), 34 AWG Eye Speed® ThinSE™ micro coax cable (ARP6-SE), or a combination of both cable types (ARP6-DS). The cable is terminated at both ends with connector that mates with the APF6-L or APF6-T socket.

The ARP6-DP series cable assemblies are available in 8 and 12 differential pairs per row, 4 or 6 rows. The data in this report is applicable to the 4-row, 8-pair ARP6-DP with 150 mm, 500 mm, and 1000 mm cable lengths.

Each ARP6 cable assembly was tested by mating it to APF6 socket at both ends. One sample of each assembly was tested. The actual part numbers that were tested are shown in Table 1, which also identifies End 1 and End 2 of each assembly. A relative sample picture is shown in Figure1.

Length	Part Number	End 1	End 2
150 mm	ARP6-DP-025-04-06.0-T-L-L	L(Squeeze Latch)	L(Squeeze Latch)
500 mm	ARP6-DP-025-04-20.0-T-L-L	L(Squeeze Latch)	L(Squeeze Latch)
1000 mm	ARP6-DP-025-04-40.0-T-L-L	L(Squeeze Latch)	L(Squeeze Latch)

Table 1: Sample Description



Figure 1: Test Sample

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row

Frequency Domain Data Summary

Bandwidth Figures – Differential Insertion Loss




Figure 2




Figure 3

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row




Figure 4

Time Domain Data Summary




Figure 5

Series: ARP6-DP**Description:** AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm
Twinax, 4-Row

Because the same type of cable is used in the cable assemblies with different lengths, only the impedance profile of 0.15 m cable assembly is reported.

Table 2 - Propagation Delay (Cable Assembly)				
Driver	Receiver	0.15 m	0.5 m	1 m
End 1_A8,A9	End 2_A18,A17	0.832 ns	2.514 ns	4.920 ns
End 1_A11,A12	End 2_A15,A14	0.836 ns	2.520 ns	4.927 ns
End 1_B8,B9	End 2_B18,B17	0.834 ns	2.515 ns	4.929 ns
End 1_B11,B12	End 2_B15,B14	0.839 ns	2.521 ns	4.938 ns
End 1_C8,C9	End 2_C18,C17	0.833 ns	2.516 ns	4.922 ns
End 1_C11,C12	End 2_C15,C14	0.838 ns	2.519 ns	4.927 ns
End 1_D8,D9	End 2_D18,D17	0.832 ns	2.514 ns	4.921 ns
End 1_D11,D12	End 2_D15,D14	0.837 ns	2.520 ns	4.930 ns

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm
Twinax, 4-Row

Characterization Details

This report presents data that characterizes the signal integrity response of a cable assembly in a controlled printed circuit board (PCB) environment. All efforts are made to reveal typical best-case responses inherent to the system under test (SUT).

In this report, the SUT includes the mating connectors, cable assembly, and footprint effects on a typical multi-layer PCB. PCB effects (trace loss) are de-embedded from test data. Board related effects, such as pad-to-ground capacitance, are included in the data presented in this report.

Additionally, intermediate test signal connections can mask the cable assembly's true performance. Such connection effects are minimized by using high performance test cables and adapters. Where appropriate, calibration and de-embedding routines are also used to reduce residual effects.

Differential and Single-Ended Data

Most Samtec cable assemblies can be used successfully in both differential and single-ended applications. However, electrical performance will differ depending on the signal drive type. In this report, data is presented for "GSSG" differential drive configuration only.

Cable assembly Signal to Ground Ratio

Samtec cable assemblies are most often designed for generic applications and can be implemented using various signal and ground pin assignments. In high-speed systems, provisions must be made in the interconnect for signal return currents. Such paths are often referred to as "ground". In some cable assemblies, a ground plane or blade, or an outer shield, is used as the signal return, while in others, cable assembly pins are used as signal returns. Various combinations of signal pins, ground blades, and shields can also be utilized. Electrical performance can vary significantly depending upon the number and location of ground pins.

In general, the more pins dedicated to ground, the better electrical performance will be. But dedicating pins to ground reduces signal density of a cable assembly. Therefore, care must be taken when choosing signal/ground ratios in cost or density-sensitive applications.

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm
Twinax, 4-Row

For this cable assembly, the following configurations are evaluated:

NEXT

ARP6-DP-025-04-XX.XT-XX SIGNAL MAPPING																																				
POSITIONS																																				
	A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12	A13	A14	A15	A16	A17	A18	A19	A20	A21	A22	A23	A24	A25	A26	A27	A28	A29	A30	A31	A32				
J1	GN21	DP	GN21	DP	GN21	DP	GN21	DP	GN21	DP	GN21	DP	GN21	DP	GN21	DP	GN21	DP	GN21	DP	GN21	DP	GN21	DP	GN21	DP	GN21	DP	GN21	DP	GN21	DP				
J2	A25	A24	A23	A22	A21	A20	A19	A18	A17	A16	A15	A14	A13	A12	A11	A10	A9	A8	A7	A6	A5	A4	A3	A2	A1	DP	A1	DP	A1	DP	A1	DP	A1	DP		
B1	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12	B13	B14	B15	B16	B17	B18	B19	B20	B21	B22	B23	B24	B25	B26	B27	B28	B29	B30	B31	B32	B33	B34		
	GN22	DP	GN22	DP	GN22	DP	GN22	DP	GN22	DP	GN22	DP	GN22	DP	GN22	DP	GN22	DP	GN22	DP	GN22	DP	GN22	DP	GN22	DP	GN22	DP	GN22	DP	GN22	DP	GN22	DP		
B25	B24	B23	B22	B21	B20	B19	B18	B17	B16	B15	B14	B13	B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1	DP	B1	DP	B1	DP	B1	DP	B1	DP	B1	DP	
J1	C1	C2	C3	C4	C5	C6	C7	C8	C9	C10	C11	C12	C13	C14	C15	C16	C17	C18	C19	C20	C21	C22	C23	C24	C25	C26	C27	C28	C29	C30	C31	C32	C33	C34		
	GN3	DP	GN3	DP	GN3	DP	GN3	DP	GN3	DP	GN3	DP	GN3	DP	GN3	DP	GN3	DP	GN3	DP	GN3	DP	GN3	DP	GN3	DP	GN3	DP	GN3	DP	GN3	DP	GN3	DP	GN3	DP
J2	C25	C24	C23	C22	C21	C20	C19	C18	C17	C16	C15	C14	C13	C12	C11	C10	C9	C8	C7	C6	C5	C4	C3	C2	C1	DP	C1	DP	C1	DP	C1	DP	C1	DP	C1	DP
D1	D1	D2	D3	D4	D5	D6	D7	D8	D9	D10	D11	D12	D13	D14	D15	D16	D17	D18	D19	D20	D21	D22	D23	D24	D25	D26	D27	D28	D29	D30	D31	D32	D33	D34	D35	
	GN4	DP	GN4	DP	GN4	DP	GN4	DP	GN4	DP	GN4	DP	GN4	DP	GN4	DP	GN4	DP	GN4	DP	GN4	DP	GN4	DP	GN4	DP	GN4	DP	GN4	DP	GN4	DP	GN4	DP	GN4	DP
J25	D25	D24	D23	D22	D21	D20	D19	D18	D17	D16	D15	D14	D13	D12	D11	D10	D9	D8	D7	D6	D5	D4	D3	D2	D1	DP	D1	DP	D1	DP	D1	DP	D1	DP	D1	DP

ALL GROUNDS ARE COMMON WITHIN A ROW AND TIED TO CABLE SHIELD

ON THE MATING BOARD ASSEMBLY, SAME-PC RECOMMENDS IMPLEMENTING A GND REFERENCE TYPING ALL GNDS TOGETHER

ARP6-DP-025-04-XX.XT.XX SIGNAL MAPPING																											
POSITIONS																											
J1	A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12	A13	A14	A15	A16	A17	A18	A19	A20	A21	A22	A23	A24	A25		
GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP		
J2	A25	A24	A23	A22	A21	A20	A19	A18	A17	A16	A15	A14	A13	A12	A11	A10	A9	A8	A7	A6	A5	A4	A3	A2	A1		
J1	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12	B13	B14	B15	B16	B17	B18	B19	B20	B21	B22	B23	B24	B25		
GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP		
J2	B25	B24	B23	B22	B21	B20	B19	B18	B17	B16	B15	B14	B13	B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1		
J1	C1	C2	C3	C4	C5	C6	C7	C8	C9	C10	C11	C12	C13	C14	C15	C16	C17	C18	C19	C20	C21	C22	C23	C24	C25		
GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP		
J2	C25	C24	C23	C22	C21	C20	C19	C18	C17	C16	C15	C14	C13	C12	C11	C10	C9	C8	C7	C6	C5	C4	C3	C2	C1		
J1	D1	D2	D3	D4	D5	D6	D7	D8	D9	D10	D11	D12	D13	D14	D15	D16	D17	D18	D19	D20	D21	D22	D23	D24	D25		
GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP		
J2	D25	D24	D23	D22	D21	D20	D19	D18	D17	D16	D15	D14	D13	D12	D11	D10	D9	D8	D7	D6	D5	D4	D3	D2	D1		

ALL GROUNDS ARE COMMON WITHIN A ROW AND TIED TO CABLE SHIELD

ON THE MATING BOARD ASSEMBLY, SAE/TEC RECOMMENDS IMPL FEMTING A GND REFERENCE TYPING ALL GND'S TOGETHER

FEXT

[illegible]

ARPE-DP-025-04-XX.XT-XX SIGNAL MAPPING																											
POSITIONS																											
	A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12	A13	A14	A15	A16	A17	A18	A19	A20	A21	A22	A23	A24	A25		
J1	GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP	GND1	DP	
J2	A25	A24	A23	A22	A21	A20	A19	A18	A17	A16	A15	A14	A13	A12	A11	A10	A9	A8	A7	A6	A5	A4	A3	A2	A1		
B1	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12	B13	B14	B15	B16	B17	B18	B19	B20	B21	B22	B23	B24	B25		
	GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP	GND2	DP	
J2	B25	B24	B23	B22	B21	B20	B19	B18	B17	B16	B15	B14	B13	B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1		
C1	C1	C2	C3	C4	C5	C6	C7	C8	C9	C10	C11	C12	C13	C14	C15	C16	C17	C18	C19	C20	C21	C22	C23	C24	C25		
	GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP	GND3	DP	
J2	C25	C24	C23	C22	C21	C20	C19	C18	C17	C16	C15	C14	C13	C12	C11	C10	C9	C8	C7	C6	C5	C4	C3	C2	C1		
D1	D1	D2	D3	D4	D5	D6	D7	D8	D9	D10	D11	D12	D13	D14	D15	D16	D17	D18	D19	D20	D21	D22	D23	D24	D25		
	GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP	GND4	DP	
J2	D25	D24	D23	D22	D21	D20	D19	D18	D17	D16	D15	D14	D13	D12	D11	D10	D9	D8	D7	D6	D5	D4	D3	D2	D1		
ALL GROUNDS ARE COMMON WITHIN A ROW AND TIED TO CABLE SHIELD																											
ON THE MATING BOARD ASSEMBLY, SAMTEC RECOMMENDS IMPLEMENTING A GND REFERENCE TYING ALL GND'S TOGETHER																											

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row

Differential Impedance (denoted by green circles):

- GSSG (Ground-positive signal-negative signal-Ground)

Differential Crosstalk (denoted by red circles):

- NEXT (Near End Crosstalk)
- FEXT (Far End Crosstalk)

See [Appendix C](#) – Product and Test System Descriptions for details

In a real system environment, active signals might be located at the outer edges of the signal contacts of concern, as opposed to the ground signals utilized in laboratory testing. For example, in a single-ended system, a pin-out of “SSSS”, or four adjacent single ended

signals might be encountered as opposed to the “GSG” and “GSSG” configurations tested in the laboratory. Electrical characteristics in such applications could vary slightly from laboratory results. But in most applications, performance can safely be considered equivalent.

Signal Edge Speed (Rise Time)

In pulse signaling applications, the perceived performance of the interconnect can vary significantly depending on the edge rate or rise time of the exciting signal. For this report, the fastest rise time used was 10 ps. Generally, this should demonstrate worst-case performance.

In many systems, the signal edge rate will be significantly slower at the cable assembly than at the driver launch point. To estimate interconnect performance at other edge rates, data is provided for several rise times between 10 ps and 30 ps.

For this report, measured rise times were at 20%-80% signal levels.

Frequency Domain Data

Frequency Domain parameters are helpful in evaluating the cable assembly system’s signal loss and crosstalk characteristics across a range of sinusoidal frequencies. In this report, parameters presented in the Frequency Domain are Insertion Loss, Return Loss, Near-End and Far-End Crosstalk, and Mode Conversion. Other parameters or formats, such as VSWR or S-Parameters, may be available upon request. Please contact our Signal Integrity Group at sig@samtec.com for more information.

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm
Twinax, 4-Row

Frequency performance characteristics for the SUT are generated directly from network analyzer measurements.

Time Domain Data

Time Domain parameters indicate Impedance mismatch versus length and signal propagation time in a pulsed signal environment.

Impedance mismatch versus length is measured by DCA-X86100D Digital Serial Analyzer. Board related effects, such as pad-to-ground capacitance and trace loss, are included in the data presented in this report. The impedance data is provided in [Appendix B](#) of this report.

The measured S-Parameters from the network analyzer are post-processed using Keysight ADS to obtain the time domain response for signal propagation time. The Time Domain procedure is provided in [Appendix D](#) of this report. Parameters or formats not included in this report may be available upon request. Please contact our Signal Integrity Group at sig@samtec.com for more information.

In this report, propagation delay is defined as the signal propagation time through the cable assembly, mating connectors, and connector footprint. It also includes 4.39mm of PCB trace on each connector side. Delay is measured at 30 picoseconds signal rise-time. Delay is calculated as the difference in time measured between the 50% amplitude levels of the input and output pulses.

Data for other configurations may be available. Please contact our Signal Integrity Group at sig@samtec.com for further information.

Additional information concerning test conditions and procedures is located in the appendices of this report. Further information may be obtained by contacting our Signal Integrity Group at sig@samtec.com.

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm
Twinax, 4-Row

Appendix A – Frequency Domain Responses

Differential Application – Insertion Loss




Figure 6




Figure 7

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row




Figure 8

Differential Application – Return Loss




Figure 9

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row




Figure 10




Figure 11

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row

Differential Application – NEXT Configurations




Figure 12




Figure 13

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row




Figure 14




Figure 15

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row




Figure 16




Figure 17

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row

Differential Application – FEXT Configurations




Figure 18




Figure 19

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row




Figure 20




Figure 21

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row




Figure 22




Figure 23

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row

Differential Application – Differential to Common Mode Conversion

0.15m: Differential to Common Mode Conversion - SCD21




Figure 24

0.5m: Differential to Common Mode Conversion - SCD21





Figure 25

Series: ARP6-DP**Description:** AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row**Figure 26**

Series: ARP6-DP**Description:** AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm
Twinax, 4-Row

Appendix B – Time Domain Responses

Differential Application – Input Pulse




Figure 27

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row

Differential Application – Cable assembly Impedance

ARP6-DP-025-04-06.0-T-L-L




Figure 28

ARP6-DP-025-04-06.0-T-L-L




Figure 29

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row

ARP6-DP-025-04-06.0-T-L-L




Figure 30

ARP6-DP-025-04-06.0-T-L-L




Figure 31

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row

ARP6-DP-025-04-06.0-T-L-L




Figure 32

ARP6-DP-025-04-06.0-T-L-L




Figure 33

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row

ARP6-DP-025-04-06.0-T-L-L




Figure 34

ARP6-DP-025-04-06.0-T-L-L




Figure 35

Series: ARP6-DP**Description:** AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm
Twinax, 4-Row

ARP6-DP-025-04-06.0-T-L-L




Figure 36

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row

Differential Application – Propagation Delay




Figure 37








Figure 38

Series: ARP6-DP**Description:** AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row**Figure 39****Figure 40**

Series: ARP6-DP**Description:** AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm
Twinax, 4-Row**Figure 41****Figure 42**

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row




Figure 43




Figure 44

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row

Appendix C – Product and Test System Descriptions

Product Description

Product test samples are 0.635 mm (.025") ARP6 Cable Assemblies. The part numbers are ARP6-DP-025-04-06.0-T-L-L, ARP6-DP-025-04-20.0-T-L-L and ARP6-DP-025-04-40.0-T-L-L. They mate with APF6-025-03.5-L-04-2-L-TR. A photo of the mated test article mounted to SI test boards is shown below.

The cable assembly terminations had a particular signal line configuration. There are a total of 8 pairs per row, the signal line numbers are shown in Table 3.

ARP6-DP-025-04-XX.X-T-X-X SIGNAL MAPPING																									
POSITIONS																									
J1	A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12	A13	A14	A15	A16	A17	A18	A19	A20	A21	A22	A23	A24	A25
	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND
J2	A25	A24	A23	A22	A21	A20	A19	A18	A17	A16	A15	A14	A13	A12	A11	A10	A9	A8	A7	A6	A5	A4	A3	A2	A1
J1	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12	B13	B14	B15	B16	B17	B18	B19	B20	B21	B22	B23	B24	B25
	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND
J2	B25	B24	B23	B22	B21	B20	B19	B18	B17	B16	B15	B14	B13	B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
J1	C1	C2	C3	C4	C5	C6	C7	C8	C9	C10	C11	C12	C13	C14	C15	C16	C17	C18	C19	C20	C21	C22	C23	C24	C25
	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND
J2	C25	C24	C23	C22	C21	C20	C19	C18	C17	C16	C15	C14	C13	C12	C11	C10	C9	C8	C7	C6	C5	C4	C3	C2	C1
J1	D1	D2	D3	D4	D5	D6	D7	D8	D9	D10	D11	D12	D13	D14	D15	D16	D17	D18	D19	D20	D21	D22	D23	D24	D25
	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND	DP	GND
J2	D25	D24	D23	D22	D21	D20	D19	D18	D17	D16	D15	D14	D13	D12	D11	D10	D9	D8	D7	D6	D5	D4	D3	D2	D1
ALL GROUNDS ARE COMMON WITHIN A ROW AND TIED TO CABLE SHIELD																									
ON THE MATING BOARD ASSEMBLY, SAMTEC RECOMMENDS IMPLEMENTING A GND REFERENCE TYING ALL GND'S TOGETHER																									

Table 3: Signal line numbers

Test System Description

The test fixtures are composed of fourteen-layer Tachyon 100G material with 92.5Ω differential signal trace and pad configurations designed for the electrical characterization of Samtec high speed cable assembly products. A PCB mount 1.85mm connector is used to interface the PNA test cables to the test fixtures. Optimization of the 1.85mm launch was performed using full wave simulation tools to minimize reflections. The test fixtures and calibration kit are specific to the ARx6 series connector set and identified by part number PCB-ARP6-112097-SIG-0.

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm
Twinax, 4-Row

PCB-ARP6-112097-SIG-0 Test Fixtures




Figure 45

PCB Fixtures

The test fixtures used are as follows:




Figure 46

PCB-ARP6-112097-SIG-0– ARP6 Cable Test Board

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm
Twinax, 4-Row

Appendix D – Test and Measurement Setup

For frequency domain measurements, the test instrument is the Agilent N5225B PNA-L network analyzer. Frequency domain data and graphs are extracted from the instrument by AFR application. The network analyzer is configured as follows:

Start Frequency – 10 MHz

Stop Frequency – 40 GHz

IFBW – 500 Hz

N5225B Measurement Setup




Figure 47

Test Instruments

<u>QTY</u>	<u>Description</u>
1	Agilent N5225B PNA-L Network Analyzer (10 MHz to 40 GHz)
1	Agilent N4694-60003 ECAL Module (10 MHz to 67 GHz)

Test Cables & Adapters

<u>QTY</u>	<u>Description</u>
32	1m Junkosha 2.4mm male to female cables

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm
Twinax, 4-Row

For impedance measurements, the test instrument is the Keysight DCA-X86100D Wide-Bandwidth Oscilloscope Mainframe. The impedance data and profiles are obtained directly from the instrument. The Digital Analyzer is configured as follows:

Vertical Scale: 5 ohm / Div

Horizontal Resolution: 500ps

Averages: 128

DCA-X86100D Measurement Setup




Figure 48

Test Instruments

<u>QTY</u>	<u>Description</u>
1	Keysight DCA-X86100D Wide-Bandwidth Oscilloscope Mainframe

Test Cables & Adapters

<u>QTY</u>	<u>Description</u>
4	Junkosha J12J103834-00

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm Twinax, 4-Row

Appendix E - Frequency and Time Domain Measurements

Frequency (S-Parameter) Domain Procedures

The quality of any data taken with a network analyzer is directly related to the quality of the calibration standards and the use of proper test procedures. For this reason, extreme care is taken in the design of the calibration standards, the SI test boards, and the selection of the PCB vendor.

A coaxial SOLT calibration is performed using a N4694-60003 ECAL module. Then DUT measurements are performed under SOLT calibration. The measurements include the effect of test fixture. The measurements of the 2X THRU line standards are required to remove the test fixture effect.

Time Domain Procedures

Mathematically, Frequency Domain data can be transformed to obtain a Time Domain response. Perfect transformation requires Frequency Domain data from DC to infinity Hz. Fortunately, a very accurate Time Domain response can be obtained with bandwidth-limited data, such as measured with modern network analyzer.

The Time Domain responses were generated using Keysight ADS 2022 update 1. This tool has a transient convolution simulator, which can generate a Time Domain response directly from measured S-Parameters. An example of a similar methodology is provided in the Samtec Technical Note on domain transformation.

http://suddendocs.samtec.com/notesandwhitepapers/tech-note_using-plts-for-time-domain-data_web.pdf

Propagation Delay (TDT)

The Propagation Delay is a measure of the Time Domain delay through the cable assembly and footprint. A step pulse is applied to the touchstone model of the cable assembly and the transmitted voltage is monitored. The same pulse is also applied to a reference channel with zero loss, and the Time Domain pulses are plotted on the same figure.

The difference in time, measured at the 50% point of the step voltage is the propagation delay.

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm
Twinax, 4-Row

Impedance (TDR)

Measurements involving digital pulses are performed using either Time Domain Reflectometer (TDR) or Time Domain Transmission (TDT) methods. The TDR method is used for the impedance measurements in this report.

The signal line(s) of the SUT's is energized with a TDR pulse and the far-end of the energized signal line is terminated in the test systems characteristic impedance (e.g., 50Ω or 100Ω terminations). By terminating the adjacent signal lines in the test systems characteristic impedance, the effects on the resultant impedance shape of the waveform are limited.

Series: ARP6-DP

Description: AcceleRate® HP High-Density, High-Performance Cable System, 34 AWG 92-Ohm
Twinax, 4-Row

Appendix F – Glossary of Terms

ADS – Keysight Advanced Design System

AFR – Automatic Fixture Removal

PCB – Printed Circuit Board

SUT – System Under Test

SOLT – acronym used to define Short, Open, Load & Thru Calibration Standards

TDR – Time Domain Reflectometry

TDT – Time Domain Transmission