




Project Number: Design Qualification Test Report	Tracking Code: 2028937_Report_Rev_1
Requested by: Jonathan Ochsner	Date: 4/23/2021
Part #: APF6-060-03.5-L-04-2-A/APM6-060-06.5-L-04-2-A	
Part description: APF6/APM6	Tech: Tony Wagoner
Test Start: 7/3/2019	Test Completed: 8/9/2019



DESIGN QUALIFICATION TEST REPORT
APF6/APM6
APF6-060-03.5-L-04-2-A/APM6-060-06.5-L-04-2-A

Tracking Code: 2028937_Report_Rev_1	Part #: APF6-060-03.5-L-04-2-A/APM6-060-06.5-L-04-2-A
Part description: APF6/APM6	

REVISION HISTORY

DATA	REV.NUM.	DESCRIPTION	ENG
4/21/2020	1	Initial Issue	KH

CERTIFICATION

All instruments and measuring equipment were calibrated to National Institute for Standards and Technology (NIST) traceable standards according to ISO 10012-1 and ANSI/NCSL 2540-1, as applicable.

All contents contained herein are the property of Samtec. No portion of this report, in part or in full shall be reproduced without prior written approval of Samtec.

SCOPE

To perform the following tests: Design Qualification test. Please see test plan.

APPLICABLE DOCUMENTS

Standards: EIA Publication 364

TEST SAMPLES AND PREPARATION

- 1) All materials were manufactured in accordance with the applicable product specification.
- 2) All test samples were identified and encoded to maintain traceability throughout the test sequences.
- 3) After soldering, the parts to be used for LLCR and DWV/IR testing were cleaned according to CO-SC-WI-3029.
- 4) Either an automated cleaning procedure or an ultrasonic cleaning procedure may be used.
- 5) The automated procedure is used with aqueous compatible soldering materials.
- 6) Parts not intended for testing LLCR and DWV/IR are visually inspected and cleaned if necessary.
- 7) Any additional preparation will be noted in the individual test sequences.
- 8) Solder Information: Lead Free
- 9) Samtec Test PCBs used: PCB-109585-TST-XX/PCB-109969-TST-XX/PCB-109582-TST-XX/
PCB-109584-TST-XX

FLOWCHARTS

Gas Tight

Group 1

APF6-060-03.5-L-04-2-A

APM6-060-06.5-L-04-2-A

8 Assemblies

Step	Description
1.	LLCR ⁽²⁾
2.	Gas Tight ⁽¹⁾
3.	LLCR ⁽²⁾ Max Delta = 15 mOhm

(1) Gas Tight = EIA-364-36

(2) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max
Test Current = 100 mA Max

Normal Force

Group 1

APF6-060-03.5-L-04-2-A

APM6-060-06.5-L-04-2-A

8 Contacts Minimum

C-481 Without Thermals

Step	Description
1.	Contact Gaps
2.	Normal Force ⁽¹⁾ Expected Force at Max Deflection = 71 g Deflection = 0.011 "

Group 2

APF6-060-03.5-L-04-2-A

APM6-060-06.5-L-04-2-A

8 Contacts Minimum

C-482 Without Thermals

Step	Description
1.	Contact Gaps
2.	Normal Force ⁽¹⁾ Expected Force at Max Deflection = 69 g Deflection = 0.011 "

Group 3

APF6-060-03.5-L-04-2-A

APM6-060-06.5-L-04-2-A

8 Contacts Minimum

C-481 With Thermals

Step	Description
1.	Contact Gaps
2.	Thermal Age ⁽²⁾
3.	Contact Gaps
4.	Normal Force ⁽¹⁾ Deflection = 0.011 " Expected Force at Max Deflection = 71 g

Group 4

APF6-060-03.5-L-04-2-A

APM6-060-06.5-L-04-2-A

8 Contacts Minimum

C-482 With Thermals

Step	Description
1.	Contact Gaps
2.	Thermal Age ⁽²⁾
3.	Contact Gaps
4.	Normal Force ⁽¹⁾ Deflection = 0.011 " Expected Force at Max Deflection = 69 g

(1) Normal Force = EIA-364-04

(2) Thermal Age = EIA-364-17

Test Condition = 4 (105°C)
Time Condition = B (250 Hours)

FLOWCHARTS Continued**Thermal Aging**Group 1

APF6-060-03.5-L-04-2-A

APM6-060-06.5-L-04-2-A

8 Assemblies

Step Description

1. Contact Gaps
2. Mating/Unmating Force (2)
3. LLCR (1)
4. Thermal Age (3)
5. LLCR (1)
Max Delta = 15 mOhm
6. Mating/Unmating Force (2)
7. Contact Gaps

(1) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(2) Mating/Unmating Force = EIA-364-13**(3) Thermal Age = EIA-364-17**

Test Condition = 4 (105°C)

Time Condition = B (250 Hours)

FLOWCHARTS Continued**Mating/Unmating/Durability**Group 1

APF6-060-03.5-L-04-2-A
APM6-060-06.5-L-04-2-A
8 Assemblies

Group 2

APF6-020-03.5-L-04-2-A
APM6-020-06.5-L-04-2-A
8 Assemblies
Smallest

Group 1

APF6-100-03.5-L-04-2-A
APM6-100-06.5-L-04-2-A
8 Assemblies
Largest

Step Description

1. Contact Gaps
2. LLCR ⁽²⁾
3. Mating/Unmating Force ⁽³⁾
4. Cycles
Quantity = 25 Cycles
5. Mating/Unmating Force ⁽³⁾
6. Contact Gaps
7. LLCR ⁽²⁾
Max Delta = 15 mOhm
8. Thermal Shock ⁽⁴⁾
9. LLCR ⁽²⁾
Max Delta = 15 mOhm
10. Humidity ⁽¹⁾
11. LLCR ⁽²⁾
Max Delta = 15 mOhm
12. Mating/Unmating Force ⁽³⁾

Step Description

1. Contact Gaps
2. Mating/Unmating Force ⁽³⁾
3. Cycles
Quantity = 25 Cycles
4. Mating/Unmating Force ⁽³⁾

Step Description

1. Contact Gaps
2. Mating/Unmating Force ⁽¹⁾
3. Cycles
Quantity = 25 Cycles
4. Mating/Unmating Force ⁽¹⁾

(1) Humidity = EIA-364-31

Test Condition = B (240 Hours)

Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)

Test Exceptions: ambient pre-condition and delete steps 7a and 7b

(2) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(3) Mating/Unmating Force = EIA-364-13

(4) Thermal Shock = EIA-364-32

Exposure Time at Temperature Extremes = 1/2 Hour

Method A, Test Condition = I (-55°C to +85°C)

Test Duration = A-3 (100 Cycles)

FLOWCHARTS Continued**IR/DWV****Pin-to-Pin**Group 1

APF6-060-03.5-L-04-2-A
APM6-060-06.5-L-04-2-A
2 Assemblies

Group 2

APF6-060-03.5-L-04-2-A

2 Assemblies

Group 3

APM6-060-06.5-L-04-2-A
2 Assemblies

Group 4

APF6-060-03.5-L-04-2-A
APM6-060-06.5-L-04-2-A
2 Assemblies

Step	Description
1.	DWV Breakdown (2)

Step	Description
1.	DWV Breakdown (2)

Step	Description
1.	DWV Breakdown (2)

Step	Description
1.	IR (4)
2.	DWV at Test Voltage (1)
3.	Thermal Shock (5)
4.	IR (4)
5.	DWV at Test Voltage (1)
6.	Humidity (3)
7.	IR (4)
8.	DWV at Test Voltage (1)

Row-to-RowGroup 5

APF6-060-03.5-L-04-2-A
APM6-060-06.5-L-04-2-A
2 Assemblies

Group 6

APF6-060-03.5-L-04-2-A

2 Assemblies

Group 7

APM6-060-06.5-L-04-2-A
2 Assemblies

Group 8

APF6-060-03.5-L-04-2-A
APM6-060-06.5-L-04-2-A
2 Assemblies

Step	Description
1.	DWV Breakdown (2)

Step	Description
1.	DWV Breakdown (2)

Step	Description
1.	DWV Breakdown (2)

Step	Description
1.	IR (4)
2.	DWV at Test Voltage (1)
3.	Thermal Shock (5)
4.	IR (4)
5.	DWV at Test Voltage (1)
6.	Humidity (3)
7.	IR (4)
8.	DWV at Test Voltage (1)

(1) DWV at Test Voltage = EIA-364-20

Test Condition = 1 (Sea Level)

DWV test voltage is equal to 75% of the lowest breakdown voltage

Test voltage applied for 60 seconds

(2) DWV Breakdown = EIA-364-20

Test Condition = 1 (Sea Level)

DWV test voltage is equal to 75% of the lowest breakdown voltage

Test voltage applied for 60 seconds

(3) Humidity = EIA-364-31

Test Condition = B (240 Hours)

Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)

Test Exceptions: ambient pre-condition and delete steps 7a and 7b

(4) IR = EIA-364-21

Test Condition = 500 Vdc, 2 Minutes Max

(5) Thermal Shock = EIA-364-32

Exposure Time at Temperature Extremes = 1/2 Hour

Method A, Test Condition = I (-55°C to +85°C)

Test Duration = A-3 (100 Cycles)

FLOWCHARTS Continued**Current Carrying Capacity**Group 1

APF6-060-03.5-L-04-2-A
 APM6-060-03.5-L-04-2-A
 4 Pins Powered
 Signal

Step	Description
1.	CCC ⁽¹⁾ Rows = 4 Number of Positions = 1

Group 2

APF6-060-03.5-L-04-2-A
 APM6-060-06.5-L-04-2-A
 8 Pins Powered
 Signal

Step	Description
1.	CCC ⁽¹⁾ Rows = 4 Number of Positions = 2

Group 3

APF6-060-03.5-L-04-2-A
 APM6-060-06.5-L-04-2-A
 12 Pins Powered
 Signal

Step	Description
1.	CCC ⁽¹⁾ Rows = 4 Number of Positions = 3

Group 5

APF6-060-03.5-L-04-2-A
 APM6-060-06.5-L-04-2-A
 240 Pins Powered
 Signal

Step	Description
1.	CCC ⁽¹⁾ Rows = 4 Number of Positions = 60

Group 1

APF6-100-03.5-L-04-2-A
 APM6-100-06.5-L-04-2-A
 400 Pins Powered
 Signal

Step	Description
1.	CCC ⁽¹⁾ Rows = 4 Number of Positions = 100

(1) CCC = EIA-364-70

Method 2, Temperature Rise Versus Current Curve

(TIN PLATING) - Tabulate calculated current at RT, 65°C, 75°C and 95°C after derating 20% and based on 105°C

(GOLD PLATING) - Tabulate calculated current at RT, 85°C, 95°C and 115°C after derating 20% and based on 125°C

FLOWCHARTS Continued**Mechanical Shock/Random Vibration/LLCR**Group 1

APF6-060-03.5-L-04-2-A

APM6-060-06.5-L-04-2-A

8 Assemblies

Step	Description
1.	LLCR ⁽¹⁾
2.	Mechanical Shock ⁽²⁾
3.	Random Vibration ⁽³⁾
4.	LLCR ⁽¹⁾ Max Delta = 15 mOhm

(1) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(2) Mechanical Shock = EIA-364-27

Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)

Number of Shocks = 3 Per Direction, Per Axis, 18 Total

(3) Random Vibration = EIA-364-28

Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

Mechanical Shock/Random Vibration/Event DetectionGroup 1

APF6-060-03.5-L-04-2-A

APM6-060-06.5-L-04-2-A

60 Points

Step	Description
1.	Nanosecond Event Detection (Mechanical Shock) ⁽¹⁾
2.	Nanosecond Event Detection (Random Vibration) ⁽²⁾

(1) Nanosecond Event Detection (Mechanical Shock)

Use EIA-364-87 for Nanosecond Event Detection:

Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-27 for Mechanical Shock:

Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)

Number of Shocks = 3 Per Direction, Per Axis, 18 Total

(2) Nanosecond Event Detection (Random Vibration)

Use EIA-364-87 for Nanosecond Event Detection:

Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-28 for Random Vibration:

Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

FLOWCHARTS Continued**Mechanical Shock/Random Vibration/LLCR**Group 1

APF6-100-03.5-L-04-2-A

APM6-100-06.5-L-04-2-A

8 Assemblies

Step Description

1. LLCR (1)
2. Mechanical Shock (2)
3. Random Vibration (3)
4. LLCR (1)
Max Delta = 15 mOhm

(1) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(2) Mechanical Shock = EIA-364-27

Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)

Number of Shocks = 3 Per Direction, Per Axis, 18 Total

(3) Random Vibration = EIA-364-28

Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

Mechanical Shock/Random Vibration/Event DetectionGroup 1

APF6-100-03.5-L-04-2-A

APM6-100-06.5-L-04-2-A

60 Points

Step Description

1. Nanosecond Event Detection
(Mechanical Shock) (1)
2. Nanosecond Event Detection
(Random Vibration) (2)

(1) Nanosecond Event Detection (Mechanical Shock)

Use EIA-364-87 for Nanosecond Event Detection:

Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-27 for Mechanical Shock:

Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)

Number of Shocks = 3 Per Direction, Per Axis, 18 Total

(2) Nanosecond Event Detection (Random Vibration)

Use EIA-364-87 for Nanosecond Event Detection:

Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-28 for Random Vibration:

Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

ATTRIBUTE DEFINITIONS

The following is a brief, simplified description of attributes.

THERMAL:

- 1) EIA-364-17, *Temperature Life with or without Electrical Load Test Procedure for Electrical Connectors*.
- 2) Test Condition at 105° C.
- 3) Test Time Condition B for 250 hours.
- 4) All test samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

THERMAL SHOCK:

- 1) EIA-364-32, *Thermal Shock (Temperature Cycling) Test Procedure for Electrical Connectors*.
- 2) Test Condition: -55°C to +85°C
- 3) Test Time: ½ hour dwell at each temperature extreme
- 4) Number of Cycles: 100
- 5) All test samples are pre-conditioned at ambient.
- 6) All test samples are exposed to environmental stressing in the mated condition.

HUMIDITY:

- 1) Reference document: EIA-364-31, *Humidity Test Procedure for Electrical Connectors*.
- 2) Test Condition B, 240 Hours.
- 3) Method III, +25° C to + 65° C, 90% to 98% Relative Humidity excluding sub-cycles 7a and 7b.
- 4) All samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

MECHANICAL SHOCK (Specified Pulse):

- 1) Reference document: EIA-364-27, *Mechanical Shock Test Procedure for Electrical Connectors*
- 2) Test Condition: C
- 3) Peak Value: 100 G
- 4) Duration: 6 Milliseconds
- 5) Wave Form: Half Sine
- 6) Velocity: 12.3 ft/s
- 7) Number of Shocks: 3 Shocks / Direction, 3 Axis (18 Total)

VIBRATION:

- 1) Reference document: EIA-364-28, *Vibration Test Procedure for Electrical Connectors*
- 2) Test Condition V, Letter B
- 3) Power Spectral Density: 0.04 G² / Hz
- 4) G 'RMS': 7.56
- 5) Frequency: 50 to 2000 Hz
- 6) Duration: 2.0 Hours per axis (3 axis total)

NANOSECOND-EVENT DETECTION:

- 1) Reference document: EIA-364-87, *Nanosecond-Event Detection for Electrical Connectors*
- 2) Prior to test, the samples were characterized to assure the low nanosecond event being monitored will trigger the detector.
- 3) After characterization it was determined the test samples could be monitored for 50 nanosecond events

MATING/UNMATING:

- 1) Reference document: EIA-364-13, *Mating and Unmating Forces Test Procedure for Electrical Connectors*.
- 2) The full insertion position was to within 0.003" to 0.004" of the plug bottoming out in the receptacle to prevent damage to the system under test.
- 3) One of the mating parts is secured to a floating X-Y table to prevent damage during cycling.

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes

NORMAL FORCE (FOR CONTACTS TESTED IN THE HOUSING):

- 1) Reference document: EIA-364-04, *Normal Force Test Procedure for Electrical Connectors*.
- 2) The contacts shall be tested in the connector housing.
- 3) If necessary, a "window" shall be made in the connector body to allow a probe to engage and deflect the contact at the same attitude and distance (plus 0.05 mm [0.002"]) as would occur in actual use.
- 4) The connector housing shall be placed in a holding fixture that does not interfere with or otherwise influence the contact force or deflection.
- 5) Said holding fixture shall be mounted on a floating, adjustable, X-Y table on the base of the Dillon TC², computer controlled test stand with a deflection measurement system accuracy of 5.0 μm (0.0002").
- 6) The nominal deflection rate shall be 5 mm (0.2")/minute.
- 7) Unless otherwise noted a minimum of five contacts shall be tested.
- 8) The force/deflection characteristic to load and unload each contact shall be repeated five times.
- 9) The system shall utilize the TC² software in order to acquire and record the test data.
- 10) The permanent set of each contact shall be measured within the TC² software.
- 11) The acquired data shall be graphed with the deflection data on the X-axis and the force data on the Y-axis and a print out will be stored with the Tracking Code paperwork.

TEMPERATURE RISE (Current Carrying Capacity, CCC):

- 1) EIA-364-70, *Temperature Rise versus Current Test Procedure for Electrical Connectors and Sockets*.
- 2) When current passes through a contact, the temperature of the contact increases as a result of I^2R (resistive) heating.
- 3) The number of contacts being investigated plays a significant part in power dissipation and therefore temperature rise.
- 4) The size of the temperature probe can affect the measured temperature.
- 5) Copper traces on PC boards will contribute to temperature rise:
 - a. Self-heating (resistive)
 - b. Reduction in heat sink capacity affecting the heated contacts
- 6) A de-rating curve, usually 20%, is calculated.
- 7) Calculated de-rated currents at four temperature points are reported:
 - a. Ambient
 - b. 85° C
 - c. 95° C
 - d. 115° C
- 8) Typically, neighboring contacts (in close proximity to maximize heat build up) are energized.
- 9) The thermocouple (or temperature measuring probe) will be positioned at a location to sense the maximum temperature in the vicinity of the heat generation area.
- 10) A computer program, *TR 803.exe*, ensures accurate stability for data acquisition.
- 11) Hook-up wire cross section is larger than the cross section of any connector leads/PC board traces, jumpers, etc.
- 12) Hook-up wire length is longer than the minimum specified in the referencing standard.

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes

LLCR:

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
 - a. $\leq +5.0$ mOhms: -----Stable
 - b. $+5.1$ to $+10.0$ mOhms:-----Minor
 - c. $+10.1$ to $+15.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms: -----Unstable
 - f. $>+1000$ mOhms:-----Open Failure

GAS TIGHT:

To provide method for evaluating the ability of the contacting surfaces in preventing penetration of harsh vapors which might lead to oxide formation that may degrade the electrical performance of the contact system.

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
 - a. $\leq +5.0$ mOhms:-----Stable
 - b. $+5.1$ to $+10.0$ mOhms:-----Minor
 - c. $+10.1$ to $+15.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms:-----Unstable
 - f. $>+1000$ mOhms:-----Open Failure
- 4) Procedure:
 - a. Reference document: EIA-364-36, *Test Procedure for Determination of Gas-Tight Characteristics for Electrical Connectors, Sockets and/or Contact Systems*.
 - b. Test Conditions:
 - i. Class II--- Mated pairs of contacts assembled to their plastic housings.
 - ii. Reagent grade Nitric Acid shall be used of sufficient volume to saturate the test chamber
 - iii. The ratio of the volume of the test chamber to the surface area of the acid shall be 10:1.
 - iv. The chamber shall be saturated with the vapor for at least 15 minutes before samples are added.
 - v. Exposure time, 55 to 65 minutes.
 - vi. The samples shall be no closer to the chamber walls than 1 inches and no closer to the surface of the acid than 3 inches.
 - vii. The samples shall be dried after exposure for a minimum of 1 hour.
 - viii. Drying temperature 50° C
 - ix. The final LLCR shall be conducted within 1 hour after drying.

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes

INSULATION RESISTANCE (IR):

To determine the resistance of insulation materials to leakage of current through or on the surface of these materials when a DC potential is applied.

- 1) PROCEDURE:
 - a. Reference document: EIA-364-21, *Insulation Resistance Test Procedure for Electrical Connectors*.
 - b. Test Conditions:
 - i. Between Adjacent Contacts or Signal-to-Ground
 - ii. Electrification Time 2.0 minutes
 - iii. Test Voltage (500 VDC) corresponds to calibration settings for measuring resistances.
- 2) MEASUREMENTS:
- 3) When the specified test voltage is applied (VDC), the insulation resistance shall not be less than 5000 megohms.

DIELECTRIC WITHSTANDING VOLTAGE (DWV):

To determine if the sockets can operate at its rated voltage and withstand momentary over potentials due to switching, surges, and other similar phenomenon. Separate samples are used to evaluate the effect of environmental stresses so not to influence the readings from arcing that occurs during the measurement process.

- 1) PROCEDURE:
 - a. Reference document: EIA-364-20, *Withstanding Voltage Test Procedure for Electrical Connectors*.
 - b. Test Conditions:
 - i. Between Adjacent Contacts or Signal-to-Ground
 - ii. Barometric Test Condition 1
 - iii. Rate of Application 500 V/Sec
 - iv. Test Voltage (VAC) until breakdown occurs
- 2) MEASUREMENTS/CALCULATIONS
 - a. The breakdown voltage shall be measured and recorded.
 - b. The dielectric withstanding voltage shall be recorded as 75% of the minimum breakdown voltage.
 - c. The working voltage shall be recorded as one-third (1/3) of the dielectric withstanding voltage (one-fourth of the breakdown voltage).

RESULTS

Temperature Rise, CCC at a 20% de-rating

- CCC for a 30°C Temperature Rise-----1.2 A per contact with 4 contacts (4x1) powered.
- CCC for a 30°C Temperature Rise-----0.9 A per contact with 8 contacts (4x2) powered.
- CCC for a 30°C Temperature Rise-----0.8 A per contact with 12 contacts (4x3) powered.
- CCC for a 30°C Temperature Rise-----0.7 A per contact with 16 contacts (4x4) powered.
- CCC for a 30°C Temperature Rise-----0.3 A per contact with 240 contacts (4x60) powered.
- CCC for a 30°C Temperature Rise-----0.25 A per contact with 400 contacts (4x100) powered.

Mating – Unmating Forces

Thermal Aging Group

- **Initial**
 - **Mating**
 - **Min** -----11.83 lbs
 - **Max** -----12.85 lbs
 - **Unmating**
 - **Min** ----- 6.76 lbs
 - **Max** ----- 7.80 lbs
- **After Thermal**
 - **Mating**
 - **Min** ----- 7.10 lbs
 - **Max** ----- 8.61 lbs
 - **Unmating**
 - **Min** -----4.86 lbs
 - **Max** ----- 5.43 lbs

Mating/Unmating Durability Group

- **Initial**
 - **Mating**
 - **Min** -----11.26 lbs
 - **Max** -----13.08 lbs
 - **Unmating**
 - **Min** ----- 5.35 lbs
 - **Max** ----- 7.25 lbs
- **After 25 Cycles**
 - **Mating**
 - **Min** -----12.67 lbs
 - **Max** -----14.09 lbs
 - **Unmating**
 - **Min** ----- 5.45 lbs
 - **Max** ----- 8.27 lbs
- **After Humidity**
 - **Mating**
 - **Min** ----- 8.23 lbs
 - **Max** ----- 8.96 lbs
 - **Unmating**
 - **Min** -----4.31 lbs
 - **Max** ----- 5.24 lbs

RESULTS Continued

Mating/Unmating Basic Group

APF6-020-03.5-L-04-2-A/APM6-020-06.5-L-04-2-A

- **Initial**
 - **Mating**
 - Min ----- 3.88 lbs
 - Max----- 4.75 lbs
 - **Unmating**
 - Min ----- 2.47 lbs
 - Max----- 3.02 lbs
- **After 25 Cycles**
 - **Mating**
 - Min ----- 4.24 lbs
 - Max----- 5.74 lbs
 - **Unmating**
 - Min ----- 2.32 lbs
 - Max----- 3.06 lbs

APF6-100-03.5-L-04-2-A/APM6-100-06.5-L-04-2-A

- **Initial**
 - **Mating**
 - Min -----20.81 lbs
 - Max-----23.27 lbs
 - **Unmating**
 - Min -----11.56 lbs
 - Max-----14.07 lbs
- **After 25 Cycles**
 - **Mating**
 - Min -----23.02 lbs
 - Max-----26.58 lbs
 - **Unmating**
 - Min -----12.88 lbs
 - Max-----14.66 lbs

Normal Force at 0.0095 inches deflection

C-481

- **Initial**
 - Min -----60.60 g Set ---- 0.0002 inches
 - Max -----64.00 g Set ---- 0.0007 inches
- **Thermal**
 - Min -----43.50 g Set-----0.0017 inches
 - Max -----48.20 g Set-----0.0028 inches

C-482

- **Initial**
 - Min -----54.60 g Set ---- 0.0001 inches
 - Max -----59.10 g Set ---- 0.0004 inches
- **Thermal**
 - Min -----44.30 g Set-----0.0015 inches
 - Max -----48.10 g Set-----0.0020 inches

RESULTS Continued**Insulation Resistance minimums, IR****Pin to Pin**

- **Initial**
 - Mated -----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- **Thermal Shock**
 - Mated -----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- **Humidity**
 - Mated -----13600 Meg Ω ----- Passed
 - Unmated -----23200 Meg Ω ----- Passed

Row to Row (1)

- **Initial**
 - Mated -----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- **Thermal Shock**
 - Mated -----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- **Humidity**
 - Mated -----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed

Row to Row (2)

- **Initial**
 - Mated -----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- **Thermal Shock**
 - Mated -----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- **Humidity**
 - Mated -----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed

Dielectric Withstanding Voltage minimums, DWV

- **Minimums**
 - Breakdown Voltage -----609 VAC
 - Test Voltage -----460 VAC
 - Working Voltage -----150 VAC

Pin to Pin

- **Initial DWV** -----Passed
- **Thermal DWV** -----Passed
- **Humidity DWV** -----Passed

Row to Row (1)

- **Initial DWV** -----Passed
- **Thermal DWV** -----Passed
- **Humidity DWV** -----Passed

Row to Row (2)

- **Initial DWV** -----Passed
- **Thermal DWV** -----Passed
- **Humidity DWV** -----Passed

RESULTS Continued**LLCR Gas Tight (192 LLCR test points)**

- **Initial** ----- 36.11 mOhms Max
- **Gas-Tight**
 - **<= +5.0 mOhms**-----192 Points ----- Stable
 - **+5.1 to +10.0 mOhms**-----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

LLCR Thermal Aging (192 LLCR test points)

- **Initial** ----- 35.13 mOhms Max
- **Thermal Aging**
 - **<= +5.0 mOhms**-----192 Points ----- Stable
 - **+5.1 to +10.0 mOhms**-----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

LLCR Durability (192 LLCR test points)

- **Initial** ----- 35.81 mOhms Max
- **Durability, 25 Cycles**
 - **<= +5.0 mOhms**-----192 Points ----- Stable
 - **+5.1 to +10.0 mOhms**-----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure
- **Thermal**
 - **<= +5.0 mOhms**-----192 Points ----- Stable
 - **+5.1 to +10.0 mOhms**-----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure
- **Humidity**
 - **<= +5.0 mOhms**-----192 Points ----- Stable
 - **+5.1 to +10.0 mOhms**-----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

RESULTS Continued**LLCR Shock & Vibration (192 LLCR test points)**

APF6-060-03.5-L-04-2-A/APM6-060-06.5-L-04-2-A

- **Initial** ----- 39.36 mOhms Max
- **Shock & Vibration**
 - **<= +5.0 mOhms**----- 192 Points ----- Stable
 - **+5.1 to +10.0 mOhms** ----- 0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** ----- 0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** ----- 0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**----- 0 Points ----- Unstable
 - **>+1000 mOhms**----- 0 Points ----- Open Failure

Mechanical Shock & Random Vibration:

- **Shock**
 - **No Damage**----- Pass
 - **50 Nanoseconds** ----- Pass
- **Vibration**
 - **No Damage**----- Pass
 - **50 Nanoseconds** ----- Pass

APF6-100-03.5-L-04-2-A/APM6-100-06.5-L-04-2-A

- **Initial** ----- 34.43 mOhms Max
- **Shock & Vibration**
 - **<= +5.0 mOhms**----- 192 Points ----- Stable
 - **+5.1 to +10.0 mOhms** ----- 0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** ----- 0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** ----- 0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**----- 0 Points ----- Unstable
 - **>+1000 mOhms**----- 0 Points ----- Open Failure

Mechanical Shock & Random Vibration:

- **Shock**
 - **No Damage**----- Pass
 - **50 Nanoseconds** ----- Pass
- **Vibration**
 - **No Damage**----- Pass
 - **50 Nanoseconds** ----- Pass


DATA SUMMARIES


TEMPERATURE RISE (Current Carrying Capacity, CCC):

- 1) High quality thermocouples whose temperature slopes track one another were used for temperature monitoring.
- 2) The thermocouples were placed at a location to sense the maximum temperature generated during testing.
- 3) Temperature readings recorded are those for which three successive readings, 15 minutes apart, differ less than 1° C (computer-controlled data acquisition).
- 4) Adjacent contacts were powered:
 - a. Linear configuration with 4 adjacent conductors/contacts powered

2028937
4 (4X1) Contacts in Series
Part Numbers: APF6-060-03.5-L-04-2-A / APM6-060-06.5-L-04-2-A

Current Rating per Contact (30 Deg. Rise, 20% Derated) = 1.2 Amps







DATA SUMMARIES Continued

b. Linear configuration with 8 adjacent conductors/contacts powered

2028937
 8 (4x2) Contacts in Series
 Part Numbers: APF6-060-03.5-L-04-2-A / APM6-060-06.5-L-04-2-A


Current Rating per Contact (30 Deg. Rise, 20% Derated) = 0.9 Amps




DATA SUMMARIES Continued

c. Linear configuration with 12 adjacent conductors/contacts powered

2028937
 12 (4x3) Contacts in Series
 Part Numbers: APF6-060-03.5-L-04-2-A / APM6-060-06.5-L-04-2-A




2028937
 12 (4x3) Contacts in Series
 Part Numbers: APF6-060-03.5-L-04-2-A / APM6-060-06.5-L-04-2-A




DATA SUMMARIES Continued

d. Linear configuration with 16 adjacent conductors/contacts powered

2028937
 16 (4x4) Contacts in Series
 Part Numbers: APF6-060-03.5-L-04-2-A / APM6-060-06.5-L-04-2-A





2028937
 16 (4x4) Contacts in Series
 Part Numbers: APF6-060-03.5-L-04-2-A / APM6-060-06.5-L-04-2-A



DATA SUMMARIES Continued

e. Linear configuration with 240 adjacent conductors/contacts powered

2028937
 240 (4X60) Contacts in Series
 Part Numbers: APF6-060-03.5-L-04-2-A / APM6-060-06.5-L-04-2-A




DATA SUMMARIES Continued


f. Linear configuration with 400 adjacent conductors/contacts powered

2246232
 400 (All Power) Contacts Powered in Series
 Part Numbers: APF6-100-06.5-L-04-2-A/APM6-100-01.5-L-04-2-A

Current Rating per Contact (30 Deg. Rise, 20% Derated) = 0.25 Amps



2246232
 400 (All Power) Contacts Powered in Series
 Part Numbers: APF6-100-06.5-L-04-2-A/APM6-100-01.5-L-04-2-A



DATA SUMMARIES Continued**MATING/UNMATING:****Thermal Aging Group**

	Initial				After Thermals			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	52.62	11.83	30.07	6.76	31.58	7.10	21.62	4.86
Maximum	57.16	12.85	34.69	7.80	38.30	8.61	24.15	5.43
Average	55.13	12.39	32.39	7.28	34.75	7.81	22.77	5.12
St Dev	1.40	0.31	1.63	0.37	2.01	0.45	0.85	0.19
Count	8	8	8	8	8	8	8	8

Mating/Unmating Durability Group**APF6-060-03.5-L-04-2-A/APM6-060-06.5-L-04-2-A**

	Initial				25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	50.07	11.26	23.80	5.35	56.33	12.67	24.24	5.45
Maximum	58.19	13.08	32.25	7.25	62.66	14.09	36.80	8.27
Average	54.23	12.19	28.06	6.31	59.46	13.37	30.86	6.94
St Dev	2.99	0.67	3.31	0.75	2.23	0.50	4.45	1.00
Count	8	8	8	8	8	8	8	8

	After Humidity			
	Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	36.60	8.23	19.15	4.31
Maximum	39.85	8.96	23.30	5.24
Average	38.19	8.59	21.54	4.84
St Dev	1.36	0.31	1.58	0.36
Count	8	8	8	8

Mating/Unmating Basic Group**APF6-020-03.5-L-04-2-A/APM6-020-06.5-L-04-2-A**

	Initial				25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	17.24	3.88	10.98	2.47	18.88	4.24	10.32	2.32
Maximum	21.14	4.75	13.41	3.02	25.54	5.74	13.59	3.06
Average	18.89	4.25	12.18	2.74	22.06	4.96	11.64	2.62
St Dev	1.47	0.33	0.85	0.19	2.39	0.54	1.12	0.25
Count	8	8	8	8	8	8	8	8

DATA SUMMARIES Continued


Mating/Unmating Basic Group

APF6-100-03.5-L-04-2-A/APM6-100-06.5-L-04-2-A

	Initial				25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)
Minimum	92.56	20.81	51.42	11.56	102.39	23.02	57.29	12.88
Maximum	103.50	23.27	62.58	14.07	118.23	26.58	65.21	14.66
Average	97.93	22.02	57.57	12.94	109.37	24.59	61.79	13.89
St Dev	4.07	0.92	3.33	0.75	5.43	1.22	2.64	0.59
Count	8	8	8	8	8	8	8	8

Mating\Unmating Force Comparison

Mating/Unmating Data for 20, 60 and 100 Position APF6/APM6



DATA SUMMARIES Continued


NORMAL FORCE (FOR CONTACTS TESTED IN THE HOUSING):

- 1) Calibrated force gauges are used along with computer-controlled positioning equipment.
- 2) For Normal force 8-10 measurements are taken and the averages reported.

C-481

Initial	Deflections in inches Forces in Grams										
	<u>0.0010</u>	<u>0.0019</u>	<u>0.0029</u>	<u>0.0038</u>	<u>0.0048</u>	<u>0.0057</u>	<u>0.0067</u>	<u>0.0076</u>	<u>0.0086</u>	<u>0.0095</u>	<i>SET</i>
Averages	5.54	12.09	18.73	25.51	31.96	38.65	45.03	51.08	56.91	62.18	0.0004
Min	4.80	10.70	17.30	24.00	30.50	37.10	43.30	49.50	55.50	60.60	0.0002
Max	6.30	12.80	20.00	26.60	33.70	40.50	47.20	53.30	58.70	64.00	0.0007
St. Dev	0.440	0.693	0.716	0.769	0.902	1.014	1.091	1.105	1.052	1.061	0.0001
Count	12	12	12	12	12	12	12	12	12	12	12

After Thermals	Deflections in inches Forces in Grams										
	<u>0.0010</u>	<u>0.0019</u>	<u>0.0029</u>	<u>0.0038</u>	<u>0.0048</u>	<u>0.0057</u>	<u>0.0067</u>	<u>0.0076</u>	<u>0.0086</u>	<u>0.0095</u>	<i>SET</i>
Averages	0.01	0.02	3.36	8.06	12.67	18.01	24.25	31.29	38.38	45.38	0.0022
Min	0.00	0.00	2.00	6.90	11.40	16.20	22.30	29.10	35.80	43.50	0.0017
Max	0.10	0.10	4.40	9.30	14.20	20.20	26.50	33.80	41.20	48.20	0.0028
St. Dev	0.029	0.039	0.854	0.738	0.904	1.152	1.361	1.363	1.443	1.382	0.0003
Count	12	12	12	12	12	12	12	12	12	12	12




DATA SUMMARIES Continued**NORMAL FORCE (FOR CONTACTS TESTED IN THE HOUSING):**

- 1) Calibrated force gauges are used along with computer-controlled positioning equipment.
- 2) For Normal force 8-10 measurements are taken and the averages reported.

C-482

Initial	Deflections in inches Forces in Grams										
	<u>0.0010</u>	<u>0.0019</u>	<u>0.0029</u>	<u>0.0038</u>	<u>0.0048</u>	<u>0.0057</u>	<u>0.0067</u>	<u>0.0076</u>	<u>0.0086</u>	<u>0.0095</u>	<i>SET</i>
Averages	5.01	10.57	16.16	21.95	27.74	33.49	39.35	45.23	50.88	56.46	0.0002
Min	4.10	9.70	15.20	20.80	26.20	32.00	37.70	43.60	48.90	54.60	0.0001
Max	5.80	11.60	17.40	23.00	29.50	35.30	40.90	46.90	53.00	59.10	0.0004
St. Dev	0.540	0.614	0.684	0.697	0.914	0.969	1.021	1.100	1.216	1.308	0.0001
Count	12	12	12	12	12	12	12	12	12	12	12

After Thermals	Deflections in inches Forces in Grams										
	<u>0.0010</u>	<u>0.0019</u>	<u>0.0029</u>	<u>0.0038</u>	<u>0.0048</u>	<u>0.0057</u>	<u>0.0067</u>	<u>0.0076</u>	<u>0.0086</u>	<u>0.0095</u>	<i>SET</i>
Averages	0.01	1.52	5.75	10.16	15.15	20.81	26.98	33.31	39.52	45.80	0.0016
Min	-0.10	0.40	4.40	9.00	14.30	18.80	25.40	31.80	38.00	44.30	0.0015
Max	0.10	2.20	6.60	11.20	16.80	23.10	29.40	35.80	41.90	48.10	0.0020
St. Dev	0.051	0.673	0.595	0.623	0.775	1.171	1.119	1.129	1.106	1.109	0.0001
Count	12	12	12	12	12	12	12	12	12	12	12

Normal Force - Average Initial vs Average Thermal

DATA SUMMARIES Continued**INSULATION RESISTANCE (IR):**

	Pin to Pin		
	Mated	Unmated	Unmated
Minimum	APF6/APM6	APF6	APM6
Initial	45000	45000	45000
Thermal	45000	45000	45000
Humidity	13600	23200	28200

	Row to Row (1)		
	Mated	Unmated	Unmated
Minimum	APF6/APM6	APF6	APM6
Initial	45000	45000	45000
Thermal	45000	45000	45000
Humidity	45000	45000	45000

	Row to Row (2)		
	Mated	Unmated	Unmated
Minimum	APF6/APM6	APF6	APM6
Initial	45000	45000	45000
Thermal	45000	45000	45000
Humidity	45000	45000	45000

DIELECTRIC WITHSTANDING VOLTAGE (DWV):

Voltage Rating Summary	
Minimum	APF6/APM6
Break Down Voltage	609
Test Voltage	460
Working Voltage	150

Pin to Pin	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed
After Humidity Test Voltage	Passed

Row to Row (1)	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed
After Humidity Test Voltage	Passed

Row to Row (2)	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed
After Humidity Test Voltage	Passed

DATA SUMMARIES Continued**LLCR Durability:**

- 1) A total of 192 points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: -----Stable
 - b. $+5.1$ to $+10.0$ mOhms: -----Minor
 - c. $+10.1$ to $+15.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms: -----Unstable
 - f. $>+1000$ mOhms: -----Open Failure

LLCR Measurement Summaries by Pin Type				
Date	7/8/2019	7/15/2019	7/29/2019	8/9/2019
Room Temp (Deg C)	23	23	23	23
Rel Humidity (%)	51	48	50	57
Technician	Tony Wagoner	Tony Wagoner	Tony Wagoner	Tony Wagoner
mOhm values	Actual Initial	Delta 25 Cycles	Delta Therm Shck	Delta Humidity
Pin Type 1: Signal				
Average	32.54	1.00	1.20	1.15
St. Dev.	1.30	0.75	0.75	0.80
Min	29.77	0.00	0.00	0.01
Max	35.81	3.63	3.01	4.43
Summary Count	192	192	192	192
Total Count	192	192	192	192

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
	≤ 5	$>5 \text{ \& } \leq 10$	$>10 \text{ \& } \leq 15$	$>15 \text{ \& } \leq 50$	$>50 \text{ \& } \leq 1000$	>1000
25 Cycles	192	0	0	0	0	0
Therm Shck	192	0	0	0	0	0
Humidity	192	0	0	0	0	0

DATA SUMMARIES Continued

LLCR Thermal Aging:

- 1) A total of 192 points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: -----Stable
 - b. $+5.1$ to $+10.0$ mOhms:-----Minor
 - c. $+10.1$ to $+15.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms -----Unstable
 - f. $>+1000$ mOhms:-----Open Failure

LLCR Measurement Summaries by Pin Type				
Date	7/3/2019	7/15/2019		
Room Temp (Deg C)	23	23		
Rel Humidity (%)	50	51		
Technician	Tony Wagoner	Tony Wagoner		
mOhm values	Actual Initial	Delta Thermal	Delta	Delta
Pin Type 1: Signal				
Average	32.36	0.37		
St. Dev.	1.26	0.27		
Min	29.89	0.01		
Max	35.13	1.81		
Summary Count	192	192		
Total Count	192	192		

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	≤ 5	>5 & ≤ 10	>10 & ≤ 15	>15 & ≤ 50	>50 & ≤ 1000	>1000
Thermal	192	0	0	0	0	0

DATA SUMMARIES Continued

LLCR Gas Tight:

- 1) A total of 192 points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: -----Stable
 - b. $+5.1$ to $+10.0$ mOhms: -----Minor
 - c. $+10.1$ to $+15.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms: -----Unstable
 - f. $>+1000$ mOhms: -----Open Failure

LLCR Measurement Summaries by Pin Type				
Date	7/5/2019	7/9/2019		
Room Temp (Deg C)	23	23		
Rel Humidity (%)	48	48		
Technician	Tony Wagoner	Tony Wagoner		
mOhm values	Actual Initial	Delta Acid Vapor	Delta	Delta
Pin Type 1: Signal				
Average	32.08	0.23		
St. Dev.	1.27	0.25		
Min	29.58	0.00		
Max	36.11	1.39		
Summary Count	192	192		
Total Count	192	192		

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
	≤ 5	$>5 \ \& \ \leq 10$	$>10 \ \& \ \leq 15$	$>15 \ \& \ \leq 50$	$>50 \ \& \ \leq 1000$	>1000
Acid Vapor	192	0	0	0	0	0

DATA SUMMARIES Continued

LLCR Shock &Vibration Group:

- 1). A total of 192 points were measured.
- 2). EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets.*
- 3). The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: -----Stable
 - b. $+5.1$ to $+10.0$ mOhms: -----Minor
 - c. $+10.1$ to $+15.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms -----Unstable
 - f. $>+1000$ mOhms:-----Open Failure

APF6-060-03.5-L-04-2-A/APM6-060-06.5-L-04-2-A

LLCR Measurement Summaries by Pin Type				
Date	7/15/2019	8/2/2019		
Room Temp (Deg C)	23	22		
Rel Humidity (%)	49	50		
Technician	Tony Wagoner	Tony Wagoner		
mOhm values	Actual	Delta	Delta	Delta
	Initial	Shock-Vib		
Pin Type 1: Signal				
Average	32.66	0.29		
St. Dev.	1.87	0.37		
Min	30.05	0.00		
Max	39.36	3.01		
Summary Count	192	192		
Total Count	192	192		

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	≤ 5	$>5 \ \& \ \leq 10$	$>10 \ \& \ \leq 15$	$>15 \ \& \ \leq 50$	$>50 \ \& \ \leq 1000$	>1000
Shock-Vib	192	0	0	0	0	0

Nanosecond Event Detection:

Shock and Vibration Event Detection Summary	
Contacts tested	60
Test Condition	C, 100g's, 6ms, Half-Sine
Shock Events	0
Test Condition	V-B, 7.56 rms g
Vibration Events	0
Total Events	0

DATA SUMMARIES Continued

LLCR Shock &Vibration Group:

- 1). A total of 192 points were measured.
- 2). EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets.*
- 3). The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: -----Stable
 - b. $+5.1$ to $+10.0$ mOhms: -----Minor
 - c. $+10.1$ to $+10.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms -----Unstable
 - f. $>+1000$ mOhms:-----Open Failure

APF6-100-03.5-L-04-2-A/APM6-100-06.5-L-04-2-A

LLCR Measurement Summaries by Pin Type				
Date	1/8/2020	2/7/2020		
Room Temp (Deg C)	23	23		
Rel Humidity (%)	34	24		
Technician	Aaron McKim	Aaron McKim		
mOhm values	Actual	Delta	Delta	Delta
	Initial	Shock-Vib		
Pin Type 1: Signal				
Average	31.93	0.61		
St. Dev.	1.02	0.57		
Min	29.31	0.01		
Max	34.43	3.55		
Summary Count	192	192		
Total Count	192	192		

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	≤ 5	$>5 \ \& \ \leq 10$	$>10 \ \& \ \leq 15$	$>15 \ \& \ \leq 50$	$>50 \ \& \ \leq 1000$	>1000
Shock-Vib	192	0	0	0	0	0

Nanosecond Event Detection:

Shock and Vibration Event Detection Summary	
Contacts tested	60
Test Condition	C, 100g's, 6ms, Half-Sine
Shock Events	0
Test Condition	V-B, 7.56 rms g
Vibration Events	0
Total Events	0

EQUIPMENT AND CALIBRATION SCHEDULES**Equipment #:** TCT-04**Description:** Dillon Quantrol TC21 25-1000 mm/min series test stand**Manufacturer:** Dillon Quantrol**Model:** TC2 I series test stand**Serial #:** 04-1041-04**Accuracy:** Speed Accuracy: +/- 5% of indicated speed; Speed Accuracy: +/- 5% of indicated speed;
... Last Cal: 05/29/2019, Next Cal: 05/29/2020**Equipment #:** MO-11**Description:** Switch/Multimeter**Manufacturer:** Keithley**Model:** 3706**Serial #:** 120169**Accuracy:** See Manual

... Last Cal: 09/11/2019, Next Cal: 09/11/2020

Equipment #: THC-05**Description:** Temperature/Humidity Chamber (Chamber Room)**Manufacturer:** Thermotron**Model:** SM-8-3800**Serial #:** 05 23 00 02**Accuracy:** See Manual

... Last Cal: 11/14/2019, Next Cal: 11/14/2020

Equipment #: TSC-01**Description:** Vertical Thermal Shock Chamber**Manufacturer:** Cincinnati Sub Zero**Model:** VTS-3-6-6-SC/AC**Serial #:** 10-VT14993**Accuracy:** See Manual

... Last Cal: 06/30/2019, Next Cal: 06/30/2020

Equipment #: HPT-01**Description:** Hipot Safety Tester**Manufacturer:** Vitrek**Model:** V73**Serial #:** 019808**Accuracy:**

... Last Cal: 05/15/2019, Next Cal: 05/15/2020

Equipment #: OV-05**Description:** Forced Air Oven, 5 Cu. Ft., 120 V (Chamber Room)**Manufacturer:** Sheldon Mfg.**Model:** CE5F**Serial #:** 02008008**Accuracy:** +/- 5 deg. C

... Last Cal: 02/05/2019, Next Cal: 02/05/2020

EQUIPMENT AND CALIBRATION SCHEDULES**Equipment #:** MO-04**Description:** Multimeter /Data Acquisition System**Manufacturer:** Keithley**Model:** 2700**Serial #:** 0798688**Accuracy:** See Manual

... Last Cal: 09/11/2019, Next Cal: 09/11/2020

Equipment #: PS-02**Description:** Power Supply**Manufacturer:** Hewlett-Packard**Model:** 6033A**Serial #:** N/A**Accuracy:** See Manual

... Last Cal: NOT CALIBRATED

Equipment #: SVC-01**Description:** Shock & Vibration Table**Manufacturer:** Data Physics**Model:** LE-DSA-10-20K**Serial #:** 10037**Accuracy:** See Manual

... Last Cal: 04/22/2019, Next Cal: 04/22/2020

Equipment #: ACLM-01**Description:** Accelerometer**Manufacturer:** PCB Piezotronics**Model:** 352C03**Serial #:** 115819**Accuracy:** See Manual

... Last Cal: 07/18/2019, Next Cal: 07/18/2020

Equipment #: ED-03**Description:** Event Detector**Manufacturer:** Analysis Tech**Model:** 32EHD**Serial #:** 1100604**Accuracy:** See Manual

... Last Cal: 10/31/2019, Next Cal: 10/31/2020