





Project Number: 227578		Tracking Code: 227578 Report Rev 2	
Requested by: Eric Mings		Date: 5/20/2013	Product Rev: 0
Part #: ET60S-00-24-06-L-RT1-GP/ET60T-00-24-06-L-RT1-GP		Tech: Tony Wagoner	Eng: Eric Mings
Part description: ET60 R/A Power Assembly			Qty to test: 23
Test Start: 11/16/2012	Test Completed: 12/15/2012		

## SAMTEC POWER CHARACTERIZATION



**Right Angle Socket Power Assembly  
ET60S-00-24-06-L-RT1-GP  
ET60T-00-24-06-L-RT1-GP**

## CERTIFICATION

All instruments and measuring equipment were calibrated to National Institute for Standards and Technology (NIST) traceable standards according to ISO 10012-1 and ANSI/NCSL 2540-1, as applicable.

All contents contained herein are the property of Samtec. No portion of this report, in part or in full shall be reproduced without prior written approval of Samtec.

### SCOPE

1. Temperature Rise/Current Carrying Capacity
  - 1.1. To determine the amount of current the device under test (DUT) can safely carry over the operating temperature range of the DUT.
  - 1.2. Contact loading will also be addressed in this document which will determine how much current can be carried as the number of energized contacts is varied.
2. Current Cycling
  - 2.1. To determine the performance of the device under test (DUT) when subjected to the power-on/power-off cycling that heats and cools the DUT in normal everyday use.
  - 2.2. Contact loading will set to 100% throughout the test.


### APPLICABLE DOCUMENTS

Standards: EIA Publication 364-70 Temperature Rise  
EIA Publication 364-06 Contact Resistance  
EIA Publication 364-55 Current Cycling  
TLPM-032 Current Carrying Capacity  
TLPM-084 Current Cycling  
IEC 512-3 Electromechanical Components for Electronic Equipment: Basic Testing Procedures and Measuring Methods, Part 3: Current Carrying Capacity Tests

### TEST SAMPLES AND PREPARATION

1. All materials shall be manufactured in accordance with the applicable product specification.
2. All test samples shall be identified and encoded to maintain traceability throughout the test sequences.
3. After soldering, the parts to be used shall be cleaned according to TLWI-0001.
4. All samples shall be visually inspected and cleaned as necessary.
5. Any additional preparation shall be noted in the individual test sequences.
6. Solder Information: Lead Free
7. Re-Flow Time/Temp: See accompanying profile.
8. All products designed to operate mounted on a printed circuits board shall be tested mounted to test boards in accordance with EIA-364-70.

PREPARED TEST SAMPLE



9. The following loading configurations shall be tested for Temperature Rise/Current Carrying Capacity testing of single row connector systems:
- 9.1. One contact energized only
  - 9.2. Two contacts energized adjacent to each other
  - 9.3. Three contacts energized adjacent to each other
  - 9.4. Four contacts energized adjacent to each other
  - 9.5. All contacts energized

✦ Indicates energized contacts

✦ Indicates thermocouple monitored, energized contacts

Test Condition as in 9.1 above

✦			
---	--	--	--

10. For Current Cycling, only 100 % loading will be tested.



# POWER INTEGRITY TEST REPORT

227578

Revision 2

## FLOWCHARTS

### POWER PINS

#### Current Carrying Capacity - Power Pins

TEST STEP	GROUP A1 3 Mated Assemblies 1 Contact Powered	GROUP A2 3 Mated Assemblies 2 Contacts Powered	GROUP A3 3 Mated Assemblies 3 Contacts Powered	GROUP A4 3 Mated Assemblies 4 Contacts Powered	GROUP A5 3 Mated Assemblies All Contacts Powered
01	CCC	CCC	CCC	CCC	CCC

### SIGNAL PINS

#### Current Carrying Capacity - Singal Pins

TEST STEP	GROUP D1 3 Mated Assemblies 1 Vertical Row Powered	GROUP D2 3 Mated Assemblies 2 Adjacent Vertical Rows Powered	GROUP D3 3 Mated Assemblies 3 Adjacent Vertical Rows Powered	GROUP D4 3 Mated Assemblies 4 Adjacent Vertical Rows Powered	GROUP D5 3 Mated Assemblies All Contacts Powered
01	CCC	CCC	CCC	CCC	CCC

### POWER & SIGNAL PINS

#### Current Carrying Capacity - Power and Signal Pins

TEST STEP	GROUP E1 3 Mated Assemblies Signal Pins @ 1/2 rated current from Group D5 Power Pins - All Contacts Powered
01	CCC

(TIN PLATING) - Tabulate calculated current at RT, 65°C, 75°C and 95°C after derating 20% and based on 105°C

(GOLD PLATING) - Tabulate calculated current at RT, 85°C, 95°C and 115°C after derating 20% and based on 125°C

CCC, Temp rise = EIA-364-70

### Current Cycling

TEST STEP	GROUP A 8 Mated Assemblies ALL CONTACTS POWERED
01	Current Cycle, 500 cycles at 125% of Rated current

Current Cycle = EIA 364-55, Condition "B", Method #4

Test at Current 125% of Rated Current

Measure at 45 minutes into ON time of cycle

Measure Voltage Drop on 5 random contacts



**POWER INTEGRITY TEST  
REPORT**

**227578**

**Revision 2**

**TEST PROCEDURES**

<b>Part No.</b>	<b>ET60T-00-24-06-L-RT1-GP</b>	<b>Mating Part No.</b>	<b>ET60S-00-24-06-L-RT1-GP</b>
<b>Sample Size</b>	<b>15</b>	<b>Technician</b>	<b>Tony Wagoner</b>
<b>Start Date</b>	<b>11/16/2012</b>	<b>Complete Date</b>	<b>12/13/2012</b>
<b>Room Ambient</b>	<b>26°C</b>	<b>Relative Humidity</b>	<b>35%</b>
<b>Equipment ID#: MO-04, PS-07, TCS-013,047,001,027,032,034,015,041</b>			

**TEMPERATURE RISE (Current Carrying Capacity, CCC):**

11. Thermocouples shall be calibrated in accordance with Samtec documents; TLWI 0003, Thermocouple Welding Procedure and TLWI 0005, Thermocouple Calibration
12. The thermocouples shall be placed at a location to sense the maximum temperature generated during testing.
13. Temperature stability shall be defined as the temperature at which three successive readings, 5 minutes apart, differ not more than 1° C (computer controlled data acquisition). This is the Temperature Rise that the Current Carrying Capacity and De-rating curves are based on.
14. The following loading configurations shall be tested (double for two row systems):
  - 14.1. One contact energized only
  - 14.2. Two contacts energized adjacent to each other
  - 14.3. Three contacts energized adjacent to each other
  - 14.4. Four contacts energized adjacent to each other
  - 14.5. All contacts energized
15. The following loading configurations shall be tested for Temperature Rise/Current Carrying Capacity testing of two row connector systems:
  - 15.1. Two by One contact energized
  - 15.2. Two by Two contacts energized adjacent to each other
  - 15.3. Two by Three contacts energized adjacent to each other
  - 15.4. Two by Four contacts energized adjacent to each other
  - 15.5. All contacts energized
16. Three samples shall be tested for each of the above configurations for a total of eighteen assemblies.
17. Temperature Rise measurements shall be made at 5 different current levels yielding temperature rises in the 10 to 70°C range.
18. The base curve for the Current Rating chart will be derived from the average (maximum) value of three test specimens in accordance with IEC 512-3, Test 5b.



**POWER INTEGRITY TEST  
REPORT**

**227578**

**Revision 2**

<b>Part No.</b>	<b>ET60T-00-24-06-L-RT1-GP</b>	<b>Mating Part No.</b>	<b>ET60S-00-24-06-L-RT1-GP</b>
<b>Sample Size</b>	<b>8</b>	<b>Technician</b>	<b>Tony Wagoner</b>
<b>Start Date</b>	<b>11/19/2012</b>	<b>Complete Date</b>	<b>12/10/2012</b>
<b>Room Ambient</b>	<b>23°C</b>	<b>Relative Humidity</b>	<b>36%</b>
<b>Equipment ID#: MO-09, RS-01</b>			

**CURRENT CYCLING**

1. Samples shall be prepared and tested as above (paragraph 14.5).
2. Current Cycling shall be performed in accordance with EIA-364-55, Test Condition
3. Testing shall be as follows:
  - 3.1. Test Current: **TEST CURRENT**(125% of 30°C Rating)
  - 3.2. "ON" Time: 45 Minutes
  - 3.3. "OFF" Time: 15 Minutes
  - 3.4. Number of Cycles: 500
  - 3.5. Measurements: 40 minutes into ON cycle
    - 3.5.1. Temperature
    - 3.5.2. Voltage Drop/Contact Resistance
4. Temperature vs. Number of Cycles and Voltage Drop vs. Number of Cycles shall be measured and recorded.

**TEST RESULTS**

**CURRENT CARRYING CAPACITY (CCC) RESULTS**

- There was no evidence of physical damage to the test samples as tested.
- The following is a summary of the observed data:

**Power Pins**

Temperature Rise, CCC at a 20% de-rating

- CCC for a 30°C Temperature Rise -----70.0 A per contact with 1 contacts (1 x 1) powered
- CCC for a 30°C Temperature Rise -----59.5A per contact with 2 contacts (1 x 2) powered
- CCC for a 30°C Temperature Rise -----52.8A per contact with 3 contacts (1 x 3) powered
- CCC for a 30°C Temperature Rise -----48.2A per contact with 4 contacts (1 x 4) powered
- CCC for a 30°C Temperature Rise -----45.0A per contact with 6 contacts (1 x 6) powered

**Signal Pins**

Temperature Rise, CCC at a 20% de-rating

- CCC for a 30°C Temperature Rise -----3.3A per contact with 3 contacts (3 x 1) powered
- CCC for a 30°C Temperature Rise -----2.5A per contact with 6 contacts (3 x 2) powered
- CCC for a 30°C Temperature Rise -----2.2A per contact with 9 contacts (3 x 3) powered
- CCC for a 30°C Temperature Rise -----2.0A per contact with 12 contacts (3 x 4) powered
- CCC for a 30°C Temperature Rise -----1.6A per contact with 24 contacts (3 x 8) powered

**Power Pins (with Signal Pins powered at 1/2 rated current at 0.95 Amps)**

Temperature Rise, CCC at a 20% de-rating

- CCC for a 30°C Temperature Rise -----43.1A per contact with 6 contacts (1 x 6) powered and 24 signal pins powered at 1/2 rated current at 0.95 Amps)



# POWER INTEGRITY TEST REPORT

227578

Revision 2

## CURRENT CYCLING RESULTS


Test Condition: 500 Cycles, 45 minutes ON and 15 minutes OFF

- Test Current -----53.8 Amps
  
- Contact Resistances, Measured 40 minutes into the FIRST and LAST ON cycle
  - Initial
    - Min -----.14mOhms
    - Max-----.19mOhms
  - Final
    - Min -----.12mOhms
    - Max-----.17mOhms
  
- Temperature Change, Measured 40 minutes into the FIRST and LAST ON cycle
  - Initial Temperature Change -----32.3°C
  - Final Temperature Change -----29.9°C

**TEST DATA (POWER)**

**CONTACT RESISTANCE @ RATED CURRENT - DC Resistance (DCR)**

The following data represents the Voltage drop and Contact Resistance at Rated Current for the 100% energized samples:




**CONTACT RESISTANCE DATA  
ALL CONTACTS ENERGIZED  
(mΩ)**

TEST CURRENT AMPS	31.46	44.49	54.53	62.95	70.4
Min	0.12	0.12	0.13	0.13	0.13
Max	0.18	0.18	0.18	0.18	0.19
Avg	0.14	0.14	0.14	0.15	0.15

**TEST DATA (POWER)**

**VOLTAGE DROP @ RATED CURRENT**

The following data represents the Voltage drop at Rated Current for the 100% energized samples:




**VOLTAGE DROP DATA  
ALL CONTACTS ENERGIZED  
(mV)**

TEST CURRENT AMPS	31.46	44.49	54.53	62.95	70.4
Min	3.71	5.43	6.85	8.14	9.35
Max	5.56	7.98	9.9	11.52	13.11
Avg	4.35	6.31	7.92	9.36	10.7

**TEST DATA (SIGNAL)**

**VOLTAGE DROP @ RATED CURRENT**

The following data represents the Voltage drop at Rated Current for the 100% energized samples:




**CONTACT RESISTANCE DATA  
ALL CONTACTS ENERGIZED  
(mΩ)**

TEST CURRENT AMPS	1.3	1.84	2.26	2.6	2.91
Min	10.42	10.52	10.59	10.75	10.85
Max	16.77	16.74	16.85	17.06	17.18
Avg	12.72	12.85	12.98	13.16	13.38

**TEST DATA (SIGNAL)**

**VOLTAGE DROP @ RATED CURRENT**

The following data represents the Voltage drop at Rated Current for the 100% energized samples:




**VOLTAGE DROP DATA  
ALL CONTACTS ENERGIZED  
(mV)**

TEST CURRENT AMPS	1.3	1.84	2.26	2.6	2.91
Min	13.54	19.36	23.94	27.96	31.56
Max	21.8	30.81	38.09	44.35	49.99
Avg	16.73	23.88	29.56	34.49	39.1


## CURRENT CARRYING CAPACITY DATA-POWER

227578 (Samtec)  
 1 (1x1-Power Pins) Contacts in Series  
 Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP

*Current Rating per Contact (30 Deg. Rise, 20% Derated) = 70.0 Amps*



227578 (Samtec)  
 1 (1x1-Power Pins) Contacts in Series  
 Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP





# POWER INTEGRITY TEST REPORT

**227578**

**Revision 2**

## TEMPERATURE RISE DATA ONE CONTACT ENERGIZED (Degrees Celsius above ambient)

TEST CURRENT AMPS	54.47	77.07	94.49	109.1	121.99
Sample 1	11.4	22.7	33.5	45.2	56.3
Sample 2	13	25.2	36.6	47.5	58.8
Sample 3	12.2	23.8	34.7	45.7	56.5
Min	11.4	22.7	33.5	45.2	56.3
Max	13	25.2	36.6	47.5	58.8
Avg	12.2	23.9	34.93	46.13	57.2

✦ Indicates energized contacts


✦ Indicates thermocouple monitored, energized contacts

Single Row Configuration




227578 (Samtec)  
 2 (1x2-Power Pins) Contacts in Series  
 Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP

*Current Rating per Contact (30 Deg. Rise, 20% Derated) = 59.5 Amps*



227578 (Samtec)  
 2 (1x2-Power Pins) Contacts in Series  
 Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP





# POWER INTEGRITY TEST REPORT

227578

Revision 2

## TEMPERATURE RISE DATA TWO CONTACTS ENERGIZED (Degrees Celsius above ambient)

TEST CURRENT AMPS	44.49	62.92	77.14	89.08	99.59
Sample 4	11.7	21.8	32.4	42.8	53
Sample 5	11.6	21.4	31.5	41.4	51.5
Sample 6	11.8	22.2	32.9	43.4	54.1
Min	11.6	21.4	31.5	41.4	51.5
Max	11.8	22.2	32.9	43.4	54.1
Avg	11.7	21.8	32.27	42.53	52.87

✦ Indicates energized contacts


✦ Indicates thermocouple monitored, energized contacts

Single Row Configuration




227578 (Samtec)  
 3 (1x3-Power Pins) Contacts in Series  
 Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP

Current Rating per Contact (30 Deg. Rise, 20% Derated) = 52.8 Amps



227578 (Samtec)  
 3 (1x3-Power Pins) Contacts in Series  
 Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP





# POWER INTEGRITY TEST REPORT

227578

Revision 2

## TEMPERATURE RISE DATA THREE CONTACTS ENERGIZED (Degrees Celsius above ambient)

TEST CURRENT AMPS	38.52	54.46	66.79	77.13	86.25
Sample 7	10.8	20.9	30.8	40.7	50.6
Sample 8	10.9	21.3	31.2	40.6	50
Sample 9	10.9	21	30.7	40.7	50.3
Min	10.8	20.9	30.7	40.6	50
Max	10.9	21.3	31.2	40.7	50.6
Avg	10.87	21.07	30.9	40.67	50.3

✦ Indicates energized contacts



✦ Indicates thermocouple monitored, energized contacts

Single Row Configuration

✦	✦	✦	
---	---	---	--

227578 (Samtec)  
 4 (1x4-Power Pins) Contacts in Series  
 Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP

Current Rating per Contact (30 Deg. Rise, 20% Derated) = 48.2 Amps





# POWER INTEGRITY TEST REPORT

227578

Revision 2

## TEMPERATURE RISE DATA FOUR CONTACTS ENERGIZED (Degrees Celsius above ambient)

TEST CURRENT AMPS	34.47	48.73	59.73	68.99	77.14
Sample 10	10.4	20.6	30.5	40.8	50.9
Sample 11	10.3	19.7	28.9	38.5	47.9
Sample 12	10.2	19.7	28.9	38.7	48
Min	10.2	19.7	28.9	38.5	47.9
Max	10.4	20.6	30.5	40.8	50.9
Avg	10.3	20	29.43	39.33	48.93

✦ Indicates energized contacts


✦ Indicates thermocouple monitored, energized contacts

Single Row Configuration




227578 (Samtec)  
 6 (All Power-Power Pins) Contacts in Series  
 Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP

*Current Rating per Contact (30 Deg. Rise, 20% Derated) = 45.0 Amps*



227578 (Samtec)  
 6 (All Power-Power Pins) Contacts in Series  
 Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP




**TEMPERATURE RISE DATA  
ALL CONTACTS ENERGIZED  
(Degrees Celsius above ambient)**

TEST CURRENT AMPS	31.46	44.49	54.53	62.95	70.4
Sample 13	9.1	18.9	28.1	37.1	45.9
Sample 14	10.1	19.8	29.3	38.8	48.4
Sample 15	9.8	18.9	27.7	36.6	45.6
Min	9.1	18.9	27.7	36.6	45.6
Max	10.1	19.8	29.3	38.8	48.4
Avg	9.67	19.2	28.37	37.5	46.63

✦ Indicates energized contacts


✦ Indicates thermocouple monitored, energized contacts




## CURRENT CARRYING CAPACITY-SIGNAL

227578 (Samtec)  
 3 (3x1-Signal Pins) Contacts in Series  
 Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP

Current Rating per Contact (30 Deg. Rise, 20% Derated) = 3.3 Amps



227578 (Samtec)  
 3 (3x1-Signal Pins) Contacts in Series  
 Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP





**POWER INTEGRITY TEST  
REPORT**

**227578**

**Revision 2**

**TEMPERATURE RISE DATA  
3 CONTACTS ENERGIZED  
(Degrees Celsius above ambient)**


TEST CURRENT AMPS	2.22	3.14	3.85	4.45	4.97
Sample 1	9.4	18.3	26.9	35.7	45.7
Sample 2	8.7	17.1	25	32.9	42
Sample 3	8.4	16.2	23.7	30.8	42.4
Min	8.4	16.2	23.7	30.8	42
Max	9.4	18.3	26.9	35.7	45.7
Avg	8.83	17.2	25.2	33.13	43.37

✦ Indicates energized contacts


✦ Indicates thermocouple monitored, energized contacts

✦			
✦			

227578 (Samtec)  
6 (3x2-Signal Pins) Contacts in Series  
Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP



227578 (Samtec)  
6 (3x2-Signal Pins) Contacts in Series  
Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP





# POWER INTEGRITY TEST REPORT

**227578**

**Revision 2**

## TEMPERATURE RISE DATA 6 CONTACTS ENERGIZED (Degrees Celsius above ambient)

TEST CURRENT AMPS	1.87	2.64	3.24	3.74	4.18
Sample 1	11.4	21.3	31.4	41.4	51.4
Sample 2	10.8	19.7	29.4	39.9	50.1
Sample 3	11.6	21.7	32.1	42.1	51.9
Min	10.8	19.7	29.4	39.9	50.1
Max	11.6	21.7	32.1	42.1	51.9
Avg	11.27	20.9	30.97	41.13	51.13


✦ Indicates energized contacts

✦ Indicates thermocouple monitored, energized contacts


✦	✦		
✦	✦		

227578 (Samtec)  
 9 (3x3-Signal Pins) Contacts in Series  
 Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP

*Current Rating per Contact (30 Deg. Rise, 20% Derated) = 2.2 Amps*



227578 (Samtec)  
 9 (3x3-Signal Pins) Contacts in Series  
 Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP





# POWER INTEGRITY TEST REPORT

**227578**

**Revision 2**

## TEMPERATURE RISE DATA 9 CONTACTS ENERGIZED (Degrees Celsius above ambient)


TEST CURRENT AMPS	1.68	2.38	2.91	3.36	3.76
Sample 1	12.1	23.6	34.7	45.7	56.4
Sample 2	11.2	21.3	31.5	41	50.8
Sample 3	12.4	24.3	35.6	46.9	57.8
Min	11.2	21.3	31.5	41	50.8
Max	12.4	24.3	35.6	46.9	57.8
Avg	11.9	23.07	33.93	44.53	55

- ✦ Indicates energized contacts
- ✦ Indicates thermocouple monitored, energized contacts


✦	✦	✦	
✦	✦	✦	

227578 (Samtec)  
 12 (3x4-Signal Pins) Contacts in Series  
 Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP

*Current Rating per Contact (30 Deg. Rise, 20% Derated) = 2.0 Amps*



227578 (Samtec)  
 12 (3x4-Signal Pins) Contacts in Series  
 Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP





# POWER INTEGRITY TEST REPORT

227578

Revision 2


## TEMPERATURE RISE DATA TWELVE CONTACTS ENERGIZED (Degrees Celsius above ambient)

TEST CURRENT AMPS	1.48	2.1	2.57	2.97	3.32
Sample 10	11.2	22.1	33.1	43.2	53.4
Sample 11	11.2	21.8	32	41.8	51.8
Sample 12	12	23.7	35.1	46.4	57.5
Min	11.2	21.8	32	41.8	51.8
Max	12	23.7	35.1	46.4	57.5
Avg	11.47	22.53	33.4	43.8	54.23


- ✦ Indicates energized contacts
- ✦ Indicates thermocouple monitored, energized contacts

✦	✦	✦	✦
✦	✦	✦	✦

227578 (Samtec)  
 24 (All Power-Signal Pins) Contacts in Series  
 Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP




227578 (Samtec)  
 24 (All Power - Signal Pins) Contacts in Series  
 Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP




**TEMPERATURE RISE DATA  
ALL CONTACTS ENERGIZED  
(Degrees Celsius above ambient)**

TEST CURRENT AMPS	1.3	1.84	2.26	2.6	2.91
Sample 13	12.5	26.9	39.6	51.8	63.3
Sample 14	12.5	26.8	39	51.3	63.6
Sample 15	12.9	27.9	40.7	53	64.9
Min	12.5	26.8	39	51.3	63.3
Max	12.9	27.9	40.7	53	64.9
Avg	12.63	27.2	39.77	52.03	63.93


- ✦ Indicates energized contacts
- ✦ Indicates thermocouple monitored, energized contacts



227578 (Samtec)(Signal Pins Powered @ 1/2 rated current @ .95 AMPS)  
6 (All Power-Power Pins) Contacts in Series




227578 (Samtec)(Signal Pins Powered @ 1/2 rated current .0.95 Amps)  
6 (All Power-Power Pins) Contacts in Series  
Part Numbers: ET60T-00-24-06-L-RT1-GP / ET60S-00-24-06-L-RT1-GP




**TEMPERATURE RISE DATA**  
**ALL POWER CONTACTS ENERGIZED (Signal Pins powered @ 1/2 rated current)(0.95 Amps)**  
**(Degrees Celsius above ambient)**

TEST CURRENT AMPS	31.46	44.49	54.53	62.95	70.4
Sample 13	11.4	20	28.5	37	45.4
Sample 14	12.2	22	31.5	40.6	50.1
Sample 15	12.3	22.4	32.1	41.3	49.9
Min	11.4	20	28.5	37	45.4
Max	12.3	22.4	32.1	41.3	50.1
Avg	11.97	21.47	30.7	39.63	48.47


- ✦ Indicates energized contacts
- ✦ Indicates thermocouple monitored, energized contacts






**TEMPERATURE RISE DATA  
ALL CONTACTS ENERGIZED  
(Degrees Celsius above ambient)**

	<b>INITIAL</b>	<b>50 CYCLES</b>	<b>100 CYCLES</b>	<b>200 CYCLES</b>	<b>500 CYCLES</b>
<b>Min</b>	30.8	28.7	28.3	28.1	28
<b>Max</b>	33.9	31.8	31.4	31	30.9
<b>Avg</b>	32.3	30.5	30.2	29.8	29.9



**CONTACT RESISTANCE DATA  
ALL CONTACTS ENERGIZED  
(mΩ)**

	INITIAL	50 CYCLES	100 CYCLES	200 CYCLES	500 CYCLES
<b>Min</b>	0.14	0.12	0.12	0.12	0.12
<b>Max</b>	0.19	0.17	0.17	0.17	0.17
<b>Avg</b>	0.16	0.14	0.14	0.14	0.14



**VOLTAGE DROP DATA  
ALL CONTACTS ENERGIZED  
(MV)**

	INITIAL	50 CYCLES	100 CYCLES	200 CYCLES	500 CYCLES
Min	7.3	6.66	6.59	6.49	6.37
Max	10.01	9.1	9.05	8.97	8.9
Avg	8.41	7.51	7.44	7.37	7.29



**EQUIPMENT AND CALIBRATION SCHEDULES**

**Equipment #:** MO-04  
**Description:** Model 2700 Multimeter/Switch System (Integra Series)  
**Manufacturer:** Keithly  
**Model:** 2700  
**Serial #:** 0798688  
**Accuracy:** See Manual  
... Last Cal:3/27/2012, Next Cal: 3/27/2013

**Equipment #:** MO-09  
**Description:** Model 2750 Multimeter/Switch System (Integra Series)  
**Manufacturer:** Keithly  
**Model:** 2750  
**Serial #:** WDC-874817  
**Accuracy:** See Manual  
... Last Cal: 10/01/2012, Next Cal: 10/01/2013

**Equipment #:** PS-06  
**Description:** 60V 50 A DC Power Supply-AutoRanging SO  
**Manufacturer:** Hewlett Packard/Agilent  
**Model:** HP 6032A  
**Serial #:** US35420827  
**Accuracy:** See Manual

**Equipment #:** PS-09  
**Description:** 60V 50 A DC Power Supply-AutoRanging SO  
**Manufacturer:** Hewlett Packard/Agilent  
**Model:** HP 6032A  
**Serial #:** US38322853  
**Accuracy:** See Manual

**Equipment #:** PS-10  
**Description:** 60V 50 A DC Power Supply-AutoRanging SO  
**Manufacturer:** Hewlett Packard/Agilent  
**Model:** AT-6032A  
**Serial #:** 3440A10457  
**Accuracy:** See Manual

**Equipment #:** RS-01  
**Description:** Shunt  
**Manufacturer:** EMPRO  
**Model:** HA5050  
**Serial #:** HA5050  
**Accuracy:**  $\pm 0.25\%$  RDG  
... Last Cal: 5/30/2012 Next Cal: 5/30/2013



**POWER INTEGRITY TEST  
REPORT**

**227578**

**Revision 2**

**Equipment #:** RS-02  
**Description:** Shunt  
**Manufacturer:** EMPRO  
**Model:** HA5050  
**Serial #:** HA5050  
**Accuracy:**  $\pm 0.25\%$  RDG  
... Last Cal: 5/30/2012, Next Cal: 5/30/2013

**Equipment #:** RS-11  
**Description:** Shunt  
**Manufacturer:** Vishay  
**Model:** VCS202  
**Serial #:** VCS202  
**Accuracy:**  $\pm 0.25\%$  RDG  
... Last Cal: 2/01/2012, Next Cal: 2/01/2013

**Equipment #:** TC111307-(TCS-005-048)  
**Description:** Calibrated Thermocouples  
**Manufacturer:** Samtec, Inc.  
**Model:**  
**Serial #:**  
**Accuracy:**  
... Last Cal: 5/16/2012, Next Cal: 5/16/2013