




Project Number: Direct Liquid Cooling Qualification Test Report	Tracking Code: 2356820_Report_Rev_1
Requested by: Donnie Baldwin	Date: 2/22/2022
Part #: SFM-150-02-L-D/TFM-150-02-L-D	
Part description: SFM/TFM	Tech: Tony Wagoner
Test Start: 6/1/2020	Test Completed: 9/2/2020



**DIRECT LIQUID COOLING QUALIFICATION TEST REPORT**  
**SFM/TFM**  
**SFM-150-02-L-D/TFM-150-02-L-D**

Tracking Code: 2356820_Report_Rev_1	Part #: SFM-150-02-L-D/TFM-150-02-L-D
Part description: SFM/TFM	

## REVISION HISTORY

DATA	REV.NUM.	DESCRIPTION	ENG
2/22/2022	1	Initial Issue	KH

## CERTIFICATION

All instruments and measuring equipment were calibrated to National Institute for Standards and Technology (NIST) traceable standards according to ISO 10012-1 and ANSI/NCSL 2540-1, as applicable.

All contents contained herein are the property of Samtec. No portion of this report, in part or in full shall be reproduced without prior written approval of Samtec.

## SCOPE

To perform the following tests: Direct Liquid Cooling Qualification test. Please see test plan.

## APPLICABLE DOCUMENTS

Standards: EIA Publication 364

## TEST SAMPLES AND PREPARATION

- 1) All materials were manufactured in accordance with the applicable product specification.
- 2) All test samples were identified and encoded to maintain traceability throughout the test sequences.
- 3) After soldering, the parts to be used for LLCr and DWV/IR testing were cleaned according to CO-SC-WI-3029.
- 4) Either an automated cleaning procedure or an ultrasonic cleaning procedure may be used.
- 5) The automated procedure is used with aqueous compatible soldering materials.
- 6) Parts not intended for testing LLCr, and DWV/IR are visually inspected and cleaned if necessary.
- 7) Any additional preparation will be noted in the individual test sequences.
- 8) Solder Information: Lead Free
- 9) Samtec Test PCBs used: PCB-110757-TST/ PCB-110758-TST

## FLOWCHARTS

### Mating/Unmating/Durability

Group 1		Group 2		Group 3	
SFM-150-02-L-D		SFM-150-02-L-D		SFM-150-02-L-D	
TFM-150-02-L-D		TFM-150-02-L-D		TFM-150-02-L-D	
8 Assemblies		8 Assemblies		8 Assemblies	
Control In Air		ElectroCool EC-130		3M Fluorinert FC-43	
Step	Description	Step	Description	Step	Description
1.	Contact Gaps	1.	LLCR <sup>(2)</sup>	1.	LLCR <sup>(2)</sup>
2.	LLCR <sup>(2)</sup>	2.	Mating/Unmating Force <sup>(3)</sup>	2.	Mating/Unmating Force <sup>(3)</sup>
3.	Mating/Unmating Force <sup>(3)</sup>	3.	Cycles	3.	Cycles
4.	Cycles	Quantity = 50 Cycles	4.	Mating/Unmating Force <sup>(3)</sup>	Quantity = 50 Cycles
5.	Mating/Unmating Force <sup>(3)</sup>	5.	LLCR <sup>(2)</sup>	5.	LLCR <sup>(2)</sup>
6.	Cycles	Max Delta = 15 mOhm	6.	Fluid Exposure	Max Delta = 15 mOhm
Quantity = 25 Cycles					
7.	Mating/Unmating Force <sup>(3)</sup>	7.	LLCR <sup>(2)</sup>	7.	LLCR <sup>(2)</sup>
8.	Cycles	Max Delta = 15 mOhm	8.	Thermal Age <sup>(4)</sup>	Max Delta = 15 mOhm
Quantity = 25 Cycles					
9.	Mating/Unmating Force <sup>(3)</sup>	9.	LLCR <sup>(2)</sup>	9.	LLCR <sup>(2)</sup>
10.	Cycles	Max Delta = 15 mOhm	10.	Remove Samples From Fluid	Max Delta = 15 mOhm
Quantity = 25 Cycles					
11.	Mating/Unmating Force <sup>(3)</sup>	11.	LLCR <sup>(2)</sup>	11.	LLCR <sup>(2)</sup>
12.	Contact Gaps	Max Delta = 15 mOhm	12.	Mating/Unmating Force <sup>(3)</sup>	Max Delta = 15 mOhm
13.	LLCR <sup>(2)</sup>	13.	Cycles	13.	Cycles
Max Delta = 15 mOhm		Quantity = 50 Cycles	14.	Mating/Unmating Force <sup>(3)</sup>	Quantity = 50 Cycles
14.	Thermal Shock <sup>(5)</sup>	14.	Mating/Unmating Force <sup>(3)</sup>	14.	Mating/Unmating Force <sup>(3)</sup>
15.	LLCR <sup>(2)</sup>	15.	LLCR <sup>(2)</sup>	15.	LLCR <sup>(2)</sup>
Max Delta = 15 mOhm		Max Delta = 15 mOhm		Max Delta = 15 mOhm	
16.	Humidity <sup>(1)</sup>				
17.	LLCR <sup>(2)</sup>				
Max Delta = 15 mOhm					
18.	Mating/Unmating Force <sup>(3)</sup>				

(1) Humidity = EIA-364-31

Test Condition = B (240 Hours)

Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)

Test Exceptions: ambient pre-condition and delete steps 7a and 7b

(2) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(3) Mating/Unmating Force = EIA-364-13

(4) Thermal Age = EIA-364-17

Test Condition = 4 (105°C)

Time Condition = B (250 Hours)

(5) Thermal Shock = EIA-364-32

Exposure Time at Temperature Extremes = 1/2 Hour

Method A, Test Condition = I (-55°C to +85°C)

Test Duration = A-3 (100 Cycles)

**FLOWCHARTS Continued****IR/DWV****Pin-to-Pin**

Group 1  
SFM-150-02-L-D  
TFM-150-02-L-D  
2 Assemblies  
Control In Air

- | Step | Description       |
|------|-------------------|
| 1.   | DWV Breakdown (2) |

Group 2  
SFM-150-02-L-D  
TFM-150-02-L-D  
2 Assemblies  
Control In Air

- | Step | Description       |
|------|-------------------|
| 1.   | DWV Breakdown (2) |

Group 3  
TFM-150-02-L-D  
2 Assemblies  
Control In Air

- | Step | Description       |
|------|-------------------|
| 1.   | DWV Breakdown (2) |

Group 4  
SFM-150-02-L-D  
TFM-150-02-L-D  
2 Assemblies  
Control In Air

- | Step | Description             |
|------|-------------------------|
| 1.   | IR (4)                  |
| 2.   | DWV at Test Voltage (1) |
| 3.   | Thermal Shock (6)       |
| 4.   | IR (4)                  |
| 5.   | DWV at Test Voltage (1) |
| 6.   | Humidity (3)            |
| 7.   | IR (4)                  |
| 8.   | DWV at Test Voltage (1) |

Group 5  
SFM-150-02-L-D  
TFM-150-02-L-D  
2 Assemblies  
ElectroCool EC-130

- | Step | Description   |
|------|---|
| 1.   | Fluid Exposure<br><i>Note: Place parts in container with ElectroCool EC-130 fluid. Allow samples to soak for 30 minutes before proceeding to next step.</i> |
| 2.   | DWV Breakdown (2)   |

Group 6  
SFM-150-02-L-D  
TFM-150-02-L-D  
2 Assemblies  
ElectroCool EC-130

- | Step | Description   |
|------|---|
| 1.   | Fluid Exposure<br><i>Note: Place parts in container with ElectroCool EC-130 fluid. Allow samples to soak for 30 minutes before proceeding to next step.</i> |
| 2.   | DWV Breakdown (2)   |

Group 7  
TFM-150-02-L-D  
2 Assemblies  
ElectroCool EC-130

- | Step | Description   |
|------|---|
| 1.   | Fluid Exposure<br><i>Note: Place parts in container with ElectroCool EC-130 fluid. Allow samples to soak for 30 minutes before proceeding to next step.</i> |
| 2.   | DWV Breakdown (2)   |

Group 8  
SFM-150-02-L-D  
TFM-150-02-L-D  
2 Assemblies  
ElectroCool EC-130

- | Step | Description   |
|------|---|
| 1.   | Fluid Exposure<br><i>Note: Place parts in container with ElectroCool EC-130 fluid. Allow samples to soak for 30 minutes before proceeding to next step.</i> |
| 2.   | IR (4)<br><i>Note: Run while in ElectroCool EC-130 fluid.</i>   |
| 3.   | DWV at Test Voltage (1)<br><i>Note: Run while in ElectroCool EC-130 fluid.</i>  |
| 4.   | Thermal Age (5)<br>Temperature = 50°C<br>Time = 250 hrs   |
| 5.   | IR (4)<br><i>Note: Run while in ElectroCool EC-130 fluid after returning to Room Temp.</i>  |
| 6.   | DWV at Test Voltage (1)<br><i>Note: Run while in ElectroCool EC-130 fluid after returning to Room Temp.</i>   |

## FLOWCHARTS Continued

**Row-to-Row**

<u>Group 9</u> SFM-150-02-L-D TFM-150-02-L-D 2 Assemblies Control In Air	<u>Group 10</u> SFM-150-02-L-D TFM-150-02-L-D 2 Assemblies Control In Air	<u>Group 11</u> TFM-150-02-L-D 2 Assemblies Control In Air	<u>Group 12</u> SFM-150-02-L-D TFM-150-02-L-D 2 Assemblies Control In Air
<b>Step Description</b> 1. DWV Breakdown <sup>(2)</sup>	<b>Step Description</b> 1. DWV Breakdown <sup>(2)</sup>	<b>Step Description</b> 1. DWV Breakdown <sup>(2)</sup>	<b>Step Description</b> 1. IR <sup>(4)</sup> 2. DWV at Test Voltage <sup>(1)</sup> 3. Thermal Shock <sup>(6)</sup> 4. IR <sup>(4)</sup> 5. DWV at Test Voltage <sup>(1)</sup> 6. Humidity <sup>(3)</sup> 7. IR <sup>(4)</sup> 8. DWV at Test Voltage <sup>(1)</sup>
<u>Group 13</u> SFM-150-02-L-D TFM-150-02-L-D 2 Assemblies ElectroCool EC-130	<u>Group 14</u> SFM-150-02-L-D TFM-150-02-L-D 2 Assemblies ElectroCool EC-130	<u>Group 15</u> TFM-150-02-L-D 2 Assemblies ElectroCool EC-130	<u>Group 16</u> SFM-150-02-L-D TFM-150-02-L-D 2 Assemblies ElectroCool EC-130
<b>Step Description</b> 1. Fluid Exposure <i>Note: Place parts in container with ElectroCool EC-130 fluid. Allow samples to soak for 30 minutes before proceeding to next step.</i> 2. DWV Breakdown <sup>(2)</sup>	<b>Step Description</b> 1. Fluid Exposure <i>Note: Place parts in container with ElectroCool EC-130 fluid. Allow samples to soak for 30 minutes before proceeding to next step.</i> 2. DWV Breakdown <sup>(2)</sup>	<b>Step Description</b> 1. Fluid Exposure <i>Note: Place parts in container with ElectroCool EC-130 fluid. Allow samples to soak for 30 minutes before proceeding to next step.</i> 2. DWV Breakdown <sup>(2)</sup>	<b>Step Description</b> 1. Fluid Exposure <i>Note: Place parts in container with ElectroCool EC-130 fluid. Allow samples to soak for 30 minutes before proceeding to next step.</i> 2. IR <sup>(4)</sup> <i>Note: Run while in ElectroCool EC-130 fluid.</i> 3. DWV at Test Voltage <sup>(1)</sup> <i>Note: Run while in ElectroCool EC-130 fluid.</i> 4. Thermal Age <sup>(5)</sup> Temperature = 50°C Time = 250 hrs 5. IR <sup>(4)</sup> <i>Note: Run while in ElectroCool EC-130 fluid after returning to Room Temp.</i> 6. DWV at Test Voltage <sup>(1)</sup> <i>Note: Run while in ElectroCool EC-130 fluid after returning to Room Temp.</i>

(1) DWV at Test Voltage = EIA-364-20

Test Condition = 1 (Sea Level)

DWV test voltage is equal to 75% of the lowest breakdown voltage

Test voltage applied for 60 seconds

(2) DWV Breakdown = EIA-364-20

Test Condition = 1 (Sea Level)

DWV test voltage is equal to 75% of the lowest breakdown voltage

Test voltage applied for 60 seconds

(3) Humidity = EIA-364-31

Test Condition = B (240 Hours)

Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)

Test Exceptions: ambient pre-condition and delete steps 7a and 7b

(4) IR = EIA-364-21

Test Condition = 500 Vdc, 2 Minutes Max

(5) Thermal Age = EIA-364-17

Test Condition = 4 (105°C)

Time Condition = B (250 Hours)

(6) Thermal Shock = EIA-364-32

Exposure Time at Temperature Extremes = 1/2 Hour

Method A, Test Condition = I (-55°C to +85°C)

Test Duration = A-3 (100 Cycles)

## FLOWCHARTS Continued

### Current Carrying Capacity

#### Control In Air

Group 1		Group 2		Group 3		Group 4	
SFM-150-02-L-D		SFM-150-02-L-D		SFM-150-02-L-D		SFM-150-02-L-D	
TFM-150-02-L-D		TFM-150-02-L-D		TFM-150-02-L-D		TFM-150-02-L-D	
2 Pins Powered		4 Pins Powered		6 Pins Powered		8 Pins Powered	
Signal		Signal		Signal		Signal	
Step	Description	Step	Description	Step	Description	Step	Description
1.	CCC <sup>(1)</sup> Rows = 2 Number of Positions = 1	1.	CCC <sup>(1)</sup> Rows = 2 Number of Positions = 2	1.	CCC <sup>(1)</sup> Rows = 2 Number of Positions = 3	1.	CCC <sup>(1)</sup> Rows = 2 Number of Positions = 4

Group 5	
SFM-150-02-L-D	
TFM-150-02-L-D	
50 Pins Powered	
Signal	
Step	Description
1.	CCC <sup>(1)</sup> Rows = 2 Number of Positions = 25

#### ElectroCool EC-130

Group 6		Group 7		Group 8		Group 9	
SFM-150-02-L-D		SFM-150-02-L-D		SFM-150-02-L-D		SFM-150-02-L-D	
TFM-150-02-L-D		TFM-150-02-L-D		TFM-150-02-L-D		TFM-150-02-L-D	
2 Pins Powered		4 Pins Powered		6 Pins Powered		8 Pins Powered	
Signal		Signal		Signal		Signal	
Step	Description	Step	Description	Step	Description	Step	Description
1.	Fluid Exposure <i>Note: Place parts in container with ElectroCool EC-130 fluid. Start circulation system and allow temp to stabilize. Allow samples to soak for 30 minutes before proceeding to next step.</i>	1.	Fluid Exposure <i>Note: Place parts in container with ElectroCool EC-130 fluid. Start circulation system and allow temp to stabilize. Allow samples to soak for 30 minutes before proceeding to next step.</i>	1.	Fluid Exposure <i>Note: Place parts in container with ElectroCool EC-130 fluid. Start circulation system and allow temp to stabilize. Allow samples to soak for 30 minutes before proceeding to next step.</i>	1.	Fluid Exposure <i>Note: Place parts in container with ElectroCool EC-130 fluid. Start circulation system and allow temp to stabilize. Allow samples to soak for 30 minutes before proceeding to next step.</i>
2.	CCC <sup>(1)</sup> Rows = 2 Number of Positions = 1 <i>Note: Run while in ElectroCool EC-130 fluid.</i>	2.	CCC <sup>(1)</sup> Rows = 2 Number of Positions = 2 <i>Note: Run while in ElectroCool EC-130 fluid.</i>	2.	CCC <sup>(1)</sup> Rows = 2 Number of Positions = 3 <i>Note: Run while in ElectroCool EC-130 fluid.</i>	2.	CCC <sup>(1)</sup> Rows = 2 Number of Positions = 4 <i>Note: Run while in ElectroCool EC-130 fluid.</i>

Group 10	
SFM-150-02-L-D	
TFM-150-02-L-D	
50 Pins Powered	
Signal	
Step	Description
1.	Fluid Exposure <i>Note: Place parts in container with ElectroCool EC-130 fluid. Start circulation system and allow temp to stabilize. Allow samples to soak for 30 minutes before proceeding to next step.</i>
2.	CCC <sup>(1)</sup> Rows = 2 Number of Positions = 25 <i>Note: Run while in ElectroCool EC-130 fluid.</i>

(1) CCC - All Power = EIA-364-70

Method 2, Temperature Rise Versus Current Curve

(TIN PLATING) - Tabulate calculated current at RT, 65°C, 75°C and 95°C after derating 20% and based on 105°C

(GOLD PLATING) - Tabulate calculated current at RT, 85°C, 95°C and 115°C after derating 20% and based on 125°C

(2) CCC = EIA-364-70

Method 2, Temperature Rise Versus Current Curve

(TIN PLATING) - Tabulate calculated current at RT, 65°C, 75°C and 95°C after derating 20% and based on 105°C

(GOLD PLATING) - Tabulate calculated current at RT, 85°C, 95°C and 115°C after derating 20% and based on 125°C

## ATTRIBUTE DEFINITIONS

The following is a brief, simplified description of attributes.

### THERMAL:

- 1) EIA-364-17, *Temperature Life with or without Electrical Load Test Procedure for Electrical Connectors*.
- 2) Test Condition at 105° C.
- 3) Test Time Condition B for 250 hours.
- 4) All test samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

### THERMAL SHOCK:

- 1) EIA-364-32, *Thermal Shock (Temperature Cycling) Test Procedure for Electrical Connectors*.
- 2) Test Condition: -55°C to +85°C
- 3) Test Time: ½ hour dwell at each temperature extreme
- 4) Number of Cycles: 100
- 5) All test samples are pre-conditioned at ambient.
- 6) All test samples are exposed to environmental stressing in the mated condition.

### HUMIDITY:

- 1) Reference document: EIA-364-31, *Humidity Test Procedure for Electrical Connectors*.
- 2) Test Condition B, 240 Hours.
- 3) Method III, +25° C to + 65° C, 90% to 98% Relative Humidity excluding sub-cycles 7a and 7b.
- 4) All samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

### MATING/UNMATING:

- 1) Reference document: EIA-364-13, *Mating and Unmating Forces Test Procedure for Electrical Connectors*.
- 2) The full insertion position was to within 0.003” to 0.004” of the plug bottoming out in the receptacle to prevent damage to the system under test.
- 3) One of the mating parts is secured to a floating X-Y table to prevent damage during cycling.



**ATTRIBUTE DEFINITIONS Continued**

The following is a brief, simplified description of attributes

**TEMPERATURE RISE (Current Carrying Capacity, CCC):**

- 1) EIA-364-70, *Temperature Rise versus Current Test Procedure for Electrical Connectors and Sockets*.
- 2) When current passes through a contact, the temperature of the contact increases as a result of  $I^2R$  (resistive) heating.
- 3) The number of contacts being investigated plays a significant part in power dissipation and therefore temperature rise.
- 4) The size of the temperature probe can affect the measured temperature.
- 5) Copper traces on PC boards will contribute to temperature rise:
  - a. Self heating (resistive)
  - b. Reduction in heat sink capacity affecting the heated contacts
- 6) A de-rating curve, usually 20%, is calculated.
- 7) Calculated de-rated currents at four temperature points are reported:
  - a. Ambient
  - b. 85° C
  - c. 95° C
  - d. 115° C
- 8) Typically, neighboring contacts (in close proximity to maximize heat build up) are energized.
- 9) The thermocouple (or temperature measuring probe) will be positioned at a location to sense the maximum temperature in the vicinity of the heat generation area.
- 10) A computer program, *TR 803.exe*, ensures accurate stability for data acquisition.
- 11) Hook-up wire cross section is larger than the cross section of any connector leads/PC board traces, jumpers, etc.
- 12) Hook-up wire length is longer than the minimum specified in the referencing standard.

**LLCR:**

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
  - a.  $\leq +5.0$  mOhms: -----Stable
  - b.  $+5.1$  to  $+10.0$  mOhms: -----Minor
  - c.  $+10.1$  to  $+15.0$  mOhms: -----Acceptable
  - d.  $+15.1$  to  $+50.0$  mOhms: -----Marginal
  - e.  $+50.1$  to  $+1000$  mOhms: -----Unstable
  - f.  $>+1000$  mOhms: -----Open Failure

**ATTRIBUTE DEFINITIONS Continued**

The following is a brief, simplified description of attributes

**INSULATION RESISTANCE (IR):**

To determine the resistance of insulation materials to leakage of current through or on the surface of these materials when a DC potential is applied.

- 1) PROCEDURE:
  - a. Reference document: EIA-364-21, *Insulation Resistance Test Procedure for Electrical Connectors*.
  - b. Test Conditions:
    - i. Between Adjacent Contacts or Signal-to-Ground
    - ii. Electrification Time 2.0 minutes
    - iii. Test Voltage (500 VDC) corresponds to calibration settings for measuring resistances.
- 2) MEASUREMENTS:
- 3) When the specified test voltage is applied (VDC), the insulation resistance shall not be less than 5000 megohms.

**DIELECTRIC WITHSTANDING VOLTAGE (DWV):**

To determine if the sockets can operate at its rated voltage and withstand momentary over potentials due to switching, surges, and other similar phenomenon. Separate samples are used to evaluate the effect of environmental stresses so not to influence the readings from arcing that occurs during the measurement process.

- 1) PROCEDURE:
  - a. Reference document: EIA-364-20, *Withstanding Voltage Test Procedure for Electrical Connectors*.
  - b. Test Conditions:
    - i. Between Adjacent Contacts or Signal-to-Ground
    - ii. Barometric Test Condition 1
    - iii. Rate of Application 500 V/Sec
    - iv. Test Voltage (VAC) until breakdown occurs
- 2) MEASUREMENTS/CALCULATIONS
  - a. The breakdown voltage shall be measured and recorded.
  - b. The dielectric withstanding voltage shall be recorded as 75% of the minimum breakdown voltage.
  - c. The working voltage shall be recorded as one-third (1/3) of the dielectric withstanding voltage (one-fourth of the breakdown voltage).

## RESULTS

### Temperature Rise, CCC at a 20% de-rating

#### Control In Air

- CCC for a 30°C Temperature Rise-----3.3 A per contact with 2 contacts (2x1) powered.
- CCC for a 30°C Temperature Rise-----2.8 A per contact with 4 contacts (2x2) powered.
- CCC for a 30°C Temperature Rise-----2.3 A per contact with 6 contacts (2x3) powered.
- CCC for a 30°C Temperature Rise-----2.1 A per contact with 8 contacts (2x4) powered.
- CCC for a 30°C Temperature Rise-----1.1 A per contact with 50 contacts (2x25) powered.

#### ElectroCool EC-130

- CCC for a 30°C Temperature Rise-----6.8 A per contact with 2 contacts (2x1) powered.
- CCC for a 30°C Temperature Rise-----5.9 A per contact with 4 contacts (2x2) powered.
- CCC for a 30°C Temperature Rise-----5.3 A per contact with 6 contacts (2x3) powered.
- CCC for a 30°C Temperature Rise-----4.9 A per contact with 8 contacts (2x4) powered.
- CCC for a 30°C Temperature Rise-----4.4 A per contact with 50 contacts (2x25) powered.

**RESULTS Continued****Mating – Unmating Forces****Mating/Unmating Durability Group****Control In Air**

- **Initial**
  - **Mating**
    - **Min** -----14.40 lbs
    - **Max** -----17.65 lbs
  - **Unmating**
    - **Min** -----10.82 lbs
    - **Max** -----15.78 lbs
- **After 25 Cycles**
  - **Mating**
    - **Min** -----18.22 lbs
    - **Max** -----22.27 lbs
  - **Unmating**
    - **Min** -----16.02 lbs
    - **Max** -----19.72 lbs
- **After 50 Cycles**
  - **Mating**
    - **Min** -----20.42 lbs
    - **Max** -----25.14 lbs
  - **Unmating**
    - **Min** -----18.20 lbs
    - **Max** -----22.09 lbs
- **After 75 Cycles**
  - **Mating**
    - **Min** -----22.52 lbs
    - **Max** -----26.75 lbs
  - **Unmating**
    - **Min** -----18.75 lbs
    - **Max** -----24.80 lbs
- **After 100 Cycles**
  - **Mating**
    - **Min** -----23.82 lbs
    - **Max** -----27.85 lbs
  - **Unmating**
    - **Min** -----19.27 lbs
    - **Max** -----26.87 lbs
- **After Humidity**
  - **Mating**
    - **Min** -----20.72 lbs
    - **Max** -----23.96 lbs
  - **Unmating**
    - **Min** -----20.34 lbs
    - **Max** -----22.86 lbs

**RESULTS Continued****ElectroCool EC-130**

- **Initial**
  - **Mating**
    - **Min** -----19.67 lbs
    - **Max** -----22.31 lbs
  - **Unmating**
    - **Min** -----17.60 lbs
    - **Max** -----21.32 lbs
- **After 50 Cycles**
  - **Mating**
    - **Min** -----25.29 lbs
    - **Max** -----28.68 lbs
  - **Unmating**
    - **Min** -----21.66 lbs
    - **Max** -----24.92 lbs
- **After Thermal**
  - **Mating**
    - **Min** -----11.65 lbs
    - **Max** -----14.48 lbs
  - **Unmating**
    - **Min** ----- 9.41 lbs
    - **Max** -----10.86 lbs
- **After 50 Cycles**
  - **Mating**
    - **Min** -----14.69 lbs
    - **Max** -----18.76 lbs
  - **Unmating**
    - **Min** -----12.81 lbs
    - **Max** -----15.09 lbs

**RESULTS Continued****3M Fluorinert FC-43**

- **Initial**
  - **Mating**
    - **Min** -----19.69 lbs
    - **Max** -----22.45 lbs
  - **Unmating**
    - **Min** -----18.46 lbs
    - **Max** -----19.86 lbs
- **After 50 Cycles**
  - **Mating**
    - **Min** -----24.47 lbs
    - **Max** -----27.71 lbs
  - **Unmating**
    - **Min** -----22.65 lbs
    - **Max** -----25.03 lbs
- **After Thermal**
  - **Mating**
    - **Min** -----15.76 lbs
    - **Max** -----24.49 lbs
  - **Unmating**
    - **Min** -----10.34 lbs
    - **Max** -----16.52 lbs
- **After 50 Cycles**
  - **Mating**
    - **Min** -----26.22 lbs
    - **Max** -----32.33 lbs
  - **Unmating**
    - **Min** -----17.62 lbs
    - **Max** -----23.01 lbs

**RESULTS Continued****Insulation Resistance minimums, IR****Control In Air****Pin to Pin**

- **Initial**
  - Mated -----45000 Meg  $\Omega$  ----- Passed
  - Unmated -----45000 Meg  $\Omega$  ----- Passed
- **Thermal Shock**
  - Mated -----45000 Meg  $\Omega$  ----- Passed
  - Unmated -----45000 Meg  $\Omega$  ----- Passed
- **Humidity**
  - Mated -----45000 Meg  $\Omega$  ----- Passed
  - Unmated -----45000 Meg  $\Omega$  ----- Passed

**Row to Row**

- **Initial**
  - Mated -----45000 Meg  $\Omega$  ----- Passed
  - Unmated -----45000 Meg  $\Omega$  ----- Passed
- **Thermal Shock**
  - Mated -----45000 Meg  $\Omega$  ----- Passed
  - Unmated -----45000 Meg  $\Omega$  ----- Passed
- **Humidity**
  - Mated -----45000 Meg  $\Omega$  ----- Passed
  - Unmated -----45000 Meg  $\Omega$  ----- Passed

**ElectroCool EC-130****Pin to Pin**

- **Initial**
  - Mated -----45000 Meg  $\Omega$  ----- Passed
  - Unmated -----45000 Meg  $\Omega$  ----- Passed
- **Thermal Aging**
  - Mated -----45000 Meg  $\Omega$  ----- Passed
  - Unmated -----45000 Meg  $\Omega$  ----- Passed

**Row to Row**

- **Initial**
  - Mated -----45000 Meg  $\Omega$  ----- Passed
  - Unmated -----45000 Meg  $\Omega$  ----- Passed
- **Thermal Aging**
  - Mated -----45000 Meg  $\Omega$  ----- Passed
  - Unmated -----45000 Meg  $\Omega$  ----- Passed

**RESULTS Continued**

**Dielectric Withstanding Voltage minimums, DWV**

**Control In Air**

- **Minimums**
  - Breakdown Voltage----- 1018 VAC
  - Test Voltage -----765 VAC
  - Working Voltage -----255 VAC

**Pin to Pin**

- Initial DWV -----Passed
- Thermal DWV-----Passed
- Humidity DWV-----Passed

**Row to Row**

- Initial DWV -----Passed
- Thermal DWV-----Passed
- Humidity DWV-----Passed

**ElectroCool EC-130**

- **Minimums**
  - Breakdown Voltage----- 5000 VAC
  - Test Voltage ----- 3750 VAC
  - Working Voltage ----- 1250 VAC

**Pin to Pin**

- Initial DWV -----Passed
- Thermal DWV -----Passed

**Row to Row**

- Initial DWV -----Passed
- Thermal DWV -----Passed



**RESULTS Continued****LLCR Durability (192 LLCR test points)****Control In Air**

- **Initial** -----7.80 mOhms Max
- **Durability, 100 Cycles**
  - **<= +5.0 mOhms**-----192 Points ----- Stable
  - **+5.1 to +10.0 mOhms** -----0 Points ----- Minor
  - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
  - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
  - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
  - **>+1000 mOhms**-----0 Points ----- Open Failure
- **Thermal**
  - **<= +5.0 mOhms**-----192 Points ----- Stable
  - **+5.1 to +10.0 mOhms** -----0 Points ----- Minor
  - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
  - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
  - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
  - **>+1000 mOhms**-----0 Points ----- Open Failure
- **Humidity**
  - **<= +5.0 mOhms**-----192 Points ----- Stable
  - **+5.1 to +10.0 mOhms** -----0 Points ----- Minor
  - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
  - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
  - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
  - **>+1000 mOhms**-----0 Points ----- Open Failure

**RESULTS Continued****ElectroCool EC-130**

- **Initial -----8.00 mOhms Max**
- **Durability, 50 Cycles**
  - <= +5.0 mOhms -----192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +1000 mOhms -----0 Points ----- Unstable
  - >+1000 mOhms -----0 Points ----- Open Failure
- **Fluid Exposure**
  - <= +5.0 mOhms -----192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +1000 mOhms -----0 Points ----- Unstable
  - >+1000 mOhms -----0 Points ----- Open Failure
- **Thermal**
  - <= +5.0 mOhms -----192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +1000 mOhms -----0 Points ----- Unstable
  - >+1000 mOhms -----0 Points ----- Open Failure
- **Remove Samples from Fluid**
  - <= +5.0 mOhms -----192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +1000 mOhms -----0 Points ----- Unstable
  - >+1000 mOhms -----0 Points ----- Open Failure
- **Durability, 50 Cycles**
  - <= +5.0 mOhms -----192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +1000 mOhms -----0 Points ----- Unstable
  - >+1000 mOhms -----0 Points ----- Open Failure

**RESULTS Continued****3M Fluorinert FC-43**


- **Initial -----8.33 mOhms Max**
- **Durability, 50 Cycles**
  - <= +5.0 mOhms -----192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +1000 mOhms -----0 Points ----- Unstable
  - >+1000 mOhms -----0 Points ----- Open Failure
- **Fluid Exposure**
  - <= +5.0 mOhms -----192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +1000 mOhms -----0 Points ----- Unstable
  - >+1000 mOhms -----0 Points ----- Open Failure
- **Thermal**
  - <= +5.0 mOhms -----192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +1000 mOhms -----0 Points ----- Unstable
  - >+1000 mOhms -----0 Points ----- Open Failure
- **Remove Samples from Fluid**
  - <= +5.0 mOhms -----192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +1000 mOhms -----0 Points ----- Unstable
  - >+1000 mOhms -----0 Points ----- Open Failure
- **Durability, 50 Cycles**
  - <= +5.0 mOhms -----192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +1000 mOhms -----0 Points ----- Unstable
  - >+1000 mOhms -----0 Points ----- Open Failure


**DATA SUMMARIES****TEMPERATURE RISE (Current Carrying Capacity, CCC):**

- 1) High quality thermocouples whose temperature slopes track one another were used for temperature monitoring.
- 2) The thermocouples were placed at a location to sense the maximum temperature generated during testing.
- 3) Temperature readings recorded are those for which three successive readings, 15 minutes apart, differ less than 1° C (computer-controlled data acquisition).
- 4) Adjacent contacts were powered:

**Control in Air**



a. Linear configuration with 2 adjacent conductors/contacts powered





**DATA SUMMARIES Continued****b. Linear configuration with 4 adjacent conductors/contacts powered**


2356820  
4 (2x2) Contacts in Series - Control (Air)  
Part Numbers: SFM-150-02-L-D / TFM-150-02-L-D




**DATA SUMMARIES Continued**

## c. Linear configuration with 6 adjacent conductors/contacts powered

2356820  
6 (2x3) Contacts in Series - Control (Air)  
Part Numbers: SFM-150-02-L-D / TFM-150-02-L-D




2356820  
6 (2x3) Contacts in Series - Control (Air)  
Part Numbers: SFM-150-02-L-D / TFM-150-02-L-D




**DATA SUMMARIES Continued****d. Linear configuration with 8 adjacent conductors/contacts powered**

2356820  
8 (2x4) Contacts in Series - Control (Air)  
Part Numbers: SFM-150-02-L-D / TFM-150-02-L-D



2356820  
8 (2x4) Contacts in Series - Control (Air)  
Part Numbers: SFM-150-02-L-D / TFM-150-02-L-D







**DATA SUMMARIES Continued**

## e. Linear configuration with 50 adjacent conductors/contacts powered

2356820


50 (2x25)(All Power) Contacts in Series - Control (Air)

Part Numbers: SFM-150-02-L-D / TFM-150-02-L-D


*Current Rating per Contact (30 Deg. Rise, 20% Derated) = 1.1 Amps*

**DATA SUMMARIES Continued****ElectroCool EC-130****f. Linear configuration with 2 adjacent conductors/contacts powered**

2356820  
2 (2x1) Contacts in Series - Immersion Cooling (EC-130)  
Part Numbers: SFM-150-02-L-D / TFM-150-02-L-D



2356820  
2 (2x1) Contacts in Series - Immersion Cooling (EC-130)  
Part Numbers: SFM-150-02-L-D / TFM-150-02-L-D




**DATA SUMMARIES Continued**

g. Linear configuration with 4 adjacent conductors/contacts powered

2356820

4 (2x2) Contacts in Series - Immersion Cooling (EC-130)


Part Numbers: SFM-150-02-L-D / TFM-150-02-L-D

*Current Rating per Contact (30 Deg. Rise, 20% Derated) = 5.9 Amps*

2356820

4 (2x2) Contacts in Series - Immersion Cooling (EC-130)

Part Numbers: SFM-150-02-L-D / TFM-150-02-L-D




**DATA SUMMARIES Continued****h. Linear configuration with 6 adjacent conductors/contacts powered**

2356820

6 (2x3) Contacts in Series - Immersion Cooling (EC-130)


Part Numbers: SFM-150-02-L-D / TFM-150-02-L-D



2356820

6 (2x3) Contacts in Series - Immersion Cooling (EC-130)

Part Numbers: SFM-150-02-L-D / TFM-150-02-L-D




**DATA SUMMARIES Continued**

## i. Linear configuration with 8 adjacent conductors/contacts powered

2356820

8 (2x4) Contacts in Series - Immersion Cooling (EC-130)


Part Numbers: SFM-150-02-L-D / TFM-150-02-L-D

*Current Rating per Contact (30 Deg. Rise, 20% Derated) = 4.9 Amps*

2356820

8 (2x4) Contacts in Series - Immersion Cooling (EC-130)


Part Numbers: SFM-150-02-L-D / TFM-150-02-L-D




**DATA SUMMARIES Continued**

j. Linear configuration with 50 adjacent conductors/contacts powered

2356820  
50 (2x25)(All Power) Contacts in Series - Immersion Cooling (EC-130)  
Part Numbers: SFM-150-02-L-D / TFM-150-02-L-D



2356820  
50 (2x25)(All Power) Contacts in Series - Immersion Cooling (EC-130)  
Part Numbers: SFM-150-02-L-D / TFM-150-02-L-D



**DATA SUMMARIES Continued****MATING/UNMATING:****Mating/Unmating Durability Group****Control In Air**

	Initial				25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)
Minimum	64.05	14.40	48.13	10.82	81.04	18.22	71.26	16.02
Maximum	78.51	17.65	70.19	15.78	99.06	22.27	87.71	19.72
<b>Average</b>	72.62	<b>16.33</b>	62.71	<b>14.10</b>	88.10	<b>19.81</b>	78.36	<b>17.62</b>
St Dev	4.29	0.96	7.32	1.65	6.24	1.40	5.57	1.25
Count	8	8	8	8	8	8	8	8
	50 Cycles				75 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)
Minimum	90.83	20.42	80.95	18.20	100.17	22.52	83.53	18.78
Maximum	111.82	25.14	98.26	22.09	118.98	26.75	110.31	24.80
<b>Average</b>	98.07	<b>22.05</b>	87.57	<b>19.69</b>	106.19	<b>23.87</b>	95.57	<b>21.49</b>
St Dev	6.89	1.55	5.84	1.31	6.61	1.49	8.32	1.87
Count	8	8	8	8	8	8	8	8
	100 Cycles				After Humidity			
	Mating		Unmating		Mating		Unmating	
	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)
Minimum	105.95	23.82	85.71	19.27	92.16	20.72	90.47	20.34
Maximum	123.88	27.85	119.52	26.87	106.57	23.96	101.68	22.86
<b>Average</b>	112.11	<b>25.21</b>	102.29	<b>23.00</b>	100.76	<b>22.65</b>	96.87	<b>21.78</b>
St Dev	7.25	1.63	10.27	2.31	4.20	0.94	3.49	0.78
Count	8	8	8	8	8	8	8	8

**DATA SUMMARIES Continued****ElectroCool EC-130**

	Initial				After 50 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)
Minimum	87.49	19.67	78.28	17.60	112.49	25.29	96.34	21.66
Maximum	99.23	22.31	94.83	21.32	127.57	28.68	110.84	24.92
<b>Average</b>	94.03	<b>21.14</b>	85.52	<b>19.23</b>	117.62	<b>26.44</b>	104.19	<b>23.42</b>
St Dev	3.68	0.83	5.06	1.14	5.24	1.18	4.90	1.10
Count	8	8	8	8	8	8	8	8
	After Thermals				50 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)
Minimum	51.82	11.65	41.86	9.41	65.34	14.69	56.98	12.81
Maximum	64.41	14.48	48.31	10.86	83.44	18.76	67.12	15.09
<b>Average</b>	56.38	<b>12.68</b>	45.90	<b>10.32</b>	72.36	<b>16.27</b>	62.82	<b>14.12</b>
St Dev	4.54	1.02	2.36	0.53	5.65	1.27	3.57	0.80
Count	8	8	8	8	8	8	8	8

**3M Fluorinert FC-43**

	Initial				After 50 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)
Minimum	87.58	19.69	82.11	18.46	108.84	24.47	100.75	22.65
Maximum	99.86	22.45	88.34	19.86	123.25	27.71	111.33	25.03
<b>Average</b>	92.75	<b>20.85</b>	84.84	<b>19.07</b>	115.23	<b>25.91</b>	104.78	<b>23.56</b>
St Dev	3.85	0.87	2.31	0.52	4.49	1.01	3.25	0.73
Count	8	8	8	8	8	8	8	8
	After Thermals				50 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)
Minimum	70.10	15.76	45.99	10.34	116.63	26.22	78.37	17.62
Maximum	108.93	24.49	73.48	16.52	143.80	32.33	102.35	23.01
<b>Average</b>	89.40	<b>20.10</b>	65.57	<b>14.74</b>	125.40	<b>28.19</b>	95.43	<b>21.46</b>
St Dev	12.20	2.74	9.02	2.03	11.55	2.60	7.87	1.77
Count	8	8	8	8	8	8	8	8



**DATA SUMMARIES Continued****INSULATION RESISTANCE (IR):****Control In Air**

	Pin to Pin		
	Mated	Unmated	Unmated
Minimum	SFM/TFM	SFM	TFM
Initial	45000	45000	45000
Thermal	45000	45000	45000
Humidity	45000	45000	45000

	Row to Row		
	Mated	Unmated	Unmated
Minimum	SFM/TFM	SFM	TFM
Initial	45000	45000	45000
Thermal	45000	45000	45000
Humidity	45000	45000	45000

**ElectroCool EC-130**

	Pin to Pin		
	Mated	Unmated	Unmated
Minimum	SFM/TFM	SFM	TFM
Initial	45000	45000	45000
Thermal	45000	45000	45000

	Row to Row		
	Mated	Unmated	Unmated
Minimum	SFM/TFM	SFM	TFM
Initial	45000	45000	45000
Thermal	45000	45000	45000

**DATA SUMMARIES Continued****DIELECTRIC WITHSTANDING VOLTAGE (DWV):****Control In Air**

Voltage Rating Summary	
Minimum	SFM/TFM
Break Down Voltage	1018
Test Voltage	765
Working Voltage	255

Pin to Pin	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed
After Humidity Test Voltage	Passed

Row to Row	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed
After Humidity Test Voltage	Passed

**ElectroCool EC-130**

Voltage Rating Summary	
Minimum	SFM/TFM
Break Down Voltage	5000
Test Voltage	3750
Working Voltage	1250

Pin to Pin	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed

Row to Row	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed

**DATA SUMMARIES Continued****LLCR Durability:**

- 1) A total of 192 points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
  - a.  $\leq +5.0$  mOhms: -----Stable
  - b.  $+5.1$  to  $+10.0$  mOhms: -----Minor
  - c.  $+10.1$  to  $+15.0$  mOhms: -----Acceptable
  - d.  $+15.1$  to  $+50.0$  mOhms: -----Marginal
  - e.  $+50.1$  to  $+1000$  mOhms: -----Unstable
  - f.  $>+1000$  mOhms: -----Open Failure

**Control In Air**

LLCR Measurement Summaries by Pin Type				
Date	2020/6/1	2020/6/9	2020/6/29	2020/7/9
Room Temp (Deg C)	22	22	22	22
Rel Humidity (%)	41	52	53	55
Technician	Tony Wagoner	Tony Wagoner	Tony Wagoner	Tony Wagoner
mOhm values	Actual	Delta	Delta	Delta
	Initial	Cycles	Therm Shck	Humidity
Pin Type: Signal 1				
Average	6.94	0.89	0.73	0.72
St. Dev.	0.29	0.77	0.7	0.77
Min	6.38	0.02	0	0
Max	7.8	3.28	2.73	3.09
Summary Count	192	192	192	192
Total Count	192	192	192	192

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
	$\leq 5.0$	$>5.1$ & $\leq 10.0$	$>10.1$ & $\leq 15.0$	$>15.1$ & $\leq 50.0$	$>50.1$ & $\leq 1000$	$>1000$
100 Cycles	192	0	0	0	0	0
Therm Shck	192	0	0	0	0	0
Humidity	192	0	0	0	0	0

**DATA SUMMARIES Continued****ElectroCool EC-130**

LLCR Measurement Summaries by Pin Type						
Date	2020/6/1	2020/7/7	2020/7/7	2020/7/21	2020/9/1	2020/9/2
Room Temp (Deg C)	23	22	22	23	23	22
Rel Humidity (%)	39	55	55	53	52	52
Technician	Tony Wagoner	Tony Wagoner	Tony Wagoner	Tony Wagoner	Tony Wagoner	Tony Wagoner
mOhm values	Actual	Delta	Delta	Delta	Delta	Delta
	Initial	50 Cycles	Fluid Exposure	Thermal Age	Ambient (Air Dried)	50 Cycles
Pin Type: Signal 1						
Average	6.91	0.66	0.65	0.86	0.97	0.92
St. Dev.	0.3	0.62	0.65	0.77	0.78	0.71
Min	6.26	0	0	0	0	0.01
Max	8	3.27	3.48	3.92	3.88	3.5
Summary Count	192	192	192	192	192	192
Total Count	192	192	192	192	192	192

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	<=5.0	>5.1 & <=10.0	>10.1 & <=15.0	>15.1 & <=50.0	>50.1 & <=1000	>1000
50 Cycles	192	0	0	0	0	0
Fluid Exposure	192	0	0	0	0	0
Thermals	192	0	0	0	0	0
Remove/Fluid	192	0	0	0	0	0
50 Cycles	192	0	0	0	0	0

**DATA SUMMARIES Continued****3M Fluorinert FC-43**

LLCR Measurement Summaries by Pin Type						
Date	2020/6/1	2020/7/7	2020/7/7	2020/7/21	2020/9/1	2020/9/2
Room Temp (Deg C)	23	22	22	23	23	22
Rel Humidity (%)	39	53	55	53	50	56
Technician	Tony Wagoner	Tony Wagoner	Tony Wagoner	Tony Wagoner	Tony Wagoner	Tony Wagoner
mOhm values	<b>Actual</b>	<b>Delta</b>	<b>Delta</b>	<b>Delta</b>	<b>Delta</b>	<b>Delta</b>
	<b>Initial</b>	<b>50 Cycles</b>	<b>Fluid Exposure</b>	<b>Thermal Age</b>	<b>Ambient (Air Dried)</b>	<b>50 Cycles</b>
Pin Type: Signal 1						
Average	6.8	1.08	0.96	1.18	1.31	0.78
St. Dev.	0.3	0.77	0.74	0.79	0.82	0.65
Min	6.1	0	0.02	0.01	0.04	0.01
Max	8.33	3.27	3.12	3.54	3.77	3.01
Summary Count	192	192	192	192	192	192
Total Count	192	192	192	192	192	192

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	<=5.0	>5.1 & <=10.0	>10.1 & <=15.0	>15.1 & <=50.0	>50.1 & <=1000	>1000
50 Cycles	192	0	0	0	0	0
Fluid Exposure	192	0	0	0	0	0
Thermals	192	0	0	0	0	0
Remove/Fluid	192	0	0	0	0	0
50 Cycles	192	0	0	0	0	0

**EQUIPMENT AND CALIBRATION SCHEDULES****Equipment #:** TCT-04**Description:** Dillon Quantrol TC21 25-1000 mm/min series test stand**Manufacturer:** Dillon Quantrol**Model:** TC2 I series test stand**Serial #:** 04-1041-04**Accuracy:** Speed Accuracy: +/- 5% of indicated speed; Speed Accuracy: +/- 5% of indicated speed;  
... Last Cal: 05/29/2021, Next Cal: 05/29/2022**Equipment #:** MO-11**Description:** Switch/Multimeter**Manufacturer:** Keithley**Model:** 3706**Serial #:** 120169**Accuracy:** See Manual

... Last Cal: 09/11/2021, Next Cal: 09/11/2022

**Equipment #:** THC-05**Description:** Temperature/Humidity Chamber (Chamber Room)**Manufacturer:** Thermotron**Model:** SM-8-3800**Serial #:** 05 23 00 02**Accuracy:** See Manual

... Last Cal: 11/14/2021, Next Cal: 11/14/2022

**Equipment #:** TSC-01**Description:** Vertical Thermal Shock Chamber**Manufacturer:** Cincinnati Sub Zero**Model:** VTS-3-6-6-SC/AC**Serial #:** 10-VT14993**Accuracy:** See Manual

... Last Cal: 06/30/2021, Next Cal: 06/30/2022

**Equipment #:** HPT-01**Description:** Hipot Safety Tester**Manufacturer:** Vitrek**Model:** V73**Serial #:** 019808**Accuracy:**

... Last Cal: 05/15/2021, Next Cal: 05/15/2022

**Equipment #:** OV-05**Description:** Forced Air Oven, 5 Cu. Ft., 120 V (Chamber Room)**Manufacturer:** Sheldon Mfg.**Model:** CE5F**Serial #:** 02008008**Accuracy:** +/- 5 deg. C

... Last Cal: 02/05/2022, Next Cal: 02/05/2023

**EQUIPMENT AND CALIBRATION SCHEDULES****Equipment #:** MO-04**Description:** Multimeter /Data Acquisition System**Manufacturer:** Keithley**Model:** 2700**Serial #:** 0798688**Accuracy:** See Manual

... Last Cal: 09/11/2021, Next Cal: 09/11/2022

**Equipment #:** PS-02**Description:** Power Supply**Manufacturer:** Hewlett-Packer**Model:** 6033A**Serial #:** N/A**Accuracy:** See Manual

... Last Cal: NOT CALIBRATED