


Project Number: Design Qualification Test Report	Tracking Code: 2651256_Report_Rev_1
Requested by: Michael Menkhaus	Date: 6/4/2021
Part #: UMPC-10-T-16-P-12.0-1/UMPT-10-01-T-RA-WT-P-TR	
Part description: UMPC/UMPT	Tech: Kason He
Test Start: 12/30/2020	Test Completed: 1/15/2021



DESIGN QUALIFICATION TEST REPORT

UMPC/UMPT
UMPC-10-T-16-P-12.0-1/UMPT-10-01-T-RA-WT-P-TR

REVISION HISTORY

DATA	REV.NUM.	DESCRIPTION	ENG
3/2/2021	1	Initial Issue	KH

CERTIFICATION

All instruments and measuring equipment were calibrated to National Institute for Standards and Technology (NIST) traceable standards according to ISO 10012-1 and ANSI/NCSL 2540-1, as applicable.

All contents contained herein are the property of Samtec. No portion of this report, in part or in full shall be reproduced without prior written approval of Samtec.

SCOPE

To perform the following tests: Design Qualification test. Please see test plan.

APPLICABLE DOCUMENTS

Standards: EIA Publication 364

TEST SAMPLES AND PREPARATION

- 1) All materials were manufactured in accordance with the applicable product specification.
- 2) All test samples were identified and encoded to maintain traceability throughout the test sequences.
- 3) After soldering, the parts to be used for LLCR and DWV/IR testing were cleaned according to TLWI-0001.
- 4) Either an automated cleaning procedure or an ultrasonic cleaning procedure may be used.
- 5) The automated procedure is used with aqueous compatible soldering materials.
- 6) Parts not intended for testing LLCR and DWV/IR are visually inspected and cleaned if necessary.
- 7) Any additional preparation will be noted in the individual test sequences.
- 8) Solder Information: Lead free
- 9) Samtec Test PCBs used: PCB-110794-TST/PCB-110793-TST/PCB-110496-TST/PCB-110472-TST/ PCB-110293-TST/PCB-110216-TST PCB-110215-TST/PCB-110214-TST.

FLOWCHARTS

IR/DWV

Pin-to-Pin

<u>Group 1</u>		<u>Group 2</u>		<u>Group 3</u>	
UMPC-04-T-16-P-06.0		UMPT-04-01-T-RA-WT-P-TR		UMPC-04-T-16-P-06.0	
2 Assemblies		2 Assemblies		2 Assemblies	
Step	Description	Step	Description	Step	Description
1.	DWV Breakdown (2)	1.	DWV Breakdown (2)	1.	IR (4)
				2.	DWV at Test Voltage (1)
				3.	Thermal Shock (5)
				4.	IR (4)
				5.	DWV at Test Voltage (1)
				6.	Humidity (3)
				7.	IR (4)
				8.	DWV at Test Voltage (1)

(1) DWV at Test Voltage = EIA-364-20
 Test Condition = 1 (Sea Level)
 DWV test voltage is equal to 75% of the lowest breakdown voltage
 Test voltage applied for 60 seconds

(2) DWV Breakdown = EIA-364-20
 Test Condition = 1 (Sea Level)
 DWV test voltage is equal to 75% of the lowest breakdown voltage
 Test voltage applied for 60 seconds

(3) Humidity = EIA-364-31
 Test Condition = B (240 Hours)
 Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)
 Test Exceptions: ambient pre-condition and delete steps 7a and 7b

(4) IR = EIA-364-21
 Test Condition = 500 Vdc, 2 Minutes Max

(5) Thermal Shock = EIA-364-32
 Exposure Time at Temperature Extremes = 1/2 Hour
 Method A, Test Condition = I (-55°C to +85°C)
 Test Duration = A-3 (100 Cycles)

FLOWCHARTS Continued

Current Carrying Capacity

<u>Group 1</u> UMPC-10-T-18-P-12.0-1 UMPT-10-01-T-RA-WT-P-TR 1 Pins Powered Signal		<u>Group 2</u> UMPC-10-T-18-P-12.0-1 UMPT-10-01-T-RA-WT-P-TR 2 Pins Powered Signal		<u>Group 3</u> UMPC-10-T-18-P-12.0-1 UMPT-10-01-T-RA-WT-P-TR 3 Pins Powered Signal		<u>Group 4</u> UMPC-10-T-18-P-12.0-1 UMPT-10-01-T-RA-WT-P-TR 4 Pins Powered Signal	
Step	Description	Step	Description	Step	Description	Step	Description
1.	CCC ⁽¹⁾ Rows = 1 Number of Positions = 1	1.	CCC ⁽¹⁾ Rows = 1 Number of Positions = 2	1.	CCC ⁽¹⁾ Rows = 1 Number of Positions = 3	1.	CCC ⁽¹⁾ Rows = 1 Number of Positions = 4
<u>Group 5</u> UMPC-10-T-18-P-12.0-1 UMPT-10-01-T-RA-WT-P-TR 10 Pins Powered Signal		<u>Group 6</u> UMPC-10-T-16-P-12.0-1 UMPT-10-01-T-RA-WT-P-TR 1 Pins Powered Signal		<u>Group 7</u> UMPC-10-T-16-P-12.0-1 UMPT-10-01-T-RA-WT-P-TR 2 Pins Powered Signal		<u>Group 8</u> UMPC-10-T-16-P-12.0-1 UMPT-10-01-T-RA-WT-P-TR 3 Pins Powered Signal	
Step	Description	Step	Description	Step	Description	Step	Description
1.	CCC ⁽¹⁾ Rows = 1 Number of Positions = 10	1.	CCC ⁽¹⁾ Rows = 1 Number of Positions = 1	1.	CCC ⁽¹⁾ Rows = 1 Number of Positions = 2	1.	CCC ⁽¹⁾ Rows = 1 Number of Positions = 3
<u>Group 9</u> UMPC-10-T-16-P-12.0-1 UMPT-10-01-T-RA-WT-P-TR 4 Pins Powered Signal		<u>Group 10</u> UMPC-10-T-16-P-12.0-1 UMPT-10-01-T-RA-WT-P-TR 10 Pins Powered Signal					
Step	Description	Step	Description				
1.	CCC ⁽¹⁾ Rows = 1 Number of Positions = 4	1.	CCC ⁽¹⁾ Rows = 1 Number of Positions = 10				

(1) CCC = EIA-364-70

Method 2, Temperature Rise Versus Current Curve

(TIN PLATING) - Tabulate calculated current at RT, 65°C, 75°C and 95°C after derating 20% and based on 105°C

(GOLD PLATING) - Tabulate calculated current at RT, 85°C, 95°C and 115°C after derating 20% and based on 125°C

FLOWCHARTS Continued

Cable Pull

Note: Pull until electrical or mechanical failure.

<u>Group 1</u>		<u>Group 2</u>		<u>Group 3</u>		<u>Group 4</u>	
UMPC-04-T-16-P-12.0-1		UMPC-04-T-16-P-12.0-1		UMPC-04-T-16-M-12.0-1		UMPC-04-T-16-M-12.0-1	
UMPT-04-01-T-RA-WT-P-TR		UMPT-04-01-T-RA-WT-P-TR		UMPT-04-01-T-RA-WT-M-TR		UMPT-04-01-T-RA-WT-M-TR	
5 Assemblies		5 Assemblies		5 Assemblies		5 Assemblies	
0 Degrees Plastic Latch		90 Degrees Plastic Latch		0 Degrees Metal Latch		90 Degrees Metal Latch	
Step	Description	Step	Description	Step	Description	Step	Description
1.	Cable Pull ⁽¹⁾	1.	Cable Pull ⁽¹⁾	1.	Cable Pull ⁽¹⁾	1.	Cable Pull ⁽¹⁾

(1) Cable Pull = EIA-364-38
 Measure and Record Force Required to Failure
 Failure = Discontinuity >1 microsecond at 10 ohms

Cable Flex

Note: Use testing voltage found during IR/DWV testing in this test plan.

<u>Group 1</u>		<u>Group 2</u>	
UMPC-04-T-16-P-16.0-1		UMPC-04-T-16-M-16.0-1	
UMPT-04-01-T-RA-WT-P-TR		UMPT-04-01-T-RA-WT-M-TR	
8 Assemblies		8 Assemblies	
Plastic Latch		Metal Latch	
Step	Description	Step	Description
1.	IR ⁽³⁾	1.	IR ⁽³⁾
2.	DWV at Test Voltage ⁽²⁾	2.	DWV at Test Voltage ⁽²⁾
3.	Cable Flex ⁽¹⁾	3.	Cable Flex ⁽¹⁾
4.	Visual Inspection	4.	Visual Inspection
5.	IR ⁽³⁾	5.	IR ⁽³⁾
6.	DWV at Test Voltage ⁽²⁾	6.	DWV at Test Voltage ⁽²⁾
7.	Rotate Cable 90°	7.	Rotate Cable 90°
8.	Cable Flex ⁽¹⁾	8.	Cable Flex ⁽¹⁾
9.	Visual Inspection	9.	Visual Inspection
10.	IR ⁽³⁾	10.	IR ⁽³⁾
11.	DWV at Test Voltage ⁽²⁾	11.	DWV at Test Voltage ⁽²⁾

(1) Cable Flex = EIA-364-41
 Circular Jacket Cable - to be tested 90° each direction (180° total)
 Flat Cable - to be tested 70° each direction (140° total)
 Monitor continuity during flex testing
 Failure = Discontinuity >1 microsecond at 10 ohms

(2) DWV at Test Voltage = EIA-364-20
 Test Condition = 1 (Sea Level)
 DWV test voltage is equal to 75% of the lowest breakdown voltage
 Test voltage applied for 60 seconds

(3) IR = EIA-364-21
 Test Condition = 500 Vdc, 2 Minutes Max

ATTRIBUTE DEFINITIONS

The following is a brief, simplified description of attributes.

THERMAL SHOCK:

- 1) EIA-364-32, *Thermal Shock (Temperature Cycling) Test Procedure for Electrical Connectors*.
- 2) Test Condition 1: -55°C to $+85^{\circ}\text{C}$
- 3) Test Time: $\frac{1}{2}$ hour dwell at each temperature extreme
- 4) Number of Cycles: 100
- 5) All test samples are pre-conditioned at ambient.
- 6) All test samples are exposed to environmental stressing in the mated condition.

HUMIDITY:

- 1) Reference document: EIA-364-31, *Humidity Test Procedure for Electrical Connectors*.
- 2) Test Condition B, 240 Hours.
- 3) Method III, $+25^{\circ}\text{C}$ to $+65^{\circ}\text{C}$, 90% to 98% Relative Humidity excluding sub-cycles 7a and 7b.
- 4) All samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

TEMPERATURE RISE (Current Carrying Capacity, CCC):

- 1) EIA-364-70, *Temperature Rise versus Current Test Procedure for Electrical Connectors and Sockets*.
- 2) When current passes through a contact, the temperature of the contact increases as a result of I^2R (resistive) heating.
- 3) The number of contacts being investigated plays a significant part in power dissipation and therefore temperature rise.
- 4) The size of the temperature probe can affect the measured temperature.
- 5) Copper traces on PC boards will contribute to temperature rise:
 - a. Self-heating (resistive)
 - b. Reduction in heat sink capacity affecting the heated contacts
- 6) A de-rating curve, usually 20%, is calculated.
- 7) Calculated de-rated currents at four temperature points are reported:
 - a. Ambient
 - b. 65°C
 - c. 75°C
 - d. 95°C
- 8) Typically, neighboring contacts (in close proximity to maximize heat buildup) are energized.
- 9) The thermocouple (or temperature measuring probe) will be positioned at a location to sense the maximum temperature in the vicinity of the heat generation area.
- 10) A computer program, *TR 803.exe*, ensures accurate stability for data acquisition.
- 11) Hook-up wire cross section is larger than the cross section of any connector leads/PC board traces, jumpers, etc.
- 12) Hook-up wire length is longer than the minimum specified in the referencing standard.

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes.

INSULATION RESISTANCE (IR):

To determine the resistance of insulation materials to leakage of current through or on the surface of these materials when a DC potential is applied.

- 1) PROCEDURE:
 - a. Reference document: EIA-364-21, *Insulation Resistance Test Procedure for Electrical Connectors*.
 - b. Test Conditions:
 - i. Between Adjacent Contacts or Signal-to-Ground
 - ii. Electrification Time 2.0 minutes
 - iii. Test Voltage (500 VDC) corresponds to calibration settings for measuring resistances.
- 2) MEASUREMENTS:
- 3) When the specified test voltage is applied (VDC), the insulation resistance shall not be less than 5000 megohms.

DIELECTRIC WITHSTANDING VOLTAGE (DWV):

To determine if the sockets can operate at its rated voltage and withstand momentary over potentials due to switching, surges, and other similar phenomenon. Separate samples are used to evaluate the effect of environmental stresses so not to influence the readings from arcing that occurs during the measurement process.

- 1) PROCEDURE:
 - a. Reference document: EIA-364-20, *Withstanding Voltage Test Procedure for Electrical Connectors*.
 - b. Test Conditions:
 - i. Between Adjacent Contacts or Signal-to-Ground
 - ii. Barometric Test Condition 1
 - iii. Rate of Application 500 V/Sec
 - iv. Test Voltage (VAC) until breakdown occurs
- 2) MEASUREMENTS/CALCULATIONS
 - a. The breakdown voltage shall be measured and recorded.
 - b. The dielectric withstand voltage shall be recorded as 75% of the minimum breakdown voltage.
 - c. The working voltage shall be recorded as one-third (1/3) of the dielectric withstand voltage (one-fourth of the breakdown voltage).

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes.

CABLE PULL:

- 1) Secure cable near center and pull on connector
 - a. At 90°, right angle to cable
 - b. At 0°, in-line with cable



Fig. 1
0° Connector pull

CABLE DURABILITY:

- 1) Oscillate and monitor electrical continuity for open circuit indication.
 - a. $\pm 70^\circ$ Flex Mode, bend up to 500 cycles with 16 oz load on cable end.



Fig. 2
(Setup picture)

RESULTS

Temperature Rise, CCC at a 20% de-rating

UMPC-10-T-16-P-12.0-1/UMPT-10-01-T-RA-WT-P-TR

- CCC for a 30°C Temperature Rise-----18.1 A per contact with 1 contact (1x1) powered
- CCC for a 30°C Temperature Rise-----15.8 A per contact with 2 contacts (1x2) powered
- CCC for a 30°C Temperature Rise-----13.5 A per contact with 3 contacts (1x3) powered
- CCC for a 30°C Temperature Rise-----12.2 A per contact with 4 contacts (1x4) powered
- CCC for a 30°C Temperature Rise-----9.2 A per contact with 10 contacts (1x10) powered

UMPC-10-T-18-P-12.0-1/UMPT-10-01-T-RA-WT-P-TR

- CCC for a 30°C Temperature Rise-----17.0 A per contact with 1 contact (1x1) powered
- CCC for a 30°C Temperature Rise-----13.9 A per contact with 2 contacts (1x2) powered
- CCC for a 30°C Temperature Rise-----11.5 A per contact with 3 contacts (1x3) powered
- CCC for a 30°C Temperature Rise-----11.0 A per contact with 4 contacts (1x4) powered
- CCC for a 30°C Temperature Rise-----8.0 A per contact with 10 contacts (1x10) powered

Cable Pull force

Plastic Latch

- 0° Pull
 - Min -----16.76 lbs
 - Max -----20.04 lbs
- 90° Pull
 - Min -----7.81 lbs
 - Max -----8.46 lbs

Metal Latch

- 0° Pull
 - Min -----24.34 lbs
 - Max -----26.51 lbs
- 90° Pull
 - Min -----10.20 lbs
 - Max -----10.60 lbs

RESULTS Continued

Insulation Resistance minimums, IR

Pin to Pin

- Initial
 - Mated ----- 45000 Meg Ω ----- Passed
 - Unmated ----- 45000 Meg Ω ----- Passed
- Thermal Shock
 - Mated ----- 45000 Meg Ω ----- Passed
 - Unmated ----- 45000 Meg Ω ----- Passed
- Humidity
 - Mated ----- 45000 Meg Ω ----- Passed
 - Unmated ----- 45000 Meg Ω ----- Passed

Dielectric Withstanding Voltage minimums, DWV

Minumums

- Breakdown Voltage ----- 2153 VAC
- Test Voltage ----- 1615 VAC
- Working Voltage ----- 535 VAC

Pin to Pin

- Initial DWV ----- Passed
- Thermal DWV ----- Passed
- Humidity DWV ----- Passed

RESULTS Continued

Cable Flex:

Plastic Latch

Insulation Resistance minimums, IR

Standard

Pin to Pin

- Initial
 - Mated ----- 45000 Meg Ω ----- Passed
- After 500 flex cycles
 - Mated ----- 45000 Meg Ω ----- Passed

Revolve 90°

Pin to Pin

- Initial
 - Mated ----- 45000 Meg Ω ----- Passed
- After 500 flex cycles
 - Mated ----- 45000 Meg Ω ----- Passed

Dielectric Withstanding Voltage minimums, DWV

- Test Voltage ----- 1615 VAC

Standard

Pin to Pin

- Initial DWV ----- Passed
- After 500 Flex cycles DWV ----- Passed

Revolve 90°

Pin to Pin

- Initial DWV ----- Passed
- After 500 Flex cycles DWV ----- Passed


DATA SUMMARIES

TEMPERATURE RISE (Current Carrying Capacity, CCC):

- 1) High quality thermocouples whose temperature slopes track one another were used for temperature monitoring.
- 2) The thermocouples were placed at a location to sense the maximum temperature generated during testing.
- 3) Temperature readings recorded are those for which three successive readings, 15 minutes apart, differ less than 1°C (computer-controlled data acquisition).
- 4) Adjacent contacts were powered:


UMPC-10-T-16-P-12.0-1/UMPT-10-01-T-RA-WT-P-TR

- a. Linear configuration with 1 adjacent conductors/contacts powered





DATA SUMMARIES Continued

2651256
1(1X1) Contacts in Series(Contact Interface)
Part Numbers: UMPc-10-T-16-P-12.0-1/UMPT-10-01-T-RA-WT-P-TR





DATA SUMMARIES Continued

b. Linear configuration with 2 adjacent conductors/contacts powered





DATA SUMMARIES Continued

c. Linear configuration with 3 adjacent conductors/contacts powered





DATA SUMMARIES Continued

d. Linear configuration with 4 adjacent conductors/contacts powered



DATA SUMMARIES Continued



e. Linear configuration with all adjacent conductors/contacts powered



DATA SUMMARIES Continued



UMPC-10-T-18-P-12.0-1/UMPT-10-01-T-RA-WT-P-TR

a. Linear configuration with 1 adjacent conductors/contacts powered





DATA SUMMARIES Continued

b. Linear configuration with 2 adjacent conductors/contacts powered





DATA SUMMARIES Continued

c. Linear configuration with 3 adjacent conductors/contacts powered





DATA SUMMARIES Continued

d. Linear configuration with 4 adjacent conductors/contacts powered



DATA SUMMARIES Continued

e. Linear configuration with all adjacent conductors/contacts powered



DATA SUMMARIES Continued**INSULATION RESISTANCE (IR):**

	Pin to Pin		
	Mated	Unmated	Unmated
Minimum	UMPC/UMPT	UMPC	UMPT
Initial	45000	45000	45000
Thermal	45000	45000	45000
Humidity	45000	45000	45000

DIELECTRIC WITHSTANDING VOLTAGE (DWV):

Voltage Rating Summary	
Minimum	UMPC/UMPT
Break Down Voltage	2153
Test Voltage	1615
Working Voltage	535

Pin to Pin	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed
After Humidity Test Voltage	Passed

DATA SUMMARIES Continued**Cable Pull Force:
Plastic Latch****0° Pull**

	Force (lbs)
Minimum	16.76
Maximum	20.04
Average	19.14

90° Pull

	Force (lbs)
Minimum	7.81
Maximum	8.46
Average	8.25

Metal Latch**0° Pull**

	Force (lbs)
Minimum	24.34
Maximum	26.51
Average	25.18

90° Pull

	Force (lbs)
Minimum	10.20
Maximum	10.60
Average	10.32

DATA SUMMARIES Continued**Cable Flex:****Plastic Latch****Insulation Resistance minimums, IR**

Pin to Pin	
Mated	
Minimum	
Initial	45000
After 500 Flex Cycles (Standard)	45000
After 500 Flex Cycles (90°)	45000

Dielectric Withstanding Voltage minimums, DWV

Voltage Rating Summary	
Minimum	
Break Down Voltage	2153
Test Voltage	1615
Working Voltage	538

Pin to Pin	
Initial Test Voltage	Passed
After 500 Flex Cycles Test Voltage (Standard)	Passed
After 500 Flex Cycles Test Voltage (90°)	Passed

Metal Latch**Insulation Resistance minimums, IR**

Pin to Pin	
Mated	
Minimum	
Initial	45000
After 500 Flex Cycles (Standard)	45000
After 500 Flex Cycles (90°)	45000

Dielectric Withstanding Voltage minimums, DWV

Voltage Rating Summary	
Minimum	
Break Down Voltage	2153
Test Voltage	1615
Working Voltage	538

Pin to Pin	
Initial Test Voltage	Passed
After 500 Flex Cycles Test Voltage (Standard)	Passed
After 500 Flex Cycles Test Voltage (90°)	Passed

EQUIPMENT AND CALIBRATION SCHEDULES

Equipment #: HZ-TCT-01

Description: Normal force analyzer

Manufacturer: Mecmesin Multitester

Model: Mecmesin Multitester 2.5-i

Serial #: 08-1049-04

Accuracy: Last Cal: 3/5/2020, Next Cal: 3/4/2021

Equipment #: DG-THC-01

Description: Humidity transmitter

Manufacturer: Thermtron

Model: SM-8-8200

Serial #: 50613

Accuracy: Last Cal: 12/4/2020, Next Cal: 12/3/2021

Equipment #: HZ-TSC-01

Description: Vertical Thermal Shock Chamber

Manufacturer: Cincinnati Sub Zero

Model: VTS-3-6-6-SC/AC

Serial #: 10-VT14994

Accuracy: See Manual

... Last Cal: 04/16/2020, Next Cal: 04/15/2021

Equipment #: DG-HPT-01

Description: Hipot Safety Tester

Manufacturer: Vitrek

Model: V73

Serial #: 025866

Accuracy:

... Last Cal: 04/16/2020, Next Cal: 04/15/2021

Equipment #: HZ-MO-01

Description: Micro-ohmmeter

Manufacturer: Keithley

Model: 2700

Serial #: 1199807

Accuracy: Last Cal: 05/19/2020, Next Cal: 05/18/2021

Equipment #: HZ-PS-01

Description: Power Supply

Manufacturer: Agilent

Model: 6031A

Serial #: MY41000982

Accuracy: Last Cal: 04/16/2020, Next Cal: 04/15/2021

Equipment #: HPT-01

Description: Hipot Safety Tester

Manufacturer: Vitrek

Model: V73

Serial #: 019808

Accuracy:

... Last Cal: 05/15/2020, Next Cal: 05/15/2021