




|  |                                    |
|--|------------------------------------|
| Project Number: Design Qualification Test Report | Tracking Code: 337665_Report_Rev_1 |
| Requested by: Catie Eichhorn                     | Date: 4/3/2015                     |
| Part #: PTF-125-01-L-D/PTT-125-01-L-D            | Tech: Peter Chen                   |
| Part description: PTF/PTT                        | Qty to test: 50                    |
| Test Start: 11/1/2014                            | Test Completed: 12/15/2014         |



## Design Qualification Test Report

**PTF/PTT**  
**PTF-125-01-L-D/PTT-125-01-L-D**

|                                    |                                       |
|------------------------------------|---------------------------------------|
| Tracking Code: 337665_Report_Rev_1 | Part #: PTF-125-01-L-D/PTT-125-01-L-D |
| Part description: PTF/PTT          |                                       |

### REVISION HISTORY

| DATA      | REV.NUM. | DESCRIPTION   | ENG |
|-----------|----------|---------------|-----|
| 3/21/2015 | 1        | Initial Issue | PC  |

## CERTIFICATION

All instruments and measuring equipment were calibrated to National Institute for Standards and Technology (NIST) traceable standards according to ISO 10012-1 and ANSI/NCSL 2540-1, as applicable.

All contents contained herein are the property of Samtec. No portion of this report, in part or in full shall be reproduced without prior written approval of Samtec.

### SCOPE

To perform the following tests: Design Qualification Test, Please see test plan.

### APPLICABLE DOCUMENTS

Standards: EIA Publication 364

### TEST SAMPLES AND PREPARATION

- 1) All materials were manufactured in accordance with the applicable product specification.
- 2) All test samples were identified and encoded to maintain traceability throughout the test sequences.
- 3) After soldering, the parts to be used for LLCR and DWV/IR testing were cleaned according to TLWI-0001.
- 4) Either an automated cleaning procedure or an ultrasonic cleaning procedure may be used.
- 5) The automated procedure is used with aqueous compatible soldering materials.
- 6) Parts not intended for testing LLCR and DWV/IR are visually inspected and cleaned if necessary.
- 7) Any additional preparation will be noted in the individual test sequences.
- 8) Samtec Test PCBs used: PCB-106435-TST-XX, PCB-106436-TST-XX , PCB-106437-TST-XX, PCB-106459-TST-XX.

**FLOWCHARTS****Gas Tight**Group 1

PTF-125-01-L-D  
 PTT-125-01-L-D  
 8 Assemblies  
 ENIG .033" PTH

**Step Description**

1. LLCR (2)
2. Gas Tight (1)
3. LLCR (2)  
Max Delta = 15 mOhm

**Compliant Pin ONLY**Group 2

PTF-125-01-L-D

30 Contacts Minimum  
 C-159 ENIG .033" PTH

*Note: Scan the individual compliant pins  
 for each of the LLCR readings.*

**Step Description**

1. LLCR (2)
2. Gas Tight (1)
3. LLCR (2)  
Max Delta = 1 mOhm

Group 3

PTT-125-01-L-D

30 Contacts Minimum  
 T-1S47: ENIG .033" PTH

*Note: Scan the individual compliant pins  
 for each of the LLCR readings.*

**Step Description**

1. LLCR (2)
2. Gas Tight (1)
3. LLCR (2)  
Max Delta = 1 mOhm

(1) Gas Tight = EIA-364-36

(2) LLCR = EIA-364-23  
 Open Circuit Voltage = 20 mV Max  
 Test Current = 100 mA Max

**Normal Force**Group 1

PTF-125-01-L-D  
 PTT-125-01-L-D

8 Contacts Minimum

Signal Without Thermals-ENIG 0.033"  
 PTH

**Step Description**

1. Contact Gaps
2. Normal Force (1)  
Deflection = 0.005 "  
Expected Force at Max Deflection = 150 g

Group 2

PTF-125-01-L-D  
 PTT-125-01-L-D

8 Contacts Minimum

Signal With Thermals-ENIG 0.033" PTH

**Step Description**

1. Contact Gaps
2. Thermal Age (2)
3. Contact Gaps
4. Normal Force (1)  
Deflection = 0.005 "  
Expected Force at Max Deflection = 150 g

(1) Normal Force = EIA-364-04

(2) Thermal Age = EIA-364-17  
 Test Condition = 4 (105°C)  
 Time Condition = B (250 Hours)

**FLOWCHARTS Continued****Thermal Aging**Group 1

PTF-125-01-L-D

PTT-125-01-L-D

8 Assemblies

ENIG 0.033" PTH

**Step Description**

1. Contact Gaps
2. Mating/Unmating Force (2)
3. LLCR (1)
4. Thermal Age (4)
5. LLCR (1)  
Max Delta = 15 mOhm
6. Mating/Unmating Force (2)
7. Contact Gaps

**COMPLIANT PIN ONLY**Group 2

PTF-125-01-L-D

30 Contacts Minimum

C-159: ENIG 0.033" PTH

*Note: probe each of the compliant pins individually to take readings.*

**Step Description**

1. LLCR (1)
2. Thermal Age (4) - Non Standard
3. LLCR (1)  
Max Delta = 1 mOhm

Group 3

PTT-125-01-L-D

30 Contacts Minimum

T-1S47: ENIG 0.033" PTH

*Note: probe each of the compliant pins individually to take readings.*

**Step Description**

1. LLCR (1)
2. Thermal Age (3) - Non Standard
3. LLCR (1)  
Max Delta = 1 mOhm

(1) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(2) Mating/Unmating Force = EIA-364-13

(3) Thermal Age = EIA-364-17

Test Condition = 4 (105°C)

Time Condition = B (250 Hours)

(4) Thermal Age = EIA-364-17

Test Condition = 4 (105°C)

Time Condition = B (250 Hours)

**FLOWCHARTS Continued****Mating/Unmating/Durability**

**Group 1**  
PTF-125-01-L-D  
PTT-125-01-L-D  
8 Assemblies  
ENIG 0.033" PTH

| Step | Description                     |
|------|---------------------------------|
| 1.   | Contact Gaps                    |
| 2.   | LLCR (2)                        |
| 3.   | Mating/Unmating Force (3)       |
| 4.   | Cycles<br>Quantity = 25 Cycles  |
| 5.   | Mating/Unmating Force (3)       |
| 6.   | Cycles<br>Quantity = 25 Cycles  |
| 7.   | Mating/Unmating Force (3)       |
| 8.   | Cycles<br>Quantity = 25 Cycles  |
| 9.   | Mating/Unmating Force (3)       |
| 10.  | Cycles<br>Quantity = 25 Cycles  |
| 11.  | Mating/Unmating Force (3)       |
| 12.  | Contact Gaps                    |
| 13.  | LLCR (2)<br>Max Delta = 15 mOhm |
| 14.  | Thermal Shock (4)               |
| 15.  | LLCR (2)<br>Max Delta = 15 mOhm |
| 16.  | Humidity (1)                    |
| 17.  | LLCR (2)<br>Max Delta = 15 mOhm |
| 18.  | Mating/Unmating Force (3)       |

**Group 2**  
PTF-105-01-L-D  
PTT-105-01-L-D  
8 Assemblies  
ENIG 0.033" PTH

| Step | Description                    |
|------|--------------------------------|
| 1.   | Contact Gaps                   |
| 2.   | Mating/Unmating Force (3)      |
| 3.   | Cycles<br>Quantity = 25 Cycles |
| 4.   | Mating/Unmating Force (3)      |
| 5.   | Cycles<br>Quantity = 25 Cycles |
| 6.   | Mating/Unmating Force (3)      |
| 7.   | Cycles<br>Quantity = 25 Cycles |
| 8.   | Mating/Unmating Force (3)      |
| 9.   | Cycles<br>Quantity = 25 Cycles |
| 10.  | Mating/Unmating Force (3)      |

**Group 3**  
PTF-150-01-L-D  
PTT-150-01-L-D  
8 Assemblies  
ENIG 0.033" PTH

| Step | Description                    |
|------|--------------------------------|
| 1.   | Contact Gaps                   |
| 2.   | Mating/Unmating Force (3)      |
| 3.   | Cycles<br>Quantity = 25 Cycles |
| 4.   | Mating/Unmating Force (3)      |
| 5.   | Cycles<br>Quantity = 25 Cycles |
| 6.   | Mating/Unmating Force (3)      |
| 7.   | Cycles<br>Quantity = 25 Cycles |
| 8.   | Mating/Unmating Force (3)      |
| 9.   | Cycles<br>Quantity = 25 Cycles |
| 10.  | Mating/Unmating Force (3)      |

**Compliant Pin Only**

**Group 4**  
PTF-125-01-L-D  
  
30 Contacts Minimum  
ENIG 0.033" C-159

| Step | Description                      |
|------|----------------------------------|
| 1.   | LLCR (2)                         |
| 2.   | Thermal Shock (4) - Non Standard |
| 3.   | LLCR (2)<br>Max Delta = 1 mOhm   |
| 4.   | Humidity (1) - Non Standard      |
| 5.   | LLCR (2)<br>Max Delta = 1 mOhm   |

**Group 5**  
PTT-125-01-L-D  
  
30 Contacts Minimum  
ENIG 0.033" T-1547

| Step | Description                      |
|------|----------------------------------|
| 1.   | LLCR (2)                         |
| 2.   | Thermal Shock (4) - Non Standard |
| 3.   | LLCR (2)<br>Max Delta = 1 mOhm   |
| 4.   | Humidity (1) - Non Standard      |
| 5.   | LLCR (2)<br>Max Delta = 1 mOhm   |

- (1) Humidity = EIA-364-31  
Test Condition = B (240 Hours)  
Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)  
Test Exceptions: ambient pre-condition and delete steps 7a and 7b
- (2) LLCR = EIA-364-23  
Open Circuit Voltage = 20 mV Max  
Test Current = 100 mA Max
- (3) Mating/Unmating Force = EIA-364-13
- (4) Thermal Shock = EIA-364-32  
Exposure Time at Temperature Extremes = 1/2 Hour  
Method A, Test Condition = I (-55°C to +85°C)  
Test Duration = A-3 (100 Cycles)

**FLOWCHARTS Continued****IR/DWV****Pin-to-Pin****Group 1**

PTF-125-01-L-D  
PTT-125-01-L-D  
2 Assemblies  
ENIG 0.033" PTH

| Step | Description       |
|------|-------------------|
| 1.   | DWV Breakdown (2) |

**Group 2**

PTF-125-01-L-D  
  
2 Assemblies  
ENIG 0.033" PTH

| Step | Description       |
|------|-------------------|
| 1.   | DWV Breakdown (2) |

**Group 3**

PTT-125-01-L-D  
2 Assemblies  
ENIG 0.033" PTH

| Step | Description       |
|------|-------------------|
| 1.   | DWV Breakdown (2) |

**Group 4**

PTF-125-01-L-D  
PTT-125-01-L-D  
2 Assemblies  
ENIG 0.033" PTH

| Step | Description             |
|------|-------------------------|
| 1.   | IR (4)                  |
| 2.   | DWV at Test Voltage (1) |
| 3.   | Thermal Shock (5)       |
| 4.   | IR (4)                  |
| 5.   | DWV at Test Voltage (1) |
| 6.   | Humidity (3)            |
| 7.   | IR (4)                  |
| 8.   | DWV at Test Voltage (1) |

**Row-to-Row****Group 5**

PTF-125-01-L-D  
PTT-125-01-L-D  
2 Assemblies  
ENIG 0.033" PTH

| Step | Description       |
|------|-------------------|
| 1.   | DWV Breakdown (2) |

**Group 6**

PTF-125-01-L-D  
  
2 Assemblies  
ENIG 0.033" PTH

| Step | Description       |
|------|-------------------|
| 1.   | DWV Breakdown (2) |

**Group 7**

PTT-125-01-L-D  
2 Assemblies  
ENIG 0.033" PTH

| Step | Description       |
|------|-------------------|
| 1.   | DWV Breakdown (2) |

**Group 8**

PTF-125-01-L-D  
PTT-125-01-L-D  
2 Assemblies  
ENIG 0.033" PTH

| Step | Description             |
|------|-------------------------|
| 1.   | IR (4)                  |
| 2.   | DWV at Test Voltage (1) |
| 3.   | Thermal Shock (5)       |
| 4.   | IR (4)                  |
| 5.   | DWV at Test Voltage (1) |
| 6.   | Humidity (3)            |
| 7.   | IR (4)                  |
| 8.   | DWV at Test Voltage (1) |

- (1) DWV at Test Voltage = EIA-364-20  
Test Condition = 1 (Sea Level)  
DWV test voltage is equal to 75% of the lowest breakdown voltage  
Test voltage applied for 60 seconds
- (2) DWV Breakdown = EIA-364-20  
Test Condition = 1 (Sea Level)  
DWV test voltage is equal to 75% of the lowest breakdown voltage  
Test voltage applied for 60 seconds
- (3) Humidity = EIA-364-31  
Test Condition = B (240 Hours)  
Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)  
Test Exceptions: ambient pre-condition and delete steps 7a and 7b
- (4) IR = EIA-364-21  
Test Condition = 500 Vdc, 2 Minutes Max
- (5) Thermal Shock = EIA-364-32  
Exposure Time at Temperature Extremes = 1/2 Hour  
Method A, Test Condition = I (-55°C to +85°C)  
Test Duration = A-3 (100 Cycles)

**FLOWCHARTS Continued****Current Carrying Capacity****ENIG- 0.033" PTH**Group 1

PTF-150-01-L-D  
 PTT-150-01-L-D  
 2 Pins Powered  
 Signal

| Step | Description                                    |
|------|--|
| 1.   | CCC (1)<br>Rows = 2<br>Number of Positions = 1 |

Group 2

PTF-150-01-L-D  
 PTT-150-01-L-D  
 4 Pins Powered  
 Signal

| Step | Description                                    |
|------|--|
| 1.   | CCC (1)<br>Rows = 2<br>Number of Positions = 2 |

Group 3

PTF-150-01-L-D  
 PTT-150-01-L-D  
 6 Pins Powered  
 Signal

| Step | Description                                    |
|------|--|
| 1.   | CCC (1)<br>Rows = 2<br>Number of Positions = 3 |

Group 4

PTF-150-01-L-D  
 PTT-150-01-L-D  
 8 Pins Powered  
 Signal

| Step | Description                                    |
|------|--|
| 1.   | CCC (1)<br>Rows = 2<br>Number of Positions = 4 |

Group 5

PTF-150-01-L-D  
 PTT-150-01-L-D  
 100 Pins Powered  
 Signal

| Step | Description                                     |
|------|---|
| 1.   | CCC (1)<br>Rows = 2<br>Number of Positions = 50 |

(1) CCC = EIA-364-70

Method 2, Temperature Rise Versus Current Curve

(TIN PLATING) - Tabulate calculated current at RT, 65°C, 75°C and 95°C after derating 20% and based on 105°C

(GOLD PLATING) - Tabulate calculated current at RT, 85°C, 95°C and 115°C after derating 20% and based on 125°C

**FLOWCHARTS Continued****Mechanical Shock/Random Vibration/LLCR**Group 1

PTF-125-01-L-D

PTT-125-01-L-D

8 Assemblies

ENIG 0.033" PTH

**Step Description**

1. LLCR <sup>(1)</sup>
2. Mechanical Shock <sup>(2)</sup>
3. Random Vibration <sup>(3)</sup>
4. LLCR <sup>(1)</sup>  
Max Delta = 15 mOhm

**Compliant Pin only**Group 2

PTF-125-01-L-D

30 Contacts Minimum  
C-159 ENIG 0.033" PTH**Step Description**

1. LLCR <sup>(1)</sup>
2. Random Vibration <sup>(3)</sup> - Non Standard
3. LLCR <sup>(1)</sup>  
Max Delta = 1 mOhm

Group 3

PTT-125-01-L-D

30 Contacts Minimum  
T-1S47 ENIG 0.033" PTH**Step Description**

1. LLCR <sup>(1)</sup>
2. Random Vibration <sup>(3)</sup> - Non Standard
3. LLCR <sup>(1)</sup>  
Max Delta = 1 mOhm

(1) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max  
Test Current = 100 mA Max

(2) Mechanical Shock = EIA-364-27

Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)  
Number of Shocks = 3 Per Direction, Per Axis, 18 Total

(3) Random Vibration = EIA-364-28

Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

**Mechanical Shock/Random Vibration/Event Detection**Group 1

PTF-125-01-L-D

PTT-125-01-L-D

60 Points

ENIG 0.033" PTH

**Step Description**

1. Nanosecond Event Detection  
(Mechanical Shock) <sup>(1)</sup>
2. Nanosecond Event Detection  
(Random Vibration) <sup>(2)</sup>

(1) Nanosecond Event Detection (Mechanical Shock)

Use EIA-364-87 for Nanosecond Event Detection:

Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-27 for Mechanical Shock:

Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)

Number of Shocks = 3 Per Direction, Per Axis, 18 Total

(2) Nanosecond Event Detection (Random Vibration)

Use EIA-364-87 for Nanosecond Event Detection:

Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-28 for Random Vibration:

Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

## FLOWCHARTS Continued

Insertion/Retention/Hole Conditioning

| <u>Group 1</u><br>PTF-125-01-L-D             |  | <u>Group 2</u><br>PTF-125-01-L-D             |  | <u>Group 3</u><br>PTF-125-01-L-D             |  | <u>Group 4</u><br>PTT-125-01-L-D              |   |
|--|--|--|--|--|--|---|---|
| 30 Contacts Minimum<br>HASL 0.027" PTH C-159 |  | 30 Contacts Minimum<br>HASL 0.033" PTH C-159 |  | 30 Contacts Minimum<br>ENIG 0.033" PTH C-159 |  | 30 Contacts Minimum<br>HASL 0.027" PTH T-1S47 |   |
| Step   | Description  | Step   | Description  | Step   | Description  | Step  | Description   |
| 1.   | Insertion Force<br>Rate = 2.54 mm/min<br><i>Note: Pin 1</i>                            | 1.   | Insertion Force<br>Rate = 2.54 mm/min<br><i>Note: Pin 1</i>                            | 1.   | Insertion Force<br>Rate = 2.54 mm/min<br><i>Note: Pin 1</i>                            | 1.  | Insertion Force<br>Rate = 2.54 mm/min<br><i>Note: Pin 1</i>                                   |
| 2.   | LLCR (1)   | 2.   | LLCR (1)   | 2.   | LLCR (1)   | 2.  | LLCR (1)  |
| 3.   | Retention Force<br>Rate = 2.54 mm/min<br><i>Note: EIA 364-29</i><br><i>Note: Pin 1</i> | 3.   | Retention Force<br>Rate = 2.54 mm/min<br><i>Note: EIA 364-29</i><br><i>Note: Pin 1</i> | 3.   | Retention Force<br>Rate = 2.54 mm/min<br><i>Note: EIA 364-29</i><br><i>Note: Pin 1</i> | 3.  | Retention Force<br>Rate = 2.54 mm/min<br><i>Note: EIA 364-29</i><br><i>Note: Pin 1</i>        |
| 4.   | Cycles<br>Quantity = 1 Cycles<br><i>Note: Pin 2</i>                                    | 4.   | Cycles<br>Quantity = 1 Cycles<br><i>Note: Pin 2</i>                                    | 4.   | Cycles<br>Quantity = 1 Cycles<br><i>Note: Pin 2</i>                                    | 4.  | Cycles<br>Quantity = 1 Cycles<br><i>Note: Pin 2</i>   |
| 5.   | Insertion Force<br>Rate = 2.54 mm/min<br><i>Note: Pin 3</i>                            | 5.   | Insertion Force<br>Rate = 2.54 mm/min<br><i>Note: Pin 3</i>                            | 5.   | Insertion Force<br>Rate = 2.54 mm/min<br><i>Note: Pin 3</i>                            | 5.  | Insertion Force<br>Rate = 2.54 mm/min<br><i>Note: Record Force data</i><br><i>Note: Pin 3</i> |
| 6.   | LLCR (1)<br>Max Delta = 1 mOhm   | 6.   | LLCR (1)<br>Max Delta = 1 mOhm   | 6.   | LLCR (1)<br>Max Delta = 1 mOhm   | 6.  | LLCR (1)<br>Max Delta = 1 mOhm  |
| 7.   | Retention Force<br>Rate = 2.54 mm/min<br><i>Note: EIA 364-29</i><br><i>Note: Pin 3</i> | 7.   | Retention Force<br>Rate = 2.54 mm/min<br><i>Note: EIA 364-29</i><br><i>Note: Pin 3</i> | 7.   | Retention Force<br>Rate = 2.54 mm/min<br><i>Note: EIA 364-29</i><br><i>Note: Pin 3</i> | 7.  | Retention Force<br>Rate = 2.54 mm/min<br><i>Note: EIA 364-29</i><br><i>Note: Pin 3</i>        |
| 8.   | Hole Integrity<br><i>Note: check for distortion of the PTH according to EIA 364-96</i> | 8.   | Hole Integrity<br><i>Note: check for distortion of the PTH according to EIA 364-96</i> | 8.   | Hole Integrity<br><i>Note: check for distortion of the PTH according to EIA 364-96</i> | 8.  | Hole Integrity<br><i>Note: check for distortion of the PTH according to EIA 364-96</i>        |

**FLOWCHARTS Continued**Group 5

PTT-125-01-L-D  
30 Contacts Minimum  
HASL 0.033" PTH T-1S47

| Step | Description   |
|------|---|
| 1.   | <b>Insertion Force</b><br>Rate = 2.54 mm/min<br><i>Note: Pin 1</i>                            |
| 2.   | <b>LLCR (1)</b>   |
| 3.   | <b>Retention Force</b><br>Rate = 2.54 mm/min<br><i>Note: EIA 364-29</i><br><i>Note: Pin 1</i> |
| 4.   | <b>Cycles</b><br>Quantity = 1 Cycles<br><i>Note: Pin 2</i>                                    |
| 5.   | <b>Insertion Force</b><br>Rate = 2.54 mm/min<br><i>Note: Pin 3</i>                            |
| 6.   | <b>LLCR (1)</b><br>Max Delta = 1 mOhm   |
| 7.   | <b>Retention Force</b><br>Rate = 2.54 mm/min<br><i>Note: EIA 364-29</i><br><i>Note: Pin 3</i> |
| 8.   | <b>Hole Integrity</b><br><i>Note: check for distortion of the PTH according to EIA 364-96</i> |

Group 6

PTT-125-01-L-D  
30 Contacts Minimum  
ENIG 0.033" PTH T-1S47

| Step | Description   |
|------|---|
| 1.   | <b>Insertion Force</b><br>Rate = 2.54 mm/min<br><i>Note: Pin 1</i>                            |
| 2.   | <b>LLCR (1)</b>   |
| 3.   | <b>Retention Force</b><br>Rate = 2.54 mm/min<br><i>Note: EIA 364-29</i><br><i>Note: Pin 1</i> |
| 4.   | <b>Cycles</b><br>Quantity = 1 Cycles<br><i>Note: Pin 2</i>                                    |
| 5.   | <b>Insertion Force</b><br>Rate = 2.54 mm/min<br><i>Note: Pin 3</i>                            |
| 6.   | <b>LLCR (1)</b><br>Max Delta = 1 mOhm   |
| 7.   | <b>Retention Force</b><br>Rate = 2.54 mm/min<br><i>Note: EIA 364-29</i><br><i>Note: Pin 3</i> |
| 8.   | <b>Hole Integrity</b><br><i>Note: check for distortion of the PTH according to EIA 364-96</i> |

(1) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

## ATTRIBUTE DEFINITIONS

The following is a brief, simplified description of attributes.

### THERMAL SHOCK:

- 1) EIA-364-32, *Thermal Shock (Temperature Cycling) Test Procedure for Electrical Connectors*.
- 2) Test Condition 1: -55°C to +85°C
- 3) Test Time: ½ hour dwell at each temperature extreme
- 4) Number of Cycles: 100
- 5) All test samples are pre-conditioned at ambient.
- 6) All test samples are exposed to environmental stressing in the mated condition.

### THERMAL:

- 1) EIA-364-17, *Temperature Life with or without Electrical Load Test Procedure for Electrical Connectors*.
- 2) Test Condition 4 at 105° C.
- 3) Test Time Condition B for 250 hours.
- 4) All test samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

### HUMIDITY:

- 1) Reference document: EIA-364-31, *Humidity Test Procedure for Electrical Connectors*.
- 2) Test Condition B, 240 Hours.
- 3) Method III, +25° C to + 65° C, 90% to 98% Relative Humidity excluding sub-cycles 7a and 7b.
- 4) All samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

### MECHANICAL SHOCK (Specified Pulse):

- 1) Reference document: EIA-364-27, *Mechanical Shock Test Procedure for Electrical Connectors*
- 2) Test Condition C
- 3) Peak Value: 100 G
- 4) Duration: 6 Milliseconds
- 5) Wave Form: Half Sine
- 6) Velocity: 12.3 ft/s
- 7) Number of Shocks: 3 Shocks / Direction, 3 Axis (18 Total)

### VIBRATION:

- 1) Reference document: EIA-364-28, *Vibration Test Procedure for Electrical Connectors*
- 2) Test Condition V, Letter B
- 3) Power Spectral Density: 0.04 G<sup>2</sup> / Hz
- 4) G 'RMS': 7.56
- 5) Frequency: 50 to 2000 Hz
- 6) Duration: 2.0 Hours per axis (3 axis total)

### NANOSECOND-EVENT DETECTION:

- 1) Reference document: EIA-364-87, *Nanosecond-Event Detection for Electrical Connectors*
- 2) Prior to test, the samples were characterized to assure the low nanosecond event being monitored will trigger the detector.
- 3) After characterization it was determined the test samples could be monitored for 50 nanosecond events

## ATTRIBUTE DEFINITIONS

The following is a brief, simplified description of attributes.

### MATING/UNMATING:

- 1) Reference document: EIA-364-13, *Mating and Unmating Forces Test Procedure for Electrical Connectors*.
- 2) The full insertion position was to within 0.003" to 0.004" of the plug bottoming out in the receptacle to prevent damage to the system under test.
- 3) One of the mating parts is secured to a floating X-Y table to prevent damage during cycling.

### NORMAL FORCE (FOR CONTACTS TESTED OUTSIDE THE HOUSING):

- 1) Reference document: EIA-364-04, *Normal Force Test Procedure for Electrical Connectors*.
- 2) The contacts shall be tested in the loose state, *not* inserted in connector housing.
- 3) The contacts shall be prepared to allow access to the spring member at the same attitude and deflection level as would occur in actual use.
- 4) In the event that portions of the contact prevent insertion of the test probe and/or deflection of the spring member under evaluation, said material shall be removed leaving the appropriate contact surfaces exposed.
- 5) In the case of multi-tine contacts, each tine shall be tested independently on separate samples as required.
- 6) The connector housing shall be simulated, if required, in order to provide an accurate representation of the actual contact system performance.
- 7) A holding fixture shall be fashioned to allow the contact to be properly deflected.
- 8) Said holding fixture shall be mounted on a floating, adjustable, X-Y table on the base of the Dillon TC<sup>2</sup>, computer controlled test stand with a deflection measurement system accuracy of 5  $\mu\text{m}$  (0.0002").
- 9) The probe shall be attached to a Dillon P/N 49761-0105, 5 N (1.1 Lb) load cell providing an accuracy of  $\pm 0.2\%$ .
- 10) The nominal deflection rate shall be 5 mm (0.2")/minute.
- 11) Unless otherwise noted a minimum of five contacts shall be tested.
- 12) The force/deflection characteristic to load and unload each contact shall be repeated five times.
- 13) The system shall utilize the TC<sup>2</sup> software in order to acquire and record the test data.
- 14) The permanent set of each contact shall be measured within the TC<sup>2</sup> software.
- 15) The acquired data shall be graphed with the deflection data on the X-axis and the force data on the Y-axis and a print out will be stored with the Tracking Code paperwork.

### INSULATION RESISTANCE (IR):

To determine the resistance of insulation materials to leakage of current through or on the surface of these materials when a DC potential is applied.

- 1) PROCEDURE:
  - a. Reference document: EIA-364-21, *Insulation Resistance Test Procedure for Electrical Connectors*.
  - b. Test Conditions:
    - i. Between Adjacent Contacts or Signal-to-Ground
    - ii. Electrification Time 2.0 minutes
    - iii. Test Voltage (500 VDC) corresponds to calibration settings for measuring resistances.
- 2) MEASUREMENTS:
- 3) When the specified test voltage is applied (VDC), the insulation resistance shall not be less than 5000 megohms.

## ATTRIBUTE DEFINITIONS

The following is a brief, simplified description of attributes.

### DIELECTRIC WITHSTANDING VOLTAGE (DWV):

To determine if the sockets can operate at its rated voltage and withstand momentary over potentials due to switching, surges, and other similar phenomenon. Separate samples are used to evaluate the effect of environmental stresses so not to influence the readings from arcing that occurs during the measurement process.

#### 1) PROCEDURE:

- a. Reference document: EIA-364-20, *Withstanding Voltage Test Procedure for Electrical Connectors*.
- b. Test Conditions:
  - i. Between Adjacent Contacts or Signal-to-Ground
  - ii. Rate of Application 500 V/Sec
  - iii. Test Voltage (VAC) until breakdown occurs

#### 2) MEASUREMENTS/CALCULATIONS

- a. The breakdown voltage shall be measured and recorded.
- b. The dielectric withstanding voltage shall be recorded as 75% of the minimum breakdown voltage.
- c. The working voltage shall be recorded as one-third (1/3) of the dielectric withstanding voltage (one-fourth of the breakdown voltage).

### TEMPERATURE RISE (Current Carrying Capacity, CCC):

- 1) EIA-364-70, *Temperature Rise versus Current Test Procedure for Electrical Connectors and Sockets*.
- 2) When current passes through a contact, the temperature of the contact increases as a result of  $I^2R$  (resistive) heating.
- 3) The number of contacts being investigated plays a significant part in power dissipation and therefore temperature rise.
- 4) The size of the temperature probe can affect the measured temperature.
- 5) Copper traces on PC boards will contribute to temperature rise:
  - a. Self heating (resistive)
  - b. Reduction in heat sink capacity affecting the heated contacts
- 6) A de-rating curve, usually 20%, is calculated.
- 7) Calculated de-rated currents at four temperature points are reported:
  - c. Ambient
  - d. 85° C
  - e. 95° C
  - f. 115° C
- 8) Typically, neighboring contacts (in close proximity to maximize heat build up) are energized.
- 9) The thermocouple (or temperature measuring probe) will be positioned at a location to sense the maximum temperature in the vicinity of the heat generation area.
- 10) A computer program, *TR 803.exe*, ensures accurate stability for data acquisition.
- 11) Hook-up wire cross section is larger than the cross section of any connector leads/PC board traces, jumpers, etc.
- 12) Hook-up wire length is longer than the minimum specified in the referencing standard.

**ATTRIBUTE DEFINITIONS**

The following is a brief, simplified description of attributes.

**LLCR:**

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
  - a.  $\leq +5.0$  mOhms:----- Stable
  - b.  $+5.1$  to  $+10.0$  mOhms:----- Minor
  - c.  $+10.1$  to  $+15.0$  mOhms:----- Acceptable
  - d.  $+15.1$  to  $+50.0$  mOhms:----- Marginal
  - e.  $+50.1$  to  $+2000$  mOhms:----- Unstable
  - f.  $>+2000$  mOhms:----- Open Failure
- 4) The following guidelines are used to categorize the changes in LLCR for compliant pin only
  - a.  $\leq +1.0$  mOhms:----- Stable
  - b.  $>+1.0$  mOhms:----- Unstable

**GAS TIGHT:**

To provide method for evaluating the ability of the contacting surfaces in preventing penetration of harsh vapors which might lead to oxide formation that may degrade the electrical performance of the contact system.

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
  - a.  $\leq +5.0$  mOhms:----- Stable
  - b.  $+5.1$  to  $+10.0$  mOhms:----- Minor
  - c.  $+10.1$  to  $+15.0$  mOhms:----- Acceptable
  - d.  $+15.1$  to  $+50.0$  mOhms:----- Marginal
  - e.  $+50.1$  to  $+2000$  mOhms:----- Unstable
  - f.  $>+2000$  mOhms:----- Open Failure
- 4) Procedure:
  - g. Reference document: EIA-364-36, *Test Procedure for Determination of Gas-Tight Characteristics for Electrical Connectors, Sockets and/or Contact Systems*.
  - h. Test Conditions:
    - i. Class II--- Mated pairs of contacts assembled to their plastic housings.
    - ii. Reagent grade Nitric Acid shall be used of sufficient volume to saturate the test chamber
    - iii. The ratio of the volume of the test chamber to the surface area of the acid shall be 10:1.
    - iv. The chamber shall be saturated with the vapor for at least 15 minutes before samples are added.
    - v. Exposure time, 55 to 65 minutes.
    - vi. The samples shall be no closer to the chamber walls than 1 inches and no closer to the surface of the acid than 3 inches.
    - vii. The samples shall be dried after exposure for a minimum of 1 hour.
    - viii. Drying temperature  $50^{\circ}$  C
    - ix. The final LLCR shall be conducted within 1 hour after drying.
- 5) The following guidelines are used to categorize the changes in LLCR for compliant pin only
  - a.  $\leq +1.0$  mOhms:----- Stable
  - b.  $>+1.0$  mOhms:----- Unstable

## RESULTS

### Temperature Rise, CCC at a 20% de-rating

- CCC for a 30°C Temperature Rise-----4.5 A per contact with 2 contacts (2x1) powered
- CCC for a 30°C Temperature Rise-----3.5 A per contact with 4 contacts (2x2) powered
- CCC for a 30°C Temperature Rise-----3.0 A per contact with 6 contacts (2x3) powered
- CCC for a 30°C Temperature Rise-----2.8 A per contact with 8 contacts (2x4) powered
- CCC for a 30°C Temperature Rise-----1.8 A per contact with 20 contacts (2x10) powered

### Mating & Unmating force

#### Thermal aging

#### PTF-125-01-L-D/PTT-125-01-L-D

- Initial
  - Mating
    - Min ----- 7.84 Lbs
    - Max----- 9.25 Lbs
  - Unmating
    - Min ----- 7.87 Lbs
    - Max----- 9.22 Lbs
- After thermal aging
  - Mating
    - Min ----- 6.28 Lbs
    - Max----- 8.45 Lbs
  - Unmating
    - Min ----- 5.30 Lbs
    - Max----- 8.27 Lbs

**RESULTS Continued**

**Mating&Unmating durability:  
PTF-125-01-L-D/PTT-125-01-L-D**

- **Initial**
  - **Mating**
    - **Min** ----- 7.57 Lbs
    - **Max**-----11.39 Lbs
  - **Unmating**
    - **Min** ----- 7.40 Lbs
    - **Max**-----10.96 Lbs
- **After 25 Cycles**
  - **Mating**
    - **Min** ----- 8.60 Lbs
    - **Max**-----13.55 Lbs
  - **Unmating**
    - **Min** ----- 9.05 Lbs
    - **Max**-----12.27 Lbs
- **After 50 Cycles**
  - **Mating**
    - **Min** -----10.97 Lbs
    - **Max**-----15.35 Lbs
  - **Unmating**
    - **Min** -----10.45 Lbs
    - **Max**-----12.89 Lbs
- **After 75 Cycles**
  - **Mating**
    - **Min** -----12.05 Lbs
    - **Max**-----16.33 Lbs
  - **Unmating**
    - **Min** -----11.33 Lbs
    - **Max**-----13.64 Lbs
- **After 100 Cycles**
  - **Mating**
    - **Min** -----13.22 Lbs
    - **Max**-----17.23 Lbs
  - **Unmating**
    - **Min** -----11.87 Lbs
    - **Max**-----14.70 Lb
- **After Humidity**
  - **Mating**
    - **Min** -----10.29 Lbs
    - **Max**-----11.44 Lbs
  - **Unmating**
    - **Min** ----- 9.25 Lbs
    - **Max**-----11.07 Lbs

**RESULTS Continued**

**Mating & Unmating basic:  
PTF-150-01-L-D/PTT-150-01-L-D**

- **Initial**
  - **Mating**
    - **Min -----18.64 Lbs**
    - **Max-----20.91 Lbs**
  - **Unmating**
    - **Min -----14.56 Lbs**
    - **Max-----19.99 Lbs**
- **After 25 Cycles**
  - **Mating**
    - **Min -----16.56 Lbs**
    - **Max-----23.24 Lbs**
  - **Unmating**
    - **Min -----16.40 Lbs**
    - **Max-----22.87 Lbs**
- **After 50 Cycles**
  - **Mating**
    - **Min -----18.20 Lbs**
    - **Max-----25.23 Lbs**
  - **Unmating**
    - **Min -----17.78 Lbs**
    - **Max-----24.78 Lbs**
- **After 75 Cycles**
  - **Mating**
    - **Min -----20.17 Lbs**
    - **Max-----26.72 Lbs**
  - **Unmating**
    - **Min -----19.64 Lbs**
    - **Max-----25.89 Lbs**
- **After 100 Cycles**
  - **Mating**
    - **Min -----22.15 Lbs**
    - **Max-----28.10 Lbs**
  - **Unmating**
    - **Min -----22.01 Lbs**
    - **Max-----26.66 Lbs**

**RESULTS Continued**

**PTF-105-01-L-D/PTT-105-01-L-D**

- **Initial**
  - **Mating**
    - **Min** ----- 1.57 Lbs
    - **Max** ----- 1.89 Lbs
  - **Unmating**
    - **Min** ----- 1.43 Lbs
    - **Max** ----- 1.94 Lbs
- **After 25 Cycles**
  - **Mating**
    - **Min** ----- 1.73 Lbs
    - **Max** ----- 2.81 Lbs
  - **Unmating**
    - **Min** ----- 1.67 Lbs
    - **Max** ----- 2.74 Lbs
- **After 50 Cycles**
  - **Mating**
    - **Min** ----- 1.91 Lbs
    - **Max** ----- 2.96 Lbs
  - **Unmating**
    - **Min** ----- 1.80 Lbs
    - **Max** ----- 2.80 Lbs
- **After 75 Cycles**
  - **Mating**
    - **Min** ----- 2.12 Lbs
    - **Max** ----- 3.02 Lbs
  - **Unmating**
    - **Min** ----- 2.03 Lbs
    - **Max** ----- 2.91 Lbs
- **After 100 Cycles**
  - **Mating**
    - **Min** ----- 2.37 Lbs
    - **Max** ----- 3.05 Lbs
  - **Unmating**
    - **Min** ----- 2.13 Lbs
    - **Max** ----- 2.98 Lbs

**Normal force:**

Signal pin at 0.0027 Inch deflections

- **Initial**
  - **Min** ----- 114.90 gf      **Set** ----- 0.0000 Inch
  - **Max** ----- 133.30 gf      **Set** ----- 0.0002 Inch
- **Thermal**
  - **Min** ----- 78.40 gf      **Set** ----- 0.0001 Inch
  - **Max** ----- 100.70 gf      **Set** ----- 0.0009 Inch

**RESULTS Continued****Compliant pin Insertion/Withdraw Forces****PTF -HASL-0.027"**

- **Initial**
  - **Mating**
    - **Min** ----- 7.58 Lbs
    - **Max** ----- 8.89 Lbs
  - **Unmating**
    - **Min** ----- 3.53 Lbs
    - **Max** ----- 5.51 Lbs
- **After 3 Cycles**
  - **Mating**
    - **Min** ----- 5.78 Lbs
    - **Max** ----- 9.71 Lbs
  - **Unmating**
    - **Min** ----- 3.52 Lbs
    - **Max** ----- 5.01 Lbs

**PTF -HASL-0.033"**

- **Initial**
  - **Mating**
    - **Min** ----- 4.25 Lbs
    - **Max** ----- 5.89 Lbs
  - **Unmating**
    - **Min** ----- 2.68 Lbs
    - **Max** ----- 3.54 Lbs
- **After 3 Cycles**
  - **Mating**
    - **Min** ----- 4.23 Lbs
    - **Max** ----- 5.34 Lbs
  - **Unmating**
    - **Min** ----- 3.00 Lbs
    - **Max** ----- 3.70 Lbs

**PTF -ENIG-0.033"**

- **Initial**
  - **Mating**
    - **Min** ----- 4.91 Lbs
    - **Max** ----- 5.90 Lbs
  - **Unmating**
    - **Min** ----- 1.15 Lbs
    - **Max** ----- 3.37 Lbs
- **After 3 Cycles**
  - **Mating**
    - **Min** ----- 4.37 Lbs
    - **Max** ----- 5.01 Lbs
  - **Unmating**
    - **Min** ----- 2.68 Lbs
    - **Max** ----- 4.84 Lbs

**RESULTS Continued**

**PTT -HASL-0.027"**

- **Initial**
  - **Mating**
    - **Min** -----10.70 Lbs
    - **Max** -----12.48 Lbs
  - **Unmating**
    - **Min** ----- 7.10 Lbs
    - **Max** ----- 8.88 Lbs
- **After 3 Cycles**
  - **Mating**
    - **Min** ----- 9.00 Lbs
    - **Max** -----11.92 Lbs
  - **Unmating**
    - **Min** ----- 5.30 Lbs
    - **Max** ----- 7.67 Lbs

**PTT-HASL-0.033"**

- **Initial**
  - **Mating**
    - **Min** ----- 7.35 Lbs
    - **Max** ----- 9.63 Lbs
  - **Unmating**
    - **Min** ----- 5.09 Lbs
    - **Max** ----- 7.82 Lbs
- **After 3 Cycles**
  - **Mating**
    - **Min** ----- 5.68 Lbs
    - **Max** ----- 8.38 Lbs
  - **Unmating**
    - **Min** ----- 3.28 Lbs
    - **Max** ----- 5.92 Lbs

**PTT -ENIG-0.033"**

- **Initial**
  - **Mating**
    - **Min** ----- 7.79 Lbs
    - **Max** ----- 9.09 Lbs
  - **Unmating**
    - **Min** ----- 3.37 Lbs
    - **Max** ----- 6.57 Lbs
- **After 3 Cycles**
  - **Mating**
    - **Min** ----- 6.08 Lbs
    - **Max** ----- 7.89 Lbs
  - **Unmating**
    - **Min** ----- 2.14 Lbs
    - **Max** ----- 4.09 Lbs

**RESULTS Continued****LLCR Durability (192 pin LLCR test points)**

- **Initial** -----4.53 mOhms Max
- **After 100 Cycles**
  - <= +5.0 mOhms ----- 192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +2000 mOhms -----0 Points ----- Unstable
  - >+2000 mOhms -----0 Points ----- Open Failure
- **After thermal shock**
  - <= +5.0 mOhms ----- 192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +2000 mOhms -----0 Points ----- Unstable
  - >+2000 mOhms -----0 Points ----- Open Failure
- **After humidity**
  - <= +5.0 mOhms ----- 192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +2000 mOhms -----0 Points ----- Unstable
  - >+2000 mOhms -----0 Points ----- Open Failure
  - >+2000 mOhms -----0 Points ----- Open Failure

**LLCR Durability-compliant pin (30 pin LLCR test points)****PTF ENIG 0.033"**

- **Initial** -----0.18 mOhms Max
- **After thermal shock**
  - <= +1.0 mOhms -----30 Points ----- Stable
  - >+1.0 mOhms -----0 Points ----- Unstable
- **After humidity**
  - <= +1.0 mOhms -----30 Points ----- Stable
  - >+1.0 mOhms -----0 Points ----- Unstable

**PTT ENIG 0.033"**

- **Initial** -----0.18 mOhms Max
- **After thermal shock**
  - <= +1.0 mOhms -----30 Points ----- Stable
  - >+1.0 mOhms -----0 Points ----- Unstable
- **After humidity**
  - <= +1.0 mOhms -----30 Points ----- Stable
  - >+1.0 mOhms -----0 Points ----- Unstable

**LLCR Thermal Aging (192 pin LLCR test points)**

- **Initial** -----5.73 mOhms Max
- **Thermal Aging**
  - <= +5.0 mOhms ----- 192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +2000 mOhms -----0 Points ----- Unstable
  - >+2000 mOhms -----0 Points ----- Open Failure

**RESULTS Continued**

**LLCR Thermal Aging (30 compliant pin LLCR test points)**

**PTF ENIG 0.033"**

- Initial -----0.18 mOhms Max
- After thermal shock
  - <= +1.0 mOhms -----30 Points ----- Stable
  - >+1.0 mOhms -----0 Points ----- Unstable
- After humidity
  - <= +1.0 mOhms -----30 Points ----- Stable
  - >+1.0 mOhms -----0 Points ----- Unstable

**PTT ENIG 0.033"**

- Initial -----0.17 mOhms Max
- After thermal shock
  - <= +1.0 mOhms -----30 Points ----- Stable
  - >+1.0 mOhms -----0 Points ----- Unstable
- After humidity
  - <= +1.0 mOhms -----30 Points ----- Stable
  - >+1.0 mOhms -----0 Points ----- Unstable

**LLCR Gas Tight (192 pin LLCR test points)**

- Initial -----4.67 mOhms Max
- Gas-Tight
  - <= +5.0 mOhms ----- 192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +2000 mOhms -----0 Points ----- Unstable
  - >+2000 mOhms -----0 Points ----- Open Failure

**LLCR Gas Tight (30 compliant pin LLCR test points)**

**PTF ENIG 0.033"**

- Initial -----0.17 mOhms Max
- After thermal shock
  - <= +1.0 mOhms -----30 Points ----- Stable
  - >+1.0 mOhms -----0 Points ----- Unstable
- After humidity
  - <= +1.0 mOhms -----30 Points ----- Stable
  - >+1.0 mOhms -----0 Points ----- Unstable

**PTT ENIG 0.033"**

- Initial -----0.18 mOhms Max
- After thermal shock
  - <= +1.0 mOhms -----30 Points ----- Stable
  - >+1.0 mOhms -----0 Points ----- Unstable
- After humidity
  - <= +1.0 mOhms -----30 Points ----- Stable
  - >+1.0 mOhms -----0 Points ----- Unstable

**RESULTS Continued**

**LLCR Shock Vib (192 pin LLCR test points)**

- **Initial** -----4.75 mOhms Max
- **S&V**
  - **<= +5.0 mOhms** ----- **192 Points** ----- **Stable**
  - **+5.1 to +10.0 mOhms** ----- **0 Points** ----- **Minor**
  - **+10.1 to +15.0 mOhms** ----- **0 Points** ----- **Acceptable**
  - **+15.1 to +50.0 mOhms** ----- **0 Points** ----- **Marginal**
  - **+50.1 to +2000 mOhms** ----- **0 Points** ----- **Unstable**
  - **>+2000 mOhms** ----- **0 Points** ----- **Open Failure**

**LLCR Shock Vib (30 compliant pin LLCR test points)**

**PTF ENIG 0.033"**

- **Initial** -----0.13 mOhms Max
- **After thermal shock**
  - **<= +1.0 mOhms** ----- **30 Points** ----- **Stable**
  - **>+1.0 mOhms** ----- **0 Points** ----- **Unstable**
- **After humidity**
  - **<= +1.0 mOhms** ----- **30 Points** ----- **Stable**
  - **>+1.0 mOhms** ----- **0 Points** ----- **Unstable**

**PTT ENIG 0.033"**

- **Initial** -----0.10 mOhms Max
- **After thermal shock**
  - **<= +1.0 mOhms** ----- **30 Points** ----- **Stable**
  - **>+1.0 mOhms** ----- **0 Points** ----- **Unstable**
- **After humidity**
  - **<= +1.0 mOhms** ----- **30 Points** ----- **Stable**
  - **>+1.0 mOhms** ----- **0 Points** ----- **Unstable**

**Mechanical Shock & Random Vibration:**

- **Shock**
  - **No Damage**----- **Passed**
  - **50 Nanoseconds**----- **Passed**
- **Vibration**
  - **No Damage**----- **Passed**
  - **50 Nanoseconds**----- **Passed**

**RESULTS Continued**

**Insulation Resistance minimums, IR**

**Pin- Pin**

- **Initial**
  - Mated-----10000 Meg  $\Omega$  ----- Pass
  - Unmated -----10000 Meg  $\Omega$  ----- Pass
- **Thermal**
  - Mated-----10000 Meg  $\Omega$  ----- Pass
  - Unmated -----10000 Meg  $\Omega$  ----- Pass
- **Humidity**
  - Mated-----10000 Meg  $\Omega$  ----- Pass
  - Unmated -----10000 Meg  $\Omega$  ----- Pass

**Row-Row**

- **Initial**
  - Mated-----10000 Meg  $\Omega$  ----- Pass
  - Unmated -----10000 Meg  $\Omega$  ----- Pass
- **Thermal**
  - Mated-----10000 Meg  $\Omega$  ----- Pass
  - Unmated -----10000 Meg  $\Omega$  ----- Pass
- **Humidity**
  - Mated-----10000 Meg  $\Omega$  ----- Pass
  - Unmated -----10000 Meg  $\Omega$  ----- Pass
  - Unmated -----10000 Meg  $\Omega$  ----- Pass

**Dielectric Withstanding Voltage minimums, DWV**

- **Minimums**
  - Breakdown Voltage----- 1000 VAC
  - Test Voltage -----750 VAC
  - Working Voltage -----250 VAC

**Pin - Pin**

- **Initial DWV** -----Passed
- **Thermal DWV**-----Passed
- **Humidity DWV**-----Passed


**Row-Row**

- **Initial DWV** -----Passed
- **Thermal DWV**-----Passed
- **Humidity DWV**-----Passed

### DATA SUMMARIES


#### TEMPERATURE RISE (Current Carrying Capacity, CCC):

- 1) High quality thermocouples whose temperature slopes track one another were used for temperature monitoring.
- 2) The thermocouples were placed at a location to sense the maximum temperature generated during testing.
- 3) Temperature readings recorded are those for which three successive readings, 15 minutes apart, differ less than 1° C (computer controlled data acquisition).
- 4) Adjacent contacts were powered:
  - a. Linear configuration with 2 adjacent power conductors/contacts powered





### DATA SUMMARIES

337665  
2 (2x1) Signal Pins Powered in Series  
Part Numbers: PTF-125-01-L-D/PTT-125-01-L-D



### DATA SUMMARIES

b. Linear configuration with 4 adjacent power conductors/contacts powered




### DATA SUMMARIES


c. Linear configuration with 6 adjacent power conductors/contacts powered

337665  
 6 (2x3) Signal Pins Powered in Series  
 Part Numbers: PTF-125-01-L-D/PTT-125-01-L-D

*Current Rating per Contact (30 Deg. Rise, 20% Derated) = 3.0 Amps*



337665  
 6 (2x3) Signal Pins Powered in Series  
 Part Numbers: PTF-125-01-L-D/PTT-125-01-L-D





### DATA SUMMARIES

d. Linear configuration with 8 adjacent power conductors/contacts powered

337665  
 8 (2x4) Signal Pins Powered in Series  
 Part Numbers: PTF-125-01-L-D/PTT-125-01-L-D


*Current Rating per Contact (30 Deg. Rise, 20% Derated) = 2.8 Amps*




### DATA SUMMARIES

e. Linear configuration with all adjacent power conductors/contacts powered

337665  
 All (2x25) Signal Pins Powered in Series  
 Part Numbers: PTF-125-01-L-D/PTT-125-01-L-D



337665  
 All (2x25) Signal Pins Powered in Series  
 Part Numbers: PTF-125-01-L-D/PTT-125-01-L-D



**DATA SUMMARIES****MATING/UNMATING FORCE:****Thermal aging (PTF-125-01-L-D/PTT-125-01-L-D):**

|                | Initial      |             |              |             | After Thermals |             |              |             |
|----------------|--------------|-------------|--------------|-------------|----------------|-------------|--------------|-------------|
|                | Mating       |             | Unmating     |             | Mating         |             | Unmating     |             |
|                | Newton's     | Force (Lbs) | Newton's     | Force (Lbs) | Newton's       | Force (Lbs) | Newton's     | Force (Lbs) |
| Minimum        | 34.87        | 7.84        | 35.01        | 7.87        | 27.93          | 6.28        | 23.57        | 5.30        |
| Maximum        | 41.14        | 9.25        | 41.01        | 9.22        | 37.59          | 8.45        | 36.78        | 8.27        |
| <b>Average</b> | <b>37.67</b> | <b>8.47</b> | <b>37.55</b> | <b>8.44</b> | <b>33.02</b>   | <b>7.42</b> | <b>31.29</b> | <b>7.04</b> |
| St Dev         | 2.38         | 0.54        | 1.87         | 0.42        | 2.87           | 0.65        | 4.43         | 1.00        |
| Count          | 8            | 8           | 8            | 8           | 8              | 8           | 8            | 8           |

**Mating/Unmating durability(PTF-125-01-L-D/PTT-125-01-L-D):**

|                | Initial          |              |              |              | After 25 Cycles |              |              |              |
|----------------|------------------|--------------|--------------|--------------|-----------------|--------------|--------------|--------------|
|                | Mating           |              | Unmating     |              | Mating          |              | Unmating     |              |
|                | Newton's         | Force (Lbs)  | Newton's     | Force (Lbs)  | Newton's        | Force (Lbs)  | Newton's     | Force (Lbs)  |
| Minimum        | 33.67            | 7.57         | 32.92        | 7.40         | 38.25           | 8.60         | 40.25        | 9.05         |
| Maximum        | 50.66            | 11.39        | 48.75        | 10.96        | 60.27           | 13.55        | 54.58        | 12.27        |
| <b>Average</b> | <b>40.80</b>     | <b>9.17</b>  | <b>40.50</b> | <b>9.11</b>  | <b>48.36</b>    | <b>10.87</b> | <b>46.33</b> | <b>10.42</b> |
| St Dev         | 5.29             | 1.19         | 6.10         | 1.37         | 7.92            | 1.78         | 5.08         | 1.14         |
| Count          | 8                | 8            | 8            | 8            | 8               | 8            | 8            | 8            |
|                | After 50 Cycles  |              |              |              | After 75 Cycles |              |              |              |
|                | Mating           |              | Unmating     |              | Mating          |              | Unmating     |              |
|                | Newton's         | Force (Lbs)  | Newton's     | Force (Lbs)  | Newton's        | Force (Lbs)  | Newton's     | Force (Lbs)  |
| Minimum        | 48.79            | 10.97        | 46.48        | 10.45        | 53.58           | 12.05        | 50.40        | 11.33        |
| Maximum        | 68.28            | 15.35        | 57.33        | 12.89        | 72.64           | 16.33        | 60.67        | 13.64        |
| <b>Average</b> | <b>55.06</b>     | <b>12.38</b> | <b>51.21</b> | <b>11.51</b> | <b>59.73</b>    | <b>13.43</b> | <b>55.54</b> | <b>12.49</b> |
| St Dev         | 7.02             | 1.58         | 3.94         | 0.89         | 6.84            | 1.54         | 3.88         | 0.87         |
| Count          | 8                | 8            | 8            | 8            | 8               | 8            | 8            | 8            |
|                | After 100 Cycles |              |              |              | After Humidity  |              |              |              |
|                | Mating           |              | Unmating     |              | Mating          |              | Unmating     |              |
|                | Newton's         | Force (Lbs)  | Newton's     | Force (Lbs)  | Newton's        | Force (Lbs)  | Newton's     | Force (Lbs)  |
| Minimum        | 58.80            | 13.22        | 52.80        | 11.87        | 45.77           | 10.29        | 41.14        | 9.25         |
| Maximum        | 76.64            | 17.23        | 65.39        | 14.70        | 50.89           | 11.44        | 49.24        | 11.07        |
| <b>Average</b> | <b>64.23</b>     | <b>14.44</b> | <b>59.37</b> | <b>13.35</b> | <b>48.29</b>    | <b>10.86</b> | <b>47.00</b> | <b>10.57</b> |
| St Dev         | 6.29             | 1.41         | 4.32         | 0.97         | 1.87            | 0.42         | 2.59         | 0.58         |
| Count          | 8                | 8            | 8            | 8            | 8               | 8            | 8            | 8            |

**DATA SUMMARIES Continued****Mating & Unmating basic:**

PTF-150-01-L-D/PTT-150-01-L-D

|                | Initial          |              |          |              | After 25 Cycles |              |          |              |
|----------------|------------------|--------------|----------|--------------|-----------------|--------------|----------|--------------|
|                | Mating           |              | Unmating |              | Mating          |              | Unmating |              |
|                | Newton's         | Force (Lbs)  | Newton's | Force (Lbs)  | Newton's        | Force (Lbs)  | Newton's | Force (Lbs)  |
| Minimum        | 82.96            | 18.65        | 64.76    | 14.56        | 73.66           | 16.56        | 72.95    | 16.40        |
| Maximum        | 93.01            | 20.91        | 88.92    | 19.99        | 103.37          | 23.24        | 101.73   | 22.87        |
| <b>Average</b> | 88.22            | <b>19.83</b> | 81.30    | <b>18.28</b> | 94.42           | <b>21.23</b> | 91.27    | <b>20.52</b> |
| St Dev         | 3.77             | 0.85         | 7.58     | 1.70         | 9.66            | 2.17         | 8.58     | 1.93         |
| Count          | 8                | 8            | 8        | 8            | 8               | 8            | 8        | 8            |
|                | After 50 Cycles  |              |          |              | After 75 Cycles |              |          |              |
|                | Mating           |              | Unmating |              | Mating          |              | Unmating |              |
|                | Newton's         | Force (Lbs)  | Newton's | Force (Lbs)  | Newton's        | Force (Lbs)  | Newton's | Force (Lbs)  |
| Minimum        | 80.95            | 18.20        | 79.09    | 17.78        | 89.72           | 20.17        | 87.36    | 19.64        |
| Maximum        | 112.22           | 25.23        | 110.22   | 24.78        | 118.85          | 26.72        | 115.16   | 25.89        |
| <b>Average</b> | 102.98           | <b>23.15</b> | 99.89    | <b>22.46</b> | 110.73          | <b>24.89</b> | 105.51   | <b>23.72</b> |
| St Dev         | 10.34            | 2.32         | 9.28     | 2.09         | 9.78            | 2.20         | 8.52     | 1.91         |
| Count          | 8                | 8            | 8        | 8            | 8               | 8            | 8        | 8            |
|                | After 100 Cycles |              |          |              |                 |              |          |              |
|                | Mating           |              | Unmating |              |                 |              |          |              |
|                | Newton's         | Force (Lbs)  | Newton's | Force (Lbs)  |                 |              |          |              |
| Minimum        | 98.52            | 22.15        | 97.90    | 22.01        |                 |              |          |              |
| Maximum        | 124.99           | 28.10        | 118.58   | 26.66        |                 |              |          |              |
| <b>Average</b> | 116.92           | <b>26.29</b> | 111.18   | <b>25.00</b> |                 |              |          |              |
| St Dev         | 8.41             | 1.89         | 6.85     | 1.54         |                 |              |          |              |
| Count          | 8                | 8            | 8        | 8            |                 |              |          |              |


**DATA SUMMARIES Continued**

PTF-105-01-L-D/PTT-105-01-L-D

|                | Initial          |             |          |             | After 25 Cycles |             |          |             |
|----------------|------------------|-------------|----------|-------------|-----------------|-------------|----------|-------------|
|                | Mating           |             | Unmating |             | Mating          |             | Unmating |             |
|                | Newton's         | Force (Lbs) | Newton's | Force (Lbs) | Newton's        | Force (Lbs) | Newton's | Force (Lbs) |
| Minimum        | 6.98             | 1.57        | 6.36     | 1.43        | 7.70            | 1.73        | 7.43     | 1.67        |
| Maximum        | 8.41             | 1.89        | 8.63     | 1.94        | 12.50           | 2.81        | 12.19    | 2.74        |
| <b>Average</b> | 7.58             | <b>1.71</b> | 7.34     | <b>1.65</b> | 8.91            | <b>2.00</b> | 8.85     | <b>1.99</b> |
| St Dev         | 0.52             | 0.12        | 0.91     | 0.20        | 1.58            | 0.36        | 1.61     | 0.36        |
| Count          | 8                | 8           | 8        | 8           | 8               | 8           | 8        | 8           |
|                | After 50 Cycles  |             |          |             | After 75 Cycles |             |          |             |
|                | Mating           |             | Unmating |             | Mating          |             | Unmating |             |
|                | Newton's         | Force (Lbs) | Newton's | Force (Lbs) | Newton's        | Force (Lbs) | Newton's | Force (Lbs) |
| Minimum        | 8.50             | 1.91        | 8.01     | 1.80        | 9.43            | 2.12        | 9.03     | 2.03        |
| Maximum        | 13.17            | 2.96        | 12.45    | 2.80        | 13.43           | 3.02        | 12.94    | 2.91        |
| <b>Average</b> | 9.87             | <b>2.22</b> | 9.79     | <b>2.20</b> | 10.89           | <b>2.45</b> | 10.76    | <b>2.42</b> |
| St Dev         | 1.65             | 0.37        | 1.65     | 0.37        | 1.43            | 0.32        | 1.64     | 0.37        |
| Count          | 8                | 8           | 8        | 8           | 8               | 8           | 8        | 8           |
|                | After 100 Cycles |             |          |             |                 |             |          |             |
|                | Mating           |             | Unmating |             |                 |             |          |             |
|                | Newton's         | Force (Lbs) | Newton's | Force (Lbs) |                 |             |          |             |
| Minimum        | 10.54            | 2.37        | 9.47     | 2.13        |                 |             |          |             |
| Maximum        | 13.57            | 3.05        | 13.26    | 2.98        |                 |             |          |             |
| <b>Average</b> | 11.79            | <b>2.65</b> | 11.56    | <b>2.60</b> |                 |             |          |             |
| St Dev         | 1.18             | 0.26        | 1.33     | 0.30        |                 |             |          |             |
| Count          | 8                | 8           | 8        | 8           |                 |             |          |             |

### DATA SUMMARIES Continued

#### Mating/Unmating Data for 5, 25 and 50 Position PTF/PTT




### DATA SUMMARIES Continued

**Normal force:**

| Initial         | Deflections in inches Forces in Grams |               |               |               |               |               |               |               |               |               |            |
|-----------------|---------------------------------------|---------------|---------------|---------------|---------------|---------------|---------------|---------------|---------------|---------------|------------|
|                 | <u>0.0003</u>                         | <u>0.0005</u> | <u>0.0008</u> | <u>0.0011</u> | <u>0.0014</u> | <u>0.0016</u> | <u>0.0019</u> | <u>0.0022</u> | <u>0.0024</u> | <u>0.0027</u> | <i>SET</i> |
| <b>Averages</b> | 10.08                                 | 23.06         | 37.43         | 46.59         | 60.53         | 74.58         | 83.38         | 96.77         | 111.05        | 123.56        | 0.0000     |
| <b>Min</b>      | 0.10                                  | 9.20          | 22.40         | 32.60         | 47.40         | 62.10         | 76.80         | 89.00         | 101.00        | 114.90        | 0.0000     |
| <b>Max</b>      | 14.60                                 | 30.40         | 46.10         | 54.80         | 71.80         | 85.00         | 95.30         | 109.30        | 124.70        | 133.30        | 0.0002     |
| <b>St. Dev</b>  | 5.101                                 | 5.767         | 6.922         | 6.125         | 6.299         | 5.781         | 5.252         | 5.448         | 5.633         | 4.791         | 0.0001     |
| <b>Count</b>    | 12                                    | 12            | 12            | 12            | 12            | 12            | 12            | 12            | 12            | 12            | 12         |

| After Thermals  | Deflections in inches Forces in Grams |               |               |               |               |               |               |               |               |               |            |
|-----------------|---------------------------------------|---------------|---------------|---------------|---------------|---------------|---------------|---------------|---------------|---------------|------------|
|                 | <u>0.0003</u>                         | <u>0.0005</u> | <u>0.0008</u> | <u>0.0011</u> | <u>0.0014</u> | <u>0.0016</u> | <u>0.0019</u> | <u>0.0022</u> | <u>0.0024</u> | <u>0.0027</u> | <i>SET</i> |
| <b>Averages</b> | 0.03                                  | 0.39          | 1.93          | 4.69          | 21.07         | 36.37         | 47.45         | 61.86         | 77.12         | 91.17         | 0.0007     |
| <b>Min</b>      | -0.10                                 | -0.10         | -0.10         | -0.10         | 11.40         | 25.10         | 38.20         | 49.00         | 66.60         | 78.40         | 0.0001     |
| <b>Max</b>      | 0.50                                  | 4.30          | 15.00         | 22.20         | 37.90         | 50.90         | 59.40         | 75.10         | 86.10         | 100.70        | 0.0009     |
| <b>St. Dev</b>  | 0.172                                 | 1.243         | 4.658         | 7.046         | 7.916         | 8.226         | 7.147         | 7.909         | 6.929         | 6.176         | 0.0002     |
| <b>Count</b>    | 12                                    | 12            | 12            | 12            | 12            | 12            | 12            | 12            | 12            | 12            | 12         |



**DATA SUMMARIES Continued****Compliant pin Insertion/withdraw force:****PTF- HASL 0.027" C-159**

| Cycle 1                 |      | Cycle 3                 |      |
|-------------------------|------|-------------------------|------|
| Insertion Force Summary |      | Insertion Force Summary |      |
| Minimum                 | 7.58 | Minimum                 | 5.78 |
| Maximum                 | 8.89 | Maximum                 | 9.71 |
| Average                 | 8.27 | Average                 | 7.10 |
| St. Dev.                | 0.33 | St. Dev.                | 0.67 |
|                         |      |                         |      |
| Cycle 1                 |      | Cycle 3                 |      |
| Retention Force Summary |      | Retention Force Summary |      |
| Minimum                 | 3.53 | Minimum                 | 3.52 |
| Maximum                 | 5.51 | Maximum                 | 5.01 |
| Average                 | 4.76 | Average                 | 4.41 |
| St. Dev.                | 0.48 | St. Dev.                | 0.39 |

**PTF- HASL 0.033" C-159**


| Cycle 1                 |      | Cycle 3                 |      |
|-------------------------|------|-------------------------|------|
| Insertion Force Summary |      | Insertion Force Summary |      |
| Minimum                 | 4.25 | Minimum                 | 4.23 |
| Maximum                 | 5.89 | Maximum                 | 5.34 |
| Average                 | 5.11 | Average                 | 4.71 |
| St. Dev.                | 0.38 | St. Dev.                | 0.25 |
|                         |      |                         |      |
| Cycle 1                 |      | Cycle 3                 |      |
| Retention Force Summary |      | Retention Force Summary |      |
| Minimum                 | 3.00 | Minimum                 | 2.68 |
| Maximum                 | 3.70 | Maximum                 | 3.54 |
| Average                 | 3.31 | Average                 | 3.13 |
| St. Dev.                | 0.19 | St. Dev.                | 0.21 |

**PTF- ENIG 0.033" C-159**

| Cycle 1                 |      | Cycle 3                 |      |
|-------------------------|------|-------------------------|------|
| Insertion Force Summary |      | Insertion Force Summary |      |
| Minimum                 | 4.91 | Minimum                 | 4.37 |
| Maximum                 | 5.90 | Maximum                 | 5.01 |
| Average                 | 5.32 | Average                 | 4.69 |
| St. Dev.                | 0.23 | St. Dev.                | 0.17 |
|                         |      |                         |      |
| Cycle 1                 |      | Cycle 3                 |      |
| Retention Force Summary |      | Retention Force Summary |      |
| Minimum                 | 1.15 | Minimum                 | 2.68 |
| Maximum                 | 3.37 | Maximum                 | 4.84 |
| Average                 | 2.40 | Average                 | 3.54 |
| St. Dev.                | 0.60 | St. Dev.                | 0.47 |

**DATA SUMMARIES Continued**

**Compliant pin summary graph- PTF**



**DATA SUMMARIES Continued****PTT-HASL 0.027" T-1S47**

| Cycle 1                 |       | Cycle 3                 |       |
|-------------------------|-------|-------------------------|-------|
| Insertion Force Summary |       | Insertion Force Summary |       |
| Minimum                 | 10.70 | Minimum                 | 9.00  |
| Maximum                 | 12.48 | Maximum                 | 11.92 |
| Average                 | 11.87 | Average                 | 10.37 |
| St. Dev.                | 0.45  | St. Dev.                | 0.65  |
|                         |       |                         |       |
| Cycle 1                 |       | Cycle 3                 |       |
| Retention Force Summary |       | Retention Force Summary |       |
| Minimum                 | 7.10  | Minimum                 | 5.30  |
| Maximum                 | 8.88  | Maximum                 | 7.67  |
| Average                 | 8.06  | Average                 | 6.78  |
| St. Dev.                | 0.51  | St. Dev.                | 0.56  |

**PTT-HASL 0.033" T-1S47**


| Cycle 1                 |      | Cycle 3                 |      |
|-------------------------|------|-------------------------|------|
| Insertion Force Summary |      | Insertion Force Summary |      |
| Minimum                 | 7.35 | Minimum                 | 5.68 |
| Maximum                 | 9.63 | Maximum                 | 8.38 |
| Average                 | 8.45 | Average                 | 7.17 |
| St. Dev.                | 0.47 | St. Dev.                | 0.61 |
|                         |      |                         |      |
| Cycle 1                 |      | Cycle 3                 |      |
| Retention Force Summary |      | Retention Force Summary |      |
| Minimum                 | 5.09 | Minimum                 | 3.28 |
| Maximum                 | 7.82 | Maximum                 | 5.92 |
| Average                 | 6.23 | Average                 | 4.99 |
| St. Dev.                | 0.74 | St. Dev.                | 0.53 |

**PTT-ENIG 0.033" T-1S47**

| Cycle 1                 |      | Cycle 3                 |      |
|-------------------------|------|-------------------------|------|
| Insertion Force Summary |      | Insertion Force Summary |      |
| Minimum                 | 7.79 | Minimum                 | 6.08 |
| Maximum                 | 9.09 | Maximum                 | 7.89 |
| Average                 | 8.30 | Average                 | 7.10 |
| St. Dev.                | 0.37 | St. Dev.                | 0.45 |
|                         |      |                         |      |
| Cycle 1                 |      | Cycle 3                 |      |
| Retention Force Summary |      | Retention Force Summary |      |
| Minimum                 | 3.37 | Minimum                 | 2.14 |
| Maximum                 | 6.57 | Maximum                 | 4.09 |
| Average                 | 4.51 | Average                 | 3.27 |
| St. Dev.                | 0.57 | St. Dev.                | 0.50 |

## DATA SUMMARIES Continued

## Compliant pin summary graph- PTT



**DATA SUMMARIES Continued****INSULATION RESISTANCE (IR):**

|                 | Pin to Pin |         |         |
|-----------------|------------|---------|---------|
|                 | Mated      | Unmated | Unmated |
| Minimum         | PTF/PTT    | PTF     | PTT     |
| <b>Initial</b>  | 10000      | 10000   | 10000   |
| <b>Thermal</b>  | 10000      | 10000   | 10000   |
| <b>Humidity</b> | 10000      | 10000   | 10000   |

|                 | Row to Row |         |         |
|-----------------|------------|---------|---------|
|                 | Mated      | Unmated | Unmated |
| Minimum         | PTF/PTT    | PTF     | PTT     |
| <b>Initial</b>  | 10000      | 10000   | 10000   |
| <b>Thermal</b>  | 10000      | 10000   | 10000   |
| <b>Humidity</b> | 10000      | 10000   | 10000   |

**DIELECTRIC WITHSTANDING VOLTAGE (DWV):**

| Voltage Rating Summary    |         |
|---------------------------|---------|
| Minimum                   | PTF/PTT |
| <b>Break Down Voltage</b> | 1000    |
| <b>Test Voltage</b>       | 750     |
| <b>Working Voltage</b>    | 250     |

| Pin to Pin                         |        |
|------------------------------------|--------|
| <b>Initial Test Voltage</b>        | Passed |
| <b>After Thermal Test Voltage</b>  | Passed |
| <b>After Humidity Test Voltage</b> | Passed |

| Row to Row                         |        |
|------------------------------------|--------|
| <b>Initial Test Voltage</b>        | Passed |
| <b>After Thermal Test Voltage</b>  | Passed |
| <b>After Humidity Test Voltage</b> | Passed |

**DATA SUMMARIES Continued**

**LLCR Durability:**

- 1) A total of 192 points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
  - a.  $\leq +5.0$  mOhms:----- Stable
  - b.  $+5.1$  to  $+10.0$  mOhms:----- Minor
  - c.  $+10.1$  to  $+15.0$  mOhms:----- Acceptable
  - d.  $+15.1$  to  $+50.0$  mOhms:----- Marginal
  - e.  $+50.1$  to  $+2000$  mOhms----- Unstable
  - f.  $>+2000$  mOhms:----- Open Failure
- 5) The following guidelines are used to categorize the changes in LLCR for compliant pin only
  - a.  $\leq +1.0$  mOhms:----- Stable
  - b.  $> +1.0$  mOhms:----- Unstable

| LLCR Measurement Summaries by Pin Type |                       |                         |                         |                       |
|--|-----------------------|-------------------------|-------------------------|-----------------------|
| Date                                   | 11/4/2014             | 11/6/2014               | 11/26/2014              | 12/10/2014            |
| Room Temp (Deg C)                      | 22                    | 22                      | 22                      | 23                    |
| Rel Humidity (%)                       | 56                    | 47                      | 52                      | 54                    |
| Technician                             | Peter Chen            | Peter Chen              | Peter Chen              | Peter Chen            |
| mOhm values                            | <b>Actual Initial</b> | <b>Delta 100 Cycles</b> | <b>Delta Therm Shck</b> | <b>Delta Humidity</b> |
| Pin Type 1: Signal                     |                       |                         |                         |                       |
| Average                                | 4.07                  | 0.11                    | 0.15                    | 0.16                  |
| St. Dev.                               | 0.14                  | 0.10                    | 0.15                    | 0.16                  |
| Min                                    | 3.82                  | 0.00                    | 0.00                    | 0.00                  |
| Max                                    | 4.53                  | 0.56                    | 1.07                    | 0.82                  |
| Summary Count                          | 192                   | 192                     | 192                     | 192                   |
| Total Count                            | 192                   | 192                     | 192                     | 192                   |

| LLCR Delta Count by Category |            |                     |                      |                      |                        |          |
|------------------------------|------------|---------------------|----------------------|----------------------|------------------------|----------|
|                              | Stable     | Minor               | Acceptable           | Marginal             | Unstable               | Open     |
| mOhms                        | $\leq 5$   | $>5 \ \& \ \leq 10$ | $>10 \ \& \ \leq 15$ | $>15 \ \& \ \leq 50$ | $>50 \ \& \ \leq 1000$ | $>1000$  |
| <b>100 Cycles</b>            | <b>192</b> | <b>0</b>            | <b>0</b>             | <b>0</b>             | <b>0</b>               | <b>0</b> |
| <b>Therm Shck</b>            | <b>192</b> | <b>0</b>            | <b>0</b>             | <b>0</b>             | <b>0</b>               | <b>0</b> |
| <b>Humidity</b>              | <b>192</b> | <b>0</b>            | <b>0</b>             | <b>0</b>             | <b>0</b>               | <b>0</b> |

**DATA SUMMARIES Continued****PTF Compliant LLCR (ENIG 0.033"):**

| <b>LLCR Measurement Summaries by Pin Type</b> |                |              |                   |                 |
|---|----------------|--------------|-------------------|-----------------|
| Date  | 11/4/2014      |              | 11/26/2014        | 12/10/2014      |
| Room Temp (Deg C)                             | 22             |              | 21                | 22              |
| Rel Humidity (%)                              | 56             |              | 51                | 54              |
| Technician                                    | Peter Chen     |              | Peter Chen        | Peter Chen      |
| mOhm values                                   | <b>Actual</b>  | <b>Delta</b> | <b>Delta</b>      | <b>Delta</b>    |
|   | <b>Initial</b> |              | <b>Therm Shck</b> | <b>Humidity</b> |
| <b>Pin Type 1: Signal</b>                     |                |              |                   |                 |
| Average                                       | 0.12           |              | 0.04              | 0.05            |
| St. Dev.                                      | 0.33           |              | 0.03              | 0.03            |
| Min   | 0.07           |              | 0.00              | 0.01            |
| Max   | 0.18           |              | 0.09              | 0.11            |
| Summary Count                                 | 30             |              | 30                | 30              |
| Total Count                                   | 30             |              | 30                | 30              |

| <b>LLCR Delta Count by Category</b> |        |           |            |            |              |       |
|-------------------------------------|--------|-----------|------------|------------|--------------|-------|
| mOhms                               | Stable | Minor     | Acceptable | Marginal   | Unstable     | Open  |
|                                     | <=5    | >5 & <=10 | >10 & <=15 | >15 & <=50 | >50 & <=1000 | >1000 |
| Therm Shck                          | 30     | 0         | 0          | 0          | 0            | 0     |
| Humidity                            | 30     | 0         | 0          | 0          | 0            | 0     |

**PTT Compliant LLCR (ENIG 0.033"):**

| <b>LLCR Measurement Summaries by Pin Type</b> |                |              |                   |                 |
|---|----------------|--------------|-------------------|-----------------|
| Date  | 11/4/2014      |              | 11/26/2014        | 12/10/2014      |
| Room Temp (Deg C)                             | 22             |              | 21                | 23              |
| Rel Humidity (%)                              | 56             |              | 51                | 54              |
| Technician                                    | Peter Chen     |              | Peter Chen        | Peter Chen      |
| mOhm values                                   | <b>Actual</b>  | <b>Delta</b> | <b>Delta</b>      | <b>Delta</b>    |
|   | <b>Initial</b> |              | <b>Therm Shck</b> | <b>Humidity</b> |
| <b>Pin Type 1: Signal</b>                     |                |              |                   |                 |
| Average                                       | 0.13           |              | 0.04              | 0.04            |
| St. Dev.                                      | 0.24           |              | 0.03              | 0.03            |
| Min   | 0.10           |              | 0.00              | 0.00            |
| Max   | 0.18           |              | 0.09              | 0.12            |
| Summary Count                                 | 30             |              | 30                | 30              |
| Total Count                                   | 30             |              | 30                | 30              |

| <b>LLCR Delta Count by Category</b> |        |           |            |            |              |       |
|-------------------------------------|--------|-----------|------------|------------|--------------|-------|
| mOhms                               | Stable | Minor     | Acceptable | Marginal   | Unstable     | Open  |
|                                     | <=5    | >5 & <=10 | >10 & <=15 | >15 & <=50 | >50 & <=1000 | >1000 |
| Therm Shck                          | 30     | 0         | 0          | 0          | 0            | 0     |
| Humidity                            | 30     | 0         | 0          | 0          | 0            | 0     |

**DATA SUMMARIES Continued**

**LLCR thermal aging**

- 1) A total of 192 points were measured
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
  - a.  $\leq +5.0$  mOhms:----- Stable
  - b.  $+5.1$  to  $+10.0$  mOhms:----- Minor
  - c.  $+10.1$  to  $+15.0$  mOhms:----- Acceptable
  - d.  $+15.1$  to  $+50.0$  mOhms:----- Marginal
  - e.  $+50.1$  to  $+2000$  mOhms ----- Unstable
  - f.  $>+2000$  mOhms:----- Open Failure
- 5) The following guidelines are used to categorize the changes in LLCR for compliant pin only
  - a.  $\leq +1.0$  mOhms:----- Stable
  - b.  $> +1.0$  mOhms: ----- Unstable

| <b>LLCR Measurement Summaries by Pin Type</b> |                       |                      |              |              |
|---|-----------------------|----------------------|--------------|--------------|
| Date  | 11/7/2014             | 11/24/2014           |              |              |
| Room Temp (Deg C)                             | 22                    | 21                   |              |              |
| Rel Humidity (%)                              | 48                    | 54                   |              |              |
| Technician                                    | Peter Chen            | Peter Chen           |              |              |
| <b>mOhm values</b>                            | <b>Actual Initial</b> | <b>Delta Thermal</b> | <b>Delta</b> | <b>Delta</b> |
| <b>Pin Type 1: Signal</b>                     |                       |                      |              |              |
| Average                                       | 4.06                  | 0.18                 |              |              |
| St. Dev.                                      | 0.24                  | 0.24                 |              |              |
| Min   | 3.43                  | 0.00                 |              |              |
| Max   | 5.73                  | 1.69                 |              |              |
| Summary Count                                 | 192                   | 192                  |              |              |
| Total Count                                   | 192                   | 192                  |              |              |

| <b>LLCR Delta Count by Category</b> |               |                     |                      |                      |                        |             |
|-------------------------------------|---------------|---------------------|----------------------|----------------------|------------------------|-------------|
|                                     | <b>Stable</b> | <b>Minor</b>        | <b>Acceptable</b>    | <b>Marginal</b>      | <b>Unstable</b>        | <b>Open</b> |
| <b>mOhms</b>                        | $\leq 5$      | $>5 \ \& \ \leq 10$ | $>10 \ \& \ \leq 15$ | $>15 \ \& \ \leq 50$ | $>50 \ \& \ \leq 1000$ | $>1000$     |
| <b>Thermal</b>                      | <b>192</b>    | <b>0</b>            | <b>0</b>             | <b>0</b>             | <b>0</b>               | <b>0</b>    |

**DATA SUMMARIES Continued****PTF Compliant LLCR (ENIG 0.033"):**

| <b>LLCR Measurement Summaries by Pin Type</b> |                       |                      |              |              |
|---|-----------------------|----------------------|--------------|--------------|
| Date  | 11/6/2014             | 11/24/2014           |              |              |
| Room Temp (Deg C)                             | 22                    | 23                   |              |              |
| Rel Humidity (%)                              | 56                    | 53                   |              |              |
| Technician                                    | Peter Chen            | Peter Chen           |              |              |
| <b>mOhm values</b>                            | <b>Actual Initial</b> | <b>Delta Thermal</b> | <b>Delta</b> | <b>Delta</b> |
| <b>Pin Type 1: Signal</b>                     |                       |                      |              |              |
| Average                                       | 0.12                  | 0.03                 |              |              |
| St. Dev.                                      | 0.03                  | 0.02                 |              |              |
| Min   | 0.07                  | 0.00                 |              |              |
| Max   | 0.18                  | 0.07                 |              |              |
| Summary Count                                 | 30                    | 30                   |              |              |
| Total Count                                   | 30                    | 30                   |              |              |

| <b>LLCR Delta Count by Category</b> |        |           |            |            |              |       |
|-------------------------------------|--------|-----------|------------|------------|--------------|-------|
|                                     | Stable | Minor     | Acceptable | Marginal   | Unstable     | Open  |
| mOhms                               | <=5    | >5 & <=10 | >10 & <=15 | >15 & <=50 | >50 & <=1000 | >1000 |
| Thermal                             | 30     | 0         | 0          | 0          | 0            | 0     |

**PTT Compliant LLCR (ENIG 0.033"):**

| <b>LLCR Measurement Summaries by Pin Type</b> |                       |                      |              |              |
|---|-----------------------|----------------------|--------------|--------------|
| Date  | 11/6/2014             | 11/24/2014           |              |              |
| Room Temp (Deg C)                             | 22                    | 22                   |              |              |
| Rel Humidity (%)                              | 56                    | 52                   |              |              |
| Technician                                    | Peter Chen            | Peter Chen           |              |              |
| <b>mOhm values</b>                            | <b>Actual Initial</b> | <b>Delta Thermal</b> | <b>Delta</b> | <b>Delta</b> |
| <b>Pin Type 1: Signal</b>                     |                       |                      |              |              |
| Average                                       | 0.12                  | 0.03                 |              |              |
| St. Dev.                                      | 0.02                  | 0.02                 |              |              |
| Min   | 0.08                  | 0.00                 |              |              |
| Max   | 0.17                  | 0.09                 |              |              |
| Summary Count                                 | 30                    | 30                   |              |              |
| Total Count                                   | 30                    | 30                   |              |              |

| <b>LLCR Delta Count by Category</b> |        |           |            |            |              |       |
|-------------------------------------|--------|-----------|------------|------------|--------------|-------|
|                                     | Stable | Minor     | Acceptable | Marginal   | Unstable     | Open  |
| mOhms                               | <=5    | >5 & <=10 | >10 & <=15 | >15 & <=50 | >50 & <=1000 | >1000 |
| Thermal                             | 30     | 0         | 0          | 0          | 0            | 0     |

**DATA SUMMARIES Continued**

**LLCR GAS TIGHT:**

- 1) A total of 192 points were measured
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
  - a.  $\leq +5.0$  mOhms:----- Stable
  - b.  $+5.1$  to  $+10.0$  mOhms:----- Minor
  - c.  $+10.1$  to  $+15.0$  mOhms:----- Acceptable
  - d.  $+15.1$  to  $+50.0$  mOhms:----- Marginal
  - e.  $+50.1$  to  $+2000$  mOhms:----- Unstable
  - f.  $>+2000$  mOhms:----- Open Failure
- 5) The following guidelines are used to categorize the changes in LLCR for compliant pin only
  - a.  $\leq +1.0$  mOhms:----- Stable
  - b.  $> +1.0$  mOhms:----- Unstable

| <b>LLCR Measurement Summaries by Pin Type</b> |                       |                         |              |              |
|---|-----------------------|-------------------------|--------------|--------------|
| Date  | 11/13/2014            | 11/20/2014              |              |              |
| Room Temp (Deg C)                             | 23                    | 22                      |              |              |
| Rel Humidity (%)                              | 54                    | 54                      |              |              |
| Technician                                    | Peter Chen            | Peter Chen              |              |              |
| <b>mOhm values</b>                            | <b>Actual Initial</b> | <b>Delta Acid Vapor</b> | <b>Delta</b> | <b>Delta</b> |
| <b>Pin Type 1: Signal</b>                     |                       |                         |              |              |
| Average                                       | 4.05                  | 0.28                    |              |              |
| St. Dev.                                      | 0.17                  | 0.15                    |              |              |
| Min   | 3.64                  | 0.01                    |              |              |
| Max   | 4.67                  | 0.77                    |              |              |
| Summary Count                                 | 192                   | 192                     |              |              |
| Total Count                                   | 192                   | 192                     |              |              |

| <b>LLCR Delta Count by Category</b> |            |                  |                   |                   |                     |          |
|-------------------------------------|------------|------------------|-------------------|-------------------|---------------------|----------|
|                                     | Stable     | Minor            | Acceptable        | Marginal          | Unstable            | Open     |
| mOhms                               | $\leq 5$   | $>5$ & $\leq 10$ | $>10$ & $\leq 15$ | $>15$ & $\leq 50$ | $>50$ & $\leq 1000$ | $>1000$  |
| <b>Acid Vapor</b>                   | <b>192</b> | <b>0</b>         | <b>0</b>          | <b>0</b>          | <b>0</b>            | <b>0</b> |

**DATA SUMMARIES Continued****PTF Compliant LLCR** (ENIG 0.033" C-159):

| <b>LLCR Measurement Summaries by Pin Type</b> |                |                   |              |              |
|---|----------------|-------------------|--------------|--------------|
| Date  | 11/13/2014     | 11/20/2014        |              |              |
| Room Temp (Deg C)                             | 23             | 22                |              |              |
| Rel Humidity (%)                              | 54             | 51                |              |              |
| Technician                                    | Peter Chen     | Peter Chen        |              |              |
| <b>mOhm values</b>                            | <b>Actual</b>  | <b>Delta</b>      | <b>Delta</b> | <b>Delta</b> |
|   | <b>Initial</b> | <b>Acid Vapor</b> |              |              |
| <b>Pin Type 1: Signal</b>                     |                |                   |              |              |
| Average                                       | 0.12           | 0.03              |              |              |
| St. Dev.                                      | 0.02           | 0.02              |              |              |
| Min   | 0.08           | 0.00              |              |              |
| Max   | 0.17           | 0.09              |              |              |
| Summary Count                                 | 30             | 30                |              |              |
| Total Count                                   | 30             | 30                |              |              |

| <b>LLCR Delta Count by Category</b> |           |           |            |            |              |          |
|-------------------------------------|-----------|-----------|------------|------------|--------------|----------|
|                                     | Stable    | Minor     | Acceptable | Marginal   | Unstable     | Open     |
| mOhms                               | <=5       | >5 & <=10 | >10 & <=15 | >15 & <=50 | >50 & <=1000 | >1000    |
| <b>Acid Vapor</b>                   | <b>30</b> | <b>0</b>  | <b>0</b>   | <b>0</b>   | <b>0</b>     | <b>0</b> |

**PTT Compliant LLCR** (ENIG 0.033" T-1S47):

| <b>LLCR Measurement Summaries by Pin Type</b> |                |                   |              |              |
|---|----------------|-------------------|--------------|--------------|
| Date  | 11/13/2014     | 11/20/2014        |              |              |
| Room Temp (Deg C)                             | 23             | 21                |              |              |
| Rel Humidity (%)                              | 54             | 51                |              |              |
| Technician                                    | Peter Chen     | Peter Chen        |              |              |
| <b>mOhm values</b>                            | <b>Actual</b>  | <b>Delta</b>      | <b>Delta</b> | <b>Delta</b> |
|   | <b>Initial</b> | <b>Acid Vapor</b> |              |              |
| <b>Pin Type 1: Signal</b>                     |                |                   |              |              |
| Average                                       | 0.12           | 0.04              |              |              |
| St. Dev.                                      | 0.03           | 0.02              |              |              |
| Min   | 0.07           | 0.00              |              |              |
| Max   | 0.18           | 0.09              |              |              |
| Summary Count                                 | 30             | 30                |              |              |
| Total Count                                   | 30             | 30                |              |              |

| <b>LLCR Delta Count by Category</b> |           |           |            |            |              |          |
|-------------------------------------|-----------|-----------|------------|------------|--------------|----------|
|                                     | Stable    | Minor     | Acceptable | Marginal   | Unstable     | Open     |
| mOhms                               | <=5       | >5 & <=10 | >10 & <=15 | >15 & <=50 | >50 & <=1000 | >1000    |
| <b>Acid Vapor</b>                   | <b>30</b> | <b>0</b>  | <b>0</b>   | <b>0</b>   | <b>0</b>     | <b>0</b> |

**DATA SUMMARIES Continued**

**LLCR Shock Vib:**

- 1) A total of 192 points were measured
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets.*
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
  - a.  $\leq +5.0$  mOhms:----- Stable
  - b.  $+5.1$  to  $+10.0$  mOhms:----- Minor
  - c.  $+10.1$  to  $+15.0$  mOhms:----- Acceptable
  - d.  $+15.1$  to  $+50.0$  mOhms:----- Marginal
  - e.  $+50.1$  to  $+2000$  mOhms:----- Unstable
  - f.  $>+2000$  mOhms:----- Open Failure
- 5) The following guidelines are used to categorize the changes in LLCR for compliant pin only
  - c.  $\leq +1.0$  mOhms:----- Stable
  - d.  $> +1.0$  mOhms:----- Unstable

| <b>LLCR Measurement Summaries by Pin Type</b> |                       |                        |              |              |
|---|-----------------------|------------------------|--------------|--------------|
| Date  | 2/26/2015             | 3/5/2015               |              |              |
| Room Temp (Deg C)                             | 22                    | 22                     |              |              |
| Rel Humidity (%)                              | 36                    | 36                     |              |              |
| Technician                                    | Tony Wagoner          | Tony Wagoner           |              |              |
| <b>mOhm values</b>                            | <b>Actual Initial</b> | <b>Delta Shock-Vib</b> | <b>Delta</b> | <b>Delta</b> |
| <b>Pin Type 1: Signal</b>                     |                       |                        |              |              |
| Average                                       | 4.00                  | 0.05                   |              |              |
| St. Dev.                                      | 0.14                  | 0.05                   |              |              |
| Min   | 3.60                  | 0.00                   |              |              |
| Max   | 4.75                  | 0.31                   |              |              |
| Summary Count                                 | 192                   | 192                    |              |              |
| Total Count                                   | 192                   | 192                    |              |              |

| <b>LLCR Delta Count by Category</b> |                            |  |   |   |   |                              |
|-------------------------------------|----------------------------|--|---|---|---|------------------------------|
|                                     | <b>Stable</b>              | <b>Minor</b>   | <b>Acceptable</b>                                     | <b>Marginal</b>                                       | <b>Unstable</b>   | <b>Open</b>                  |
| <b>mOhms</b>                        | <b><math>\leq 5</math></b> | <b><math>&gt;5</math> &amp; <math>\leq 10</math></b> | <b><math>&gt;10</math> &amp; <math>\leq 15</math></b> | <b><math>&gt;15</math> &amp; <math>\leq 50</math></b> | <b><math>&gt;50</math> &amp; <math>\leq 1000</math></b> | <b><math>&gt;1000</math></b> |
| <b>Shock-Vib</b>                    | <b>192</b>                 | <b>0</b>   | <b>0</b>  | <b>0</b>  | <b>0</b>  | <b>0</b>                     |

**DATA SUMMARIES Continued****PTF Compliant LLCR (ENIG 0.033"):**

| <b>LLCR Measurement Summaries by Pin Type</b> |                       |                        |              |              |
|---|-----------------------|------------------------|--------------|--------------|
| Date  | 2/26/2015             | 3/5/2015               |              |              |
| Room Temp (Deg C)                             | 22                    | 22                     |              |              |
| Rel Humidity (%)                              | 36                    | 36                     |              |              |
| Technician                                    | Tony Wagoner          | Tony Wagoner           |              |              |
| <b>mOhm values</b>                            | <b>Actual Initial</b> | <b>Delta Shock-Vib</b> | <b>Delta</b> | <b>Delta</b> |
| <b>Pin Type 1: Signal</b>                     |                       |                        |              |              |
| Average                                       | 0.05                  | 0.02                   |              |              |
| St. Dev.                                      | 0.02                  | 0.01                   |              |              |
| Min   | 0.02                  | 0.00                   |              |              |
| Max   | 0.13                  | 0.05                   |              |              |
| Summary Count                                 | 29                    | 30                     |              |              |
| Total Count                                   | 30                    | 30                     |              |              |

| <b>LLCR Delta Count by Category</b> |               |                            |                             |                             |                               |                 |
|-------------------------------------|---------------|----------------------------|-----------------------------|-----------------------------|-------------------------------|-----------------|
|                                     | <b>Stable</b> | <b>Minor</b>               | <b>Acceptable</b>           | <b>Marginal</b>             | <b>Unstable</b>               | <b>Open</b>     |
| <b>mOhms</b>                        | <b>&lt;=5</b> | <b>&gt;5 &amp; &lt;=10</b> | <b>&gt;10 &amp; &lt;=15</b> | <b>&gt;15 &amp; &lt;=50</b> | <b>&gt;50 &amp; &lt;=1000</b> | <b>&gt;1000</b> |
| <b>Shock-Vib</b>                    | <b>30</b>     | <b>0</b>                   | <b>0</b>                    | <b>0</b>                    | <b>0</b>                      | <b>0</b>        |

**PTT Compliant LLCR (ENIG 0.033"):**

| <b>LLCR Measurement Summaries by Pin Type</b> |                       |                        |              |              |
|---|-----------------------|------------------------|--------------|--------------|
| Date  | 2/26/2015             | 3/5/2015               |              |              |
| Room Temp (Deg C)                             | 22                    | 22                     |              |              |
| Rel Humidity (%)                              | 36                    | 36                     |              |              |
| Technician                                    | Tony Wagoner          | Tony Wagoner           |              |              |
| <b>mOhm values</b>                            | <b>Actual Initial</b> | <b>Delta Shock-Vib</b> | <b>Delta</b> | <b>Delta</b> |
| <b>Pin Type 1: Signal</b>                     |                       |                        |              |              |
| Average                                       | 0.04                  | 0.01                   |              |              |
| St. Dev.                                      | 0.03                  | 0.01                   |              |              |
| Min   | 0.01                  | 0.00                   |              |              |
| Max   | 0.10                  | 0.05                   |              |              |
| Summary Count                                 | 30                    | 30                     |              |              |
| Total Count                                   | 30                    | 30                     |              |              |

| <b>LLCR Delta Count by Category</b> |               |                            |                             |                             |                               |                 |
|-------------------------------------|---------------|----------------------------|-----------------------------|-----------------------------|-------------------------------|-----------------|
|                                     | <b>Stable</b> | <b>Minor</b>               | <b>Acceptable</b>           | <b>Marginal</b>             | <b>Unstable</b>               | <b>Open</b>     |
| <b>mOhms</b>                        | <b>&lt;=5</b> | <b>&gt;5 &amp; &lt;=10</b> | <b>&gt;10 &amp; &lt;=15</b> | <b>&gt;15 &amp; &lt;=50</b> | <b>&gt;50 &amp; &lt;=1000</b> | <b>&gt;1000</b> |
| <b>Shock-Vib</b>                    | <b>30</b>     | <b>0</b>                   | <b>0</b>                    | <b>0</b>                    | <b>0</b>                      | <b>0</b>        |

**DATA SUMMARIES Continued**

**Shock Vibration Event Detection:**

| <b>Shock and Vibration Event Detection Summary</b> |                           |
|--|---------------------------|
| Contacts tested                                    | 60                        |
| Test Condition                                     | C, 100g's, 6ms, Half-Sine |
| Shock Events                                       | 0                         |
| Test Condition                                     | V-B, 7.56 rms g           |
| Vibration Events                                   | 0                         |
| <b>Total Events</b>                                | <b>0</b>                  |

**EQUIPMENT AND CALIBRATION SCHEDULES****Equipment #:** HZ-HPM-01**Description:** IR/DWV Tester**Manufacturer:** AN9636H**Model:** AN9636H**Serial #:** 089601091**Accuracy:** Last Cal: 2014-7-6, Next Cal: 2015-7-5**Equipment #:** HZ-TCT-01**Description:** Normal force analyzer**Manufacturer:** Mecmesin Multitester**Model:** Mecmesin Multitester 2.5-i**Serial #:** 08-1049-04**Accuracy:** Last Cal: 2014-4-28, Next Cal: 2015-4-27**Equipment #:** HZ-OV-01**Description:** Oven**Manufacturer:** Huida**Model:** CS101-1E**Serial #:** CS101-1E-B**Accuracy:** Last Cal: 2014-12-14, Next Cal: 2015-12-13**Equipment #:** HZ-THC-01**Description:** Humidity transmitter**Manufacturer:** Thermtron**Model:** HMM30C**Serial #:** D0240037**Accuracy:** Last Cal: 2014-3-3, Next Cal: 2015-3-2**Equipment #:** HZ-TSC-01**Description:** Thermal Shock transmitter**Manufacturer:** CSZ**Model:** 10-VT14994**Serial #:** VTS-3-6-6-SC/AC**Accuracy:** Last Cal: 2014-11-1, Next Cal: 2015-11-1**Equipment #:** HZ-MO-05**Description:** Micro-ohmmeter**Manufacturer:** Keithley**Model:** 3706**Serial #:** 297288**Accuracy:** Last Cal: 2014-8-6, Next Cal: 2015-8-5

**EQUIPMENT AND CALIBRATION SCHEDULES****Equipment #:** MO-02**Description:** Multimeter /Data Acquisition System**Manufacturer:** Keithley**Model:** 2700**Serial #:** 0780546**Accuracy:** Last Cal: 2014-6-16, Next Cal: 2015-6-16**Equipment #:** PS-01**Description:** Power Supply**Manufacturer:** Hewlett Packard**Model:** 6033A**Serial #:** 3329A-07330**Accuracy:** Last Cal: 2014-6-12, Next Cal: 2015-6-12**Equipment #:** PS-02**Description:** Power Supply**Manufacturer:** Hewlett Packard**Model:** 6033A**Serial #:** 2847A-04167**Accuracy:** Last Cal: 2014-6-12, Next Cal: 2015-6-12**Equipment #:** SVC-01**Description:** Shock & Vibration Table**Manufacturer:** Data Physics**Model:** LE-DSA-10-20K**Serial #:** 10037**Accuracy:** See Manual

... Last Cal: 2014-11-31, Next Cal: 2015-11-31

**Equipment #:** ACLM-01**Description:** Accelerometer**Manufacturer:** PCB Piezotronics**Model:** 352C03**Serial #:** 115819**Accuracy:** See Manual

... Last Cal: 2014-07-9, Next Cal: 2015-7-9

**Equipment #:** ED-03**Description:** Event Detector**Manufacturer:** Analysis Tech**Model:** 32EHD**Serial #:** 1100604**Accuracy:** See Manual

... Last Cal: 2014-06-4, Next Cal: 2015-06-4