


Project Number: Design Qualification Test Report	Tracking Code: 479958_Report_Rev_1
Requested by: Catie Eichhorn	Date: 11/12/2015
Part #: SAL1-127-01-S-S-A-TR/EDGE CARD	Tech: Peter Chen
Part description: SAL1/EDGE CARD	Qty to test: 60
Test Start: 05/25/2015	Test Completed: 07/10/2015



DESIGN QUALIFICATION TEST REPORT

SAL1/EDGE CARD
SAL1-127-01-S-S-A-TR/EDGE CARD

REVISION HISTORY

DATA	REV.NUM.	DESCRIPTION	ENG
11/05/2015	1	Initial Issue	PC

CERTIFICATION

All instruments and measuring equipment were calibrated to National Institute for Standards and Technology (NIST) traceable standards according to ISO 10012-1 and ANSI/NCSL 2540-1, as applicable.

All contents contained herein are the property of Samtec. No portion of this report, in part or in full shall be reproduced without prior written approval of Samtec.

SCOPE

To perform the following tests: Design Qualification test. Please see test plan.

APPLICABLE DOCUMENTS

Standards: EIA Publication 364

TEST SAMPLES AND PREPARATION

- 1) All materials were manufactured in accordance with the applicable product specification.
- 2) All test samples were identified and encoded to maintain traceability throughout the test sequences.
- 3) After soldering, the parts to be used for LLCR and DWV/IR testing were cleaned according to TLWI-0001.
- 4) Either an automated cleaning procedure or an ultrasonic cleaning procedure may be used.
- 5) The automated procedure is used with aqueous compatible soldering materials.
- 6) Parts not intended for testing LLCR and DWV/IR are visually inspected and cleaned if necessary.
- 7) Any additional preparation will be noted in the individual test sequences.
- 8) Solder Information: Lead free
- 9) Samtec Test PCBs used: PCB-106742-TST-XX/ PCB-106743-TST-XX/ PCB-106744-TST-XX.

FLOWCHARTS

Gas Tight

Group 1
 SAL1-127-01-S-S-A-TR
 0.056" EDGE CARD
 8 Assemblies
 Lower Board Thickness

Step Description

1. LLCR (2)
Max Delta = 15 mOhm
2. Gas Tight (1)
3. LLCR (2)
Max Delta = 15 mOhm

(1) Gas Tight = EIA-364-36

(2) LLCR = EIA-364-23
Open Circuit Voltage = 20 mV Max
Test Current = 100 mA Max

Normal Force

Group 1
 SAL1-127-01-S-S-A-TR
 8 Contacts Minimum
 Signal Without Thermals

Step Description

1. Contact Gaps
2. Normal Force (1)
Deflection = 0.015 "
Expected Force at Max Deflection = 90 g

Group 2
 SAL1-127-01-S-S-A-TR
 0.068" EDGE CARD
 8 Contacts Minimum
 Signal With Thermals

Step Description

1. Contact Gaps
2. Thermal Age (2)
3. Contact Gaps
4. Normal Force (1)
Deflection = 0.015 "
Expected Force at Max Deflection = 90 g

(1) Normal Force = EIA-364-04

(2) Thermal Age = EIA-364-17

Test Condition = 4 (105°C)
Time Condition = B (250 Hours)

FLOWCHARTS Continued**Thermal Aging**

<u>Group 1</u>		<u>Group 2</u>	
Step	Description	Step	Description
1.	Contact Gaps	1.	Contact Gaps
2.	Mating/Unmating Force ⁽²⁾	2.	Mating/Unmating Force ⁽²⁾
3.	LLCR ⁽¹⁾ Max Delta = 15 mOhm	3.	LLCR ⁽¹⁾ Max Delta = 15 mOhm
4.	Thermal Age ⁽³⁾	4.	Thermal Age ⁽³⁾
5.	LLCR ⁽¹⁾ Max Delta = 15 mOhm	5.	LLCR ⁽¹⁾ Max Delta = 15 mOhm
6.	Mating/Unmating Force ⁽²⁾	6.	Mating/Unmating Force ⁽²⁾
7.	Contact Gaps	7.	Contact Gaps

(1) LLCR = EIA-364-23
Open Circuit Voltage = 20 mV Max
Test Current = 100 mA Max

(2) Mating/Unmating Force = EIA-364-13

(3) Thermal Age = EIA-364-17
Test Condition = 4 (105°C)
Time Condition = B (250 Hours)

FLOWCHARTS Continued

Mating/Unmating/Durability

Group 1		Group 2		Group 3		Group 4	
Step	Description	Step	Description	Step	Description	Step	Description
1.	Contact Gaps	1.	Contact Gaps	1.	Contact Gaps	1.	Contact Gaps
2.	LLCR (2) Max Delta = 15 mOhm	2.	Mating/Unmating Force (3)	2.	Mating/Unmating Force (3)	2.	LLCR (2) Max Delta = 15 mOhm
3.	Mating/Unmating Force (3)	3.	Cycles Quantity = 25 Cycles	3.	Cycles Quantity = 25 Cycles	3.	Mating/Unmating Force (3)
4.	Cycles Quantity = 25 Cycles	4.	Mating/Unmating Force (3)	4.	Mating/Unmating Force (3)	4.	Cycles Quantity = 25 Cycles
5.	Mating/Unmating Force (3)	5.	Cycles Quantity = 25 Cycles	5.	Cycles Quantity = 25 Cycles	5.	Mating/Unmating Force (3)
6.	Cycles Quantity = 25 Cycles	6.	Mating/Unmating Force (3)	6.	Mating/Unmating Force (3)	6.	Cycles Quantity = 25 Cycles
7.	Mating/Unmating Force (3)	7.	Cycles Quantity = 25 Cycles	7.	Cycles Quantity = 25 Cycles	7.	Mating/Unmating Force (3)
8.	Cycles Quantity = 25 Cycles	8.	Mating/Unmating Force (3)	8.	Mating/Unmating Force (3)	8.	Cycles Quantity = 25 Cycles
9.	Mating/Unmating Force (3)	9.	Cycles Quantity = 25 Cycles	9.	Cycles Quantity = 25 Cycles	9.	Mating/Unmating Force (3)
10.	Cycles Quantity = 25 Cycles	10.	Mating/Unmating Force (3)	10.	Mating/Unmating Force (3)	10.	Cycles Quantity = 25 Cycles
11.	Mating/Unmating Force (3)					11.	Mating/Unmating Force (3)
12.	Contact Gaps					12.	Contact Gaps
13.	LLCR (2) Max Delta = 15 mOhm					13.	LLCR (2) Max Delta = 15 mOhm
14.	Thermal Shock (4)					14.	Thermal Shock (4)
15.	LLCR (2) Max Delta = 15 mOhm					15.	LLCR (2) Max Delta = 15 mOhm
16.	Humidity (1)					16.	Humidity (1)
17.	LLCR (2) Max Delta = 15 mOhm					17.	LLCR (2) Max Delta = 15 mOhm
18.	Mating/Unmating Force (3)					18.	Mating/Unmating Force (3)

(1) Humidity = EIA-364-31

Test Condition = B (240 Hours)

Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)

Test Exceptions: ambient pre-condition and delete steps 7a and 17a

(2) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(3) Mating/Unmating Force = EIA-364-13

(4) Thermal Shock = EIA-364-32

Exposure Time at Temperature Extremes = 1/2 Hour

Method A, Test Condition = I (-55°C to +85°C)

Test Duration = A-3 (100 Cycles)

FLOWCHARTS Continued**IR/DWV****Pin-to-Pin**

Group 1
 SAL1-127-01-S-S-A-TR
 0.056" EDGE CARD
 2 Assemblies

Group 2
 SAL1-127-01-S-S-A-TR
 2 Assemblies

Group 3
 SAL1-127-01-S-S-A-TR
 0.056" EDGE CARD
 2 Assemblies

Step **Description**
 1. DWV Breakdown ⁽²⁾

Step **Description**
 1. DWV Breakdown ⁽²⁾

Step **Description**
 1. IR ⁽⁴⁾
 2. DWV at Test Voltage ⁽¹⁾
 3. Thermal Shock ⁽⁵⁾
 4. IR ⁽⁴⁾
 5. DWV at Test Voltage ⁽¹⁾
 6. Humidity ⁽³⁾
 7. IR ⁽⁴⁾
 8. DWV at Test Voltage ⁽¹⁾

Pin-to-Closest Metallic Hardware

Group 4
 SAL1-127-01-S-S-A-TR
 0.056" EDGE CARD
 2 Assemblies

Group 5
 SAL1-127-01-S-S-A-TR
 2 Assemblies

Group 6
 SAL1-127-01-S-S-A-TR
 0.056" EDGE CARD
 2 Assemblies

Step **Description**
 1. DWV Breakdown ⁽²⁾

Step **Description**
 1. DWV Breakdown ⁽²⁾

Step **Description**
 1. IR ⁽⁴⁾
 2. DWV at Test Voltage ⁽¹⁾
 3. Thermal Shock ⁽⁵⁾
 4. IR ⁽⁴⁾
 5. DWV at Test Voltage ⁽¹⁾
 6. Humidity ⁽³⁾
 7. IR ⁽⁴⁾
 8. DWV at Test Voltage ⁽¹⁾

(1) DWV at Test Voltage = EIA-364-20
 Test Condition = 1 (Sea Level)
 DWV test voltage is equal to 75% of the lowest breakdown voltage
 Test voltage applied for 60 seconds

(2) DWV Breakdown = EIA-364-20
 Test Condition = 1 (Sea Level)
 DWV test voltage is equal to 75% of the lowest breakdown voltage
 Test voltage applied for 60 seconds

(3) Humidity = EIA-364-31
 Test Condition = B (240 Hours)
 Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)
 Test Exceptions: ambient pre-condition and delete steps 7a and 7b

(4) IR = EIA-364-21
 Test Condition = 500 Vdc, 2 Minutes Max

(5) Thermal Shock = EIA-364-32
 Exposure Time at Temperature Extremes = 1/2 Hour
 Method A, Test Condition = I (-55°C to +85°C)
 Test Duration = A-3 (100 Cycles)

FLOWCHARTS Continued

Current Carrying Capacity

Group 1
 SAL1-140-01-S-S-A-TR
 0.056" EDGE CARD
 2 Pins Powered
 Signal

Step **Description**
 1. CCC (1)
 Rows = 2
 Number of Positions = 1

Group 2
 SAL1-140-01-S-S-A-TR
 0.056" EDGE CARD
 4 Pins Powered
 Signal

Step **Description**
 1. CCC (1)
 Rows = 2
 Number of Positions = 2

Group 3
 SAL1-140-01-S-S-A-TR
 0.056" EDGE CARD
 6 Pins Powered
 Signal

Step **Description**
 1. CCC (1)
 Rows = 2
 Number of Positions = 3

Group 4
 SAL1-140-01-S-S-A-TR
 0.056" EDGE CARD
 8 Pins Powered
 Signal

Step **Description**
 1. CCC (1)
 Rows = 2
 Number of Positions = 4

Group 5
 SAL1-140-01-S-S-A-TR
 0.056" EDGE CARD
 80 Pins Powered
 Signal

Step **Description**
 1. CCC (1)
 Rows = 2
 Number of Positions = 40

(1) CCC = EIA-364-70

Method 2, Temperature Rise Versus Current Curve

(TIN PLATING) - Tabulate calculated current at RT, 65°C, 75°C and 95°C after derating 20% and based on 105°C

(GOLD PLATING) - Tabulate calculated current at RT, 85°C, 95°C and 115°C after derating 20% and based on 125°C

FLOWCHARTS Continued**Mechanical Shock/Random Vibration/LLCR**

Group 1		Group 2	
SAL1-127-01-S-S-A-TR		SAL1-127-01-S-S-A-TR	
0.068" EDGE CARD		0.056" EDGE CARD	
8 Assemblies		8 Assemblies	
Upper Board Thickness		Lower Board Thickness	
Step	Description	Step	Description
1.	LLCR ⁽¹⁾ Max Delta = 15 mOhm	1.	LLCR ⁽¹⁾ Max Delta = 15 mOhm
2.	Mechanical Shock ⁽²⁾	2.	Mechanical Shock ⁽²⁾
3.	Random Vibration ⁽³⁾	3.	Random Vibration ⁽³⁾
4.	LLCR ⁽¹⁾ Max Delta = 15 mOhm	4.	LLCR ⁽¹⁾ Max Delta = 15 mOhm

(1) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max
Test Current = 100 mA Max

(2) Mechanical Shock = EIA-364-27

Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)
Number of Shocks = 3 Per Direction, Per Axis, 18 Total

(3) Random Vibration = EIA-364-28

Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

Mechanical Shock/Random Vibration/Event Detection

Group 1	
SAL1-127-01-S-S-A-TR	
0.056" EDGE CARD	
60 Points	
Lower Board Thickness	
Step	Description
1.	Nanosecond Event Detection (Mechanical Shock) ⁽¹⁾
2.	Nanosecond Event Detection (Random Vibration) ⁽²⁾

(1) Nanosecond Event Detection (Mechanical Shock)

Use EIA-364-87 for Nanosecond Event Detection:
Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-27 for Mechanical Shock:
Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)
Number of Shocks = 3 Per Direction, Per Axis, 18 Total

(2) Nanosecond Event Detection (Random Vibration)

Use EIA-364-87 for Nanosecond Event Detection:

Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-28 for Random Vibration:
Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

ATTRIBUTE DEFINITIONS

The following is a brief, simplified description of attributes.

THERMAL SHOCK:

- 1) EIA-364-32, *Thermal Shock (Temperature Cycling) Test Procedure for Electrical Connectors.*
- 2) Test Condition 1: -55°C to +85°C
- 3) Test Time: ½ hour dwell at each temperature extreme
- 4) Number of Cycles: 100
- 5) All test samples are pre-conditioned at ambient.
- 6) All test samples are exposed to environmental stressing in the mated condition.

THERMAL:

- 1) EIA-364-17, *Temperature Life with or without Electrical Load Test Procedure for Electrical Connectors.*
- 2) Test Condition 4 at 105° C
- 3) Test Time Condition B for 250 hours.
- 4) All test samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

HUMIDITY:

- 1) Reference document: EIA-364-31, *Humidity Test Procedure for Electrical Connectors.*
- 2) Test Condition B, 240 Hours.
- 3) Method III, +25° C to + 65° C, 90% to 98% Relative Humidity excluding sub-cycles 7a and 7b.
- 4) All samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

MECHANICAL SHOCK (Specified Pulse):

- 1) Reference document: EIA-364-27, *Mechanical Shock Test Procedure for Electrical Connectors*
- 2) Test Condition C
- 3) Peak Value: 100 G
- 4) Duration: 6 Milliseconds
- 5) Wave Form: Half Sine
- 6) Velocity: 12.3 ft/s
- 7) Number of Shocks: 3 Shocks / Direction, 3 Axis (18 Total)

VIBRATION:

- 1) Reference document: EIA-364-28, *Vibration Test Procedure for Electrical Connectors*
- 2) Test Condition V, Letter B
- 3) Power Spectral Density: 0.04 G² / Hz
- 4) G 'RMS': 7.56
- 5) Frequency: 50 to 2000 Hz
- 6) Duration: 2.0 Hours per axis (3 axis total)

NANOSECOND-EVENT DETECTION:

- 1) Reference document: EIA-364-87, *Nanosecond-Event Detection for Electrical Connectors*
- 2) Prior to test, the samples were characterized to assure the low nanosecond event being monitored will trigger the detector.
- 3) After characterization it was determined the test samples could be monitored for 50 nanosecond events

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes.

MATING/UNMATING:

- 1) Reference document: EIA-364-13, *Mating and Unmating Forces Test Procedure for Electrical Connectors*.
- 2) The full insertion position was to within 0.003" to 0.004" of the plug bottoming out in the receptacle to prevent damage to the system under test.
- 3) One of the mating parts is secured to a floating X-Y table to prevent damage during cycling.

TEMPERATURE RISE (Current Carrying Capacity, CCC):

- 1) EIA-364-70, *Temperature Rise versus Current Test Procedure for Electrical Connectors and Sockets*.
- 2) When current passes through a contact, the temperature of the contact increases as a result of I^2R (resistive) heating.
- 3) The number of contacts being investigated plays a significant part in power dissipation and therefore temperature rise.
- 4) The size of the temperature probe can affect the measured temperature.
- 5) Copper traces on PC boards will contribute to temperature rise:
 - a. Self heating (resistive)
 - b. Reduction in heat sink capacity affecting the heated contacts
- 6) A de-rating curve, usually 20%, is calculated.
- 7) Calculated de-rated currents at four temperature points are reported:
 - a. Ambient
 - b. 85°C
 - c. 95°C
 - d. 115°C
- 8) Typically, neighboring contacts (in close proximity to maximize heat build up) are energized.
- 9) The thermocouple (or temperature measuring probe) will be positioned at a location to sense the maximum temperature in the vicinity of the heat generation area.
- 10) A computer program, *TR 803.exe*, ensures accurate stability for data acquisition.
- 11) Hook-up wire cross section is larger than the cross section of any connector leads/PC board traces, jumpers, etc.
- 12) Hook-up wire length is longer than the minimum specified in the referencing standard.

LLCR:

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
 - a. $\leq +5.0 \text{ mOhms}$:----- Stable
 - b. $+5.1 \text{ to } +10.0 \text{ mOhms}$:----- Minor
 - c. $+10.1 \text{ to } +15.0 \text{ mOhms}$:----- Acceptable
 - d. $+15.1 \text{ to } +50.0 \text{ mOhms}$:----- Marginal
 - e. $+50.1 \text{ to } +2000 \text{ mOhms}$:----- Unstable
 - f. $>+2000 \text{ mOhms}$:----- Open Failure

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes.

GAS TIGHT:

To provide method for evaluating the ability of the contacting surfaces in preventing penetration of harsh vapors which might lead to oxide formation that may degrade the electrical performance of the contact system.

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
 - a. $\leq +5.0$ mOhms: ----- Stable
 - b. $+5.1$ to $+10.0$ mOhms: ----- Minor
 - c. $+10.1$ to $+15.0$ mOhms: ----- Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: ----- Marginal
 - e. $+50.1$ to $+2000$ mOhms: ----- Unstable
 - f. $>+2000$ mOhms: ----- Open Failure
- 4) Procedure:
 - a. Reference document: EIA-364-36, *Test Procedure for Determination of Gas-Tight Characteristics for Electrical Connectors, Sockets and/or Contact Systems*.
 - b. Test Conditions:
 - i. Class II--- Mated pairs of contacts assembled to their plastic housings.
 - ii. Reagent grade Nitric Acid shall be used of sufficient volume to saturate the test chamber
 - iii. The ratio of the volume of the test chamber to the surface area of the acid shall be 10:1.
 - iv. The chamber shall be saturated with the vapor for at least 15 minutes before samples are added.
 - v. Exposure time, 55 to 65 minutes.
 - vi. The samples shall be no closer to the chamber walls than 1 inches and no closer to the surface of the acid than 3 inches.
 - vii. The samples shall be dried after exposure for a minimum of 1 hour.
 - viii. Drying temperature 50°C
 - ix. The final LLCR shall be conducted within 1 hour after drying.

NORMAL FORCE (FOR CONTACTS TESTED IN THE HOUSING):

- 1) Reference document: EIA-364-04, *Normal Force Test Procedure for Electrical Connectors*.
- 2) The contacts shall be tested in the connector housing.
- 3) If necessary, a “window” shall be made in the connector body to allow a probe to engage and deflect the contact at the same attitude and distance (plus 0.05 mm [0.002”]) as would occur in actual use.
- 4) The connector housing shall be placed in a holding fixture that does not interfere with or otherwise influence the contact force or deflection.
- 5) Said holding fixture shall be mounted on a floating, adjustable, X-Y table on the base of the Dillon TC², computer controlled test stand with a deflection measurement system accuracy of 5.0 μm (0.0002”).
- 6) The nominal deflection rate shall be 5 mm (0.2”)/minute.
- 7) Unless otherwise noted a minimum of five contacts shall be tested.
- 8) The force/deflection characteristic to load and unload each contact shall be repeated five times.
- 9) The system shall utilize the TC² software in order to acquire and record the test data.
- 10) The permanent set of each contact shall be measured within the TC² software.
- 11) The acquired data shall be graphed with the deflection data on the X-axis and the force data on the Y-axis and a print out will be stored with the Tracking Code paperwork.

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes

INSULATION RESISTANCE (IR):

To determine the resistance of insulation materials to leakage of current through or on the surface of these materials when a DC potential is applied.

- 1) PROCEDURE:
 - a. Reference document: EIA-364-21, *Insulation Resistance Test Procedure for Electrical Connectors*.
 - b. Test Conditions:
 - i. Between Adjacent Contacts or Signal-to-Ground
 - ii. Electrification Time 2.0 minutes
 - iii. Test Voltage (500 VDC) corresponds to calibration settings for measuring resistances.
- 2) MEASUREMENTS:
- 3) When the specified test voltage is applied (VDC), the insulation resistance shall not be less than 5000 megohms.

DIELECTRIC WITHSTANDING VOLTAGE (DWV):

To determine if the sockets can operate at its rated voltage and withstand momentary over potentials due to switching, surges, and other similar phenomenon. Separate samples are used to evaluate the effect of environmental stresses so not to influence the readings from arcing that occurs during the measurement process.

- 1) PROCEDURE:
 - a. Reference document: EIA-364-20, *Withstanding Voltage Test Procedure for Electrical Connectors*.
 - b. Test Conditions:
 - i. Between Adjacent Contacts or Signal-to-Ground
 - ii. Barometric Test Condition 1
 - iii. Rate of Application 500 V/Sec
 - iv. Test Voltage (VAC) until breakdown occurs
- 2) MEASUREMENTS/CALCULATIONS
 - a. The breakdown voltage shall be measured and recorded.
 - b. The dielectric withstand voltage shall be recorded as 75% of the minimum breakdown voltage.
 - c. The working voltage shall be recorded as one-third (1/3) of the dielectric withstand voltage (one-fourth of the breakdown voltage).

RESULTS

Temperature Rise, CCC at a 20% de-rating

- CCC for a 30°C Temperature Rise-----2.9 A per contact with 2 contacts (2x1) powered
- CCC for a 30°C Temperature Rise-----2.4 A per contact with 4 contacts (2x2) powered
- CCC for a 30°C Temperature Rise-----1.9 A per contact with 6 contacts (2x3) powered
- CCC for a 30°C Temperature Rise-----1.8 A per contact with 8 contacts (2x4) powered
- CCC for a 30°C Temperature Rise-----0.9 A per contact with 80 contacts (2x40) powered

Mating – Unmating Forces

Thermal Aging Group (SAL1-127-01-S-S-A-TR/0.056" EDGE CARD)

- **Initial**
 - Mating
 - Min ----- 3.39 Lbs
 - Max----- 4.10 Lbs
 - Unmating
 - Min ----- 2.37 Lbs
 - Max----- 2.79 Lbs
- **After Thermal**
 - Mating
 - Min ----- 3.40 Lbs
 - Max----- 3.96 Lbs
 - Unmating
 - Min ----- 2.28 Lbs
 - Max----- 3.75 Lbs

Thermal Aging Group (SAL1-127-01-S-S-A-TR/0.068" EDGE CARD)

- **Initial**
 - Mating
 - Min ----- 3.29 Lbs
 - Max----- 5.20 Lbs
 - Unmating
 - Min ----- 3.25 Lbs
 - Max----- 4.14 Lbs
- **After Thermal**
 - Mating
 - Min ----- 3.95 Lbs
 - Max----- 5.42 Lbs
 - Unmating
 - Min ----- 4.08 Lbs
 - Max----- 5.80 Lbs

RESULTS Continued

Mating – Unmating Forces

Mating-Unmating Durability Gaps Group (SAL1-127-01-S-S-A-TR/0.056" EDGE CARD)

- **Initial**
 - **Mating**
 - Min ----- 3.24 Lbs
 - Max ----- 4.48 Lbs
 - **Unmating**
 - Min ----- 2.26 Lbs
 - Max ----- 2.87 Lbs
- **After 25 Cycles**
 - **Mating**
 - Min ----- 3.71 Lbs
 - Max ----- 5.54 Lbs
 - **Unmating**
 - Min ----- 2.92 Lbs
 - Max ----- 3.84 Lbs
- **After 50 Cycles**
 - **Mating**
 - Min ----- 3.93 Lbs
 - Max ----- 5.54 Lbs
 - **Unmating**
 - Min ----- 3.32 Lbs
 - Max ----- 4.71 Lbs
- **After 75 Cycles**
 - **Mating**
 - Min ----- 3.97 Lbs
 - Max ----- 5.75 Lbs
 - **Unmating**
 - Min ----- 3.55 Lbs
 - Max ----- 5.25 Lbs
- **After 100 Cycles**
 - **Mating**
 - Min ----- 4.22 Lbs
 - Max ----- 6.05 Lbs
 - **Unmating**
 - Min ----- 3.75 Lbs
 - Max ----- 5.54 Lbs
- **Humidity**
 - **Mating**
 - Min ----- 4.08 Lbs
 - Max ----- 4.98 Lbs
 - **Unmating**
 - Min ----- 3.24 Lbs
 - Max ----- 5.51 Lbs

RESULTS Continued

Mating – Unmating Forces

Mating-Unmating Durability Gaps Group (SAL1-127-01-S-S-A-TR/0.068" EDGE CARD)

- **Initial**
 - **Mating**
 - Min ----- 4.72 Lbs
 - Max ----- 5.61 Lbs
 - **Unmating**
 - Min ----- 3.11 Lbs
 - Max ----- 4.69 Lbs
- **After 25 Cycles**
 - **Mating**
 - Min ----- 6.08 Lbs
 - Max ----- 7.10 Lbs
 - **Unmating**
 - Min ----- 4.79 Lbs
 - Max ----- 7.56 Lbs
- **After 50 Cycles**
 - **Mating**
 - Min ----- 6.31 Lbs
 - Max ----- 7.23 Lbs
 - **Unmating**
 - Min ----- 5.50 Lbs
 - Max ----- 8.12 Lbs
- **After 75 Cycles**
 - **Mating**
 - Min ----- 6.43 Lbs
 - Max ----- 7.34 Lbs
 - **Unmating**
 - Min ----- 6.02 Lbs
 - Max ----- 8.45 Lbs
- **After 100 Cycles**
 - **Mating**
 - Min ----- 6.49 Lbs
 - Max ----- 7.34 Lbs
 - **Unmating**
 - Min ----- 6.35 Lbs
 - Max ----- 8.78 Lbs
- **Humidity**
 - **Mating**
 - Min ----- 5.94 Lbs
 - Max ----- 7.04 Lbs
 - **Unmating**
 - Min ----- 5.47 Lbs
 - Max ----- 8.78 Lbs

RESULTS Continued

Mating – Unmating Forces

Mating-Unmating Basic (SAL1-140-01-S-S-A-TR/0.068" EDGE CARD)

- Initial
 - Mating
 - Min ----- 6.59 Lbs
 - Max----- 7.89 Lbs
 - Unmating
 - Min ----- 5.25 Lbs
 - Max----- 6.95 Lbs
- After 25 Cycles
 - Mating
 - Min ----- 6.25 Lbs
 - Max----- 11.43 Lbs
 - Unmating
 - Min ----- 6.22 Lbs
 - Max----- 10.40 Lbs
- After 50 Cycles
 - Mating
 - Min ----- 8.03 Lbs
 - Max----- 11.81 Lbs
 - Unmating
 - Min ----- 6.91 Lbs
 - Max----- 12.04 Lbs
- After 75 Cycles
 - Mating
 - Min ----- 8.71 Lbs
 - Max----- 12.63 Lbs
 - Unmating
 - Min ----- 7.14 Lbs
 - Max----- 12.07 Lbs
- After 100 Cycles
 - Mating
 - Min ----- 8.94 Lbs
 - Max----- 13.03 Lbs
 - Unmating
 - Min ----- 7.42 Lbs
 - Max----- 12.53 Lbs

RESULTS Continued

Mating – Unmating Forces

Mating-Unmating Basic (SAL1-120-01-S-S-A-TR/0.068" EDGE CARD)

- Initial
 - Mating
 - Min ----- 3.01 Lbs
 - Max ----- 3.52 Lbs
 - Unmating
 - Min ----- 2.88 Lbs
 - Max ----- 3.63 Lbs
- After 25 Cycles
 - Mating
 - Min ----- 3.61 Lbs
 - Max ----- 5.12 Lbs
 - Unmating
 - Min ----- 3.94 Lbs
 - Max ----- 5.17 Lbs
- After 50 Cycles
 - Mating
 - Min ----- 4.59 Lbs
 - Max ----- 5.79 Lbs
 - Unmating
 - Min ----- 3.69 Lbs
 - Max ----- 5.76 Lbs
- After 75 Cycles
 - Mating
 - Min ----- 5.02 Lbs
 - Max ----- 5.95 Lbs
 - Unmating
 - Min ----- 3.47 Lbs
 - Max ----- 6.40 Lbs
- After 100 Cycles
 - Mating
 - Min ----- 5.15 Lbs
 - Max ----- 6.12 Lbs
 - Unmating
 - Min ----- 3.74 Lbs
 - Max ----- 6.75 Lbs

Normal Force at 0.0191 inch deflection

- Initial
 - Min ----- 133.20 gf Set ----- 0.0004 in
 - Max ----- 142.80 gf Set ----- 0.0007 in
- Thermal
 - Min ----- 117.80 gf Set ----- 0.0021 in
 - Max ----- 135.10 gf Set ----- 0.0031 in

RESULTS Continued

Insulation Resistance minimums, IR

Pin to Pin

- Initial
 - Mated ----- 10000 Meg Ω ----- Passed
 - Unmated ----- 10000 Meg Ω ----- Passed
- Thermal Shock
 - Mated ----- 10000 Meg Ω ----- Passed
 - Unmated ----- 10000 Meg Ω ----- Passed
- Humidity
 - Mated ----- 10000 Meg Ω ----- Passed
 - Unmated ----- 10000 Meg Ω ----- Passed

Pin to Closest Metallic Hardware

- Initial
 - Mated ----- 10000 Meg Ω ----- Passed
 - Unmated ----- 10000 Meg Ω ----- Passed
- Thermal Shock
 - Mated ----- 10000 Meg Ω ----- Passed
 - Unmated ----- 10000 Meg Ω ----- Passed
- Humidity
 - Mated ----- 10000 Meg Ω ----- Passed
 - Unmated ----- 10000 Meg Ω ----- Passed

Dielectric Withstanding Voltage minimums, DWV

- Minimums
 - Breakdown Voltage ----- 875 VAC
 - Test Voltage ----- 655 VAC
 - Working Voltage ----- 215 VAC

Pin to Pin

- Initial DWV ----- Passed
- Thermal DWV ----- Passed
- Humidity DWV ----- Passed

Pin to Closest Metallic Hardware

- Initial DWV ----- Passed
- Thermal DWV ----- Passed
- Humidity DWV ----- Passed

RESULTS Continued

LLCR Thermal Aging Group (192 LLCR test points)

SAL1-127-01-S-S-A-TR/0.056" EDGE CARD

- Initial ----- 12.22 mOhms Max
- Thermal
 - <= +5.0 mOhms ----- 192 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
 - >+2000 mOhms ----- 0 Points ----- Open Failure

SAL1-127-01-S-S-A-TR/0.068" EDGE CARD

- Initial ----- 10.52 mOhms Max
- Thermal
 - <= +5.0 mOhms ----- 192 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
 - >+2000 mOhms ----- 0 Points ----- Open Failure

LLCR Mating/Unmating Durability Group (192 LLCR test points)

SAL1-127-01-S-S-A-TR/0.056" EDGE CARD

- Initial ----- 12.28 mOhms Max
- Durability, 100 Cycles
 - <= +5.0 mOhms ----- 192 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
 - >+2000 mOhms ----- 0 Points ----- Open Failure
- Thermal Shock
 - <= +5.0 mOhms ----- 192 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
 - >+2000 mOhms ----- 0 Points ----- Open Failure
- Humidity
 - <= +5.0 mOhms ----- 189 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 3 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
 - >+2000 mOhms ----- 0 Points ----- Open Failure

RESULTS Continued

LLCR Mating/Unmating Durability Group (192 LLCR test points)

SAL1-127-01-S-S-A-TR/0.068" EDGE CARD

- Initial ----- 10.99 mOhms Max
- Durability, 100 Cycles
 - <= +5.0 mOhms ----- 192 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
 - >+2000 mOhms ----- 0 Points ----- Open Failure
- Thermal Shock
 - <= +5.0 mOhms ----- 191 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 1 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
 - >+2000 mOhms ----- 0 Points ----- Open Failure
- Humidity
 - <= +5.0 mOhms ----- 188 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 4 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
 - >+2000 mOhms ----- 0 Points ----- Open Failure

LLCR Gas Tight Group (192 LLCR test points)

SAL1-127-01-S-S-A-TR/0.056" EDGE CARD

- Initial ----- 11.53 mOhms Max
- Gas-Tight
 - <= +5.0 mOhms ----- 192 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
 - >+2000 mOhms ----- 0 Points ----- Open Failure

RESULTS Continued

LLCR Shock & Vibration Group (192 LLCR test points)

SAL1-127-01-S-S-A-TR/0.056" EDGE CARD

- Initial ----- 12.20 mOhms Max
- Shock & Vibration
 - <= +5.0 mOhms ----- 192 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
 - >+2000 mOhms ----- 0 Points ----- Open Failure

SAL1-127-01-S-S-A-TR/0.068" EDGE CARD

- Initial ----- 10.47 mOhms Max
- Shock & Vibration
 - <= +5.0 mOhms ----- 192 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
 - >+2000 mOhms ----- 0 Points ----- Open Failure

Mechanical Shock & Random Vibration:


- Shock
 - No Damage----- ----- Pass
 - 50 Nanoseconds----- ----- Pass
- Vibration
 - No Damage----- ----- Pass
 - 50 Nanoseconds----- ----- Pass


DATA SUMMARIES

TEMPERATURE RISE (Current Carrying Capacity, CCC):

- 1) High quality thermocouples whose temperature slopes track one another were used for temperature monitoring.
- 2) The thermocouples were placed at a location to sense the maximum temperature generated during testing.
- 3) Temperature readings recorded are those for which three successive readings, 15 minutes apart, differ less than 1°C (computer controlled data acquisition).
- 4) Adjacent contacts were powered:



- a. Linear configuration with 2 adjacent conductors/contacts powered



DATA SUMMARIES Continued



DATA SUMMARIES Continued

b. Linear configuration with 4 adjacent conductors/contacts powered





DATA SUMMARIES Continued

c. Linear configuration with 6 adjacent conductors/contacts powered





DATA SUMMARIES Continued

d. Linear configuration with 8 adjacent conductors/contacts powered



DATA SUMMARIES Continued

e. Linear configuration with all adjacent conductors/contacts powered



DATA SUMMARIES Continued**MATING-UNMATING FORCE:**

Thermal Aging Group (SAL1-127-01-S-S-A-TR/0.056" EDGE CARD)

	Initial				After Thermals			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	15.08	3.39	10.54	2.37	15.12	3.40	10.14	2.28
Maximum	18.24	4.10	12.41	2.79	17.61	3.96	16.68	3.75
Average	16.67	3.75	11.06	2.49	16.72	3.76	12.87	2.89
St Dev	1.03	0.23	0.74	0.17	0.88	0.20	2.30	0.52
Count	8	8	8	8	7	7	7	7

Thermal Aging Group (SAL1-127-01-S-S-A-TR/0.068" EDGE CARD)

	Initial				After Thermals			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	16.86	3.79	14.46	3.25	17.57	3.95	18.15	4.08
Maximum	23.13	5.20	18.41	4.14	24.11	5.42	25.80	5.80
Average	20.39	4.58	16.66	3.75	21.29	4.79	22.99	5.17
St Dev	1.80	0.41	1.12	0.25	2.15	0.48	2.53	0.57
Count	8	8	8	8	8	8	8	8

DATA SUMMARIES Continued

Mating-Unmating Durability Gaps Group (SAL1-127-01-S-S-A-TR/0.056"EDGE CARD)

	Initial				After 25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	14.41	3.24	10.05	2.26	16.50	3.71	12.99	2.92
Maximum	19.93	4.48	12.77	2.87	24.64	5.54	17.08	3.84
Average	17.74	3.99	11.50	2.59	21.10	4.74	15.35	3.45
St Dev	1.64	0.37	1.16	0.26	2.56	0.58	1.30	0.29
Count	8	8	8	8	8	8	8	8
	After 50 Cycles				After 75 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	17.48	3.93	14.77	3.32	17.66	3.97	15.79	3.55
Maximum	24.64	5.54	20.95	4.71	25.58	5.75	23.35	5.25
Average	22.36	5.03	18.28	4.11	23.11	5.20	20.58	4.63
St Dev	2.41	0.54	1.79	0.40	2.64	0.59	2.53	0.57
Count	8	8	8	8	8	8	8	8
	After 100 Cycles				After Humidity			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	18.77	4.22	16.68	3.75	18.15	4.08	14.41	3.24
Maximum	26.91	6.05	24.64	5.54	22.15	4.98	24.51	5.51
Average	24.16	5.43	22.45	5.05	20.62	4.64	19.84	4.46
St Dev	2.63	0.59	2.71	0.61	1.31	0.30	3.36	0.75
Count	8	8	8	8	8	8	8	8

DATA SUMMARIES Continued

Mating-Unmating Durability Gaps Group (SAL1-127-01-S-S-A-TR/0.068"EDGE CARD)


	Initial				After 25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	20.99	4.72	13.83	3.11	27.04	6.08	21.31	4.79
Maximum	24.95	5.61	20.86	4.69	31.58	7.10	33.63	7.56
Average	22.63	5.09	17.17	3.86	28.42	6.39	27.42	6.16
St Dev	1.54	0.35	2.41	0.54	1.52	0.34	3.63	0.82
Count	8	8	8	8	8	8	8	8
	After 50 Cycles				After 75 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	28.07	6.31	24.46	5.50	28.60	6.43	26.78	6.02
Maximum	32.16	7.23	36.12	8.12	32.65	7.34	37.59	8.45
Average	29.47	6.63	30.36	6.83	29.97	6.74	31.95	7.18
St Dev	1.34	0.30	3.15	0.71	1.34	0.30	2.96	0.67
Count	8	8	8	8	8	8	8	8
	After 100 Cycles				After Humidity			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	28.87	6.49	28.24	6.35	26.42	5.94	24.33	5.47
Maximum	32.65	7.34	39.05	8.78	31.31	7.04	39.05	8.78
Average	30.26	6.80	32.83	7.38	28.40	6.39	33.38	7.50
St Dev	1.31	0.29	3.33	0.75	1.90	0.43	4.53	1.02
Count	8	8	8	8	8	8	8	8

DATA SUMMARIES Continued**Mating-Unmating Basic (SAL1-140-01-S-S-A-TR/0.068"EDGE CARD)**

	Initial				After 25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	29.31	6.59	23.35	5.25	27.80	6.25	27.67	6.22
Maximum	35.09	7.89	30.91	6.95	50.84	11.43	46.26	10.40
Average	31.59	7.10	25.93	5.83	37.24	8.37	33.12	7.45
St Dev	1.84	0.41	2.78	0.63	7.06	1.59	6.07	1.37
Count	8	8	8	8	8	8	8	8
	After 50 Cycles				After 75 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	35.72	8.03	30.74	6.91	38.74	8.71	31.76	7.14
Maximum	52.53	11.81	53.55	12.04	56.18	12.63	53.69	12.07
Average	41.38	9.30	40.30	9.06	43.73	9.83	44.12	9.92
St Dev	5.87	1.32	6.93	1.56	6.20	1.39	7.26	1.63
Count	8	8	8	8	8	8	8	8
	After 100 Cycles							
	Mating		Unmating					
	Newton	Force (Lbs)	Newton	Force (Lbs)				
Minimum	39.77	8.94	33.00	7.42				
Maximum	57.96	13.03	55.73	12.53				
Average	45.51	10.23	46.58	10.47				
St Dev	6.10	1.37	8.31	1.87				
Count	8	8	8	8				

DATA SUMMARIES Continued**Mating-Unmating Basic (SAL1-120-01-S-S-A-TR/0.068"EDGE CARD)**

	Initial				After 25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	13.39	3.01	12.81	2.88	16.06	3.61	17.53	3.94
Maximum	15.66	3.52	16.15	3.63	22.77	5.12	23.00	5.17
Average	14.25	3.20	14.83	3.33	18.68	4.20	19.24	4.33
St Dev	0.77	0.17	0.99	0.22	2.23	0.50	1.76	0.40
Count	8	8	8	8	8	8	8	8
	After 50 Cycles				After 75 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	20.42	4.59	16.41	3.69	22.33	5.02	15.43	3.47
Maximum	25.75	5.79	25.62	5.76	26.47	5.95	28.47	6.40
Average	22.56	5.07	21.96	4.94	24.02	5.40	23.77	5.34
St Dev	1.85	0.42	3.53	0.79	1.55	0.35	4.16	0.94
Count	8	8	8	8	8	8	8	8
	After 100 Cycles							
	Mating		Unmating					
	Newton	Force (Lbs)	Newton	Force (Lbs)				
Minimum	22.91	5.15	16.64	3.74				
Maximum	27.22	6.12	30.02	6.75				
Average	24.56	5.52	24.45	5.50				
St Dev	1.43	0.32	3.76	0.84				
Count	8	8	8	8				

DATA SUMMARIES Continued**Mating\Unmating Force Comparison****Mating/Unmating Data for 20, 27 and 40 Position SAL1/ 0.068" CARD**

DATA SUMMARIES Continued


NORMAL FORCE (FOR CONTACTS TESTED OUT THE HOUSING):

- 1) Calibrated force gauges are used along with computer controlled positioning equipment.
- 2) For Normal force 8-10 measurements are taken and the averages reported.

Initial	Deflections in inches Forces in Grams										
	0.0019	0.0038	0.0057	0.0076	0.0096	0.0115	0.0134	0.0153	0.0172	0.0191	SET
Averages	16.78	31.44	45.57	60.03	73.88	88.17	100.92	112.83	125.19	137.50	0.0006
Min	15.80	29.90	43.20	58.10	71.10	85.30	97.40	108.50	121.30	133.20	0.0004
Max	18.00	34.40	49.00	62.30	77.80	92.30	104.50	118.40	128.40	142.80	0.0007
St. Dev	0.751	1.241	2.019	1.319	1.880	2.101	2.199	2.780	2.258	2.754	0.0001
Count	12	12	12	12	12	12	12	12	12	12	12

After Thermals	Deflections in inches Forces in Grams										
	0.0019	0.0038	0.0057	0.0076	0.0096	0.0115	0.0134	0.0153	0.0172	0.0191	SET
Averages	0.01	11.63	25.55	38.71	52.34	65.38	78.97	94.13	109.66	125.78	0.0026
Min	-0.10	7.20	21.10	33.00	46.00	58.80	73.20	86.60	103.40	117.80	0.0021
Max	0.10	15.10	28.20	41.80	57.20	69.60	84.30	100.70	118.30	135.10	0.0031
St. Dev	0.090	2.599	2.194	2.506	3.134	3.393	3.637	4.319	4.605	4.966	0.0003
Count	12	12	12	12	12	12	12	12	12	12	12

Normal Force - Average Initial vs Average Thermal



DATA SUMMARIES Continued**INSULATION RESISTANCE (IR):**

	Pin to Pin		
	Mated	Unmated	Unmated
Minimum	SAL1/Card	SAL1	Card
Initial	10000	10000	Not Tested
Thermal	10000	10000	Not Tested
Humidity	10000	10000	Not Tested

	Pin to Closest Metallic Hardware		
	Mated	Unmated	Unmated
Minimum	SAL1/Card	SAL1	Card
Initial	10000	10000	Not Tested
Thermal	10000	10000	Not Tested
Humidity	10000	10000	Not Tested

DIELECTRIC WITHSTANDING VOLTAGE (DWV):

Voltage Rating Summary	
Minimum	SAL1/Card
Break Down Voltage	875
Test Voltage	655
Working Voltage	215

Pin to Pin	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed
After Humidity Test Voltage	Passed

Pin to Closest Metallic Hardware	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed
After Humidity Test Voltage	Passed

DATA SUMMARIES Continued

LLCR Thermal Aging Group

- 1) A total of 192 points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: ----- Stable
 - b. $+5.1$ to $+10.0$ mOhms: ----- Minor
 - c. $+10.1$ to $+15.0$ mOhms: ----- Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: ----- Marginal
 - e. $+50.1$ to $+2000$ mOhms ----- Unstable
 - f. $>+2000$ mOhms: ----- Open Failure

SAL1-127-01-S-S-A-TR/0.056"EDGE CARD

LLCR Measurement Summaries by Pin Type					
mOhm values	Date	6/2/2015	6/16/2015		
	Room Temp (Deg C)	23	23		
	Rel Humidity (%)	56	56		
	Technician	Peter Chen	Peter Chen		
	Actual	Delta	Delta	Delta	
	Initial	Thermal			
	Pin Type 1: Signal				
	Average	9.41	1.66		
	St. Dev.	0.51	1.01		
	Min	8.41	0.03		
	Max	12.22	4.48		
	Summary Count	192	192		
	Total Count	192	192		

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
	≤ 5	$>5 \text{ & } \leq 10$	$>10 \text{ & } \leq 15$	$>15 \text{ & } \leq 50$	$>50 \text{ & } \leq 1000$	>1000
Thermal	192	0	0	0	0	0

DATA SUMMARIES Continued

SAL1-127-01-S-S-A-TR/0.068"EDGE CARD

LLCR Measurement Summaries by Pin Type			
Date	6/2/2015	6/16/2015	
Room Temp (Deg C)	23	23	
Rel Humidity (%)	56	56	
Technician	Peter Chen	Peter Chen	
mOhm values	Actual Initial	Delta Thermal	Delta
Pin Type 1: Signal			
Average	8.87	0.79	
St. Dev.	0.33	0.65	
Min	8.10	0.01	
Max	10.52	4.15	
Summary Count	192	192	
Total Count	192	192	

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
	<=5	>5 & <=10	>10 & <=15	>15 & <=50	>50 & <=1000	>1000
Thermal	192	0	0	0	0	0

DATA SUMMARIES Continued

LLCR Mating/Unmating Durability Group

- 1). A total of 192 points were measured.
- 2). EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3). A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4). The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: ----- Stable
 - b. $+5.1$ to $+10.0$ mOhms: ----- Minor
 - c. $+10.1$ to $+15.0$ mOhms: ----- Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: ----- Marginal
 - e. $+50.1$ to $+2000$ mOhms ----- Unstable
 - f. $> +2000$ mOhms: ----- Open Failure

SAL1-127-01-S-S-A-TR/0.056"EDGE CARD

		LLCR Measurement Summaries by Pin Type			
		5/30/2015	6/3/2015	6/16/2015	7/6/2015
Date	Room Temp (Deg C)	23	23	23	23
	Rel Humidity (%)	56	56	56	56
Technician	Peter Chen	Peter Chen	Peter Chen	Peter Chen	Peter Chen
	Actual Initial	Delta 100 Cycles	Delta Therm Shck	Delta Humidity	
Pin Type 1: Signal					
mOhm values	Average	9.58	0.75	0.93	1.28
	St. Dev.	0.70	0.79	0.78	1.25
	Min	8.57	0.00	0.00	0.00
	Max	12.28	3.81	4.54	5.39
Summary Count	Count	192	192	192	192
	Total Count	192	192	192	192

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
	≤ 5	$>5 \text{ & } \leq 10$	$>10 \text{ & } \leq 15$	$>15 \text{ & } \leq 50$	$>50 \text{ & } \leq 1000$	>1000
100 Cycles	192	0	0	0	0	0
Therm Shck	192	0	0	0	0	0
Humidity	189	3	0	0	0	0

DATA SUMMARIES Continued

SAL1-127-01-S-S-A-TR/0.068"EDGE CARD

		LLCR Measurement Summaries by Pin Type			
		5/30/2015	6/3/2015	6/16/2015	7/6/2015
Room Temp (Deg C)	23	23	23	23	23
Rel Humidity (%)	56	56	56	56	56
Technician	Peter Chen	Peter Chen	Peter Chen	Peter Chen	Peter Chen
mOhm values	Actual Initial	Delta 100 Cycles	Delta Therm Shck	Delta Humidity	
Pin Type 1: Signal					
Average	8.78	0.61	0.82	1.55	
St. Dev.	0.36	0.57	0.84	1.23	
Min	8.17	0.01	0.01	0.01	
Max	10.99	3.00	5.23	5.80	
Summary Count	192	192	192	192	
Total Count	192	192	192	192	

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
	<=5	>5 & <=10	>10 & <=15	>15 & <=50	>50 & <=1000	>1000
100 Cycles	192	0	0	0	0	0
Therm Shck	191	1	0	0	0	0
Humidity	188	4	0	0	0	0

DATA SUMMARIES Continued

LLCR Gas Tight Group

- 1) A total of 192 points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: ----- Stable
 - b. $+5.1$ to $+10.0$ mOhms: ----- Minor
 - c. $+10.1$ to $+15.0$ mOhms: ----- Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: ----- Marginal
 - e. $+50.1$ to $+2000$ mOhms: ----- Unstable
 - f. $>+2000$ mOhms: ----- Open Failure

SAL1-127-01-S-S-A-TR/0.056"EDGE CARD

LLCR Measurement Summaries by Pin Type						
mOhm values	Date	6/8/2015	7/1/2015			
	Room Temp (Deg C)	23	23			
	Rel Humidity (%)	56	54			
	Technician	Peter Chen	Peter Chen			
	Actual		Delta	Delta	Delta	
	Initial		Acid Vapor			
	Pin Type 1: Signal					
	Average	9.57	0.60			
	St. Dev.	0.56	0.61			
	Min	8.59	0.00			
	Max	11.53	3.52			
	Summary Count	192	192			
	Total Count	192	192			

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
	≤ 5	$>5 \text{ & } \leq 10$	$>10 \text{ & } \leq 15$	$>15 \text{ & } \leq 50$	$>50 \text{ & } \leq 1000$	>1000
Acid Vapor	192	0	0	0	0	0

DATA SUMMARIES Continued

LLCR Shock & Vibration Group

- 1) A total of 192 points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: ----- Stable
 - b. $+5.1$ to $+10.0$ mOhms: ----- Minor
 - c. $+10.1$ to $+15.0$ mOhms: ----- Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: ----- Marginal
 - e. $+50.1$ to $+2000$ mOhms ----- Unstable
 - f. $>+2000$ mOhms: ----- Open Failure

SAL1-127-01-S-S-A-TR/0.056"EDGE CARD

LLCR Measurement Summaries by Pin Type						
Date Room Temp (Deg C) Rel Humidity (%) Technician mOhm values	7/6/2015	9/22/2015				
	22	22				
	46	45				
	Aaron McKim	Aaron McKim				
	Actual Initial	Delta Shock-Vib	Delta	Delta		
	Pin Type 1: Signal					
	Average	9.36	0.39			
St. Dev.	0.61	0.39				
Min	8.30	0.00				
Max	12.20	2.69				
Summary Count	192	192				
Total Count	192	192				

LLCR Delta Count by Category						
mOhms Shock-Vib	Stable	Minor	Acceptable	Marginal	Unstable	Open
	≤ 5	$>5 \text{ & } \leq 10$	$>10 \text{ & } \leq 15$	$>15 \text{ & } \leq 50$	$>50 \text{ & } \leq 1000$	>1000
192	0	0	0	0	0	0

DATA SUMMARIES Continued

SAL1-127-01-S-S-A-TR/0.068"EDGE CARD

		LLCR Measurement Summaries by Pin Type			
Date	7/6/2015	9/23/2015			
Room Temp (Deg C)	23	22			
Rel Humidity (%)	46	46			
Technician	Aaron McKim	Aaron McKim			
mOhm values	Actual	Delta	Delta	Delta	
	Initial	Shock-Vib			
Pin Type 1: Signal					
Average	8.92	0.31			
St. Dev.	0.41	0.25			
Min	8.14	0.01			
Max	10.47	1.94			
Summary Count	192	192			
Total Count	192	192			

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
	<=5	>5 & <=10	>10 & <=15	>15 & <=50	>50 & <=1000	>1000
Shock-Vib	192	0	0	0	0	0

Nanosecond Event Detection:

Shock and Vibration Event Detection Summary	
Contacts tested	60
Test Condition	C, 100g's, 6ms, Half-Sine
Shock Events	0
Test Condition	V-B, 7.56 rms g
Vibration Events	0
Total Events	0

EQUIPMENT AND CALIBRATION SCHEDULES

Equipment #: HZ-TCT-01

Description: Normal force analyzer

Manufacturer: Mecmesin Multitester

Model: Mecmesin Multitester 2.5-i

Serial #: 08-1049-04

Accuracy: Last Cal: 4/26/2015, Next Cal: 4/25/2016

Equipment #: HZ-OV-01

Description: Oven

Manufacturer: Huida

Model: CS101-1E

Serial #: CS101-1E-B

Accuracy: Last Cal: 12/13/2014, Next Cal: 12/12/2015

Equipment #: HZ-THC-01

Description: Humidity transmitter

Manufacturer: Thermtron

Model: SM-8-8200

Serial #: 38846

Accuracy: Last Cal: 2/28/2015, Next Cal: 2/27/2016

Equipment #: HZ-TSC-01

Description: Vertical Thermal Shock Chamber

Manufacturer: Cincinnati Sub Zero

Model: VTS-3-6-6-SC/AC

Serial #: 10-VT14994

Accuracy: See Manual

... Last Cal: 06/28/2015, Next Cal: 06/27/2016

Equipment #: HZ-HPM-01

Description: NA9636H

Manufacturer: Ainuo

Model: 6031A

Serial #: 089601091

Accuracy: Last Cal: 3/7/2015, Next Cal: 3/6/2016

Equipment #: HZ-MO-05

Description: Micro-ohmmeter

Manufacturer: Keithley

Model: 3706

Serial #: 1285188

Accuracy: Last Cal: 11/15/2014, Next Cal: 11/14/2015

EQUIPMENT AND CALIBRATION SCHEDULES Continued**Equipment #:** MO-04**Description:** Multimeter /Data Acquisition System**Manufacturer:** Keithley**Model:** 2700**Serial #:** 0798688**Accuracy:** See Manual

... Last Cal: 04/30/2015, Next Cal: 04/30/2016

Equipment #: HZ-MO-01**Description:** Micro-ohmmeter**Manufacturer:** Keithley**Model:** 2700**Serial #:** 1199807**Accuracy:** Last Cal: 04/28/2015, Next Cal: 04/28/2016**Equipment #:** HZ-PS-01**Description:** Power Supply**Manufacturer:** Agilent**Model:** 6031A**Serial #:** MY41000982**Accuracy:** Last Cal: 04/28/2015, Next Cal: 04/28/2016**Equipment #:** SVC-01**Description:** Shock & Vibration Table**Manufacturer:** Data Physics**Model:** LE-DSA-10-20K**Serial #:** 10037**Accuracy:** See Manual

... Last Cal: 11/31/2014, Next Cal: 11/31/2015

Equipment #: ACLM-01**Description:** Accelerometer**Manufacturer:** PCB Piezotronics**Model:** 352C03**Serial #:** 115819**Accuracy:** See Manual

... Last Cal: 07/09/2015, Next Cal: 07/09/2016

Equipment #: ED-03**Description:** Event Detector**Manufacturer:** Analysis Tech**Model:** 32EHD**Serial #:** 1100604**Accuracy:** See Manual

... Last Cal: 06/04/2015, Next Cal: 06/04/2016