



Project Number: Design Qualification Test Report	Tracking Code: 411557_Report_Rev_1
Requested by: Catie Eichhorn	Date: 4/23/2015
Part #: SS4-30-3.00-L-D-K-TR/ST4-30-1.00-L-D-P-TR	
Part description: SS4/ST4	Tech: Kason He
Test Start: 1/4/2015	Test Completed: 2/10/2015



DESIGN QUALIFICATION TEST REPORT

SS4/ST4
SS4-30-3.00-L-D-K-TR/ST4-30-1.00-L-D-P-TR

Tracking Code: 411557 Report Rev_1	Part #: SS4-30-3.00-L-D-K-TR/ST4-30-1.00-L-D-P-TR
Part description: SS4/ST4	

REVISION HISTORY

DATE	REV.NUM.	DESCRIPTION	ENG
4/23/2015	1	Initial Issue	KH

Tracking Code: 411557 Report Rev_1	Part #: SS4-30-3.00-L-D-K-TR/ST4-30-1.00-L-D-P-TR
Part description: SS4/ST4	

CERTIFICATION

All instruments and measuring equipment were calibrated to National Institute for Standards and Technology (NIST) traceable standards according to ISO 10012-1 and ANSI/NCSL 2540-1, as applicable.

All contents contained herein are the property of Samtec. No portion of this report, in part or in full shall be reproduced without prior written approval of Samtec.

SCOPE

To perform the following tests: Design Qualification test. Please see test plan.

APPLICABLE DOCUMENTS

Standards: EIA Publication 364

TEST SAMPLES AND PREPARATION

- 1) All materials were manufactured in accordance with the applicable product specification.
- 2) All test samples were identified and encoded to maintain traceability throughout the test sequences.
- 3) After soldering, the parts to be used for LLCR testing were cleaned according to TLWI-0001.
- 4) Either an automated cleaning procedure or an ultrasonic cleaning procedure may be used.
- 5) The automated procedure is used with aqueous compatible soldering materials.
- 6) Parts not intended for testing LLCR are visually inspected and cleaned if necessary.
- 7) Any additional preparation will be noted in the individual test sequences.
- 8) Solder Information: Lead Free
- 9) Samtec Test PCBs used: PCB-106623-TST/PCB-106624-TST//PCB-106625-TST

FLOWCHARTS**Gas Tight****Group 1**

SS4-30-3.00-L-D-K-TR

ST4-30-1.00-L-D-P-TR

8 Assemblies

Step Description

1. LLCR ⁽²⁾
2. Gas Tight ⁽¹⁾
3. LLCR ⁽²⁾
Max Delta = 15 mOhm

(1) Gas Tight = EIA-364-36

(2) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

Normal Force**Group 1**

SS4-30-3.00-L-D-K-TR

ST4-30-1.00-L-D-P-TR

8 Contacts Minimum

Signal Without Thermals

Group 2

SS4-30-3.00-L-D-K-TR

ST4-30-1.00-L-D-P-TR

8 Contacts Minimum

Signal With Thermals

Step Description

1. Contact Gaps
2. Normal Force ⁽¹⁾
Deflection = 0.007"
Expected Force at Max Deflection = 65 g

Step Description

1. Contact Gaps
2. Thermal Age ⁽²⁾
3. Contact Gaps
4. Normal Force ⁽¹⁾
Deflection = 0.007"
Expected Force at Max Deflection = 65 g

(1) Normal Force = EIA-364-04

(2) Thermal Age = EIA-364-17

Test Condition = 4 (105°C)

Time Condition = B (250 Hours)

FLOWCHARTS Continued**Thermal Aging****Group 1**

SS4-30-3.00-L-D-K-TR

ST4-30-1.00-L-D-P-TR

8 Assemblies

Step Description

1. Contact Gaps
2. Mating/Unmating Force⁽²⁾
3. LLCR⁽¹⁾
4. Thermal Age⁽³⁾
5. LLCR⁽¹⁾
Max Delta = 15 mOhm
6. Mating/Unmating Force⁽²⁾
7. Contact Gaps

⁽¹⁾ LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

⁽²⁾ Mating/Unmating Force = EIA-364-13⁽³⁾ Thermal Age = EIA-364-17

Test Condition = 4 (105°C)

Time Condition = B (250 Hours)

FLOWCHARTS Continued

Mating/Unmating/Durability

<u>Group 1</u>		<u>Group 2</u>		<u>Group 3</u>	
SS4-30-3.00-L-D-K-TR		SS4-10-3.00-L-D-K-TR		SS4-50-3.00-L-D-K-TR	
ST4-30-1.00-L-D-P-TR		ST4-10-1.00-L-D-P-TR		ST4-50-1.00-L-D-P-TR	
8 Assemblies		8 Assemblies		8 Assemblies	
Step	Description	Step	Description	Step	Description
1.	Contact Gaps	1.	Contact Gaps	1.	Contact Gaps
2.	LLCR (2)	2.	Mating/Unmating Force (3)	2.	Mating/Unmating Force (3)
3.	Mating/Unmating Force (3)	3.	Cycles	3.	Cycles
4.	Cycles	<i>Quantity = 100 Cycles</i>		<i>Quantity = 100 Cycles</i>	
5.	Mating/Unmating Force (3)	4.	Mating/Unmating Force (3)	4.	Mating/Unmating Force (3)
6.	Contact Gaps				
7.	LLCR (2)				
	Max Delta = 15 mOhm				
8.	Thermal Shock (4)				
9.	LLCR (2)				
	Max Delta = 15 mOhm				
10.	Humidity (1)				
11.	LLCR (2)				
	Max Delta = 15 mOhm				
12.	Mating/Unmating Force (3)				

(1) Humidity = EIA-364-31

Test Condition = B (240 Hours)

Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)

Test Exceptions: ambient pre-condition and delete steps 7a and 7b

(2) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(3) Mating/Unmating Force = EIA-364-13

(4) Thermal Shock = EIA-364-32

Exposure Time at Temperature Extremes = 1/2 Hour

Method A, Test Condition = I (-55°C to +85°C)

Test Duration = A-3 (100 Cycles)

FLOWCHARTS Continued

IR/DWV

Pin-to-Pin

Group 1		Group 2		Group 3		Group 4	
SS4-30-3.00-L-D-K-TR		SS4-30-3.00-L-D-K-TR		ST4-30-1.00-L-D-P-TR		SS4-30-3.00-L-D-K-TR	
ST4-30-1.00-L-D-P-TR		2 Assemblies		2 Assemblies		ST4-30-1.00-L-D-P-TR	
Step	Description	Step	Description	Step	Description	Step	Description
1.	DWV Breakdown ⁽²⁾	1.	DWV Breakdown ⁽²⁾	1.	DWV Breakdown ⁽²⁾	1.	IR ⁽⁴⁾
							DWV at Test Voltage ⁽¹⁾
							Thermal Shock ⁽⁵⁾
							IR ⁽⁴⁾
							DWV at Test Voltage ⁽¹⁾
							Humidity ⁽³⁾
							IR ⁽⁴⁾
							DWV at Test Voltage ⁽¹⁾

Row-to-Row

Group 5		Group 6		Group 7		Group 8	
SS4-30-3.00-L-D-K-TR		SS4-30-3.00-L-D-K-TR		ST4-30-1.00-L-D-P-TR		SS4-30-3.00-L-D-K-TR	
ST4-30-1.00-L-D-P-TR		2 Assemblies		2 Assemblies		ST4-30-1.00-L-D-P-TR	
Step	Description	Step	Description	Step	Description	Step	Description
1.	DWV Breakdown ⁽²⁾	1.	DWV Breakdown ⁽²⁾	1.	DWV Breakdown ⁽²⁾	1.	IR ⁽⁴⁾
							DWV at Test Voltage ⁽¹⁾
							Thermal Shock ⁽⁵⁾
							IR ⁽⁴⁾
							DWV at Test Voltage ⁽¹⁾
							Humidity ⁽³⁾
							IR ⁽⁴⁾
							DWV at Test Voltage ⁽¹⁾

(1) DWV at Test Voltage = EIA-364-20

Test Condition = 1 (Sea Level)

DWV test voltage is equal to 75% of the lowest breakdown voltage

Test voltage applied for 60 seconds

(2) DWV Breakdown = EIA-364-20

Test Condition = 1 (Sea Level)

DWV test voltage is equal to 75% of the lowest breakdown voltage

Test voltage applied for 60 seconds

(3) Humidity = EIA-364-31

Test Condition = B (240 Hours)

Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)

Test Exceptions: ambient pre-condition and delete steps 7a and 7b

(4) IR = EIA-364-21

Test Condition = 500 Vdc, 2 Minutes Max

(5) Thermal Shock = EIA-364-32

Exposure Time at Temperature Extremes = 1/2 Hour

Method A, Test Condition = I (-55°C to +85°C)

Test Duration = A-3 (100 Cycles)

FLOWCHARTS Continued

Current Carrying Capacity

Group 1
 SS4-50-3.00-L-D-K-TR
 ST4-50-1.00-L-D-P-TR
 1 Pins Powered
 Signal

Step **Description**
 1. CCC(1)
 Rows = 1
 Number of Positions = 1

Group 2
 SS4-50-3.00-L-D-K-TR
 ST4-50-1.00-L-D-P-TR
 2 Pins Powered
 Signal

Step **Description**
 1. CCC(1)
 Rows = 1
 Number of Positions = 2

Group 3
 SS4-50-3.00-L-D-K-TR
 ST4-50-1.00-L-D-P-TR
 3 Pins Powered
 Signal

Step **Description**
 1. CCC(1)
 Rows = 1
 Number of Positions = 3

Group 4
 SS4-50-3.00-L-D-K-TR
 ST4-50-1.00-L-D-P-TR
 4 Pins Powered
 Signal

Step **Description**
 1. CCC(1)
 Rows = 1
 Number of Positions = 4

Group 5
 SS4-50-3.00-L-D-K-TR
 ST4-50-1.00-L-D-P-TR
 50 Pins Powered
 Signal

Step **Description**
 1. CCC(1)
 Rows = 1
 Number of Positions = 50

(1) CCC = EIA-364-70

Method 2, Temperature Rise Versus Current Curve

(TIN PLATING) - Tabulate calculated current at RT, 65°C, 75°C and 95°C after derating 20% and based on 105°C

(GOLD PLATING) - Tabulate calculated current at RT, 85°C, 95°C and 115°C after derating 20% and based on 125°C

FLOWCHARTS Continued**Mechanical Shock/Random Vibration/LLCR**Group 1

SS4-30-3.00-L-D-K-TR

ST4-30-1.00-L-D-P-TR

8 Assemblies

Step Description

1. LLCR ⁽¹⁾
2. Mechanical Shock ⁽²⁾
3. Random Vibration ⁽³⁾
4. LLCR ⁽¹⁾
Max Delta = 15 mOhm

(1) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(2) Mechanical Shock = EIA-364-27

Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)

Number of Shocks = 3 Per Direction, Per Axis, 18 Total

(3) Random Vibration = EIA-364-28

Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

Mechanical Shock/Random Vibration/Event DetectionGroup 1

SS4-30-3.00-L-D-K-TR

ST4-30-1.00-L-D-P-TR

60 Points

Step Description

1. Nanosecond Event Detection
(Mechanical Shock) ⁽¹⁾
2. Nanosecond Event Detection
(Random Vibration) ⁽²⁾

(1) Nanosecond Event Detection (Mechanical Shock)

Use EIA-364-87 for Nanosecond Event Detection:

Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-27 for Mechanical Shock:

Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)

Number of Shocks = 3 Per Direction, Per Axis, 18 Total

(2) Nanosecond Event Detection (Random Vibration)

Use EIA-364-87 for Nanosecond Event Detection:

Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-28 for Random Vibration:

Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

Tracking Code: 411557 Report Rev_1	Part #: SS4-30-3.00-L-D-K-TR/ST4-30-1.00-L-D-P-TR
	Part description: SS4/ST4

ATTRIBUTE DEFINITIONS

The following is a brief, simplified description of attributes.

THERMAL SHOCK:

- 1) EIA-364-32, *Thermal Shock (Temperature Cycling) Test Procedure for Electrical Connectors.*
- 2) Test Condition 1: -55°C to +85°C
- 3) Test Time: ½ hour dwell at each temperature extreme
- 4) Number of Cycles: 100
- 5) All test samples are pre-conditioned at ambient.
- 6) All test samples are exposed to environmental stressing in the mated condition.

THERMAL:

- 1) EIA-364-17, *Temperature Life with or without Electrical Load Test Procedure for Electrical Connectors.*
- 2) Test Condition 4 at 105°C.
- 3) Test Time Condition B for 250 hours.
- 4) All test samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

HUMIDITY:

- 1) Reference document: EIA-364-31, *Humidity Test Procedure for Electrical Connectors.*
- 2) Test Condition B, 240 Hours.
- 3) Method III, +25°C to +65°C, 90% to 98% Relative Humidity excluding sub-cycles 7a and 7b.
- 4) All samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

MECHANICAL SHOCK (Specified Pulse):

- 1) Reference document: EIA-364-27, *Mechanical Shock Test Procedure for Electrical Connectors*
- 2) Test Condition C
- 3) Peak Value: 100 G
- 4) Duration: 6 Milliseconds
- 5) Wave Form: Half Sine
- 6) Velocity: 12.3 ft/s
- 7) Number of Shocks: 3 Shocks / Direction, 3 Axis (18 Total)

VIBRATION:

- 1) Reference document: EIA-364-28, *Vibration Test Procedure for Electrical Connectors*
- 2) Test Condition V, Letter B
- 3) Power Spectral Density: 0.04 G² / Hz
- 4) G 'RMS': 7.56
- 5) Frequency: 50 to 2000 Hz
- 6) Duration: 2.0 Hours per axis (3 axis total)

NANOSECOND-EVENT DETECTION:

- 1) Reference document: EIA-364-87, *Nanosecond-Event Detection for Electrical Connectors*
- 2) Prior to test, the samples were characterized to assure the low nanosecond event being monitored will trigger the detector.
- 3) After characterization it was determined the test samples could be monitored for 50 nanosecond events

MATING/UNMATING:

- 1) Reference document: EIA-364-13, *Mating and Unmating Forces Test Procedure for Electrical Connectors.*
- 2) The full insertion position was to within 0.003" to 0.004" of the plug bottoming out in the receptacle to prevent damage to the system under test.
- 3) One of the mating parts is secured to a floating X-Y table to prevent damage during cycling.

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes

NORMAL FORCE (FOR CONTACTS TESTED IN THE HOUSING):

- 1) Reference document: EIA-364-04, *Normal Force Test Procedure for Electrical Connectors*.
- 2) The contacts shall be tested in the connector housing.
- 3) If necessary, a “window” shall be made in the connector body to allow a probe to engage and deflect the contact at the same attitude and distance (plus 0.05 mm [0.002”]) as would occur in actual use.
- 4) The connector housing shall be placed in a holding fixture that does not interfere with or otherwise influence the contact force or deflection.
- 5) Said holding fixture shall be mounted on a floating, adjustable, X-Y table on the base of the Dillon TC², computer controlled test stand with a deflection measurement system accuracy of 5.0 μm (0.0002”).
- 6) The nominal deflection rate shall be 5 mm (0.2”)/minute.
- 7) Unless otherwise noted a minimum of five contacts shall be tested.
- 8) The force/deflection characteristic to load and unload each contact shall be repeated five times.
- 9) The system shall utilize the TC² software in order to acquire and record the test data.
- 10) The permanent set of each contact shall be measured within the TC² software.
- 11) The acquired data shall be graphed with the deflection data on the X-axis and the force data on the Y-axis and a print out will be stored with the Tracking Code paperwork.

TEMPERATURE RISE (Current Carrying Capacity, CCC):

- 1) EIA-364-70, *Temperature Rise versus Current Test Procedure for Electrical Connectors and Sockets*.
- 2) When current passes through a contact, the temperature of the contact increases as a result of I^2R (resistive) heating.
- 3) The number of contacts being investigated plays a significant part in power dissipation and therefore temperature rise.
- 4) The size of the temperature probe can affect the measured temperature.
- 5) Copper traces on PC boards will contribute to temperature rise:
 - a. Self heating (resistive)
 - b. Reduction in heat sink capacity affecting the heated contacts
- 6) A de-rating curve, usually 20%, is calculated.
- 7) Calculated de-rated currents at four temperature points are reported:
 - a. Ambient
 - b. 85° C
 - c. 95° C
 - d. 115° C
- 8) Typically, neighboring contacts (in close proximity to maximize heat build up) are energized.
- 9) The thermocouple (or temperature measuring probe) will be positioned at a location to sense the maximum temperature in the vicinity of the heat generation area.
- 10) A computer program, *TR 803.exe*, ensures accurate stability for data acquisition.
- 11) Hook-up wire cross section is larger than the cross section of any connector leads/PC board traces, jumpers, etc.
- 12) Hook-up wire length is longer than the minimum specified in the referencing standard.

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes

LLCR:

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
 - a. $\leq +5.0$ mOhms: ----- Stable
 - b. $+5.1$ to $+10.0$ mOhms: ----- Minor
 - c. $+10.1$ to $+15.0$ mOhms: ----- Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: ----- Marginal
 - e. $+50.1$ to $+2000$ mOhms: ----- Unstable
 - f. $>+2000$ mOhms: ----- Open Failure

GAS TIGHT:

To provide method for evaluating the ability of the contacting surfaces in preventing penetration of harsh vapors which might lead to oxide formation that may degrade the electrical performance of the contact system.

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
 - a. $\leq +5.0$ mOhms: ----- Stable
 - b. $+5.1$ to $+10.0$ mOhms: ----- Minor
 - c. $+10.1$ to $+15.0$ mOhms: ----- Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: ----- Marginal
 - e. $+50.1$ to $+2000$ mOhms: ----- Unstable
 - f. $>+2000$ mOhms: ----- Open Failure
- 4) Procedure:
 - a. Reference document: EIA-364-36, *Test Procedure for Determination of Gas-Tight Characteristics for Electrical Connectors, Sockets and/or Contact Systems*.
 - b. Test Conditions:
 - i. Class II--- Mated pairs of contacts assembled to their plastic housings.
 - ii. Reagent grade Nitric Acid shall be used of sufficient volume to saturate the test chamber
 - iii. The ratio of the volume of the test chamber to the surface area of the acid shall be 10:1.
 - iv. The chamber shall be saturated with the vapor for at least 15 minutes before samples are added.
 - v. Exposure time, 55 to 65 minutes.
 - vi. The samples shall be no closer to the chamber walls than 1 inches and no closer to the surface of the acid than 3 inches.
 - vii. The samples shall be dried after exposure for a minimum of 1 hour.
 - viii. Drying temperature 50°C
 - ix. The final LLCR shall be conducted within 1 hour after drying.

Tracking Code: 411557 Report Rev_1	Part #: SS4-30-3.00-L-D-K-TR/ST4-30-1.00-L-D-P-TR
Part description: SS4/ST4	

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes

INSULATION RESISTANCE (IR):

To determine the resistance of insulation materials to leakage of current through or on the surface of these materials when a DC potential is applied.

- 1) PROCEDURE:
 - a. Reference document: EIA-364-21, *Insulation Resistance Test Procedure for Electrical Connectors*.
 - b. Test Conditions:
 - i. Between Adjacent Contacts or Signal-to-Ground
 - ii. Electrification Time 2.0 minutes
 - iii. Test Voltage (500 VDC) corresponds to calibration settings for measuring resistances.
- 2) MEASUREMENTS:
- 3) When the specified test voltage is applied (VDC), the insulation resistance shall not be less than 5000 megohms.

DIELECTRIC WITHSTANDING VOLTAGE (DWV):

To determine if the sockets can operate at its rated voltage and withstand momentary over potentials due to switching, surges, and other similar phenomenon. Separate samples are used to evaluate the effect of environmental stresses so not to influence the readings from arcing that occurs during the measurement process.

- 1) PROCEDURE:
 - a. Reference document: EIA-364-20, *Withstanding Voltage Test Procedure for Electrical Connectors*.
 - b. Test Conditions:
 - i. Between Adjacent Contacts or Signal-to-Ground
 - ii. Barometric Test Condition 1
 - iii. Rate of Application 500 V/Sec
 - iv. Test Voltage (VAC) until breakdown occurs
- 2) MEASUREMENTS/CALCULATIONS
 - a. The breakdown voltage shall be measured and recorded.
 - b. The dielectric withstand voltage shall be recorded as 75% of the minimum breakdown voltage.
 - c. The working voltage shall be recorded as one-third (1/3) of the dielectric withstand voltage (one-fourth of the breakdown voltage).

RESULTS

Temperature Rise, CCC at a 20% de-rating

- CCC for a 30°C Temperature Rise-----1.6 A per contact with 2 contacts (2x1) powered
- CCC for a 30°C Temperature Rise-----1.2 A per contact with 4 contacts (2x2) powered
- CCC for a 30°C Temperature Rise-----1.0 A per contact with 6 contacts (2x3) powered
- CCC for a 30°C Temperature Rise-----0.9 A per contact with 8 contacts (2x4) powered
- CCC for a 30°C Temperature Rise-----0.4 A per contact with 100 contacts (2x50) powered

Mating/Unmating Forces: Thermal Aging Group

- Initial
 - Mating
 - Min ----- 4.38 Lbs
 - Max----- 5.70 Lbs
 - Unmating
 - Min ----- 2.56 Lbs
 - Max----- 3.21 Lbs
- After Thermal
 - Mating
 - Min ----- 2.23 Lbs
 - Max----- 2.72 Lbs
 - Unmating
 - Min ----- 1.85 Lbs
 - Max----- 2.44 Lbs

RESULTS Continued

Mating/Unmating Forces: Mating/Unmating Durability Group

SS4-30-3.00-L-D-K-TR/ST4-30-1.00-L-D-P-TR

- Initial
 - Mating
 - Min ----- 3.51 Lbs
 - Max ----- 5.25 Lbs
 - Unmating
 - Min ----- 2.43 Lbs
 - Max ----- 3.29 Lbs
- After 25 Cycles
 - Mating
 - Min ----- 3.28 Lbs
 - Max ----- 4.93 Lbs
 - Unmating
 - Min ----- 2.50 Lbs
 - Max ----- 3.48 Lbs
- After 50 Cycles
 - Mating
 - Min ----- 3.28 Lbs
 - Max ----- 5.24 Lbs
 - Unmating
 - Min ----- 2.55 Lbs
 - Max ----- 3.74 Lbs
- After 75 Cycles
 - Mating
 - Min ----- 3.29 Lbs
 - Max ----- 5.48 Lbs
 - Unmating
 - Min ----- 2.70 Lbs
 - Max ----- 3.90 Lbs
- After 100 Cycles
 - Mating
 - Min ----- 3.36 Lbs
 - Max ----- 5.78 Lbs
 - Unmating
 - Min ----- 2.79 Lbs
 - Max ----- 4.37 Lbs
- After Humidity
 - Mating
 - Min ----- 1.41 Lbs
 - Max ----- 2.63 Lbs
 - Unmating
 - Min ----- 1.11 Lbs
 - Max ----- 1.90 Lbs

RESULTS Continued

Mating/Unmating Forces: Mating/Unmating Basic Group

SS4-10-3.00-L-D-K-TR/ST4-10-1.00-L-D-P-TR

- Initial
 - Mating
 - Min ----- 1.09 Lbs
 - Max ----- 1.44 Lbs
 - Unmating
 - Min ----- 0.70 Lbs
 - Max ----- 0.98 Lbs
- After 25 Cycles
 - Mating
 - Min ----- 1.03 Lbs
 - Max ----- 1.66 Lbs
 - Unmating
 - Min ----- 0.70 Lbs
 - Max ----- 1.07 Lbs
- After 50 Cycles
 - Mating
 - Min ----- 1.05 Lbs
 - Max ----- 2.20 Lbs
 - Unmating
 - Min ----- 0.74 Lbs
 - Max ----- 1.21 Lbs
- After 75 Cycles
 - Mating
 - Min ----- 1.06 Lbs
 - Max ----- 2.49 Lbs
 - Unmating
 - Min ----- 0.77 Lbs
 - Max ----- 1.25 Lbs
- After 100 Cycles
 - Mating
 - Min ----- 1.06 Lbs
 - Max ----- 2.67 Lbs
 - Unmating
 - Min ----- 0.79 Lbs
 - Max ----- 1.43 Lbs

RESULTS Continued

Mating/Unmating Forces: Mating/Unmating Basic Group

SS4-50-3.00-L-D-K-TR/ST4-50-1.00-L-D-P-TR

- Initial
 - Mating
 - Min ----- 7.24 Lbs
 - Max ----- 9.06 Lbs
 - Unmating
 - Min ----- 3.34 Lbs
 - Max ----- 4.62 Lbs
- After 25 Cycles
 - Mating
 - Min ----- 5.88 Lbs
 - Max ----- 8.26 Lbs
 - Unmating
 - Min ----- 3.17 Lbs
 - Max ----- 4.97 Lbs
- After 50 Cycles
 - Mating
 - Min ----- 5.83 Lbs
 - Max ----- 8.47 Lbs
 - Unmating
 - Min ----- 3.11 Lbs
 - Max ----- 5.30 Lbs
- After 75 Cycles
 - Mating
 - Min ----- 5.86 Lbs
 - Max ----- 8.73 Lbs
 - Unmating
 - Min ----- 3.16 Lbs
 - Max ----- 5.58 Lbs
- After 100 Cycles
 - Mating
 - Min ----- 5.79 Lbs
 - Max ----- 9.05 Lbs
 - Unmating
 - Min ----- 3.26 Lbs
 - Max ----- 5.75 Lbs

Normal Force at 0.0075 inch deflection

- Initial
 - Min ----- 77.00 gf Set ----- 0.0004 in
 - Max ----- 86.80 gf Set ----- 0.0011 in
- Thermal
 - Min ----- 42.00 gf Set ----- 0.0030 in
 - Max ----- 62.30 gf Set ----- 0.0039 in

RESULTS Continued

Insulation Resistance minimums, IR

Pin to Pin

- Initial
 - Mated ----- 10000 Meg Ω ----- Passed
 - Unmated ----- 10000 Meg Ω ----- Passed
- Thermal
 - Mated ----- 10000 Meg Ω ----- Passed
 - Unmated ----- 10000 Meg Ω ----- Passed
- Humidity
 - Mated ----- 3984 Meg Ω ----- Passed
 - Unmated ----- 5126 Meg Ω ----- Passed

Row to Row

- Initial
 - Mated ----- 10000 Meg Ω ----- Passed
 - Unmated ----- 10000 Meg Ω ----- Passed
- Thermal
 - Mated ----- 10000 Meg Ω ----- Passed
 - Unmated ----- 10000 Meg Ω ----- Passed
- Humidity
 - Mated ----- 10000 Meg Ω ----- Passed
 - Unmated ----- 10000 Meg Ω ----- Passed

Dielectric Withstanding Voltage minimums, DWV

- Minimums
 - Breakdown Voltage ----- 625 VAC
 - Test Voltage ----- 470 VAC
 - Working Voltage ----- 155 VAC

Pin to Pin

- Initial DWV ----- Passed
- Thermal DWV ----- Passed
- Humidity DWV ----- Passed

Row to Row

- Initial DWV ----- Passed
- Thermal DWV ----- Passed
- Humidity DWV ----- Passed

RESULTS Continued

LLCR Gas Tight (192 LLCR test points)

- Initial ----- **24.40 mOhms Max**
- Gas-Tight
 - <= +5.0 mOhms ----- 192 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
 - >+2000 mOhms ----- 0 Points ----- Open Failure

LLCR Thermal Aging (192 LLCR test points)

- Initial ----- **21.95 mOhms Max**
- Thermal Aging
 - <= +5.0 mOhms ----- 192 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
 - >+2000 mOhms ----- 0 Points ----- Open Failure

LLCR Durability (192 LLCR test points)

- Initial ----- **23.02 mOhms Max**
- Durability, 100 Cycles
 - <= +5.0 mOhms ----- 192 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
 - >+2000 mOhms ----- 0 Points ----- Open Failure
- Thermal
 - <= +5.0 mOhms ----- 192 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
 - >+2000 mOhms ----- 0 Points ----- Open Failure
- Humidity
 - <= +5.0 mOhms ----- 192 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 0 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +2000 mOhms ----- 0 Points ----- Unstable
 - >+2000 mOhms ----- 0 Points ----- Open Failure

RESULTS Continued

LLCR Shock & Vibration (192 LLCR test points)

- Initial ----- 25.69 mOhms Max
- Shock &Vibration
 - <= +5.0 mOhms ----- 191 Points ----- Stable
 - +5.1 to +10.0 mOhms ----- 1 Points ----- Minor
 - +10.1 to +15.0 mOhms ----- 0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms ----- 0 Points ----- Marginal
 - +50.1 to +2000 mOhms----- 0 Points ----- Unstable
 - >+2000 mOhms ----- 0 Points ----- Open Failure


Mechanical Shock & Random Vibration:

- Shock
 - No Damage----- Pass
 - 50 Nanoseconds----- Pass
- Vibration
 - No Damage----- Pass
 - 50 Nanoseconds----- Pass


DATA SUMMARIES

TEMPERATURE RISE (Current Carrying Capacity, CCC):

- 1) High quality thermocouples whose temperature slopes track one another were used for temperature monitoring.
- 2) The thermocouples were placed at a location to sense the maximum temperature generated during testing.
- 3) Temperature readings recorded are those for which three successive readings, 15 minutes apart, differ less than 1°C (computer controlled data acquisition).
- 4) Adjacent contacts were powered:
 - a. Linear configuration with 2 adjacent conductors/contacts powered





411557
2(2X1) Contacts in series
Part Numbers: SS4-50-3.00-L-D-K-TR/ST4-50-1.00-L-D-P-TR





DATA SUMMARIES Continued

b. Linear configuration with 4 adjacent conductors/contacts powered





DATA SUMMARIES Continued

c. Linear configuration with 6 adjacent conductors/contacts powered





DATA SUMMARIES Continued

d. Linear configuration with 8 adjacent conductors/contacts powered



DATA SUMMARIES Continued

e. Linear configuration with all adjacent conductors/contacts powered



DATA SUMMARIES Continued

Mating\Unmating Force: Thermal Aging Group

	Initial				After Thermals			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	19.48	4.38	11.39	2.56	9.92	2.23	8.23	1.85
Maximum	25.35	5.70	14.28	3.21	12.10	2.72	10.85	2.44
Average	22.27	5.01	12.95	2.91	11.05	2.49	9.20	2.07
St Dev	1.98	0.45	0.88	0.20	0.74	0.17	0.78	0.18
Count	8	8	8	8	8	8	8	8

Mating\Unmating Force: Mating\Unmating Durability Group

SS4-30-3.00-L-D-K-TR/ST4-30-1.00-L-D-P-TR

	Initial				After 25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	15.61	3.51	10.81	2.43	14.59	3.28	11.12	2.50
Maximum	23.35	5.25	14.63	3.29	21.93	4.93	15.48	3.48
Average	20.76	4.67	12.55	2.82	18.83	4.23	13.62	3.06
St Dev	2.25	0.50	1.31	0.29	2.07	0.47	1.35	0.30
Count	8	8	8	8	8	8	8	8
	After 50 Cycles				After 75 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	14.59	3.28	11.34	2.55	14.63	3.29	12.01	2.70
Maximum	23.31	5.24	16.64	3.74	24.38	5.48	17.35	3.90
Average	19.73	4.44	14.37	3.23	20.45	4.60	15.11	3.40
St Dev	2.58	0.58	1.52	0.34	2.86	0.64	1.80	0.41
Count	8	8	8	8	8	8	8	8
	After 100 Cycles				After Humidity			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	14.95	3.36	12.41	2.79	6.27	1.41	4.94	1.11
Maximum	25.71	5.78	19.44	4.37	11.70	2.63	8.45	1.90
Average	21.39	4.81	16.20	3.64	9.06	2.04	6.10	1.37
St Dev	3.16	0.71	2.16	0.48	1.74	0.39	1.13	0.25
Count	8	8	8	8	8	8	8	8

DATA SUMMARIES Continued

Mating\Unmating Force: Mating\Unmating Basic Group

SS4-10-3.00-L-D-K-TR/ST4-10-1.00-L-D-P-TR

	Initial				After 25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	4.85	1.09	3.11	0.70	4.58	1.03	3.11	0.70
Maximum	6.41	1.44	4.36	0.98	7.38	1.66	4.76	1.07
Average	5.66	1.27	3.69	0.83	5.59	1.26	3.97	0.89
St Dev	0.54	0.12	0.46	0.10	0.90	0.20	0.62	0.14
Count	8	8	8	8	8	8	8	8
After 50 Cycles				After 75 Cycles				
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
	4.67	1.05	3.29	0.74	4.71	1.06	3.42	0.77
Minimum	9.79	2.20	5.38	1.21	11.08	2.49	5.56	1.25
Average	6.24	1.40	4.19	0.94	6.56	1.47	4.35	0.98
St Dev	1.65	0.37	0.73	0.16	2.12	0.48	0.81	0.18
Count	8	8	8	8	8	8	8	8
After 100 Cycles								
	Mating		Unmating					
	Newton	Force (Lbs)	Newton	Force (Lbs)				
	4.71	1.06	3.51	0.79				
Minimum	11.88	2.67	6.36	1.43				
Average	7.03	1.58	4.59	1.03				
St Dev	2.36	0.53	1.05	0.24				
Count	8	8	8	8				


Tracking Code: 411557 Report Rev_1	Part #: SS4-30-3.00-L-D-K-TR/ST4-30-1.00-L-D-P-TR
Part description: SS4/ST4	

DATA SUMMARIES Continued

Mating\Unmating Force: Mating\Unmating Basic Group

SS4-50-3.00-L-D-K-TR/ST4-50-1.00-L-D-P-TR

	Initial				After 25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
Minimum	32.20	7.24	14.86	3.34	26.15	5.88	14.10	3.17
Maximum	40.30	9.06	20.55	4.62	36.74	8.26	22.11	4.97
Average	36.49	8.20	18.75	4.22	33.28	7.48	19.31	4.34
St Dev	2.56	0.58	1.93	0.43	3.69	0.83	2.82	0.63
Count	8	8	8	8	8	8	8	8
After 50 Cycles				After 75 Cycles				
	Mating		Unmating		Mating		Unmating	
	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)	Newton	Force (Lbs)
	25.93	5.83	13.83	3.11	26.07	5.86	14.06	3.16
Minimum	25.93	5.83	13.83	3.11	26.07	5.86	14.06	3.16
Maximum	37.67	8.47	23.57	5.30	38.83	8.73	24.82	5.58
Average	33.82	7.60	20.98	4.72	34.86	7.84	22.06	4.96
St Dev	4.07	0.91	3.45	0.77	4.51	1.01	3.84	0.86
Count	8	8	8	8	8	8	8	8
After 100 Cycles								
	Mating		Unmating					
	Newton	Force (Lbs)	Newton	Force (Lbs)				
	25.75	5.79	14.50	3.26				
Minimum	25.75	5.79	14.50	3.26				
Maximum	40.25	9.05	25.58	5.75				
Average	35.92	8.08	22.95	5.16				
St Dev	4.99	1.12	3.94	0.89				
Count	8	8	8	8				

DATA SUMMARIES Continued**Mating\Unmating Force Comparison****Mating/Unmating Data for 10, 30 and 50 Position SS4/ST4**


DATA SUMMARIES Continued

NORMAL FORCE (FOR CONTACTS TESTED IN THE HOUSING):

- 1) Calibrated force gauges are used along with computer controlled positioning equipment.
- 2) For Normal force 8-10 measurements are taken and the averages reported.

Initial	Deflections in inches Forces in Grams										
	0.0008	0.0015	0.0023	0.0030	0.0038	0.0045	0.0053	0.0060	0.0068	0.0075	SET
Averages	10.05	20.16	29.21	38.73	47.83	56.94	65.03	73.12	79.21	82.77	0.0008
Min	8.00	17.50	25.90	33.70	42.70	49.90	57.10	65.30	71.10	77.00	0.0004
Max	11.80	22.90	32.80	43.00	51.60	60.30	69.40	78.10	85.80	86.80	0.0011
St. Dev	1.433	1.523	2.335	2.752	2.935	3.324	3.547	3.593	3.732	3.126	0.0002
Count	12	12	12	12	12	12	12	12	12	12	12

After Thermals	Deflections in inches Forces in Grams										
	0.0008	0.0015	0.0023	0.0030	0.0038	0.0045	0.0053	0.0060	0.0068	0.0075	SET
Averages	-0.03	-0.03	-0.03	0.92	6.32	16.03	25.02	35.24	44.20	54.17	0.0034
Min	-0.10	-0.10	-0.10	-0.10	0.00	8.50	16.60	25.80	34.20	42.00	0.0030
Max	0.10	0.10	0.10	4.50	14.30	23.50	31.70	42.60	51.10	62.30	0.0039
St. Dev	0.087	0.089	0.087	1.777	5.003	5.326	5.348	5.591	5.575	6.270	0.0003
Count	12	12	12	12	12	12	12	12	12	12	12



DATA SUMMARIES Continued**INSULATION RESISTANCE (IR):**

		Pin to Pin		
		Mated	Unmated	Unmated
Minimum	SS4/ST4	SS4	ST4	
Initial	10000	10000	10000	
Thermal	10000	10000	10000	
Humidity	3984	10000	5126	

		Row to Row		
		Mated	Unmated	Unmated
Minimum	SS4/ST4	SS4	ST4	
Initial	10000	10000	10000	
Thermal	10000	10000	10000	
Humidity	10000	10000	10000	

DIELECTRIC WITHSTANDING VOLTAGE (DWV):

Voltage Rating Summary	
Minimum	SS4/ST4
Break Down Voltage	625
Test Voltage	470
Working Voltage	155

Pin to Pin	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed
After Humidity Test Voltage	Passed

Row to Row	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed
After Humidity Test Voltage	Passed

DATA SUMMARIES Continued

LLCR Durability:

- 1) A total of 192 points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: ----- Stable
 - b. $+5.1$ to $+10.0$ mOhms: ----- Minor
 - c. $+10.1$ to $+15.0$ mOhms: ----- Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: ----- Marginal
 - e. $+50.1$ to $+2000$ mOhms----- Unstable
 - f. $>+2000$ mOhms: ----- Open Failure

		LLCR Measurement Summaries by Pin Type			
		1/4/2015	1/6/2015	1/13/2015	1/26/2015
Date	Room Temp (Deg C)	19	24	20	22
	Rel Humidity (%)	46	54	50	53
	Technician	Kason He	Kason He	Kason He	Kason He
mOhm values	Actual	Delta	Delta	Delta	
	Initial	100 Cycles	Therm Shck	Humidity	
Pin Type 1: Signal					
Average	20.59	0.46	0.95	0.66	
St. Dev.	0.58	0.40	0.74	0.53	
Min	18.94	0.00	0.01	0.00	
Max	23.02	2.64	3.63	2.34	
Summary Count	192	192	192	192	
Total Count	192	192	192	192	

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
100 Cycles	≤ 5	$>5 \text{ & } \leq 10$	$>10 \text{ & } \leq 15$	$>15 \text{ & } \leq 50$	$>50 \text{ & } \leq 1000$	>1000
Therm Shck	192	0	0	0	0	0
Humidity	192	0	0	0	0	0

DATA SUMMARIES Continued

LLCR Thermal Aging:

- 1) A total of 192 points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: Stable
 - b. $+5.1$ to $+10.0$ mOhms: Minor
 - c. $+10.1$ to $+15.0$ mOhms: Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: Marginal
 - e. $+50.1$ to $+2000$ mOhms: Unstable
 - f. $>+2000$ mOhms: Open Failure

		LLCR Measurement Summaries by Pin Type			
Date	1/4/2015	1/16/2015	Delta	Delta	Delta
	19	21			
Room Temp (Deg C)	46	44			
	Kason He	Kason He			
mOhm values	Actual	Delta	Delta	Delta	Delta
	Initial	Thermal			
Pin Type 1: Signal					
Average	20.58	0.51			
St. Dev.	0.42	0.51			
Min	19.27	0.00			
Max	21.95	2.88			
Summary Count	192	192			
Total Count	192	192			

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
	≤ 5	$>5 \text{ & } \leq 10$	$>10 \text{ & } \leq 15$	$>15 \text{ & } \leq 50$	$>50 \text{ & } \leq 1000$	>1000
Thermal	192	0	0	0	0	0

DATA SUMMARIES Continued

LLCR Gas Tight:

- 1) A total of 192 points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: ----- Stable
 - b. $+5.1$ to $+10.0$ mOhms: ----- Minor
 - c. $+10.1$ to $+15.0$ mOhms: ----- Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: ----- Marginal
 - e. $+50.1$ to $+2000$ mOhms: ----- Unstable
 - f. $>+2000$ mOhms: ----- Open Failure

		LLCR Measurement Summaries by Pin Type			
mOhm values	Date	1/6/2015	1/16/2015		
	Room Temp (Deg C)	24	20		
	Rel Humidity (%)	54	44		
	Technician	Kason He	Kason He		
	Actual	Delta		Delta	Delta
	Initial	Acid Vapor			
	Pin Type 1: Signal				
	Average	21.45	0.54		
	St. Dev.	1.00	0.41		
	Min	18.77	0.00		
	Max	24.40	2.58		
	Summary Count	192	192		
	Total Count	192	192		

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
	≤ 5	$>5 \text{ & } \leq 10$	$>10 \text{ & } \leq 15$	$>15 \text{ & } \leq 50$	$>50 \text{ & } \leq 1000$	>1000
Acid Vapor	192	0	0	0	0	0

DATA SUMMARIES Continued

LLCR Shock & Vibration:

- 1). A total of 192 points were measured.
- 2). EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3). The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: ----- Stable
 - b. $+5.1$ to $+10.0$ mOhms: ----- Minor
 - c. $+10.1$ to $+15.0$ mOhms: ----- Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: ----- Marginal
 - e. $+50.1$ to $+2000$ mOhms ----- Unstable
 - f. $>+2000$ mOhms: ----- Open Failure

		LLCR Measurement Summaries by Pin Type			
Date	Room Temp (Deg C)	4/1/2015	4/3/2015		
		22	22		
Rel Humidity (%)	Technician	32	40		
		Aaron McKim	Craig Ryan		
mOhm values	Actual	Delta		Delta	Delta
	Initial	Shock-Vib			
Pin Type 1: Signal					
Average	21.44	0.55			
	0.78	0.53			
St. Dev.	19.33	0.01			
	25.69	5.69			
Min					
Max					
Summary Count	192	192			
Total Count	192	192			

LLCR Delta Count by Category						
mOhms	Stable	Minor	Acceptable	Marginal	Unstable	Open
	≤ 5	$>5 \text{ & } \leq 10$	$>10 \text{ & } \leq 15$	$>15 \text{ & } \leq 50$	$>50 \text{ & } \leq 1000$	>1000
Shock-Vib	191	1	0	0	0	0

Nanosecond Event Detection:

Shock and Vibration Event Detection Summary						
Events	Count	Category	Count	Category	Count	Category
Contacts tested	60					
Test Condition		C, 100g's, 6ms, Half-Sine				
Shock Events	0					
Test Condition		V-B, 7.56 rms g				
Vibration Events	0					
Total Events	0					

Tracking Code: 411557 Report Rev_1	Part #: SS4-30-3.00-L-D-K-TR/ST4-30-1.00-L-D-P-TR
Part description: SS4/ST4	

EQUIPMENT AND CALIBRATION SCHEDULES

Equipment #: HZ-TCT-01

Description: Normal force analyzer

Manufacturer: Mecmesin Multitester

Model: Mecmesin Multitester 2.5-i

Serial #: 08-1049-04

Accuracy: Last Cal: 4/26/2014, Next Cal: 4/27/2015

Equipment #: HZ-OV-01

Description: Oven

Manufacturer: Huida

Model: CS101-1E

Serial #: CS101-1E-B

Accuracy: Last Cal: 12/12/2014, Next Cal: 12/11/2015

Equipment #: HZ-THC-01

Description: Humidity transmitter

Manufacturer: Thermtron

Model: HMM30C

Serial #: D0240037

Accuracy: Last Cal: 3/1/2014, Next Cal: 2/28/2015

Equipment #: HZ-HPM-01

Description: NA9636H

Manufacturer: Ainuo

Model: 6031A

Serial #: 089601091

Accuracy: Last Cal: 3/8/2014, Next Cal: 3/7/2015

Equipment #: HZ-MO-05

Description: Micro-ohmmeter

Manufacturer: Keithley

Model: 3706

Serial #: 1285188

Accuracy: Last Cal: 11/14/2014, Next Cal: 11/13/2015

Equipment #: HZ-MO-01

Description: Multimeter /Data Acquisition System

Manufacturer: Keithley

Model: 2700

Serial #: 1199807

Accuracy: See Manual

... Last Cal: 07/01/2014, Next Cal: 06/30/2015

Tracking Code: 411557 Report Rev_1	Part #: SS4-30-3.00-L-D-K-TR/ST4-30-1.00-L-D-P-TR
	Part description: SS4/ST4

EQUIPMENT AND CALIBRATION SCHEDULES

Equipment #: HZ-PS-01

Description: 120 Amp Power Supply

Manufacturer: Agilent

Model: 6031A PS

Serial #: MY41000982

Accuracy: See Manual

... Last Cal: 07/02/2014, Next Cal: 07/01/2015

Equipment #: HZ-TSC-01

Description: Vertical Thermal Shock Chamber

Manufacturer: Cincinnati Sub Zero

Model: VTS-3-6-6-SC/AC

Serial #: 10-VT14994

Accuracy: See Manual

... Last Cal: 06/28/2014, Next Cal: 06/27/2015

Equipment #: SVC-01

Description: Shock & Vibration Table

Manufacturer: Data Physics

Model: LE-DSA-10-20K

Serial #: 10037

Accuracy: See Manual

... Last Cal: 11/30/2014, Next Cal: 11/30/2015

Equipment #: ACLM-01

Description: Accelerometer

Manufacturer: PCB Piezotronics

Model: 352C03

Serial #: 115819

Accuracy: See Manual

... Last Cal: 07/09/2014, Next Cal: 07/09/2015

Equipment #: ED-03

Description: Event Detector

Manufacturer: Analysis Tech

Model: 32EHD

Serial #: 1100604

Accuracy: See Manual

... Last Cal: 06/04/2014, Next Cal: 06/04/2015

Equipment #: MO-11

Description: Switch/Multimeter

Manufacturer: Keithley

Model: 3706

Serial #: 120169

Accuracy: See Manual

... Last Cal: 08/21/2014, Next Cal: 08/21/2015