



Project Number: Design Qualification Test Report	Tracking Code: CR-1104501_Report_Rev_2
Requested by: Corey Rose	Date: 11/19/2025
Part #: EBTM-6-12-2.0-S-RA-5/EBTF-6-12-2.0-S-RA-5	
Part description: EBTM/EBTF	Tech: Brian Stemle
Test Start: 5/20/2024	Test Completed: 6/28/2024



DESIGN QUALIFICATION TEST REPORT
EBTM/EBTF
EBTM-6-12-2.0-S-RA-5/EBTF-6-12-2.0-S-RA-5

REVISION HISTORY

DATA	REV.NUM.	DESCRIPTION	ENG
8/28/2024	1	Initial test	KH
11/19/2025	2	Update the part number and IR test data.	KH

CERTIFICATION

All instruments and measuring equipment were calibrated to National Institute for Standards and Technology (NIST) traceable standards according to ISO 10012-1 and ANSI/NCSL 2540-1, as applicable.

All contents contained herein are the property of Samtec. No portion of this report, in part or in full shall be reproduced without prior written approval of Samtec.

SCOPE

To perform the following tests: Design Qualification test. Please see test plan.

APPLICABLE DOCUMENTS

Standards: EIA Publication 364

TEST SAMPLES AND PREPARATION

- 1) All materials were manufactured in accordance with the applicable product specification.
- 2) All test samples were identified and encoded to maintain traceability throughout the test sequences.
- 3) After soldering, the parts to be used for LLCR and DWV/IR testing were cleaned according to CO-SC-WI-3029.
- 4) Either an automated cleaning procedure or an ultrasonic cleaning procedure may be used.
- 5) The automated procedure is used with aqueous compatible soldering materials.
- 6) Parts not intended for testing LLCR and DWV/IR are visually inspected and cleaned if necessary.
- 7) Any additional preparation will be noted in the individual test sequences.
- 8) Solder Information: Lead Free
- 9) Samtec Test PCBs used: PCB-113536-TST-XX, PCB-113322-TST-XX.

FLOWCHARTS**Gas Tight**Group 1

EBTM-6-12-2.0-S-RA-5

EBTF-6-12-2.0-S-RA-5

8 Assemblies

Tin (IMMERSION) .016" SIG PTH, .022"
GND PTH**Step Description**

1. LLCR (2)
2. Gas Tight (1)
3. LLCR (2)
Max Delta = 15 mOhm

(1) Gas Tight = EIA-364-36

(2) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

Thermal AgingGroup 1

EBTM-6-12-2.0-S-RA-5

EBTF-6-12-2.0-S-RA-5

8 Assemblies

Tin (IMMERSION) .016" SIG PTH, .022"
GND PTH**Step Description**

1. Contact Gaps
2. Mating/Unmating Force (2)
3. LLCR (1)
4. Thermal Age (3)
5. LLCR (1)
Max Delta = 15 mOhm
6. Mating/Unmating Force (2)
7. Contact Gaps

(1) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(2) Mating/Unmating Force = EIA-364-13

(3) Thermal Age = EIA-364-17

Test Condition = 4 (105°C)

Time Condition = B (250 Hours)

FLOWCHARTS Continued**Mating/Unmating/Durability**Group 1

EBTM-6-12-2.0-S-RA-5

EBTF-6-12-2.0-S-RA-5

8 Assemblies

Tin (IMMERSION) .016" SIG PTH, .022"

GND PTH

Step	Description
1.	Contact Gaps
2.	LLCR (2)
3.	Mating/Unmating Force (3)
4.	Cycles Quantity = 25 Cycles
5.	Mating/Unmating Force (3)
6.	Cycles Quantity = 25 Cycles
7.	Mating/Unmating Force (3)
8.	Cycles Quantity = 25 Cycles
9.	Mating/Unmating Force (3)
10.	Cycles Quantity = 25 Cycles
11.	Mating/Unmating Force (3)
12.	Contact Gaps
13.	LLCR (2) Max Delta = 15 mOhm
14.	Thermal Shock (4)
15.	LLCR (2) Max Delta = 15 mOhm
16.	Humidity (1)
17.	LLCR (2) Max Delta = 15 mOhm
18.	Mating/Unmating Force (3)

(1) Humidity = EIA-364-31

Test Condition = B (240 Hours)

Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)

Test Exceptions: ambient pre-condition and delete steps 7a and 7b

(2) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(3) Mating/Unmating Force = EIA-364-13

(4) Thermal Shock = EIA-364-32

Exposure Time at Temperature Extremes = 1/2 Hour

Method A, Test Condition = I (-55°C to +85°C)

Test Duration = A-3 (100 Cycles)

FLOWCHARTS Continued**IR/DWV****Pin-to-Pin**

<u>Group 1</u>		<u>Group 2</u>		<u>Group 3</u>		<u>Group 4</u>	
EBTM-6-12-2.0-S-RA-5 EBTF-6-12-2.0-S-RA-5 2 Assemblies		EBTM-6-12-2.0-S-RA-5 2 Assemblies		EBTF-6-12-2.0-S-RA-5 2 Assemblies		EBTM-6-12-2.0-S-RA-5 EBTF-6-12-2.0-S-RA-5 2 Assemblies	
Tin (IMMERSION) .016" SIG PTH, .022" GND PTH		Tin (IMMERSION) .016" SIG PTH, .022" GND PTH		Tin (IMMERSION) .016" SIG PTH, .022" GND PTH		Tin (IMMERSION) .016" SIG PTH, .022" GND PTH	
Step	Description	Step	Description	Step	Description	Step	Description
1.	DWV Breakdown (2)	1.	DWV Breakdown (2)	1.	DWV Breakdown (2)	1.	IR (4)
						2.	DWV at Test Voltage(1) Test Voltage = 650 V
						3.	Thermal Shock (5)
						4.	IR (4)
						5.	DWV at Test Voltage(1) Test Voltage = 650 V
						6.	Humidity (3)
						7.	IR (4)
						8.	DWV at Test Voltage(1) Test Voltage = 650 V

Row-to-Row

<u>Group 5</u>		<u>Group 6</u>		<u>Group 7</u>		<u>Group 8</u>	
EBTM-6-12-2.0-S-RA-5 EBTF-6-12-2.0-S-RA-5 2 Assemblies		EBTM-6-12-2.0-S-RA-5 2 Assemblies		EBTF-6-12-2.0-S-RA-5 2 Assemblies		EBTM-6-12-2.0-S-RA-5 EBTF-6-12-2.0-S-RA-5 2 Assemblies	
Tin (IMMERSION) .016" SIG PTH, .022" GND PTH		Tin (IMMERSION) .016" SIG PTH, .022" GND PTH		Tin (IMMERSION) .016" SIG PTH, .022" GND PTH		Tin (IMMERSION) .016" SIG PTH, .022" GND PTH	
Step	Description	Step	Description	Step	Description	Step	Description
1.	DWV Breakdown (2)	1.	DWV Breakdown (2)	1.	DWV Breakdown (2)	1.	IR (4)
						2.	DWV at Test Voltage(1) Test Voltage = 650 V
						3.	Thermal Shock (5)
						4.	IR (4)
						5.	DWV at Test Voltage(1) Test Voltage = 650 V
						6.	Humidity (3)
						7.	IR (4)
						8.	DWV at Test Voltage(1) Test Voltage = 650 V

FLOWCHARTS Continued

Pin-to-Ground

<u>Group 9</u>		<u>Group 10</u>		<u>Group 11</u>		<u>Group 12</u>	
EBTM-6-12-2.0-S-RA-5 EBTF-6-12-2.0-S-RA-5 2 Assemblies Tin (IMMERSION) .016" SIG PTH, .022" GND PTH		EBTM-6-12-2.0-S-RA-5 2 Assemblies Tin (IMMERSION) .016" SIG PTH, .022" GND PTH		EBTF-6-12-2.0-S-RA-5 2 Assemblies Tin (IMMERSION) .016" SIG PTH, .022" GND PTH		EBTM-6-12-2.0-S-RA-5 EBTF-6-12-2.0-S-RA-5 2 Assemblies Tin (IMMERSION) .016" SIG PTH, .022" GND PTH	
Step	Description	Step	Description	Step	Description	Step	Description
1.	DWV Breakdown ⁽²⁾	1.	DWV Breakdown ⁽²⁾	1.	DWV Breakdown ⁽²⁾	1.	IR ⁽⁴⁾
						2.	DWV at Test Voltage ⁽¹⁾ Test Voltage = 650 V
						3.	Thermal Shock ⁽⁵⁾
						4.	IR ⁽⁴⁾
						5.	DWV at Test Voltage ⁽¹⁾ Test Voltage = 650 V
						6.	Humidity ⁽³⁾
						7.	IR ⁽⁴⁾
						8.	DWV at Test Voltage ⁽¹⁾ Test Voltage = 650 V

- (1) DWV at Test Voltage = EIA-364-20
Test Condition = 1 (Sea Level)
DWV test voltage is equal to 75% of the lowest breakdown voltage
Test voltage applied for 60 seconds
- (2) DWV Breakdown = EIA-364-20
Test Condition = 1 (Sea Level)
DWV test voltage is equal to 75% of the lowest breakdown voltage
Test voltage applied for 60 seconds
- (3) Humidity = EIA-364-31
Test Condition = B (240 Hours)
Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)
Test Exceptions: ambient pre-condition and delete steps 7a and 7b
- (4) IR = EIA-364-21
Test Condition = 500 Vdc, 2 Minutes Max
- (5) Thermal Shock = EIA-364-32
Exposure Time at Temperature Extremes = 1/2 Hour
Method A, Test Condition = I (-55°C to +85°C)
Test Duration = A-3 (100 Cycles)

Current Carrying Capacity

Note: Tin (IMMERSION) .016" SIG PTH, .022" GND PTH

<u>Group 1</u>		<u>Group 2</u>		<u>Group 3</u>	
EBTM-6-12-2.0-S-RA-5 EBTF-6-12-2.0-S-RA-5 1 Pins Powered Signal		EBTM-6-12-2.0-S-RA-5 EBTF-6-12-2.0-S-RA-5 20 Pins Powered Signal		EBTM-6-12-2.0-S-RA-5 EBTF-6-12-2.0-S-RA-5 40 Pins Powered Signal	
Note: EBTF signal pin "S" row to EBTM signal pin "S" row					
Step	Description	Step	Description	Step	Description
1.	CCC ⁽¹⁾ Number of Positions = 1 Rows = 1 Note: Center of connector location.	1.	CCC ⁽¹⁾ Number of Positions = 20 Rows = 1 Note: All signal pins combined carry supply while all grounds on that wafer carry return.	1.	CCC ⁽¹⁾ Number of Positions = 20 Rows = 2 Note: Center wafer carries supply while adjacent wafer carries return.

- (1) CCC = EIA-364-70
Method 2, Temperature Rise Versus Current Curve
(TIN PLATING) - Tabulate calculated current at RT,65°C, 75°C and 95°C after derating 20% and based on 105°C
(GOLD PLATING) - Tabulate calculated current at RT,85°C, 95°C and 115°C after derating 20% and based on 125°C

FLOWCHARTS Continued**Mechanical Shock/Random Vibration/LLCR**Group 1

EBTM-6-12-2.0-S-RA-5

EBTF-6-12-2.0-S-RA-5

8 Assemblies

Tin (IMMERSION) .016" SIG PTH, .022"

GND PTH

Step Description

1. LLCR ⁽¹⁾
2. Mechanical Shock ⁽²⁾
3. Random Vibration ⁽³⁾
4. LLCR ⁽¹⁾
Max Delta = 15 mOhm

(1) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(2) Mechanical Shock = EIA-364-27

Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)

Number of Shocks = 3 Per Direction, Per Axis, 18 Total

(3) Random Vibration = EIA-364-28

Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

Mechanical Shock/Random Vibration/Event DetectionGroup 1

EBTM-6-12-2.0-S-RA-5

EBTF-6-12-2.0-S-RA-5

60 Points

Tin (IMMERSION) .016" SIG PTH, .022"

GND PTH

Step Description

1. Nanosecond Event Detection
(Mechanical Shock) ⁽¹⁾
2. Nanosecond Event Detection
(Random Vibration) ⁽²⁾

(1) Nanosecond Event Detection (Mechanical Shock)

Use EIA-364-87 for Nanosecond Event Detection:

Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-27 for Mechanical Shock:

Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)

Number of Shocks = 3 Per Direction, Per Axis, 18 Total

(2) Nanosecond Event Detection (Random Vibration)

Use EIA-364-87 for Nanosecond Event Detection:

Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-28 for Random Vibration:

Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

ATTRIBUTE DEFINITIONS

The following is a brief, simplified description of attributes.

THERMAL:

- 1) EIA-364-17, *Temperature Life with or without Electrical Load Test Procedure for Electrical Connectors*.
- 2) Test Condition at 105° C.
- 3) Test Time Condition B for 250 hours.
- 4) All test samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

THERMAL SHOCK:

- 1) EIA-364-32, *Thermal Shock (Temperature Cycling) Test Procedure for Electrical Connectors*.
- 2) Test Condition I: -55°C to +85°C.
- 3) Test Time: ½ hour dwell at each temperature extreme.
- 4) Number of Cycles: 100
- 5) All test samples are pre-conditioned at ambient.
- 6) All test samples are exposed to environmental stressing in the mated condition.

HUMIDITY:

- 1) Reference document: EIA-364-31, *Humidity Test Procedure for Electrical Connectors*.
- 2) Test Condition B, 240 Hours.
- 3) Method III, +25° C to + 65° C, 90% to 98% Relative Humidity excluding sub-cycles 7a and 7b.
- 4) All samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

MECHANICAL SHOCK (Specified Pulse):

- 1) Reference document: EIA-364-27, *Mechanical Shock Test Procedure for Electrical Connectors*
- 2) Test Condition C
- 3) Peak Value: 100 G
- 4) Duration: 6 Milliseconds
- 5) Wave Form: Half Sine
- 6) Velocity: 12.3 ft/s
- 7) Number of Shocks: 3 Shocks / Direction, 3 Axis (18 Total)

VIBRATION:

- 1) Reference document: EIA-364-28, *Vibration Test Procedure for Electrical Connectors*
- 2) Test Condition V, Letter B
- 3) Power Spectral Density: 0.04 G² / Hz
- 4) G 'RMS': 7.56
- 5) Frequency: 50 to 2000 Hz
- 6) Duration: 2.0 Hours per axis (3 axis total)

NANOSECOND-EVENT DETECTION:

- 1) Reference document: EIA-364-87, *Nanosecond-Event Detection for Electrical Connectors*
- 2) Prior to test, the samples were characterized to assure the low nanosecond event being monitored will trigger the detector.
- 3) After characterization it was determined the test samples could be monitored for 50 nanosecond events

MATING/UNMATING:

- 1) Reference document: EIA-364-13, *Mating and Unmating Forces Test Procedure for Electrical Connectors*.
- 2) The full insertion position was to within 0.003" to 0.004" of the plug bottoming out in the receptacle to prevent damage to the system under test.
- 3) One of the mating parts is secured to a floating X-Y table to prevent damage during cycling.

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes.

TEMPERATURE RISE (Current Carrying Capacity, CCC):

- 1) EIA-364-70, *Temperature Rise versus Current Test Procedure for Electrical Connectors and Sockets*.
- 2) When current passes through a contact, the temperature of the contact increases as a result of I^2R (resistive) heating.
- 3) The number of contacts being investigated plays a significant part in power dissipation and therefore temperature rise.
- 4) The size of the temperature probe can affect the measured temperature.
- 5) Copper traces on PC boards will contribute to temperature rise:
 - a. Self-heating (resistive)
 - b. Reduction in heat sink capacity affecting the heated contacts.
- 6) A de-rating curve, usually 20%, is calculated.
- 7) Calculated de-rated currents at four temperature points are reported:
 - a. Ambient
 - b. 85° C
 - c. 95° C
 - d. 115° C
- 8) Typically, neighboring contacts (in close proximity to maximize heat buildup) are energized.
- 9) The thermocouple (or temperature measuring probe) will be positioned at a location to sense the maximum temperature in the vicinity of the heat generation area.
- 10) A computer program, *TR 803.exe*, ensures accurate stability for data acquisition.
- 11) Hook-up wire cross section is larger than the cross section of any connector leads/PC board traces, jumpers, etc.
- 12) Hook-up wire length is longer than the minimum specified in the referencing standard.

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes.

LLCR:

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: -----Stable
 - b. $+5.1$ to $+10.0$ mOhms:-----Minor
 - c. $+10.1$ to $+15.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms: -----Unstable
 - f. $>+1000$ mOhms:-----Open Failure

GAS TIGHT:

To provide method for evaluating the ability of the contacting surfaces in preventing penetration of harsh vapors which might lead to oxide formation that may degrade the electrical performance of the contact system.

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms:-----Stable
 - b. $+5.1$ to $+10.0$ mOhms: -----Minor
 - c. $+10.1$ to $+15.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms:-----Unstable
 - f. $>+1000$ mOhms:-----Open Failure
- 4) Procedure:
 - a. Reference document: EIA-364-36, *Test Procedure for Determination of Gas-Tight Characteristics for Electrical Connectors, Sockets and/or Contact Systems*.
 - b. Test Conditions:
 - i. Class II--- Mated pairs of contacts assembled to their plastic housings.
 - ii. Reagent grade Nitric Acid shall be used of sufficient volume to saturate the test chamber.
 - iii. The ratio of the volume of the test chamber to the surface area of the acid shall be 10:1.
 - iv. The chamber shall be saturated with the vapor for at least 15 minutes before samples are added.
 - v. Exposure time, 55 to 65 minutes.
 - vi. The samples shall be no closer to the chamber walls than 1 inch and no closer to the surface of the acid than 3 inches.
 - vii. The samples shall be dried after exposure for a minimum of 1 hour.
 - viii. Drying temperature 50° C
 - ix. The final LLCR shall be conducted within 1 hour after drying.

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes.

INSULATION RESISTANCE (IR):

To determine the resistance of insulation materials to leakage of current through or on the surface of these materials when a DC potential is applied.

- 1) PROCEDURE:
 - a. Reference document: EIA-364-21, *Insulation Resistance Test Procedure for Electrical Connectors*.
 - b. Test Conditions:
 - i. Between Adjacent Contacts or Signal-to-Ground
 - ii. Electrification Time 2.0 minutes
 - iii. Test Voltage (500 VDC) corresponds to calibration settings for measuring resistances.
- 2) MEASUREMENTS:
- 3) When the specified test voltage is applied (VDC), the insulation resistance shall not be less than 1000 megohms.

DIELECTRIC WITHSTANDING VOLTAGE (DWV):

To determine if the sockets can operate at its rated voltage and withstand momentary over potentials due to switching, surges, and other similar phenomenon. Separate samples are used to evaluate the effect of environmental stresses so not to influence the readings from arcing that occurs during the measurement process.

- 1) PROCEDURE:
 - a. Reference document: EIA-364-20, *Withstanding Voltage Test Procedure for Electrical Connectors*.
 - b. Test Conditions:
 - i. Between Adjacent Contacts or Signal-to-Ground
 - ii. Barometric Test Condition 1
 - iii. Rate of Application 500 V/Sec
 - iv. Test Voltage (VAC) until breakdown occurs.
- 2) MEASUREMENTS/CALCULATIONS
 - a. The breakdown voltage shall be measured and recorded.
 - b. The dielectric withstanding voltage shall be recorded as 75% of the minimum breakdown voltage.
 - c. The working voltage shall be recorded as one-third (1/3) of the dielectric withstanding voltage (one-fourth of the breakdown voltage).

RESULTS

Temperature Rise, CCC at a 20% de-rating

- CCC for a 30°C Temperature Rise-----5.1 A per contact with 1 contact (1x1) powered.
- CCC for a 30°C Temperature Rise-----15.3 A with 20 contacts (1x20) powered.
- CCC for a 30°C Temperature Rise-----16.3 A with 40 contacts (2x20) powered.

Mating – Unmating Forces

Thermal Aging Group

- **Initial**
 - **Mating**
 - **Min** -----16.15 lbs
 - **Max** -----18.10 lbs
 - **Unmating**
 - **Min** -----10.55 lbs
 - **Max** -----11.90 lbs
- **After Thermal**
 - **Mating**
 - **Min** ----- 8.21 lbs
 - **Max** ----- 9.86 lbs
 - **Unmating**
 - **Min** ----- 7.70 lbs
 - **Max** ----- 8.15 lbs

RESULTS Continued**Mating/Unmating Durability Group**

- **Initial**
 - **Mating**
 - **Min** -----14.59 lbs
 - **Max** -----15.85 lbs
 - **Unmating**
 - **Min** -----10.08 lbs
 - **Max** -----11.16 lbs
- **After 25 Cycles**
 - **Mating**
 - **Min** -----17.85 lbs
 - **Max** -----20.26 lbs
 - **Unmating**
 - **Min** -----13.46 lbs
 - **Max** -----15.76 lbs
- **After 50 Cycles**
 - **Mating**
 - **Min** -----17.61 lbs
 - **Max** -----18.74 lbs
 - **Unmating**
 - **Min** -----14.41 lbs
 - **Max** -----16.21 lbs
- **After 75 Cycles**
 - **Mating**
 - **Min** -----17.10 lbs
 - **Max** -----19.46 lbs
 - **Unmating**
 - **Min** -----14.25 lbs
 - **Max** -----16.06 lbs
- **After 100 Cycles**
 - **Mating**
 - **Min** -----16.82 lbs
 - **Max** -----18.59 lbs
 - **Unmating**
 - **Min** -----13.90 lbs
 - **Max** -----15.45 lbs
- **After Humidity**
 - **Mating**
 - **Min** ----- 7.83 lbs
 - **Max** -----10.23 lbs
 - **Unmating**
 - **Min** ----- 7.22 lbs
 - **Max** ----- 8.01 lbs

RESULTS Continued**Insulation Resistance minimums, IR****Pin to Pin**

- **Initial**
 - Mated-----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- **Thermal Shock**
 - Mated-----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- **Humidity**
 - Mated----- 3900 Meg Ω ----- Passed
 - Unmated -----10300 Meg Ω ----- Passed

Row to Row

- **Initial**
 - Mated-----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- **Thermal Shock**
 - Mated-----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- **Humidity**
 - Mated-----13200 Meg Ω ----- Passed
 - Unmated -----27100 Meg Ω ----- Passed

Pin to Ground

- **Initial**
 - Mated-----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- **Thermal Shock**
 - Mated-----45000 Meg Ω ----- Passed
 - Unmated -----45000 Meg Ω ----- Passed
- **Humidity**
 - Mated-----172 Meg Ω ----- Passed
 - Unmated -----139 Meg Ω ----- Passed

Dielectric Withstanding Voltage minimums, DWV

- **Minimums**
 - Breakdown Voltage-----866 VAC
 - Test Voltage -----650 VAC
 - Working Voltage -----217 VAC

Pin to Pin

- **Initial DWV**-----Passed
- **Thermal DWV**-----Passed

Row to Row

- **Initial DWV**-----Passed
- **Thermal DWV**-----Passed

Pin to Ground

- **Initial DWV**-----Passed
- **Thermal DWV**-----Passed

RESULTS Continued**LLCR Thermal Aging (56 signal1,56 signal2,32 signal3 and 48 ground LLCR test points)****Signal 1**

- **Initial** ----- 13.80 mOhms Max
- **Thermal Aging**
 - **<= +5.0 mOhms**----- 56 Points ----- Stable
 - **+5.1 to +10.0 mOhms**-----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms**-----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms**-----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

Signal 2

- **Initial** ----- 19.37 mOhms Max
- **Thermal Aging**
 - **<= +5.0 mOhms**----- 56 Points ----- Stable
 - **+5.1 to +10.0 mOhms**-----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms**-----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms**-----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

Signal 3

- **Initial** ----- 25.90 mOhms Max
- **Thermal Aging**
 - **<= +5.0 mOhms**----- 32 Points ----- Stable
 - **+5.1 to +10.0 mOhms**-----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms**-----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms**-----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

Ground

- **Initial** ----- 14.65 mOhms Max
- **Thermal Aging**
 - **<= +5.0 mOhms**----- 48 Points ----- Stable
 - **+5.1 to +10.0 mOhms**-----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms**-----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms**-----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

RESULTS Continued**LLCR Gas Tight (56 signal1,56 signal2,32 signal3 and 48 ground LLCR test points)****Signal 1**

- **Initial** ----- 13.75 mOhms Max
- **Gas-Tight**
 - **<= +5.0 mOhms**----- 56 Points ----- Stable
 - **+5.1 to +10.0 mOhms**-----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms**-----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms**-----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

Signal 2

- **Initial** ----- 19.47 mOhms Max
- **Gas-Tight**
 - **<= +5.0 mOhms**----- 56 Points ----- Stable
 - **+5.1 to +10.0 mOhms**-----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms**-----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms**-----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

Signal 3

- **Initial** ----- 24.95 mOhms Max
- **Gas-Tight**
 - **<= +5.0 mOhms**----- 32 Points ----- Stable
 - **+5.1 to +10.0 mOhms**-----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms**-----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms**-----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

Ground

- **Initial** ----- 14.57 mOhms Max
- **Gas-Tight**
 - **<= +5.0 mOhms**----- 48 Points ----- Stable
 - **+5.1 to +10.0 mOhms**-----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms**-----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms**-----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

RESULTS Continued**LLCR Durability (56 signal1,56 signal2,32 signal3 and 48 ground LLCR test points)****Signal 1**

- **Initial** ----- 13.85 mOhms Max
- **Durability, 100 Cycles**
 - **<= +5.0 mOhms**----- 56 Points ----- Stable
 - **+5.1 to +10.0 mOhms**----- 0 Points ----- Minor
 - **+10.1 to +15.0 mOhms**----- 0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms**----- 0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**----- 0 Points ----- Unstable
 - **>+1000 mOhms**----- 0 Points ----- Open Failure
- **Thermal**
 - **<= +5.0 mOhms**----- 56 Points ----- Stable
 - **+5.1 to +10.0 mOhms**----- 0 Points ----- Minor
 - **+10.1 to +15.0 mOhms**----- 0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms**----- 0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**----- 0 Points ----- Unstable
 - **>+1000 mOhms**----- 0 Points ----- Open Failure
- **Humidity**
 - **<= +5.0 mOhms**----- 56 Points ----- Stable
 - **+5.1 to +10.0 mOhms**----- 0 Points ----- Minor
 - **+10.1 to +15.0 mOhms**----- 0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms**----- 0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**----- 0 Points ----- Unstable
 - **>+1000 mOhms**----- 0 Points ----- Open Failure

Signal 2

- **Initial** ----- 19.46 mOhms Max
- **Durability, 100 Cycles**
 - **<= +5.0 mOhms**----- 56 Points ----- Stable
 - **+5.1 to +10.0 mOhms**----- 0 Points ----- Minor
 - **+10.1 to +15.0 mOhms**----- 0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms**----- 0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**----- 0 Points ----- Unstable
 - **>+1000 mOhms**----- 0 Points ----- Open Failure
- **Thermal**
 - **<= +5.0 mOhms**----- 56 Points ----- Stable
 - **+5.1 to +10.0 mOhms**----- 0 Points ----- Minor
 - **+10.1 to +15.0 mOhms**----- 0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms**----- 0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**----- 0 Points ----- Unstable
 - **>+1000 mOhms**----- 0 Points ----- Open Failure
- **Humidity**
 - **<= +5.0 mOhms**----- 56 Points ----- Stable
 - **+5.1 to +10.0 mOhms**----- 0 Points ----- Minor
 - **+10.1 to +15.0 mOhms**----- 0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms**----- 0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**----- 0 Points ----- Unstable
 - **>+1000 mOhms**----- 0 Points ----- Open Failure

Signal 3

- **Initial** ----- 24.97 mOhms Max
- **Durability, 100 Cycles**
 - **<= +5.0 mOhms**----- 32 Points ----- Stable
 - **+5.1 to +10.0 mOhms** -----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure
- **Thermal**
 - **<= +5.0 mOhms**----- 31 Points ----- Stable
 - **+5.1 to +10.0 mOhms** -----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----1 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure
- **Humidity**
 - **<= +5.0 mOhms**----- 31 Points ----- Stable
 - **+5.1 to +10.0 mOhms** -----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----1 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

Ground

- **Initial** ----- 14.63 mOhms Max
- **Durability, 100 Cycles**
 - **<= +5.0 mOhms**----- 48 Points ----- Stable
 - **+5.1 to +10.0 mOhms** -----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure
- **Thermal**
 - **<= +5.0 mOhms**----- 48 Points ----- Stable
 - **+5.1 to +10.0 mOhms** -----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure
- **Humidity**
 - **<= +5.0 mOhms**----- 48 Points ----- Stable
 - **+5.1 to +10.0 mOhms** -----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

RESULTS Continued**LLCR Shock & Vibration (56 signal1,56 signal2,32 signal3 and 48 ground LLCR test points)****Signal 1**

- **Initial** ----- 14.22 mOhms Max
- **Shock &Vibration**
 - **<= +5.0 mOhms**----- 56 Points ----- Stable
 - **+5.1 to +10.0 mOhms**-----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

Signal 2

- **Initial** ----- 19.57 mOhms Max
- **Shock &Vibration**
 - **<= +5.0 mOhms**----- 56 Points ----- Stable
 - **+5.1 to +10.0 mOhms** -----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

Signal 3

- **Initial** ----- 25.14 mOhms Max
- **Shock &Vibration**
 - **<= +5.0 mOhms**----- 32 Points ----- Stable
 - **+5.1 to +10.0 mOhms** -----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

Ground

- **Initial** ----- 14.51 mOhms Max
- **Shock &Vibration**
 - **<= +5.0 mOhms**----- 48 Points ----- Stable
 - **+5.1 to +10.0 mOhms** -----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

Mechanical Shock & Random Vibration:

- **Shock**
 - **No Damage**----- Pass
 - **50 Nanoseconds** ----- Pass
- **Vibration**
 - **No Damage**----- Pass
 - **50 Nanoseconds** ----- Pass


DATA SUMMARIES

TEMPERATURE RISE (Current Carrying Capacity, CCC):

- 1) High quality thermocouples whose temperature slopes track one another were used for temperature monitoring.
- 2) The thermocouples were placed at a location to sense the maximum temperature generated during testing.
- 3) Temperature readings recorded are those for which three successive readings, 15 minutes apart, differ less than 1° C (computer-controlled data acquisition).
- 4) Adjacent contacts were powered:
 - a. Linear configuration with 1 adjacent conductors/contacts powered.


CR-1104501
1 (1X1) Contacts in Series
Part Numbers: EBTM-6-12-2.0-S-RA-5 / EBTF-6-12-2.0-S-RA-5

Current Rating per Contact (30 Deg. Rise, 20% Derated) =5.1 Amps



DATA SUMMARIES Continued


CR-1104501
1 (1X1) Contacts in Series
Part Numbers: EBTM-6-12-2.0-S-RA-5 / EBTF-6-12-2.0-S-RA-5




DATA SUMMARIES Continued

b. Linear configuration with 20 adjacent conductors/contacts powered.

CR-1104501
 20 (1X20) Contacts in Series
 Part Numbers: EBTM-6-12-2.0-S-RA-5/EBTF-6-12-2.0-S-RA-5





CR-1104501
 20 (1X20) Contacts in Series
 Part Numbers: EBTM-6-12-2.0-S-RA-5/EBTF-6-12-2.0-S-RA-5



DATA SUMMARIES Continued

c. Linear configuration with 40 adjacent conductors/contacts powered.

CR-1104501
 40 (2x20) Contacts in Series
 Part Numbers: EBTM-6-12-2.0-S-RA-5/EBTF-6-12-2.0-S-RA-5



DATA SUMMARIES Continued**MATING/UNMATING:****Thermal Aging Group**

	Initial				After Thermals			
	Mating		Unmating		Mating		Unmating	
	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)
Minimum	71.84	16.15	46.93	10.55	36.52	8.21	34.25	7.70
Maximum	80.51	18.10	52.93	11.90	43.86	9.86	36.25	8.15
Average	75.67	17.01	50.68	11.39	39.05	8.78	35.00	7.87
St Dev	2.53	0.57	1.93	0.43	2.73	0.61	0.68	0.15
Count	8	8	8	8	8	8	8	8

Mating/Unmating Durability Group

	Initial				25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)
Minimum	64.90	14.59	44.84	10.08	79.40	17.85	59.87	13.46
Maximum	70.50	15.85	49.64	11.16	90.12	20.26	70.10	15.76
Average	67.63	15.21	47.42	10.66	85.16	19.15	64.64	14.53
St Dev	1.96	0.44	1.60	0.36	3.44	0.77	3.57	0.80
Count	8	8	8	8	8	8	8	8

	50 Cycles				75 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)
Minimum	78.33	17.61	64.10	14.41	76.06	17.10	63.38	14.25
Maximum	83.36	18.74	72.10	16.21	86.56	19.46	71.43	16.06
Average	81.20	18.26	67.75	15.23	79.82	17.95	66.84	15.03
St Dev	1.90	0.43	3.44	0.77	3.44	0.77	2.80	0.63
Count	8	8	8	8	8	8	8	8

	100 Cycles				After Humidity			
	Mating		Unmating		Mating		Unmating	
	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)	Newtons	Force (Lbs)
Minimum	74.82	16.82	61.83	13.90	34.83	7.83	32.11	7.22
Maximum	82.69	18.59	68.72	15.45	45.50	10.23	35.63	8.01
Average	78.25	17.59	65.14	14.64	42.06	9.46	34.09	7.66
St Dev	2.71	0.61	2.65	0.60	3.70	0.83	1.21	0.27
Count	8	8	8	8	8	8	8	8

DATA SUMMARIES Continued**INSULATION RESISTANCE (IR):**

	Pin to Pin		
	Mated	Unmated	Unmated
Minimum	EBTM/EBTF	EBTM	EBTF
Initial	45000	45000	45000
Thermal	45000	45000	45000
Humidity	3900	45000	10300

	Row to Row		
	Mated	Unmated	Unmated
Minimum	EBTM/EBTF	EBTM	EBTF
Initial	45000	45000	45000
Thermal	45000	45000	45000
Humidity	13200	27100	36000

	Pin to Ground		
	Mated	Unmated	Unmated
Minimum	EBTM/EBTF	EBTM	EBTF
Initial	45000	45000	45000
Thermal	45000	45000	45000
Humidity	172	236	139

DIELECTRIC WITHSTANDING VOLTAGE (DWV):

Voltage Rating Summary	
Minimum	EBTM/EBTF
Break Down Voltage	866
Test Voltage	650
Working Voltage	217

Pin to Pin	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed

Row to Row	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed

Pin to Ground	
Initial Test Voltage	Passed
After Thermal Test Voltage	Passed

DATA SUMMARIES Continued**LLCR Thermal Aging:**

- 1) A total of 56 signal1,56 signal2,32 signal3 and 48 ground points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: -----Stable
 - b. $+5.1$ to $+10.0$ mOhms:-----Minor
 - c. $+10.1$ to $+15.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms: -----Unstable
 - f. $>+1000$ mOhms:-----Open Failure

DATA SUMMARIES Continued

LLCR Measurement Summaries by Pin Type			
Date	2024/5/29	2024/6/14	
Room Temp (Deg C)	22	22	
Rel Humidity (%)	45	53	
Technician	Brian Stemle	Brian Stemle	
mOhm values	Actual	Delta	
	Initial	Thermal	
Pin Type: Signal 1			
Average	11.63	0.42	
St. Dev.	0.97	0.41	
Min	9.29	0.02	
Max	13.8	1.59	
Summary Count	56	56	
Total Count	56	56	
Pin Type: Signal 2			
Average	16.93	0.54	
St. Dev.	1.91	0.63	
Min	13.82	0	
Max	19.37	3.34	
Summary Count	56	56	
Total Count	56	56	
Pin Type: Signal 3			
Average	23.38	0.44	
St. Dev.	1.45	0.67	
Min	21.59	0	
Max	25.9	3.15	
Summary Count	32	32	
Total Count	32	32	
Pin Type: GND 1			
Average	10.41	0.38	
St. Dev.	2.66	0.66	
Min	6.07	0.01	
Max	14.65	3.75	
Summary Count	48	48	
Total Count	48	48	

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	<=5	>5 & <=10	>10 & <=15	>15 & <=50	>50 & <=1000	>1000
Thermal	192	0	0	0	0	0

DATA SUMMARIES Continued**LLCR Durability:**

- 1) A total of 56 signal1,56 signal2,32 signal3 and 48 ground points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: -----Stable
 - b. $+5.1$ to $+10.0$ mOhms: -----Minor
 - c. $+10.1$ to $+15.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms -----Unstable
 - f. $>+1000$ mOhms: -----Open Failure

DATA SUMMARIES Continued

LLCR Measurement Summaries by Pin Type				
Date	2024/5/28	2024/6/6	2024/6/11	2024/6/24
Room Temp (Deg C)	22	22	22	22
Rel Humidity (%)	52	55	44	54
Technician	Brian Stemle	Brian Stemle	Brian Stemle	Brian Stemle
mOhm values	Actual Initial	Delta 100 Cycles	Delta Therm Shck	Delta Humidity
Pin Type: Signal 1				
Average	11.69	0.18	0.47	0.36
St. Dev.	0.89	0.19	0.33	0.25
Min	10.14	0	0.01	0
Max	13.85	0.7	1.52	1.11
Summary Count	56	56	56	56
Total Count	56	56	56	56
Pin Type: Signal 2				
Average	16.87	0.18	0.57	0.36
St. Dev.	1.89	0.17	0.35	0.32
Min	14.05	0	0.01	0
Max	19.46	0.88	1.47	1.57
Summary Count	56	56	56	56
Total Count	56	56	56	56
Pin Type: Signal 3				
Average	23.29	0.22	1.01	0.88
St. Dev.	1.39	0.19	1.83	2.17
Min	21.66	0	0.07	0.01
Max	24.97	0.85	10.81	12.63
Summary Count	32	32	32	32
Total Count	32	32	32	32
Pin Type: GND 1				
Average	10.45	0.21	0.24	0.24
St. Dev.	2.61	0.15	0.18	0.28
Min	6.17	0.01	0.01	0.01
Max	14.63	0.73	1.04	1.64
Summary Count	48	48	48	48
Total Count	48	48	48	48

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	<=5	>5 & <=10	>10 & <=15	>15 & <=50	>50 & <=1000	>1000
100 Cycles	192	0	0	0	0	0
Therm Shck	191	0	1	0	0	0
Humidity	191	0	1	0	0	0

DATA SUMMARIES Continued**LLCR Gas Tight:**

- 1) A total of 56 signal1,56 signal2,32 signal3 and 48 ground points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: -----Stable
 - b. $+5.1$ to $+10.0$ mOhms: -----Minor
 - c. $+10.1$ to $+15.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms: -----Unstable
 - f. $>+1000$ mOhms: -----Open Failure

DATA SUMMARIES Continued

LLCR Measurement Summaries by Pin Type			
Date	2024/5/21	2024/5/21	
Room Temp (Deg C)	22	23	
Rel Humidity (%)	52	54	
Technician	Brian Stemle	Brian Stemle	
mOhm values	Actual	Delta	
	Initial	Acid Vapor	
Pin Type: Signal 1			
Average	11.57	0.32	
St. Dev.	0.87	0.12	
Min	10.03	0.01	
Max	13.75	0.53	
Summary Count	56	56	
Total Count	56	56	
Pin Type: Signal 2			
Average	16.84	0.58	
St. Dev.	1.89	0.14	
Min	13.96	0.08	
Max	19.47	0.84	
Summary Count	56	56	
Total Count	56	56	
Pin Type: Signal 3			
Average	23.18	0.72	
St. Dev.	1.46	0.13	
Min	21.42	0.3	
Max	24.95	1.06	
Summary Count	32	32	
Total Count	32	32	
Pin Type: GND 1			
Average	10.35	0.33	
St. Dev.	2.61	0.17	
Min	6.07	0.01	
Max	14.57	0.9	
Summary Count	48	48	
Total Count	48	48	

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	<=5	>5 & <=10	>10 & <=15	>15 & <=50	>50 & <=1000	>1000
Acid Vapor	192	0	0	0	0	0

DATA SUMMARIES Continued**LLCR Shock & Vibration:**

- 1). A total of 56 signal1,56 signal2,32 signal3 and 48 ground points were measured.
- 2). EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3). The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: -----Stable
 - b. $+5.1$ to $+10.0$ mOhms: -----Minor
 - c. $+10.1$ to $+15.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms -----Unstable
 - f. $>+1000$ mOhms:-----Open Failure

DATA SUMMARIES Continued

LLCR Measurement Summaries by Pin Type			
Date	2024/5/20	2024/6/28	
Room Temp (Deg C)	22	23	
Rel Humidity (%)	54	50	
Technician	Brian Stemle	Brian Stemle	
mOhm values	Actual	Delta	
	Initial	Shock-Vib	
Pin Type: Signal 1			
Average	11.62	0.41	
St. Dev.	0.87	0.33	
Min	9.87	0	
Max	14.22	1.84	
Summary Count	56	56	
Total Count	56	56	
Pin Type: Signal 2			
Average	16.97	0.41	
St. Dev.	1.82	0.3	
Min	14.22	0.01	
Max	19.57	1.36	
Summary Count	56	56	
Total Count	56	56	
Pin Type: Signal 3			
Average	23.43	0.33	
St. Dev.	1.36	0.28	
Min	21.67	0	
Max	25.14	1.16	
Summary Count	32	32	
Total Count	32	32	
Pin Type: GND 1			
Average	10.42	0.15	
St. Dev.	2.61	0.17	
Min	6.06	0.01	
Max	14.51	0.86	
Summary Count	48	48	
Total Count	48	48	

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	≤5	>5 & ≤10	>10 & ≤15	>15 & ≤50	>50 & ≤1000	>1000
Shock-Vib	192	0	0	0	0	0

DATA SUMMARIES Continued

Nanosecond Event Detection:

Shock and Vibration Event Detection Summary	
Contacts tested	60
Test Condition	C, 100g's, 6ms, Half-Sine
Shock Events	0
Test Condition	V-B, 7.56 rms g
Vibration Events	0
Total Events	0

EQUIPMENT AND CALIBRATION SCHEDULES**Equipment #:** TCT-04**Description:** Dillon Quantrol TC21 25-1000 mm/min series test stand**Manufacturer:** Dillon Quantrol**Model:** TC2 I series test stand**Serial #:** 04-1041-04**Accuracy:** Speed Accuracy: +/- 5% of indicated speed; Speed Accuracy: +/- 5% of indicated speed;
... Last Cal: 05/29/2024, Next Cal: 05/29/2025**Equipment #:** MO-11**Description:** Switch/Multimeter**Manufacturer:** Keithley**Model:** 3706**Serial #:** 120169**Accuracy:** See Manual

... Last Cal: 09/11/2023, Next Cal: 09/11/2024

Equipment #: TSC-01**Description:** Vertical Thermal Shock Chamber**Manufacturer:** Cincinnati Sub Zero**Model:** VTS-3-6-6-SC/AC**Serial #:** 10-VT14993**Accuracy:** See Manual

... Last Cal: 06/30/2024, Next Cal: 06/30/2025

Equipment #: THC-05**Description:** Temperature/Humidity Chamber (Chamber Room)**Manufacturer:** Thermotron**Model:** SM-8-3800**Serial #:** 05 23 00 02**Accuracy:** See Manual

... Last Cal: 11/14/2023, Next Cal: 11/14/2024

Equipment #: HPT-01**Description:** Hipot Safety Tester**Manufacturer:** Vitrek**Model:** V73**Serial #:** 019808**Accuracy:**

... Last Cal: 05/15/2024, Next Cal: 05/15/2025

EQUIPMENT AND CALIBRATION SCHEDULES**Equipment #:** PS-02**Description:** Power Supply**Manufacturer:** Hewlett-Packard**Model:** 6033A**Serial #:** N/A**Accuracy:** See Manual

... Last Cal: NOT CALIBRATED

Equipment #: MO-04**Description:** Multimeter /Data Acquisition System**Manufacturer:** Keithley**Model:** 2700**Serial #:** 0798688**Accuracy:** See Manual

... Last Cal: 09/11/2023, Next Cal: 09/11/2024

Equipment #: SVC-01**Description:** Shock & Vibration Table**Manufacturer:** Data Physics**Model:** LE-DSA-10-20K**Serial #:** 10037**Accuracy:** See Manual

... Last Cal: 04/22/2024, Next Cal: 04/22/2025

Equipment #: ACLM-01**Description:** Accelerometer**Manufacturer:** PCB Piezotronics**Model:** 352C03**Serial #:** 115819**Accuracy:** See Manual

... Last Cal: 07/18/2024, Next Cal: 07/18/2025

Equipment #: ED-03**Description:** Event Detector**Manufacturer:** Analysis Tech**Model:** 32EHD**Serial #:** 1100604**Accuracy:** See Manual

... Last Cal: 10/31/2023, Next Cal: 10/31/2024