




Project Number: Design Qualification Test Report	Tracking Code: CR-1142002_Report_Rev_1
Requested by: Joe Huang	Date: 2/13/2025
Part #: RF047-A-M0RJ-505050-0305	
Part description: RF047-A-M0RJ	Tech: Keney Chen
Test Start: 8/21/2024	Test Completed: 1/4/2025



DESIGN QUALIFICATION TEST REPORT

RF047-A-M0RJ
RF047-A-M0RJ-505050-0305

Tracking Code: CR-1142002_Report_Rev_1	Part #: RF047--A-M0RJ-505050-0305
Part description: RF047-A-M0RJ	

REVISION HISTORY

DATA	REV.NUM.	DESCRIPTION	ENG
1/13/2025	1	Initial Issue	KC

CERTIFICATION

All instruments and measuring equipment were calibrated to National Institute for Standards and Technology (NIST) traceable standards according to ISO 10012-1 and ANSI/NCSL 2540-1, as applicable.

All contents contained herein are the property of Samtec. No portion of this report, in part or in full shall be reproduced without prior written approval of Samtec.

SCOPE

To perform the following tests: Design Qualification test. Please see test plan.

APPLICABLE DOCUMENTS

Standards: EIA-364 and MIL-PRF-39012.

TEST SAMPLES AND PREPARATION

- 1) All materials were manufactured in accordance with the applicable product specification.
- 2) All test samples were identified and encoded to maintain traceability throughout the test sequences.
- 3) Parts not intended for testing LLCR and DWV/IR are visually inspected and cleaned if necessary.
- 4) Any additional preparation will be noted in the individual test sequences.

FLOWCHARTS**IR/DWV****Pin-to-Ground**Group 1

RF047-A-M0RJ-505050-0305

5 Assemblies

Step	Description
1.	Interface Gaging <i>Note: Measure and record center contact recession below the body. Spec 0.00~0.140mm</i>
2.	IR (2) - Non Standard
3.	DWV at Test Voltage ⁽¹⁾ - Non Standard Test Voltage = 500 V
4.	LLCR (3)
5.	Thermal Shock (4) - Non Standard
6.	IR (2) - Non Standard
7.	DWV at Test Voltage ⁽¹⁾ - Non Standard Test Voltage = 500 V
8.	LLCR (3) Max Delta = 15 mOhm
9.	Interface Gaging <i>Note: Measure and record center contact recession below the body. Spec 0.00~0.140mm</i>
10.	Visual Inspection <i>Note: Take a photo if failed</i>

(1) DWV at Test Voltage = Other

325 V rms min. at sea level
per DSCC 10020

(2) IR = Other

MIL-PRF-39012
5,000 megohms minimum per DSCC 10020

(3) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max
Test Current = 100 mA Max

(4) Thermal Shock = EIA-364-32

Exposure Time at Temperature Extremes = 1/2 Hour
Method A, Test Condition = I (-55°C to +85°C)
Test Duration = A-3 (100 Cycles)

FLOWCHARTS Continued

Mechanical Shock/Random Vibration/Event Detection

Group 1

RF047-A-M0RJ-505050-0305

RF047-A-M0SP-505050-0305

5 Assemblies

Mated Before Test

Step	Description
1.	LLCR ⁽¹⁾
2.	Nanosecond Event Detection (Mechanical Shock) ⁽²⁾ - Non Standard
3.	High Frequency Vibration <i>Note: MIL-STD-202, method 204, Condition D</i>
4.	LLCR ⁽¹⁾ Max Delta = 15 mOhm

(1) LLCR = EIA-364-23
Open Circuit Voltage = 20 mV Max
Test Current = 100 mA Max

(2) Nanosecond Event Detection (Mechanical Shock) = Other
MIL-STD-202, method 213, condition I

FLOWCHARTS Continued

Cable Pull

Group 1
 RF047-A-M0RJ-505050-0305

 5 Assemblies
 Pull To Destruct

- | Step | Description |
|------|--|
| 1. | Cable Pull ⁽¹⁾ - Non Standard
<i>Note: Record the force</i> |

Group 2
 RF047-A-M0RJ-505050-0305

 5 Assemblies

- | Step | Description |
|------|---|
| 1. | Interface Gaging
<i>Note: Measure and record center contact recession below the body. Spec 0.00~0.140mm</i> |
| 2. | LLCR ⁽³⁾
<i>Note: Signal to ground</i> |
| 3. | Cable Retention ⁽²⁾ - Non Standard
<i>Note: Apply 5 pounds for cable retention test.</i> |
| 4. | LLCR ⁽³⁾
Max Delta = 15 mOhm
<i>Note: Signal to ground</i> |
| 5. | Interface Gaging
<i>Note: Measure and record center contact recession below the body. Spec 0.00~0.140mm</i> |

(1) Cable Pull = Other
 Pull to destruct. Record destruction force.
 (2) Cable Retention = Other
 (3) LLCR = EIA-364-23
 Open Circuit Voltage = 20 mV Max
 Test Current = 100 mA Max

ATTRIBUTE DEFINITIONS

The following is a brief, simplified description of attributes.

THERMAL SHOCK:

- 1) EIA-364-32, *Thermal Shock (Temperature Cycling) Test Procedure for Electrical Connectors*.
- 2) Test Condition 1: -55°C to +85°C
- 3) Test Time: ½ hour dwell at each temperature extreme
- 4) Number of Cycles: 100
- 5) All test samples are pre-conditioned at ambient.
- 6) All test samples are exposed to environmental stressing in the mated condition.

LLCR:

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
 - a. $\leq +5.0$ mOhms: -----Stable
 - b. $+5.1$ to $+10.0$ mOhms:-----Minor
 - c. $+10.1$ to $+15.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms: -----Unstable
 - f. $>+1000$ mOhms:-----Open Failure

MECHANICAL SHOCK (Specified Pulse):

- 1) Reference document: EIA-364-27, *Mechanical Shock Test Procedure for Electrical Connectors*
- 2) Test Condition C
- 3) Peak Value: 100 G
- 4) Duration: 6 Milliseconds
- 5) Wave Form: Half Sine
- 6) Velocity: 12.3 ft/s
- 7) Number of Shocks: 3 Shocks / Direction, 3 Axis (18 Total)

VIBRATION:

- 1) Reference document: EIA-364-28, *Vibration Test Procedure for Electrical Connectors*
- 2) Test Condition V, Letter B
- 3) Power Spectral Density: $0.04 \text{ G}^2 / \text{Hz}$
- 4) G 'RMS': 7.56
- 5) Frequency: 50 to 2000 Hz
- 6) Duration: 2.0 Hours per axis (3 axis total)

ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes

INSULATION RESISTANCE (IR):

To determine the resistance of insulation materials to leakage of current through or on the surface of these materials when a DC potential is applied.

- 1) PROCEDURE:
 - a. Reference document: MIL-PRF-39012, paragraph. 4.6.8 per MIL-STD-202-302.
 - b. Test Conditions:
 - i. Between Adjacent Contacts or Signal-to-Ground
 - ii. Electrification Time 2.0 minutes
 - iii. Test Voltage (500 VDC) corresponds to calibration settings for measuring resistances.
- 2) MEASUREMENTS:
- 3) When the specified test voltage is applied (VDC), the insulation resistance shall not be less than 1000 megohms.

DIELECTRIC WITHSTANDING VOLTAGE (DWV):

To determine if the sockets can operate at its rated voltage and withstand momentary over potentials due to switching, surges, and other similar phenomenon. Separate samples are used to evaluate the effect of environmental stresses so not to influence the readings from arcing that occurs during the measurement process.

- 1) PROCEDURE:
 - a. Reference document: At sea level per DSCC 10020.
 - b. Test Conditions:
 - i. Between Adjacent Contacts or Signal-to-Ground
 - ii. Barometric Test Condition 1(Sea Level) Test voltage applied for 60 seconds.
 - iii. Rate of Application 500 V/Sec
 - iv. Test Voltage (VAC) until breakdown occurs
- 2) MEASUREMENTS/CALCULATIONS
 - a. The breakdown voltage shall be measured and recorded.
 - b. The dielectric withstanding voltage shall be recorded as 75% of the minimum breakdown voltage.
 - c. The working voltage shall be recorded as one-third (1/3) of the dielectric withstanding voltage (one-fourth of the breakdown voltage).

RESULTS

Cable Pull force

- Min -----11.18 lbs
- Max -----15.81 lbs

Insulation Resistance minimums, IR

Pin to Ground

- Initial
 - Mated-----45000 Meg Ω ----- Passed
- Thermal Shock
 - Mated-----45000 Meg Ω ----- Passed

Dielectric Withstanding Voltage minimums, DWV

- Minimums
 - Test Voltage -----500 VAC

Pin to Ground

- Initial DWV -----Passed
- Thermal DWV -----Passed

Interface Gaging

IR/DWV Group

Initial

- Min -----0.084 mm
- Max -----0.096 mm

After Thermal Shock

- Min -----0.085 mm
- Max -----0.099 mm

Cable Pull Group

Initial

- Min -----0.085mm
- Max -----0.094 mm

After Retention

- Min -----0.090 mm
- Max -----0.096 mm

RESULTS Continued

LLCR IR/DWV (5 ground and 5 signal LLCR test points)

- Ground pin**
- **Initial** ----- 17.28 mOhms Max
 - **Thermal Shock**
 - **<= +5.0 mOhms**-----5 Points ----- Stable
 - **+5.1 to +10.0 mOhms** -----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure
- Signal pin**
- **Initial** ----- 44.14 mOhms Max
 - **Thermal Shock**
 - **<= +5.0 mOhms**-----5 Points ----- Stable
 - **+5.1 to +10.0 mOhms** -----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

LLCR Cable Pull (5 ground and 5 signal LLCR test points)

- Ground pin**
- **Initial** ----- 15.48 mOhms Max
 - **After 5lb Retention**
 - **<= +5.0 mOhms**-----5 Points ----- Stable
 - **+5.1 to +10.0 mOhms** -----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure
- Signal pin**
- **Initial** ----- 44.35 mOhms Max
 - **After 5lb Retention**
 - **<= +5.0 mOhms**-----5 Points ----- Stable
 - **+5.1 to +10.0 mOhms** -----0 Points ----- Minor
 - **+10.1 to +15.0 mOhms** -----0 Points ----- Acceptable
 - **+15.1 to +50.0 mOhms** -----0 Points ----- Marginal
 - **+50.1 to +1000 mOhms**-----0 Points ----- Unstable
 - **>+1000 mOhms**-----0 Points ----- Open Failure

RESULTS Continued

LLCR Mechanical Shock & Random Vibration (5 ground and 5 signal LLCR test points)

Ground pin

- **Initial** ----- 51.23 mOhms Max
- **After Shock &Vibration**
 - <= +5.0 mOhms-----5 Points ----- Stable
 - +5.1 to +10.0 mOhms -----0 Points ----- Minor
 - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
 - +50.1 to +1000 mOhms-----0 Points ----- Unstable
 - >+1000 mOhms-----0 Points ----- Open Failure

Signal pin

- **Initial** ----- 119.53 mOhms Max
- **After Shock &Vibration**
 - <= +5.0 mOhms-----5 Points ----- Stable
 - +5.1 to +10.0 mOhms -----0 Points ----- Minor
 - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
 - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
 - +50.1 to +1000 mOhms-----0 Points ----- Unstable
 - >+1000 mOhms-----0 Points ----- Open Failure

DATA SUMMARIES

INSULATION RESISTANCE (IR):

Pin to Ground	
Mated	
Minimum	RF047-A-M0RJ
Initial	45000
Thermal Shock	45000

DIELECTRIC WITHSTANDING VOLTAGE (DWV):

IR/DWV Group

Voltage Rating Summary	
Minimum	RF047-A-M0RJ
Test Voltage	500
Pin to Ground	
Initial Test Voltage	Pass
After Thermal Shock Test Voltage	Pass

Cable Pull Force:

Force (lbs)	
Minimum	11.18
Maximum	15.81
Average	13.04

DATA SUMMARIES Continued

LLCR IR/DWV:

- 1) A total of 5 signal and 5 ground points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: -----Stable
 - b. $+5.1$ to $+10.0$ mOhms:-----Minor
 - c. $+10.1$ to $+15.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms: -----Unstable
 - f. $>+1000$ mOhms:-----Open Failure

LLCR Measurement Summaries by Pin Type				
Date	8/22/2024	9/3/2024		
Room Temp (Deg C)	22	22		
Rel Humidity (%)	50	50		
Technician	Keney Chen	Keney Chen		
mOhm values	Actual	Delta		
	Initial	Thermal Shock		
Pin Type: Signal 1				
Average	42.908	1.388		
St. Dev.	1.3780	0.8634		
Min	40.55	0.09		
Max	44.14	2.24		
Summary Count	5	5		
Total Count	5	5		
Pin Type: GND 1				
Average	15.892	2.964		
St. Dev.	1.0368	1.0572		
Min	14.81	1.87		
Max	17.28	4.55		
Summary Count	5	5		
Total Count	5	5		

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	≤ 5	$>5 \ \& \ \leq 10$	$>10 \ \& \ \leq 15$	$>15 \ \& \ \leq 50$	$>50 \ \& \ \leq 1000$	>1000
After Thermal Shock	10	0	0	0	0	0

DATA SUMMARIES Continued

LLCR Cable Pull:

- 1) A total of 5 signal and 5 ground points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: -----Stable
 - b. $+5.1$ to $+10.0$ mOhms: -----Minor
 - c. $+10.1$ to $+15.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms: -----Unstable
 - f. $>+1000$ mOhms: -----Open Failure

LLCR Measurement Summaries by Pin Type				
Date	8/26/2024	8/26/2024		
Room Temp (Deg C)	20	20		
Rel Humidity (%)	50	50		
Technician	Keney Chen	Keney Chen		
mOhm values	Actual	Delta		
	Initial	after 5lb Retention		
Pin Type: Signal 1				
Average	42.97	0.36		
St. Dev.	0.86	0.30		
Min	42.14	0.04		
Max	44.35	0.76		
Summary Count	5	5		
Total Count	5	5		
Pin Type: GND 1				
Average	13.80	0.61		
St. Dev.	1.12	0.38		
Min	12.58	0.31		
Max	15.48	1.18		
Summary Count	5	5		
Total Count	5	5		

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	≤ 5	$>5 \ \& \ \leq 10$	$>10 \ \& \ \leq 15$	$>15 \ \& \ \leq 50$	$>50 \ \& \ \leq 1000$	>1000
After 5lb Retention	10	0	0	0	0	0

DATA SUMMARIES Continued

LLCR Mechanical Shock & Random Vibration:

- 1) A total of 5 signal and 5 ground points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
 - a. $\leq +5.0$ mOhms: -----Stable
 - b. $+5.1$ to $+10.0$ mOhms: -----Minor
 - c. $+10.1$ to $+15.0$ mOhms: -----Acceptable
 - d. $+15.1$ to $+50.0$ mOhms: -----Marginal
 - e. $+50.1$ to $+1000$ mOhms: -----Unstable
 - f. $>+1000$ mOhms: -----Open Failure

LLCR Measurement Summaries by Pin Type				
Date	12/5/2024	12/31/2024		
Room Temp (Deg C)	22	22		
Rel Humidity (%)	33	39		
Technician	Richard Ison	Richard Ison		
mOhm values	Actual Initial	Delta Shock-Vib		
Pin Type: Signal 1				
Average	118.56	1.63		
St. Dev.	0.99	1.05		
Min	117.18	0.49		
Max	119.53	3.33		
Summary Count	5	5		
Total Count	5	5		
Pin Type: GND 1				
Average	48.58	1.52		
St. Dev.	2.02	0.69		
Min	46.32	0.67		
Max	51.23	2.35		
Summary Count	5	5		
Total Count	5	5		

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	≤ 5	>5 & ≤ 10	>10 & ≤ 15	>15 & ≤ 50	>50 & ≤ 1000	>1000
Shock-Vib	10	0	0	0	0	0

EQUIPMENT AND CALIBRATION SCHEDULES**Equipment #:** HZ-TCT-01**Description:** Normal force analyzer**Manufacturer:** Mecmesin Multitester**Model:** Mecmesin Multitester 2.5-i**Serial #:** 08-1049-04**Accuracy:** Last Cal: 3/4/2024, Next Cal: 3/3/2025**Equipment #:** HZ-TSC-01**Description:** Vertical Thermal Shock Chamber**Manufacturer:** Cincinnatti Sub Zero**Model:** VTS-3-6-6-SC/AC**Serial #:** 10-VT14994**Accuracy:** See Manual

... Last Cal: 04/16/2024, Next Cal: 04/15/2025

Equipment #: DG-HPT-01**Description:** Hipot Safety Tester**Manufacturer:** Vitrek**Model:** V73**Serial #:** 025866**Accuracy:**

... Last Cal: 04/16/2024, Next Cal: 04/15/2025

Equipment #: HZ-MO-05**Description:** Micro-ohmmeter**Manufacturer:** Keithley**Model:** 3706**Serial #:** 1285188**Accuracy:** Last Cal: 12/17/2024, Next Cal: 12/16/2025**Equipment #:** ED-03**Description:** Event Detector**Manufacturer:** Analysis Tech**Model:** 32EHD**Serial #:** 1100604**Accuracy:** See Manual

... Last Cal: 06/04/2024, Next Cal: 06/04/2025

Equipment #: SVC-01**Description:** Shock & Vibration Table**Manufacturer:** Data Physics**Model:** LE-DSA-10-20K**Serial #:** 10037**Accuracy:** See Manual

... Last Cal: 11/31/2024, Next Cal: 11/31/2025

EQUIPMENT AND CALIBRATION SCHEDULES Continued

Equipment #: ACLM-01
Description: Accelerometer
Manufacturer: PCB Piezotronics
Model: 352C03
Serial #: 115819
Accuracy: See Manual
... Last Cal: 07/09/2024, Next Cal: 07/09/2025