





Project Project: Design Qualification Test Report	Tracking Code: CR-1068202_Report_Rev_1
Requested by: Andy Chen	Date: 11/1/2024
Part #: ET60S-S03-5-08-S03-S-VP-S/ET60T-S03-5-08-S03-S-RP-S-H	
Part description: ET60S/ET60T	Tech: Peter Chen
Test Start: 3/25/2024	Test Completed: 9/20/2024



**DESIGN QUALIFICATION TEST REPORT**

**ET60S/ET60T**

**ET60S-S03-5-08-S03-S-VP-S/ET60T-S03-5-08-S03-S-RP-S-H**

Tracking Code: CR-1068202_Report_Rev_2	Part #: ET60S-S03-5-08-S03-S-VP-S/ET60T-S03-5-08-S03-S-RP-S-H
Part description: ET60S/ET60T	

### REVISION HISTORY

DATA	REV.NUM.	DESCRIPTION	ENG
9/26/2024	1	Initial test	PC

## CERTIFICATION

All instruments and measuring equipment were calibrated to National Institute for Standards and Technology (NIST) traceable standards according to ISO 10012-1 and ANSI/NCSL 2540-1, as applicable.

All contents contained herein are the property of Samtec. No portion of this report, in part or in full shall be reproduced without prior written approval of Samtec.

### SCOPE

To perform the following tests: Design Qualification test. Please see test plan.

### APPLICABLE DOCUMENTS

Standards: EIA Publication 364

### TEST SAMPLES AND PREPARATION

- 1) All materials were manufactured in accordance with the applicable product specification.
- 2) All test samples were identified and encoded to maintain traceability throughout the test sequences.
- 3) After soldering, the parts to be used for LLCR and DWV/IR testing were cleaned according to CO-SC-WI-3029.
- 4) Either an automated cleaning procedure or an ultrasonic cleaning procedure may be used.
- 5) The automated procedure is used with aqueous compatible soldering materials.
- 6) Parts not intended for testing LLCR and DWV/IR are visually inspected and cleaned if necessary.
- 7) Any additional preparation will be noted in the individual test sequences.
- 8) Solder Information: Lead Free
- 9) Samtec Test PCBs used: PCB-113933-TST/PCB-113934-TST.

## FLOWCHARTS

**Mating/Unmating/Durability****Group 1**

ET60S-S03-5-08-S03-S-VP-S  
ET60T-S03-5-08-S03-S-RP-S-H  
8 Assemblies

Step	Description
1.	Contact Gaps
2.	LLCR <sup>(2)</sup>
3.	Mating/Unmating Force <sup>(3)</sup>
4.	Cycles Quantity = 25 Cycles
5.	Mating/Unmating Force <sup>(3)</sup>
6.	Cycles Quantity = 25 Cycles
7.	Mating/Unmating Force <sup>(3)</sup>
8.	Cycles Quantity = 25 Cycles
9.	Mating/Unmating Force <sup>(3)</sup>
10.	Cycles Quantity = 25 Cycles
11.	Mating/Unmating Force <sup>(3)</sup>
12.	Contact Gaps
13.	LLCR <sup>(2)</sup> Max Delta = 15 mOhm
14.	Thermal Shock <sup>(4)</sup>
15.	LLCR <sup>(2)</sup> Max Delta = 15 mOhm
16.	Humidity <sup>(1)</sup>
17.	LLCR <sup>(2)</sup> Max Delta = 15 mOhm
18.	Mating/Unmating Force <sup>(3)</sup>

**Group 2**

ET60S-S01-5-01-S01-S-VP-S  
ET60T-S01-5-01-S01-S-RP-S-H  
8 Assemblies

Step	Description
1.	Contact Gaps
2.	Mating/Unmating Force <sup>(3)</sup>
3.	Cycles Quantity = 25 Cycles
4.	Mating/Unmating Force <sup>(3)</sup>
5.	Cycles Quantity = 25 Cycles
6.	Mating/Unmating Force <sup>(3)</sup>
7.	Cycles Quantity = 25 Cycles
8.	Mating/Unmating Force <sup>(3)</sup>
9.	Cycles Quantity = 25 Cycles
10.	Mating/Unmating Force <sup>(3)</sup>

**Group 3**

ET60S-S02-5-05-S02-S-VP-S  
ET60T-S02-5-05-S02-S-RP-S-H  
8 Assemblies

Step	Description
1.	Contact Gaps
2.	Mating/Unmating Force <sup>(3)</sup>
3.	Cycles Quantity = 25 Cycles
4.	Mating/Unmating Force <sup>(3)</sup>
5.	Cycles Quantity = 25 Cycles
6.	Mating/Unmating Force <sup>(3)</sup>
7.	Cycles Quantity = 25 Cycles
8.	Mating/Unmating Force <sup>(3)</sup>
9.	Cycles Quantity = 25 Cycles
10.	Mating/Unmating Force <sup>(3)</sup>

(1) Humidity = EIA-364-31

Test Condition = B (240 Hours)

Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)

Test Exceptions: ambient pre-condition and delete steps 7a and 7b

(2) LLCR = EIA-364-23

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

(3) Mating/Unmating Force = EIA-364-13

(4) Thermal Shock = EIA-364-32

Exposure Time at Temperature Extremes = 1/2 Hour

Method A, Test Condition = I (-55°C to +85°C)

Test Duration = A-3 (100 Cycles)

## FLOWCHARTS Continued

### IR/DWV

#### Split power module single blade

<u>Group 1</u>		<u>Group 2</u>		<u>Group 3</u>		<u>Group 4</u>	
ET60S-S03-5-08-S03-S-VP-S		ET60S-S03-5-08-S03-S-VP-S		ET60T-S03-5-08-S03-S-RP-S-H		ET60S-S03-5-08-S03-S-VP-S	
ET60T-S03-5-08-S03-S-RP-S-H						ET60T-S03-5-08-S03-S-RP-S-H	
2 Assemblies		2 Assemblies		2 Assemblies		2 Assemblies	
Left Blade To Right Blade		Left Blade To Right Blade		Left Blade To Right Blade		Left Blade To Right Blade	
Step	Description	Step	Description	Step	Description	Step	Description
1.	DWV Breakdown (2)	1.	DWV Breakdown (2)	1.	DWV Breakdown (2)	1.	IR (4)
						2.	DWV at Test Voltage (1)
						3.	Thermal Shock (5)
						4.	IR (4)
						5.	DWV at Test Voltage (1)
						6.	Humidity (3)
						7.	IR (4)
						8.	DWV at Test Voltage (1)

- 
- (1) DWV at Test Voltage = EIA-364-20  
 Test Condition = 1 (Sea Level)  
 DWV test voltage is equal to 75% of the lowest breakdown voltage  
 Test voltage applied for 60 seconds
  - (2) DWV Breakdown = EIA-364-20  
 Test Condition = 1 (Sea Level)  
 DWV test voltage is equal to 75% of the lowest breakdown voltage  
 Test voltage applied for 60 seconds
  - (3) Humidity = EIA-364-31  
 Test Condition = B (240 Hours)  
 Test Method = III (+25°C to +65°C @ 90% RH to 98% RH)  
 Test Exceptions: ambient pre-condition and delete steps 7a and 7b
  - (4) IR = EIA-364-21  
 Test Condition = 500 Vdc, 2 Minutes Max
  - (5) Thermal Shock = EIA-364-32  
 Exposure Time at Temperature Extremes = 1/2 Hour  
 Method A, Test Condition = I (-55°C to +85°C)  
 Test Duration = A-3 (100 Cycles)

## FLOWCHARTS Continued

### Current Carrying Capacity

<p><u>Group 1</u> ET60S-S03-5-08-S03-S-VP-S ET60T-S03-5-08-S03-S-RP-S-H 1 Pins Powered Power</p>	<p><u>Group 2</u> ET60S-S03-5-08-S03-S-VP-S ET60T-S03-5-08-S03-S-RP-S-H 2 Pins Powered Power</p>	<p><u>Group 3</u> ET60S-S03-5-08-S03-S-VP-S ET60T-S03-5-08-S03-S-RP-S-H 3 Pins Powered Power</p>	<p><u>Group 4</u> ET60S-S03-5-08-S03-S-VP-S ET60T-S03-5-08-S03-S-RP-S-H 4 Pins Powered Power</p>																
<table style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">Step</th> <th style="text-align: left;">Description</th> </tr> </thead> <tbody> <tr> <td>1.</td> <td>CCC <sup>(1)</sup> Rows = 1 Number of Positions = 1</td> </tr> </tbody> </table>	Step	Description	1.	CCC <sup>(1)</sup> Rows = 1 Number of Positions = 1	<table style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">Step</th> <th style="text-align: left;">Description</th> </tr> </thead> <tbody> <tr> <td>1.</td> <td>CCC <sup>(1)</sup> Rows = 1 Number of Positions = 2</td> </tr> </tbody> </table>	Step	Description	1.	CCC <sup>(1)</sup> Rows = 1 Number of Positions = 2	<table style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">Step</th> <th style="text-align: left;">Description</th> </tr> </thead> <tbody> <tr> <td>1.</td> <td>CCC <sup>(1)</sup> Rows = 1 Number of Positions = 3</td> </tr> </tbody> </table>	Step	Description	1.	CCC <sup>(1)</sup> Rows = 1 Number of Positions = 3	<table style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">Step</th> <th style="text-align: left;">Description</th> </tr> </thead> <tbody> <tr> <td>1.</td> <td>CCC <sup>(1)</sup> Rows = 1 Number of Positions = 4</td> </tr> </tbody> </table>	Step	Description	1.	CCC <sup>(1)</sup> Rows = 1 Number of Positions = 4
Step	Description																		
1.	CCC <sup>(1)</sup> Rows = 1 Number of Positions = 1																		
Step	Description																		
1.	CCC <sup>(1)</sup> Rows = 1 Number of Positions = 2																		
Step	Description																		
1.	CCC <sup>(1)</sup> Rows = 1 Number of Positions = 3																		
Step	Description																		
1.	CCC <sup>(1)</sup> Rows = 1 Number of Positions = 4																		
<p style="text-align: center;"><u>Group 5</u> ET60S-S03-5-08-S03-S-VP-S ET60T-S03-5-08-S03-S-RP-S-H 12 Pins Powered Power</p> <table style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">Step</th> <th style="text-align: left;">Description</th> </tr> </thead> <tbody> <tr> <td>1.</td> <td>CCC <sup>(1)</sup> Rows = 1 Number of Positions = 12</td> </tr> </tbody> </table>				Step	Description	1.	CCC <sup>(1)</sup> Rows = 1 Number of Positions = 12												
Step	Description																		
1.	CCC <sup>(1)</sup> Rows = 1 Number of Positions = 12																		

(1) CCC = EIA-364-70

Method 2, Temperature Rise Versus Current Curve

(TIN PLATING) - Tabulate calculated current at RT, 65°C, 75°C and 95°C after derating 20% and based on 105°C

(GOLD PLATING) - Tabulate calculated current at RT, 85°C, 95°C and 115°C after derating 20% and based on 125°C

**FLOWCHARTS Continued****Mechanical Shock/Random Vibration/LLCR**Group 1

ET60S-S03-5-08-S03-S-VP-S

ET60T-S03-5-08-S03-S-RP-S-H

8 Assemblies

**Step Description**

1. LLCR <sup>(1)</sup>
2. Mechanical Shock <sup>(2)</sup>
3. Random Vibration <sup>(3)</sup>
4. LLCR <sup>(1)</sup>  
Max Delta = 15 mOhm

**(1) LLCR = EIA-364-23**

Open Circuit Voltage = 20 mV Max

Test Current = 100 mA Max

**(2) Mechanical Shock = EIA-364-27**

Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)

Number of Shocks = 3 Per Direction, Per Axis, 18 Total

**(3) Random Vibration = EIA-364-28**

Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

**Mechanical Shock/Random Vibration/Event Detection**Group 1

ET60S-S03-5-08-S03-S-VP-S

ET60T-S03-5-08-S03-S-RP-S-H

60 Points

**Step Description**

1. Nanosecond Event Detection  
(Mechanical Shock) <sup>(1)</sup>
2. Nanosecond Event Detection  
(Random Vibration) <sup>(2)</sup>

**(1) Nanosecond Event Detection (Mechanical Shock)**

Use EIA-364-87 for Nanosecond Event Detection:

Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-27 for Mechanical Shock:

Test Condition = C (100 G Peak, 6 milliseconds, Half Sine)

Number of Shocks = 3 Per Direction, Per Axis, 18 Total

**(2) Nanosecond Event Detection (Random Vibration)**

Use EIA-364-87 for Nanosecond Event Detection:

Test Condition = F (50 nanoseconds at 10 ohms)

Use EIA-364-28 for Random Vibration:

Condition = VB (7.56 gRMS Average, 2 Hours/Axis)

## ATTRIBUTE DEFINITIONS

The following is a brief, simplified description of attributes.

### THERMAL SHOCK:

- 1) EIA-364-32, *Thermal Shock (Temperature Cycling) Test Procedure for Electrical Connectors*.
- 2) Test Condition I: -55°C to +85°C
- 3) Test Time: ½ hour dwell at each temperature extreme
- 4) Number of Cycles: 100
- 5) All test samples are pre-conditioned at ambient.
- 6) All test samples are exposed to environmental stressing in the mated condition.

### HUMIDITY:

- 1) Reference document: EIA-364-31, *Humidity Test Procedure for Electrical Connectors*.
- 2) Test Condition B, 240 Hours.
- 3) Method III, +25° C to + 65° C, 90% to 98% Relative Humidity excluding sub-cycles 7a and 7b.
- 4) All samples are pre-conditioned at ambient.
- 5) All test samples are exposed to environmental stressing in the mated condition.

### MECHANICAL SHOCK (Specified Pulse):

- 1) Reference document: EIA-364-27, *Mechanical Shock Test Procedure for Electrical Connectors*
- 2) Test Condition G
- 3) Peak Value: 100 G
- 4) Duration: 6 Milliseconds
- 5) Wave Form: Sawtooth
- 6) Velocity: 12.3 ft/s
- 7) Number of Shocks: 3 Shocks / Direction, 3 Axis (18 Total)

### VIBRATION:

- 1) Reference document: EIA-364-28, *Vibration Test Procedure for Electrical Connectors*
- 2) Test Condition V, Letter B
- 3) Power Spectral Density: 0.10 G<sup>2</sup> / Hz
- 4) G 'RMS': 7.56
- 5) Frequency: 50 to 2000 Hz
- 6) Duration: 2.0 Hours per axis (3 axis total)

### NANOSECOND-EVENT DETECTION:

- 1) Reference document: EIA-364-87, *Nanosecond-Event Detection for Electrical Connectors*
- 2) Prior to test, the samples were characterized to assure the low nanosecond event being monitored will trigger the detector.
- 3) After characterization it was determined the test samples could be monitored for 50 nanosecond events

### MATING/UNMATING:

- 1) Reference document: EIA-364-13, *Mating and Unmating Forces Test Procedure for Electrical Connectors*.
- 2) The full insertion position was to within 0.003" to 0.004" of the plug bottoming out in the receptacle to prevent damage to the system under test.
- 3) One of the mating parts is secured to a floating X-Y table to prevent damage during cycling.

**ATTRIBUTE DEFINITIONS Continued**

The following is a brief, simplified description of attributes

**TEMPERATURE RISE (Current Carrying Capacity, CCC):**

- 1) EIA-364-70, *Temperature Rise versus Current Test Procedure for Electrical Connectors and Sockets*.
- 2) When current passes through a contact, the temperature of the contact increases as a result of  $I^2R$  (resistive) heating.
- 3) The number of contacts being investigated plays a significant part in power dissipation and therefore temperature rise.
- 4) The size of the temperature probe can affect the measured temperature.
- 5) Copper traces on PC boards will contribute to temperature rise:
  - a. Self-heating (resistive)
  - b. Reduction in heat sink capacity affecting the heated contacts
- 6) A de-rating curve, usually 20%, is calculated.
- 7) Calculated de-rated currents at four temperature points are reported:
  - a. Ambient
  - b. 65° C
  - c. 75° C
  - d. 95° C
- 8) Typically, neighboring contacts (in close proximity to maximize heat buildup) are energized.
- 9) The thermocouple (or temperature measuring probe) will be positioned at a location to sense the maximum temperature in the vicinity of the heat generation area.
- 10) A computer program, *TR 803.exe*, ensures accurate stability for data acquisition.
- 11) Hook-up wire cross section is larger than the cross section of any connector leads/PC board traces, jumpers, etc.
- 12) Hook-up wire length is longer than the minimum specified in the referencing standard.

**LLCR:**

- 1) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 2) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 3) The following guidelines are used to categorize the changes in LLCR as a result from stressing
  - a.  $\leq +5.0$  mOhms: -----Stable
  - b.  $+5.1$  to  $+10.0$  mOhms:-----Minor
  - c.  $+10.1$  to  $+15.0$  mOhms: -----Acceptable
  - d.  $+15.1$  to  $+50.0$  mOhms: -----Marginal
  - e.  $+50.1$  to  $+1000$  mOhms: -----Unstable
  - f.  $>+1000$  mOhms:-----Open Failure
- 4) The following guidelines are used to categorize the changes in LLCR for power pin only
  - a.  $\leq +1.0$  mOhms: -----Stable
  - b.  $+1.1$  to  $+2.0$  mOhms: -----Minor
  - c.  $+2.1$  to  $+5.0$  mOhms: -----Acceptable
  - d.  $+5.1$  to  $+15.0$  mOhms:-----Marginal
  - e.  $+15.1$  to  $+1000$  mOhms -----Unstable
  - f.  $>+1000$  mOhms:-----Open Failure

## ATTRIBUTE DEFINITIONS Continued

The following is a brief, simplified description of attributes

### INSULATION RESISTANCE (IR):

To determine the resistance of insulation materials to leakage of current through or on the surface of these materials when a DC potential is applied.

- 1) PROCEDURE:
  - a. Reference document: EIA-364-21, *Insulation Resistance Test Procedure for Electrical Connectors*.
  - b. Test Conditions:
    - i. Between Adjacent Contacts or Signal-to-Ground
    - ii. Electrification Time 2.0 minutes
    - iii. Test Voltage (500 VDC) corresponds to calibration settings for measuring resistances.
- 2) MEASUREMENTS:
- 3) When the specified test voltage is applied (VDC), the insulation resistance shall not be less than 5000 megohms.

### DIELECTRIC WITHSTANDING VOLTAGE (DWV):

To determine if the sockets can operate at its rated voltage and withstand momentary over potentials due to switching, surges, and other similar phenomenon. Separate samples are used to evaluate the effect of environmental stresses so not to influence the readings from arcing that occurs during the measurement process.

- 1) PROCEDURE:
  - a. Reference document: EIA-364-20, *Withstanding Voltage Test Procedure for Electrical Connectors*.
  - b. Test Conditions:
    - i. Between Adjacent Contacts or Signal-to-Ground
    - ii. Barometric Test Condition 1
    - iii. Rate of Application 500 V/Sec
    - iv. Test Voltage (VAC) until breakdown occurs
- 2) MEASUREMENTS/CALCULATIONS
  - a. The breakdown voltage shall be measured and recorded.
  - b. The dielectric withstanding voltage shall be recorded as 75% of the minimum breakdown voltage.
  - c. The working voltage shall be recorded as one-third (1/3) of the dielectric withstanding voltage (one-fourth of the breakdown voltage).

## RESULTS

### Temperature Rise, CCC at a 20% de-rating

- CCC for a 30°C Temperature Rise-----69.7 A per contact with 1 contact (1 x 1) powered
- CCC for a 30°C Temperature Rise-----54.6 A per contact with 2 contacts (1 x 2) powered
- CCC for a 30°C Temperature Rise-----50.2 A per contact with 3 contacts (1 x 3) powered
- CCC for a 30°C Temperature Rise-----46.1 A per contact with 4 contacts (1 x 4) powered
- CCC for a 30°C Temperature Rise-----35.8 A per contact with All contacts (1x12) powered

### Mating – Unmating Forces

#### Mating/Unmating Durability Group

- **Initial**
  - **Mating**
    - **Min** ----- 9.68 lbs
    - **Max** ----- 11.65 lbs
  - **Unmating**
    - **Min** ----- 7.01 lbs
    - **Max** ----- 7.75 lbs
- **After 25 Cycles**
  - **Mating**
    - **Min** ----- 8.44 lbs
    - **Max** ----- 9.07 lbs
  - **Unmating**
    - **Min** ----- 6.76 lbs
    - **Max** ----- 7.86 lbs
- **After 50 Cycles**
  - **Mating**
    - **Min** ----- 8.09 lbs
    - **Max** ----- 8.72 lbs
  - **Unmating**
    - **Min** ----- 6.49 lbs
    - **Max** ----- 7.63 lbs
- **After 75 Cycles**
  - **Mating**
    - **Min** ----- 7.85 lbs
    - **Max** ----- 8.70 lbs
  - **Unmating**
    - **Min** ----- 6.55 lbs
    - **Max** ----- 7.57 lbs
- **After 100 Cycles**
  - **Mating**
    - **Min** ----- 7.86 lbs
    - **Max** ----- 8.70 lbs
  - **Unmating**
    - **Min** ----- 6.64 lbs
    - **Max** ----- 7.72 lbs
- **After Humidity**
  - **Mating**
    - **Min** ----- 5.03 lbs
    - **Max** ----- 5.45 lbs
  - **Unmating**
    - **Min** ----- 4.17 lbs
    - **Max** ----- 4.57 lbs

### RESULTS Continued

**Mating/Unmating Basic (ET60S-S01-5-01-S01-S-VP-S/ ET60T-S01-5-01-S01-S-RP-S-H)**

- **Initial**
  - **Mating**
    - **Min** ----- 3.76 lbs
    - **Max** ----- 4.49 lbs
  - **Unmating**
    - **Min** ----- 2.21 lbs
    - **Max** ----- 2.68 lbs
- **After 25 Cycles**
  - **Mating**
    - **Min** ----- 3.03 lbs
    - **Max** ----- 3.23 lbs
  - **Unmating**
    - **Min** ----- 2.09 lbs
    - **Max** ----- 2.25 lbs
- **After 50 Cycles**
  - **Mating**
    - **Min** ----- 2.84 lbs
    - **Max** ----- 3.04 lbs
  - **Unmating**
    - **Min** ----- 2.06 lbs
    - **Max** ----- 2.22 lbs
- **After 75 Cycles**
  - **Mating**
    - **Min** ----- 2.72 lbs
    - **Max** ----- 2.94 lbs
  - **Unmating**
    - **Min** ----- 2.04 lbs
    - **Max** ----- 2.28 lbs
- **After 100 Cycles**
  - **Mating**
    - **Min** ----- 2.70 lbs
    - **Max** ----- 2.90 lbs
  - **Unmating**
    - **Min** ----- 2.11 lbs
    - **Max** ----- 2.45 lbs

### RESULTS Continued

**Mating/Unmating Basic (ET60S-S02-5-05-S02-S-VP-S/ ET60T-S02-5-05-S02-S-RP-S-H)**

- **Initial**
  - **Mating**
    - **Min** ----- 7.55 lbs
    - **Max** ----- 8.92 lbs
  - **Unmating**
    - **Min** ----- 5.01 lbs
    - **Max** ----- 5.91 lbs
- **After 25 Cycles**
  - **Mating**
    - **Min** ----- 6.15 lbs
    - **Max** ----- 7.00 lbs
  - **Unmating**
    - **Min** ----- 4.87 lbs
    - **Max** ----- 5.66 lbs
- **After 50 Cycles**
  - **Mating**
    - **Min** ----- 5.88 lbs
    - **Max** ----- 6.64 lbs
  - **Unmating**
    - **Min** ----- 4.98 lbs
    - **Max** ----- 5.71 lbs
- **After 75 Cycles**
  - **Mating**
    - **Min** ----- 5.64 lbs
    - **Max** ----- 6.31 lbs
  - **Unmating**
    - **Min** ----- 4.98 lbs
    - **Max** ----- 5.67 lbs
- **After 100 Cycles**
  - **Mating**
    - **Min** ----- 5.59 lbs
    - **Max** ----- 6.26 lbs
  - **Unmating**
    - **Min** ----- 4.98 lbs
    - **Max** ----- 5.74 lbs

**RESULTS Continued**

**Insulation Resistance minimums, IR**

**Power to Power**

- **Initial**
  - Mated -----45000 Meg  $\Omega$  ----- Passed
  - Unmated -----45000 Meg  $\Omega$  ----- Passed
- **Thermal Shock**
  - Mated -----45000 Meg  $\Omega$  ----- Passed
  - Unmated -----45000 Meg  $\Omega$  ----- Passed
- **Humidity**
  - Mated -----45000 Meg  $\Omega$  ----- Passed
  - Unmated -----45000 Meg  $\Omega$  ----- Passed

**Dielectric Withstanding Voltage minimums, DWV**

- **Minimums**
  - Breakdown Voltage ----- 1945 VAC
  - Test Voltage ----- 1460 VAC
  - Working Voltage -----485 VAC

**Power to Power**

- **Initial DWV -----Passed**
- **Thermal DWV-----Passed**
- **Humidity DWV-----Passed**

**RESULTS Continued**

**LLCR Durability (192 LLCR test points)**

**Signal pin:**

- Initial ----- 26.07 mOhms Max

**Power pin:**

- Initial -----0.26 mOhms Max
- Durability, 100 Cycles
  - <= +5.0 mOhms-----192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +1000 mOhms-----0 Points ----- Unstable
  - >+1000 mOhms-----0 Points ----- Open Failure
- Thermal
  - <= +5.0 mOhms-----190 Points ----- Stable
  - +5.1 to +10.0 mOhms -----2 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +1000 mOhms-----0 Points ----- Unstable
  - >+1000 mOhms-----0 Points ----- Open Failure
- Humidity
  - <= +5.0 mOhms-----192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +1000 mOhms-----0 Points ----- Unstable
  - >+1000 mOhms-----0 Points ----- Open Failure

**LLCR Shock & Vibration (192 LLCR test points)**

**Signal pin:**

- Initial ----- 25.79 mOhms Max

**Power pin:**

- Initial -----0.22 mOhms Max
- Shock &Vibration
  - <= +5.0 mOhms-----192 Points ----- Stable
  - +5.1 to +10.0 mOhms -----0 Points ----- Minor
  - +10.1 to +15.0 mOhms -----0 Points ----- Acceptable
  - +15.1 to +50.0 mOhms -----0 Points ----- Marginal
  - +50.1 to +1000 mOhms-----0 Points ----- Unstable
  - >+1000 mOhms-----0 Points ----- Open Failure


**Mechanical Shock & Random Vibration:**

- Shock
  - No Damage----- Pass
  - 50 Nanoseconds ----- Pass
- Vibration
  - No Damage----- Pass
  - 50 Nanoseconds ----- Pass

### DATA SUMMARIES


#### TEMPERATURE RISE (Current Carrying Capacity, CCC):

- 1) High quality thermocouples whose temperature slopes track one another were used for temperature monitoring.
- 2) The thermocouples were placed at a location to sense the maximum temperature generated during testing.
- 3) Temperature readings recorded are those for which three successive readings, 15 minutes apart, differ less than 1° C (computer controlled data acquisition).
- 4) Adjacent contacts were powered:
  - a. Linear configuration with 1 adjacent conductors/contacts powered





### DATA SUMMARIES Continued

CR-1142801  
1 (1x1) Power Pins Powered in Series  
Part Numbers: ET60S-S03-5-08-S03-S-VP-S/ET60T-S03-5-08-S03-RP-S-H





**DATA SUMMARIES Continued**

b. Linear configuration with 2 adjacent conductors/contacts powered





### DATA SUMMARIES Continued

c. Linear configuration with 3 adjacent conductors/contacts powered





### DATA SUMMARIES Continued

d. Linear configuration with 4 adjacent conductors/contacts powered



### DATA SUMMARIES Continued

e. Linear configuration with All adjacent conductors/contacts powered



### DATA SUMMARIES Continued

**MATING/UNMATING:**

**Mating/Unmating Durability Group**

	Initial				25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)
Minimum	43.06	9.68	31.18	7.01	37.54	8.44	30.07	6.76
Maximum	51.82	11.65	34.47	7.75	40.34	9.07	34.96	7.86
<b>Average</b>	48.60	<b>10.93</b>	32.63	<b>7.34</b>	38.96	<b>8.76</b>	31.50	<b>7.08</b>
St Dev	2.63	0.59	1.17	0.26	1.01	0.23	1.62	0.36
Count	8	8	8	8	8	8	8	8
	50 Cycles				75 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)
Minimum	35.98	8.09	28.87	6.49	34.92	7.85	29.13	6.55
Maximum	38.79	8.72	33.94	7.63	38.70	8.70	33.67	7.57
<b>Average</b>	37.20	<b>8.36</b>	31.26	<b>7.03</b>	36.33	<b>8.17</b>	31.77	<b>7.14</b>
St Dev	1.12	0.25	1.52	0.34	1.34	0.30	1.38	0.31
Count	8	8	8	8	8	8	8	8
	100 Cycles				After Humidity			
	Mating		Unmating		Mating		Unmating	
	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)
Minimum	34.96	7.86	29.53	6.64	22.37	5.03	18.55	4.17
Maximum	38.70	8.70	34.34	7.72	24.24	5.45	20.33	4.57
<b>Average</b>	36.13	<b>8.12</b>	32.42	<b>7.29</b>	23.45	<b>5.27</b>	19.50	<b>4.38</b>
St Dev	1.19	0.27	1.38	0.31	0.57	0.13	0.62	0.14
Count	8	8	8	8	8	8	8	8

### DATA SUMMARIES Continued

#### Mating/Unmating Basic (ET60S-S01-5-01-S01-S-VP-S/ ET60T-S01-5-01-S01-S-RP-S-H)

	Initial				After 25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)
Minimum	16.72	3.76	9.83	2.21	13.48	3.03	9.30	2.09
Maximum	19.97	4.49	11.92	2.68	14.37	3.23	10.01	2.25
<b>Average</b>	17.97	<b>4.04</b>	10.75	<b>2.42</b>	13.94	<b>3.13</b>	9.59	<b>2.16</b>
St Dev	1.12	0.25	0.69	0.16	0.35	0.08	0.28	0.06
Count	8	8	8	8	8	8	8	8
	After 50 Cycles				After 75 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)
Minimum	12.63	2.84	9.16	2.06	12.10	2.72	9.07	2.04
Maximum	13.52	3.04	9.87	2.22	13.08	2.94	10.14	2.28
<b>Average</b>	13.13	<b>2.95</b>	9.51	<b>2.14</b>	12.67	<b>2.85</b>	9.59	<b>2.16</b>
St Dev	0.34	0.08	0.30	0.07	0.34	0.08	0.37	0.08
Count	8	8	8	8	8	8	8	8
	After 100 Cycles							
	Mating		Unmating					
	Newton's	Force (Lbs)	Newton's	Force (Lbs)				
Minimum	12.01	2.70	9.39	2.11				
Maximum	12.90	2.90	10.90	2.45				
<b>Average</b>	12.50	<b>2.81</b>	9.92	<b>2.23</b>				
St Dev	0.35	0.08	0.47	0.11				
Count	8	8	8	8				

### DATA SUMMARIES Continued

#### Mating/Unmating Basic (ET60S-S02-5-05-S02-S-VP-S/ ET60T-S02-5-05-S02-S-RP-S-H)

	Initial				After 25 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)
Minimum	33.58	7.55	22.28	5.01	27.36	6.15	21.66	4.87
Maximum	39.68	8.92	26.29	5.91	31.14	7.00	25.18	5.66
<b>Average</b>	36.85	<b>8.28</b>	24.63	<b>5.54</b>	29.62	<b>6.66</b>	23.51	<b>5.29</b>
St Dev	2.08	0.47	1.16	0.26	1.59	0.36	1.06	0.24
Count	8	8	8	8	8	8	8	8
	After 50 Cycles				After 75 Cycles			
	Mating		Unmating		Mating		Unmating	
	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)	Newton's	Force (Lbs)
Minimum	26.15	5.88	22.15	4.98	25.09	5.64	22.15	4.98
Maximum	29.53	6.64	25.40	5.71	28.07	6.31	25.22	5.67
<b>Average</b>	28.06	<b>6.31</b>	23.51	<b>5.29</b>	26.93	<b>6.06</b>	23.67	<b>5.32</b>
St Dev	1.30	0.29	1.03	0.23	1.19	0.27	0.93	0.21
Count	8	8	8	8	8	8	8	8
	After 100 Cycles							
	Mating		Unmating					
	Newton's	Force (Lbs)	Newton's	Force (Lbs)				
Minimum	24.86	5.59	22.15	4.98				
Maximum	27.84	6.26	25.53	5.74				
<b>Average</b>	26.55	<b>5.97</b>	23.45	<b>5.27</b>				
St Dev	1.01	0.23	1.06	0.24				
Count	8	8	8	8				

**DATA SUMMARIES Continued**

**INSULATION RESISTANCE (IR):**

	Power to Power		
	Mated	Unmated	Unmated
Minimum	<b>ET60S/ET60T</b>	<b>ET60S</b>	<b>ET60T</b>
<b>Initial</b>	45000	45000	45000
<b>Thermal</b>	45000	45000	45000
<b>Humidity</b>	45000	45000	45000

**DIELECTRIC WITHSTANDING VOLTAGE (DWV):**

Voltage Rating Summary	
Minimum	ET60S/ET60T
<b>Break Down Voltage</b>	1945
<b>Test Voltage</b>	1460
<b>Working Voltage</b>	485

Power to Power	
<b>Initial Test Voltage</b>	Passed
<b>After Thermal Test Voltage</b>	Passed
<b>After Humidity Test Voltage</b>	Passed

### DATA SUMMARIES Continued

**LLCR Durability:**

- 1) A total of 192 points were measured.
- 2) EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets*.
- 3) A computer program, *LLCR 221.exe*, ensures repeatability for data acquisition.
- 4) The following guidelines are used to categorize the changes in LLCR as a result from stressing.
  - a.  $\leq +5.0$  mOhms: -----Stable
  - b.  $+5.1$  to  $+10.0$  mOhms: -----Minor
  - c.  $+10.1$  to  $+15.0$  mOhms: -----Acceptable
  - d.  $+15.1$  to  $+50.0$  mOhms: -----Marginal
  - e.  $+50.1$  to  $+1000$  mOhms: -----Unstable
  - f.  $>+1000$  mOhms: -----Open Failure

LLCR Measurement Summaries by Pin Type				
Date	3/25/2024	3/27/2024	4/10/2024	5/10/2024
Room Temp (Deg C)	22	22	22	22
Rel Humidity (%)	52	52	52	52
Technician	Kason He	Kason He	Kason He	Kason He
<b>mOhm values</b>				
	Actual	<b>Delta</b>	<b>Delta</b>	<b>Delta</b>
	<b>Initial</b>	<b>100 Cycles</b>	<b>Therm Shck</b>	<b>Humidity</b>
<b>Pin Type: Signal 1</b>				
Average	20.31	0.96	1.42	1.1
St. Dev.	3.72	0.69	0.98	0.76
Min	13.61	0.02	0.11	0.01
Max	26.07	4.12	9.23	3.47
Summary Count	176	176	176	176
Total Count	176	176	176	176
<b>Pin Type: Power 1</b>				
Average	0.21	0.02	0.03	0.09
St. Dev.	0.03	0.02	0.02	0.08
Min	0.18	0	0	0.01
Max	0.26	0.06	0.07	0.3
Summary Count	16	16	16	16
Total Count	16	16	16	16

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	$\leq 5$	$>5 \ \& \ \leq 10$	$>10 \ \& \ \leq 15$	$>15 \ \& \ \leq 50$	$>50 \ \& \ \leq 1000$	$>1000$
<b>100 Cycles</b>	<b>192</b>	<b>0</b>	<b>0</b>	<b>0</b>	<b>0</b>	<b>0</b>
<b>Therm Shck</b>	<b>190</b>	<b>2</b>	<b>0</b>	<b>0</b>	<b>0</b>	<b>0</b>
<b>Humidity</b>	<b>192</b>	<b>0</b>	<b>0</b>	<b>0</b>	<b>0</b>	<b>0</b>

### DATA SUMMARIES Continued

#### LLCR Shock &Vibration:

- 1). A total of 192 points were measured.
- 2). EIA-364-23, *Low Level Contact Resistance Test Procedure for Electrical Connectors and Sockets.*
- 3). The following guidelines are used to categorize the changes in LLCR as a result from stressing.
  - a.  $\leq +5.0$  mOhms: -----Stable
  - b.  $+5.1$  to  $+10.0$  mOhms: -----Minor
  - c.  $+10.1$  to  $+15.0$  mOhms: -----Acceptable
  - d.  $+15.1$  to  $+50.0$  mOhms: -----Marginal
  - e.  $+50.1$  to  $+1000$  mOhms -----Unstable
  - f.  $>+1000$  mOhms: -----Open Failure

LLCR Measurement Summaries by Pin Type			
Date	6/21/2024	7/11/2024	
Room Temp (Deg C)	22	22	
Rel Humidity (%)	54	54	
Technician	Aaron McKim	Aaron McKim	
mOhm values	Actual	Delta	
	Initial	Shock-Vib	
<b>Pin Type: Signal 1</b>			
Average	19.79	0.68	
St. Dev.	3.81	0.6	
Min	12.97	0.01	
Max	25.79	3.84	
Summary Count	176	176	
Total Count	176	176	
<b>Pin Type: Power 1</b>			
Average	0.18	0.04	
St. Dev.	0.02	0.03	
Min	0.15	0.01	
Max	0.22	0.13	
Summary Count	16	16	
Total Count	16	16	

LLCR Delta Count by Category						
	Stable	Minor	Acceptable	Marginal	Unstable	Open
mOhms	$\leq 5$	$>5 \ \& \ \leq 10$	$>10 \ \& \ \leq 15$	$>15 \ \& \ \leq 50$	$>50 \ \& \ \leq 1000$	$>1000$
Shock-Vib	192	0	0	0	0	0

**DATA SUMMARIES Continued**

**Nanosecond Event Detection:**

<b>Shock and Vibration Event Detection Summary</b>	
Contacts tested	60
Test Condition	C, 100g's, 6ms, Half-Sine
Shock Events	0
Test Condition	V-B, 7.56 rms g
Vibration Events	0
<b>Total Events</b>	<b>0</b>

**EQUIPMENT AND CALIBRATION SCHEDULES****Equipment #:** HZ-TCT-01**Description:** Normal force analyzer**Manufacturer:** Mecmesin Multitester**Model:** Mecmesin Multitester 2.5-i**Serial #:** 08-1049-04**Accuracy:** Last Cal: 4/26/2024, Next Cal: 4/27/2025**Equipment #:** HZ-THC-01**Description:** Humidity transmitter**Manufacturer:** Thermtron**Model:** HMM30C**Serial #:** D0240037**Accuracy:** Last Cal: 3/1/2024, Next Cal: 2/28/2025**Equipment #:** HZ-HPM-01**Description:** NA9636H**Manufacturer:** Ainuo**Model:** 6031A**Serial #:** 089601091**Accuracy:** Last Cal: 3/8/2024, Next Cal: 3/7/2025**Equipment #:** MO-04**Description:** Multimeter /Data Acquisition System**Manufacturer:** Keithley**Model:** 2700**Serial #:** 0798688**Accuracy:** Last Cal: 4/20/2024, Next Cal: 4/20/2025**Equipment #:** PS-11**Description:** Power Supply**Manufacturer:** Hewlett Packard / Agilent**Model:** AT-6032A**Serial #:** 3440A10457**Accuracy:** Last Cal: no calibrate, Next Cal: no calibrate**Equipment #:** HZ-MO-05**Description:** Micro-ohmmeter**Manufacturer:** Keithley**Model:** 3706**Serial #:** 1285188**Accuracy:** Last Cal: 11/15/2023, Next Cal: 11/14/2024

**EQUIPMENT AND CALIBRATION SCHEDULES****Equipment #:** HZ-TSC-01**Description:** Vertical Thermal Shock Chamber**Manufacturer:** Cincinnatti Sub Zero**Model:** VTS-3-6-6-SC/AC**Serial #:** 10-VT14994**Accuracy:** See Manual

... Last Cal: 06/28/2024, Next Cal: 06/27/2025

**Equipment #:** SVC-01**Description:** Shock & Vibration Table**Manufacturer:** Data Physics**Model:** LE-DSA-10-20K**Serial #:** 10037**Accuracy:** See Manual

... Last Cal: 11/30/2023, Next Cal: 11/30/2024

**Equipment #:** ACLM-01**Description:** Accelerometer**Manufacturer:** PCB Piezotronics**Model:** 352C03**Serial #:** 115819**Accuracy:** See Manual

... Last Cal: 07/09/2024, Next Cal: 07/09/2025

**Equipment #:** ED-03**Description:** Event Detector**Manufacturer:** Analysis Tech**Model:** 32EHD**Serial #:** 1100604**Accuracy:** See Manual

... Last Cal: 06/04/2024, Next Cal: 06/04/2025