





High Speed Characterization Report

QMS-XXX-01-XX-D-RA



Mates with

QFS-XXX-01-XX-D-RA



Description:
Micro High-Speed Board-to-Board,
0.635mm Pitch, Right Angle to Right Angle

Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Table of Contents

Connector Overview	1
Connector System Speed Rating	1
Frequency Domain Data Summary	3
Table 1 - Single-Ended Connector System Performance	3
Table 2 - Differential Connector System Performance.....	3
Bandwidth Chart – Single-Ended & Differential Insertion Loss	4
Time Domain Data Summary	5
Table 3 - Single-Ended Impedance (Ω)	5
Table 4 - Differential Impedance (Ω).....	6
Table 5 - Single-Ended Crosstalk (%).....	7
Table 6 - Differential Crosstalk (%).....	7
Table 7 - Propagation Delay (Mated Connector)	7
Characterization Details	8
Differential and Single-Ended Data.....	8
Connector Signal to Ground Ratio	8
Frequency Domain Data	10
Time Domain Data	10
Appendix A – Frequency Domain Response Graphs	12
Single-Ended Application – Insertion Loss	12
Single-Ended Application – Return Loss	12
Single-Ended Application – NEXT Configurations	13
Single-Ended Application – FEXT Configurations	14
Differential Application – Insertion Loss	15
Differential Application – Return Loss.....	15
Differential Application – NEXT Configurations	16
Differential Application – FEXT Configurations	17
Appendix B – Time Domain Response Graphs	18
Single-Ended Application – Input Pulse	18
Single-Ended Application – Impedance	19
Single-Ended Application – Propagation Delay	20
Single-Ended Application – NEXT, Worst Case Configuration	21
Single-Ended Application – FEXT, Worst Case Configuration.....	22
Single-Ended Application – NEXT, Best Case Configuration	23
Single-Ended Application – FEXT, Best Case Configuration.....	24
Single-Ended Application – NEXT, Across Row Configuration	25
Single-Ended Application – FEXT, Across Row Configuration	25
Differential Application – Input Pulse	26
Differential Application – Impedance	27
Differential Application – Propagation Delay.....	28

Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Differential Application – NEXT, Worst Case Configuration.....	29
Differential Application – FEXT, Worst Case Configuration	30
Differential Application – NEXT, Best Case Configuration	31
Differential Application – FEXT, Best Case Configuration	32
Differential Application – NEXT, Across Row Case Configuration	33
Differential Application – FEXT, Across Row Case Configuration	33
Appendix C – Product and Test System Descriptions	34
Product Description	34
Test System Description.....	34
PCB-103658-TST-XX Test Fixtures.....	34
PCB-103658-TST-XX PCB Layout Panel	35
PCB Fixtures	35
Calibration Board.....	37
Appendix D – Test and Measurement Setup.....	39
N5230C Measurement Setup	39
Test Instruments	39
Test Cables & Adapters.....	39
Appendix E - Frequency and Time Domain Measurements	40
Frequency (S-Parameter) Domain Procedures	40
Time Domain Procedures	40
Impedance (TDR).....	40
Propagation Delay (TDT)	41
Near-End Crosstalk (TDT) & Far End Crosstalk (TDT)	41
Appendix F – Glossary of Terms	42

Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Connector Overview


Samtec's QMS/QFS Series Micro High-Speed, 0.635mm (0.0250") pitch interfaces are available with up to 104 contacts per row. QFS/QMS series connector tail options include: double row vertical, right angle and edge-mount styles. The data in this report is applicable only to QMS right angle connector mated to QFS right angle connector.

QMS-RA/QFS-RA possesses two terminal types, with each terminal type having different performance. The signal integrity performance of these two terminal types is documented in this report. The terminology used in this report to define which connector terminal is as follows:

*The short terminal of the connector is referred to as "Case 1"

*The long terminal of the connector is referred to as "Case 2"

This is illustrated in the following figure.



Connector System Speed Rating

QFS-RA/QMS-RA, Micro High Speed Board-to-Board, 0.635mm Pitch, Right Angle

<u>Case</u>	<u>Signaling</u>	<u>Speed Rating</u>
1 (Short Row)	Single-Ended:	14.5 GHz/ 29 Gbps
	Differential:	7 GHz/ 14 Gbps
2 (Long Row)	Single-Ended:	20 GHz/ 40 Gbps
	Differential:	5 GHz/ 10 Gbps

Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

The Speed Rating is based on the -3 dB insertion loss point of the connector system. The -3 dB point can be used to estimate usable system bandwidth in a typical, two-level signaling environment.

To calculate the Speed Rating, the measured -3 dB point is rounded-up to the nearest half-GHz level. The up rounding corrects for a portion of the test board's trace loss, since a short length of trace loss included in the loss data in this report. The resulting loss value is then doubled to determine the approximate maximum data rate in Gigabits per second (Gbps).

For example, a connector with a -3 dB point of 7.8 GHz would have a Speed Rating of 8 GHz/ 16 Gbps. A connector with a -3 dB point of 7.2 GHz would have a Speed Rating of 7.5 GHz/ 15 Gbps.

Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Frequency Domain Data Summary

Table 1 - Single-Ended Connector System Performance			
Case 1 = Short Row; Case 2 = Long Row			
Case	Test Parameter	Configuration	
1	Insertion Loss	GSG	3dB@ 14.5 GHz
	Return Loss	GSG	>10dB to 5.9 GHz
	Near-End Crosstalk	GAQG	<-20dB to 0.4 GHz
		GAGQG	<-20dB to 9.4 GHz
		Xrow, GAG to GQG	<-20dB to 20 GHz
	Far-End Crosstalk	GAQG	<-20dB to 7 GHz
		GAGQG	<-20dB to 13.8 GHz
Xrow, GAG to GQG		<-20dB to 20 GHz	
2	Insertion Loss	GSG	3dB@ 20 GHz
	Return Loss	GSG	>10dB to 4 GHz
	Near-End Crosstalk	GAQG	<-20dB to 0.3 GHz
		GAGQG	<-20dB to 20.0 GHz
	Far-End Crosstalk	GAQG	<-20dB to 4.5 GHz
		GAGQG	<-20dB to 6.9 GHz

Table 2 - Differential Connector System Performance			
Case 1 = Short Row; Case 2 = Long Row			
Case	Test Parameter	Configuration	
1	Insertion Loss	GSSG	3dB@ 7 GHz
	Return Loss	GSSG	>10dB to 1.2 GHz
	Near-End Crosstalk	GAAQQG	<-20dB to 2 GHz
		GAAGQQG	<-20dB to 20 GHz
		Xrow, GAAG to GQQG	<-20dB to 20 GHz
	Far-End Crosstalk	GAAQQG	<-20dB to 20 GHz
		GAAGQQG	<-20dB to 20 GHz
Xrow, GAAG to GQQG		<-20dB to 20 GHz	
2	Insertion Loss	GSSG	3dB@ 4.7 GHz
	Return Loss	GSSG	>10dB to 0.8 GHz
	Near-End Crosstalk	GAAQQG	<-20dB to 1.5 GHz
		GAAGQQG	<-20dB to 20 GHz
	Far-End Crosstalk	GAAQQG	<-20dB to 7.4 GHz
		GAAGQQG	<-20dB to 20 GHz



Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Bandwidth Chart – Single-Ended & Differential Insertion Loss

Case 1 = Short Row; Case 2 = Long Row

QFS-RA/QMS-RA Connector Series




Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle


Time Domain Data Summary

Table 3 - Single-Ended Impedance (Ω)						
Case 1 = Short Row; Case 2 = Long Row						
Case	Signal Rise-time	30ps	50ps	100ps	250ps	500ps
1	Maximum Impedance	55.7	52.1	51.0	50.6	50.4
	Minimum Impedance	36.0	38.4	42.9	45.3	46.5
2	Maximum Impedance	54.9	51.5	50.7	50.6	50.5
	Minimum Impedance	35.6	36.7	38.8	42.1	44.5

Single-Ended Impedance - Case 1, Short Row



Single-Ended Impedance - Case 2, Long Row




Series: QMS-RA/QFS-RA


Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Table 4 - Differential Impedance (Ω)						
Case 1 = Short Row; Case 2 = Long Row						
Case	Signal Rise-time	30ps	50ps	100ps	250ps	500ps
1	Maximum Impedance	100.5	100.5	100.4	100.3	100.3
	Minimum Impedance	51.8	56.8	66.6	73.4	82.5
2	Maximum Impedance	101.2	101.2	101.1	100.8	100.7
	Minimum Impedance	50.8	52.2	57.2	65.8	76.1

Differential Impedance - Case 1, Short Row



Differential Impedance - Case 2, Long Row



Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Table 5 - Single-Ended Crosstalk (%)							
Case 1 = Short Row; Case 2 = Long Row							
Case	Input(tr)		30ps	50ps	100ps	250ps	500ps
1	NEXT	GAQG	21.53	20.65	19.40	13.08	7.48
		GAGQG	2.17	1.90	1.63	1.06	0.63
		Xrow	0.28	0.16	<0.1	<0.1	<0.1
	FEXT	GAQG	6.14	2.54	0.65	0.13	0.13
		GAGQG	2.21	1.04	0.34	<0.1	<0.1
		Xrow	0.15	0.14	0.12	<0.1	<0.1
2	NEXT	GAQG	21.90	21.44	20.40	17.16	10.95
		GAGQG	2.07	1.89	1.59	1.14	0.73
	FEXT	GAQG	2.21	1.04	0.34	<0.1	<0.1
		GAGQG	1.43	1.10	0.62	0.22	<0.1

Table 6 - Differential Crosstalk (%)							
Case 1 = Short Row; Case 2 = Long Row							
Case	Input(tr)		30ps	50ps	100ps	250ps	500ps
1	NEXT	GAAQQG	6.52	6.24	5.84	4.14	2.47
		GAAGQQG	0.41	0.38	0.30	0.20	0.12
		Xrow	<0.1	<0.1	<0.1	<0.1	<0.1
	FEXT	GAAQQG	2.95	2.06	1.51	1.06	0.61
		GAAGQQG	0.28	0.12	0.10	<0.1	<0.1
		Xrow	<0.1	<0.1	<0.1	<0.1	<0.1
2	NEXT	GAAQQG	6.92	6.58	6.18	5.35	3.65
		GAAGQQG	0.43	0.38	0.30	0.20	0.13
	FEXT	GAAQQG	4.10	3.37	2.33	1.76	1.20
		GAAGQQG	0.50	0.30	0.16	<0.1	<0.1

Table 7 - Propagation Delay (Mated Connector)		
Case 1 = Short Row; Case 2 = Long Row		
Case 1	Single-Ended	95 ps
	Differential	89 ps
Case 2	Single-Ended	141 ps
	Differential	129 ps

Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Characterization Details

This report presents data that characterizes the signal integrity response of a connector pair in a controlled printed circuit board (PCB) environment. All efforts are made to reveal typical best-case responses inherent to the system under test (SUT).

In this report, the SUT includes the connector pair and footprint effects on a typical multi-layer PCB. PCB effects (trace loss) are de-embedded from test data. Board related effects, such as pad-to-ground capacitance, are included in the data presented in this report.

Additionally, intermediate test signal connections can mask the connector's true performance. Such connection effects are minimized by using high performance test cables and adapters. Where appropriate, calibration and de-embedding routines are also used to reduce residual effects.

Differential and Single-Ended Data

Most Samtec connectors can be used successfully in both differential and single-ended applications. However, electrical performance will differ depending on the signal drive type. In this report, data is presented for both differentially and single-ended driven scenarios.

Connector Signal to Ground Ratio

Samtec connectors are most often designed for generic applications and can be implemented using various signal and ground pin assignments. In high-speed systems, provisions must be made in the interconnect for signal return currents. Such paths are often referred to as "ground". In some connectors, a ground plane or blade, or an outer shield, is used as the signal return, while in others, connector pins are used as signal returns. Various combinations of signal pins, ground blades, and shields can also be utilized. Electrical performance can vary significantly depending upon the number and location of ground pins.

In general, the more pins dedicated to ground, the better electrical performance will be. However, dedicating pins to ground reduces signal density of a connector. Therefore, care must be taken when choosing signal/ground ratios in cost or density-sensitive applications.

Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

For this connector, the following configurations were evaluated:

Single-Ended Impedance:

- GSG (Ground-Signal-Ground)

Single-Ended Crosstalk:

- Electrical “worst case”: GAQG (Ground-Active-Quiet-Ground)
- Electrical “best case”: GAGQG (Ground-Active-Ground-Quiet-Ground)
- Across row: “xrow case”: GAG to GQG (from one row of terminals to the other row)

Differential Impedance:

- GSSG (Ground-positive Signal-negative Signal-Ground)

Differential Crosstalk:

- Electrical “worst case”: GAAQQG (Ground-Active-Active-Quiet-Quiet-Ground)
- Electrical “best case”: GAAGQQG (Ground-Active-Active-Ground-Quiet-Quiet-Ground)
- Across row: “xrow case”: GAAG to GQQG (from one row of terminals to the other row)

In all cases in this report, the center blade of the connector was grounded to the PCB. Only one single-ended signal or differential pair was driven for crosstalk measurements.

Other configurations can be evaluated upon request. Please contact sig@samtec.com for more information.

In a real system environment, active signals might be located at the outer edges of the signal contacts of concern, as opposed to the ground signals utilized in laboratory testing. For example, in a single-ended system, a pin-out of “SSSS”, or four adjacent single ended signals might be encountered as opposed to the “GSG” and “GSSG” configurations tested in the laboratory. Electrical characteristics in such applications could vary slightly from laboratory results. However, in most applications, performance can safely be considered equivalent.

Signal Edge Speed (Rise Time):

In pulse signaling applications, the perceived performance of the interconnect can vary significantly depending on the edge rate or rise time of the exciting signal. For this report, the fastest rise time used was 30 ps. Generally, this should demonstrate worst-case performance.

Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

In many systems, the signal edge rate will be significantly slower at the connector than at the driver launch point. To estimate interconnect performance at other edge rates, data is provided for several rise times between 30ps and 500ps.

For this report, measured rise times were at 10%-90% signal levels.

Frequency Domain Data

Frequency Domain parameters are helpful in evaluating the connector system's signal loss and crosstalk characteristics across a range of sinusoidal frequencies. In this report, parameters presented in the Frequency Domain are Insertion Loss, Return Loss, and Near-End and Far-End Crosstalk. Other parameters or formats, such as VSWR or S-Parameters, may be available upon request. Please contact our Signal Integrity Group at sig@samtec.com for more information.

Frequency performance characteristics for the SUT are generated directly from network analyzer measurements.

Time Domain Data

Time Domain parameters indicate Impedance mismatch versus length, signal propagation time, and crosstalk in a pulsed signal environment. The measured S-Parameters from the network analyzer are post-processed using Agilent Advanced Design System to obtain the time domain response. Time Domain procedure is provided in [Appendix E](#) of this report. Parameters or formats not included in this report may be available upon request. Please contact our Signal Integrity Group at sig@samtec.com for more information.

In this report, propagation delay is defined as the signal propagation time through the connector and connector footprint. It includes 10 mils of PCB trace on the QFS and QMS connector side each. Delay is measured at 100 picoseconds signal rise time. Delay is calculated as the difference in time measured between the 50% amplitude levels of the input and output pulses.

Crosstalk or coupled noise data is provided for various signal configurations. All measurements are single disturber. Crosstalk is calculated as a ratio of the input line voltage to the coupled line voltage. The input line is sometimes described as the active or drive line. The coupled line is sometimes described as the quiet or victim line. Crosstalk ratio is tabulated in this report as a percentage. Measurements are made at both the near-end and far-end of the SUT.

Data for other configurations may be available. Please contact our Signal Integrity Group at sig@samtec.com for further information.

Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

As a rule of thumb, 10% crosstalk levels are often used as a general first pass limit for determining acceptable interconnect performance. However, modern system crosstalk tolerance can vary greatly. For advice on connector suitability for specific applications, please contact our Signal Integrity Group at sig@samtec.com.

Additional information concerning test conditions and procedures is located in the appendices of this report. Further information may be obtained by contacting our Signal Integrity Group at sig@samtec.com.


Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Appendix A – Frequency Domain Response Graphs


Single-Ended Application – Insertion Loss

Case 1 = Short Row; Case 2 = Long Row



Single-Ended Application – Return Loss

Case 1 = Short Row; Case 2 = Long Row




Series: QMS-RA/QFS-RA


Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Single-Ended Application – NEXT Configurations

Case 1 (Short Row)



Case 2 (Long Row)




Series: QMS-RA/QFS-RA


Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Single-Ended Application – FEXT Configurations

Case 1 (Short Row)



Case 2 (Long Row)




Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle


Differential Application – Insertion Loss

Case 1 = Short Row; Case 2 = Long Row



Differential Application – Return Loss

Case 1 = Short Row; Case 2 = Long Row




Series: QMS-RA/QFS-RA


Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Differential Application – NEXT Configurations

Case 1 (Short Row)



Case 2 (Long Row)




Series: QMS-RA/QFS-RA


Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Differential Application – FEXT Configurations

Case 1 (Short Row)



Case 2 (Long Row)




Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Appendix B – Time Domain Response Graphs

Single-Ended Application – Input Pulse




Series: QMS-RA/QFS-RA


Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Single-Ended Application – Impedance

Case 1 (Short Row)



Case 2 (Long Row)




Series: QMS-RA/QFS-RA


Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Single-Ended Application – Propagation Delay

Case 1 (Short Row)



Case 2 (Long Row)




Series: QMS-RA/QFS-RA


Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Single-Ended Application – NEXT, Worst Case Configuration

Case 1 (Short Row)



Case 2 (Long Row)




Series: QMS-RA/QFS-RA


Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Single-Ended Application – FEXT, Worst Case Configuration

Case 1 (Short Row)



Case 2 (Long Row)




Series: QMS-RA/QFS-RA


Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Single-Ended Application – NEXT, Best Case Configuration

Case 1 (Short Row)



Case 2 (Long Row)




Series: QMS-RA/QFS-RA


Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Single-Ended Application – FEXT, Best Case Configuration

Case 1 (Short Row)




Case 2 (Long Row)




Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Single-Ended Application – NEXT, Across Row Configuration




Single-Ended Application – FEXT, Across Row Configuration



Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Differential Application – Input Pulse




Series: QMS-RA/QFS-RA


Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Differential Application – Impedance

Case 1 (Short Row)



Case 2 (Long Row)




Series: QMS-RA/QFS-RA


Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Differential Application – Propagation Delay

Case 1 (Short Row)



Case 2 (Long Row)




Series: QMS-RA/QFS-RA


Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Differential Application – NEXT, Worst Case Configuration

Case 1 (Short Row)



Case 2 (Long Row)




Series: QMS-RA/QFS-RA


Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Differential Application – FEXT, Worst Case Configuration

Case 1 (Short Row)



Case 2 (Long Row)




Series: QMS-RA/QFS-RA


Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Differential Application – NEXT, Best Case Configuration

Case 1 (Short Row)



Case 2 (Long Row)




Series: QMS-RA/QFS-RA


Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Differential Application – FEXT, Best Case Configuration

Case 1 (Short Row)




Case 2 (Long Row)




Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Differential Application – NEXT, Across Row Case Configuration



Differential Application – FEXT, Across Row Case Configuration



Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Appendix C – Product and Test System Descriptions

Product Description


Product test samples are the right angle QFS-RA/QMS-RA series connectors. The part numbers are QFS-052-01-SL-D-RA and QMS-052-01-SL-D-RA. Both the right angle style connectors are PCB surface mount products. The right angle surface mount design forces the top row terminals to have a longer electrical length than those of the bottom row; hence, the electrical characteristics between the short row and long row will differentiate. When mated the connectors locate on a horizontal. Each connector structure consists of two rows of 52 contact terminals. Terminal centerlines are evenly spaced at a 0.635mm (0.025") pitch. A photo of the test articles mounted to SI test boards is shown below.

Test System Description

The test fixtures are composed of four-layer FR-4 material with 50Ω signal trace and pad configurations designed for the electrical characterization of Samtec high speed connector products. A PCB mount SMA connector is used to interface the VNA test cables to the test fixtures. Optimization of the SMA launch was performed using full wave simulation tools to minimize reflections. Six test fixtures are specific to the QFS-RA/QMS-RA series connector set and identified by part numbers PCB-103658-TST-01A and D through PCB-103658-TST-03A and D. Calibration standards specific to the QFS-RA/QMS-RA series is located on the calibration boards PCB-103658-TST-04. To keep trace lengths short, three different test board sets were required to access the necessary signal pins.

PCB-103658-TST-XX Test Fixtures

Shown below is a photograph of the one of the three test board sets.




Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

PCB-103658-TST-XX PCB Layout Panel

Artwork of the PCB design is shown below.



PCB Fixtures

The test fixtures used are as follows:

PCB-103658-TST-01A – QMS-RA Series Test Board for differential worst-case crosstalk of long pin and short pin

PCB-103658-TST-01D – QFS-RA Series Test Board for differential worst-case crosstalk of long pin and short pin

PCB-103658-TST-02A – QMS-RA Series Test Board for differential best-case crosstalk of long pin and short pin




PCB-103658-TST-02D – QFS-RA Series Test Board for differential best-case crosstalk of long pin and short pin

PCB-103658-TST-03A – QMS-RA Series Test Board for single-ended best-case crosstalk, single-ended worst-case crosstalk, single-ended across row crosstalk and differential across row crosstalk

PCB-103658-TST-03D – QFS-RA Series Test Board for single-ended best-case crosstalk, single-ended worst-case crosstalk, single-ended across row crosstalk and differential across row crosstalk

Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle




Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Calibration Board

Test fixture losses and test point reflections were removed from the data by use of TRL calibration. The calibration board is shown below. Prior to making any measurements, the calibration board is characterized to obtain parameters required to define the calibration kit. Once a calibration kit is defined, calibration using the standards on the calibration board can be performed. Finally, the device can be measured and the test board effects are automatically removed.



- Thru line – 2980 mils
- Open Reflect – 1490 mils
- Line 1 – 6370 mils
- Line 2 – 3660 mils
- Line 3 – 3120 mils
- Match – 1490 mils


Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

All traces on the test boards are length matched to 1.5" measured from the edge of the pad to the SMA. The TRL calibration effectively removes 1.49" of test board trace effects. This means that 10 mils of test board trace length effects are included in the both sides of test boards in the measurement. The S-Parameter measurement includes:

- A- The QFS-RA/QMS-RA Series connector set
- B- Test board vias, pads (footprint effects) for the QFS-RA connector side.
- C- 10 mils of 9.5 mil wide microstrip trace.
- D- Test board vias, pads (footprint effects) for the QMS-RA connector side.
- E- 10 mils of 9.5 mil wide microstrip trace.

The figure below shows the location of the measurement reference plane.



Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Appendix D – Test and Measurement Setup

The test instrument is the Agilent N5230C PNA-L network analyzer. Frequency domain data and graphs are obtained directly from the instrument. Post-processed time domain data and graphs are generated using convolution algorithms within Agilent ADS. The network analyzer is configured as follows:

Start Frequency – 300 KHz


Stop Frequency – 20 GHz

Number of points -1601

IFBW – 1 KHz

With these settings, the measurement time is approximately 20 seconds.

N5230C Measurement Setup



Test Instruments

<u>QTY</u>	<u>Description</u>
1	Agilent N5230C PNA-L Network Analyzer (300 KHz to 20 GHz)
1	Agilent N4433A ecal module (300 KHz to 20 GHz)

Test Cables & Adapters

<u>QTY</u>	<u>Description</u>
4	Gore OWD01D02039-4 (DC-50 GHz)

Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Appendix E - Frequency and Time Domain Measurements

Frequency (S-Parameter) Domain Procedures

The quality of any data taken with a network analyzer is directly related to the quality of the calibration standards and the use of proper test procedures. For this reason, extreme care is taken in the design of the LRM calibration standards, the SI test boards, and the selection of the PCB vendor.

The measurement process begins with a measurement of the LRM calibration standards. A coaxial SOLT calibration is performed using an N4433A ecal module. This measurement is required in order to obtain precise values of the line standard offset delay and frequency bandwidths. Measurements of the reflect and 2x through line standard can be used to determine the maximum frequency for which the calibration standards are valid. For the QFS-RA/QMS-RA Series test boards, this is greater than 20 GHz.

From the LRM calibration standard measurements, a user defined calibration kit is developed and stored in the network analyzer. Calibration is then performed on all 4 ports following the calibration wizard within the Agilent N5230C. This calibration is saved and can be recalled at any time. Calibration takes roughly 30 minutes to perform.

Time Domain Procedures

Mathematically, Frequency Domain data can be transformed to obtain a Time Domain response. Perfect transformation requires Frequency Domain data from DC to infinity Hz. Fortunately, a very accurate Time Domain response can be obtained with bandwidth-limited data, such as measured with modern network analyzer.

The Time Domain responses were generated using Agilent ADS 2009 update 1. This tool has a transient convolution simulator, which can generate a Time Domain response directly from measured S-Parameters. An example of a similar methodology is provided in the Samtec Technical Note on domain transformation.

[http://www.samtec.com/Technical_Library/reference/articles/pdfs/tech-note_using-PLTS-for-time-domain-data_web.pdf](http://www.samtec.com/Technical_Library/reference/articles/pdfs/tech-note_using_PLTS-for-time-domain-data_web.pdf)

Impedance (TDR)

A step pulse is applied to the touchstone model of the connector and the reflected voltage is monitored. The reflected voltage is converted to a reflection coefficient and then transformed into an impedance profile. All ports of the Touchstone model are terminated in 50 ohms.

Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Propagation Delay (TDT)

The Propagation Delay is a measure of the Time Domain delay through the connector and footprint. A step pulse is applied to the touchstone model of the connector and the transmitted voltage is monitored. The same pulse is also applied to a reference channel with zero loss, and the Time Domain pulses are plotted on the same graph. The difference in time, measured at the 50% point of the step voltage is the propagation delay.

Near-End Crosstalk (TDT) & Far End Crosstalk (TDT)

A step pulse is applied to the touchstone model of the connector and the coupled voltage is monitored. The amplitude of the peak-coupled voltage is recorded and reported as a percentage of the input pulse.

Series: QMS-RA/QFS-RA

Description: Board-to-Board, 0.635mm Pitch, Right Angle to Right Angle

Appendix F – Glossary of Terms

ADS – Advanced Design Systems

BC – Best Case crosstalk configuration

DUT – Device under test, term used for TDA IConnect & Propagation Delay waveforms

FD – Frequency domain

FEXT – Far-End Crosstalk

GSG – Ground–Signal–Ground; geometric configuration

GSSG - Ground–Signal–Signal–Ground; geometric configuration

HDV – High Density Vertical

NEXT – Near-End Crosstalk

OV – Optimal Vertical

OH – Optimal Horizontal

PCB – Printed Circuit Board

PPO – Pin Population Option

SE – Single-Ended

SI – Signal Integrity

SUT – System Under Test

S – Static (independent of PCB ground)

SOLT – acronym used to define Short, Open, Load & Thru Calibration Standards

TD – Time Domain

TDA – Time Domain Analysis

TDR – Time Domain Reflectometry

TDT – Time Domain Transmission

WC – Worst Case crosstalk configuration

Z – Impedance (expressed in ohms)