




Project Number:		Tracking Code: TC0631--1126	
Requested by: John Reid		Date: 8/3/2006	Product Rev: 08/03/2006
Part #: 6QDP-016-06.0-STR-TTL-1		Lot #: 06/26/2006	Tech: Troy Cook/Tony Wagoner Eng: Dave Scopelliti
Part description: 6QDP			Qty to test: 60
Test Start: 09/06/2006	Test Completed: 9/27/2006		



6QDP DVT Report

**Mated with: QFS-016-01-X-D-DP-A
QMS-016-11-X-D-DP-A**

CERTIFICATION

All instruments and measuring equipment were calibrated to National Institute for Standards and Technology (NIST) traceable standards according to ISO 10012-1 and ANSI/NCSL 2540-1, as applicable.

All contents contained herein are the property of Samtec. No portion of this report, in part or in full shall be reproduced without prior written approval of Samtec.

SCOPE


To perform the following tests: DVT same as 6QDPS

APPLICABLE DOCUMENTS

Standards: EIA Publication 364

TEST SAMPLES AND PREPARATION

- 1) All materials were manufactured in accordance with the applicable product specification.
- 2) All test samples were identified and encoded to maintain traceability throughout the test sequences.
- 3) After soldering, the parts to be used for LLCR and DWV/IR testing were cleaned according to TLWI-0001.
- 4) Either an automated cleaning procedure or an ultrasonic cleaning procedure may be used.
- 5) The automated procedure is used with aqueous compatible soldering materials.
- 6) Parts not intended for testing LLCR and DWV/IR are visually inspected and cleaned if necessary.
- 7) Any additional preparation will be noted in the individual test sequences.
- 8) Solder Information: Lead Free
- 9) Re-Flow Time/Temp: See accompanying profile.
- 10) Internal Test PCBs used: PCB-100591-TST-XX

OVEN PROFILE (Soldering Parts to Test Boards)

FLOWCHARTS**Current Carrying Capacity**

TEST STEP	GROUP 1 Both Cables Powered 6 Adjacent Contacts in both cables
01	CCC

Tabulate calculated current at RT, 60° C, 75° C and 80° C
after derating 20% and based on 105° C
CCC, Temp rise = EIA-364-70

IR

TEST STEP	GROUP 1A TOP Cable, Conductor - to - Conductor	GROUP 1B BOTTOM Cable, Conductor to - Conductor
01	IR	IR
02	Data Review	Data Review
03	Thermal Aging	Thermal Aging
04	IR	IR
05	Data Review	Data Review
06	Humidity	Humidity
07	IR	IR

Thermal Aging = EIA-364-17, Test Condition 4, 105 deg C;

Time Condition 'B' (250 hours)

Humidity =EIA-364-31, Test Condition B (240 Hours)

and Method III (+25° C to +65° C @ 90%RH to 98% RH)
delete steps 7a and 7b

FLOWCHARTS Continued**DWV**

TEST STEP	GROUP 1 TOP Cable, Conductor - to - Conductor Ambient	GROUP 2 BOTTOM Cable, Conductor - to - Conductor Ambient	GROUP 3 TOP Cable, Conductor - to - Conductor Thermal	GROUP 4 BOTTOM Cable, Conductor - to - Conductor Thermal	GROUP 5 TOP Cable, Conductor - to - Conductor Humidity	GROUP 6 BOTTOM Cable, Conductor - to - Conductor Humidity
01	DWV/Working Voltage	DWV/Working Voltage	Thermal Aging	Thermal Aging	Humidity	Humidity
02			DWV/Working Voltage	DWV/Working Voltage	DWV/Working Voltage	DWV/Working Voltage

Thermal Aging = EIA-364-17, Test Condition 4, 105 deg C;

Time Condition 'B' (250 hours)

Humidity = EIA-364-31, Test Condition B (240 Hours)

and Method III (+25 ° C to +65 ° C @ 90%RH to 98% RH)

delete steps 7a and 7b

Connector Pull

TEST STEP	GROUP 1	GROUP 2
	DV SIG 0°	DV SIG 90°
01	Pull test, Continuity	Pull test, Continuity

**Secure both cables in the center
Monitor continuity and pull
record forces when continuity fails.**

FLOWCHARTS Continued**Resistance, SIG Contiinity**

TEST STEP	GROUP 1 DV End 90° SIG	GROUP 1A DV End 35° SIG
01	Resistance	Resistance
02	1000 Cycles	1000 Cycles
03	Resistance	Resistance
04	Data Review	Data Review
05	2000 Cycles	2000 Cycles
06	Resistance	Resistance
07	Data Review	Data Review
08	3000 Cycles	3000 Cycles
09	Resistance	Resistance
10	Data Review	Data Review
11	4000 Cycles	4000 Cycles
12	Resistance	Resistance
13	Data Review	Data Review
14	5000 Cycles	5000 Cycles
15	Resistance	Resistance

ATTRIBUTE DEFINITIONS

The following is a brief, simplified description of attributes.

THERMAL:

- 1) EIA-364-17, *Temperature Life with or without Electrical Load Test Procedure for Electrical Connectors*.
- 2) Test Condition 4 at 105° C.
- 3) Test Time Condition B for 250 hours.
- 4) Connectors are sometimes mated and all samples are pre-conditioned at ambient.

HUMIDITY:

- 1) Reference document: EIA-364-31, *Humidity Test Procedure for Electrical Connectors*.
- 2) Test Condition B, 240 Hours.
- 3) Method III, +25° C to + 65° C, 90% to 98% Relative Humidity excluding sub-cycles 7a and 7b.
- 4) Connectors are sometimes mated and all samples are pre-conditioned at ambient.

TEMPERATURE RISE (Current Carrying Capacity, CCC):

- 1) EIA-364-70, *Temperature Rise versus Current Test Procedure for Electrical Connectors and Sockets*.
- 2) When current passes through a contact, the temperature of the contact increases as a result of I^2R (resistive) heating.
- 3) The number of contacts being investigated plays a significant part in power dissipation and therefore temperature rise.
- 4) The size of the temperature probe can affect the measured temperature.
- 5) Copper traces on PC boards will contribute to temperature rise:
 - a. Self heating (resistive)
 - b. Reduction in heat sink capacity affecting the heated contacts
- 6) A de-rating curve, usually 20%, is calculated.
- 7) Calculated de-rated currents at three temperature points are reported:
 - a. Ambient
 - b. 60° C
 - c. 75° C
 - d. 80° C
- 8) Typically, neighboring contacts (in close proximity to maximize heat build up) are energized.
- 9) The thermocouple (or temperature measuring probe) will be positioned at a location to sense the maximum temperature in the vicinity of the heat generation area.
- 10) A computer program, *TR 803.exe*, ensures accurate stability for data acquisition.
- 11) Hook-up wire cross section is larger than the cross section of any connector leads/PC board traces, jumpers, etc.
- 12) Hook-up wire length is longer than the minimum specified in the referencing standard.

INSULATION RESISTANCE (IR):

To determine the resistance of insulation materials to leakage of current through or on the surface of these materials when a DC potential is applied.

- 1) PROCEDURE:
 - a. Reference document: EIA-364-21, *Insulation Resistance Test Procedure for Electrical Connectors*.
 - b. Test Conditions:
 - i. Between Adjacent Contacts
 - ii. Electrification Time 2.0 minutes
 - iii. Test Voltage (500 VDC) corresponds to calibration settings for measuring resistances.
- 2) MEASUREMENTS:
- 3) When the specified test voltage is applied (VDC), the insulation resistance shall not be less than 5000 megohms.

DIELECTRIC WITHSTANDING VOLTAGE (DWV):

To determine if the sockets can operate at its rated voltage and withstand momentary over potentials due to switching, surges, and other similar phenomenon. Separate samples are used to evaluate the effect of environmental stresses so not to influence the readings from arcing that occurs during the measurement process.

- 1) PROCEDURE:
 - a. Reference document: EIA-364-20, *Withstanding Voltage Test Procedure for Electrical Connectors*.
 - b. Test Conditions:
 - i. Between Adjacent Contacts
 - ii. Rate of Application 500 V/Sec
 - iii. Test Voltage (VAC) until breakdown occurs
- 2) MEASUREMENTS/CALCULATIONS
 - a. The breakdown voltage shall be measured and recorded.
 - b. The dielectric withstanding voltage shall be recorded as 75% of the minimum breakdown voltage.
 - c. The working voltage shall be recorded as one-third (1/3) of the dielectric withstanding voltage (one-fourth of the breakdown voltage).

SUPPLEMENTAL TESTS**CONNECTOR PULL:**

- 1) Secure cable near center and pull on connector
 - a. At 90°, right angle to cable
 - b. At 0°, in-line with cable




Fig. 1
(Typical set-up, actual part not depicted.)
0° Connector pull, notice the electrical continuity hook-up wires.

CABLE DURABILITY:

- 1) Oscillate and monitor electrical continuity for open circuit indication.
 - a. $\pm 35^\circ$ Pendulum Mode, bend up to 5,000 cycles with 8 oz. load on cable end.




Fig. 2
(Typical set-up, actual part not depicted.)

- b. $\pm 90^\circ$ Flex Mode, bend up to 5,000 cycles with 8 oz. load on cable end.




Fig. 3
(Typical set-up, actual part not depicted.)

RESULTS

Temperature Rise, CCC at a 20% de-rating

- CCC for a 30°C Temperature Rise-----0.7 A per contact with 6 adjacent contacts powered (both cables)

Insulation Resistance minimums, IR

- Initial
 - Top Cable ----- 50,000 Meg Ω ----- Pass
 - Bottom Cable ----- 50,000 Meg Ω
- Thermal
 - Top Cable ----- 100,000 Meg Ω
 - Bottom Cable ----- 100,000 Meg Ω
- Humidity
 - Top Cable ----- 25,000 Meg Ω
 - Bottom Cable ----- 8,000 Meg Ω

Dielectric Withstanding Voltage minimums, DWV

- Initial
 - Breakdown
 - Top Cable-----860 VAC
 - Bottom Cable -----780 VAC
 - DWV
 - Top Cable-----645 VAC
 - Bottom Cable -----585 VAC
 - Working voltage
 - Top Cable-----215 VAC
 - Bottom Cable -----195 VAC
- Thermal
 - Breakdown
 - Top Cable-----1,020 VAC
 - Bottom Cable -----960 VAC
 - DWV
 - Top Cable-----765 VAC
 - Bottom Cable -----720 VAC
 - Working voltage
 - Top Cable-----255 VAC
 - Bottom Cable -----240 VAC
- Humidity
 - Breakdown
 - Top Cable-----860 VAC
 - Bottom Cable -----880 VAC
 - DWV
 - Top Cable-----645 VAC
 - Bottom Cable -----660 VAC
 - Working voltage
 - Top Cable-----215 VAC
 - Bottom Cable -----220 VAC

SUPPLEMENTAL TESTING**Supplemental – Connector/Cable Pull**

- 0° ----- 144.75 lbs min
- 90° ----- 110.49 lbs min


Supplemental – Cable Bend 25,000 Cycles

- $\pm 35^\circ$ Pendulum Mode ----- No Electrical Failures
- $\pm 90^\circ$ Flex Mode ----- 2 of 5 Cables failed at 4,563 Cycles

DATA SUMMARIES

TEMPERATURE RISE (Current Carrying Capacity, CCC):

- 1) High quality thermocouples whose temperature slopes track one another were used for temperature monitoring.
- 2) The thermocouples were placed at a location to sense the maximum temperature generated during testing.
- 3) Temperature readings recorded are those for which three successive readings, 15 minutes apart, differ less than 1° C (computer controlled data acquisition).
- 4) Adjacent contacts were powered:
 - a. Linear configuration with SIX adjacent conductors/contacts powered



DATA SUMMARIES Continued**INSULATION RESISTANCE (IR):**

	Initial, Meg Ohms		Thermal, Meg Ohms		Humidity, Meg Ohms	
	Top	Bottom	Top	Bottom	Top	Bottom
	<u>Insulation Resistance</u>	<u>Insulation Resistance</u>	<u>Insulation Resistance</u>	<u>Insulation Resistance</u>	<u>Insulation Resistance</u>	<u>Insulation Resistance</u>
Average	50000	50000	100000	100000	25000	9000
Min	50000	50000	100000	100000	25000	8000
Max	50000	50000	100000	100000	25000	10000

DIELECTRIC WITHSTANDING VOLTAGE (DWV):

	Initial, VAC Top			Initial, VAC Bottom		
	<u>Breakdown Voltage</u>	<u>DWV</u>	<u>Working Voltage</u>	<u>Breakdown Voltage</u>	<u>DWV</u>	<u>Working Voltage</u>
Average	983	738	246	930	698	233
Min	860	645	215	780	585	195
Max	1120	840	280	1060	795	265
	Thermal, VAC Top			Thermal, VAC Bottom		
	<u>Breakdown Voltage</u>	<u>DWV</u>	<u>Working Voltage</u>	<u>Breakdown Voltage</u>	<u>DWV</u>	<u>Working Voltage</u>
Average	1070	803	268	1010	758	253
Min	1020	765	255	960	720	240
Max	1120	840	280	1060	795	265
	Humidity, VAC Top			Humidity, VAC Bottom		
	<u>Breakdown Voltage</u>	<u>DWV</u>	<u>Working Voltage</u>	<u>Breakdown Voltage</u>	<u>DWV</u>	<u>Working Voltage</u>
Average	900	675	225	910	683	228
Min	860	645	215	880	660	220
Max	940	705	235	940	705	235

DATA SUMMARIES Continued**SUPPLEMENTAL TESTS****CONNECTOR/CABLE PULL:**

	0 Deg.	90 Deg.
Pull DV	Force (Lbs)	Force (Lbs)
Minimum	144.75	110.49
Maximum	273.61	265.33
Average	236.5	145.2

CABLE BEND:

35 Deg. Flex Test - Resistance, Ohms						
	Initial	1000Cycles	2000 Cycles	3000 Cycles	4000 Cycles	5000 Cycles
Avg	3.4104	3.4116	3.3946	3.3946	3.3946	3.4370
Min	2.7780	2.7800	2.7910	2.7910	2.7910	2.9400
Max	3.9880	3.9810	3.8700	3.8700	3.8700	3.8200
St. Dev.	0.4294	0.4262	0.3866	0.3866	0.3866	0.3163
Count	5	5	5	5	5	5

90 Deg. Flex Test - Resistance, Ohms						
	Initial	1000Cycles	2000 Cycles	3000 Cycles	4000 Cycles	5000 Cycles
Avg	3.3612	3.3736	3.3630	3.3674	3.5125	3.7270
Min	2.8670	2.9100	2.8680	2.8690	3.1400	3.6660
Max	3.6330	3.6320	3.6310	3.6370	3.6500	3.7880
St. Dev.	0.2894	0.2724	0.2891	0.2913	0.2490	0.0863
Count	5	5	5	5	4	2

DATA**INSULATION RESISTANCE (IR):**

Sample#	Initial, Meg Ohms		Thermal, Meg Ohms		Humidity, Meg Ohms	
	Top	Bottom	Top	Bottom	Top	Bottom
	<u>Insulation Resistance</u>	<u>Insulation Resistance</u>	<u>Insulation Resistance</u>	<u>Insulation Resistance</u>	<u>Insulation Resistance</u>	<u>Insulation Resistance</u>
1	50000	50000	100000	100000	25000	10000
2	50000	50000	100000	100000	25000	8000

DIELECTRIC WITHSTANDING VOLTAGE (DWV):

Sample #	Initial, VAC Top			Initial, VAC Bottom		
	<u>Breakdown Voltage</u>	<u>DWV</u>	<u>Working Voltage</u>	<u>Breakdown Voltage</u>	<u>DWV</u>	<u>Working Voltage</u>
1	1000	750	250	960	720	240
2	960	720	240	780	585	195

Sample #	Thermal, VAC Top			Thermal, VAC Bottom		
	<u>Breakdown Voltage</u>	<u>DWV</u>	<u>Working Voltage</u>	<u>Breakdown Voltage</u>	<u>DWV</u>	<u>Working Voltage</u>
1	1020	765	255	1060	795	265
2	1120	840	280	960	720	240

Sample #	Humidity, VAC Top			Humidity, VAC Bottom		
	<u>Breakdown Voltage</u>	<u>DWV</u>	<u>Working Voltage</u>	<u>Breakdown Voltage</u>	<u>DWV</u>	<u>Working Voltage</u>
1	860	645	215	880	660	220
2	940	705	235	940	705	235

DATA Continued**SUPPLEMENTAL****CONNECTOR/CABLE PULL:**

	0 Deg.	90 Deg.
Sample#	Maximum Force (Lbs)	Maximum Force (Lbs)
1	144.75	110.49
2	260.31	113.81
3	234.48	118.10
4	269.26	118.07
5	273.61	265.33

CABLE BEND:

Cable	Uses a 8 oz. Load					
	35 Deg. Flex Test - Resistance, Ohms					
	Initial	1000Cycles	2000 Cycles	3000 Cycles	4000 Cycles	5000 Cycles
1	3.4040	3.4100	3.4170	3.4170	3.4170	3.5120
2	3.4740	3.4700	3.4750	3.4750	3.4750	3.4630
3	2.7780	2.7800	2.7910	2.7910	2.7910	2.9400
4	3.9880	3.9810	3.8700	3.8700	3.8700	3.8200
5	3.4080	3.4170	3.4200	3.4200	3.4200	3.4500

Cable	Uses a 8 oz. Load					
	90 Deg. Flex Test - Resistance, Ohms					
	Initial	1000Cycles	2000 Cycles	3000 Cycles	4000 Cycles	5000 Cycles
1	3.4420	3.4380	3.4360	3.4440	Failed at 3434 Cycles	N/A
2	3.4470	3.4680	3.4530	3.4640	3.6100	Failed at 4563 Cycles
3	2.8670	2.9100	2.8680	2.8690	3.1400	Failed at 4565 Cycles
4	3.6330	3.6320	3.6310	3.6370	3.6500	3.6660
5	3.4170	3.4200	3.4270	3.4230	3.6500	3.7880

EQUIPMENT AND CALIBRATION SCHEDULES**Equipment #:** THL-02**Description:** Temperature/Humidity Chart Recorder**Manufacturer:** Dickson**Model:** THDX**Serial #:** 00120351**Accuracy:** Temp: +/- 1C; Humidity: +/-2% RH (0 - 60%) +/- 3% RH (61 - 95%).

... Last Cal: 06/16/06, Next Cal: 06/16/07

Equipment #: MO-01**Description:** Micro-Ohmeter**Manufacturer:** Keithley**Model:** 580**Serial #:** 0772740**Accuracy:** See Manual

... Last Cal: 05/12/06, Next Cal: 05/12/07

Equipment #: MO-03**Description:** Multimeter /Data Acquisition System**Manufacturer:** Keithley**Model:** 2700**Serial #:** 0791975**Accuracy:** See Manual

... Last Cal: 05/12/06, Next Cal: 05/12/07

Equipment #: MO-02**Description:** Multimeter /Data Acquisition System**Manufacturer:** Keithley**Model:** 2700**Serial #:** 0780546**Accuracy:** See Manual

... Last Cal: 05/12/06, Next Cal: 05/12/07

Equipment #: PS-01**Description:** System Power Supply**Manufacturer:** Hewlett Packard**Model:** HP 6033A**Serial #:** (HP) 3329A-07330**Accuracy:** See Manual

... Last Cal: 05/12/06, Next Cal: 05/12/07

Equipment #: TC090601-109/118**Description:** IC Thermocouple-109/118**Manufacturer:** Samtec**Model:****Serial #:** TC090601-109/118**Accuracy:** +/- 1 degree C

... Last Cal: , Next Cal:

Equipment #: HPM-01**Description:** Hipot Megommeter**Manufacturer:** Hipotronics**Model:** H306B-A**Serial #:** M9905004**Accuracy:** 2 % Full Scale Accuracy 2 % Full Scale Accuracy

... Last Cal: 5/12/06, Next Cal: 05/12/07

Equipment #: OV-03**Description:** Cascade Tek Forced Air Oven**Manufacturer:** Cascade Tek**Model:** TFO-5**Serial #:** 0500100**Accuracy:** Temp. Stability: +/- .1C/C change in ambient

... Last Cal: 05/12/06, Next Cal: 05/12/07

Equipment #: THC-01**Description:** Temperature/Humidity Chamber**Manufacturer:** Thermotron**Model:** SM-8-7800**Serial #:** 30676**Accuracy:** See Manual

... Last Cal: 8/18/2006, Next Cal: 8/18/2007

Equipment #: TCT-03**Description:** Dillon Quantrol TC2 Test Stand**Manufacturer:** Dillon Quantrol**Model:** TC2**Serial #:** 02-1033-03**Accuracy:** Speed Accuracy: +/- 5% of indicated speed; Displacement: +/- 5 micrometers.

... Last Cal: 5/12/06, Next Cal: 5/12/07

Equipment #: LC-2500N(icell)**Description:** 2500 N Load Cell for Dillon Quantrol**Manufacturer:** Dillon Quantrol**Model:** icell**Serial #:** 00120351**Accuracy:** .10% of capacity

... Last Cal: 6/13/06, Next Cal: 6/13/07

Equipment #: HDR - 01**Description:** HDR Flex Tester**Manufacturer:** Samtec Inc.**Model:** AT-1440-000**Serial #:** AT-1440-000**Accuracy:** N/A

... Last Cal: No Calibration Required, Next Cal: ...